

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P631509

Luminaire Tested: GWS-SA1F-827-U-T2R-W-HSS

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P631509  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-14)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA1F-827-U-T2R-W-HSS  
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II ROADWAY OPTICS WITH HOUSE SIDE SHIELD  
Light Source: (16) 2700K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4994.8 lumens  
Efficiency: N/A  
Efficacy: 74.3 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type II - Short  
BUG Rating: B0 - U0 - G1  
  
Input Watts (W): 67.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P631509  
 CATALOG NUMBER: GWS-SA1F-827-U-T2R-W-HSS

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 15 fc  
 Type II - Short - N/A

REPORT NUMBER: P631509  
CATALOG NUMBER: GWS-SA1F-827-U-T2R-W-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 76-Deg Lateral    - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P631509  
 CATALOG NUMBER: GWS-SA1F-827-U-T2R-W-HSS


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 276.2    | 0.0    | 276.2  |
|                    | % Fixture | 5.5      | 0.0    | 5.5    |
| <b>Street Side</b> | Lumens    | 4718.6   | 0.0    | 4718.6 |
|                    | % Fixture | 94.5     | 0.0    | 94.5   |
| <b>Total</b>       | Lumens    | 4994.8   | 0.0    | 4994.8 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 53.8   | 1.1       |
| 10°-20°   | 204.1  | 4.1       |
| 20°-30°   | 416.5  | 8.3       |
| 30°-40°   | 740.7  | 14.8      |
| 40°-50°   | 1094.9 | 21.9      |
| 50°-60°   | 1253.6 | 25.1      |
| 60°-70°   | 956.5  | 19.1      |
| 70°-80°   | 267.9  | 5.4       |
| 80°-90°   | 6.7    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 4994.8 | 100.0     |
| 0°-180°   | 4994.8 | 100.0     |

**Coefficient of Utilization**




REPORT NUMBER: P631509

CATALOG NUMBER: GWS-SA1F-827-U-T2R-W-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 595.6  | 11.9      |                         |      |         |
| FM (30°-60°)   | 2953.0 | 59.1      |                         |      |         |
| FH (60°-80°)   | 1163.7 | 23.3      |                         |      | G1/1800 |
| FVH (80°-90°)  | 6.4    | 0.1       |                         |      | G0/10   |
| BL (0°-30°)    | 78.8   | 1.6       | B0/110                  |      |         |
| BM (30°-60°)   | 136.3  | 2.7       | B0/220                  |      |         |
| BH (60°-80°)   | 60.7   | 1.2       | B0/110                  |      | G0/110  |
| BVH (80°-90°)  | 0.4    | 0.0       |                         |      | G0/10   |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B0-U0-G1**  
 Type II Short





REPORT NUMBER: P631509

CATALOG NUMBER: GWS-SA1F-827-U-T2R-W-HSS

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 76°    | 85°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 442.2  | 442.2  | 442.2  | 442.2  | 442.2  | 442.2  | 442.2  | 442.2  | 442.2  | 442.2  | 442.2  |
| 2.5°  | 681.5  | 691.7  | 683.8  | 670.4  | 644.7  | 619.8  | 587.9  | 543.9  | 508.8  | 504.4  | 471.5  |
| 5°    | 920.4  | 919.5  | 902.2  | 884.9  | 857.8  | 815.2  | 750.8  | 669.1  | 590.5  | 583.9  | 510.2  |
| 7.5°  | 1062.5 | 1063.8 | 1054.1 | 1040.7 | 1014.1 | 970.1  | 903.1  | 804.5  | 689.5  | 676.2  | 563.0  |
| 10°   | 1181.9 | 1181.5 | 1174.4 | 1168.2 | 1144.2 | 1114.9 | 1043.0 | 934.6  | 796.1  | 775.2  | 622.0  |
| 12.5° | 1271.6 | 1274.7 | 1278.3 | 1284.5 | 1274.3 | 1245.4 | 1177.5 | 1059.4 | 904.0  | 880.9  | 689.5  |
| 15°   | 1342.6 | 1343.5 | 1356.9 | 1380.8 | 1389.3 | 1374.2 | 1312.5 | 1180.1 | 1010.5 | 990.6  | 767.2  |
| 17.5° | 1364.0 | 1365.7 | 1388.4 | 1432.3 | 1476.7 | 1485.2 | 1438.6 | 1301.8 | 1115.3 | 1094.0 | 842.7  |
| 20°   | 1408.8 | 1412.8 | 1429.7 | 1468.3 | 1524.2 | 1569.5 | 1551.3 | 1424.8 | 1220.1 | 1192.1 | 920.0  |
| 22.5° | 1550.0 | 1552.2 | 1546.4 | 1551.3 | 1580.2 | 1632.6 | 1643.7 | 1543.8 | 1327.6 | 1297.8 | 1003.4 |
| 25°   | 1792.9 | 1793.8 | 1753.3 | 1715.2 | 1693.4 | 1703.2 | 1727.6 | 1653.4 | 1434.1 | 1404.8 | 1081.1 |
| 27.5° | 2045.1 | 2048.2 | 1999.8 | 1934.9 | 1857.2 | 1812.8 | 1805.7 | 1753.8 | 1541.6 | 1509.1 | 1157.9 |
| 30°   | 2282.6 | 2282.6 | 2231.5 | 2152.5 | 2048.6 | 1962.0 | 1911.0 | 1855.0 | 1656.6 | 1621.0 | 1236.5 |
| 32.5° | 2496.2 | 2494.4 | 2429.1 | 2343.4 | 2240.9 | 2145.8 | 2038.4 | 1960.7 | 1784.4 | 1744.9 | 1327.1 |
| 35°   | 2672.4 | 2668.0 | 2593.8 | 2511.7 | 2402.0 | 2331.4 | 2211.6 | 2074.4 | 1923.0 | 1883.4 | 1420.3 |
| 37.5° | 2805.6 | 2800.7 | 2732.8 | 2645.8 | 2544.1 | 2498.4 | 2398.0 | 2210.7 | 2069.0 | 2033.1 | 1523.8 |
| 40°   | 2878.0 | 2868.2 | 2821.2 | 2756.3 | 2671.1 | 2631.1 | 2589.4 | 2379.8 | 2240.9 | 2196.0 | 1645.9 |
| 42.5° | 2899.3 | 2887.8 | 2856.7 | 2826.5 | 2775.0 | 2743.5 | 2788.3 | 2570.7 | 2429.6 | 2390.9 | 1785.3 |
| 45°   | 2836.3 | 2829.6 | 2826.9 | 2848.7 | 2858.0 | 2866.9 | 2977.5 | 2782.1 | 2637.8 | 2608.5 | 1960.7 |
| 47.5° | 2684.4 | 2682.6 | 2706.2 | 2796.7 | 2895.3 | 2989.0 | 3183.0 | 3042.7 | 2907.7 | 2876.2 | 2205.8 |
| 50°   | 2403.8 | 2422.0 | 2487.7 | 2646.7 | 2843.8 | 3058.3 | 3375.3 | 3404.1 | 3344.6 | 3298.5 | 2525.5 |
| 52.5° | 1965.1 | 2000.2 | 2147.6 | 2389.2 | 2672.4 | 3038.7 | 3464.1 | 3693.6 | 3754.4 | 3706.5 | 2754.6 |
| 55°   | 1542.0 | 1574.9 | 1706.3 | 2012.6 | 2390.5 | 2890.0 | 3468.1 | 3793.5 | 3926.3 | 3881.9 | 2909.5 |
| 57.5° | 1148.6 | 1178.8 | 1298.3 | 1591.3 | 2006.9 | 2597.4 | 3373.1 | 3849.0 | 4130.1 | 4101.7 | 3154.2 |
| 60°   | 750.8  | 780.5  | 888.4  | 1144.6 | 1556.7 | 2171.2 | 3139.1 | 3837.5 | 4407.6 | 4404.9 | 3454.7 |
| 62.5° | 416.5  | 440.0  | 518.1  | 717.9  | 1086.5 | 1681.4 | 2771.4 | 3721.6 | 4676.2 | 4693.1 | 3702.5 |
| 65°   | 213.1  | 228.2  | 275.7  | 394.7  | 657.6  | 1192.1 | 2287.9 | 3456.1 | 4800.5 | 4843.1 | 3767.8 |
| 67.5° | 139.4  | 144.3  | 155.8  | 205.1  | 352.1  | 749.9  | 1721.8 | 3030.3 | 4625.6 | 4675.3 | 3548.9 |
| 70°   | 113.2  | 117.2  | 123.9  | 136.8  | 181.6  | 398.3  | 1130.9 | 2420.2 | 3865.0 | 3898.7 | 2826.0 |
| 72.5° | 83.0   | 88.4   | 101.2  | 109.7  | 131.0  | 218.4  | 588.3  | 1588.6 | 2654.2 | 2713.7 | 1776.0 |
| 75°   | 61.3   | 64.4   | 75.0   | 86.6   | 107.0  | 138.1  | 225.1  | 835.2  | 1370.6 | 1336.0 | 745.9  |
| 77.5° | 36.9   | 39.1   | 48.0   | 55.5   | 76.4   | 86.1   | 78.6   | 308.6  | 416.9  | 392.1  | 180.3  |
| 80°   | 18.2   | 20.4   | 31.5   | 41.7   | 48.8   | 34.6   | 32.9   | 86.1   | 92.8   | 92.8   | 45.3   |
| 82.5° | 6.2    | 8.0    | 16.9   | 27.5   | 24.0   | 13.3   | 15.5   | 22.2   | 24.9   | 26.2   | 13.3   |
| 85°   | 0.0    | 0.0    | 4.0    | 8.0    | 3.6    | 1.8    | 4.0    | 4.9    | 6.2    | 6.7    | 4.4    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.4    | 1.3    | 1.8    | 1.8    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P631509

CATALOG NUMBER: GWS-SA1F-827-U-T2R-W-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°   | 105°  | 115°  | 125°  | 135°  | 145°  | 155°  | 165°  | 175°  | 180°  |
|-------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°    | 442.2  | 442.2 | 442.2 | 442.2 | 442.2 | 442.2 | 442.2 | 442.2 | 442.2 | 442.2 | 442.2 |
| 2.5°  | 453.8  | 432.9 | 401.4 | 373.0 | 351.2 | 330.8 | 315.2 | 302.8 | 300.6 | 293.5 | 294.4 |
| 5°    | 474.2  | 436.5 | 378.3 | 333.4 | 301.9 | 280.6 | 262.8 | 249.5 | 243.8 | 238.0 | 233.5 |
| 7.5°  | 505.7  | 451.1 | 369.4 | 314.8 | 277.9 | 245.1 | 217.6 | 195.4 | 184.7 | 178.0 | 173.6 |
| 10°   | 544.3  | 471.5 | 369.9 | 303.7 | 249.1 | 198.9 | 161.2 | 136.8 | 125.2 | 121.7 | 121.2 |
| 12.5° | 590.5  | 497.3 | 373.4 | 285.5 | 207.3 | 147.9 | 119.4 | 108.3 | 104.8 | 101.7 | 101.7 |
| 15°   | 639.4  | 526.1 | 373.4 | 252.2 | 158.1 | 115.4 | 103.5 | 96.3  | 91.9  | 90.1  | 89.2  |
| 17.5° | 690.9  | 553.2 | 364.5 | 206.5 | 121.2 | 101.7 | 91.9  | 85.2  | 81.7  | 79.0  | 78.1  |
| 20°   | 745.9  | 579.0 | 342.3 | 158.1 | 103.9 | 91.0  | 81.7  | 75.0  | 71.5  | 68.8  | 68.8  |
| 22.5° | 801.9  | 602.9 | 306.4 | 121.7 | 91.9  | 80.8  | 71.9  | 65.7  | 62.2  | 59.5  | 59.5  |
| 25°   | 853.8  | 618.9 | 260.2 | 100.3 | 83.0  | 71.9  | 63.9  | 57.7  | 53.7  | 51.9  | 51.1  |
| 27.5° | 902.2  | 629.1 | 209.1 | 88.4  | 74.6  | 64.4  | 55.9  | 50.2  | 47.1  | 45.7  | 44.8  |
| 30°   | 952.4  | 631.8 | 159.8 | 80.4  | 67.5  | 56.8  | 48.8  | 44.4  | 41.7  | 40.0  | 40.0  |
| 32.5° | 1001.2 | 628.7 | 122.1 | 73.7  | 61.3  | 50.2  | 43.5  | 39.5  | 37.3  | 36.0  | 35.5  |
| 35°   | 1050.9 | 614.5 | 99.0  | 67.9  | 55.1  | 44.0  | 38.6  | 35.5  | 34.2  | 32.4  | 32.4  |
| 37.5° | 1105.1 | 595.4 | 86.1  | 62.2  | 48.8  | 39.5  | 34.6  | 32.4  | 30.6  | 29.3  | 28.9  |
| 40°   | 1172.6 | 573.2 | 79.0  | 57.3  | 43.1  | 35.5  | 31.1  | 28.9  | 27.5  | 26.2  | 25.8  |
| 42.5° | 1252.5 | 551.4 | 75.5  | 51.9  | 38.6  | 31.5  | 28.0  | 25.3  | 24.0  | 22.2  | 21.8  |
| 45°   | 1365.7 | 546.6 | 71.5  | 46.2  | 34.6  | 28.4  | 24.4  | 21.8  | 20.0  | 18.6  | 18.2  |
| 47.5° | 1547.8 | 560.3 | 64.8  | 40.0  | 30.6  | 24.9  | 20.9  | 18.6  | 16.4  | 15.1  | 14.2  |
| 50°   | 1728.5 | 556.8 | 58.2  | 34.6  | 27.1  | 21.3  | 17.8  | 15.5  | 13.3  | 12.0  | 11.5  |
| 52.5° | 1827.1 | 539.9 | 51.9  | 30.6  | 23.5  | 18.2  | 15.1  | 12.4  | 11.1  | 9.8   | 9.3   |
| 55°   | 1916.3 | 533.2 | 45.7  | 26.6  | 20.0  | 16.0  | 12.4  | 10.2  | 9.3   | 8.0   | 7.5   |
| 57.5° | 2091.2 | 548.8 | 40.4  | 23.1  | 17.3  | 13.8  | 10.7  | 8.4   | 7.5   | 6.2   | 5.8   |
| 60°   | 2274.2 | 550.6 | 34.6  | 20.0  | 15.1  | 11.5  | 8.4   | 6.7   | 5.8   | 4.4   | 4.0   |
| 62.5° | 2369.6 | 505.7 | 28.4  | 16.9  | 12.4  | 9.8   | 7.1   | 5.3   | 4.4   | 2.7   | 2.7   |
| 65°   | 2289.7 | 408.9 | 24.0  | 13.8  | 9.8   | 7.5   | 5.3   | 4.0   | 2.7   | 1.3   | 0.4   |
| 67.5° | 2026.4 | 290.8 | 20.0  | 11.1  | 7.1   | 5.3   | 4.0   | 2.7   | 0.4   | 0.0   | 0.0   |
| 70°   | 1483.8 | 166.1 | 15.5  | 8.0   | 5.3   | 3.6   | 2.7   | 1.3   | 0.0   | 0.0   | 0.0   |
| 72.5° | 912.0  | 88.8  | 11.5  | 5.3   | 4.0   | 2.7   | 2.2   | 0.9   | 0.0   | 0.0   | 0.0   |
| 75°   | 345.9  | 42.6  | 7.1   | 3.6   | 3.1   | 2.2   | 1.3   | 0.4   | 0.0   | 0.0   | 0.0   |
| 77.5° | 93.7   | 20.9  | 4.0   | 2.7   | 2.2   | 1.3   | 0.9   | 0.0   | 0.0   | 0.0   | 0.0   |
| 80°   | 24.4   | 9.8   | 2.7   | 1.8   | 1.3   | 0.9   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 82.5° | 8.4    | 4.4   | 1.3   | 1.3   | 0.9   | 0.4   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 85°   | 3.6    | 1.8   | 0.9   | 0.9   | 0.4   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 87.5° | 1.3    | 0.4   | 0.4   | 0.4   | 0.4   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 90°   | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2407-157-9  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/03/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Invue  
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**  
 Description: Epic Modern Light Square 40W 5WQ Optic

**Spectral Parameters**

CCT (K): 2764  
 CIE u': 0.2591  
 CIE v': 0.5290  
 Duv: 0.0020  
 CIE x: 0.4581  
 CIE y: 0.4156  
 CIE z: 0.1263  
 Peak Wavelength (nm): 603  
 Dominant Wavelength (nm): 583  
 Purity: 62.2537  
 Rf: 84.7  
 Rg: 94.6

|           |      |      |      |
|-----------|------|------|------|
| CRI (Ra): | 80.9 |      |      |
| R1:       | 78.8 | R9:  | -1.5 |
| R2:       | 89.9 | R10: | 77.9 |
| R3:       | 96.2 | R11: | 78.9 |
| R4:       | 79.1 | R12: | 71.6 |
| R5:       | 79.1 | R13: | 81.2 |
| R6:       | 88.8 | R14: | 98.5 |
| R7:       | 81.3 | R15: | 69.9 |
| R8:       | 54.3 |      |      |



**Test Conditions**

Stabilization Time: 81M  
 Operation Time: 2H 21M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

**Photopic Flux vs. Wavelength**



**Photopic Lumens: 4337.9**

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | 0.0                            | 490               | 18018                                | 2.6                            | 620               | 87426                                | 22.8                           | 750               | 2680                                 | 0.0                            | 880               | 58                                   | 0.0                            |
| 365               | 0                                    | 0.0                            | 495               | 22295                                | 3.9                            | 625               | 83013                                | 18.2                           | 755               | 2287                                 | 0.0                            | 885               | 46                                   | 0.0                            |
| 370               | 0                                    | 0.0                            | 500               | 26478                                | 5.8                            | 630               | 78077                                | 14.1                           | 760               | 1944                                 | 0.0                            | 890               | 45                                   | 0.0                            |
| 375               | 0                                    | 0.0                            | 505               | 30524                                | 8.5                            | 635               | 72080                                | 10.7                           | 765               | 1653                                 | 0.0                            | 895               | 41                                   | 0.0                            |
| 380               | 0                                    | 0.0                            | 510               | 33611                                | 11.5                           | 640               | 66249                                | 7.9                            | 770               | 1413                                 | 0.0                            | 900               | 38                                   | 0.0                            |
| 385               | 0                                    | 0.0                            | 515               | 36490                                | 15.2                           | 645               | 59973                                | 5.7                            | 775               | 1198                                 | 0.0                            | 905               | 33                                   | 0.0                            |
| 390               | 0                                    | 0.0                            | 520               | 38610                                | 18.7                           | 650               | 53972                                | 3.9                            | 780               | 1025                                 | 0.0                            | 910               | 30                                   | 0.0                            |
| 395               | 0                                    | 0.0                            | 525               | 40511                                | 21.9                           | 655               | 48369                                | 2.7                            | 785               | 874                                  | 0.0                            | 915               | 23                                   | 0.0                            |
| 400               | 48                                   | 0.0                            | 530               | 42223                                | 24.9                           | 660               | 42641                                | 1.8                            | 790               | 747                                  | 0.0                            | 920               | 24                                   | 0.0                            |
| 405               | 201                                  | 0.0                            | 535               | 44137                                | 27.6                           | 665               | 37602                                | 1.1                            | 795               | 639                                  | 0.0                            | 925               | 22                                   | 0.0                            |
| 410               | 457                                  | 0.0                            | 540               | 46032                                | 30.0                           | 670               | 32798                                | 0.7                            | 800               | 547                                  | 0.0                            | 930               | 22                                   | 0.0                            |
| 415               | 925                                  | 0.0                            | 545               | 48553                                | 32.5                           | 675               | 28558                                | 0.5                            | 805               | 473                                  | 0.0                            | 935               | 17                                   | 0.0                            |
| 420               | 1816                                 | 0.0                            | 550               | 51408                                | 34.9                           | 680               | 24782                                | 0.3                            | 810               | 401                                  | 0.0                            | 940               | 13                                   | 0.0                            |
| 425               | 3217                                 | 0.0                            | 555               | 54711                                | 37.4                           | 685               | 21386                                | 0.2                            | 815               | 351                                  | 0.0                            | 945               | 6                                    | 0.0                            |
| 430               | 5520                                 | 0.0                            | 560               | 58847                                | 40.0                           | 690               | 18413                                | 0.1                            | 820               | 307                                  | 0.0                            | 950               | 10                                   | 0.0                            |
| 435               | 9225                                 | 0.1                            | 565               | 63386                                | 42.4                           | 695               | 15721                                | 0.1                            | 825               | 261                                  | 0.0                            | 955               | 11                                   | 0.0                            |
| 440               | 15522                                | 0.2                            | 570               | 68196                                | 44.3                           | 700               | 13432                                | 0.0                            | 830               | 228                                  | 0.0                            | 960               | 8                                    | 0.0                            |
| 445               | 27642                                | 0.6                            | 575               | 73613                                | 46.0                           | 705               | 11513                                | 0.0                            | 835               | 193                                  | 0.0                            | 965               | 12                                   | 0.0                            |
| 450               | 36602                                | 0.9                            | 580               | 79207                                | 47.1                           | 710               | 9780                                 | 0.0                            | 840               | 174                                  | 0.0                            | 970               | 3                                    | 0.0                            |
| 455               | 28292                                | 0.9                            | 585               | 84248                                | 47.0                           | 715               | 8356                                 | 0.0                            | 845               | 151                                  | 0.0                            | 975               | 8                                    | 0.0                            |
| 460               | 21166                                | 0.9                            | 590               | 88397                                | 45.7                           | 720               | 7161                                 | 0.0                            | 850               | 123                                  | 0.0                            | 980               | 2                                    | 0.0                            |
| 465               | 19092                                | 1.0                            | 595               | 91428                                | 43.4                           | 725               | 6067                                 | 0.0                            | 855               | 106                                  | 0.0                            | 985               | 13                                   | 0.0                            |
| 470               | 14951                                | 0.9                            | 600               | 93452                                | 40.3                           | 730               | 5164                                 | 0.0                            | 860               | 95                                   | 0.0                            | 990               | 16                                   | 0.0                            |
| 475               | 12606                                | 1.0                            | 605               | 93959                                | 36.4                           | 735               | 4393                                 | 0.0                            | 865               | 82                                   | 0.0                            | 995               | 20                                   | 0.0                            |
| 480               | 13323                                | 1.3                            | 610               | 93079                                | 32.0                           | 740               | 3694                                 | 0.0                            | 870               | 77                                   | 0.0                            | 1000              | 0                                    | 0.0                            |
| 485               | 15164                                | 1.8                            | 615               | 90707                                | 27.3                           | 745               | 3157                                 | 0.0                            | 875               | 65                                   | 0.0                            |                   |                                      |                                |

REPORT NUMBER: SP1-2407-157-9

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: 5286.7**

**S/P: 1.22**

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | 0.0                            | 490               | 18018                                | 75.9                           | 620               | 87426                                | 0.4                            | 750               | 2680                                 | 0.0                            | 880               | 58                                   | 0.0                            |
| 365               | 0                                    | 0.0                            | 495               | 22295                                | 93.2                           | 625               | 83013                                | 0.2                            | 755               | 2287                                 | 0.0                            | 885               | 46                                   | 0.0                            |
| 370               | 0                                    | 0.0                            | 500               | 26478                                | 107.8                          | 630               | 78077                                | 0.1                            | 760               | 1944                                 | 0.0                            | 890               | 45                                   | 0.0                            |
| 375               | 0                                    | 0.0                            | 505               | 30524                                | 118.7                          | 635               | 72080                                | 0.1                            | 765               | 1653                                 | 0.0                            | 895               | 41                                   | 0.0                            |
| 380               | 0                                    | 0.0                            | 510               | 33611                                | 122.2                          | 640               | 66249                                | 0.1                            | 770               | 1413                                 | 0.0                            | 900               | 38                                   | 0.0                            |
| 385               | 0                                    | 0.0                            | 515               | 36490                                | 120.8                          | 645               | 59973                                | 0.0                            | 775               | 1198                                 | 0.0                            | 905               | 33                                   | 0.0                            |
| 390               | 0                                    | 0.0                            | 520               | 38610                                | 113.9                          | 650               | 53972                                | 0.0                            | 780               | 1025                                 | 0.0                            | 910               | 30                                   | 0.0                            |
| 395               | 0                                    | 0.0                            | 525               | 40511                                | 104.1                          | 655               | 48369                                | 0.0                            | 785               | 874                                  | 0.0                            | 915               | 23                                   | 0.0                            |
| 400               | 48                                   | 0.0                            | 530               | 42223                                | 92.4                           | 660               | 42641                                | 0.0                            | 790               | 747                                  | 0.0                            | 920               | 24                                   | 0.0                            |
| 405               | 201                                  | 0.0                            | 535               | 44137                                | 80.5                           | 665               | 37602                                | 0.0                            | 795               | 639                                  | 0.0                            | 925               | 22                                   | 0.0                            |
| 410               | 457                                  | 0.1                            | 540               | 46032                                | 68.2                           | 670               | 32798                                | 0.0                            | 800               | 547                                  | 0.0                            | 930               | 22                                   | 0.0                            |
| 415               | 925                                  | 0.3                            | 545               | 48553                                | 57.1                           | 675               | 28558                                | 0.0                            | 805               | 473                                  | 0.0                            | 935               | 17                                   | 0.0                            |
| 420               | 1816                                 | 1.1                            | 550               | 51408                                | 46.7                           | 680               | 24782                                | 0.0                            | 810               | 401                                  | 0.0                            | 940               | 13                                   | 0.0                            |
| 425               | 3217                                 | 2.5                            | 555               | 54711                                | 37.4                           | 685               | 21386                                | 0.0                            | 815               | 351                                  | 0.0                            | 945               | 6                                    | 0.0                            |
| 430               | 5520                                 | 5.9                            | 560               | 58847                                | 29.4                           | 690               | 18413                                | 0.0                            | 820               | 307                                  | 0.0                            | 950               | 10                                   | 0.0                            |
| 435               | 9225                                 | 12.5                           | 565               | 63386                                | 22.5                           | 695               | 15721                                | 0.0                            | 825               | 261                                  | 0.0                            | 955               | 11                                   | 0.0                            |
| 440               | 15522                                | 26.3                           | 570               | 68196                                | 16.9                           | 700               | 13432                                | 0.0                            | 830               | 228                                  | 0.0                            | 960               | 8                                    | 0.0                            |
| 445               | 27642                                | 55.2                           | 575               | 73613                                | 12.4                           | 705               | 11513                                | 0.0                            | 835               | 193                                  | 0.0                            | 965               | 12                                   | 0.0                            |
| 450               | 36602                                | 85.4                           | 580               | 79207                                | 9.0                            | 710               | 9780                                 | 0.0                            | 840               | 174                                  | 0.0                            | 970               | 3                                    | 0.0                            |
| 455               | 28292                                | 75.1                           | 585               | 84248                                | 6.3                            | 715               | 8356                                 | 0.0                            | 845               | 151                                  | 0.0                            | 975               | 8                                    | 0.0                            |
| 460               | 21166                                | 63.2                           | 590               | 88397                                | 4.4                            | 720               | 7161                                 | 0.0                            | 850               | 123                                  | 0.0                            | 980               | 2                                    | 0.0                            |
| 465               | 19092                                | 63.2                           | 595               | 91428                                | 3.0                            | 725               | 6067                                 | 0.0                            | 855               | 106                                  | 0.0                            | 985               | 13                                   | 0.0                            |
| 470               | 14951                                | 54.2                           | 600               | 93452                                | 2.0                            | 730               | 5164                                 | 0.0                            | 860               | 95                                   | 0.0                            | 990               | 16                                   | 0.0                            |
| 475               | 12606                                | 48.8                           | 605               | 93959                                | 1.3                            | 735               | 4393                                 | 0.0                            | 865               | 82                                   | 0.0                            | 995               | 20                                   | 0.0                            |
| 480               | 13323                                | 54.2                           | 610               | 93079                                | 0.9                            | 740               | 3694                                 | 0.0                            | 870               | 77                                   | 0.0                            | 1000              | 0                                    | 0.0                            |
| 485               | 15164                                | 63.3                           | 615               | 90707                                | 0.5                            | 745               | 3157                                 | 0.0                            | 875               | 65                                   | 0.0                            |                   |                                      |                                |

REPORT NUMBER: SP1-2407-157-9

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 9797**

**M/P: 2.26**


| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 0             | 0.0           | 490    | 18018         | 27.7          | 620    | 87426         | 1.1           | 750    | 2680          | 0.0           | 880    | 58            | 0.0           |
| 365    | 0             | 0.0           | 495    | 22295         | 36.0          | 625    | 83013         | 0.7           | 755    | 2287          | 0.0           | 885    | 46            | 0.0           |
| 370    | 0             | 0.0           | 500    | 26478         | 44.2          | 630    | 78077         | 0.4           | 760    | 1944          | 0.0           | 890    | 45            | 0.0           |
| 375    | 0             | 0.0           | 505    | 30524         | 51.8          | 635    | 72080         | 0.3           | 765    | 1653          | 0.0           | 895    | 41            | 0.0           |
| 380    | 0             | 0.0           | 510    | 33611         | 57.0          | 640    | 66249         | 0.2           | 770    | 1413          | 0.0           | 900    | 38            | 0.0           |
| 385    | 0             | 0.0           | 515    | 36490         | 60.5          | 645    | 59973         | 0.1           | 775    | 1198          | 0.0           | 905    | 33            | 0.0           |
| 390    | 0             | 0.0           | 520    | 38610         | 61.4          | 650    | 53972         | 0.1           | 780    | 1025          | 0.0           | 910    | 30            | 0.0           |
| 395    | 0             | 0.0           | 525    | 40511         | 60.6          | 655    | 48369         | 0.0           | 785    | 874           | 0.0           | 915    | 23            | 0.0           |
| 400    | 48            | 0.0           | 530    | 42223         | 58.2          | 660    | 42641         | 0.0           | 790    | 747           | 0.0           | 920    | 24            | 0.0           |
| 405    | 201           | 0.0           | 535    | 44137         | 55.0          | 665    | 37602         | 0.0           | 795    | 639           | 0.0           | 925    | 22            | 0.0           |
| 410    | 457           | 0.0           | 540    | 46032         | 50.9          | 670    | 32798         | 0.0           | 800    | 547           | 0.0           | 930    | 22            | 0.0           |
| 415    | 925           | 0.1           | 545    | 48553         | 46.6          | 675    | 28558         | 0.0           | 805    | 473           | 0.0           | 935    | 17            | 0.0           |
| 420    | 1816          | 0.3           | 550    | 51408         | 42.0          | 680    | 24782         | 0.0           | 810    | 401           | 0.0           | 940    | 13            | 0.0           |
| 425    | 3217          | 0.8           | 555    | 54711         | 37.4          | 685    | 21386         | 0.0           | 815    | 351           | 0.0           | 945    | 6             | 0.0           |
| 430    | 5520          | 1.9           | 560    | 58847         | 32.9          | 690    | 18413         | 0.0           | 820    | 307           | 0.0           | 950    | 10            | 0.0           |
| 435    | 9225          | 4.1           | 565    | 63386         | 28.4          | 695    | 15721         | 0.0           | 825    | 261           | 0.0           | 955    | 11            | 0.0           |
| 440    | 15522         | 8.7           | 570    | 68196         | 24.1          | 700    | 13432         | 0.0           | 830    | 228           | 0.0           | 960    | 8             | 0.0           |
| 445    | 27642         | 18.5          | 575    | 73613         | 20.0          | 705    | 11513         | 0.0           | 835    | 193           | 0.0           | 965    | 12            | 0.0           |
| 450    | 36602         | 28.3          | 580    | 79207         | 16.3          | 710    | 9780          | 0.0           | 840    | 174           | 0.0           | 970    | 3             | 0.0           |
| 455    | 28292         | 24.7          | 585    | 84248         | 12.9          | 715    | 8356          | 0.0           | 845    | 151           | 0.0           | 975    | 8             | 0.0           |
| 460    | 21166         | 20.4          | 590    | 88397         | 9.8           | 720    | 7161          | 0.0           | 850    | 123           | 0.0           | 980    | 2             | 0.0           |
| 465    | 19092         | 20.1          | 595    | 91428         | 7.3           | 725    | 6067          | 0.0           | 855    | 106           | 0.0           | 985    | 13            | 0.0           |
| 470    | 14951         | 17.2          | 600    | 93452         | 5.3           | 730    | 5164          | 0.0           | 860    | 95            | 0.0           | 990    | 16            | 0.0           |
| 475    | 12606         | 15.7          | 605    | 93959         | 3.7           | 735    | 4393          | 0.0           | 865    | 82            | 0.0           | 995    | 20            | 0.0           |
| 480    | 13323         | 18.0          | 610    | 93079         | 2.5           | 740    | 3694          | 0.0           | 870    | 77            | 0.0           | 1000   | 0             | 0.0           |
| 485    | 15164         | 21.9          | 615    | 90707         | 1.7           | 745    | 3157          | 0.0           | 875    | 65            | 0.0           |        |               |               |

**Summary**

$R_f = 84.7$   
 $R_g = 94.6$   
 $CIE R_a = 80.9$   
 $R_g = -1.5$



**Color Vector Graphics**






Individual Sample Fidelity Index ( $R_{f,i}$ )

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 |            |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)