

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P631515

Luminaire Tested: GWS-SA1F-827-U-T3R-W-GRSBK

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P631515  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA1F-827-U-T3R-W-GRSBK  
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III ROADWAY OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK  
Light Source: (16) 2700K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3884.4 lumens  
Efficiency: N/A  
Efficacy: 57.8 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type II - Short  
BUG Rating: B1 - U0 - G0  
  
Input Watts (W): 67.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P631515  
 CATALOG NUMBER: GWS-SA1F-827-U-T3R-W-GRSBK

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 9.7 fc  
 Type II - Short - N/A

REPORT NUMBER: P631515  
CATALOG NUMBER: GWS-SA1F-827-U-T3R-W-GRSBK

### Luminous Intensity Polar Plot



— Vertical Plane Through 38-Deg Lateral    - - - Horizontal Cone Through 55-Deg Vertical

REPORT NUMBER: P631515  
 CATALOG NUMBER: GWS-SA1F-827-U-T3R-W-GRSBK

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 756.8    | 0.0    | 756.8  |
|                    | % Fixture | 19.5     | 0.0    | 19.5   |
| <b>Street Side</b> | Lumens    | 3127.6   | 0.0    | 3127.6 |
|                    | % Fixture | 80.5     | 0.0    | 80.5   |
| <b>Total</b>       | Lumens    | 3884.4   | 0.0    | 3884.4 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 86.1   | 2.2       |
| 10°-20°   | 231.9  | 6.0       |
| 20°-30°   | 397.9  | 10.2      |
| 30°-40°   | 660.0  | 17.0      |
| 40°-50°   | 970.2  | 25.0      |
| 50°-60°   | 1133.7 | 29.2      |
| 60°-70°   | 384.3  | 9.9       |
| 70°-80°   | 19.6   | 0.5       |
| 80°-90°   | 0.8    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 3884.4 | 100.0     |
| 0°-180°   | 3884.4 | 100.0     |

**Coefficient of Utilization**




REPORT NUMBER: P631515  
 CATALOG NUMBER: GWS-SA1F-827-U-T3R-W-GRSBK

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |        |
|----------------|--------|-----------|-------------------------|------|--------|
|                |        |           | B                       | U    | G      |
| FL (0°-30°)    | 427.6  | 11.0      |                         |      |        |
| FM (30°-60°)   | 2346.1 | 60.4      |                         |      |        |
| FH (60°-80°)   | 353.5  | 9.1       |                         |      | G0/660 |
| FVH (80°-90°)  | 0.4    | 0.0       |                         |      | G0/10  |
| BL (0°-30°)    | 288.3  | 7.4       | B1/500                  |      |        |
| BM (30°-60°)   | 417.7  | 10.8      | B1/1000                 |      |        |
| BH (60°-80°)   | 50.4   | 1.3       | B0/110                  |      | G0/110 |
| BVH (80°-90°)  | 0.4    | 0.0       |                         |      | G0/10  |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |        |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |        |

**BUG Rating: B1-U0-G0**  
 Type II Short





REPORT NUMBER: P631515

CATALOG NUMBER: GWS-SA1F-827-U-T3R-W-GRSBK

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 38°    | 45°    | 55°    | 65°    | 75°    | 85°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 931.5  | 931.5  | 931.5  | 931.5  | 931.5  | 931.5  | 931.5  | 931.5  | 931.5  | 931.5  | 931.5  |
| 2.5°  | 867.6  | 865.8  | 869.3  | 876.5  | 883.1  | 885.3  | 892.0  | 901.3  | 907.1  | 920.9  | 932.0  |
| 5°    | 828.5  | 827.6  | 831.2  | 837.4  | 846.3  | 849.4  | 859.6  | 875.1  | 890.7  | 914.6  | 938.2  |
| 7.5°  | 793.0  | 792.5  | 797.9  | 811.6  | 824.5  | 828.5  | 840.9  | 860.0  | 880.9  | 917.7  | 952.4  |
| 10°   | 746.4  | 746.8  | 757.0  | 776.6  | 800.1  | 808.1  | 828.1  | 855.6  | 882.7  | 930.2  | 978.1  |
| 12.5° | 731.3  | 732.2  | 737.5  | 752.6  | 778.3  | 788.5  | 816.5  | 858.2  | 892.9  | 947.9  | 1011.4 |
| 15°   | 768.1  | 768.1  | 763.7  | 765.5  | 777.0  | 786.3  | 815.6  | 867.1  | 910.2  | 969.2  | 1044.3 |
| 17.5° | 839.6  | 836.9  | 825.8  | 810.7  | 806.7  | 809.9  | 833.4  | 886.2  | 934.6  | 994.1  | 1081.6 |
| 20°   | 936.4  | 937.3  | 915.5  | 884.0  | 858.7  | 858.2  | 872.5  | 920.0  | 969.7  | 1023.9 | 1122.0 |
| 22.5° | 1053.6 | 1050.1 | 1021.2 | 978.1  | 934.2  | 930.6  | 936.4  | 971.5  | 1020.3 | 1070.9 | 1171.7 |
| 25°   | 1189.5 | 1187.7 | 1146.8 | 1089.1 | 1031.0 | 1022.5 | 1022.5 | 1057.2 | 1092.7 | 1138.0 | 1231.2 |
| 27.5° | 1331.6 | 1331.6 | 1292.0 | 1225.4 | 1148.2 | 1133.1 | 1130.9 | 1171.7 | 1195.2 | 1204.1 | 1281.4 |
| 30°   | 1477.6 | 1475.9 | 1436.8 | 1368.4 | 1285.8 | 1270.3 | 1264.1 | 1294.3 | 1311.1 | 1284.5 | 1344.0 |
| 32.5° | 1625.9 | 1629.0 | 1589.5 | 1526.0 | 1452.3 | 1442.1 | 1423.0 | 1423.0 | 1436.8 | 1399.5 | 1442.6 |
| 35°   | 1785.3 | 1784.4 | 1753.4 | 1710.3 | 1647.2 | 1635.7 | 1604.2 | 1554.9 | 1575.8 | 1559.3 | 1578.9 |
| 37.5° | 1926.1 | 1932.7 | 1917.6 | 1885.7 | 1834.6 | 1823.1 | 1771.1 | 1681.9 | 1697.9 | 1723.6 | 1740.9 |
| 40°   | 2069.0 | 2074.4 | 2089.5 | 2079.2 | 2014.9 | 1993.6 | 1901.2 | 1754.7 | 1772.4 | 1860.8 | 1910.5 |
| 42.5° | 2209.3 | 2212.0 | 2242.6 | 2259.5 | 2173.4 | 2136.1 | 1999.8 | 1799.1 | 1817.7 | 1968.2 | 2055.3 |
| 45°   | 2298.6 | 2304.4 | 2355.0 | 2406.5 | 2313.2 | 2262.2 | 2085.5 | 1855.9 | 1863.9 | 2042.8 | 2162.3 |
| 47.5° | 2295.0 | 2308.3 | 2403.4 | 2497.0 | 2433.6 | 2378.5 | 2188.5 | 1946.9 | 1933.6 | 2113.0 | 2232.9 |
| 50°   | 2223.5 | 2239.5 | 2375.8 | 2524.6 | 2520.1 | 2469.1 | 2303.0 | 2078.8 | 2037.1 | 2175.1 | 2241.7 |
| 52.5° | 2075.2 | 2121.4 | 2327.4 | 2528.1 | 2589.8 | 2564.1 | 2444.7 | 2256.4 | 2176.9 | 2264.4 | 2256.0 |
| 55°   | 1754.7 | 1811.5 | 2180.5 | 2497.9 | 2652.9 | 2656.0 | 2593.4 | 2441.5 | 2328.8 | 2418.0 | 2343.4 |
| 57.5° | 1332.0 | 1377.3 | 1678.3 | 2223.5 | 2548.6 | 2599.6 | 2651.1 | 2539.2 | 2422.5 | 2522.8 | 2363.8 |
| 60°   | 802.7  | 855.1  | 1050.9 | 1631.7 | 2058.4 | 2145.4 | 2347.4 | 2325.7 | 2184.9 | 2228.0 | 1938.5 |
| 62.5° | 325.5  | 353.0  | 485.3  | 899.1  | 1295.6 | 1376.8 | 1570.4 | 1603.3 | 1568.6 | 1524.7 | 1175.7 |
| 65°   | 119.0  | 130.1  | 194.5  | 371.6  | 595.8  | 625.6  | 727.7  | 785.9  | 833.8  | 710.0  | 437.3  |
| 67.5° | 73.7   | 80.8   | 126.5  | 190.9  | 216.7  | 201.6  | 205.1  | 244.6  | 233.5  | 144.3  | 78.1   |
| 70°   | 54.6   | 60.4   | 99.0   | 132.3  | 87.5   | 67.5   | 45.7   | 48.8   | 44.0   | 38.6   | 38.2   |
| 72.5° | 37.7   | 43.1   | 74.1   | 78.1   | 33.7   | 24.0   | 16.9   | 23.5   | 26.6   | 26.2   | 27.1   |
| 75°   | 24.9   | 28.9   | 46.6   | 30.6   | 8.4    | 6.7    | 5.8    | 12.4   | 16.0   | 16.0   | 16.4   |
| 77.5° | 14.7   | 16.9   | 16.4   | 6.2    | 1.8    | 1.8    | 1.3    | 2.2    | 3.6    | 4.0    | 4.9    |
| 80°   | 1.8    | 1.3    | 0.9    | 0.9    | 0.9    | 0.9    | 0.9    | 0.9    | 1.3    | 1.3    | 1.3    |
| 82.5° | 0.4    | 0.4    | 0.4    | 0.9    | 0.9    | 0.9    | 0.9    | 0.9    | 0.9    | 1.3    | 1.3    |
| 85°   | 0.0    | 0.0    | 0.4    | 0.4    | 0.9    | 0.9    | 0.9    | 0.9    | 0.9    | 1.3    | 1.3    |
| 87.5° | 0.0    | 0.0    | 0.4    | 0.4    | 0.9    | 0.9    | 0.9    | 0.9    | 0.9    | 1.3    | 1.3    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P631515

CATALOG NUMBER: GWS-SA1F-827-U-T3R-W-GRSBK

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°  | 135°  | 145°  | 155°  | 165°  | 175°  | 180°  |
|-------|--------|--------|--------|--------|-------|-------|-------|-------|-------|-------|-------|
| 0°    | 931.5  | 931.5  | 931.5  | 931.5  | 931.5 | 931.5 | 931.5 | 931.5 | 931.5 | 931.5 | 931.5 |
| 2.5°  | 940.4  | 937.3  | 950.2  | 959.5  | 967.0 | 970.6 | 965.7 | 965.3 | 965.3 | 955.5 | 952.8 |
| 5°    | 951.5  | 952.8  | 971.0  | 979.0  | 980.3 | 975.9 | 964.8 | 957.3 | 952.8 | 942.6 | 936.8 |
| 7.5°  | 972.8  | 977.2  | 994.6  | 993.2  | 981.2 | 960.8 | 931.5 | 908.9 | 894.2 | 878.2 | 868.5 |
| 10°   | 1003.4 | 1011.9 | 1022.5 | 1003.9 | 965.7 | 913.7 | 853.4 | 810.3 | 784.5 | 766.3 | 755.2 |
| 12.5° | 1040.7 | 1049.2 | 1045.6 | 1001.7 | 922.2 | 829.4 | 751.7 | 689.5 | 659.8 | 643.4 | 631.8 |
| 15°   | 1078.5 | 1083.8 | 1060.7 | 975.0  | 845.4 | 720.6 | 634.0 | 572.3 | 535.9 | 522.6 | 512.8 |
| 17.5° | 1117.1 | 1115.8 | 1063.4 | 922.6  | 742.8 | 598.1 | 512.8 | 470.6 | 460.4 | 458.2 | 457.3 |
| 20°   | 1157.5 | 1145.5 | 1052.7 | 847.6  | 619.4 | 476.9 | 428.5 | 431.1 | 449.8 | 458.7 | 460.4 |
| 22.5° | 1203.7 | 1173.5 | 1026.1 | 745.9  | 493.3 | 397.4 | 402.3 | 428.5 | 453.8 | 465.8 | 467.5 |
| 25°   | 1253.0 | 1199.2 | 981.7  | 615.4  | 388.9 | 365.4 | 394.3 | 424.5 | 451.5 | 466.2 | 468.0 |
| 27.5° | 1285.4 | 1205.5 | 908.9  | 484.0  | 333.9 | 353.0 | 383.6 | 412.5 | 440.4 | 456.4 | 458.7 |
| 30°   | 1320.5 | 1202.8 | 809.9  | 373.0  | 315.2 | 342.3 | 369.0 | 395.2 | 420.9 | 438.7 | 440.4 |
| 32.5° | 1372.0 | 1201.0 | 689.1  | 302.8  | 307.7 | 333.9 | 353.4 | 375.2 | 392.9 | 403.2 | 401.8 |
| 35°   | 1439.4 | 1198.8 | 548.3  | 273.1  | 303.3 | 327.2 | 342.8 | 353.0 | 333.4 | 327.2 | 328.6 |
| 37.5° | 1526.0 | 1204.1 | 429.8  | 260.6  | 301.9 | 325.5 | 338.8 | 309.5 | 279.3 | 267.7 | 266.0 |
| 40°   | 1621.9 | 1217.9 | 327.7  | 255.7  | 306.4 | 329.9 | 323.7 | 275.3 | 238.0 | 215.3 | 210.5 |
| 42.5° | 1718.3 | 1233.0 | 259.3  | 254.0  | 313.9 | 342.3 | 298.8 | 250.4 | 194.5 | 181.6 | 179.8 |
| 45°   | 1789.8 | 1230.3 | 224.2  | 250.9  | 320.6 | 349.4 | 292.2 | 214.9 | 173.6 | 167.8 | 168.3 |
| 47.5° | 1825.7 | 1201.0 | 205.1  | 243.8  | 323.2 | 342.3 | 275.7 | 200.2 | 159.4 | 165.6 | 170.9 |
| 50°   | 1806.6 | 1125.1 | 187.4  | 230.0  | 317.5 | 333.0 | 249.5 | 189.1 | 152.3 | 178.0 | 190.0 |
| 52.5° | 1783.5 | 1031.9 | 167.8  | 208.7  | 303.7 | 320.1 | 239.3 | 186.0 | 147.9 | 171.8 | 180.7 |
| 55°   | 1814.2 | 972.8  | 135.9  | 175.8  | 276.6 | 289.9 | 231.3 | 185.6 | 137.6 | 133.6 | 132.3 |
| 57.5° | 1771.1 | 855.1  | 97.2   | 126.5  | 212.2 | 229.5 | 225.6 | 182.5 | 122.1 | 121.7 | 123.4 |
| 60°   | 1368.8 | 521.7  | 66.6   | 80.4   | 130.1 | 146.5 | 204.7 | 174.5 | 105.2 | 96.8  | 97.2  |
| 62.5° | 777.9  | 222.0  | 45.7   | 49.7   | 66.6  | 79.0  | 156.3 | 158.5 | 97.2  | 92.4  | 97.2  |
| 65°   | 270.8  | 79.5   | 35.5   | 33.3   | 36.9  | 42.2  | 89.7  | 122.5 | 88.4  | 79.9  | 80.8  |
| 67.5° | 55.9   | 39.5   | 31.5   | 27.5   | 27.5  | 27.5  | 45.7  | 76.4  | 72.8  | 63.5  | 64.4  |
| 70°   | 35.5   | 33.7   | 27.5   | 23.5   | 22.6  | 20.9  | 26.2  | 42.2  | 50.2  | 46.2  | 46.6  |
| 72.5° | 26.2   | 25.8   | 21.8   | 19.1   | 16.9  | 15.1  | 16.4  | 20.9  | 25.8  | 26.6  | 27.1  |
| 75°   | 16.0   | 16.4   | 14.2   | 12.0   | 10.7  | 9.3   | 9.8   | 9.8   | 9.8   | 8.9   | 9.8   |
| 77.5° | 4.9    | 5.3    | 4.4    | 3.6    | 3.1   | 3.1   | 3.1   | 2.7   | 2.2   | 1.3   | 1.3   |
| 80°   | 1.3    | 1.3    | 1.3    | 1.3    | 1.3   | 0.9   | 0.9   | 0.4   | 0.4   | 0.0   | 0.0   |
| 82.5° | 1.3    | 1.3    | 1.3    | 1.3    | 0.9   | 0.9   | 0.4   | 0.4   | 0.0   | 0.0   | 0.0   |
| 85°   | 1.3    | 1.3    | 1.3    | 1.3    | 0.9   | 0.9   | 0.4   | 0.4   | 0.0   | 0.0   | 0.0   |
| 87.5° | 1.3    | 1.3    | 1.3    | 1.3    | 0.9   | 0.9   | 0.4   | 0.4   | 0.0   | 0.0   | 0.0   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2407-157-9  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/03/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Invue  
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**  
 Description: Epic Modern Light Square 40W 5WQ Optic

**Spectral Parameters**

CCT (K): 2764  
 CIE u': 0.2591  
 CIE v': 0.5290  
 Duv: 0.0020  
 CIE x: 0.4581  
 CIE y: 0.4156  
 CIE z: 0.1263  
 Peak Wavelength (nm): 603  
 Dominant Wavelength (nm): 583  
 Purity: 62.2537  
 Rf: 84.7  
 Rg: 94.6

|           |      |      |      |
|-----------|------|------|------|
| CRI (Ra): | 80.9 |      |      |
| R1:       | 78.8 | R9:  | -1.5 |
| R2:       | 89.9 | R10: | 77.9 |
| R3:       | 96.2 | R11: | 78.9 |
| R4:       | 79.1 | R12: | 71.6 |
| R5:       | 79.1 | R13: | 81.2 |
| R6:       | 88.8 | R14: | 98.5 |
| R7:       | 81.3 | R15: | 69.9 |
| R8:       | 54.3 |      |      |



**Test Conditions**

Stabilization Time: 81M  
 Operation Time: 2H 21M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

**Photopic Flux vs. Wavelength**



**Photopic Lumens: 4337.9**

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | 0.0                            | 490               | 18018                                | 2.6                            | 620               | 87426                                | 22.8                           | 750               | 2680                                 | 0.0                            | 880               | 58                                   | 0.0                            |
| 365               | 0                                    | 0.0                            | 495               | 22295                                | 3.9                            | 625               | 83013                                | 18.2                           | 755               | 2287                                 | 0.0                            | 885               | 46                                   | 0.0                            |
| 370               | 0                                    | 0.0                            | 500               | 26478                                | 5.8                            | 630               | 78077                                | 14.1                           | 760               | 1944                                 | 0.0                            | 890               | 45                                   | 0.0                            |
| 375               | 0                                    | 0.0                            | 505               | 30524                                | 8.5                            | 635               | 72080                                | 10.7                           | 765               | 1653                                 | 0.0                            | 895               | 41                                   | 0.0                            |
| 380               | 0                                    | 0.0                            | 510               | 33611                                | 11.5                           | 640               | 66249                                | 7.9                            | 770               | 1413                                 | 0.0                            | 900               | 38                                   | 0.0                            |
| 385               | 0                                    | 0.0                            | 515               | 36490                                | 15.2                           | 645               | 59973                                | 5.7                            | 775               | 1198                                 | 0.0                            | 905               | 33                                   | 0.0                            |
| 390               | 0                                    | 0.0                            | 520               | 38610                                | 18.7                           | 650               | 53972                                | 3.9                            | 780               | 1025                                 | 0.0                            | 910               | 30                                   | 0.0                            |
| 395               | 0                                    | 0.0                            | 525               | 40511                                | 21.9                           | 655               | 48369                                | 2.7                            | 785               | 874                                  | 0.0                            | 915               | 23                                   | 0.0                            |
| 400               | 48                                   | 0.0                            | 530               | 42223                                | 24.9                           | 660               | 42641                                | 1.8                            | 790               | 747                                  | 0.0                            | 920               | 24                                   | 0.0                            |
| 405               | 201                                  | 0.0                            | 535               | 44137                                | 27.6                           | 665               | 37602                                | 1.1                            | 795               | 639                                  | 0.0                            | 925               | 22                                   | 0.0                            |
| 410               | 457                                  | 0.0                            | 540               | 46032                                | 30.0                           | 670               | 32798                                | 0.7                            | 800               | 547                                  | 0.0                            | 930               | 22                                   | 0.0                            |
| 415               | 925                                  | 0.0                            | 545               | 48553                                | 32.5                           | 675               | 28558                                | 0.5                            | 805               | 473                                  | 0.0                            | 935               | 17                                   | 0.0                            |
| 420               | 1816                                 | 0.0                            | 550               | 51408                                | 34.9                           | 680               | 24782                                | 0.3                            | 810               | 401                                  | 0.0                            | 940               | 13                                   | 0.0                            |
| 425               | 3217                                 | 0.0                            | 555               | 54711                                | 37.4                           | 685               | 21386                                | 0.2                            | 815               | 351                                  | 0.0                            | 945               | 6                                    | 0.0                            |
| 430               | 5520                                 | 0.0                            | 560               | 58847                                | 40.0                           | 690               | 18413                                | 0.1                            | 820               | 307                                  | 0.0                            | 950               | 10                                   | 0.0                            |
| 435               | 9225                                 | 0.1                            | 565               | 63386                                | 42.4                           | 695               | 15721                                | 0.1                            | 825               | 261                                  | 0.0                            | 955               | 11                                   | 0.0                            |
| 440               | 15522                                | 0.2                            | 570               | 68196                                | 44.3                           | 700               | 13432                                | 0.0                            | 830               | 228                                  | 0.0                            | 960               | 8                                    | 0.0                            |
| 445               | 27642                                | 0.6                            | 575               | 73613                                | 46.0                           | 705               | 11513                                | 0.0                            | 835               | 193                                  | 0.0                            | 965               | 12                                   | 0.0                            |
| 450               | 36602                                | 0.9                            | 580               | 79207                                | 47.1                           | 710               | 9780                                 | 0.0                            | 840               | 174                                  | 0.0                            | 970               | 3                                    | 0.0                            |
| 455               | 28292                                | 0.9                            | 585               | 84248                                | 47.0                           | 715               | 8356                                 | 0.0                            | 845               | 151                                  | 0.0                            | 975               | 8                                    | 0.0                            |
| 460               | 21166                                | 0.9                            | 590               | 88397                                | 45.7                           | 720               | 7161                                 | 0.0                            | 850               | 123                                  | 0.0                            | 980               | 2                                    | 0.0                            |
| 465               | 19092                                | 1.0                            | 595               | 91428                                | 43.4                           | 725               | 6067                                 | 0.0                            | 855               | 106                                  | 0.0                            | 985               | 13                                   | 0.0                            |
| 470               | 14951                                | 0.9                            | 600               | 93452                                | 40.3                           | 730               | 5164                                 | 0.0                            | 860               | 95                                   | 0.0                            | 990               | 16                                   | 0.0                            |
| 475               | 12606                                | 1.0                            | 605               | 93959                                | 36.4                           | 735               | 4393                                 | 0.0                            | 865               | 82                                   | 0.0                            | 995               | 20                                   | 0.0                            |
| 480               | 13323                                | 1.3                            | 610               | 93079                                | 32.0                           | 740               | 3694                                 | 0.0                            | 870               | 77                                   | 0.0                            | 1000              | 0                                    | 0.0                            |
| 485               | 15164                                | 1.8                            | 615               | 90707                                | 27.3                           | 745               | 3157                                 | 0.0                            | 875               | 65                                   | 0.0                            |                   |                                      |                                |

REPORT NUMBER: SP1-2407-157-9

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: 5286.7**

**S/P: 1.22**

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | 0.0                            | 490               | 18018                                | 75.9                           | 620               | 87426                                | 0.4                            | 750               | 2680                                 | 0.0                            | 880               | 58                                   | 0.0                            |
| 365               | 0                                    | 0.0                            | 495               | 22295                                | 93.2                           | 625               | 83013                                | 0.2                            | 755               | 2287                                 | 0.0                            | 885               | 46                                   | 0.0                            |
| 370               | 0                                    | 0.0                            | 500               | 26478                                | 107.8                          | 630               | 78077                                | 0.1                            | 760               | 1944                                 | 0.0                            | 890               | 45                                   | 0.0                            |
| 375               | 0                                    | 0.0                            | 505               | 30524                                | 118.7                          | 635               | 72080                                | 0.1                            | 765               | 1653                                 | 0.0                            | 895               | 41                                   | 0.0                            |
| 380               | 0                                    | 0.0                            | 510               | 33611                                | 122.2                          | 640               | 66249                                | 0.1                            | 770               | 1413                                 | 0.0                            | 900               | 38                                   | 0.0                            |
| 385               | 0                                    | 0.0                            | 515               | 36490                                | 120.8                          | 645               | 59973                                | 0.0                            | 775               | 1198                                 | 0.0                            | 905               | 33                                   | 0.0                            |
| 390               | 0                                    | 0.0                            | 520               | 38610                                | 113.9                          | 650               | 53972                                | 0.0                            | 780               | 1025                                 | 0.0                            | 910               | 30                                   | 0.0                            |
| 395               | 0                                    | 0.0                            | 525               | 40511                                | 104.1                          | 655               | 48369                                | 0.0                            | 785               | 874                                  | 0.0                            | 915               | 23                                   | 0.0                            |
| 400               | 48                                   | 0.0                            | 530               | 42223                                | 92.4                           | 660               | 42641                                | 0.0                            | 790               | 747                                  | 0.0                            | 920               | 24                                   | 0.0                            |
| 405               | 201                                  | 0.0                            | 535               | 44137                                | 80.5                           | 665               | 37602                                | 0.0                            | 795               | 639                                  | 0.0                            | 925               | 22                                   | 0.0                            |
| 410               | 457                                  | 0.1                            | 540               | 46032                                | 68.2                           | 670               | 32798                                | 0.0                            | 800               | 547                                  | 0.0                            | 930               | 22                                   | 0.0                            |
| 415               | 925                                  | 0.3                            | 545               | 48553                                | 57.1                           | 675               | 28558                                | 0.0                            | 805               | 473                                  | 0.0                            | 935               | 17                                   | 0.0                            |
| 420               | 1816                                 | 1.1                            | 550               | 51408                                | 46.7                           | 680               | 24782                                | 0.0                            | 810               | 401                                  | 0.0                            | 940               | 13                                   | 0.0                            |
| 425               | 3217                                 | 2.5                            | 555               | 54711                                | 37.4                           | 685               | 21386                                | 0.0                            | 815               | 351                                  | 0.0                            | 945               | 6                                    | 0.0                            |
| 430               | 5520                                 | 5.9                            | 560               | 58847                                | 29.4                           | 690               | 18413                                | 0.0                            | 820               | 307                                  | 0.0                            | 950               | 10                                   | 0.0                            |
| 435               | 9225                                 | 12.5                           | 565               | 63386                                | 22.5                           | 695               | 15721                                | 0.0                            | 825               | 261                                  | 0.0                            | 955               | 11                                   | 0.0                            |
| 440               | 15522                                | 26.3                           | 570               | 68196                                | 16.9                           | 700               | 13432                                | 0.0                            | 830               | 228                                  | 0.0                            | 960               | 8                                    | 0.0                            |
| 445               | 27642                                | 55.2                           | 575               | 73613                                | 12.4                           | 705               | 11513                                | 0.0                            | 835               | 193                                  | 0.0                            | 965               | 12                                   | 0.0                            |
| 450               | 36602                                | 85.4                           | 580               | 79207                                | 9.0                            | 710               | 9780                                 | 0.0                            | 840               | 174                                  | 0.0                            | 970               | 3                                    | 0.0                            |
| 455               | 28292                                | 75.1                           | 585               | 84248                                | 6.3                            | 715               | 8356                                 | 0.0                            | 845               | 151                                  | 0.0                            | 975               | 8                                    | 0.0                            |
| 460               | 21166                                | 63.2                           | 590               | 88397                                | 4.4                            | 720               | 7161                                 | 0.0                            | 850               | 123                                  | 0.0                            | 980               | 2                                    | 0.0                            |
| 465               | 19092                                | 63.2                           | 595               | 91428                                | 3.0                            | 725               | 6067                                 | 0.0                            | 855               | 106                                  | 0.0                            | 985               | 13                                   | 0.0                            |
| 470               | 14951                                | 54.2                           | 600               | 93452                                | 2.0                            | 730               | 5164                                 | 0.0                            | 860               | 95                                   | 0.0                            | 990               | 16                                   | 0.0                            |
| 475               | 12606                                | 48.8                           | 605               | 93959                                | 1.3                            | 735               | 4393                                 | 0.0                            | 865               | 82                                   | 0.0                            | 995               | 20                                   | 0.0                            |
| 480               | 13323                                | 54.2                           | 610               | 93079                                | 0.9                            | 740               | 3694                                 | 0.0                            | 870               | 77                                   | 0.0                            | 1000              | 0                                    | 0.0                            |
| 485               | 15164                                | 63.3                           | 615               | 90707                                | 0.5                            | 745               | 3157                                 | 0.0                            | 875               | 65                                   | 0.0                            |                   |                                      |                                |

REPORT NUMBER: SP1-2407-157-9

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 9797**

**M/P: 2.26**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 0             | 0.0           | 490    | 18018         | 27.7          | 620    | 87426         | 1.1           | 750    | 2680          | 0.0           | 880    | 58            | 0.0           |
| 365    | 0             | 0.0           | 495    | 22295         | 36.0          | 625    | 83013         | 0.7           | 755    | 2287          | 0.0           | 885    | 46            | 0.0           |
| 370    | 0             | 0.0           | 500    | 26478         | 44.2          | 630    | 78077         | 0.4           | 760    | 1944          | 0.0           | 890    | 45            | 0.0           |
| 375    | 0             | 0.0           | 505    | 30524         | 51.8          | 635    | 72080         | 0.3           | 765    | 1653          | 0.0           | 895    | 41            | 0.0           |
| 380    | 0             | 0.0           | 510    | 33611         | 57.0          | 640    | 66249         | 0.2           | 770    | 1413          | 0.0           | 900    | 38            | 0.0           |
| 385    | 0             | 0.0           | 515    | 36490         | 60.5          | 645    | 59973         | 0.1           | 775    | 1198          | 0.0           | 905    | 33            | 0.0           |
| 390    | 0             | 0.0           | 520    | 38610         | 61.4          | 650    | 53972         | 0.1           | 780    | 1025          | 0.0           | 910    | 30            | 0.0           |
| 395    | 0             | 0.0           | 525    | 40511         | 60.6          | 655    | 48369         | 0.0           | 785    | 874           | 0.0           | 915    | 23            | 0.0           |
| 400    | 48            | 0.0           | 530    | 42223         | 58.2          | 660    | 42641         | 0.0           | 790    | 747           | 0.0           | 920    | 24            | 0.0           |
| 405    | 201           | 0.0           | 535    | 44137         | 55.0          | 665    | 37602         | 0.0           | 795    | 639           | 0.0           | 925    | 22            | 0.0           |
| 410    | 457           | 0.0           | 540    | 46032         | 50.9          | 670    | 32798         | 0.0           | 800    | 547           | 0.0           | 930    | 22            | 0.0           |
| 415    | 925           | 0.1           | 545    | 48553         | 46.6          | 675    | 28558         | 0.0           | 805    | 473           | 0.0           | 935    | 17            | 0.0           |
| 420    | 1816          | 0.3           | 550    | 51408         | 42.0          | 680    | 24782         | 0.0           | 810    | 401           | 0.0           | 940    | 13            | 0.0           |
| 425    | 3217          | 0.8           | 555    | 54711         | 37.4          | 685    | 21386         | 0.0           | 815    | 351           | 0.0           | 945    | 6             | 0.0           |
| 430    | 5520          | 1.9           | 560    | 58847         | 32.9          | 690    | 18413         | 0.0           | 820    | 307           | 0.0           | 950    | 10            | 0.0           |
| 435    | 9225          | 4.1           | 565    | 63386         | 28.4          | 695    | 15721         | 0.0           | 825    | 261           | 0.0           | 955    | 11            | 0.0           |
| 440    | 15522         | 8.7           | 570    | 68196         | 24.1          | 700    | 13432         | 0.0           | 830    | 228           | 0.0           | 960    | 8             | 0.0           |
| 445    | 27642         | 18.5          | 575    | 73613         | 20.0          | 705    | 11513         | 0.0           | 835    | 193           | 0.0           | 965    | 12            | 0.0           |
| 450    | 36602         | 28.3          | 580    | 79207         | 16.3          | 710    | 9780          | 0.0           | 840    | 174           | 0.0           | 970    | 3             | 0.0           |
| 455    | 28292         | 24.7          | 585    | 84248         | 12.9          | 715    | 8356          | 0.0           | 845    | 151           | 0.0           | 975    | 8             | 0.0           |
| 460    | 21166         | 20.4          | 590    | 88397         | 9.8           | 720    | 7161          | 0.0           | 850    | 123           | 0.0           | 980    | 2             | 0.0           |
| 465    | 19092         | 20.1          | 595    | 91428         | 7.3           | 725    | 6067          | 0.0           | 855    | 106           | 0.0           | 985    | 13            | 0.0           |
| 470    | 14951         | 17.2          | 600    | 93452         | 5.3           | 730    | 5164          | 0.0           | 860    | 95            | 0.0           | 990    | 16            | 0.0           |
| 475    | 12606         | 15.7          | 605    | 93959         | 3.7           | 735    | 4393          | 0.0           | 865    | 82            | 0.0           | 995    | 20            | 0.0           |
| 480    | 13323         | 18.0          | 610    | 93079         | 2.5           | 740    | 3694          | 0.0           | 870    | 77            | 0.0           | 1000   | 0             | 0.0           |
| 485    | 15164         | 21.9          | 615    | 90707         | 1.7           | 745    | 3157          | 0.0           | 875    | 65            | 0.0           |        |               |               |

**Summary**

$R_f = 84.7$   
 $R_g = 94.6$   
 CIE  $R_a = 80.9$   
 $R_g = -1.5$



**Color Vector Graphics**





Individual Sample Fidelity Index ( $R_{f,i}$ )

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 |            |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)