

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P633990

Luminaire Tested: GWS-SA2F-827-U-T3R-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P633990
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA2F-827-U-T3R-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (2) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III ROADWAY OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (32) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7479.6 lumens
Efficiency: N/A
Efficacy: 60.1 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B2 - U0 - G1


Input Watts (W): 124.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P633990
 CATALOG NUMBER: GWS-SA2F-827-U-T3R-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 18.7 fc
 Type II - Short - N/A

REPORT NUMBER: P633990
CATALOG NUMBER: GWS-SA2F-827-U-T3R-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 38-Deg Lateral - - - Horizontal Cone Through 55-Deg Vertical

REPORT NUMBER: P633990
 CATALOG NUMBER: GWS-SA2F-827-U-T3R-W-GRSBK

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 1457.3 | 0.0 | 1457.3 |
| | % Fixture | 19.5 | 0.0 | 19.5 |
| Street Side | Lumens | 6022.4 | 0.0 | 6022.4 |
| | % Fixture | 80.5 | 0.0 | 80.5 |
| Total | Lumens | 7479.6 | 0.0 | 7479.6 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 165.8 | 2.2 |
| 10°-20° | 446.5 | 6.0 |
| 20°-30° | 766.2 | 10.2 |
| 30°-40° | 1270.8 | 17.0 |
| 40°-50° | 1868.1 | 25.0 |
| 50°-60° | 2182.9 | 29.2 |
| 60°-70° | 739.9 | 9.9 |
| 70°-80° | 37.8 | 0.5 |
| 80°-90° | 1.5 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 7479.6 | 100.0 |
| 0°-180° | 7479.6 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P633990

CATALOG NUMBER: GWS-SA2F-827-U-T3R-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 823.3 | 11.0 | | | |
| FM (30°-60°) | 4517.5 | 60.4 | | | |
| FH (60°-80°) | 680.8 | 9.1 | | | G1/1800 |
| FVH (80°-90°) | 0.8 | 0.0 | | | G0/10 |
| BL (0°-30°) | 555.2 | 7.4 | B2/1000 | | |
| BM (30°-60°) | 804.4 | 10.8 | B1/1000 | | |
| BH (60°-80°) | 97.0 | 1.3 | B0/110 | | G0/110 |
| BVH (80°-90°) | 0.7 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G1
 Type II Short





REPORT NUMBER: P633990

CATALOG NUMBER: GWS-SA2F-827-U-T3R-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 38° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1793.7 | 1793.7 | 1793.7 | 1793.7 | 1793.7 | 1793.7 | 1793.7 | 1793.7 | 1793.7 | 1793.7 | 1793.7 |
| 2.5° | 1670.6 | 1667.1 | 1674.0 | 1687.7 | 1700.5 | 1704.8 | 1717.6 | 1735.5 | 1746.6 | 1773.1 | 1794.5 |
| 5° | 1595.3 | 1593.6 | 1600.4 | 1612.4 | 1629.5 | 1635.5 | 1655.2 | 1685.1 | 1715.0 | 1761.2 | 1806.5 |
| 7.5° | 1526.9 | 1526.1 | 1536.3 | 1562.8 | 1587.6 | 1595.3 | 1619.3 | 1656.0 | 1696.2 | 1767.2 | 1833.8 |
| 10° | 1437.2 | 1438.0 | 1457.7 | 1495.3 | 1540.6 | 1556.0 | 1594.5 | 1647.5 | 1699.6 | 1791.1 | 1883.4 |
| 12.5° | 1408.1 | 1409.8 | 1420.1 | 1449.1 | 1498.7 | 1518.4 | 1572.2 | 1652.6 | 1719.3 | 1825.3 | 1947.6 |
| 15° | 1479.0 | 1479.0 | 1470.5 | 1473.9 | 1496.1 | 1514.1 | 1570.5 | 1669.7 | 1752.6 | 1866.3 | 2010.8 |
| 17.5° | 1616.7 | 1611.6 | 1590.2 | 1561.1 | 1553.4 | 1559.4 | 1604.7 | 1706.5 | 1799.6 | 1914.2 | 2082.6 |
| 20° | 1803.1 | 1804.8 | 1762.9 | 1702.2 | 1653.5 | 1652.6 | 1680.0 | 1771.4 | 1867.2 | 1971.5 | 2160.4 |
| 22.5° | 2028.8 | 2021.9 | 1966.4 | 1883.4 | 1798.8 | 1792.0 | 1803.1 | 1870.6 | 1964.7 | 2062.1 | 2256.2 |
| 25° | 2290.4 | 2287.0 | 2208.3 | 2097.2 | 1985.2 | 1968.9 | 1968.9 | 2035.6 | 2104.0 | 2191.2 | 2370.8 |
| 27.5° | 2564.0 | 2564.0 | 2487.9 | 2359.6 | 2210.9 | 2181.8 | 2177.5 | 2256.2 | 2301.5 | 2318.6 | 2467.4 |
| 30° | 2845.2 | 2841.8 | 2766.6 | 2634.9 | 2475.9 | 2446.0 | 2434.0 | 2492.2 | 2524.6 | 2473.3 | 2587.9 |
| 32.5° | 3130.8 | 3136.8 | 3060.7 | 2938.4 | 2796.5 | 2776.8 | 2740.1 | 2740.1 | 2766.6 | 2694.8 | 2777.7 |
| 35° | 3437.7 | 3436.0 | 3376.2 | 3293.2 | 3171.8 | 3149.6 | 3088.9 | 2994.0 | 3034.2 | 3002.6 | 3040.2 |
| 37.5° | 3708.7 | 3721.6 | 3692.5 | 3630.9 | 3532.6 | 3510.4 | 3410.4 | 3238.5 | 3269.3 | 3318.9 | 3352.2 |
| 40° | 3984.0 | 3994.3 | 4023.4 | 4003.7 | 3879.7 | 3838.7 | 3660.9 | 3378.7 | 3412.9 | 3583.1 | 3678.8 |
| 42.5° | 4254.2 | 4259.3 | 4318.3 | 4350.8 | 4184.9 | 4113.1 | 3850.7 | 3464.2 | 3500.1 | 3790.0 | 3957.5 |
| 45° | 4426.0 | 4437.1 | 4534.6 | 4633.8 | 4454.2 | 4355.9 | 4015.7 | 3573.7 | 3589.0 | 3933.6 | 4163.6 |
| 47.5° | 4419.2 | 4444.8 | 4627.8 | 4808.2 | 4685.9 | 4579.9 | 4214.0 | 3748.9 | 3723.3 | 4068.7 | 4299.5 |
| 50° | 4281.5 | 4312.3 | 4574.8 | 4861.2 | 4852.6 | 4754.3 | 4434.6 | 4002.8 | 3922.5 | 4188.4 | 4316.6 |
| 52.5° | 3996.0 | 4084.9 | 4481.6 | 4868.0 | 4986.9 | 4937.3 | 4707.3 | 4344.8 | 4191.8 | 4360.2 | 4344.0 |
| 55° | 3378.7 | 3488.2 | 4198.6 | 4809.9 | 5108.3 | 5114.3 | 4993.7 | 4701.3 | 4484.2 | 4656.0 | 4512.4 |
| 57.5° | 2564.8 | 2652.0 | 3231.7 | 4281.5 | 4907.4 | 5005.7 | 5104.9 | 4889.4 | 4664.6 | 4857.8 | 4551.7 |
| 60° | 1545.7 | 1646.6 | 2023.6 | 3141.9 | 3963.5 | 4131.1 | 4520.1 | 4478.2 | 4207.2 | 4290.1 | 3732.7 |
| 62.5° | 626.7 | 679.7 | 934.5 | 1731.3 | 2494.7 | 2651.2 | 3023.9 | 3087.2 | 3020.5 | 2935.9 | 2263.9 |
| 65° | 229.1 | 250.5 | 374.5 | 715.6 | 1147.3 | 1204.6 | 1401.2 | 1513.2 | 1605.6 | 1367.1 | 842.1 |
| 67.5° | 141.9 | 155.6 | 243.7 | 367.6 | 417.2 | 388.1 | 395.0 | 471.1 | 449.7 | 277.9 | 150.5 |
| 70° | 105.2 | 116.3 | 190.7 | 254.8 | 168.4 | 130.0 | 88.1 | 94.0 | 84.6 | 74.4 | 73.5 |
| 72.5° | 72.7 | 82.9 | 142.8 | 150.5 | 65.0 | 46.2 | 32.5 | 45.3 | 51.3 | 50.4 | 52.2 |
| 75° | 47.9 | 55.6 | 89.8 | 59.0 | 16.2 | 12.8 | 11.1 | 23.9 | 30.8 | 30.8 | 31.6 |
| 77.5° | 28.2 | 32.5 | 31.6 | 12.0 | 3.4 | 3.4 | 2.6 | 4.3 | 6.8 | 7.7 | 9.4 |
| 80° | 3.4 | 2.6 | 1.7 | 1.7 | 1.7 | 1.7 | 1.7 | 1.7 | 2.6 | 2.6 | 2.6 |
| 82.5° | 0.9 | 0.9 | 0.9 | 1.7 | 1.7 | 1.7 | 1.7 | 1.7 | 1.7 | 2.6 | 2.6 |
| 85° | 0.0 | 0.0 | 0.9 | 0.9 | 1.7 | 1.7 | 1.7 | 1.7 | 1.7 | 2.6 | 2.6 |
| 87.5° | 0.0 | 0.0 | 0.9 | 0.9 | 1.7 | 1.7 | 1.7 | 1.7 | 1.7 | 2.6 | 2.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P633990

CATALOG NUMBER: GWS-SA2F-827-U-T3R-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1793.7 | 1793.7 | 1793.7 | 1793.7 | 1793.7 | 1793.7 | 1793.7 | 1793.7 | 1793.7 | 1793.7 | 1793.7 |
| 2.5° | 1810.8 | 1804.8 | 1829.6 | 1847.5 | 1862.1 | 1868.9 | 1859.5 | 1858.6 | 1858.6 | 1839.8 | 1834.7 |
| 5° | 1832.1 | 1834.7 | 1869.8 | 1885.1 | 1887.7 | 1879.2 | 1857.8 | 1843.3 | 1834.7 | 1815.0 | 1803.9 |
| 7.5° | 1873.2 | 1881.7 | 1915.1 | 1912.5 | 1889.4 | 1850.1 | 1793.7 | 1750.1 | 1721.9 | 1691.1 | 1672.3 |
| 10° | 1932.2 | 1948.4 | 1968.9 | 1933.0 | 1859.5 | 1759.5 | 1643.2 | 1560.3 | 1510.7 | 1475.6 | 1454.3 |
| 12.5° | 2004.0 | 2020.2 | 2013.4 | 1928.7 | 1775.7 | 1597.0 | 1447.4 | 1327.7 | 1270.4 | 1238.8 | 1216.6 |
| 15° | 2076.7 | 2086.9 | 2042.5 | 1877.4 | 1627.8 | 1387.6 | 1220.9 | 1102.0 | 1031.9 | 1006.3 | 987.5 |
| 17.5° | 2151.0 | 2148.5 | 2047.6 | 1776.6 | 1430.3 | 1151.6 | 987.5 | 906.2 | 886.6 | 882.3 | 880.6 |
| 20° | 2228.8 | 2205.7 | 2027.1 | 1632.1 | 1192.6 | 918.2 | 825.0 | 830.1 | 866.1 | 883.2 | 886.6 |
| 22.5° | 2317.7 | 2259.6 | 1975.8 | 1436.3 | 949.8 | 765.2 | 774.6 | 825.0 | 873.7 | 896.8 | 900.3 |
| 25° | 2412.6 | 2309.2 | 1890.3 | 1184.9 | 748.9 | 703.6 | 759.2 | 817.3 | 869.5 | 897.7 | 901.1 |
| 27.5° | 2475.1 | 2321.2 | 1750.1 | 931.9 | 642.9 | 679.7 | 738.7 | 794.2 | 848.1 | 878.9 | 883.2 |
| 30° | 2542.6 | 2316.0 | 1559.4 | 718.2 | 607.0 | 659.2 | 710.5 | 760.9 | 810.5 | 844.7 | 848.1 |
| 32.5° | 2641.8 | 2312.6 | 1326.9 | 583.1 | 592.5 | 642.9 | 680.5 | 722.4 | 756.6 | 776.3 | 773.7 |
| 35° | 2771.7 | 2308.3 | 1055.9 | 525.8 | 583.9 | 630.1 | 660.0 | 679.7 | 642.1 | 630.1 | 632.7 |
| 37.5° | 2938.4 | 2318.6 | 827.6 | 501.9 | 581.4 | 626.7 | 652.3 | 595.9 | 537.8 | 515.5 | 512.1 |
| 40° | 3123.1 | 2345.1 | 630.9 | 492.4 | 589.9 | 635.2 | 623.3 | 530.1 | 458.2 | 414.6 | 405.2 |
| 42.5° | 3308.6 | 2374.2 | 499.3 | 489.0 | 604.4 | 659.2 | 575.4 | 482.2 | 374.5 | 349.7 | 346.3 |
| 45° | 3446.3 | 2369.0 | 431.7 | 483.0 | 617.3 | 672.8 | 562.6 | 413.8 | 334.3 | 323.2 | 324.0 |
| 47.5° | 3515.5 | 2312.6 | 395.0 | 469.4 | 622.4 | 659.2 | 530.9 | 385.6 | 306.9 | 318.9 | 329.2 |
| 50° | 3478.8 | 2166.4 | 360.8 | 442.9 | 611.3 | 641.2 | 480.5 | 364.2 | 293.2 | 342.8 | 365.9 |
| 52.5° | 3434.3 | 1986.9 | 323.2 | 401.8 | 584.8 | 616.4 | 460.8 | 358.2 | 284.7 | 330.9 | 348.0 |
| 55° | 3493.3 | 1873.2 | 261.6 | 338.6 | 532.6 | 558.3 | 445.4 | 357.4 | 265.0 | 257.3 | 254.8 |
| 57.5° | 3410.4 | 1646.6 | 187.2 | 243.7 | 408.7 | 442.0 | 434.3 | 351.4 | 235.1 | 234.3 | 237.7 |
| 60° | 2635.8 | 1004.6 | 128.2 | 154.7 | 250.5 | 282.1 | 394.1 | 336.0 | 202.6 | 186.4 | 187.2 |
| 62.5° | 1497.9 | 427.5 | 88.1 | 95.8 | 128.2 | 152.2 | 300.9 | 305.2 | 187.2 | 177.8 | 187.2 |
| 65° | 521.5 | 153.0 | 68.4 | 64.1 | 71.0 | 81.2 | 172.7 | 236.0 | 170.1 | 153.9 | 155.6 |
| 67.5° | 107.7 | 76.1 | 60.7 | 53.0 | 53.0 | 53.0 | 88.1 | 147.0 | 140.2 | 122.3 | 124.0 |
| 70° | 68.4 | 65.0 | 53.0 | 45.3 | 43.6 | 40.2 | 50.4 | 81.2 | 96.6 | 88.9 | 89.8 |
| 72.5° | 50.4 | 49.6 | 41.9 | 36.8 | 32.5 | 29.1 | 31.6 | 40.2 | 49.6 | 51.3 | 52.2 |
| 75° | 30.8 | 31.6 | 27.4 | 23.1 | 20.5 | 18.0 | 18.8 | 18.8 | 18.8 | 17.1 | 18.8 |
| 77.5° | 9.4 | 10.3 | 8.5 | 6.8 | 6.0 | 6.0 | 6.0 | 5.1 | 4.3 | 2.6 | 2.6 |
| 80° | 2.6 | 2.6 | 2.6 | 2.6 | 2.6 | 1.7 | 1.7 | 0.9 | 0.9 | 0.0 | 0.0 |
| 82.5° | 2.6 | 2.6 | 2.6 | 2.6 | 1.7 | 1.7 | 0.9 | 0.9 | 0.0 | 0.0 | 0.0 |
| 85° | 2.6 | 2.6 | 2.6 | 2.6 | 1.7 | 1.7 | 0.9 | 0.9 | 0.0 | 0.0 | 0.0 |
| 87.5° | 2.6 | 2.6 | 2.6 | 2.6 | 1.7 | 1.7 | 0.9 | 0.9 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_g = -1.5$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)