

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P636452

Luminaire Tested: GWS-SA3F-827-U-T1-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P636452
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA3F-827-U-T1-W
Description: GALLEON WALL SLIM LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE I OPTICS
Light Source: (48) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 17941.2 lumens
Efficiency: N/A
Efficacy: 97.9 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification: Type I - Medium
BUG Rating: B4 - U0 - G4


Input Watts (W): 183.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P636452
 CATALOG NUMBER: GWS-SA3F-827-U-T1-W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 5.3 fc
 Type I - Medium - N/A

REPORT NUMBER: P636452
CATALOG NUMBER: GWS-SA3F-827-U-T1-W

Luminous Intensity Polar Plot



— Vertical Plane Through 89-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P636452

CATALOG NUMBER: GWS-SA3F-827-U-T1-W

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 8892.0 | 0.0 | 8892.0 |
| | % Fixture | 49.6 | 0.0 | 49.6 |
| Street Side | Lumens | 9049.2 | 0.0 | 9049.2 |
| | % Fixture | 50.4 | 0.0 | 50.4 |
| Total | Lumens | 17941.2 | 0.0 | 17941.2 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 302.1 | 1.7 |
| 10°-20° | 983.5 | 5.5 |
| 20°-30° | 1662.6 | 9.3 |
| 30°-40° | 2281.7 | 12.7 |
| 40°-50° | 2909.7 | 16.2 |
| 50°-60° | 3650.7 | 20.3 |
| 60°-70° | 4403.0 | 24.5 |
| 70°-80° | 1592.9 | 8.9 |
| 80°-90° | 154.9 | 0.9 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 17941.2 | 100.0 |
| 0°-180° | 17941.2 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P636452


CATALOG NUMBER: GWS-SA3F-827-U-T1-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1453.1 | 8.1 | | | |
| FM (30°-60°) | 4390.6 | 24.5 | | | |
| FH (60°-80°) | 3123.8 | 17.4 | | | G2/5000 |
| FVH (80°-90°) | 81.7 | 0.5 | | | G1/100 |
| BL (0°-30°) | 1495.1 | 8.3 | B3/2500 | | |
| BM (30°-60°) | 4451.6 | 24.8 | B3/5000 | | |
| BH (60°-80°) | 2872.1 | 16.0 | B4/5000 | | G4/5000 |
| BVH (80°-90°) | 73.2 | 0.4 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B4-U0-G4

Type I Medium





REPORT NUMBER: P636452
 CATALOG NUMBER: GWS-SA3F-827-U-T1-W

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° | 89° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|---------|---------|---------|
| 0° | 3011.3 | 3011.3 | 3011.3 | 3011.3 | 3011.3 | 3011.3 | 3011.3 | 3011.3 | 3011.3 | 3011.3 | 3011.3 |
| 2.5° | 3020.3 | 3017.7 | 3011.3 | 3030.6 | 3026.7 | 3028.0 | 3035.8 | 3030.6 | 3021.6 | 3006.1 | 3028.0 |
| 5° | 3105.3 | 3104.1 | 3089.9 | 3101.5 | 3088.6 | 3079.6 | 3078.3 | 3065.4 | 3055.1 | 3038.3 | 3061.5 |
| 7.5° | 3187.8 | 3186.5 | 3174.9 | 3195.5 | 3185.2 | 3174.9 | 3163.3 | 3137.6 | 3113.1 | 3088.6 | 3114.4 |
| 10° | 3251.0 | 3249.7 | 3247.1 | 3276.7 | 3279.3 | 3283.2 | 3278.0 | 3234.2 | 3191.7 | 3162.0 | 3187.8 |
| 12.5° | 3287.0 | 3290.9 | 3297.3 | 3351.5 | 3378.5 | 3404.3 | 3410.7 | 3374.7 | 3303.8 | 3261.3 | 3292.2 |
| 15° | 3262.5 | 3270.3 | 3302.5 | 3400.4 | 3475.2 | 3533.1 | 3557.6 | 3528.0 | 3436.5 | 3365.6 | 3400.4 |
| 17.5° | 3145.3 | 3151.7 | 3214.9 | 3364.3 | 3529.3 | 3663.3 | 3703.2 | 3685.2 | 3583.4 | 3497.1 | 3530.6 |
| 20° | 2982.9 | 2997.1 | 3065.4 | 3274.1 | 3520.3 | 3753.5 | 3860.4 | 3854.0 | 3743.2 | 3610.5 | 3650.4 |
| 22.5° | 2836.0 | 2852.8 | 2925.0 | 3155.6 | 3459.7 | 3776.7 | 4018.9 | 4035.7 | 3888.8 | 3723.8 | 3756.1 |
| 25° | 2671.1 | 2686.6 | 2779.4 | 3015.2 | 3355.3 | 3758.6 | 4154.2 | 4230.2 | 4053.7 | 3854.0 | 3883.6 |
| 27.5° | 2502.3 | 2513.9 | 2605.4 | 2856.7 | 3218.7 | 3725.1 | 4261.2 | 4444.1 | 4216.1 | 3944.2 | 3964.8 |
| 30° | 2354.1 | 2369.6 | 2453.4 | 2698.2 | 3069.3 | 3658.1 | 4348.8 | 4672.2 | 4402.9 | 4046.0 | 4062.7 |
| 32.5° | 2211.1 | 2224.0 | 2315.5 | 2542.3 | 2910.8 | 3555.0 | 4427.4 | 4940.2 | 4679.9 | 4235.4 | 4235.4 |
| 35° | 2030.7 | 2053.9 | 2157.0 | 2392.8 | 2761.3 | 3418.5 | 4484.1 | 5252.0 | 5058.8 | 4515.0 | 4516.3 |
| 37.5° | 1864.5 | 1877.4 | 1985.6 | 2224.0 | 2604.1 | 3263.8 | 4489.2 | 5575.5 | 5538.1 | 4870.6 | 4873.2 |
| 40° | 1675.1 | 1691.8 | 1807.8 | 2043.6 | 2423.7 | 3101.5 | 4440.3 | 5877.0 | 6040.6 | 5236.6 | 5222.4 |
| 42.5° | 1483.1 | 1507.6 | 1618.4 | 1849.0 | 2229.2 | 2903.0 | 4310.1 | 6164.3 | 6678.4 | 5660.5 | 5625.7 |
| 45° | 1297.5 | 1313.0 | 1423.8 | 1641.6 | 2006.2 | 2666.0 | 4101.4 | 6440.1 | 7436.1 | 6304.8 | 6254.5 |
| 47.5° | 1088.8 | 1095.2 | 1209.9 | 1418.7 | 1775.6 | 2401.8 | 3802.4 | 6686.2 | 8268.5 | 7157.8 | 7071.4 |
| 50° | 903.3 | 912.3 | 1002.5 | 1181.6 | 1493.4 | 2088.7 | 3430.1 | 6830.5 | 9328.9 | 8321.3 | 8171.8 |
| 52.5° | 730.6 | 739.6 | 811.8 | 954.8 | 1234.4 | 1731.8 | 2968.8 | 6797.0 | 10404.8 | 9765.7 | 9548.0 |
| 55° | 590.1 | 596.6 | 645.6 | 757.7 | 971.5 | 1377.4 | 2423.7 | 6496.7 | 11599.3 | 11652.1 | 11183.1 |
| 57.5° | 498.7 | 501.2 | 534.7 | 603.0 | 758.9 | 1061.7 | 1870.9 | 5788.1 | 12851.8 | 14059.1 | 13288.6 |
| 60° | 445.8 | 447.1 | 462.6 | 505.1 | 599.2 | 810.5 | 1371.0 | 4659.3 | 14149.3 | 17070.4 | 16013.8 |
| 62.5° | 412.3 | 412.3 | 425.2 | 449.7 | 497.4 | 623.6 | 1007.6 | 3346.3 | 15080.9 | 20347.1 | 19297.0 |
| 65° | 380.1 | 380.1 | 389.1 | 409.8 | 435.5 | 509.0 | 756.4 | 2158.3 | 15538.3 | 23086.5 | 22853.3 |
| 67.5° | 338.9 | 340.2 | 346.6 | 368.5 | 391.7 | 425.2 | 573.4 | 1459.9 | 14588.7 | 23844.2 | 25024.5 |
| 70° | 300.2 | 301.5 | 310.5 | 324.7 | 344.0 | 367.2 | 448.4 | 1006.3 | 10618.7 | 19858.8 | 22375.3 |
| 72.5° | 257.7 | 262.9 | 269.3 | 284.8 | 296.4 | 313.1 | 365.9 | 652.0 | 6178.5 | 12774.4 | 14791.0 |
| 75° | 211.3 | 217.8 | 225.5 | 241.0 | 248.7 | 255.1 | 301.5 | 465.2 | 2972.6 | 6473.6 | 7371.7 |
| 77.5° | 163.6 | 170.1 | 179.1 | 193.3 | 198.4 | 206.2 | 230.6 | 336.3 | 1423.8 | 2869.5 | 3093.8 |
| 80° | 109.5 | 112.1 | 119.8 | 136.6 | 145.6 | 150.8 | 170.1 | 229.4 | 618.5 | 1151.9 | 1141.6 |
| 82.5° | 67.0 | 68.3 | 70.9 | 81.2 | 85.0 | 90.2 | 110.8 | 140.4 | 295.1 | 1309.1 | 1501.1 |
| 85° | 24.5 | 23.2 | 21.9 | 28.3 | 33.5 | 38.7 | 51.5 | 70.9 | 128.9 | 899.4 | 1006.3 |
| 87.5° | 0.0 | 0.0 | 0.0 | 1.3 | 2.6 | 2.6 | 5.2 | 10.3 | 30.9 | 336.3 | 230.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P636452
 CATALOG NUMBER: GWS-SA3F-827-U-T1-W

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|---------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3011.3 | 3011.3 | 3011.3 | 3011.3 | 3011.3 | 3011.3 | 3011.3 | 3011.3 | 3011.3 | 3011.3 | 3011.3 |
| 2.5° | 3021.6 | 3007.4 | 3025.5 | 3038.3 | 3066.7 | 3077.0 | 3079.6 | 3070.6 | 3070.6 | 3055.1 | 3057.7 |
| 5° | 3056.4 | 3047.4 | 3077.0 | 3098.9 | 3140.1 | 3155.6 | 3165.9 | 3159.5 | 3163.3 | 3153.0 | 3155.6 |
| 7.5° | 3109.2 | 3101.5 | 3153.0 | 3195.5 | 3238.1 | 3256.1 | 3265.1 | 3260.0 | 3261.3 | 3248.4 | 3252.2 |
| 10° | 3182.7 | 3185.2 | 3247.1 | 3302.5 | 3359.2 | 3377.2 | 3381.1 | 3365.6 | 3352.7 | 3329.6 | 3330.8 |
| 12.5° | 3283.2 | 3296.1 | 3383.7 | 3445.5 | 3503.5 | 3529.3 | 3500.9 | 3444.2 | 3391.4 | 3351.5 | 3346.3 |
| 15° | 3392.7 | 3415.9 | 3542.2 | 3620.8 | 3683.9 | 3671.0 | 3587.3 | 3459.7 | 3355.3 | 3296.1 | 3284.5 |
| 17.5° | 3524.1 | 3558.9 | 3717.4 | 3811.5 | 3865.6 | 3783.1 | 3607.9 | 3417.2 | 3271.6 | 3191.7 | 3176.2 |
| 20° | 3647.8 | 3703.2 | 3902.9 | 4025.4 | 4031.8 | 3846.3 | 3598.9 | 3330.8 | 3147.9 | 3049.9 | 3029.3 |
| 22.5° | 3761.2 | 3832.1 | 4097.5 | 4253.4 | 4169.7 | 3874.6 | 3543.4 | 3208.4 | 2998.4 | 2883.7 | 2865.7 |
| 25° | 3884.9 | 3985.4 | 4324.3 | 4469.9 | 4307.5 | 3863.0 | 3427.5 | 3056.4 | 2818.0 | 2700.8 | 2687.9 |
| 27.5° | 3969.9 | 4096.2 | 4552.4 | 4691.5 | 4420.9 | 3797.3 | 3278.0 | 2890.2 | 2653.1 | 2542.3 | 2524.2 |
| 30° | 4067.9 | 4228.9 | 4803.6 | 4932.5 | 4490.5 | 3700.6 | 3118.2 | 2735.5 | 2499.7 | 2379.9 | 2367.0 |
| 32.5° | 4245.7 | 4448.0 | 5115.4 | 5187.6 | 4512.4 | 3580.8 | 2964.9 | 2586.1 | 2340.0 | 2220.1 | 2202.1 |
| 35° | 4531.7 | 4768.8 | 5553.5 | 5472.4 | 4495.7 | 3449.4 | 2819.3 | 2410.8 | 2176.3 | 2064.2 | 2046.2 |
| 37.5° | 4892.5 | 5187.6 | 6041.9 | 5728.8 | 4449.3 | 3305.1 | 2646.6 | 2263.9 | 2029.4 | 1916.0 | 1905.7 |
| 40° | 5228.8 | 5592.2 | 6589.5 | 5950.4 | 4355.2 | 3127.3 | 2480.4 | 2110.6 | 1870.9 | 1751.1 | 1727.9 |
| 42.5° | 5650.2 | 6133.4 | 7223.5 | 6142.4 | 4200.6 | 2914.6 | 2293.6 | 1921.2 | 1672.5 | 1564.3 | 1535.9 |
| 45° | 6290.6 | 6891.0 | 7960.5 | 6326.7 | 3969.9 | 2653.1 | 2059.1 | 1690.5 | 1454.7 | 1343.9 | 1322.0 |
| 47.5° | 7089.5 | 7838.1 | 8759.4 | 6436.2 | 3619.5 | 2377.3 | 1793.6 | 1447.0 | 1211.2 | 1086.2 | 1075.9 |
| 50° | 8211.8 | 9215.5 | 9616.3 | 6416.9 | 3227.8 | 2050.0 | 1494.7 | 1157.1 | 960.0 | 869.8 | 855.6 |
| 52.5° | 9578.9 | 10944.7 | 10542.7 | 6184.9 | 2811.6 | 1677.7 | 1164.8 | 908.4 | 761.5 | 697.1 | 685.5 |
| 55° | 11293.9 | 13015.4 | 11518.1 | 5687.6 | 2285.8 | 1284.7 | 914.9 | 716.4 | 615.9 | 577.3 | 572.1 |
| 57.5° | 13417.4 | 15696.8 | 12457.5 | 4850.0 | 1718.9 | 980.6 | 704.8 | 591.4 | 543.8 | 520.6 | 519.3 |
| 60° | 16220.0 | 18543.2 | 13273.1 | 3768.9 | 1230.5 | 749.9 | 582.4 | 528.3 | 490.9 | 475.5 | 474.2 |
| 62.5° | 19552.1 | 21128.0 | 13780.8 | 2566.7 | 925.2 | 597.9 | 512.8 | 479.3 | 457.4 | 448.4 | 447.1 |
| 65° | 22977.0 | 22761.8 | 13538.5 | 1681.5 | 702.2 | 507.7 | 460.0 | 442.0 | 422.6 | 413.6 | 413.6 |
| 67.5° | 25000.0 | 22416.5 | 11679.2 | 1167.4 | 556.6 | 445.8 | 414.9 | 398.2 | 365.9 | 358.2 | 358.2 |
| 70° | 22143.3 | 18164.4 | 7655.1 | 854.3 | 451.0 | 390.4 | 360.8 | 337.6 | 324.7 | 317.0 | 315.7 |
| 72.5° | 14645.4 | 11819.7 | 4070.5 | 592.7 | 376.2 | 332.4 | 305.4 | 296.4 | 280.9 | 273.2 | 271.9 |
| 75° | 7289.2 | 6208.1 | 2086.1 | 427.8 | 313.1 | 266.7 | 255.1 | 251.3 | 238.4 | 228.1 | 225.5 |
| 77.5° | 3038.3 | 2763.9 | 972.8 | 310.5 | 238.4 | 215.2 | 204.9 | 204.9 | 190.7 | 179.1 | 174.0 |
| 80° | 1145.5 | 1020.5 | 460.0 | 212.6 | 176.5 | 159.8 | 153.3 | 148.2 | 136.6 | 122.4 | 114.7 |
| 82.5° | 1532.1 | 1001.2 | 225.5 | 132.7 | 116.0 | 103.1 | 94.1 | 90.2 | 83.8 | 77.3 | 72.2 |
| 85° | 992.2 | 711.3 | 101.8 | 68.3 | 58.0 | 43.8 | 38.7 | 36.1 | 32.2 | 28.3 | 25.8 |
| 87.5° | 202.3 | 238.4 | 30.9 | 12.9 | 7.7 | 3.9 | 3.9 | 1.3 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_g = -1.5$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)