

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P638925

Luminaire Tested: GWS-SA4F-827-U-SLR-W-HSS

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P638925  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-44)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA4F-827-U-SLR-W-HSS  
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND  
SPILL LIGHT ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD  
Light Source: (64) 2700K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 15522.3 lumens  
Efficiency: N/A  
Efficacy: 68.9 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B2 - U0 - G3  
  
Input Watts (W): 225.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P638925  
 CATALOG NUMBER: GWS-SA4F-827-U-SLR-W-HSS

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 5 fc  
 Type IV - Short - N/A

REPORT NUMBER: P638925  
CATALOG NUMBER: GWS-SA4F-827-U-SLR-W-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral    - - - Horizontal Cone Through 62.5-Deg Vertical

REPORT NUMBER: P638925  
 CATALOG NUMBER: GWS-SA4F-827-U-SLR-W-HSS

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 1915.4   | 0.0    | 1915.4  |
|                    | % Fixture | 12.3     | 0.0    | 12.3    |
| <b>Street Side</b> | Lumens    | 13606.9  | 0.0    | 13606.9 |
|                    | % Fixture | 87.7     | 0.0    | 87.7    |
| <b>Total</b>       | Lumens    | 15522.3  | 0.0    | 15522.3 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 71.6    | 0.5       |
| 10°-20°   | 270.6   | 1.7       |
| 20°-30°   | 588.3   | 3.8       |
| 30°-40°   | 965.6   | 6.2       |
| 40°-50°   | 1775.1  | 11.4      |
| 50°-60°   | 3812.0  | 24.6      |
| 60°-70°   | 5120.2  | 33.0      |
| 70°-80°   | 2666.1  | 17.2      |
| 80°-90°   | 252.8   | 1.6       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 15522.3 | 100.0     |
| 0°-180°   | 15522.3 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P638925


CATALOG NUMBER: GWS-SA4F-827-U-SLR-W-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 655.7  | 4.2       |                         |      |         |
| FM (30°-60°)   | 5448.1 | 35.1      |                         |      |         |
| FH (60°-80°)   | 7261.5 | 46.8      |                         |      | G3/7500 |
| FVH (80°-90°)  | 241.5  | 1.6       |                         |      | G3/500  |
| BL (0°-30°)    | 274.8  | 1.8       | B1/500                  |      |         |
| BM (30°-60°)   | 1104.6 | 7.1       | B2/2500                 |      |         |
| BH (60°-80°)   | 524.8  | 3.4       | B2/1000                 |      | G2/1000 |
| BVH (80°-90°)  | 11.3   | 0.1       |                         |      | G1/100  |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B2-U0-G3**

Type IV Short





REPORT NUMBER: P638925

CATALOG NUMBER: GWS-SA4F-827-U-SLR-W-HSS

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 1°      | 5°      | 15°     | 25°     | 35°     | 45°     | 55°     | 65°     | 75°     | 85°     |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 806.8   | 806.8   | 806.8   | 806.8   | 806.8   | 806.8   | 806.8   | 806.8   | 806.8   | 806.8   | 806.8   |
| 2.5°  | 823.0   | 826.6   | 830.1   | 842.7   | 851.7   | 858.8   | 860.6   | 855.2   | 842.7   | 830.1   | 812.2   |
| 5°    | 797.9   | 801.5   | 814.0   | 848.1   | 882.1   | 909.0   | 918.0   | 912.6   | 882.1   | 842.7   | 801.5   |
| 7.5°  | 796.1   | 803.2   | 833.7   | 905.4   | 979.0   | 1034.5  | 1048.9  | 1036.3  | 979.0   | 900.1   | 815.8   |
| 10°   | 860.6   | 873.2   | 918.0   | 1047.1  | 1181.6  | 1280.2  | 1319.6  | 1265.8  | 1174.4  | 1031.0  | 892.9   |
| 12.5° | 1029.2  | 1050.7  | 1136.7  | 1325.0  | 1533.0  | 1663.9  | 1717.7  | 1651.3  | 1507.9  | 1299.9  | 1081.2  |
| 15°   | 1294.5  | 1326.8  | 1455.9  | 1737.4  | 1983.0  | 2099.6  | 2117.5  | 2079.8  | 1913.1  | 1683.6  | 1389.5  |
| 17.5° | 1669.3  | 1715.9  | 1916.7  | 2203.6  | 2381.1  | 2422.3  | 2416.9  | 2377.5  | 2255.6  | 2097.8  | 1819.9  |
| 20°   | 2117.5  | 2173.1  | 2370.3  | 2607.0  | 2624.9  | 2576.5  | 2549.6  | 2526.3  | 2485.1  | 2458.2  | 2241.2  |
| 22.5° | 2569.3  | 2637.5  | 2843.6  | 2902.8  | 2741.4  | 2601.6  | 2535.3  | 2553.2  | 2614.1  | 2746.8  | 2659.0  |
| 25°   | 3019.4  | 3083.9  | 3277.5  | 3118.0  | 2795.2  | 2562.1  | 2477.9  | 2520.9  | 2666.1  | 2953.0  | 3066.0  |
| 27.5° | 3544.7  | 3593.1  | 3707.9  | 3265.0  | 2804.2  | 2529.9  | 2447.4  | 2513.7  | 2691.2  | 3082.1  | 3512.4  |
| 30°   | 4091.5  | 4120.2  | 4064.7  | 3304.4  | 2773.7  | 2481.5  | 2416.9  | 2513.7  | 2734.3  | 3168.2  | 3847.7  |
| 32.5° | 4493.2  | 4498.6  | 4317.5  | 3308.0  | 2757.6  | 2442.0  | 2388.2  | 2503.0  | 2775.5  | 3239.9  | 4172.2  |
| 35°   | 4907.3  | 4880.5  | 4559.5  | 3361.8  | 2800.6  | 2456.4  | 2409.7  | 2533.5  | 2840.1  | 3324.2  | 4457.3  |
| 37.5° | 5326.9  | 5278.5  | 4830.3  | 3449.7  | 2911.8  | 2612.4  | 2583.7  | 2689.4  | 2944.1  | 3440.7  | 4771.1  |
| 40°   | 5757.2  | 5690.9  | 5111.7  | 3582.3  | 3159.2  | 3143.1  | 3241.7  | 3229.1  | 3229.1  | 3589.5  | 5093.8  |
| 42.5° | 6282.6  | 6205.5  | 5527.7  | 3957.1  | 3736.5  | 4096.9  | 4365.9  | 4199.1  | 3890.7  | 3932.0  | 5513.4  |
| 45°   | 6976.4  | 6910.1  | 6248.5  | 4674.3  | 4642.0  | 5470.3  | 5832.5  | 5502.6  | 4735.2  | 4722.7  | 6214.4  |
| 47.5° | 8086.3  | 8073.7  | 7397.8  | 5506.2  | 5750.0  | 7218.5  | 7917.7  | 7283.0  | 5698.0  | 5560.0  | 7541.2  |
| 50°   | 9646.2  | 9608.5  | 8830.4  | 6481.6  | 7067.9  | 9384.4  | 10632.3 | 9574.4  | 6861.7  | 6537.2  | 9318.0  |
| 52.5° | 11403.3 | 11442.7 | 10836.7 | 7546.6  | 8468.2  | 11794.1 | 13531.5 | 12199.3 | 8125.7  | 7779.7  | 11553.9 |
| 55°   | 13058.2 | 13284.1 | 13124.5 | 8792.7  | 9836.2  | 14454.9 | 16715.8 | 15078.8 | 9691.0  | 9405.9  | 14060.4 |
| 57.5° | 14352.7 | 14989.2 | 16108.0 | 10603.6 | 11444.5 | 17567.5 | 20271.3 | 18200.4 | 11518.0 | 12046.9 | 17472.5 |
| 60°   | 14424.4 | 15267.1 | 17865.1 | 14392.1 | 13513.6 | 20237.2 | 23821.3 | 21250.2 | 14390.3 | 16531.1 | 20145.8 |
| 62.5° | 13343.3 | 14246.9 | 16721.2 | 16113.4 | 15767.3 | 22508.9 | 25643.0 | 23473.5 | 17216.1 | 19157.8 | 19353.3 |
| 65°   | 12106.1 | 13018.7 | 15444.6 | 14160.8 | 15505.6 | 22412.1 | 25180.4 | 23525.5 | 17472.5 | 17372.0 | 17935.0 |
| 67.5° | 10236.0 | 11055.4 | 13251.8 | 12534.6 | 14291.7 | 21330.9 | 23043.2 | 22042.7 | 16097.2 | 16247.9 | 16498.9 |
| 70°   | 7471.3  | 8260.2  | 10298.8 | 10334.7 | 12480.8 | 19382.0 | 19799.7 | 19661.7 | 14824.2 | 14983.8 | 14266.6 |
| 72.5° | 5396.8  | 6062.0  | 7820.9  | 8475.4  | 9963.5  | 16253.2 | 15964.6 | 16497.1 | 12719.3 | 13345.0 | 11458.8 |
| 75°   | 3880.0  | 4378.4  | 5737.5  | 7372.7  | 7898.0  | 12070.2 | 11428.4 | 12776.7 | 10205.6 | 11491.1 | 8615.2  |
| 77.5° | 1574.2  | 1749.9  | 2257.3  | 4966.5  | 5190.6  | 8120.3  | 6996.2  | 9280.4  | 7275.9  | 7550.2  | 4175.8  |
| 80°   | 64.5    | 71.7    | 93.2    | 2563.9  | 3559.0  | 4568.5  | 3743.7  | 4961.1  | 4805.1  | 3040.9  | 986.1   |
| 82.5° | 7.2     | 7.2     | 16.1    | 738.7   | 1558.1  | 2520.9  | 1764.3  | 2858.0  | 2433.1  | 1289.1  | 448.2   |
| 85°   | 1.8     | 1.8     | 3.6     | 84.3    | 365.8   | 403.4   | 238.5   | 876.8   | 1131.4  | 527.1   | 0.0     |
| 87.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 9.0     | 16.1    | 17.9    | 0.0     |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P638925

CATALOG NUMBER: GWS-SA4F-827-U-SLR-W-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 90°     | 95°     | 105°   | 115°   | 125°  | 135°  | 145°  | 155°  | 165°  | 175°  | 180°  |
|-------|---------|---------|--------|--------|-------|-------|-------|-------|-------|-------|-------|
| 0°    | 806.8   | 806.8   | 806.8  | 806.8  | 806.8 | 806.8 | 806.8 | 806.8 | 806.8 | 806.8 | 806.8 |
| 2.5°  | 812.2   | 803.2   | 792.5  | 781.7  | 776.4 | 762.0 | 756.6 | 753.0 | 749.5 | 751.3 | 751.3 |
| 5°    | 785.3   | 765.6   | 742.3  | 719.0  | 706.4 | 692.1 | 684.9 | 681.3 | 683.1 | 690.3 | 690.3 |
| 7.5°  | 781.7   | 744.1   | 693.9  | 663.4  | 649.1 | 638.3 | 631.1 | 627.5 | 629.3 | 638.3 | 641.9 |
| 10°   | 840.9   | 774.6   | 684.9  | 632.9  | 616.8 | 606.0 | 598.9 | 593.5 | 589.9 | 597.1 | 598.9 |
| 12.5° | 968.2   | 876.8   | 727.9  | 629.3  | 600.6 | 586.3 | 580.9 | 570.2 | 564.8 | 568.4 | 570.2 |
| 15°   | 1231.8  | 1074.0  | 814.0  | 643.7  | 586.3 | 570.2 | 561.2 | 552.2 | 543.3 | 541.5 | 543.3 |
| 17.5° | 1576.0  | 1350.1  | 944.9  | 677.7  | 575.5 | 555.8 | 543.3 | 530.7 | 518.2 | 516.4 | 514.6 |
| 20°   | 2002.7  | 1689.0  | 1127.8 | 731.5  | 566.6 | 543.3 | 525.3 | 507.4 | 491.3 | 485.9 | 485.9 |
| 22.5° | 2391.8  | 2097.8  | 1362.7 | 797.9  | 554.0 | 525.3 | 503.8 | 482.3 | 464.4 | 455.4 | 453.6 |
| 25°   | 2867.0  | 2531.7  | 1644.1 | 875.0  | 536.1 | 502.0 | 478.7 | 457.2 | 439.3 | 428.5 | 424.9 |
| 27.5° | 3345.7  | 2988.9  | 1963.3 | 975.4  | 514.6 | 478.7 | 457.2 | 437.5 | 417.8 | 405.2 | 401.6 |
| 30°   | 3810.1  | 3481.9  | 2321.9 | 1100.9 | 498.4 | 455.4 | 437.5 | 417.8 | 399.8 | 380.1 | 374.7 |
| 32.5° | 4308.5  | 3985.8  | 2723.5 | 1240.7 | 485.9 | 439.3 | 419.6 | 401.6 | 378.3 | 360.4 | 351.4 |
| 35°   | 4789.0  | 4505.7  | 3166.4 | 1377.0 | 473.3 | 424.9 | 403.4 | 385.5 | 360.4 | 340.7 | 328.1 |
| 37.5° | 5273.1  | 5034.6  | 3629.0 | 1459.5 | 455.4 | 405.2 | 385.5 | 371.1 | 342.5 | 319.1 | 304.8 |
| 40°   | 5785.9  | 5581.5  | 4129.2 | 1425.4 | 439.3 | 383.7 | 372.9 | 356.8 | 324.5 | 297.6 | 279.7 |
| 42.5° | 6348.9  | 6103.3  | 4638.4 | 1294.5 | 424.9 | 365.8 | 355.0 | 338.9 | 308.4 | 276.1 | 252.8 |
| 45°   | 7057.1  | 6675.2  | 5056.2 | 1097.3 | 432.1 | 347.8 | 326.3 | 322.7 | 294.0 | 252.8 | 224.1 |
| 47.5° | 8274.5  | 7553.8  | 5380.7 | 970.0  | 480.5 | 328.1 | 303.0 | 312.0 | 281.5 | 229.5 | 197.2 |
| 50°   | 10137.4 | 9009.7  | 5683.7 | 961.0  | 554.0 | 319.1 | 281.5 | 304.8 | 268.9 | 206.2 | 173.9 |
| 52.5° | 11912.5 | 10488.9 | 5877.3 | 1039.9 | 618.6 | 342.5 | 260.0 | 295.8 | 260.0 | 190.1 | 157.8 |
| 55°   | 13610.4 | 11342.3 | 5531.3 | 1097.3 | 679.5 | 412.4 | 243.8 | 281.5 | 249.2 | 181.1 | 152.4 |
| 57.5° | 15441.0 | 11722.4 | 4355.1 | 1213.8 | 722.6 | 471.6 | 247.4 | 260.0 | 234.9 | 175.7 | 150.6 |
| 60°   | 15987.9 | 11236.5 | 2628.5 | 1366.2 | 699.3 | 489.5 | 274.3 | 231.3 | 215.2 | 165.0 | 145.2 |
| 62.5° | 15138.0 | 10083.6 | 1550.9 | 1244.3 | 679.5 | 462.6 | 313.8 | 213.4 | 195.4 | 150.6 | 134.5 |
| 65°   | 13866.8 | 8518.4  | 1011.2 | 1050.7 | 720.8 | 412.4 | 333.5 | 204.4 | 177.5 | 136.3 | 118.3 |
| 67.5° | 12414.5 | 6861.7  | 708.2  | 620.4  | 665.2 | 371.1 | 281.5 | 202.6 | 159.6 | 114.7 | 96.8  |
| 70°   | 10456.6 | 5138.6  | 498.4  | 410.6  | 554.0 | 329.9 | 218.7 | 197.2 | 139.9 | 93.2  | 75.3  |
| 72.5° | 8079.1  | 3216.6  | 371.1  | 265.4  | 394.5 | 268.9 | 173.9 | 166.7 | 113.0 | 77.1  | 57.4  |
| 75°   | 5958.0  | 1834.2  | 261.8  | 191.8  | 260.0 | 204.4 | 129.1 | 118.3 | 96.8  | 73.5  | 52.0  |
| 77.5° | 3110.8  | 918.0   | 163.2  | 147.0  | 148.8 | 127.3 | 93.2  | 86.1  | 89.6  | 73.5  | 48.4  |
| 80°   | 597.1   | 182.9   | 98.6   | 107.6  | 80.7  | 80.7  | 68.1  | 71.7  | 78.9  | 59.2  | 41.2  |
| 82.5° | 249.2   | 39.4    | 53.8   | 61.0   | 50.2  | 55.6  | 55.6  | 57.4  | 55.6  | 43.0  | 30.5  |
| 85°   | 0.0     | 0.0     | 23.3   | 25.1   | 34.1  | 34.1  | 28.7  | 28.7  | 28.7  | 25.1  | 17.9  |
| 87.5° | 0.0     | 0.0     | 0.0    | 0.0    | 1.8   | 5.4   | 10.8  | 12.6  | 14.3  | 10.8  | 7.2   |
| 90°   | 0.0     | 0.0     | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |





REPORT NUMBER: P638925  
 CATALOG NUMBER: GWS-SA4F-827-U-SLR-W-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 185°  | 195°  | 205°  | 215°  | 225°  | 235°  | 245°  | 255°  | 265°  | 270°  | 275°  |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°    | 806.8 | 806.8 | 806.8 | 806.8 | 806.8 | 806.8 | 806.8 | 806.8 | 806.8 | 806.8 | 806.8 |
| 2.5°  | 749.5 | 745.9 | 751.3 | 754.8 | 758.4 | 758.4 | 754.8 | 751.3 | 745.9 | 751.3 | 745.9 |
| 5°    | 692.1 | 697.5 | 706.4 | 710.0 | 713.6 | 706.4 | 702.8 | 692.1 | 683.1 | 684.9 | 681.3 |
| 7.5°  | 647.3 | 652.6 | 663.4 | 670.6 | 670.6 | 667.0 | 656.2 | 645.5 | 631.1 | 631.1 | 629.3 |
| 10°   | 606.0 | 613.2 | 625.7 | 634.7 | 638.3 | 634.7 | 624.0 | 609.6 | 597.1 | 597.1 | 591.7 |
| 12.5° | 572.0 | 580.9 | 595.3 | 607.8 | 611.4 | 607.8 | 597.1 | 582.7 | 568.4 | 568.4 | 564.8 |
| 15°   | 543.3 | 554.0 | 570.2 | 584.5 | 589.9 | 584.5 | 572.0 | 554.0 | 539.7 | 541.5 | 536.1 |
| 17.5° | 516.4 | 525.3 | 546.9 | 563.0 | 568.4 | 563.0 | 546.9 | 523.5 | 509.2 | 512.8 | 509.2 |
| 20°   | 485.9 | 496.7 | 518.2 | 536.1 | 541.5 | 536.1 | 518.2 | 493.1 | 478.7 | 478.7 | 480.5 |
| 22.5° | 453.6 | 464.4 | 485.9 | 498.4 | 505.6 | 500.2 | 482.3 | 459.0 | 444.7 | 444.7 | 446.4 |
| 25°   | 424.9 | 430.3 | 446.4 | 459.0 | 460.8 | 455.4 | 441.1 | 423.1 | 412.4 | 417.8 | 419.6 |
| 27.5° | 398.0 | 398.0 | 405.2 | 412.4 | 410.6 | 405.2 | 399.8 | 385.5 | 383.7 | 389.1 | 394.5 |
| 30°   | 369.4 | 360.4 | 356.8 | 351.4 | 349.6 | 347.8 | 353.2 | 353.2 | 356.8 | 364.0 | 369.4 |
| 32.5° | 344.2 | 326.3 | 310.2 | 294.0 | 285.1 | 292.3 | 306.6 | 319.1 | 331.7 | 342.5 | 347.8 |
| 35°   | 315.6 | 286.9 | 260.0 | 238.5 | 224.1 | 234.9 | 258.2 | 281.5 | 303.0 | 317.4 | 326.3 |
| 37.5° | 286.9 | 245.6 | 213.4 | 186.5 | 175.7 | 184.7 | 209.8 | 242.1 | 274.3 | 292.3 | 304.8 |
| 40°   | 256.4 | 204.4 | 166.7 | 145.2 | 134.5 | 143.4 | 168.5 | 200.8 | 243.8 | 267.2 | 283.3 |
| 42.5° | 225.9 | 168.5 | 134.5 | 113.0 | 107.6 | 113.0 | 132.7 | 165.0 | 211.6 | 240.3 | 261.8 |
| 45°   | 195.4 | 139.9 | 107.6 | 91.4  | 86.1  | 91.4  | 107.6 | 134.5 | 181.1 | 213.4 | 238.5 |
| 47.5° | 168.5 | 118.3 | 89.6  | 75.3  | 71.7  | 77.1  | 89.6  | 113.0 | 152.4 | 184.7 | 213.4 |
| 50°   | 147.0 | 104.0 | 77.1  | 64.5  | 61.0  | 66.3  | 77.1  | 95.0  | 129.1 | 157.8 | 188.3 |
| 52.5° | 132.7 | 96.8  | 68.1  | 55.6  | 53.8  | 57.4  | 66.3  | 80.7  | 109.4 | 134.5 | 163.2 |
| 55°   | 129.1 | 96.8  | 62.8  | 50.2  | 48.4  | 52.0  | 59.2  | 69.9  | 95.0  | 116.5 | 141.6 |
| 57.5° | 132.7 | 104.0 | 59.2  | 43.0  | 41.2  | 44.8  | 52.0  | 61.0  | 82.5  | 100.4 | 123.7 |
| 60°   | 132.7 | 105.8 | 52.0  | 34.1  | 32.3  | 35.9  | 43.0  | 53.8  | 73.5  | 87.9  | 107.6 |
| 62.5° | 120.1 | 96.8  | 43.0  | 26.9  | 23.3  | 26.9  | 35.9  | 44.8  | 64.5  | 78.9  | 95.0  |
| 65°   | 104.0 | 82.5  | 35.9  | 19.7  | 16.1  | 19.7  | 28.7  | 37.7  | 55.6  | 68.1  | 86.1  |
| 67.5° | 84.3  | 62.8  | 26.9  | 14.3  | 10.8  | 14.3  | 21.5  | 30.5  | 46.6  | 59.2  | 77.1  |
| 70°   | 62.8  | 44.8  | 21.5  | 12.6  | 10.8  | 12.6  | 19.7  | 28.7  | 41.2  | 53.8  | 71.7  |
| 72.5° | 46.6  | 30.5  | 17.9  | 12.6  | 9.0   | 12.6  | 17.9  | 26.9  | 39.4  | 52.0  | 68.1  |
| 75°   | 39.4  | 25.1  | 16.1  | 10.8  | 9.0   | 10.8  | 16.1  | 25.1  | 35.9  | 48.4  | 64.5  |
| 77.5° | 37.7  | 23.3  | 14.3  | 9.0   | 7.2   | 9.0   | 14.3  | 21.5  | 32.3  | 44.8  | 62.8  |
| 80°   | 32.3  | 19.7  | 12.6  | 7.2   | 5.4   | 7.2   | 12.6  | 17.9  | 25.1  | 34.1  | 48.4  |
| 82.5° | 25.1  | 16.1  | 9.0   | 3.6   | 1.8   | 3.6   | 9.0   | 10.8  | 16.1  | 19.7  | 28.7  |
| 85°   | 16.1  | 9.0   | 3.6   | 0.0   | 0.0   | 0.0   | 3.6   | 7.2   | 7.2   | 9.0   | 14.3  |
| 87.5° | 7.2   | 1.8   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 1.8   | 3.6   | 5.4   |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P638925  
 CATALOG NUMBER: GWS-SA4F-827-U-SLR-W-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 285°  | 295°  | 305°  | 315°  | 325°  | 335°   | 345°   | 355°    | 359°    | 360°    |
|-------|-------|-------|-------|-------|-------|--------|--------|---------|---------|---------|
| 0°    | 806.8 | 806.8 | 806.8 | 806.8 | 806.8 | 806.8  | 806.8  | 806.8   | 806.8   | 806.8   |
| 2.5°  | 756.6 | 758.4 | 762.0 | 767.4 | 779.9 | 790.7  | 801.5  | 815.8   | 823.0   | 823.0   |
| 5°    | 684.9 | 686.7 | 688.5 | 695.7 | 713.6 | 727.9  | 751.3  | 779.9   | 794.3   | 797.9   |
| 7.5°  | 629.3 | 632.9 | 636.5 | 641.9 | 659.8 | 679.5  | 710.0  | 763.8   | 790.7   | 796.1   |
| 10°   | 597.1 | 602.4 | 609.6 | 620.4 | 636.5 | 658.0  | 710.0  | 806.8   | 851.7   | 860.6   |
| 12.5° | 572.0 | 580.9 | 588.1 | 600.6 | 620.4 | 654.4  | 758.4  | 928.8   | 1007.6  | 1029.2  |
| 15°   | 546.9 | 557.6 | 568.4 | 580.9 | 602.4 | 667.0  | 851.7  | 1147.5  | 1278.4  | 1294.5  |
| 17.5° | 521.8 | 534.3 | 548.6 | 563.0 | 589.9 | 697.5  | 998.7  | 1450.5  | 1633.4  | 1669.3  |
| 20°   | 493.1 | 509.2 | 528.9 | 546.9 | 577.3 | 745.9  | 1203.1 | 1810.9  | 2040.4  | 2117.5  |
| 22.5° | 462.6 | 482.3 | 505.6 | 528.9 | 563.0 | 805.0  | 1450.5 | 2198.2  | 2519.1  | 2569.3  |
| 25°   | 437.5 | 457.2 | 478.7 | 502.0 | 539.7 | 876.8  | 1749.9 | 2678.7  | 2970.9  | 3019.4  |
| 27.5° | 414.2 | 433.9 | 453.6 | 475.1 | 516.4 | 970.0  | 2110.3 | 3189.7  | 3494.5  | 3544.7  |
| 30°   | 389.1 | 412.4 | 432.1 | 453.6 | 494.9 | 1084.7 | 2526.3 | 3756.3  | 4044.9  | 4091.5  |
| 32.5° | 367.6 | 390.9 | 410.6 | 432.1 | 478.7 | 1210.3 | 2963.8 | 4258.3  | 4493.2  | 4493.2  |
| 35°   | 349.6 | 374.7 | 389.1 | 417.8 | 466.2 | 1290.9 | 3377.9 | 4737.0  | 4914.5  | 4907.3  |
| 37.5° | 329.9 | 360.4 | 371.1 | 390.9 | 450.0 | 1299.9 | 3767.0 | 5242.6  | 5373.5  | 5326.9  |
| 40°   | 310.2 | 342.5 | 358.6 | 369.4 | 432.1 | 1226.4 | 4193.7 | 5707.0  | 5818.2  | 5757.2  |
| 42.5° | 292.3 | 317.4 | 340.7 | 353.2 | 421.3 | 1097.3 | 4536.2 | 6203.7  | 6336.3  | 6282.6  |
| 45°   | 274.3 | 295.8 | 310.2 | 333.5 | 428.5 | 1007.6 | 4830.3 | 6782.8  | 7015.9  | 6976.4  |
| 47.5° | 256.4 | 274.3 | 283.3 | 319.1 | 476.9 | 966.4  | 5009.5 | 7679.3  | 8118.6  | 8086.3  |
| 50°   | 236.7 | 258.2 | 258.2 | 315.6 | 548.6 | 980.8  | 5165.5 | 8977.4  | 9656.9  | 9646.2  |
| 52.5° | 216.9 | 240.3 | 236.7 | 342.5 | 604.2 | 1047.1 | 5343.0 | 10123.1 | 11304.7 | 11403.3 |
| 55°   | 197.2 | 218.7 | 222.3 | 396.2 | 636.5 | 1104.5 | 4656.3 | 10605.4 | 12712.1 | 13058.2 |
| 57.5° | 175.7 | 188.3 | 231.3 | 437.5 | 625.7 | 1271.2 | 3189.7 | 10693.2 | 13610.4 | 14352.7 |
| 60°   | 152.4 | 163.2 | 261.8 | 428.5 | 591.7 | 1174.4 | 2008.1 | 9904.3  | 13483.1 | 14424.4 |
| 62.5° | 132.7 | 150.6 | 276.1 | 378.3 | 602.4 | 1018.4 | 1280.2 | 8441.3  | 12269.3 | 13343.3 |
| 65°   | 116.5 | 145.2 | 251.0 | 342.5 | 609.6 | 690.3  | 864.2  | 6867.1  | 11084.1 | 12106.1 |
| 67.5° | 104.0 | 161.4 | 206.2 | 304.8 | 523.5 | 485.9  | 593.5  | 5335.9  | 9319.8  | 10236.0 |
| 70°   | 95.0  | 165.0 | 168.5 | 261.8 | 405.2 | 312.0  | 390.9  | 3591.3  | 6424.2  | 7471.3  |
| 72.5° | 86.1  | 121.9 | 127.3 | 209.8 | 261.8 | 190.1  | 252.8  | 2054.7  | 4683.2  | 5396.8  |
| 75°   | 82.5  | 82.5  | 87.9  | 136.3 | 145.2 | 138.1  | 163.2  | 1226.4  | 3358.2  | 3880.0  |
| 77.5° | 77.1  | 62.8  | 55.6  | 87.9  | 78.9  | 98.6   | 96.8   | 545.1   | 1455.9  | 1574.2  |
| 80°   | 61.0  | 44.8  | 37.7  | 55.6  | 53.8  | 66.3   | 57.4   | 44.8    | 66.3    | 64.5    |
| 82.5° | 37.7  | 28.7  | 26.9  | 34.1  | 30.5  | 34.1   | 26.9   | 7.2     | 7.2     | 7.2     |
| 85°   | 17.9  | 16.1  | 14.3  | 14.3  | 16.1  | 14.3   | 10.8   | 3.6     | 1.8     | 1.8     |
| 87.5° | 9.0   | 9.0   | 7.2   | 5.4   | 7.2   | 7.2    | 5.4    | 1.8     | 0.0     | 0.0     |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     |

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2407-157-9  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/03/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Invue  
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**  
 Description: Epic Modern Light Square 40W 5WQ Optic

**Spectral Parameters**

CCT (K): 2764  
 CIE u': 0.2591  
 CIE v': 0.5290  
 Duv: 0.0020  
 CIE x: 0.4581  
 CIE y: 0.4156  
 CIE z: 0.1263  
 Peak Wavelength (nm): 603  
 Dominant Wavelength (nm): 583  
 Purity: 62.2537  
 Rf: 84.7  
 Rg: 94.6

|           |      |      |      |
|-----------|------|------|------|
| CRI (Ra): | 80.9 |      |      |
| R1:       | 78.8 | R9:  | -1.5 |
| R2:       | 89.9 | R10: | 77.9 |
| R3:       | 96.2 | R11: | 78.9 |
| R4:       | 79.1 | R12: | 71.6 |
| R5:       | 79.1 | R13: | 81.2 |
| R6:       | 88.8 | R14: | 98.5 |
| R7:       | 81.3 | R15: | 69.9 |
| R8:       | 54.3 |      |      |



**Test Conditions**

Stabilization Time: 81M  
 Operation Time: 2H 21M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

**Photopic Flux vs. Wavelength**



**Photopic Lumens: 4337.9**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 0             | 0.0           | 490    | 18018         | 2.6           | 620    | 87426         | 22.8          | 750    | 2680          | 0.0           | 880    | 58            | 0.0           |
| 365    | 0             | 0.0           | 495    | 22295         | 3.9           | 625    | 83013         | 18.2          | 755    | 2287          | 0.0           | 885    | 46            | 0.0           |
| 370    | 0             | 0.0           | 500    | 26478         | 5.8           | 630    | 78077         | 14.1          | 760    | 1944          | 0.0           | 890    | 45            | 0.0           |
| 375    | 0             | 0.0           | 505    | 30524         | 8.5           | 635    | 72080         | 10.7          | 765    | 1653          | 0.0           | 895    | 41            | 0.0           |
| 380    | 0             | 0.0           | 510    | 33611         | 11.5          | 640    | 66249         | 7.9           | 770    | 1413          | 0.0           | 900    | 38            | 0.0           |
| 385    | 0             | 0.0           | 515    | 36490         | 15.2          | 645    | 59973         | 5.7           | 775    | 1198          | 0.0           | 905    | 33            | 0.0           |
| 390    | 0             | 0.0           | 520    | 38610         | 18.7          | 650    | 53972         | 3.9           | 780    | 1025          | 0.0           | 910    | 30            | 0.0           |
| 395    | 0             | 0.0           | 525    | 40511         | 21.9          | 655    | 48369         | 2.7           | 785    | 874           | 0.0           | 915    | 23            | 0.0           |
| 400    | 48            | 0.0           | 530    | 42223         | 24.9          | 660    | 42641         | 1.8           | 790    | 747           | 0.0           | 920    | 24            | 0.0           |
| 405    | 201           | 0.0           | 535    | 44137         | 27.6          | 665    | 37602         | 1.1           | 795    | 639           | 0.0           | 925    | 22            | 0.0           |
| 410    | 457           | 0.0           | 540    | 46032         | 30.0          | 670    | 32798         | 0.7           | 800    | 547           | 0.0           | 930    | 22            | 0.0           |
| 415    | 925           | 0.0           | 545    | 48553         | 32.5          | 675    | 28558         | 0.5           | 805    | 473           | 0.0           | 935    | 17            | 0.0           |
| 420    | 1816          | 0.0           | 550    | 51408         | 34.9          | 680    | 24782         | 0.3           | 810    | 401           | 0.0           | 940    | 13            | 0.0           |
| 425    | 3217          | 0.0           | 555    | 54711         | 37.4          | 685    | 21386         | 0.2           | 815    | 351           | 0.0           | 945    | 6             | 0.0           |
| 430    | 5520          | 0.0           | 560    | 58847         | 40.0          | 690    | 18413         | 0.1           | 820    | 307           | 0.0           | 950    | 10            | 0.0           |
| 435    | 9225          | 0.1           | 565    | 63386         | 42.4          | 695    | 15721         | 0.1           | 825    | 261           | 0.0           | 955    | 11            | 0.0           |
| 440    | 15522         | 0.2           | 570    | 68196         | 44.3          | 700    | 13432         | 0.0           | 830    | 228           | 0.0           | 960    | 8             | 0.0           |
| 445    | 27642         | 0.6           | 575    | 73613         | 46.0          | 705    | 11513         | 0.0           | 835    | 193           | 0.0           | 965    | 12            | 0.0           |
| 450    | 36602         | 0.9           | 580    | 79207         | 47.1          | 710    | 9780          | 0.0           | 840    | 174           | 0.0           | 970    | 3             | 0.0           |
| 455    | 28292         | 0.9           | 585    | 84248         | 47.0          | 715    | 8356          | 0.0           | 845    | 151           | 0.0           | 975    | 8             | 0.0           |
| 460    | 21166         | 0.9           | 590    | 88397         | 45.7          | 720    | 7161          | 0.0           | 850    | 123           | 0.0           | 980    | 2             | 0.0           |
| 465    | 19092         | 1.0           | 595    | 91428         | 43.4          | 725    | 6067          | 0.0           | 855    | 106           | 0.0           | 985    | 13            | 0.0           |
| 470    | 14951         | 0.9           | 600    | 93452         | 40.3          | 730    | 5164          | 0.0           | 860    | 95            | 0.0           | 990    | 16            | 0.0           |
| 475    | 12606         | 1.0           | 605    | 93959         | 36.4          | 735    | 4393          | 0.0           | 865    | 82            | 0.0           | 995    | 20            | 0.0           |
| 480    | 13323         | 1.3           | 610    | 93079         | 32.0          | 740    | 3694          | 0.0           | 870    | 77            | 0.0           | 1000   | 0             | 0.0           |
| 485    | 15164         | 1.8           | 615    | 90707         | 27.3          | 745    | 3157          | 0.0           | 875    | 65            | 0.0           |        |               |               |

REPORT NUMBER: SP1-2407-157-9

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: 5286.7**

**S/P: 1.22**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 0             | 0.0           | 490    | 18018         | 75.9          | 620    | 87426         | 0.4           | 750    | 2680          | 0.0           | 880    | 58            | 0.0           |
| 365    | 0             | 0.0           | 495    | 22295         | 93.2          | 625    | 83013         | 0.2           | 755    | 2287          | 0.0           | 885    | 46            | 0.0           |
| 370    | 0             | 0.0           | 500    | 26478         | 107.8         | 630    | 78077         | 0.1           | 760    | 1944          | 0.0           | 890    | 45            | 0.0           |
| 375    | 0             | 0.0           | 505    | 30524         | 118.7         | 635    | 72080         | 0.1           | 765    | 1653          | 0.0           | 895    | 41            | 0.0           |
| 380    | 0             | 0.0           | 510    | 33611         | 122.2         | 640    | 66249         | 0.1           | 770    | 1413          | 0.0           | 900    | 38            | 0.0           |
| 385    | 0             | 0.0           | 515    | 36490         | 120.8         | 645    | 59973         | 0.0           | 775    | 1198          | 0.0           | 905    | 33            | 0.0           |
| 390    | 0             | 0.0           | 520    | 38610         | 113.9         | 650    | 53972         | 0.0           | 780    | 1025          | 0.0           | 910    | 30            | 0.0           |
| 395    | 0             | 0.0           | 525    | 40511         | 104.1         | 655    | 48369         | 0.0           | 785    | 874           | 0.0           | 915    | 23            | 0.0           |
| 400    | 48            | 0.0           | 530    | 42223         | 92.4          | 660    | 42641         | 0.0           | 790    | 747           | 0.0           | 920    | 24            | 0.0           |
| 405    | 201           | 0.0           | 535    | 44137         | 80.5          | 665    | 37602         | 0.0           | 795    | 639           | 0.0           | 925    | 22            | 0.0           |
| 410    | 457           | 0.1           | 540    | 46032         | 68.2          | 670    | 32798         | 0.0           | 800    | 547           | 0.0           | 930    | 22            | 0.0           |
| 415    | 925           | 0.3           | 545    | 48553         | 57.1          | 675    | 28558         | 0.0           | 805    | 473           | 0.0           | 935    | 17            | 0.0           |
| 420    | 1816          | 1.1           | 550    | 51408         | 46.7          | 680    | 24782         | 0.0           | 810    | 401           | 0.0           | 940    | 13            | 0.0           |
| 425    | 3217          | 2.5           | 555    | 54711         | 37.4          | 685    | 21386         | 0.0           | 815    | 351           | 0.0           | 945    | 6             | 0.0           |
| 430    | 5520          | 5.9           | 560    | 58847         | 29.4          | 690    | 18413         | 0.0           | 820    | 307           | 0.0           | 950    | 10            | 0.0           |
| 435    | 9225          | 12.5          | 565    | 63386         | 22.5          | 695    | 15721         | 0.0           | 825    | 261           | 0.0           | 955    | 11            | 0.0           |
| 440    | 15522         | 26.3          | 570    | 68196         | 16.9          | 700    | 13432         | 0.0           | 830    | 228           | 0.0           | 960    | 8             | 0.0           |
| 445    | 27642         | 55.2          | 575    | 73613         | 12.4          | 705    | 11513         | 0.0           | 835    | 193           | 0.0           | 965    | 12            | 0.0           |
| 450    | 36602         | 85.4          | 580    | 79207         | 9.0           | 710    | 9780          | 0.0           | 840    | 174           | 0.0           | 970    | 3             | 0.0           |
| 455    | 28292         | 75.1          | 585    | 84248         | 6.3           | 715    | 8356          | 0.0           | 845    | 151           | 0.0           | 975    | 8             | 0.0           |
| 460    | 21166         | 63.2          | 590    | 88397         | 4.4           | 720    | 7161          | 0.0           | 850    | 123           | 0.0           | 980    | 2             | 0.0           |
| 465    | 19092         | 63.2          | 595    | 91428         | 3.0           | 725    | 6067          | 0.0           | 855    | 106           | 0.0           | 985    | 13            | 0.0           |
| 470    | 14951         | 54.2          | 600    | 93452         | 2.0           | 730    | 5164          | 0.0           | 860    | 95            | 0.0           | 990    | 16            | 0.0           |
| 475    | 12606         | 48.8          | 605    | 93959         | 1.3           | 735    | 4393          | 0.0           | 865    | 82            | 0.0           | 995    | 20            | 0.0           |
| 480    | 13323         | 54.2          | 610    | 93079         | 0.9           | 740    | 3694          | 0.0           | 870    | 77            | 0.0           | 1000   | 0             | 0.0           |
| 485    | 15164         | 63.3          | 615    | 90707         | 0.5           | 745    | 3157          | 0.0           | 875    | 65            | 0.0           |        |               |               |



REPORT NUMBER: SP1-2407-157-9

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 9797**

**M/P: 2.26**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 0             | 0.0           | 490    | 18018         | 27.7          | 620    | 87426         | 1.1           | 750    | 2680          | 0.0           | 880    | 58            | 0.0           |
| 365    | 0             | 0.0           | 495    | 22295         | 36.0          | 625    | 83013         | 0.7           | 755    | 2287          | 0.0           | 885    | 46            | 0.0           |
| 370    | 0             | 0.0           | 500    | 26478         | 44.2          | 630    | 78077         | 0.4           | 760    | 1944          | 0.0           | 890    | 45            | 0.0           |
| 375    | 0             | 0.0           | 505    | 30524         | 51.8          | 635    | 72080         | 0.3           | 765    | 1653          | 0.0           | 895    | 41            | 0.0           |
| 380    | 0             | 0.0           | 510    | 33611         | 57.0          | 640    | 66249         | 0.2           | 770    | 1413          | 0.0           | 900    | 38            | 0.0           |
| 385    | 0             | 0.0           | 515    | 36490         | 60.5          | 645    | 59973         | 0.1           | 775    | 1198          | 0.0           | 905    | 33            | 0.0           |
| 390    | 0             | 0.0           | 520    | 38610         | 61.4          | 650    | 53972         | 0.1           | 780    | 1025          | 0.0           | 910    | 30            | 0.0           |
| 395    | 0             | 0.0           | 525    | 40511         | 60.6          | 655    | 48369         | 0.0           | 785    | 874           | 0.0           | 915    | 23            | 0.0           |
| 400    | 48            | 0.0           | 530    | 42223         | 58.2          | 660    | 42641         | 0.0           | 790    | 747           | 0.0           | 920    | 24            | 0.0           |
| 405    | 201           | 0.0           | 535    | 44137         | 55.0          | 665    | 37602         | 0.0           | 795    | 639           | 0.0           | 925    | 22            | 0.0           |
| 410    | 457           | 0.0           | 540    | 46032         | 50.9          | 670    | 32798         | 0.0           | 800    | 547           | 0.0           | 930    | 22            | 0.0           |
| 415    | 925           | 0.1           | 545    | 48553         | 46.6          | 675    | 28558         | 0.0           | 805    | 473           | 0.0           | 935    | 17            | 0.0           |
| 420    | 1816          | 0.3           | 550    | 51408         | 42.0          | 680    | 24782         | 0.0           | 810    | 401           | 0.0           | 940    | 13            | 0.0           |
| 425    | 3217          | 0.8           | 555    | 54711         | 37.4          | 685    | 21386         | 0.0           | 815    | 351           | 0.0           | 945    | 6             | 0.0           |
| 430    | 5520          | 1.9           | 560    | 58847         | 32.9          | 690    | 18413         | 0.0           | 820    | 307           | 0.0           | 950    | 10            | 0.0           |
| 435    | 9225          | 4.1           | 565    | 63386         | 28.4          | 695    | 15721         | 0.0           | 825    | 261           | 0.0           | 955    | 11            | 0.0           |
| 440    | 15522         | 8.7           | 570    | 68196         | 24.1          | 700    | 13432         | 0.0           | 830    | 228           | 0.0           | 960    | 8             | 0.0           |
| 445    | 27642         | 18.5          | 575    | 73613         | 20.0          | 705    | 11513         | 0.0           | 835    | 193           | 0.0           | 965    | 12            | 0.0           |
| 450    | 36602         | 28.3          | 580    | 79207         | 16.3          | 710    | 9780          | 0.0           | 840    | 174           | 0.0           | 970    | 3             | 0.0           |
| 455    | 28292         | 24.7          | 585    | 84248         | 12.9          | 715    | 8356          | 0.0           | 845    | 151           | 0.0           | 975    | 8             | 0.0           |
| 460    | 21166         | 20.4          | 590    | 88397         | 9.8           | 720    | 7161          | 0.0           | 850    | 123           | 0.0           | 980    | 2             | 0.0           |
| 465    | 19092         | 20.1          | 595    | 91428         | 7.3           | 725    | 6067          | 0.0           | 855    | 106           | 0.0           | 985    | 13            | 0.0           |
| 470    | 14951         | 17.2          | 600    | 93452         | 5.3           | 730    | 5164          | 0.0           | 860    | 95            | 0.0           | 990    | 16            | 0.0           |
| 475    | 12606         | 15.7          | 605    | 93959         | 3.7           | 735    | 4393          | 0.0           | 865    | 82            | 0.0           | 995    | 20            | 0.0           |
| 480    | 13323         | 18.0          | 610    | 93079         | 2.5           | 740    | 3694          | 0.0           | 870    | 77            | 0.0           | 1000   | 0             | 0.0           |
| 485    | 15164         | 21.9          | 615    | 90707         | 1.7           | 745    | 3157          | 0.0           | 875    | 65            | 0.0           |        |               |               |

**Summary**

$R_f = 84.7$   
 $R_g = 94.6$   
 CIE  $R_a = 80.9$   
 $R_9 = -1.5$




**Color Vector Graphics**



Individual Sample Fidelity Index ( $R_{f,i}$ )

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 |            |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)