

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P629017

Luminaire Tested: GWS-SA1A-827-U-SL3-W-HSS

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P629017
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-34)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA1A-827-U-SL3-W-HSS
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III SPILL LIGHT ELIMINATOR OPTICS WITH HOUSE SIDE SHIELD
Light Source: (16) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1693 lumens
Efficiency: N/A
Efficacy: 85.9 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type III - Short
BUG Rating: B0 - U0 - G1


Input Watts (W): 19.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P629017
 CATALOG NUMBER: GWS-SA1A-827-U-SL3-W-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 4.9 fc
 Type III - Short - N/A

REPORT NUMBER: P629017
CATALOG NUMBER: GWS-SA1A-827-U-SL3-W-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 58-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P629017
 CATALOG NUMBER: GWS-SA1A-827-U-SL3-W-HSS


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 165.4 | 0.0 | 165.4 |
| | % Fixture | 9.8 | 0.0 | 9.8 |
| Street Side | Lumens | 1527.7 | 0.0 | 1527.7 |
| | % Fixture | 90.2 | 0.0 | 90.2 |
| Total | Lumens | 1693.0 | 0.0 | 1693.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 39.7 | 2.3 |
| 10°-20° | 82.6 | 4.9 |
| 20°-30° | 111.4 | 6.6 |
| 30°-40° | 156.5 | 9.2 |
| 40°-50° | 241.8 | 14.3 |
| 50°-60° | 386.6 | 22.8 |
| 60°-70° | 457.8 | 27.0 |
| 70°-80° | 202.5 | 12.0 |
| 80°-90° | 14.1 | 0.8 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 1693.0 | 100.0 |
| 0°-180° | 1693.0 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P629017


CATALOG NUMBER: GWS-SA1A-827-U-SL3-W-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|--------|
| | | | B | U | G |
| FL (0°-30°) | 174.2 | 10.3 | | | |
| FM (30°-60°) | 720.0 | 42.5 | | | |
| FH (60°-80°) | 619.9 | 36.6 | | | G0/660 |
| FVH (80°-90°) | 13.5 | 0.8 | | | G1/100 |
| BL (0°-30°) | 59.5 | 3.5 | B0/110 | | |
| BM (30°-60°) | 64.9 | 3.8 | B0/220 | | |
| BH (60°-80°) | 40.4 | 2.4 | B0/110 | | G0/110 |
| BVH (80°-90°) | 0.6 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B0-U0-G1

Type III Short





REPORT NUMBER: P629017

CATALOG NUMBER: GWS-SA1A-827-U-SL3-W-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 58° | 65° | 75° | 85° |
|-------|-------|-------|-------|-------|-------|--------|--------|--------|--------|--------|--------|
| 0° | 488.4 | 488.4 | 488.4 | 488.4 | 488.4 | 488.4 | 488.4 | 488.4 | 488.4 | 488.4 | 488.4 |
| 2.5° | 513.7 | 514.6 | 515.8 | 517.3 | 517.0 | 515.6 | 514.0 | 510.2 | 507.9 | 500.4 | 491.2 |
| 5° | 497.2 | 497.1 | 500.1 | 502.9 | 508.0 | 510.7 | 514.4 | 511.0 | 509.8 | 500.8 | 486.0 |
| 7.5° | 465.0 | 466.6 | 470.1 | 474.6 | 481.9 | 489.9 | 498.9 | 497.8 | 501.4 | 495.4 | 477.0 |
| 10° | 433.4 | 432.5 | 437.9 | 444.6 | 455.9 | 466.0 | 479.1 | 478.9 | 488.4 | 487.8 | 466.8 |
| 12.5° | 405.7 | 405.5 | 409.7 | 417.3 | 430.5 | 444.8 | 462.4 | 462.9 | 474.6 | 479.4 | 458.1 |
| 15° | 382.3 | 382.6 | 386.6 | 394.6 | 408.2 | 425.6 | 446.1 | 449.9 | 463.0 | 472.8 | 449.6 |
| 17.5° | 365.6 | 365.8 | 368.2 | 375.1 | 388.4 | 407.0 | 431.7 | 436.8 | 453.8 | 467.8 | 442.7 |
| 20° | 358.0 | 357.4 | 357.8 | 361.3 | 371.6 | 388.6 | 417.0 | 423.6 | 445.2 | 464.4 | 436.4 |
| 22.5° | 359.0 | 358.1 | 356.0 | 355.6 | 360.2 | 373.1 | 401.5 | 409.5 | 435.9 | 462.3 | 430.7 |
| 25° | 368.3 | 366.4 | 363.4 | 358.9 | 357.1 | 363.5 | 387.8 | 396.2 | 427.2 | 462.4 | 426.3 |
| 27.5° | 382.6 | 380.5 | 376.7 | 370.7 | 363.7 | 361.0 | 378.5 | 386.5 | 421.1 | 465.9 | 424.2 |
| 30° | 400.7 | 399.1 | 395.5 | 388.3 | 378.8 | 367.7 | 376.6 | 383.2 | 418.1 | 472.9 | 425.1 |
| 32.5° | 422.1 | 420.9 | 417.9 | 411.3 | 400.6 | 383.6 | 383.2 | 388.3 | 420.5 | 483.1 | 428.6 |
| 35° | 442.8 | 443.3 | 443.4 | 439.8 | 428.3 | 407.7 | 401.3 | 403.1 | 430.4 | 498.4 | 436.4 |
| 37.5° | 465.1 | 464.1 | 469.5 | 472.0 | 460.9 | 439.1 | 429.3 | 429.5 | 449.3 | 521.0 | 451.1 |
| 40° | 482.1 | 482.4 | 494.1 | 504.6 | 499.9 | 478.8 | 464.8 | 464.7 | 478.3 | 552.1 | 474.7 |
| 42.5° | 498.0 | 499.9 | 517.1 | 535.1 | 541.6 | 522.8 | 512.8 | 509.0 | 519.1 | 594.0 | 510.2 |
| 45° | 514.9 | 517.7 | 541.9 | 567.5 | 584.4 | 573.3 | 565.4 | 566.9 | 568.1 | 642.9 | 558.1 |
| 47.5° | 534.7 | 536.5 | 566.3 | 602.4 | 634.0 | 631.2 | 631.6 | 629.8 | 629.2 | 704.5 | 621.3 |
| 50° | 558.7 | 562.8 | 597.2 | 640.3 | 683.5 | 702.4 | 708.7 | 709.4 | 699.7 | 771.6 | 686.8 |
| 52.5° | 609.6 | 614.7 | 644.1 | 681.8 | 737.4 | 777.1 | 802.8 | 797.7 | 782.7 | 836.6 | 758.6 |
| 55° | 669.7 | 673.6 | 701.9 | 741.0 | 803.4 | 859.1 | 919.9 | 917.8 | 881.1 | 905.1 | 817.6 |
| 57.5° | 675.4 | 679.7 | 723.6 | 783.6 | 888.0 | 960.4 | 1024.4 | 1031.1 | 977.3 | 953.7 | 870.3 |
| 60° | 611.4 | 620.2 | 680.2 | 760.8 | 920.4 | 1096.6 | 1138.9 | 1140.2 | 1047.9 | 1003.0 | 934.8 |
| 62.5° | 490.0 | 494.2 | 554.6 | 659.8 | 870.5 | 1176.0 | 1313.8 | 1285.3 | 1138.6 | 1079.2 | 1036.8 |
| 65° | 256.8 | 273.9 | 326.5 | 443.0 | 706.0 | 1148.3 | 1524.2 | 1516.4 | 1301.6 | 1188.5 | 1116.3 |
| 67.5° | 176.2 | 176.1 | 188.5 | 230.9 | 420.9 | 988.7 | 1627.4 | 1713.1 | 1490.1 | 1225.9 | 1058.7 |
| 70° | 134.1 | 134.6 | 145.7 | 173.2 | 218.0 | 658.2 | 1514.1 | 1660.7 | 1525.2 | 1113.1 | 856.3 |
| 72.5° | 89.0 | 89.9 | 108.3 | 140.0 | 174.1 | 322.6 | 1176.6 | 1328.7 | 1283.3 | 894.0 | 602.7 |
| 75° | 53.2 | 53.9 | 67.1 | 101.7 | 154.8 | 180.6 | 747.6 | 918.6 | 883.4 | 616.2 | 323.1 |
| 77.5° | 21.9 | 22.5 | 34.5 | 63.4 | 113.3 | 140.3 | 413.4 | 601.1 | 529.1 | 245.0 | 88.3 |
| 80° | 9.1 | 9.4 | 16.6 | 44.4 | 81.7 | 88.0 | 191.5 | 282.5 | 216.8 | 52.7 | 27.0 |
| 82.5° | 3.3 | 3.4 | 6.1 | 24.4 | 50.8 | 66.2 | 96.7 | 111.6 | 61.1 | 17.2 | 14.5 |
| 85° | 0.1 | 0.1 | 1.5 | 8.2 | 19.3 | 18.7 | 55.3 | 53.5 | 20.2 | 7.2 | 8.7 |
| 87.5° | 0.0 | 0.0 | 0.1 | 0.1 | 0.3 | 0.7 | 5.2 | 9.3 | 4.3 | 1.8 | 3.7 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P629017
 CATALOG NUMBER: GWS-SA1A-827-U-SL3-W-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 488.4 | 488.4 | 488.4 | 488.4 | 488.4 | 488.4 | 488.4 | 488.4 | 488.4 | 488.4 | 488.4 |
| 2.5° | 485.2 | 477.3 | 468.6 | 460.5 | 447.6 | 440.0 | 430.5 | 426.3 | 420.3 | 418.8 | 419.7 |
| 5° | 475.3 | 461.7 | 440.9 | 422.0 | 397.6 | 377.9 | 358.1 | 349.8 | 339.0 | 331.8 | 328.8 |
| 7.5° | 461.4 | 443.6 | 411.0 | 376.7 | 343.2 | 307.3 | 280.1 | 262.1 | 245.8 | 236.8 | 235.0 |
| 10° | 447.3 | 424.1 | 377.5 | 328.3 | 276.3 | 233.5 | 196.6 | 169.3 | 147.2 | 137.1 | 129.3 |
| 12.5° | 432.8 | 403.9 | 343.3 | 279.2 | 218.8 | 160.3 | 114.8 | 88.3 | 72.4 | 66.1 | 67.1 |
| 15° | 419.4 | 384.4 | 309.4 | 230.0 | 154.0 | 96.8 | 63.4 | 53.5 | 49.8 | 48.6 | 48.4 |
| 17.5° | 406.7 | 365.9 | 275.7 | 182.2 | 101.6 | 59.3 | 48.6 | 46.2 | 45.1 | 44.5 | 44.5 |
| 20° | 395.2 | 348.3 | 242.8 | 137.3 | 65.6 | 47.1 | 43.9 | 42.7 | 41.8 | 41.4 | 41.4 |
| 22.5° | 384.4 | 331.2 | 210.5 | 97.1 | 48.4 | 42.3 | 40.3 | 39.1 | 38.1 | 37.5 | 37.5 |
| 25° | 374.6 | 315.7 | 179.8 | 66.8 | 41.7 | 38.7 | 36.6 | 35.2 | 33.4 | 32.4 | 32.4 |
| 27.5° | 367.6 | 302.0 | 150.3 | 48.7 | 37.6 | 34.8 | 32.4 | 30.6 | 28.6 | 27.4 | 27.1 |
| 30° | 363.4 | 290.3 | 120.5 | 40.0 | 33.9 | 31.0 | 28.3 | 26.1 | 23.8 | 22.6 | 22.5 |
| 32.5° | 361.0 | 279.5 | 93.2 | 34.9 | 30.7 | 27.4 | 24.4 | 22.0 | 19.8 | 18.4 | 18.3 |
| 35° | 361.9 | 271.1 | 69.8 | 31.5 | 27.7 | 24.3 | 21.0 | 18.6 | 16.6 | 15.4 | 15.1 |
| 37.5° | 369.7 | 267.3 | 52.4 | 28.8 | 25.2 | 21.6 | 18.1 | 15.9 | 14.1 | 13.2 | 13.0 |
| 40° | 384.8 | 268.1 | 41.2 | 26.7 | 23.1 | 18.9 | 15.6 | 13.5 | 12.1 | 11.4 | 11.2 |
| 42.5° | 408.3 | 274.4 | 34.0 | 24.9 | 20.8 | 16.5 | 13.5 | 11.8 | 10.5 | 9.7 | 9.6 |
| 45° | 443.4 | 287.4 | 29.7 | 22.8 | 18.4 | 14.2 | 11.7 | 10.2 | 9.0 | 8.1 | 7.9 |
| 47.5° | 494.2 | 310.0 | 26.8 | 20.8 | 16.3 | 12.3 | 10.0 | 8.5 | 7.5 | 6.7 | 6.6 |
| 50° | 548.3 | 337.2 | 24.4 | 18.9 | 14.5 | 10.6 | 8.5 | 7.0 | 6.1 | 5.4 | 5.2 |
| 52.5° | 606.0 | 366.4 | 22.6 | 17.1 | 12.9 | 9.1 | 7.2 | 5.8 | 4.9 | 4.2 | 4.0 |
| 55° | 661.4 | 395.8 | 20.5 | 15.9 | 10.9 | 7.8 | 6.0 | 4.8 | 3.9 | 3.3 | 3.3 |
| 57.5° | 715.4 | 422.7 | 18.3 | 13.9 | 9.0 | 6.6 | 4.9 | 3.9 | 3.1 | 2.7 | 2.5 |
| 60° | 779.8 | 460.0 | 15.7 | 11.8 | 7.5 | 5.5 | 4.0 | 3.1 | 2.5 | 2.1 | 2.1 |
| 62.5° | 875.6 | 498.9 | 13.5 | 9.9 | 6.3 | 4.6 | 3.3 | 2.5 | 2.1 | 1.8 | 1.6 |
| 65° | 906.9 | 477.9 | 11.4 | 8.1 | 5.1 | 3.7 | 2.7 | 2.2 | 1.8 | 1.6 | 1.5 |
| 67.5° | 823.3 | 391.7 | 9.4 | 6.6 | 4.2 | 3.1 | 2.4 | 1.9 | 1.6 | 1.5 | 1.3 |
| 70° | 642.4 | 278.0 | 7.3 | 4.9 | 3.4 | 2.5 | 2.1 | 1.8 | 1.5 | 1.3 | 1.3 |
| 72.5° | 437.0 | 164.4 | 5.8 | 3.7 | 2.8 | 2.2 | 1.8 | 1.6 | 1.5 | 1.3 | 1.2 |
| 75° | 215.2 | 58.4 | 4.5 | 2.8 | 2.2 | 1.9 | 1.6 | 1.5 | 1.3 | 1.2 | 1.2 |
| 77.5° | 58.0 | 16.2 | 3.4 | 2.2 | 1.8 | 1.5 | 1.5 | 1.5 | 1.3 | 1.0 | 1.0 |
| 80° | 19.6 | 6.7 | 2.5 | 1.6 | 1.5 | 1.2 | 1.0 | 1.3 | 1.2 | 1.0 | 0.9 |
| 82.5° | 10.8 | 3.3 | 1.8 | 1.3 | 1.0 | 0.9 | 0.9 | 0.9 | 0.9 | 0.7 | 0.7 |
| 85° | 6.9 | 1.8 | 1.2 | 1.0 | 1.0 | 0.7 | 0.6 | 0.6 | 0.4 | 0.4 | 0.4 |
| 87.5° | 3.1 | 1.0 | 1.0 | 0.9 | 0.9 | 0.7 | 0.4 | 0.3 | 0.1 | 0.1 | 0.1 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions


Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) | λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) | λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) | λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) | λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) |
|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_g = -1.5$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)