

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P631973

Luminaire Tested: GWS-SA2B-827-U-AFL-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P631973
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-47)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA2B-827-U-AFL-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (2) LIGHTSQUARES WITH 16 LEDS EACH AND AUTOMOTIVE FRONTLINE OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH
Light Source: (32) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4602.4 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B1 - U0 - G1


Input Watts (W): 46.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P631973
 CATALOG NUMBER: GWS-SA2B-827-U-AFL-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 16.7 fc
 Type II - Short - N/A

REPORT NUMBER: P631973
CATALOG NUMBER: GWS-SA2B-827-U-AFL-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 51-Deg Lateral - - - Horizontal Cone Through 52.5-Deg Vertical

REPORT NUMBER: P631973

CATALOG NUMBER: GWS-SA2B-827-U-AFL-W-GRSWH

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 896.7 | 0.0 | 896.7 |
| | % Fixture | 19.5 | 0.0 | 19.5 |
| Street Side | Lumens | 3705.7 | 0.0 | 3705.7 |
| | % Fixture | 80.5 | 0.0 | 80.5 |
| Total | Lumens | 4602.4 | 0.0 | 4602.4 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 127.9 | 2.8 |
| 10°-20° | 332.3 | 7.2 |
| 20°-30° | 540.2 | 11.7 |
| 30°-40° | 856.2 | 18.6 |
| 40°-50° | 1291.3 | 28.1 |
| 50°-60° | 1117.1 | 24.3 |
| 60°-70° | 253.2 | 5.5 |
| 70°-80° | 74.7 | 1.6 |
| 80°-90° | 9.6 | 0.2 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 4602.4 | 100.0 |
| 0°-180° | 4602.4 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P631973

CATALOG NUMBER: GWS-SA2B-827-U-AFL-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|--------|
| | | | B | U | G |
| FL (0°-30°) | 686.9 | 14.9 | | | |
| FM (30°-60°) | 2815.8 | 61.2 | | | |
| FH (60°-80°) | 199.3 | 4.3 | | | G0/660 |
| FVH (80°-90°) | 3.6 | 0.1 | | | G0/10 |
| BL (0°-30°) | 313.5 | 6.8 | B1/500 | | |
| BM (30°-60°) | 448.7 | 9.7 | B1/1000 | | |
| BH (60°-80°) | 128.6 | 2.8 | B1/500 | | G1/500 |
| BVH (80°-90°) | 6.0 | 0.1 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G1
 Type II Short





REPORT NUMBER: P631973

CATALOG NUMBER: GWS-SA2B-827-U-AFL-W-GRSWH

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 51° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1370.4 | 1370.4 | 1370.4 | 1370.4 | 1370.4 | 1370.4 | 1370.4 | 1370.4 | 1370.4 | 1370.4 | 1370.4 |
| 2.5° | 1527.1 | 1535.8 | 1522.4 | 1517.3 | 1508.9 | 1494.4 | 1477.7 | 1472.9 | 1436.9 | 1413.3 | 1386.7 |
| 5° | 1680.6 | 1685.3 | 1674.4 | 1663.5 | 1642.8 | 1616.9 | 1584.6 | 1577.7 | 1512.2 | 1458.0 | 1401.6 |
| 7.5° | 1714.8 | 1713.0 | 1722.4 | 1728.6 | 1726.0 | 1715.9 | 1687.1 | 1673.7 | 1595.5 | 1509.7 | 1426.4 |
| 10° | 1579.5 | 1569.3 | 1604.2 | 1645.7 | 1695.5 | 1753.0 | 1749.7 | 1748.6 | 1680.6 | 1579.1 | 1458.0 |
| 12.5° | 1400.2 | 1395.1 | 1423.5 | 1475.5 | 1569.7 | 1697.0 | 1744.6 | 1781.7 | 1757.3 | 1645.3 | 1493.3 |
| 15° | 1297.6 | 1295.8 | 1315.1 | 1352.5 | 1427.5 | 1588.2 | 1690.0 | 1763.5 | 1823.2 | 1716.2 | 1530.7 |
| 17.5° | 1279.1 | 1280.2 | 1286.7 | 1308.2 | 1362.0 | 1494.4 | 1612.2 | 1714.8 | 1874.4 | 1794.1 | 1577.7 |
| 20° | 1333.3 | 1340.5 | 1329.3 | 1332.5 | 1361.6 | 1460.6 | 1559.1 | 1665.7 | 1907.2 | 1872.2 | 1628.2 |
| 22.5° | 1453.6 | 1451.1 | 1426.4 | 1411.8 | 1412.2 | 1481.3 | 1553.3 | 1642.8 | 1928.6 | 1948.3 | 1674.0 |
| 25° | 1590.0 | 1587.1 | 1557.7 | 1525.3 | 1504.9 | 1537.7 | 1595.1 | 1667.1 | 1947.9 | 2017.7 | 1710.8 |
| 27.5° | 1751.1 | 1742.0 | 1709.3 | 1667.9 | 1622.8 | 1636.9 | 1675.9 | 1733.0 | 1977.7 | 2086.1 | 1735.1 |
| 30° | 1907.2 | 1917.7 | 1870.8 | 1821.7 | 1774.1 | 1765.3 | 1787.9 | 1839.5 | 2038.5 | 2166.1 | 1764.2 |
| 32.5° | 2114.1 | 2110.5 | 2058.5 | 1994.4 | 1926.4 | 1919.9 | 1937.7 | 1985.0 | 2147.6 | 2276.7 | 1808.6 |
| 35° | 2364.7 | 2365.4 | 2291.6 | 2205.0 | 2108.3 | 2090.8 | 2120.6 | 2166.5 | 2310.1 | 2426.5 | 1878.8 |
| 37.5° | 2625.1 | 2624.0 | 2559.6 | 2461.4 | 2329.4 | 2304.7 | 2338.9 | 2373.0 | 2513.4 | 2630.5 | 1987.9 |
| 40° | 2807.6 | 2814.9 | 2784.7 | 2733.1 | 2608.0 | 2547.6 | 2577.8 | 2601.4 | 2734.5 | 2870.6 | 2131.6 |
| 42.5° | 2911.3 | 2922.2 | 2928.8 | 2959.7 | 2893.8 | 2829.5 | 2818.6 | 2830.9 | 2932.0 | 3093.5 | 2266.5 |
| 45° | 2933.5 | 2948.0 | 2995.7 | 3110.2 | 3135.7 | 3117.5 | 3081.9 | 3052.0 | 3079.3 | 3251.7 | 2354.9 |
| 47.5° | 2835.6 | 2861.1 | 2962.9 | 3163.3 | 3312.1 | 3369.2 | 3329.5 | 3284.1 | 3164.4 | 3292.4 | 2345.8 |
| 50° | 2448.0 | 2477.8 | 2707.3 | 3055.0 | 3337.2 | 3545.2 | 3548.8 | 3481.6 | 3154.2 | 3175.0 | 2231.6 |
| 52.5° | 1938.1 | 1958.4 | 2089.7 | 2589.8 | 3091.0 | 3537.9 | 3683.4 | 3611.4 | 3105.1 | 3028.0 | 2088.6 |
| 55° | 1158.3 | 1191.1 | 1313.6 | 1708.6 | 2408.0 | 3135.7 | 3445.5 | 3480.5 | 3081.1 | 2904.8 | 1991.2 |
| 57.5° | 391.0 | 407.0 | 524.1 | 754.6 | 1419.1 | 2295.9 | 2662.2 | 2804.0 | 2797.1 | 2716.4 | 1801.0 |
| 60° | 186.2 | 189.8 | 213.5 | 286.2 | 568.1 | 1199.8 | 1575.8 | 1739.5 | 1888.6 | 1903.5 | 1120.5 |
| 62.5° | 141.8 | 144.0 | 156.0 | 171.7 | 228.4 | 505.5 | 722.3 | 847.4 | 905.2 | 776.8 | 408.1 |
| 65° | 118.6 | 120.4 | 129.5 | 139.3 | 155.3 | 218.9 | 277.1 | 319.7 | 288.0 | 224.4 | 194.6 |
| 67.5° | 98.9 | 100.4 | 107.3 | 117.8 | 128.7 | 146.6 | 153.8 | 158.2 | 165.8 | 186.2 | 178.9 |
| 70° | 77.5 | 78.9 | 86.2 | 95.3 | 105.8 | 110.2 | 117.1 | 121.5 | 136.7 | 162.9 | 162.2 |
| 72.5° | 59.6 | 61.5 | 65.5 | 71.3 | 80.0 | 84.4 | 92.0 | 97.1 | 105.8 | 126.9 | 135.7 |
| 75° | 43.6 | 44.7 | 48.4 | 50.2 | 51.3 | 50.2 | 57.8 | 63.6 | 75.3 | 83.3 | 85.5 |
| 77.5° | 17.8 | 20.0 | 19.3 | 19.3 | 22.9 | 27.6 | 31.6 | 35.3 | 43.3 | 48.0 | 48.4 |
| 80° | 7.3 | 8.0 | 9.5 | 10.5 | 12.7 | 16.4 | 18.9 | 20.4 | 24.0 | 26.9 | 29.1 |
| 82.5° | 4.4 | 4.7 | 5.5 | 5.8 | 7.3 | 9.5 | 10.9 | 12.0 | 14.9 | 17.8 | 18.9 |
| 85° | 2.2 | 2.2 | 2.5 | 2.9 | 3.6 | 4.4 | 5.1 | 5.8 | 7.6 | 9.5 | 10.5 |
| 87.5° | 0.4 | 0.4 | 0.4 | 0.7 | 1.1 | 1.5 | 1.8 | 2.2 | 2.5 | 2.9 | 3.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P631973

CATALOG NUMBER: GWS-SA2B-827-U-AFL-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1370.4 | 1370.4 | 1370.4 | 1370.4 | 1370.4 | 1370.4 | 1370.4 | 1370.4 | 1370.4 | 1370.4 | 1370.4 |
| 2.5° | 1371.1 | 1351.5 | 1328.5 | 1310.4 | 1289.3 | 1273.6 | 1251.4 | 1237.6 | 1224.5 | 1213.6 | 1205.6 |
| 5° | 1372.5 | 1339.5 | 1291.8 | 1249.6 | 1206.0 | 1164.5 | 1122.0 | 1087.4 | 1056.5 | 1030.7 | 1028.5 |
| 7.5° | 1380.9 | 1333.3 | 1258.7 | 1184.9 | 1099.8 | 1017.6 | 935.4 | 868.5 | 817.6 | 791.0 | 785.6 |
| 10° | 1395.1 | 1332.5 | 1224.9 | 1107.1 | 961.9 | 829.6 | 732.1 | 681.2 | 651.7 | 641.2 | 637.5 |
| 12.5° | 1410.0 | 1330.7 | 1181.6 | 997.2 | 795.7 | 679.7 | 626.3 | 620.1 | 625.5 | 626.3 | 625.9 |
| 15° | 1428.2 | 1329.6 | 1127.1 | 868.5 | 674.3 | 610.3 | 613.9 | 627.0 | 639.7 | 642.6 | 642.6 |
| 17.5° | 1450.4 | 1327.1 | 1052.9 | 742.6 | 598.3 | 596.8 | 616.1 | 633.5 | 645.5 | 647.7 | 647.7 |
| 20° | 1473.7 | 1320.5 | 961.6 | 640.1 | 567.3 | 588.4 | 609.2 | 622.6 | 631.0 | 633.9 | 634.3 |
| 22.5° | 1489.7 | 1303.1 | 856.5 | 564.1 | 548.1 | 572.4 | 587.4 | 601.2 | 601.2 | 593.9 | 591.7 |
| 25° | 1492.9 | 1265.6 | 742.6 | 512.1 | 525.2 | 547.7 | 563.0 | 555.0 | 540.1 | 534.3 | 533.9 |
| 27.5° | 1480.9 | 1211.1 | 630.3 | 475.0 | 497.5 | 520.1 | 517.5 | 505.9 | 499.3 | 493.5 | 495.7 |
| 30° | 1466.4 | 1145.6 | 532.8 | 444.4 | 465.5 | 487.7 | 479.0 | 475.0 | 470.2 | 463.7 | 465.2 |
| 32.5° | 1456.6 | 1072.5 | 457.9 | 420.8 | 444.1 | 447.7 | 453.9 | 453.5 | 449.2 | 436.8 | 436.1 |
| 35° | 1459.5 | 998.7 | 407.7 | 401.5 | 426.2 | 424.8 | 436.4 | 434.2 | 404.1 | 387.0 | 385.9 |
| 37.5° | 1482.7 | 927.8 | 378.2 | 386.2 | 397.9 | 407.0 | 417.1 | 391.0 | 380.4 | 369.5 | 370.2 |
| 40° | 1527.1 | 861.9 | 362.2 | 377.9 | 380.8 | 394.2 | 370.6 | 370.2 | 365.5 | 355.7 | 355.3 |
| 42.5° | 1577.3 | 806.3 | 351.3 | 373.9 | 369.9 | 372.4 | 347.3 | 350.2 | 349.9 | 343.7 | 341.9 |
| 45° | 1607.9 | 755.0 | 342.6 | 359.0 | 360.0 | 334.6 | 327.0 | 330.2 | 332.0 | 328.8 | 328.4 |
| 47.5° | 1576.2 | 696.1 | 333.5 | 336.0 | 345.5 | 317.5 | 308.0 | 308.4 | 311.7 | 312.0 | 310.6 |
| 50° | 1487.5 | 630.3 | 322.6 | 316.4 | 310.2 | 299.7 | 290.9 | 289.1 | 292.4 | 295.7 | 296.8 |
| 52.5° | 1372.9 | 567.3 | 304.4 | 294.9 | 280.4 | 280.4 | 276.4 | 270.6 | 274.9 | 279.3 | 280.8 |
| 55° | 1288.9 | 520.8 | 278.6 | 268.0 | 252.0 | 257.5 | 256.8 | 251.7 | 257.5 | 260.8 | 261.9 |
| 57.5° | 1116.9 | 418.6 | 245.1 | 241.9 | 228.4 | 234.9 | 236.4 | 229.8 | 226.9 | 227.7 | 228.8 |
| 60° | 663.0 | 270.2 | 221.1 | 220.8 | 208.8 | 216.4 | 220.8 | 214.2 | 205.5 | 206.6 | 208.0 |
| 62.5° | 297.5 | 206.6 | 190.9 | 189.5 | 189.1 | 198.9 | 203.7 | 197.5 | 185.1 | 186.2 | 187.7 |
| 65° | 187.3 | 178.6 | 165.8 | 165.8 | 171.7 | 180.0 | 183.7 | 178.6 | 164.4 | 162.6 | 164.0 |
| 67.5° | 173.8 | 166.2 | 153.1 | 150.6 | 153.5 | 160.4 | 160.7 | 150.9 | 142.6 | 141.1 | 141.1 |
| 70° | 156.0 | 150.2 | 137.5 | 132.4 | 131.3 | 130.9 | 129.8 | 127.3 | 121.8 | 120.4 | 121.1 |
| 72.5° | 129.1 | 125.1 | 117.1 | 111.7 | 108.7 | 108.4 | 104.0 | 101.8 | 97.1 | 96.4 | 96.0 |
| 75° | 85.5 | 86.6 | 86.6 | 85.8 | 83.3 | 82.2 | 77.5 | 75.3 | 69.8 | 67.6 | 67.3 |
| 77.5° | 50.6 | 51.6 | 53.1 | 53.5 | 53.1 | 53.1 | 48.7 | 46.2 | 40.7 | 37.8 | 37.1 |
| 80° | 30.9 | 31.6 | 32.4 | 33.5 | 32.0 | 30.9 | 26.9 | 24.4 | 21.8 | 20.0 | 19.6 |
| 82.5° | 20.0 | 20.7 | 21.1 | 21.8 | 21.1 | 19.6 | 16.4 | 14.9 | 13.1 | 11.6 | 11.3 |
| 85° | 11.3 | 11.6 | 12.4 | 12.4 | 11.3 | 10.2 | 8.4 | 7.3 | 6.2 | 5.5 | 5.5 |
| 87.5° | 4.0 | 4.0 | 4.0 | 4.4 | 3.6 | 3.3 | 2.2 | 1.5 | 1.1 | 1.1 | 1.1 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9


| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) | λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) | λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) | λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) | λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) |
|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_9 = -1.5$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)