

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P634470

Luminaire Tested: GWS-SA3B-827-U-SLR-W-HSS

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P634470
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA3B-827-U-SLR-W-HSS
Description: GALLEON WALL SLIM LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND
SPILL LIGHT ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD
Light Source: (48) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4745.2 lumens
Efficiency: N/A
Efficacy: 69.5 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 68.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P634470
 CATALOG NUMBER: GWS-SA3B-827-U-SLR-W-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 9.6 fc
 Type IV - Short - N/A

REPORT NUMBER: P634470
CATALOG NUMBER: GWS-SA3B-827-U-SLR-W-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 62.5-Deg Vertical

REPORT NUMBER: P634470
 CATALOG NUMBER: GWS-SA3B-827-U-SLR-W-HSS

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 585.6 | 0.0 | 585.6 |
| | % Fixture | 12.3 | 0.0 | 12.3 |
| Street Side | Lumens | 4159.6 | 0.0 | 4159.6 |
| | % Fixture | 87.7 | 0.0 | 87.7 |
| Total | Lumens | 4745.2 | 0.0 | 4745.2 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 21.9 | 0.5 |
| 10°-20° | 82.7 | 1.7 |
| 20°-30° | 179.8 | 3.8 |
| 30°-40° | 295.2 | 6.2 |
| 40°-50° | 542.6 | 11.4 |
| 50°-60° | 1165.4 | 24.6 |
| 60°-70° | 1565.2 | 33.0 |
| 70°-80° | 815.0 | 17.2 |
| 80°-90° | 77.3 | 1.6 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 4745.2 | 100.0 |
| 0°-180° | 4745.2 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P634470
 CATALOG NUMBER: GWS-SA3B-827-U-SLR-W-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 200.5 | 4.2 | | | |
| FM (30°-60°) | 1665.5 | 35.1 | | | |
| FH (60°-80°) | 2219.8 | 46.8 | | | G2/5000 |
| FVH (80°-90°) | 73.8 | 1.6 | | | G1/100 |
| BL (0°-30°) | 84.0 | 1.8 | B0/110 | | |
| BM (30°-60°) | 337.7 | 7.1 | B1/1000 | | |
| BH (60°-80°) | 160.4 | 3.4 | B1/500 | | G1/500 |
| BVH (80°-90°) | 3.4 | 0.1 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G2
 Type IV Short





REPORT NUMBER: P634470
 CATALOG NUMBER: GWS-SA3B-827-U-SLR-W-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 1° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 246.7 | 246.7 | 246.7 | 246.7 | 246.7 | 246.7 | 246.7 | 246.7 | 246.7 | 246.7 | 246.7 |
| 2.5° | 251.6 | 252.7 | 253.8 | 257.6 | 260.4 | 262.5 | 263.1 | 261.5 | 257.6 | 253.8 | 248.3 |
| 5° | 243.9 | 245.0 | 248.8 | 259.3 | 269.7 | 277.9 | 280.6 | 279.0 | 269.7 | 257.6 | 245.0 |
| 7.5° | 243.4 | 245.6 | 254.9 | 276.8 | 299.3 | 316.3 | 320.6 | 316.8 | 299.3 | 275.2 | 249.4 |
| 10° | 263.1 | 266.9 | 280.6 | 320.1 | 361.2 | 391.4 | 403.4 | 387.0 | 359.0 | 315.2 | 273.0 |
| 12.5° | 314.6 | 321.2 | 347.5 | 405.1 | 468.6 | 508.6 | 525.1 | 504.8 | 461.0 | 397.4 | 330.5 |
| 15° | 395.7 | 405.6 | 445.1 | 531.1 | 606.2 | 641.8 | 647.3 | 635.8 | 584.8 | 514.7 | 424.8 |
| 17.5° | 510.3 | 524.5 | 585.9 | 673.6 | 727.9 | 740.5 | 738.9 | 726.8 | 689.5 | 641.3 | 556.3 |
| 20° | 647.3 | 664.3 | 724.6 | 797.0 | 802.4 | 787.6 | 779.4 | 772.3 | 759.7 | 751.5 | 685.1 |
| 22.5° | 785.4 | 806.3 | 869.3 | 887.4 | 838.1 | 795.3 | 775.0 | 780.5 | 799.1 | 839.7 | 812.9 |
| 25° | 923.0 | 942.8 | 1002.0 | 953.2 | 854.5 | 783.3 | 757.5 | 770.6 | 815.0 | 902.7 | 937.3 |
| 27.5° | 1083.6 | 1098.4 | 1133.5 | 998.1 | 857.2 | 773.4 | 748.2 | 768.5 | 822.7 | 942.2 | 1073.8 |
| 30° | 1250.8 | 1259.6 | 1242.6 | 1010.2 | 847.9 | 758.6 | 738.9 | 768.5 | 835.9 | 968.5 | 1176.3 |
| 32.5° | 1373.6 | 1375.2 | 1319.9 | 1011.3 | 843.0 | 746.5 | 730.1 | 765.2 | 848.5 | 990.4 | 1275.5 |
| 35° | 1500.2 | 1492.0 | 1393.9 | 1027.7 | 856.2 | 750.9 | 736.7 | 774.5 | 868.2 | 1016.2 | 1362.6 |
| 37.5° | 1628.4 | 1613.6 | 1476.6 | 1054.6 | 890.1 | 798.6 | 789.8 | 822.2 | 900.0 | 1051.8 | 1458.5 |
| 40° | 1760.0 | 1739.7 | 1562.7 | 1095.1 | 965.8 | 960.8 | 991.0 | 987.2 | 987.2 | 1097.3 | 1557.2 |
| 42.5° | 1920.6 | 1897.0 | 1689.8 | 1209.7 | 1142.3 | 1252.4 | 1334.7 | 1283.7 | 1189.4 | 1202.0 | 1685.4 |
| 45° | 2132.7 | 2112.4 | 1910.2 | 1428.9 | 1419.1 | 1672.3 | 1783.0 | 1682.2 | 1447.6 | 1443.7 | 1899.8 |
| 47.5° | 2472.0 | 2468.2 | 2261.5 | 1683.3 | 1757.8 | 2206.7 | 2420.5 | 2226.4 | 1741.9 | 1699.7 | 2305.4 |
| 50° | 2948.9 | 2937.3 | 2699.5 | 1981.4 | 2160.7 | 2868.8 | 3250.3 | 2926.9 | 2097.6 | 1998.4 | 2848.5 |
| 52.5° | 3486.0 | 3498.1 | 3312.8 | 2307.0 | 2588.7 | 3605.5 | 4136.6 | 3729.4 | 2484.1 | 2378.3 | 3532.0 |
| 55° | 3991.9 | 4061.0 | 4012.2 | 2687.9 | 3007.0 | 4418.9 | 5110.1 | 4609.6 | 2962.6 | 2875.4 | 4298.3 |
| 57.5° | 4387.6 | 4582.2 | 4924.3 | 3241.5 | 3498.6 | 5370.4 | 6197.0 | 5563.9 | 3521.1 | 3682.8 | 5341.4 |
| 60° | 4409.6 | 4667.2 | 5461.4 | 4399.7 | 4131.1 | 6186.6 | 7282.2 | 6496.2 | 4399.2 | 5053.6 | 6158.6 |
| 62.5° | 4079.1 | 4355.3 | 5111.7 | 4925.9 | 4820.1 | 6881.0 | 7839.1 | 7175.9 | 5263.0 | 5856.6 | 5916.3 |
| 65° | 3700.9 | 3979.9 | 4721.4 | 4329.0 | 4740.1 | 6851.4 | 7697.7 | 7191.8 | 5341.4 | 5310.7 | 5482.8 |
| 67.5° | 3129.2 | 3379.7 | 4051.1 | 3831.9 | 4369.0 | 6520.9 | 7044.4 | 6738.5 | 4921.0 | 4967.0 | 5043.7 |
| 70° | 2284.0 | 2525.2 | 3148.4 | 3159.3 | 3815.4 | 5925.1 | 6052.8 | 6010.6 | 4531.8 | 4580.6 | 4361.3 |
| 72.5° | 1649.8 | 1853.2 | 2390.9 | 2590.9 | 3045.9 | 4968.6 | 4880.4 | 5043.2 | 3888.3 | 4079.6 | 3503.0 |
| 75° | 1186.1 | 1338.5 | 1754.0 | 2253.8 | 2414.4 | 3689.9 | 3493.7 | 3905.9 | 3119.9 | 3512.9 | 2633.7 |
| 77.5° | 481.2 | 535.0 | 690.1 | 1518.3 | 1586.8 | 2482.4 | 2138.7 | 2837.0 | 2224.2 | 2308.1 | 1276.6 |
| 80° | 19.7 | 21.9 | 28.5 | 783.8 | 1088.0 | 1396.6 | 1144.5 | 1516.6 | 1468.9 | 929.6 | 301.5 |
| 82.5° | 2.2 | 2.2 | 4.9 | 225.8 | 476.3 | 770.6 | 539.3 | 873.7 | 743.8 | 394.1 | 137.0 |
| 85° | 0.5 | 0.5 | 1.1 | 25.8 | 111.8 | 123.3 | 72.9 | 268.0 | 345.9 | 161.1 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 2.7 | 4.9 | 5.5 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P634470
 CATALOG NUMBER: GWS-SA3B-827-U-SLR-W-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 246.7 | 246.7 | 246.7 | 246.7 | 246.7 | 246.7 | 246.7 | 246.7 | 246.7 | 246.7 | 246.7 |
| 2.5° | 248.3 | 245.6 | 242.3 | 239.0 | 237.3 | 232.9 | 231.3 | 230.2 | 229.1 | 229.7 | 229.7 |
| 5° | 240.1 | 234.0 | 226.9 | 219.8 | 216.0 | 211.6 | 209.4 | 208.3 | 208.8 | 211.0 | 211.0 |
| 7.5° | 239.0 | 227.5 | 212.1 | 202.8 | 198.4 | 195.1 | 192.9 | 191.8 | 192.4 | 195.1 | 196.2 |
| 10° | 257.1 | 236.8 | 209.4 | 193.5 | 188.6 | 185.3 | 183.1 | 181.4 | 180.3 | 182.5 | 183.1 |
| 12.5° | 296.0 | 268.0 | 222.5 | 192.4 | 183.6 | 179.2 | 177.6 | 174.3 | 172.7 | 173.8 | 174.3 |
| 15° | 376.6 | 328.3 | 248.8 | 196.8 | 179.2 | 174.3 | 171.6 | 168.8 | 166.1 | 165.5 | 166.1 |
| 17.5° | 481.8 | 412.7 | 288.9 | 207.2 | 175.9 | 169.9 | 166.1 | 162.2 | 158.4 | 157.9 | 157.3 |
| 20° | 612.2 | 516.3 | 344.8 | 223.6 | 173.2 | 166.1 | 160.6 | 155.1 | 150.2 | 148.5 | 148.5 |
| 22.5° | 731.2 | 641.3 | 416.6 | 243.9 | 169.4 | 160.6 | 154.0 | 147.4 | 142.0 | 139.2 | 138.7 |
| 25° | 876.4 | 773.9 | 502.6 | 267.5 | 163.9 | 153.5 | 146.3 | 139.8 | 134.3 | 131.0 | 129.9 |
| 27.5° | 1022.8 | 913.7 | 600.2 | 298.2 | 157.3 | 146.3 | 139.8 | 133.7 | 127.7 | 123.9 | 122.8 |
| 30° | 1164.7 | 1064.4 | 709.8 | 336.5 | 152.4 | 139.2 | 133.7 | 127.7 | 122.2 | 116.2 | 114.6 |
| 32.5° | 1317.1 | 1218.5 | 832.6 | 379.3 | 148.5 | 134.3 | 128.3 | 122.8 | 115.7 | 110.2 | 107.4 |
| 35° | 1464.0 | 1377.4 | 968.0 | 421.0 | 144.7 | 129.9 | 123.3 | 117.8 | 110.2 | 104.1 | 100.3 |
| 37.5° | 1612.0 | 1539.1 | 1109.4 | 446.2 | 139.2 | 123.9 | 117.8 | 113.5 | 104.7 | 97.6 | 93.2 |
| 40° | 1768.8 | 1706.3 | 1262.3 | 435.8 | 134.3 | 117.3 | 114.0 | 109.1 | 99.2 | 91.0 | 85.5 |
| 42.5° | 1940.9 | 1865.8 | 1418.0 | 395.7 | 129.9 | 111.8 | 108.5 | 103.6 | 94.3 | 84.4 | 77.3 |
| 45° | 2157.4 | 2040.6 | 1545.7 | 335.4 | 132.1 | 106.3 | 99.8 | 98.7 | 89.9 | 77.3 | 68.5 |
| 47.5° | 2529.5 | 2309.2 | 1644.9 | 296.5 | 146.9 | 100.3 | 92.6 | 95.4 | 86.1 | 70.2 | 60.3 |
| 50° | 3099.0 | 2754.3 | 1737.5 | 293.8 | 169.4 | 97.6 | 86.1 | 93.2 | 82.2 | 63.0 | 53.2 |
| 52.5° | 3641.7 | 3206.5 | 1796.7 | 317.9 | 189.1 | 104.7 | 79.5 | 90.4 | 79.5 | 58.1 | 48.2 |
| 55° | 4160.7 | 3467.4 | 1690.9 | 335.4 | 207.7 | 126.1 | 74.5 | 86.1 | 76.2 | 55.4 | 46.6 |
| 57.5° | 4720.4 | 3583.6 | 1331.4 | 371.1 | 220.9 | 144.2 | 75.6 | 79.5 | 71.8 | 53.7 | 46.0 |
| 60° | 4887.5 | 3435.0 | 803.5 | 417.7 | 213.8 | 149.6 | 83.9 | 70.7 | 65.8 | 50.4 | 44.4 |
| 62.5° | 4627.7 | 3082.6 | 474.1 | 380.4 | 207.7 | 141.4 | 95.9 | 65.2 | 59.7 | 46.0 | 41.1 |
| 65° | 4239.1 | 2604.1 | 309.1 | 321.2 | 220.3 | 126.1 | 101.9 | 62.5 | 54.3 | 41.7 | 36.2 |
| 67.5° | 3795.1 | 2097.6 | 216.5 | 189.6 | 203.4 | 113.5 | 86.1 | 61.9 | 48.8 | 35.1 | 29.6 |
| 70° | 3196.6 | 1570.9 | 152.4 | 125.5 | 169.4 | 100.9 | 66.9 | 60.3 | 42.8 | 28.5 | 23.0 |
| 72.5° | 2469.8 | 983.3 | 113.5 | 81.1 | 120.6 | 82.2 | 53.2 | 51.0 | 34.5 | 23.6 | 17.5 |
| 75° | 1821.4 | 560.7 | 80.0 | 58.6 | 79.5 | 62.5 | 39.5 | 36.2 | 29.6 | 22.5 | 15.9 |
| 77.5° | 951.0 | 280.6 | 49.9 | 44.9 | 45.5 | 38.9 | 28.5 | 26.3 | 27.4 | 22.5 | 14.8 |
| 80° | 182.5 | 55.9 | 30.1 | 32.9 | 24.7 | 24.7 | 20.8 | 21.9 | 24.1 | 18.1 | 12.6 |
| 82.5° | 76.2 | 12.1 | 16.4 | 18.6 | 15.3 | 17.0 | 17.0 | 17.5 | 17.0 | 13.2 | 9.3 |
| 85° | 0.0 | 0.0 | 7.1 | 7.7 | 10.4 | 10.4 | 8.8 | 8.8 | 8.8 | 7.7 | 5.5 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.5 | 1.6 | 3.3 | 3.8 | 4.4 | 3.3 | 2.2 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P634470
 CATALOG NUMBER: GWS-SA3B-827-U-SLR-W-HSS

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 246.7 | 246.7 | 246.7 | 246.7 | 246.7 | 246.7 | 246.7 | 246.7 | 246.7 | 246.7 | 246.7 |
| 2.5° | 229.1 | 228.0 | 229.7 | 230.8 | 231.9 | 231.9 | 230.8 | 229.7 | 228.0 | 229.7 | 228.0 |
| 5° | 211.6 | 213.2 | 216.0 | 217.1 | 218.1 | 216.0 | 214.9 | 211.6 | 208.8 | 209.4 | 208.3 |
| 7.5° | 197.9 | 199.5 | 202.8 | 205.0 | 205.0 | 203.9 | 200.6 | 197.3 | 192.9 | 192.9 | 192.4 |
| 10° | 185.3 | 187.5 | 191.3 | 194.0 | 195.1 | 194.0 | 190.7 | 186.4 | 182.5 | 182.5 | 180.9 |
| 12.5° | 174.8 | 177.6 | 182.0 | 185.8 | 186.9 | 185.8 | 182.5 | 178.1 | 173.8 | 173.8 | 172.7 |
| 15° | 166.1 | 169.4 | 174.3 | 178.7 | 180.3 | 178.7 | 174.8 | 169.4 | 165.0 | 165.5 | 163.9 |
| 17.5° | 157.9 | 160.6 | 167.2 | 172.1 | 173.8 | 172.1 | 167.2 | 160.0 | 155.7 | 156.8 | 155.7 |
| 20° | 148.5 | 151.8 | 158.4 | 163.9 | 165.5 | 163.9 | 158.4 | 150.7 | 146.3 | 146.3 | 146.9 |
| 22.5° | 138.7 | 142.0 | 148.5 | 152.4 | 154.6 | 152.9 | 147.4 | 140.3 | 135.9 | 135.9 | 136.5 |
| 25° | 129.9 | 131.5 | 136.5 | 140.3 | 140.9 | 139.2 | 134.8 | 129.4 | 126.1 | 127.7 | 128.3 |
| 27.5° | 121.7 | 121.7 | 123.9 | 126.1 | 125.5 | 123.9 | 122.2 | 117.8 | 117.3 | 118.9 | 120.6 |
| 30° | 112.9 | 110.2 | 109.1 | 107.4 | 106.9 | 106.3 | 108.0 | 108.0 | 109.1 | 111.3 | 112.9 |
| 32.5° | 105.2 | 99.8 | 94.8 | 89.9 | 87.2 | 89.3 | 93.7 | 97.6 | 101.4 | 104.7 | 106.3 |
| 35° | 96.5 | 87.7 | 79.5 | 72.9 | 68.5 | 71.8 | 78.9 | 86.1 | 92.6 | 97.0 | 99.8 |
| 37.5° | 87.7 | 75.1 | 65.2 | 57.0 | 53.7 | 56.5 | 64.1 | 74.0 | 83.9 | 89.3 | 93.2 |
| 40° | 78.4 | 62.5 | 51.0 | 44.4 | 41.1 | 43.8 | 51.5 | 61.4 | 74.5 | 81.7 | 86.6 |
| 42.5° | 69.1 | 51.5 | 41.1 | 34.5 | 32.9 | 34.5 | 40.6 | 50.4 | 64.7 | 73.4 | 80.0 |
| 45° | 59.7 | 42.8 | 32.9 | 28.0 | 26.3 | 28.0 | 32.9 | 41.1 | 55.4 | 65.2 | 72.9 |
| 47.5° | 51.5 | 36.2 | 27.4 | 23.0 | 21.9 | 23.6 | 27.4 | 34.5 | 46.6 | 56.5 | 65.2 |
| 50° | 44.9 | 31.8 | 23.6 | 19.7 | 18.6 | 20.3 | 23.6 | 29.1 | 39.5 | 48.2 | 57.6 |
| 52.5° | 40.6 | 29.6 | 20.8 | 17.0 | 16.4 | 17.5 | 20.3 | 24.7 | 33.4 | 41.1 | 49.9 |
| 55° | 39.5 | 29.6 | 19.2 | 15.3 | 14.8 | 15.9 | 18.1 | 21.4 | 29.1 | 35.6 | 43.3 |
| 57.5° | 40.6 | 31.8 | 18.1 | 13.2 | 12.6 | 13.7 | 15.9 | 18.6 | 25.2 | 30.7 | 37.8 |
| 60° | 40.6 | 32.3 | 15.9 | 10.4 | 9.9 | 11.0 | 13.2 | 16.4 | 22.5 | 26.9 | 32.9 |
| 62.5° | 36.7 | 29.6 | 13.2 | 8.2 | 7.1 | 8.2 | 11.0 | 13.7 | 19.7 | 24.1 | 29.1 |
| 65° | 31.8 | 25.2 | 11.0 | 6.0 | 4.9 | 6.0 | 8.8 | 11.5 | 17.0 | 20.8 | 26.3 |
| 67.5° | 25.8 | 19.2 | 8.2 | 4.4 | 3.3 | 4.4 | 6.6 | 9.3 | 14.3 | 18.1 | 23.6 |
| 70° | 19.2 | 13.7 | 6.6 | 3.8 | 3.3 | 3.8 | 6.0 | 8.8 | 12.6 | 16.4 | 21.9 |
| 72.5° | 14.3 | 9.3 | 5.5 | 3.8 | 2.7 | 3.8 | 5.5 | 8.2 | 12.1 | 15.9 | 20.8 |
| 75° | 12.1 | 7.7 | 4.9 | 3.3 | 2.7 | 3.3 | 4.9 | 7.7 | 11.0 | 14.8 | 19.7 |
| 77.5° | 11.5 | 7.1 | 4.4 | 2.7 | 2.2 | 2.7 | 4.4 | 6.6 | 9.9 | 13.7 | 19.2 |
| 80° | 9.9 | 6.0 | 3.8 | 2.2 | 1.6 | 2.2 | 3.8 | 5.5 | 7.7 | 10.4 | 14.8 |
| 82.5° | 7.7 | 4.9 | 2.7 | 1.1 | 0.5 | 1.1 | 2.7 | 3.3 | 4.9 | 6.0 | 8.8 |
| 85° | 4.9 | 2.7 | 1.1 | 0.0 | 0.0 | 0.0 | 1.1 | 2.2 | 2.2 | 2.7 | 4.4 |
| 87.5° | 2.2 | 0.5 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.5 | 1.1 | 1.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P634470
 CATALOG NUMBER: GWS-SA3B-827-U-SLR-W-HSS

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 359° | 360° |
|-------|-------|-------|-------|-------|-------|-------|--------|--------|--------|--------|
| 0° | 246.7 | 246.7 | 246.7 | 246.7 | 246.7 | 246.7 | 246.7 | 246.7 | 246.7 | 246.7 |
| 2.5° | 231.3 | 231.9 | 232.9 | 234.6 | 238.4 | 241.7 | 245.0 | 249.4 | 251.6 | 251.6 |
| 5° | 209.4 | 209.9 | 210.5 | 212.7 | 218.1 | 222.5 | 229.7 | 238.4 | 242.8 | 243.9 |
| 7.5° | 192.4 | 193.5 | 194.6 | 196.2 | 201.7 | 207.7 | 217.1 | 233.5 | 241.7 | 243.4 |
| 10° | 182.5 | 184.2 | 186.4 | 189.6 | 194.6 | 201.2 | 217.1 | 246.7 | 260.4 | 263.1 |
| 12.5° | 174.8 | 177.6 | 179.8 | 183.6 | 189.6 | 200.1 | 231.9 | 283.9 | 308.0 | 314.6 |
| 15° | 167.2 | 170.5 | 173.8 | 177.6 | 184.2 | 203.9 | 260.4 | 350.8 | 390.8 | 395.7 |
| 17.5° | 159.5 | 163.3 | 167.7 | 172.1 | 180.3 | 213.2 | 305.3 | 443.4 | 499.3 | 510.3 |
| 20° | 150.7 | 155.7 | 161.7 | 167.2 | 176.5 | 228.0 | 367.8 | 553.6 | 623.8 | 647.3 |
| 22.5° | 141.4 | 147.4 | 154.6 | 161.7 | 172.1 | 246.1 | 443.4 | 672.0 | 770.1 | 785.4 |
| 25° | 133.7 | 139.8 | 146.3 | 153.5 | 165.0 | 268.0 | 535.0 | 818.9 | 908.2 | 923.0 |
| 27.5° | 126.6 | 132.6 | 138.7 | 145.3 | 157.9 | 296.5 | 645.1 | 975.1 | 1068.3 | 1083.6 |
| 30° | 118.9 | 126.1 | 132.1 | 138.7 | 151.3 | 331.6 | 772.3 | 1148.3 | 1236.5 | 1250.8 |
| 32.5° | 112.4 | 119.5 | 125.5 | 132.1 | 146.3 | 370.0 | 906.0 | 1301.8 | 1373.6 | 1373.6 |
| 35° | 106.9 | 114.6 | 118.9 | 127.7 | 142.5 | 394.6 | 1032.6 | 1448.1 | 1502.4 | 1500.2 |
| 37.5° | 100.9 | 110.2 | 113.5 | 119.5 | 137.6 | 397.4 | 1151.6 | 1602.7 | 1642.7 | 1628.4 |
| 40° | 94.8 | 104.7 | 109.6 | 112.9 | 132.1 | 374.9 | 1282.0 | 1744.6 | 1778.6 | 1760.0 |
| 42.5° | 89.3 | 97.0 | 104.1 | 108.0 | 128.8 | 335.4 | 1386.7 | 1896.5 | 1937.0 | 1920.6 |
| 45° | 83.9 | 90.4 | 94.8 | 101.9 | 131.0 | 308.0 | 1476.6 | 2073.5 | 2144.8 | 2132.7 |
| 47.5° | 78.4 | 83.9 | 86.6 | 97.6 | 145.8 | 295.4 | 1531.4 | 2347.6 | 2481.9 | 2472.0 |
| 50° | 72.4 | 78.9 | 78.9 | 96.5 | 167.7 | 299.8 | 1579.1 | 2744.4 | 2952.1 | 2948.9 |
| 52.5° | 66.3 | 73.4 | 72.4 | 104.7 | 184.7 | 320.1 | 1633.4 | 3094.6 | 3455.9 | 3486.0 |
| 55° | 60.3 | 66.9 | 68.0 | 121.1 | 194.6 | 337.6 | 1423.5 | 3242.1 | 3886.1 | 3991.9 |
| 57.5° | 53.7 | 57.6 | 70.7 | 133.7 | 191.3 | 388.6 | 975.1 | 3268.9 | 4160.7 | 4387.6 |
| 60° | 46.6 | 49.9 | 80.0 | 131.0 | 180.9 | 359.0 | 613.9 | 3027.8 | 4121.8 | 4409.6 |
| 62.5° | 40.6 | 46.0 | 84.4 | 115.7 | 184.2 | 311.3 | 391.4 | 2580.5 | 3750.7 | 4079.1 |
| 65° | 35.6 | 44.4 | 76.7 | 104.7 | 186.4 | 211.0 | 264.2 | 2099.3 | 3388.4 | 3700.9 |
| 67.5° | 31.8 | 49.3 | 63.0 | 93.2 | 160.0 | 148.5 | 181.4 | 1631.2 | 2849.1 | 3129.2 |
| 70° | 29.1 | 50.4 | 51.5 | 80.0 | 123.9 | 95.4 | 119.5 | 1097.9 | 1963.9 | 2284.0 |
| 72.5° | 26.3 | 37.3 | 38.9 | 64.1 | 80.0 | 58.1 | 77.3 | 628.1 | 1431.7 | 1649.8 |
| 75° | 25.2 | 25.2 | 26.9 | 41.7 | 44.4 | 42.2 | 49.9 | 374.9 | 1026.6 | 1186.1 |
| 77.5° | 23.6 | 19.2 | 17.0 | 26.9 | 24.1 | 30.1 | 29.6 | 166.6 | 445.1 | 481.2 |
| 80° | 18.6 | 13.7 | 11.5 | 17.0 | 16.4 | 20.3 | 17.5 | 13.7 | 20.3 | 19.7 |
| 82.5° | 11.5 | 8.8 | 8.2 | 10.4 | 9.3 | 10.4 | 8.2 | 2.2 | 2.2 | 2.2 |
| 85° | 5.5 | 4.9 | 4.4 | 4.4 | 4.9 | 4.4 | 3.3 | 1.1 | 0.5 | 0.5 |
| 87.5° | 2.7 | 2.7 | 2.2 | 1.6 | 2.2 | 2.2 | 1.6 | 0.5 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26




| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_g = -1.5$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)