

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P636916

Luminaire Tested: GWS-SA4B-827-U-5NQ-W-GRSBK

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P636916  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA4B-827-U-5NQ-W-GRSBK  
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE V NARROW OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK  
Light Source: (64) 2700K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7487.4 lumens  
Efficiency: N/A  
Efficacy: 79.3 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B3 - U0 - G0  
  
Input Watts (W): 94.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P636916  
 CATALOG NUMBER: GWS-SA4B-827-U-5NQ-W-GRSBK

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 12.2 fc  
 Type V - Short - N/A

REPORT NUMBER: P636916  
CATALOG NUMBER: GWS-SA4B-827-U-5NQ-W-GRSBK

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral    - - - Horizontal Cone Through 55-Deg Vertical

REPORT NUMBER: P636916

CATALOG NUMBER: GWS-SA4B-827-U-5NQ-W-GRSBK

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 3743.7   | 0.0    | 3743.7 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Street Side</b> | Lumens    | 3743.7   | 0.0    | 3743.7 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Total</b>       | Lumens    | 7487.4   | 0.0    | 7487.4 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 118.6  | 1.6       |
| 10°-20°   | 384.5  | 5.1       |
| 20°-30°   | 744.6  | 9.9       |
| 30°-40°   | 1334.0 | 17.8      |
| 40°-50°   | 2236.5 | 29.9      |
| 50°-60°   | 2394.1 | 32.0      |
| 60°-70°   | 263.1  | 3.5       |
| 70°-80°   | 11.6   | 0.2       |
| 80°-90°   | 0.6    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 7487.4 | 100.0     |
| 0°-180°   | 7487.4 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P636916


CATALOG NUMBER: GWS-SA4B-827-U-5NQ-W-GRSBK

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |        |
|----------------|--------|-----------|-------------------------|------|--------|
|                |        |           | B                       | U    | G      |
| FL (0°-30°)    | 623.8  | 8.3       |                         |      |        |
| FM (30°-60°)   | 2982.3 | 39.8      |                         |      |        |
| FH (60°-80°)   | 137.3  | 1.8       |                         |      | G0/660 |
| FVH (80°-90°)  | 0.3    | 0.0       |                         |      | G0/10  |
| BL (0°-30°)    | 623.8  | 8.3       | B2/1000                 |      |        |
| BM (30°-60°)   | 2982.3 | 39.8      | B3/5000                 |      |        |
| BH (60°-80°)   | 137.3  | 1.8       | B1/500                  |      | G0/660 |
| BVH (80°-90°)  | 0.3    | 0.0       |                         |      | G0/10  |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |        |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |        |

**BUG Rating: B3-U0-G0**

Type V Short





REPORT NUMBER: P636916

CATALOG NUMBER: GWS-SA4B-827-U-5NQ-W-GRSBK

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    | 90°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1210.6 | 1210.6 | 1210.6 | 1210.6 | 1210.6 | 1210.6 | 1210.6 | 1210.6 | 1210.6 | 1210.6 | 1210.6 |
| 2.5°  | 1208.3 | 1208.3 | 1211.3 | 1213.6 | 1213.6 | 1219.7 | 1217.4 | 1215.1 | 1215.1 | 1212.1 | 1218.2 |
| 5°    | 1225.8 | 1225.1 | 1228.1 | 1229.6 | 1226.6 | 1232.7 | 1228.9 | 1226.6 | 1225.1 | 1222.0 | 1228.1 |
| 7.5°  | 1244.9 | 1245.7 | 1246.4 | 1249.5 | 1247.9 | 1254.0 | 1251.0 | 1246.4 | 1244.9 | 1240.3 | 1246.4 |
| 10°   | 1267.8 | 1267.8 | 1269.3 | 1273.1 | 1273.9 | 1281.5 | 1278.5 | 1273.1 | 1268.5 | 1264.0 | 1270.1 |
| 12.5° | 1296.8 | 1297.5 | 1299.8 | 1305.2 | 1308.2 | 1316.6 | 1312.0 | 1301.3 | 1294.5 | 1289.1 | 1296.0 |
| 15°   | 1338.7 | 1338.0 | 1341.0 | 1348.6 | 1352.4 | 1358.6 | 1351.7 | 1337.2 | 1328.8 | 1322.7 | 1327.3 |
| 17.5° | 1384.5 | 1384.5 | 1386.0 | 1393.6 | 1399.0 | 1408.1 | 1399.7 | 1382.2 | 1374.6 | 1366.2 | 1370.8 |
| 20°   | 1434.8 | 1437.1 | 1438.6 | 1444.0 | 1453.1 | 1462.3 | 1455.4 | 1437.9 | 1429.5 | 1418.8 | 1424.2 |
| 22.5° | 1501.2 | 1498.9 | 1499.7 | 1508.8 | 1521.8 | 1530.9 | 1525.6 | 1505.0 | 1490.5 | 1482.1 | 1485.2 |
| 25°   | 1575.2 | 1574.4 | 1576.7 | 1590.4 | 1604.9 | 1614.9 | 1607.2 | 1580.5 | 1566.0 | 1551.5 | 1557.6 |
| 27.5° | 1666.0 | 1666.7 | 1668.3 | 1685.0 | 1707.9 | 1722.4 | 1703.3 | 1676.6 | 1656.8 | 1637.7 | 1642.3 |
| 30°   | 1773.5 | 1772.0 | 1776.6 | 1799.5 | 1833.0 | 1855.9 | 1833.8 | 1796.4 | 1768.2 | 1749.9 | 1752.2 |
| 32.5° | 1887.9 | 1889.5 | 1901.7 | 1938.3 | 1982.5 | 2023.0 | 1977.9 | 1928.4 | 1891.8 | 1857.4 | 1862.0 |
| 35°   | 2011.5 | 2015.3 | 2042.8 | 2096.9 | 2169.4 | 2223.6 | 2161.0 | 2079.4 | 2027.5 | 1983.3 | 1984.8 |
| 37.5° | 2157.2 | 2166.4 | 2204.5 | 2285.4 | 2389.1 | 2461.6 | 2370.0 | 2261.7 | 2194.6 | 2139.7 | 2135.8 |
| 40°   | 2348.7 | 2359.3 | 2411.2 | 2507.3 | 2633.2 | 2699.6 | 2593.5 | 2482.2 | 2399.0 | 2339.5 | 2330.4 |
| 42.5° | 2568.4 | 2582.1 | 2638.5 | 2736.9 | 2862.8 | 2907.8 | 2804.1 | 2710.2 | 2635.5 | 2565.3 | 2562.3 |
| 45°   | 2816.3 | 2823.9 | 2869.7 | 2945.2 | 3036.0 | 3046.6 | 2968.8 | 2917.0 | 2841.4 | 2775.8 | 2770.5 |
| 47.5° | 3048.9 | 3056.6 | 3087.8 | 3126.7 | 3148.1 | 3109.9 | 3096.2 | 3073.3 | 2975.7 | 2894.8 | 2878.1 |
| 50°   | 3225.9 | 3232.0 | 3270.9 | 3286.2 | 3226.7 | 3145.8 | 3172.5 | 3123.7 | 3017.6 | 2926.9 | 2900.9 |
| 52.5° | 3213.7 | 3228.9 | 3328.9 | 3415.8 | 3378.5 | 3312.9 | 3241.1 | 3135.9 | 2971.1 | 2846.8 | 2814.7 |
| 55°   | 2766.7 | 2787.3 | 3001.6 | 3287.7 | 3543.2 | 3571.4 | 3284.6 | 2945.2 | 2635.5 | 2453.2 | 2420.4 |
| 57.5° | 1778.1 | 1783.4 | 2045.1 | 2446.3 | 3022.2 | 3203.8 | 2724.0 | 2220.5 | 1835.3 | 1634.7 | 1621.0 |
| 60°   | 653.7  | 643.0  | 840.6  | 1173.2 | 1740.7 | 1932.9 | 1603.4 | 1122.8 | 800.9  | 659.1  | 647.6  |
| 62.5° | 157.1  | 158.7  | 196.8  | 295.2  | 546.2  | 675.8  | 534.0  | 298.3  | 189.9  | 159.4  | 157.9  |
| 65°   | 79.3   | 77.8   | 78.6   | 84.7   | 116.7  | 139.6  | 114.4  | 80.9   | 77.8   | 78.6   | 77.8   |
| 67.5° | 51.1   | 50.3   | 51.9   | 52.6   | 51.9   | 48.8   | 48.1   | 49.6   | 49.6   | 50.3   | 48.8   |
| 70°   | 31.3   | 30.5   | 32.0   | 34.3   | 32.8   | 29.0   | 30.5   | 32.0   | 30.5   | 29.7   | 29.7   |
| 72.5° | 16.8   | 16.8   | 18.3   | 19.8   | 18.3   | 16.8   | 16.8   | 17.5   | 16.8   | 16.8   | 16.8   |
| 75°   | 7.6    | 7.6    | 8.4    | 9.2    | 7.6    | 7.6    | 7.6    | 7.6    | 7.6    | 7.6    | 7.6    |
| 77.5° | 2.3    | 2.3    | 3.1    | 3.1    | 2.3    | 2.3    | 2.3    | 2.3    | 3.1    | 3.1    | 3.1    |
| 80°   | 0.8    | 1.5    | 1.5    | 0.8    | 0.8    | 0.8    | 0.8    | 0.8    | 1.5    | 1.5    | 1.5    |
| 82.5° | 0.8    | 0.8    | 0.8    | 0.8    | 0.8    | 0.8    | 0.8    | 0.8    | 0.8    | 0.8    | 0.8    |
| 85°   | 0.8    | 0.8    | 0.8    | 0.0    | 0.0    | 0.0    | 0.0    | 0.8    | 0.8    | 0.8    | 0.8    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.8    | 0.8    | 0.8    | 0.8    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine



**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2407-157-9  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/03/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Invue  
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**  
 Description: Epic Modern Light Square 40W 5WQ Optic

**Spectral Parameters**

CCT (K): 2764  
 CIE u': 0.2591  
 CIE v': 0.5290  
 Duv: 0.0020  
 CIE x: 0.4581  
 CIE y: 0.4156  
 CIE z: 0.1263  
 Peak Wavelength (nm): 603  
 Dominant Wavelength (nm): 583  
 Purity: 62.2537  
 Rf: 84.7  
 Rg: 94.6

|           |      |      |      |
|-----------|------|------|------|
| CRI (Ra): | 80.9 |      |      |
| R1:       | 78.8 | R9:  | -1.5 |
| R2:       | 89.9 | R10: | 77.9 |
| R3:       | 96.2 | R11: | 78.9 |
| R4:       | 79.1 | R12: | 71.6 |
| R5:       | 79.1 | R13: | 81.2 |
| R6:       | 88.8 | R14: | 98.5 |
| R7:       | 81.3 | R15: | 69.9 |
| R8:       | 54.3 |      |      |



**Test Conditions**

Stabilization Time: 81M  
 Operation Time: 2H 21M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

**Photopic Flux vs. Wavelength**



**Photopic Lumens: 4337.9**

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | 0.0                            | 490               | 18018                                | 2.6                            | 620               | 87426                                | 22.8                           | 750               | 2680                                 | 0.0                            | 880               | 58                                   | 0.0                            |
| 365               | 0                                    | 0.0                            | 495               | 22295                                | 3.9                            | 625               | 83013                                | 18.2                           | 755               | 2287                                 | 0.0                            | 885               | 46                                   | 0.0                            |
| 370               | 0                                    | 0.0                            | 500               | 26478                                | 5.8                            | 630               | 78077                                | 14.1                           | 760               | 1944                                 | 0.0                            | 890               | 45                                   | 0.0                            |
| 375               | 0                                    | 0.0                            | 505               | 30524                                | 8.5                            | 635               | 72080                                | 10.7                           | 765               | 1653                                 | 0.0                            | 895               | 41                                   | 0.0                            |
| 380               | 0                                    | 0.0                            | 510               | 33611                                | 11.5                           | 640               | 66249                                | 7.9                            | 770               | 1413                                 | 0.0                            | 900               | 38                                   | 0.0                            |
| 385               | 0                                    | 0.0                            | 515               | 36490                                | 15.2                           | 645               | 59973                                | 5.7                            | 775               | 1198                                 | 0.0                            | 905               | 33                                   | 0.0                            |
| 390               | 0                                    | 0.0                            | 520               | 38610                                | 18.7                           | 650               | 53972                                | 3.9                            | 780               | 1025                                 | 0.0                            | 910               | 30                                   | 0.0                            |
| 395               | 0                                    | 0.0                            | 525               | 40511                                | 21.9                           | 655               | 48369                                | 2.7                            | 785               | 874                                  | 0.0                            | 915               | 23                                   | 0.0                            |
| 400               | 48                                   | 0.0                            | 530               | 42223                                | 24.9                           | 660               | 42641                                | 1.8                            | 790               | 747                                  | 0.0                            | 920               | 24                                   | 0.0                            |
| 405               | 201                                  | 0.0                            | 535               | 44137                                | 27.6                           | 665               | 37602                                | 1.1                            | 795               | 639                                  | 0.0                            | 925               | 22                                   | 0.0                            |
| 410               | 457                                  | 0.0                            | 540               | 46032                                | 30.0                           | 670               | 32798                                | 0.7                            | 800               | 547                                  | 0.0                            | 930               | 22                                   | 0.0                            |
| 415               | 925                                  | 0.0                            | 545               | 48553                                | 32.5                           | 675               | 28558                                | 0.5                            | 805               | 473                                  | 0.0                            | 935               | 17                                   | 0.0                            |
| 420               | 1816                                 | 0.0                            | 550               | 51408                                | 34.9                           | 680               | 24782                                | 0.3                            | 810               | 401                                  | 0.0                            | 940               | 13                                   | 0.0                            |
| 425               | 3217                                 | 0.0                            | 555               | 54711                                | 37.4                           | 685               | 21386                                | 0.2                            | 815               | 351                                  | 0.0                            | 945               | 6                                    | 0.0                            |
| 430               | 5520                                 | 0.0                            | 560               | 58847                                | 40.0                           | 690               | 18413                                | 0.1                            | 820               | 307                                  | 0.0                            | 950               | 10                                   | 0.0                            |
| 435               | 9225                                 | 0.1                            | 565               | 63386                                | 42.4                           | 695               | 15721                                | 0.1                            | 825               | 261                                  | 0.0                            | 955               | 11                                   | 0.0                            |
| 440               | 15522                                | 0.2                            | 570               | 68196                                | 44.3                           | 700               | 13432                                | 0.0                            | 830               | 228                                  | 0.0                            | 960               | 8                                    | 0.0                            |
| 445               | 27642                                | 0.6                            | 575               | 73613                                | 46.0                           | 705               | 11513                                | 0.0                            | 835               | 193                                  | 0.0                            | 965               | 12                                   | 0.0                            |
| 450               | 36602                                | 0.9                            | 580               | 79207                                | 47.1                           | 710               | 9780                                 | 0.0                            | 840               | 174                                  | 0.0                            | 970               | 3                                    | 0.0                            |
| 455               | 28292                                | 0.9                            | 585               | 84248                                | 47.0                           | 715               | 8356                                 | 0.0                            | 845               | 151                                  | 0.0                            | 975               | 8                                    | 0.0                            |
| 460               | 21166                                | 0.9                            | 590               | 88397                                | 45.7                           | 720               | 7161                                 | 0.0                            | 850               | 123                                  | 0.0                            | 980               | 2                                    | 0.0                            |
| 465               | 19092                                | 1.0                            | 595               | 91428                                | 43.4                           | 725               | 6067                                 | 0.0                            | 855               | 106                                  | 0.0                            | 985               | 13                                   | 0.0                            |
| 470               | 14951                                | 0.9                            | 600               | 93452                                | 40.3                           | 730               | 5164                                 | 0.0                            | 860               | 95                                   | 0.0                            | 990               | 16                                   | 0.0                            |
| 475               | 12606                                | 1.0                            | 605               | 93959                                | 36.4                           | 735               | 4393                                 | 0.0                            | 865               | 82                                   | 0.0                            | 995               | 20                                   | 0.0                            |
| 480               | 13323                                | 1.3                            | 610               | 93079                                | 32.0                           | 740               | 3694                                 | 0.0                            | 870               | 77                                   | 0.0                            | 1000              | 0                                    | 0.0                            |
| 485               | 15164                                | 1.8                            | 615               | 90707                                | 27.3                           | 745               | 3157                                 | 0.0                            | 875               | 65                                   | 0.0                            |                   |                                      |                                |

REPORT NUMBER: SP1-2407-157-9

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: 5286.7**

**S/P: 1.22**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 0             | 0.0           | 490    | 18018         | 75.9          | 620    | 87426         | 0.4           | 750    | 2680          | 0.0           | 880    | 58            | 0.0           |
| 365    | 0             | 0.0           | 495    | 22295         | 93.2          | 625    | 83013         | 0.2           | 755    | 2287          | 0.0           | 885    | 46            | 0.0           |
| 370    | 0             | 0.0           | 500    | 26478         | 107.8         | 630    | 78077         | 0.1           | 760    | 1944          | 0.0           | 890    | 45            | 0.0           |
| 375    | 0             | 0.0           | 505    | 30524         | 118.7         | 635    | 72080         | 0.1           | 765    | 1653          | 0.0           | 895    | 41            | 0.0           |
| 380    | 0             | 0.0           | 510    | 33611         | 122.2         | 640    | 66249         | 0.1           | 770    | 1413          | 0.0           | 900    | 38            | 0.0           |
| 385    | 0             | 0.0           | 515    | 36490         | 120.8         | 645    | 59973         | 0.0           | 775    | 1198          | 0.0           | 905    | 33            | 0.0           |
| 390    | 0             | 0.0           | 520    | 38610         | 113.9         | 650    | 53972         | 0.0           | 780    | 1025          | 0.0           | 910    | 30            | 0.0           |
| 395    | 0             | 0.0           | 525    | 40511         | 104.1         | 655    | 48369         | 0.0           | 785    | 874           | 0.0           | 915    | 23            | 0.0           |
| 400    | 48            | 0.0           | 530    | 42223         | 92.4          | 660    | 42641         | 0.0           | 790    | 747           | 0.0           | 920    | 24            | 0.0           |
| 405    | 201           | 0.0           | 535    | 44137         | 80.5          | 665    | 37602         | 0.0           | 795    | 639           | 0.0           | 925    | 22            | 0.0           |
| 410    | 457           | 0.1           | 540    | 46032         | 68.2          | 670    | 32798         | 0.0           | 800    | 547           | 0.0           | 930    | 22            | 0.0           |
| 415    | 925           | 0.3           | 545    | 48553         | 57.1          | 675    | 28558         | 0.0           | 805    | 473           | 0.0           | 935    | 17            | 0.0           |
| 420    | 1816          | 1.1           | 550    | 51408         | 46.7          | 680    | 24782         | 0.0           | 810    | 401           | 0.0           | 940    | 13            | 0.0           |
| 425    | 3217          | 2.5           | 555    | 54711         | 37.4          | 685    | 21386         | 0.0           | 815    | 351           | 0.0           | 945    | 6             | 0.0           |
| 430    | 5520          | 5.9           | 560    | 58847         | 29.4          | 690    | 18413         | 0.0           | 820    | 307           | 0.0           | 950    | 10            | 0.0           |
| 435    | 9225          | 12.5          | 565    | 63386         | 22.5          | 695    | 15721         | 0.0           | 825    | 261           | 0.0           | 955    | 11            | 0.0           |
| 440    | 15522         | 26.3          | 570    | 68196         | 16.9          | 700    | 13432         | 0.0           | 830    | 228           | 0.0           | 960    | 8             | 0.0           |
| 445    | 27642         | 55.2          | 575    | 73613         | 12.4          | 705    | 11513         | 0.0           | 835    | 193           | 0.0           | 965    | 12            | 0.0           |
| 450    | 36602         | 85.4          | 580    | 79207         | 9.0           | 710    | 9780          | 0.0           | 840    | 174           | 0.0           | 970    | 3             | 0.0           |
| 455    | 28292         | 75.1          | 585    | 84248         | 6.3           | 715    | 8356          | 0.0           | 845    | 151           | 0.0           | 975    | 8             | 0.0           |
| 460    | 21166         | 63.2          | 590    | 88397         | 4.4           | 720    | 7161          | 0.0           | 850    | 123           | 0.0           | 980    | 2             | 0.0           |
| 465    | 19092         | 63.2          | 595    | 91428         | 3.0           | 725    | 6067          | 0.0           | 855    | 106           | 0.0           | 985    | 13            | 0.0           |
| 470    | 14951         | 54.2          | 600    | 93452         | 2.0           | 730    | 5164          | 0.0           | 860    | 95            | 0.0           | 990    | 16            | 0.0           |
| 475    | 12606         | 48.8          | 605    | 93959         | 1.3           | 735    | 4393          | 0.0           | 865    | 82            | 0.0           | 995    | 20            | 0.0           |
| 480    | 13323         | 54.2          | 610    | 93079         | 0.9           | 740    | 3694          | 0.0           | 870    | 77            | 0.0           | 1000   | 0             | 0.0           |
| 485    | 15164         | 63.3          | 615    | 90707         | 0.5           | 745    | 3157          | 0.0           | 875    | 65            | 0.0           |        |               |               |

REPORT NUMBER: SP1-2407-157-9

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 9797**

**M/P: 2.26**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 0             | 0.0           | 490    | 18018         | 27.7          | 620    | 87426         | 1.1           | 750    | 2680          | 0.0           | 880    | 58            | 0.0           |
| 365    | 0             | 0.0           | 495    | 22295         | 36.0          | 625    | 83013         | 0.7           | 755    | 2287          | 0.0           | 885    | 46            | 0.0           |
| 370    | 0             | 0.0           | 500    | 26478         | 44.2          | 630    | 78077         | 0.4           | 760    | 1944          | 0.0           | 890    | 45            | 0.0           |
| 375    | 0             | 0.0           | 505    | 30524         | 51.8          | 635    | 72080         | 0.3           | 765    | 1653          | 0.0           | 895    | 41            | 0.0           |
| 380    | 0             | 0.0           | 510    | 33611         | 57.0          | 640    | 66249         | 0.2           | 770    | 1413          | 0.0           | 900    | 38            | 0.0           |
| 385    | 0             | 0.0           | 515    | 36490         | 60.5          | 645    | 59973         | 0.1           | 775    | 1198          | 0.0           | 905    | 33            | 0.0           |
| 390    | 0             | 0.0           | 520    | 38610         | 61.4          | 650    | 53972         | 0.1           | 780    | 1025          | 0.0           | 910    | 30            | 0.0           |
| 395    | 0             | 0.0           | 525    | 40511         | 60.6          | 655    | 48369         | 0.0           | 785    | 874           | 0.0           | 915    | 23            | 0.0           |
| 400    | 48            | 0.0           | 530    | 42223         | 58.2          | 660    | 42641         | 0.0           | 790    | 747           | 0.0           | 920    | 24            | 0.0           |
| 405    | 201           | 0.0           | 535    | 44137         | 55.0          | 665    | 37602         | 0.0           | 795    | 639           | 0.0           | 925    | 22            | 0.0           |
| 410    | 457           | 0.0           | 540    | 46032         | 50.9          | 670    | 32798         | 0.0           | 800    | 547           | 0.0           | 930    | 22            | 0.0           |
| 415    | 925           | 0.1           | 545    | 48553         | 46.6          | 675    | 28558         | 0.0           | 805    | 473           | 0.0           | 935    | 17            | 0.0           |
| 420    | 1816          | 0.3           | 550    | 51408         | 42.0          | 680    | 24782         | 0.0           | 810    | 401           | 0.0           | 940    | 13            | 0.0           |
| 425    | 3217          | 0.8           | 555    | 54711         | 37.4          | 685    | 21386         | 0.0           | 815    | 351           | 0.0           | 945    | 6             | 0.0           |
| 430    | 5520          | 1.9           | 560    | 58847         | 32.9          | 690    | 18413         | 0.0           | 820    | 307           | 0.0           | 950    | 10            | 0.0           |
| 435    | 9225          | 4.1           | 565    | 63386         | 28.4          | 695    | 15721         | 0.0           | 825    | 261           | 0.0           | 955    | 11            | 0.0           |
| 440    | 15522         | 8.7           | 570    | 68196         | 24.1          | 700    | 13432         | 0.0           | 830    | 228           | 0.0           | 960    | 8             | 0.0           |
| 445    | 27642         | 18.5          | 575    | 73613         | 20.0          | 705    | 11513         | 0.0           | 835    | 193           | 0.0           | 965    | 12            | 0.0           |
| 450    | 36602         | 28.3          | 580    | 79207         | 16.3          | 710    | 9780          | 0.0           | 840    | 174           | 0.0           | 970    | 3             | 0.0           |
| 455    | 28292         | 24.7          | 585    | 84248         | 12.9          | 715    | 8356          | 0.0           | 845    | 151           | 0.0           | 975    | 8             | 0.0           |
| 460    | 21166         | 20.4          | 590    | 88397         | 9.8           | 720    | 7161          | 0.0           | 850    | 123           | 0.0           | 980    | 2             | 0.0           |
| 465    | 19092         | 20.1          | 595    | 91428         | 7.3           | 725    | 6067          | 0.0           | 855    | 106           | 0.0           | 985    | 13            | 0.0           |
| 470    | 14951         | 17.2          | 600    | 93452         | 5.3           | 730    | 5164          | 0.0           | 860    | 95            | 0.0           | 990    | 16            | 0.0           |
| 475    | 12606         | 15.7          | 605    | 93959         | 3.7           | 735    | 4393          | 0.0           | 865    | 82            | 0.0           | 995    | 20            | 0.0           |
| 480    | 13323         | 18.0          | 610    | 93079         | 2.5           | 740    | 3694          | 0.0           | 870    | 77            | 0.0           | 1000   | 0             | 0.0           |
| 485    | 15164         | 21.9          | 615    | 90707         | 1.7           | 745    | 3157          | 0.0           | 875    | 65            | 0.0           |        |               |               |

**Summary**

$R_f = 84.7$   
 $R_g = 94.6$   
 CIE  $R_a = 80.9$   
 $R_g = -1.5$



**Color Vector Graphics**



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 |            |





Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)