

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P636949

Luminaire Tested: GWS-SA4B-827-U-T2-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P636949
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA4B-827-U-T2-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II OPTICS W/ FACTORY INSALLED GLARE SHIELD, WH
Light Source: (64) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8871 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B2 - U0 - G1


Input Watts (W): 94.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P636949
 CATALOG NUMBER: GWS-SA4B-827-U-T2-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 23.5 fc
 Type II - Short - N/A

REPORT NUMBER: P636949
CATALOG NUMBER: GWS-SA4B-827-U-T2-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 75-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P636949

CATALOG NUMBER: GWS-SA4B-827-U-T2-W-GRSWH


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 2399.8 | 0.0 | 2399.8 |
| | % Fixture | 27.1 | 0.0 | 27.1 |
| Street Side | Lumens | 6471.2 | 0.0 | 6471.2 |
| | % Fixture | 72.9 | 0.0 | 72.9 |
| Total | Lumens | 8871.0 | 0.0 | 8871.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 166.2 | 1.9 |
| 10°-20° | 529.3 | 6.0 |
| 20°-30° | 938.7 | 10.6 |
| 30°-40° | 1437.0 | 16.2 |
| 40°-50° | 2000.9 | 22.6 |
| 50°-60° | 2292.6 | 25.8 |
| 60°-70° | 1178.0 | 13.3 |
| 70°-80° | 296.6 | 3.3 |
| 80°-90° | 31.7 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 8871.0 | 100.0 |
| 0°-180° | 8871.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P636949

CATALOG NUMBER: GWS-SA4B-827-U-T2-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 996.7 | 11.2 | | | |
| FM (30°-60°) | 4468.4 | 50.4 | | | |
| FH (60°-80°) | 994.3 | 11.2 | | | G1/1800 |
| FVH (80°-90°) | 11.7 | 0.1 | | | G1/100 |
| BL (0°-30°) | 637.5 | 7.2 | B2/1000 | | |
| BM (30°-60°) | 1262.1 | 14.2 | B2/2500 | | |
| BH (60°-80°) | 480.2 | 5.4 | B1/500 | | G1/500 |
| BVH (80°-90°) | 20.0 | 0.2 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G1
 Type II Short





REPORT NUMBER: P636949

CATALOG NUMBER: GWS-SA4B-827-U-T2-W-GRSWH

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 74° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1661.3 | 1661.3 | 1661.3 | 1661.3 | 1661.3 | 1661.3 | 1661.3 | 1661.3 | 1661.3 | 1661.3 | 1661.3 |
| 2.5° | 1784.9 | 1789.5 | 1784.9 | 1792.5 | 1777.3 | 1770.4 | 1753.6 | 1728.4 | 1708.6 | 1705.6 | 1683.4 |
| 5° | 1923.7 | 1933.6 | 1927.5 | 1924.5 | 1903.9 | 1888.6 | 1863.5 | 1813.1 | 1771.9 | 1765.8 | 1722.3 |
| 7.5° | 2013.0 | 2019.8 | 2019.8 | 2022.1 | 2014.5 | 1996.9 | 1970.2 | 1910.8 | 1852.8 | 1843.6 | 1778.0 |
| 10° | 2042.7 | 2048.1 | 2058.0 | 2077.0 | 2092.3 | 2097.6 | 2080.1 | 2022.9 | 1951.9 | 1942.8 | 1851.3 |
| 12.5° | 2049.6 | 2055.7 | 2070.9 | 2106.0 | 2148.0 | 2186.1 | 2189.2 | 2147.2 | 2067.9 | 2058.0 | 1935.9 |
| 15° | 2062.5 | 2068.6 | 2089.2 | 2132.7 | 2194.5 | 2267.7 | 2312.7 | 2283.8 | 2196.0 | 2185.4 | 2032.0 |
| 17.5° | 2061.0 | 2067.9 | 2098.4 | 2156.4 | 2239.5 | 2345.5 | 2432.5 | 2444.7 | 2353.9 | 2335.6 | 2141.1 |
| 20° | 2057.2 | 2063.3 | 2096.1 | 2167.0 | 2270.0 | 2415.7 | 2572.8 | 2636.2 | 2538.5 | 2521.7 | 2268.5 |
| 22.5° | 2087.7 | 2094.6 | 2119.8 | 2178.5 | 2286.0 | 2469.9 | 2702.5 | 2855.1 | 2757.4 | 2733.8 | 2414.9 |
| 25° | 2156.4 | 2166.3 | 2181.5 | 2222.0 | 2315.0 | 2517.9 | 2835.2 | 3103.0 | 3003.0 | 2974.8 | 2574.4 |
| 27.5° | 2262.4 | 2274.6 | 2296.0 | 2315.0 | 2379.9 | 2578.9 | 2967.2 | 3380.6 | 3280.7 | 3250.9 | 2742.9 |
| 30° | 2392.1 | 2408.1 | 2435.5 | 2448.5 | 2492.8 | 2669.0 | 3110.6 | 3666.7 | 3608.7 | 3567.5 | 2932.9 |
| 32.5° | 2571.3 | 2593.4 | 2619.4 | 2623.2 | 2649.9 | 2805.5 | 3252.5 | 3950.4 | 3949.7 | 3920.7 | 3148.7 |
| 35° | 2804.7 | 2828.4 | 2833.7 | 2839.1 | 2852.0 | 2993.1 | 3424.1 | 4209.0 | 4308.9 | 4275.4 | 3383.7 |
| 37.5° | 3059.5 | 3093.8 | 3102.2 | 3078.6 | 3096.9 | 3218.9 | 3617.1 | 4416.5 | 4621.7 | 4585.8 | 3611.0 |
| 40° | 3331.8 | 3345.5 | 3368.4 | 3331.0 | 3353.9 | 3477.5 | 3806.3 | 4549.2 | 4855.1 | 4816.9 | 3790.2 |
| 42.5° | 3527.1 | 3552.2 | 3586.6 | 3572.8 | 3585.8 | 3698.7 | 3939.0 | 4613.3 | 5021.4 | 4983.2 | 3919.1 |
| 45° | 3739.1 | 3746.8 | 3768.9 | 3765.8 | 3773.5 | 3878.7 | 4034.3 | 4641.5 | 5170.1 | 5135.8 | 4029.0 |
| 47.5° | 3923.7 | 3935.2 | 3949.7 | 3932.9 | 3916.1 | 3984.7 | 4112.1 | 4665.9 | 5341.7 | 5300.5 | 4144.2 |
| 50° | 4101.4 | 4111.4 | 4128.9 | 4080.1 | 4017.5 | 4035.1 | 4150.3 | 4699.5 | 5502.7 | 5473.7 | 4234.9 |
| 52.5° | 4134.2 | 4144.9 | 4227.3 | 4237.2 | 4157.1 | 4095.3 | 4217.4 | 4773.4 | 5597.2 | 5578.9 | 4267.7 |
| 55° | 3721.6 | 3740.7 | 3904.6 | 4093.1 | 4290.6 | 4270.8 | 4324.9 | 4812.4 | 5634.6 | 5639.2 | 4326.5 |
| 57.5° | 2888.6 | 2916.1 | 3155.6 | 3414.2 | 3829.9 | 4173.9 | 4338.7 | 4802.4 | 5621.7 | 5646.8 | 4386.7 |
| 60° | 1894.7 | 1910.8 | 2194.5 | 2484.4 | 2915.3 | 3391.3 | 3883.3 | 4623.9 | 5506.5 | 5542.3 | 4371.5 |
| 62.5° | 1144.2 | 1162.5 | 1390.5 | 1610.2 | 1864.2 | 2182.3 | 2633.9 | 3716.2 | 4615.6 | 4695.6 | 3501.1 |
| 65° | 798.6 | 823.0 | 1022.9 | 1203.7 | 1291.4 | 1225.8 | 1334.1 | 2075.5 | 2875.7 | 2909.2 | 2139.6 |
| 67.5° | 578.9 | 595.7 | 759.7 | 974.8 | 1071.7 | 865.8 | 659.8 | 919.1 | 1252.5 | 1264.7 | 882.5 |
| 70° | 379.1 | 398.2 | 546.9 | 742.2 | 874.9 | 701.8 | 493.5 | 497.3 | 527.1 | 533.2 | 512.6 |
| 72.5° | 208.2 | 219.7 | 337.9 | 492.8 | 517.2 | 419.5 | 385.2 | 413.4 | 434.0 | 434.0 | 439.4 |
| 75° | 107.6 | 117.5 | 138.1 | 162.5 | 196.0 | 229.6 | 277.7 | 319.6 | 341.7 | 343.2 | 341.0 |
| 77.5° | 54.9 | 58.7 | 74.0 | 80.1 | 87.7 | 102.2 | 132.7 | 170.1 | 189.9 | 197.6 | 196.0 |
| 80° | 25.9 | 27.5 | 31.3 | 36.6 | 45.0 | 57.2 | 71.7 | 85.4 | 97.6 | 99.2 | 107.6 |
| 82.5° | 13.7 | 15.3 | 16.8 | 19.8 | 24.4 | 30.5 | 42.0 | 50.3 | 58.0 | 59.5 | 66.4 |
| 85° | 5.3 | 6.1 | 6.9 | 7.6 | 10.7 | 13.0 | 17.5 | 23.6 | 29.0 | 29.0 | 34.3 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.8 | 1.5 | 3.1 | 3.8 | 5.3 | 5.3 | 9.2 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P636949

CATALOG NUMBER: GWS-SA4B-827-U-T2-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1661.3 | 1661.3 | 1661.3 | 1661.3 | 1661.3 | 1661.3 | 1661.3 | 1661.3 | 1661.3 | 1661.3 | 1661.3 |
| 2.5° | 1678.1 | 1656.0 | 1646.1 | 1630.1 | 1617.1 | 1602.6 | 1591.1 | 1582.8 | 1577.4 | 1574.4 | 1571.3 |
| 5° | 1705.6 | 1672.0 | 1645.3 | 1613.3 | 1591.1 | 1569.8 | 1552.2 | 1540.0 | 1533.9 | 1529.4 | 1526.3 |
| 7.5° | 1748.3 | 1703.3 | 1652.9 | 1603.4 | 1564.5 | 1530.1 | 1508.0 | 1495.0 | 1486.6 | 1483.6 | 1481.3 |
| 10° | 1807.0 | 1744.5 | 1661.3 | 1582.8 | 1524.8 | 1487.4 | 1472.2 | 1466.1 | 1466.8 | 1465.3 | 1464.5 |
| 12.5° | 1873.4 | 1787.9 | 1659.0 | 1546.1 | 1482.1 | 1460.0 | 1460.7 | 1470.6 | 1482.1 | 1485.1 | 1485.9 |
| 15° | 1945.1 | 1830.7 | 1636.9 | 1498.9 | 1448.5 | 1450.8 | 1470.6 | 1494.3 | 1515.6 | 1524.0 | 1525.6 |
| 17.5° | 2022.9 | 1866.5 | 1596.5 | 1447.0 | 1421.1 | 1445.5 | 1482.1 | 1521.0 | 1552.2 | 1566.0 | 1569.8 |
| 20° | 2109.8 | 1897.0 | 1539.3 | 1395.9 | 1395.1 | 1435.5 | 1488.9 | 1540.0 | 1579.7 | 1598.0 | 1601.1 |
| 22.5° | 2202.1 | 1916.1 | 1469.1 | 1348.6 | 1368.4 | 1422.6 | 1483.6 | 1537.0 | 1578.9 | 1597.3 | 1601.1 |
| 25° | 2295.2 | 1922.2 | 1392.1 | 1305.1 | 1341.0 | 1402.0 | 1457.7 | 1500.4 | 1540.0 | 1556.1 | 1559.1 |
| 27.5° | 2382.1 | 1904.7 | 1318.8 | 1267.7 | 1315.8 | 1371.5 | 1408.8 | 1431.7 | 1459.2 | 1471.4 | 1473.7 |
| 30° | 2470.6 | 1869.6 | 1257.1 | 1238.0 | 1287.6 | 1329.5 | 1346.3 | 1347.8 | 1358.5 | 1358.5 | 1360.0 |
| 32.5° | 2559.9 | 1817.7 | 1202.9 | 1209.0 | 1252.5 | 1279.9 | 1282.2 | 1264.7 | 1251.7 | 1230.4 | 1229.6 |
| 35° | 2662.8 | 1765.1 | 1158.7 | 1176.2 | 1211.3 | 1228.1 | 1221.2 | 1187.6 | 1156.4 | 1121.3 | 1119.8 |
| 37.5° | 2758.2 | 1710.9 | 1121.3 | 1142.6 | 1164.8 | 1177.0 | 1160.9 | 1120.5 | 1094.6 | 1058.7 | 1053.4 |
| 40° | 2836.8 | 1662.1 | 1085.4 | 1107.6 | 1118.2 | 1128.9 | 1103.0 | 1070.2 | 1074.0 | 1054.2 | 1053.4 |
| 42.5° | 2882.5 | 1614.8 | 1051.9 | 1068.6 | 1075.5 | 1083.1 | 1060.3 | 1035.8 | 1056.4 | 1041.2 | 1042.0 |
| 45° | 2916.1 | 1573.6 | 1021.4 | 1027.5 | 1044.2 | 1055.7 | 1034.3 | 1006.9 | 1011.4 | 952.7 | 939.0 |
| 47.5° | 2954.2 | 1550.7 | 992.4 | 986.3 | 1016.0 | 1035.8 | 1003.0 | 963.4 | 935.9 | 878.0 | 872.6 |
| 50° | 2994.7 | 1542.3 | 961.9 | 945.1 | 980.9 | 1000.0 | 961.9 | 912.3 | 876.4 | 845.2 | 842.1 |
| 52.5° | 3008.4 | 1541.6 | 923.7 | 895.5 | 931.3 | 958.0 | 926.0 | 875.7 | 833.0 | 802.4 | 800.9 |
| 55° | 3062.5 | 1563.7 | 874.9 | 827.6 | 861.2 | 916.1 | 892.4 | 820.0 | 785.7 | 771.9 | 770.4 |
| 57.5° | 3125.9 | 1567.5 | 797.9 | 753.6 | 800.2 | 865.0 | 835.2 | 772.7 | 735.3 | 718.5 | 717.0 |
| 60° | 3099.9 | 1473.7 | 715.5 | 697.2 | 748.3 | 816.9 | 789.5 | 735.3 | 691.8 | 675.8 | 674.3 |
| 62.5° | 2362.3 | 1040.4 | 655.2 | 648.4 | 692.6 | 747.5 | 742.2 | 685.7 | 644.5 | 633.1 | 631.6 |
| 65° | 1421.1 | 730.7 | 597.3 | 596.5 | 627.8 | 680.4 | 687.3 | 641.5 | 598.0 | 582.0 | 582.0 |
| 67.5° | 702.5 | 559.1 | 531.7 | 527.8 | 547.7 | 585.0 | 614.0 | 576.7 | 540.0 | 524.8 | 522.5 |
| 70° | 496.6 | 492.8 | 483.6 | 472.9 | 476.7 | 492.0 | 504.2 | 472.9 | 434.0 | 418.8 | 415.7 |
| 72.5° | 429.4 | 430.2 | 424.1 | 415.7 | 412.7 | 402.0 | 391.3 | 368.4 | 344.8 | 328.8 | 330.3 |
| 75° | 333.3 | 334.9 | 338.7 | 335.6 | 327.2 | 315.8 | 304.3 | 275.4 | 256.3 | 241.0 | 238.0 |
| 77.5° | 194.5 | 202.1 | 214.3 | 211.3 | 212.8 | 196.8 | 192.2 | 164.0 | 146.5 | 135.8 | 133.5 |
| 80° | 109.8 | 114.4 | 119.8 | 123.6 | 119.0 | 112.1 | 102.2 | 87.0 | 81.6 | 74.0 | 72.5 |
| 82.5° | 66.4 | 70.9 | 73.2 | 76.3 | 74.8 | 65.6 | 58.0 | 48.1 | 43.5 | 39.7 | 38.9 |
| 85° | 33.6 | 36.6 | 38.9 | 40.4 | 35.9 | 29.7 | 26.7 | 21.4 | 18.3 | 16.0 | 16.0 |
| 87.5° | 8.4 | 9.2 | 10.7 | 9.2 | 8.4 | 3.8 | 3.1 | 0.8 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions


Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_g = -1.5$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)


| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)