

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P630480

Luminaire Tested: GWS-SA1D-827-U-5MQ-W

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P630480  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA1D-827-U-5MQ-W  
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE V MEDIUM OPTICS  
Light Source: (16) 2700K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4616.2 lumens  
Efficiency: N/A  
Efficacy: 104.2 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B3 - U0 - G1  
  
Input Watts (W): 44.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P630480  
 CATALOG NUMBER: GWS-SA1D-827-U-5MQ-W

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 4.8 fc  
 Type V - Short - N/A

REPORT NUMBER: P630480  
CATALOG NUMBER: GWS-SA1D-827-U-5MQ-W

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral    - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P630480

CATALOG NUMBER: GWS-SA1D-827-U-5MQ-W


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 2308.1   | 0.0    | 2308.1 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Street Side</b> | Lumens    | 2308.1   | 0.0    | 2308.1 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Total</b>       | Lumens    | 4616.2   | 0.0    | 4616.2 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 45.8   | 1.0       |
| 10°-20°   | 134.4  | 2.9       |
| 20°-30°   | 231.8  | 5.0       |
| 30°-40°   | 376.9  | 8.2       |
| 40°-50°   | 634.6  | 13.7      |
| 50°-60°   | 1124.5 | 24.4      |
| 60°-70°   | 1607.3 | 34.8      |
| 70°-80°   | 441.1  | 9.6       |
| 80°-90°   | 19.8   | 0.4       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 4616.2 | 100.0     |
| 0°-180°   | 4616.2 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P630480


CATALOG NUMBER: GWS-SA1D-827-U-5MQ-W

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 206.0  | 4.5       |                         |      |         |
| FM (30°-60°)   | 1068.0 | 23.1      |                         |      |         |
| FH (60°-80°)   | 1024.2 | 22.2      |                         |      | G1/1800 |
| FVH (80°-90°)  | 9.9    | 0.2       |                         |      | G0/10   |
| BL (0°-30°)    | 206.0  | 4.5       | B1/500                  |      |         |
| BM (30°-60°)   | 1068.0 | 23.1      | B2/2500                 |      |         |
| BH (60°-80°)   | 1024.2 | 22.2      | B3/2500                 |      | G1/1800 |
| BVH (80°-90°)  | 9.9    | 0.2       |                         |      | G0/10   |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B3-U0-G1**

Type V Short





REPORT NUMBER: P630480  
 CATALOG NUMBER: GWS-SA1D-827-U-5MQ-W

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    | 90°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 483.5  | 483.5  | 483.5  | 483.5  | 483.5  | 483.5  | 483.5  | 483.5  | 483.5  | 483.5  | 483.5  |
| 2.5°  | 480.3  | 480.0  | 481.5  | 482.5  | 482.2  | 484.4  | 484.1  | 483.5  | 483.5  | 482.5  | 485.1  |
| 5°    | 480.3  | 480.0  | 481.2  | 481.5  | 480.9  | 482.8  | 482.2  | 481.5  | 481.5  | 480.3  | 482.5  |
| 7.5°  | 477.7  | 478.0  | 479.0  | 479.6  | 479.0  | 480.6  | 479.6  | 478.4  | 478.0  | 476.8  | 479.0  |
| 10°   | 472.9  | 473.2  | 474.2  | 475.8  | 476.1  | 479.0  | 477.4  | 475.2  | 474.2  | 472.9  | 475.2  |
| 12.5° | 470.0  | 470.4  | 471.3  | 473.2  | 473.9  | 477.7  | 476.1  | 472.6  | 471.0  | 469.7  | 472.0  |
| 15°   | 469.4  | 469.7  | 471.0  | 472.9  | 473.9  | 477.7  | 476.1  | 472.0  | 469.7  | 468.1  | 470.0  |
| 17.5° | 469.4  | 470.0  | 472.0  | 474.8  | 476.8  | 480.6  | 478.7  | 473.9  | 470.7  | 467.8  | 469.7  |
| 20°   | 469.7  | 470.7  | 473.6  | 477.7  | 482.5  | 487.9  | 485.4  | 479.0  | 474.5  | 471.0  | 472.3  |
| 22.5° | 472.6  | 474.2  | 477.7  | 483.1  | 490.2  | 496.6  | 494.3  | 485.7  | 479.3  | 474.5  | 475.8  |
| 25°   | 482.5  | 483.1  | 487.6  | 494.6  | 501.4  | 506.8  | 504.6  | 496.6  | 488.6  | 482.8  | 484.4  |
| 27.5° | 500.1  | 501.7  | 505.5  | 512.9  | 518.6  | 521.5  | 521.2  | 515.7  | 507.8  | 502.6  | 503.9  |
| 30°   | 521.2  | 522.8  | 527.9  | 536.2  | 541.9  | 545.1  | 544.2  | 540.0  | 532.7  | 525.6  | 526.9  |
| 32.5° | 545.8  | 546.4  | 552.5  | 561.8  | 567.8  | 572.6  | 569.4  | 564.9  | 555.7  | 547.4  | 548.0  |
| 35°   | 577.1  | 578.0  | 584.4  | 593.1  | 597.9  | 601.7  | 601.1  | 596.6  | 586.7  | 577.7  | 580.0  |
| 37.5° | 616.4  | 617.0  | 622.8  | 633.6  | 637.5  | 640.4  | 641.0  | 638.8  | 628.5  | 617.0  | 619.3  |
| 40°   | 665.3  | 665.6  | 672.0  | 681.6  | 685.7  | 687.7  | 688.0  | 688.3  | 677.7  | 669.1  | 668.5  |
| 42.5° | 722.2  | 723.8  | 732.7  | 742.0  | 743.9  | 742.9  | 746.1  | 749.3  | 739.1  | 727.3  | 728.2  |
| 45°   | 790.2  | 791.2  | 803.3  | 813.6  | 810.0  | 806.8  | 812.9  | 819.3  | 810.0  | 794.7  | 790.2  |
| 47.5° | 870.7  | 872.7  | 885.8  | 896.0  | 890.2  | 884.5  | 894.4  | 901.1  | 886.1  | 869.8  | 865.6  |
| 50°   | 961.8  | 963.1  | 981.6  | 994.4  | 987.7  | 977.2  | 989.6  | 996.6  | 976.5  | 956.4  | 947.4  |
| 52.5° | 1069.5 | 1066.9 | 1091.6 | 1113.9 | 1109.8 | 1096.0 | 1106.3 | 1107.5 | 1077.5 | 1049.1 | 1040.1 |
| 55°   | 1200.8 | 1198.3 | 1222.9 | 1247.5 | 1257.7 | 1254.2 | 1249.4 | 1241.7 | 1197.3 | 1167.0 | 1158.7 |
| 57.5° | 1353.9 | 1345.9 | 1380.4 | 1413.6 | 1436.0 | 1442.4 | 1422.0 | 1404.1 | 1368.9 | 1331.5 | 1321.9 |
| 60°   | 1496.1 | 1495.8 | 1550.4 | 1607.9 | 1669.3 | 1694.8 | 1643.1 | 1594.5 | 1515.6 | 1447.5 | 1433.8 |
| 62.5° | 1536.0 | 1542.7 | 1632.2 | 1774.7 | 1926.2 | 2016.6 | 1880.2 | 1719.5 | 1567.0 | 1464.5 | 1446.2 |
| 65°   | 1437.6 | 1454.2 | 1581.4 | 1806.4 | 2105.5 | 2326.6 | 2018.5 | 1722.3 | 1509.8 | 1382.0 | 1362.8 |
| 67.5° | 1059.6 | 1092.8 | 1261.2 | 1630.0 | 2090.1 | 2406.1 | 1993.9 | 1562.9 | 1311.4 | 1159.3 | 1132.8 |
| 70°   | 522.8  | 554.4  | 688.0  | 1072.4 | 1719.8 | 2150.8 | 1725.2 | 1177.8 | 885.8  | 739.4  | 715.1  |
| 72.5° | 192.4  | 205.1  | 257.6  | 458.9  | 949.0  | 1588.8 | 1179.7 | 657.9  | 429.1  | 341.6  | 325.3  |
| 75°   | 94.3   | 96.5   | 104.5  | 154.0  | 350.2  | 747.7  | 554.4  | 252.4  | 157.9  | 137.4  | 132.9  |
| 77.5° | 60.1   | 61.0   | 64.9   | 73.5   | 112.5  | 235.5  | 168.1  | 99.7   | 77.3   | 74.1   | 74.1   |
| 80°   | 33.6   | 34.5   | 39.6   | 45.7   | 52.7   | 80.8   | 60.4   | 59.8   | 50.8   | 44.4   | 43.5   |
| 82.5° | 16.0   | 17.6   | 25.2   | 24.9   | 27.8   | 40.6   | 35.5   | 32.3   | 32.6   | 24.6   | 23.3   |
| 85°   | 7.3    | 7.3    | 9.9    | 11.8   | 12.5   | 13.7   | 16.3   | 18.5   | 18.2   | 12.5   | 13.4   |
| 87.5° | 3.5    | 3.5    | 3.5    | 3.2    | 2.9    | 2.6    | 3.5    | 5.8    | 8.3    | 5.8    | 5.4    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine



**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2407-157-9  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/03/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Invue  
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**  
 Description: Epic Modern Light Square 40W 5WQ Optic

**Spectral Parameters**

CCT (K): 2764  
 CIE u': 0.2591  
 CIE v': 0.5290  
 Duv: 0.0020  
 CIE x: 0.4581  
 CIE y: 0.4156  
 CIE z: 0.1263  
 Peak Wavelength (nm): 603  
 Dominant Wavelength (nm): 583  
 Purity: 62.2537  
 Rf: 84.7  
 Rg: 94.6

|           |      |      |      |
|-----------|------|------|------|
| CRI (Ra): | 80.9 |      |      |
| R1:       | 78.8 | R9:  | -1.5 |
| R2:       | 89.9 | R10: | 77.9 |
| R3:       | 96.2 | R11: | 78.9 |
| R4:       | 79.1 | R12: | 71.6 |
| R5:       | 79.1 | R13: | 81.2 |
| R6:       | 88.8 | R14: | 98.5 |
| R7:       | 81.3 | R15: | 69.9 |
| R8:       | 54.3 |      |      |



**Test Conditions**


Stabilization Time: 81M  
 Operation Time: 2H 21M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

**Photopic Flux vs. Wavelength**




**Photopic Lumens: 4337.9**

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | 0.0                            | 490               | 18018                                | 2.6                            | 620               | 87426                                | 22.8                           | 750               | 2680                                 | 0.0                            | 880               | 58                                   | 0.0                            |
| 365               | 0                                    | 0.0                            | 495               | 22295                                | 3.9                            | 625               | 83013                                | 18.2                           | 755               | 2287                                 | 0.0                            | 885               | 46                                   | 0.0                            |
| 370               | 0                                    | 0.0                            | 500               | 26478                                | 5.8                            | 630               | 78077                                | 14.1                           | 760               | 1944                                 | 0.0                            | 890               | 45                                   | 0.0                            |
| 375               | 0                                    | 0.0                            | 505               | 30524                                | 8.5                            | 635               | 72080                                | 10.7                           | 765               | 1653                                 | 0.0                            | 895               | 41                                   | 0.0                            |
| 380               | 0                                    | 0.0                            | 510               | 33611                                | 11.5                           | 640               | 66249                                | 7.9                            | 770               | 1413                                 | 0.0                            | 900               | 38                                   | 0.0                            |
| 385               | 0                                    | 0.0                            | 515               | 36490                                | 15.2                           | 645               | 59973                                | 5.7                            | 775               | 1198                                 | 0.0                            | 905               | 33                                   | 0.0                            |
| 390               | 0                                    | 0.0                            | 520               | 38610                                | 18.7                           | 650               | 53972                                | 3.9                            | 780               | 1025                                 | 0.0                            | 910               | 30                                   | 0.0                            |
| 395               | 0                                    | 0.0                            | 525               | 40511                                | 21.9                           | 655               | 48369                                | 2.7                            | 785               | 874                                  | 0.0                            | 915               | 23                                   | 0.0                            |
| 400               | 48                                   | 0.0                            | 530               | 42223                                | 24.9                           | 660               | 42641                                | 1.8                            | 790               | 747                                  | 0.0                            | 920               | 24                                   | 0.0                            |
| 405               | 201                                  | 0.0                            | 535               | 44137                                | 27.6                           | 665               | 37602                                | 1.1                            | 795               | 639                                  | 0.0                            | 925               | 22                                   | 0.0                            |
| 410               | 457                                  | 0.0                            | 540               | 46032                                | 30.0                           | 670               | 32798                                | 0.7                            | 800               | 547                                  | 0.0                            | 930               | 22                                   | 0.0                            |
| 415               | 925                                  | 0.0                            | 545               | 48553                                | 32.5                           | 675               | 28558                                | 0.5                            | 805               | 473                                  | 0.0                            | 935               | 17                                   | 0.0                            |
| 420               | 1816                                 | 0.0                            | 550               | 51408                                | 34.9                           | 680               | 24782                                | 0.3                            | 810               | 401                                  | 0.0                            | 940               | 13                                   | 0.0                            |
| 425               | 3217                                 | 0.0                            | 555               | 54711                                | 37.4                           | 685               | 21386                                | 0.2                            | 815               | 351                                  | 0.0                            | 945               | 6                                    | 0.0                            |
| 430               | 5520                                 | 0.0                            | 560               | 58847                                | 40.0                           | 690               | 18413                                | 0.1                            | 820               | 307                                  | 0.0                            | 950               | 10                                   | 0.0                            |
| 435               | 9225                                 | 0.1                            | 565               | 63386                                | 42.4                           | 695               | 15721                                | 0.1                            | 825               | 261                                  | 0.0                            | 955               | 11                                   | 0.0                            |
| 440               | 15522                                | 0.2                            | 570               | 68196                                | 44.3                           | 700               | 13432                                | 0.0                            | 830               | 228                                  | 0.0                            | 960               | 8                                    | 0.0                            |
| 445               | 27642                                | 0.6                            | 575               | 73613                                | 46.0                           | 705               | 11513                                | 0.0                            | 835               | 193                                  | 0.0                            | 965               | 12                                   | 0.0                            |
| 450               | 36602                                | 0.9                            | 580               | 79207                                | 47.1                           | 710               | 9780                                 | 0.0                            | 840               | 174                                  | 0.0                            | 970               | 3                                    | 0.0                            |
| 455               | 28292                                | 0.9                            | 585               | 84248                                | 47.0                           | 715               | 8356                                 | 0.0                            | 845               | 151                                  | 0.0                            | 975               | 8                                    | 0.0                            |
| 460               | 21166                                | 0.9                            | 590               | 88397                                | 45.7                           | 720               | 7161                                 | 0.0                            | 850               | 123                                  | 0.0                            | 980               | 2                                    | 0.0                            |
| 465               | 19092                                | 1.0                            | 595               | 91428                                | 43.4                           | 725               | 6067                                 | 0.0                            | 855               | 106                                  | 0.0                            | 985               | 13                                   | 0.0                            |
| 470               | 14951                                | 0.9                            | 600               | 93452                                | 40.3                           | 730               | 5164                                 | 0.0                            | 860               | 95                                   | 0.0                            | 990               | 16                                   | 0.0                            |
| 475               | 12606                                | 1.0                            | 605               | 93959                                | 36.4                           | 735               | 4393                                 | 0.0                            | 865               | 82                                   | 0.0                            | 995               | 20                                   | 0.0                            |
| 480               | 13323                                | 1.3                            | 610               | 93079                                | 32.0                           | 740               | 3694                                 | 0.0                            | 870               | 77                                   | 0.0                            | 1000              | 0                                    | 0.0                            |
| 485               | 15164                                | 1.8                            | 615               | 90707                                | 27.3                           | 745               | 3157                                 | 0.0                            | 875               | 65                                   | 0.0                            |                   |                                      |                                |

REPORT NUMBER: SP1-2407-157-9

**Scotopic Flux vs. Wavelength**




**Scotopic Lumens: 5286.7**

**S/P: 1.22**

| $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360            | 0                                 | 0.0                         | 490            | 18018                             | 75.9                        | 620            | 87426                             | 0.4                         | 750            | 2680                              | 0.0                         | 880            | 58                                | 0.0                         |
| 365            | 0                                 | 0.0                         | 495            | 22295                             | 93.2                        | 625            | 83013                             | 0.2                         | 755            | 2287                              | 0.0                         | 885            | 46                                | 0.0                         |
| 370            | 0                                 | 0.0                         | 500            | 26478                             | 107.8                       | 630            | 78077                             | 0.1                         | 760            | 1944                              | 0.0                         | 890            | 45                                | 0.0                         |
| 375            | 0                                 | 0.0                         | 505            | 30524                             | 118.7                       | 635            | 72080                             | 0.1                         | 765            | 1653                              | 0.0                         | 895            | 41                                | 0.0                         |
| 380            | 0                                 | 0.0                         | 510            | 33611                             | 122.2                       | 640            | 66249                             | 0.1                         | 770            | 1413                              | 0.0                         | 900            | 38                                | 0.0                         |
| 385            | 0                                 | 0.0                         | 515            | 36490                             | 120.8                       | 645            | 59973                             | 0.0                         | 775            | 1198                              | 0.0                         | 905            | 33                                | 0.0                         |
| 390            | 0                                 | 0.0                         | 520            | 38610                             | 113.9                       | 650            | 53972                             | 0.0                         | 780            | 1025                              | 0.0                         | 910            | 30                                | 0.0                         |
| 395            | 0                                 | 0.0                         | 525            | 40511                             | 104.1                       | 655            | 48369                             | 0.0                         | 785            | 874                               | 0.0                         | 915            | 23                                | 0.0                         |
| 400            | 48                                | 0.0                         | 530            | 42223                             | 92.4                        | 660            | 42641                             | 0.0                         | 790            | 747                               | 0.0                         | 920            | 24                                | 0.0                         |
| 405            | 201                               | 0.0                         | 535            | 44137                             | 80.5                        | 665            | 37602                             | 0.0                         | 795            | 639                               | 0.0                         | 925            | 22                                | 0.0                         |
| 410            | 457                               | 0.1                         | 540            | 46032                             | 68.2                        | 670            | 32798                             | 0.0                         | 800            | 547                               | 0.0                         | 930            | 22                                | 0.0                         |
| 415            | 925                               | 0.3                         | 545            | 48553                             | 57.1                        | 675            | 28558                             | 0.0                         | 805            | 473                               | 0.0                         | 935            | 17                                | 0.0                         |
| 420            | 1816                              | 1.1                         | 550            | 51408                             | 46.7                        | 680            | 24782                             | 0.0                         | 810            | 401                               | 0.0                         | 940            | 13                                | 0.0                         |
| 425            | 3217                              | 2.5                         | 555            | 54711                             | 37.4                        | 685            | 21386                             | 0.0                         | 815            | 351                               | 0.0                         | 945            | 6                                 | 0.0                         |
| 430            | 5520                              | 5.9                         | 560            | 58847                             | 29.4                        | 690            | 18413                             | 0.0                         | 820            | 307                               | 0.0                         | 950            | 10                                | 0.0                         |
| 435            | 9225                              | 12.5                        | 565            | 63386                             | 22.5                        | 695            | 15721                             | 0.0                         | 825            | 261                               | 0.0                         | 955            | 11                                | 0.0                         |
| 440            | 15522                             | 26.3                        | 570            | 68196                             | 16.9                        | 700            | 13432                             | 0.0                         | 830            | 228                               | 0.0                         | 960            | 8                                 | 0.0                         |
| 445            | 27642                             | 55.2                        | 575            | 73613                             | 12.4                        | 705            | 11513                             | 0.0                         | 835            | 193                               | 0.0                         | 965            | 12                                | 0.0                         |
| 450            | 36602                             | 85.4                        | 580            | 79207                             | 9.0                         | 710            | 9780                              | 0.0                         | 840            | 174                               | 0.0                         | 970            | 3                                 | 0.0                         |
| 455            | 28292                             | 75.1                        | 585            | 84248                             | 6.3                         | 715            | 8356                              | 0.0                         | 845            | 151                               | 0.0                         | 975            | 8                                 | 0.0                         |
| 460            | 21166                             | 63.2                        | 590            | 88397                             | 4.4                         | 720            | 7161                              | 0.0                         | 850            | 123                               | 0.0                         | 980            | 2                                 | 0.0                         |
| 465            | 19092                             | 63.2                        | 595            | 91428                             | 3.0                         | 725            | 6067                              | 0.0                         | 855            | 106                               | 0.0                         | 985            | 13                                | 0.0                         |
| 470            | 14951                             | 54.2                        | 600            | 93452                             | 2.0                         | 730            | 5164                              | 0.0                         | 860            | 95                                | 0.0                         | 990            | 16                                | 0.0                         |
| 475            | 12606                             | 48.8                        | 605            | 93959                             | 1.3                         | 735            | 4393                              | 0.0                         | 865            | 82                                | 0.0                         | 995            | 20                                | 0.0                         |
| 480            | 13323                             | 54.2                        | 610            | 93079                             | 0.9                         | 740            | 3694                              | 0.0                         | 870            | 77                                | 0.0                         | 1000           | 0                                 | 0.0                         |
| 485            | 15164                             | 63.3                        | 615            | 90707                             | 0.5                         | 745            | 3157                              | 0.0                         | 875            | 65                                | 0.0                         |                |                                   |                             |

REPORT NUMBER: SP1-2407-157-9

**Melanopic Flux vs. Wavelength**




**Melanopic Lumens: 9797**

**M/P: 2.26**





| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 0             | 0.0           | 490    | 18018         | 27.7          | 620    | 87426         | 1.1           | 750    | 2680          | 0.0           | 880    | 58            | 0.0           |
| 365    | 0             | 0.0           | 495    | 22295         | 36.0          | 625    | 83013         | 0.7           | 755    | 2287          | 0.0           | 885    | 46            | 0.0           |
| 370    | 0             | 0.0           | 500    | 26478         | 44.2          | 630    | 78077         | 0.4           | 760    | 1944          | 0.0           | 890    | 45            | 0.0           |
| 375    | 0             | 0.0           | 505    | 30524         | 51.8          | 635    | 72080         | 0.3           | 765    | 1653          | 0.0           | 895    | 41            | 0.0           |
| 380    | 0             | 0.0           | 510    | 33611         | 57.0          | 640    | 66249         | 0.2           | 770    | 1413          | 0.0           | 900    | 38            | 0.0           |
| 385    | 0             | 0.0           | 515    | 36490         | 60.5          | 645    | 59973         | 0.1           | 775    | 1198          | 0.0           | 905    | 33            | 0.0           |
| 390    | 0             | 0.0           | 520    | 38610         | 61.4          | 650    | 53972         | 0.1           | 780    | 1025          | 0.0           | 910    | 30            | 0.0           |
| 395    | 0             | 0.0           | 525    | 40511         | 60.6          | 655    | 48369         | 0.0           | 785    | 874           | 0.0           | 915    | 23            | 0.0           |
| 400    | 48            | 0.0           | 530    | 42223         | 58.2          | 660    | 42641         | 0.0           | 790    | 747           | 0.0           | 920    | 24            | 0.0           |
| 405    | 201           | 0.0           | 535    | 44137         | 55.0          | 665    | 37602         | 0.0           | 795    | 639           | 0.0           | 925    | 22            | 0.0           |
| 410    | 457           | 0.0           | 540    | 46032         | 50.9          | 670    | 32798         | 0.0           | 800    | 547           | 0.0           | 930    | 22            | 0.0           |
| 415    | 925           | 0.1           | 545    | 48553         | 46.6          | 675    | 28558         | 0.0           | 805    | 473           | 0.0           | 935    | 17            | 0.0           |
| 420    | 1816          | 0.3           | 550    | 51408         | 42.0          | 680    | 24782         | 0.0           | 810    | 401           | 0.0           | 940    | 13            | 0.0           |
| 425    | 3217          | 0.8           | 555    | 54711         | 37.4          | 685    | 21386         | 0.0           | 815    | 351           | 0.0           | 945    | 6             | 0.0           |
| 430    | 5520          | 1.9           | 560    | 58847         | 32.9          | 690    | 18413         | 0.0           | 820    | 307           | 0.0           | 950    | 10            | 0.0           |
| 435    | 9225          | 4.1           | 565    | 63386         | 28.4          | 695    | 15721         | 0.0           | 825    | 261           | 0.0           | 955    | 11            | 0.0           |
| 440    | 15522         | 8.7           | 570    | 68196         | 24.1          | 700    | 13432         | 0.0           | 830    | 228           | 0.0           | 960    | 8             | 0.0           |
| 445    | 27642         | 18.5          | 575    | 73613         | 20.0          | 705    | 11513         | 0.0           | 835    | 193           | 0.0           | 965    | 12            | 0.0           |
| 450    | 36602         | 28.3          | 580    | 79207         | 16.3          | 710    | 9780          | 0.0           | 840    | 174           | 0.0           | 970    | 3             | 0.0           |
| 455    | 28292         | 24.7          | 585    | 84248         | 12.9          | 715    | 8356          | 0.0           | 845    | 151           | 0.0           | 975    | 8             | 0.0           |
| 460    | 21166         | 20.4          | 590    | 88397         | 9.8           | 720    | 7161          | 0.0           | 850    | 123           | 0.0           | 980    | 2             | 0.0           |
| 465    | 19092         | 20.1          | 595    | 91428         | 7.3           | 725    | 6067          | 0.0           | 855    | 106           | 0.0           | 985    | 13            | 0.0           |
| 470    | 14951         | 17.2          | 600    | 93452         | 5.3           | 730    | 5164          | 0.0           | 860    | 95            | 0.0           | 990    | 16            | 0.0           |
| 475    | 12606         | 15.7          | 605    | 93959         | 3.7           | 735    | 4393          | 0.0           | 865    | 82            | 0.0           | 995    | 20            | 0.0           |
| 480    | 13323         | 18.0          | 610    | 93079         | 2.5           | 740    | 3694          | 0.0           | 870    | 77            | 0.0           | 1000   | 0             | 0.0           |
| 485    | 15164         | 21.9          | 615    | 90707         | 1.7           | 745    | 3157          | 0.0           | 875    | 65            | 0.0           |        |               |               |

**Summary**

$R_f = 84.7$   
 $R_g = 94.6$   
 $CIE R_a = 80.9$   
 $R_g = -1.5$




**Color Vector Graphics**






**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 |            |







Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)