

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P630491

Luminaire Tested: GWS-SA1D-827-U-RW-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P630491
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-50)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA1D-827-U-RW-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND RECTANGULAR WIDE OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (16) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2889.1 lumens
Efficiency: N/A
Efficacy: 65.2 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type V - Short
BUG Rating: B2 - U0 - G0


Input Watts (W): 44.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P630491
 CATALOG NUMBER: GWS-SA1D-827-U-RW-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 4.9 fc
 Type V - Short - N/A

REPORT NUMBER: P630491
CATALOG NUMBER: GWS-SA1D-827-U-RW-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 43-Deg Lateral - - - Horizontal Cone Through 50-Deg Vertical

REPORT NUMBER: P630491
 CATALOG NUMBER: GWS-SA1D-827-U-RW-W-GRSBK


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 1444.5 | 0.0 | 1444.5 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Street Side | Lumens | 1444.6 | 0.0 | 1444.6 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Total | Lumens | 2889.1 | 0.0 | 2889.1 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 40.5 | 1.4 |
| 10°-20° | 139.3 | 4.8 |
| 20°-30° | 281.7 | 9.8 |
| 30°-40° | 522.7 | 18.1 |
| 40°-50° | 867.7 | 30.0 |
| 50°-60° | 885.5 | 30.7 |
| 60°-70° | 145.2 | 5.0 |
| 70°-80° | 6.4 | 0.2 |
| 80°-90° | 0.1 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 2889.1 | 100.0 |
| 0°-180° | 2889.1 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P630491


CATALOG NUMBER: GWS-SA1D-827-U-RW-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|--------|
| | | | B | U | G |
| FL (0°-30°) | 232.8 | 8.1 | | | |
| FM (30°-60°) | 1140.8 | 39.5 | | | |
| FH (60°-80°) | 71.0 | 2.5 | | | G0/660 |
| FVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| BL (0°-30°) | 228.7 | 7.9 | B1/500 | | |
| BM (30°-60°) | 1135.2 | 39.3 | B2/2500 | | |
| BH (60°-80°) | 80.5 | 2.8 | B0/110 | | G0/660 |
| BVH (80°-90°) | 0.1 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G0

Type V Short





REPORT NUMBER: P630491

CATALOG NUMBER: GWS-SA1D-827-U-RW-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 43° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 410.9 | 410.9 | 410.9 | 410.9 | 410.9 | 410.9 | 410.9 | 410.9 | 410.9 | 410.9 | 410.9 |
| 2.5° | 403.3 | 404.2 | 405.5 | 406.8 | 408.4 | 410.0 | 410.9 | 413.8 | 413.2 | 415.7 | 415.7 |
| 5° | 398.8 | 399.7 | 401.3 | 404.2 | 407.7 | 411.2 | 413.8 | 419.6 | 422.8 | 427.9 | 429.8 |
| 7.5° | 401.0 | 402.3 | 404.2 | 408.7 | 414.1 | 419.6 | 422.4 | 431.7 | 438.1 | 447.7 | 453.1 |
| 10° | 408.4 | 409.7 | 412.8 | 420.5 | 427.5 | 435.2 | 438.7 | 450.6 | 460.8 | 473.9 | 481.5 |
| 12.5° | 416.7 | 418.3 | 424.7 | 436.2 | 448.3 | 458.5 | 463.3 | 476.4 | 487.0 | 501.7 | 513.8 |
| 15° | 425.3 | 427.9 | 437.8 | 454.7 | 472.0 | 485.7 | 490.8 | 504.9 | 515.4 | 531.1 | 544.8 |
| 17.5° | 445.4 | 448.3 | 459.5 | 477.7 | 501.4 | 517.3 | 521.8 | 536.5 | 544.5 | 555.0 | 569.4 |
| 20° | 470.7 | 476.1 | 489.9 | 511.9 | 537.8 | 553.1 | 556.3 | 570.7 | 570.1 | 574.5 | 587.0 |
| 22.5° | 502.0 | 505.8 | 520.9 | 547.1 | 576.1 | 593.1 | 600.4 | 606.5 | 598.5 | 594.7 | 602.7 |
| 25° | 534.6 | 539.1 | 555.4 | 584.1 | 616.7 | 636.2 | 642.3 | 647.1 | 634.3 | 619.9 | 620.9 |
| 27.5° | 576.8 | 580.0 | 595.9 | 626.6 | 659.2 | 681.3 | 686.7 | 695.0 | 678.1 | 655.1 | 648.7 |
| 30° | 626.9 | 630.1 | 647.1 | 679.3 | 711.6 | 730.5 | 738.8 | 749.0 | 730.5 | 701.7 | 694.4 |
| 32.5° | 685.7 | 688.9 | 710.7 | 743.9 | 770.4 | 790.9 | 798.9 | 809.7 | 795.0 | 762.7 | 754.4 |
| 35° | 756.0 | 757.9 | 783.5 | 819.6 | 847.7 | 867.6 | 873.0 | 885.8 | 869.5 | 837.2 | 832.7 |
| 37.5° | 837.5 | 839.8 | 867.6 | 909.4 | 938.2 | 960.2 | 968.8 | 972.4 | 952.5 | 916.4 | 912.9 |
| 40° | 927.0 | 934.3 | 961.5 | 1006.6 | 1038.8 | 1066.6 | 1074.3 | 1062.5 | 1034.7 | 985.5 | 979.1 |
| 42.5° | 1020.3 | 1026.7 | 1057.0 | 1105.9 | 1143.3 | 1171.8 | 1172.1 | 1146.5 | 1099.2 | 1031.2 | 1021.6 |
| 45° | 1097.9 | 1100.5 | 1139.8 | 1189.0 | 1235.0 | 1255.2 | 1257.1 | 1210.7 | 1139.5 | 1057.7 | 1037.2 |
| 47.5° | 1151.3 | 1155.5 | 1189.6 | 1236.9 | 1287.7 | 1306.0 | 1302.1 | 1244.3 | 1158.7 | 1074.9 | 1041.1 |
| 50° | 1151.9 | 1159.0 | 1196.0 | 1241.7 | 1290.9 | 1313.0 | 1307.6 | 1253.9 | 1169.5 | 1075.6 | 1031.8 |
| 52.5° | 1050.0 | 1061.5 | 1121.9 | 1188.1 | 1263.5 | 1301.2 | 1302.4 | 1266.3 | 1165.4 | 1065.3 | 1023.5 |
| 55° | 792.1 | 804.6 | 880.7 | 993.5 | 1139.2 | 1244.3 | 1262.5 | 1251.6 | 1160.6 | 1069.8 | 1038.2 |
| 57.5° | 419.2 | 409.7 | 451.8 | 563.7 | 746.8 | 932.7 | 986.1 | 1073.0 | 1107.2 | 1075.3 | 1065.3 |
| 60° | 91.4 | 97.5 | 129.7 | 174.8 | 291.4 | 438.7 | 490.8 | 639.7 | 816.7 | 895.4 | 952.2 |
| 62.5° | 39.3 | 38.7 | 40.3 | 45.7 | 66.8 | 111.2 | 135.8 | 221.8 | 349.9 | 480.6 | 569.1 |
| 65° | 32.3 | 32.6 | 33.9 | 33.9 | 31.6 | 32.0 | 33.6 | 50.8 | 81.8 | 114.7 | 154.0 |
| 67.5° | 24.3 | 24.6 | 26.8 | 27.5 | 25.9 | 23.0 | 22.7 | 19.2 | 20.1 | 25.2 | 26.2 |
| 70° | 15.3 | 15.3 | 16.6 | 17.3 | 17.3 | 16.0 | 15.7 | 13.7 | 13.4 | 15.3 | 17.3 |
| 72.5° | 8.3 | 8.3 | 8.9 | 9.3 | 8.9 | 8.6 | 8.6 | 8.3 | 8.0 | 9.3 | 11.8 |
| 75° | 3.5 | 3.5 | 3.8 | 3.8 | 3.5 | 3.5 | 3.5 | 3.5 | 3.5 | 4.2 | 6.4 |
| 77.5° | 0.6 | 1.0 | 1.3 | 1.0 | 0.6 | 0.6 | 0.6 | 1.0 | 1.0 | 1.3 | 1.9 |
| 80° | 0.3 | 0.3 | 0.6 | 0.3 | 0.0 | 0.0 | 0.0 | 0.0 | 0.3 | 0.3 | 0.3 |
| 82.5° | 0.3 | 0.3 | 0.3 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.3 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P630491
 CATALOG NUMBER: GWS-SA1D-827-U-RW-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 410.9 | 410.9 | 410.9 | 410.9 | 410.9 | 410.9 | 410.9 | 410.9 | 410.9 | 410.9 | 410.9 |
| 2.5° | 418.0 | 414.4 | 415.7 | 416.4 | 415.4 | 414.8 | 411.2 | 410.3 | 408.7 | 406.1 | 405.5 |
| 5° | 432.0 | 429.1 | 428.8 | 426.9 | 422.4 | 417.0 | 410.3 | 407.4 | 404.2 | 401.0 | 400.4 |
| 7.5° | 455.7 | 452.1 | 449.9 | 443.5 | 433.3 | 424.7 | 413.5 | 407.4 | 403.3 | 399.1 | 398.1 |
| 10° | 486.0 | 481.9 | 475.5 | 463.7 | 449.9 | 437.5 | 424.3 | 416.4 | 410.0 | 404.2 | 403.9 |
| 12.5° | 518.3 | 513.8 | 502.3 | 487.3 | 470.7 | 459.2 | 442.6 | 431.4 | 421.8 | 413.2 | 412.2 |
| 15° | 552.2 | 546.7 | 531.1 | 513.2 | 497.8 | 486.0 | 467.8 | 449.9 | 435.2 | 422.8 | 421.5 |
| 17.5° | 578.0 | 571.3 | 552.8 | 539.4 | 526.9 | 514.8 | 494.3 | 470.7 | 451.2 | 436.2 | 432.7 |
| 20° | 594.3 | 588.0 | 570.4 | 563.0 | 557.3 | 548.7 | 524.4 | 499.8 | 478.0 | 459.5 | 456.3 |
| 22.5° | 610.0 | 602.3 | 587.0 | 587.0 | 591.5 | 588.0 | 561.8 | 533.6 | 508.1 | 486.7 | 481.9 |
| 25° | 627.6 | 621.5 | 610.6 | 619.6 | 630.8 | 630.5 | 603.6 | 568.5 | 539.1 | 515.1 | 510.3 |
| 27.5° | 653.1 | 647.1 | 643.2 | 660.2 | 674.2 | 673.3 | 643.9 | 605.8 | 574.9 | 551.2 | 546.7 |
| 30° | 698.2 | 692.4 | 688.3 | 708.7 | 726.6 | 719.9 | 687.7 | 650.9 | 619.6 | 592.7 | 589.6 |
| 32.5° | 758.3 | 752.2 | 746.8 | 767.2 | 783.2 | 774.6 | 743.9 | 709.4 | 673.3 | 647.1 | 640.7 |
| 35° | 837.2 | 824.4 | 819.0 | 843.3 | 850.0 | 840.4 | 811.0 | 780.6 | 742.3 | 712.3 | 708.1 |
| 37.5° | 918.7 | 903.7 | 899.8 | 920.9 | 931.8 | 928.3 | 893.8 | 862.1 | 820.6 | 787.3 | 782.6 |
| 40° | 988.3 | 974.6 | 967.9 | 1000.8 | 1025.4 | 1027.6 | 996.6 | 958.0 | 909.1 | 874.6 | 866.0 |
| 42.5° | 1029.2 | 1017.4 | 1015.8 | 1066.9 | 1107.2 | 1136.0 | 1098.9 | 1059.0 | 1007.5 | 968.5 | 961.5 |
| 45° | 1038.5 | 1030.8 | 1044.3 | 1111.4 | 1174.0 | 1226.4 | 1194.8 | 1152.6 | 1097.0 | 1055.8 | 1049.1 |
| 47.5° | 1037.5 | 1035.0 | 1059.0 | 1134.4 | 1213.6 | 1278.2 | 1262.5 | 1214.9 | 1161.2 | 1118.1 | 1111.7 |
| 50° | 1023.8 | 1024.1 | 1064.1 | 1145.9 | 1229.6 | 1292.2 | 1276.6 | 1232.5 | 1184.5 | 1142.0 | 1136.9 |
| 52.5° | 1018.4 | 1016.5 | 1054.5 | 1142.4 | 1245.9 | 1285.8 | 1250.7 | 1201.2 | 1147.8 | 1095.4 | 1087.7 |
| 55° | 1037.5 | 1032.8 | 1055.8 | 1139.5 | 1247.8 | 1282.3 | 1189.6 | 1082.3 | 973.0 | 911.0 | 905.9 |
| 57.5° | 1066.3 | 1061.2 | 1072.1 | 1118.4 | 1147.8 | 1066.3 | 875.5 | 702.3 | 589.9 | 542.3 | 521.5 |
| 60° | 952.2 | 948.7 | 940.4 | 884.5 | 758.6 | 572.3 | 389.8 | 248.6 | 178.6 | 144.4 | 144.4 |
| 62.5° | 590.8 | 586.0 | 541.0 | 402.0 | 292.1 | 169.0 | 93.0 | 58.2 | 44.1 | 41.2 | 40.9 |
| 65° | 165.8 | 164.9 | 136.4 | 96.5 | 61.4 | 38.0 | 33.6 | 34.2 | 33.6 | 32.6 | 32.3 |
| 67.5° | 24.9 | 27.5 | 27.5 | 22.4 | 21.4 | 24.0 | 28.1 | 30.0 | 28.4 | 26.8 | 26.2 |
| 70° | 16.0 | 17.3 | 16.6 | 14.4 | 15.3 | 17.9 | 20.1 | 20.5 | 19.5 | 17.9 | 17.6 |
| 72.5° | 11.2 | 12.5 | 10.2 | 9.3 | 9.6 | 10.5 | 11.5 | 11.5 | 11.2 | 10.5 | 9.9 |
| 75° | 6.7 | 6.7 | 4.8 | 4.5 | 4.5 | 4.8 | 4.8 | 5.4 | 5.4 | 5.1 | 4.8 |
| 77.5° | 2.2 | 2.6 | 1.6 | 1.3 | 1.3 | 1.3 | 1.6 | 1.9 | 1.9 | 1.6 | 1.3 |
| 80° | 0.3 | 0.6 | 0.3 | 0.3 | 0.3 | 0.3 | 0.3 | 0.3 | 0.6 | 0.6 | 0.3 |
| 82.5° | 0.3 | 0.3 | 0.3 | 0.0 | 0.0 | 0.0 | 0.0 | 0.3 | 0.3 | 0.3 | 0.3 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.3 | 0.3 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_9 = -1.5$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)