

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P630510

Luminaire Tested: GWS-SA1D-827-U-SLR-W-HSS

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P630510
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA1D-827-U-SLR-W-HSS
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND
SPILL LIGHT ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD
Light Source: (16) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2766.4 lumens
Efficiency: N/A
Efficacy: 62.4 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B0 - U0 - G1


Input Watts (W): 44.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P630510
 CATALOG NUMBER: GWS-SA1D-827-U-SLR-W-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 5.6 fc
 Type IV - Short - N/A

REPORT NUMBER: P630510
CATALOG NUMBER: GWS-SA1D-827-U-SLR-W-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 62.5-Deg Vertical

REPORT NUMBER: P630510
 CATALOG NUMBER: GWS-SA1D-827-U-SLR-W-HSS


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 341.4 | 0.0 | 341.4 |
| | % Fixture | 12.3 | 0.0 | 12.3 |
| Street Side | Lumens | 2425.0 | 0.0 | 2425.0 |
| | % Fixture | 87.7 | 0.0 | 87.7 |
| Total | Lumens | 2766.4 | 0.0 | 2766.4 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 12.8 | 0.5 |
| 10°-20° | 48.2 | 1.7 |
| 20°-30° | 104.8 | 3.8 |
| 30°-40° | 172.1 | 6.2 |
| 40°-50° | 316.4 | 11.4 |
| 50°-60° | 679.4 | 24.6 |
| 60°-70° | 912.5 | 33.0 |
| 70°-80° | 475.2 | 17.2 |
| 80°-90° | 45.1 | 1.6 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 2766.4 | 100.0 |
| 0°-180° | 2766.4 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P630510
 CATALOG NUMBER: GWS-SA1D-827-U-SLR-W-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 116.9 | 4.2 | | | |
| FM (30°-60°) | 971.0 | 35.1 | | | |
| FH (60°-80°) | 1294.1 | 46.8 | | | G1/1800 |
| FVH (80°-90°) | 43.0 | 1.6 | | | G1/100 |
| BL (0°-30°) | 49.0 | 1.8 | B0/110 | | |
| BM (30°-60°) | 196.9 | 7.1 | B0/220 | | |
| BH (60°-80°) | 93.5 | 3.4 | B0/110 | | G0/110 |
| BVH (80°-90°) | 2.0 | 0.1 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B0-U0-G1
 Type IV Short





REPORT NUMBER: P630510
 CATALOG NUMBER: GWS-SA1D-827-U-SLR-W-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 1° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 143.8 | 143.8 | 143.8 | 143.8 | 143.8 | 143.8 | 143.8 | 143.8 | 143.8 | 143.8 | 143.8 |
| 2.5° | 146.7 | 147.3 | 147.9 | 150.2 | 151.8 | 153.1 | 153.4 | 152.4 | 150.2 | 147.9 | 144.8 |
| 5° | 142.2 | 142.8 | 145.1 | 151.1 | 157.2 | 162.0 | 163.6 | 162.6 | 157.2 | 150.2 | 142.8 |
| 7.5° | 141.9 | 143.2 | 148.6 | 161.4 | 174.5 | 184.4 | 186.9 | 184.7 | 174.5 | 160.4 | 145.4 |
| 10° | 153.4 | 155.6 | 163.6 | 186.6 | 210.6 | 228.2 | 235.2 | 225.6 | 209.3 | 183.7 | 159.1 |
| 12.5° | 183.4 | 187.3 | 202.6 | 236.1 | 273.2 | 296.5 | 306.1 | 294.3 | 268.7 | 231.7 | 192.7 |
| 15° | 230.7 | 236.5 | 259.5 | 309.6 | 353.4 | 374.2 | 377.4 | 370.7 | 341.0 | 300.1 | 247.6 |
| 17.5° | 297.5 | 305.8 | 341.6 | 392.7 | 424.4 | 431.7 | 430.7 | 423.7 | 402.0 | 373.9 | 324.3 |
| 20° | 377.4 | 387.3 | 422.4 | 464.6 | 467.8 | 459.2 | 454.4 | 450.2 | 442.9 | 438.1 | 399.4 |
| 22.5° | 457.9 | 470.0 | 506.8 | 517.3 | 488.6 | 463.7 | 451.8 | 455.0 | 465.9 | 489.5 | 473.9 |
| 25° | 538.1 | 549.6 | 584.1 | 555.7 | 498.2 | 456.6 | 441.6 | 449.3 | 475.2 | 526.3 | 546.4 |
| 27.5° | 631.7 | 640.4 | 660.8 | 581.9 | 499.8 | 450.9 | 436.2 | 448.0 | 479.6 | 549.3 | 626.0 |
| 30° | 729.2 | 734.3 | 724.4 | 588.9 | 494.3 | 442.2 | 430.7 | 448.0 | 487.3 | 564.6 | 685.7 |
| 32.5° | 800.8 | 801.7 | 769.5 | 589.6 | 491.5 | 435.2 | 425.6 | 446.1 | 494.7 | 577.4 | 743.6 |
| 35° | 874.6 | 869.8 | 812.6 | 599.1 | 499.1 | 437.8 | 429.5 | 451.5 | 506.2 | 592.4 | 794.4 |
| 37.5° | 949.4 | 940.7 | 860.9 | 614.8 | 518.9 | 465.6 | 460.5 | 479.3 | 524.7 | 613.2 | 850.3 |
| 40° | 1026.1 | 1014.2 | 911.0 | 638.4 | 563.0 | 560.2 | 577.7 | 575.5 | 575.5 | 639.7 | 907.8 |
| 42.5° | 1119.7 | 1105.9 | 985.2 | 705.2 | 665.9 | 730.2 | 778.1 | 748.4 | 693.4 | 700.8 | 982.6 |
| 45° | 1243.3 | 1231.5 | 1113.6 | 833.1 | 827.3 | 974.9 | 1039.5 | 980.7 | 843.9 | 841.7 | 1107.5 |
| 47.5° | 1441.1 | 1438.9 | 1318.4 | 981.3 | 1024.8 | 1286.5 | 1411.1 | 1298.0 | 1015.5 | 990.9 | 1344.0 |
| 50° | 1719.1 | 1712.4 | 1573.8 | 1155.2 | 1259.6 | 1672.5 | 1894.9 | 1706.4 | 1222.9 | 1165.1 | 1660.7 |
| 52.5° | 2032.3 | 2039.3 | 1931.3 | 1345.0 | 1509.2 | 2102.0 | 2411.6 | 2174.2 | 1448.2 | 1386.5 | 2059.1 |
| 55° | 2327.2 | 2367.5 | 2339.1 | 1567.0 | 1753.0 | 2576.2 | 2979.1 | 2687.4 | 1727.1 | 1676.3 | 2505.9 |
| 57.5° | 2558.0 | 2671.4 | 2870.8 | 1889.8 | 2039.7 | 3130.9 | 3612.8 | 3243.7 | 2052.8 | 2147.0 | 3114.0 |
| 60° | 2570.7 | 2720.9 | 3183.9 | 2565.0 | 2408.4 | 3606.7 | 4245.5 | 3787.2 | 2564.7 | 2946.2 | 3590.4 |
| 62.5° | 2378.0 | 2539.1 | 2980.1 | 2871.7 | 2810.1 | 4011.6 | 4570.1 | 4183.5 | 3068.3 | 3414.3 | 3449.2 |
| 65° | 2157.6 | 2320.2 | 2752.6 | 2523.8 | 2763.4 | 3994.3 | 4487.7 | 4192.7 | 3114.0 | 3096.1 | 3196.4 |
| 67.5° | 1824.3 | 1970.3 | 2361.8 | 2233.9 | 2547.1 | 3801.6 | 4106.8 | 3928.5 | 2868.9 | 2895.7 | 2940.4 |
| 70° | 1331.5 | 1472.1 | 1835.5 | 1841.9 | 2224.3 | 3454.3 | 3528.7 | 3504.1 | 2642.0 | 2670.4 | 2542.6 |
| 72.5° | 961.8 | 1080.4 | 1393.9 | 1510.5 | 1775.7 | 2896.7 | 2845.2 | 2940.1 | 2266.8 | 2378.4 | 2042.2 |
| 75° | 691.5 | 780.3 | 1022.5 | 1314.0 | 1407.6 | 2151.2 | 2036.8 | 2277.1 | 1818.8 | 2048.0 | 1535.4 |
| 77.5° | 280.6 | 311.9 | 402.3 | 885.1 | 925.1 | 1447.2 | 1246.9 | 1654.0 | 1296.7 | 1345.6 | 744.2 |
| 80° | 11.5 | 12.8 | 16.6 | 456.9 | 634.3 | 814.2 | 667.2 | 884.2 | 856.4 | 541.9 | 175.7 |
| 82.5° | 1.3 | 1.3 | 2.9 | 131.7 | 277.7 | 449.3 | 314.4 | 509.4 | 433.6 | 229.8 | 79.9 |
| 85° | 0.3 | 0.3 | 0.6 | 15.0 | 65.2 | 71.9 | 42.5 | 156.3 | 201.6 | 93.9 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 1.6 | 2.9 | 3.2 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P630510

CATALOG NUMBER: GWS-SA1D-827-U-SLR-W-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 143.8 | 143.8 | 143.8 | 143.8 | 143.8 | 143.8 | 143.8 | 143.8 | 143.8 | 143.8 | 143.8 |
| 2.5° | 144.8 | 143.2 | 141.2 | 139.3 | 138.4 | 135.8 | 134.8 | 134.2 | 133.6 | 133.9 | 133.9 |
| 5° | 140.0 | 136.4 | 132.3 | 128.1 | 125.9 | 123.3 | 122.1 | 121.4 | 121.7 | 123.0 | 123.0 |
| 7.5° | 139.3 | 132.6 | 123.7 | 118.2 | 115.7 | 113.8 | 112.5 | 111.8 | 112.2 | 113.8 | 114.4 |
| 10° | 149.9 | 138.0 | 122.1 | 112.8 | 109.9 | 108.0 | 106.7 | 105.8 | 105.1 | 106.4 | 106.7 |
| 12.5° | 172.6 | 156.3 | 129.7 | 112.2 | 107.0 | 104.5 | 103.5 | 101.6 | 100.7 | 101.3 | 101.6 |
| 15° | 219.5 | 191.4 | 145.1 | 114.7 | 104.5 | 101.6 | 100.0 | 98.4 | 96.8 | 96.5 | 96.8 |
| 17.5° | 280.9 | 240.6 | 168.4 | 120.8 | 102.6 | 99.1 | 96.8 | 94.6 | 92.3 | 92.0 | 91.7 |
| 20° | 356.9 | 301.0 | 201.0 | 130.4 | 101.0 | 96.8 | 93.6 | 90.4 | 87.6 | 86.6 | 86.6 |
| 22.5° | 426.3 | 373.9 | 242.9 | 142.2 | 98.7 | 93.6 | 89.8 | 86.0 | 82.8 | 81.2 | 80.8 |
| 25° | 511.0 | 451.2 | 293.0 | 155.9 | 95.5 | 89.5 | 85.3 | 81.5 | 78.3 | 76.4 | 75.7 |
| 27.5° | 596.3 | 532.7 | 349.9 | 173.8 | 91.7 | 85.3 | 81.5 | 78.0 | 74.5 | 72.2 | 71.6 |
| 30° | 679.0 | 620.6 | 413.8 | 196.2 | 88.8 | 81.2 | 78.0 | 74.5 | 71.3 | 67.7 | 66.8 |
| 32.5° | 767.9 | 710.3 | 485.4 | 221.1 | 86.6 | 78.3 | 74.8 | 71.6 | 67.4 | 64.2 | 62.6 |
| 35° | 853.5 | 803.0 | 564.3 | 245.4 | 84.4 | 75.7 | 71.9 | 68.7 | 64.2 | 60.7 | 58.5 |
| 37.5° | 939.8 | 897.3 | 646.8 | 260.1 | 81.2 | 72.2 | 68.7 | 66.1 | 61.0 | 56.9 | 54.3 |
| 40° | 1031.2 | 994.7 | 735.9 | 254.0 | 78.3 | 68.4 | 66.5 | 63.6 | 57.8 | 53.0 | 49.8 |
| 42.5° | 1131.5 | 1087.7 | 826.7 | 230.7 | 75.7 | 65.2 | 63.3 | 60.4 | 55.0 | 49.2 | 45.1 |
| 45° | 1257.7 | 1189.7 | 901.1 | 195.6 | 77.0 | 62.0 | 58.2 | 57.5 | 52.4 | 45.1 | 39.9 |
| 47.5° | 1474.7 | 1346.2 | 959.0 | 172.9 | 85.6 | 58.5 | 54.0 | 55.6 | 50.2 | 40.9 | 35.1 |
| 50° | 1806.7 | 1605.7 | 1013.0 | 171.3 | 98.7 | 56.9 | 50.2 | 54.3 | 47.9 | 36.7 | 31.0 |
| 52.5° | 2123.1 | 1869.3 | 1047.5 | 185.3 | 110.2 | 61.0 | 46.3 | 52.7 | 46.3 | 33.9 | 28.1 |
| 55° | 2425.7 | 2021.4 | 985.8 | 195.6 | 121.1 | 73.5 | 43.5 | 50.2 | 44.4 | 32.3 | 27.2 |
| 57.5° | 2751.9 | 2089.2 | 776.2 | 216.3 | 128.8 | 84.0 | 44.1 | 46.3 | 41.9 | 31.3 | 26.8 |
| 60° | 2849.4 | 2002.6 | 468.5 | 243.5 | 124.6 | 87.2 | 48.9 | 41.2 | 38.3 | 29.4 | 25.9 |
| 62.5° | 2697.9 | 1797.1 | 276.4 | 221.8 | 121.1 | 82.4 | 55.9 | 38.0 | 34.8 | 26.8 | 24.0 |
| 65° | 2471.4 | 1518.2 | 180.2 | 187.3 | 128.5 | 73.5 | 59.4 | 36.4 | 31.6 | 24.3 | 21.1 |
| 67.5° | 2212.5 | 1222.9 | 126.2 | 110.6 | 118.6 | 66.1 | 50.2 | 36.1 | 28.4 | 20.5 | 17.3 |
| 70° | 1863.6 | 915.8 | 88.8 | 73.2 | 98.7 | 58.8 | 39.0 | 35.1 | 24.9 | 16.6 | 13.4 |
| 72.5° | 1439.9 | 573.3 | 66.1 | 47.3 | 70.3 | 47.9 | 31.0 | 29.7 | 20.1 | 13.7 | 10.2 |
| 75° | 1061.8 | 326.9 | 46.7 | 34.2 | 46.3 | 36.4 | 23.0 | 21.1 | 17.3 | 13.1 | 9.3 |
| 77.5° | 554.4 | 163.6 | 29.1 | 26.2 | 26.5 | 22.7 | 16.6 | 15.3 | 16.0 | 13.1 | 8.6 |
| 80° | 106.4 | 32.6 | 17.6 | 19.2 | 14.4 | 14.4 | 12.1 | 12.8 | 14.1 | 10.5 | 7.3 |
| 82.5° | 44.4 | 7.0 | 9.6 | 10.9 | 8.9 | 9.9 | 9.9 | 10.2 | 9.9 | 7.7 | 5.4 |
| 85° | 0.0 | 0.0 | 4.2 | 4.5 | 6.1 | 6.1 | 5.1 | 5.1 | 5.1 | 4.5 | 3.2 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.3 | 1.0 | 1.9 | 2.2 | 2.6 | 1.9 | 1.3 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P630510
 CATALOG NUMBER: GWS-SA1D-827-U-SLR-W-HSS

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 143.8 | 143.8 | 143.8 | 143.8 | 143.8 | 143.8 | 143.8 | 143.8 | 143.8 | 143.8 | 143.8 |
| 2.5° | 133.6 | 132.9 | 133.9 | 134.5 | 135.2 | 135.2 | 134.5 | 133.9 | 132.9 | 133.9 | 132.9 |
| 5° | 123.3 | 124.3 | 125.9 | 126.5 | 127.2 | 125.9 | 125.3 | 123.3 | 121.7 | 122.1 | 121.4 |
| 7.5° | 115.4 | 116.3 | 118.2 | 119.5 | 119.5 | 118.9 | 117.0 | 115.0 | 112.5 | 112.5 | 112.2 |
| 10° | 108.0 | 109.3 | 111.5 | 113.1 | 113.8 | 113.1 | 111.2 | 108.6 | 106.4 | 106.4 | 105.4 |
| 12.5° | 101.9 | 103.5 | 106.1 | 108.3 | 109.0 | 108.3 | 106.4 | 103.9 | 101.3 | 101.3 | 100.7 |
| 15° | 96.8 | 98.7 | 101.6 | 104.2 | 105.1 | 104.2 | 101.9 | 98.7 | 96.2 | 96.5 | 95.5 |
| 17.5° | 92.0 | 93.6 | 97.5 | 100.3 | 101.3 | 100.3 | 97.5 | 93.3 | 90.8 | 91.4 | 90.8 |
| 20° | 86.6 | 88.5 | 92.3 | 95.5 | 96.5 | 95.5 | 92.3 | 87.9 | 85.3 | 85.3 | 85.6 |
| 22.5° | 80.8 | 82.8 | 86.6 | 88.8 | 90.1 | 89.2 | 86.0 | 81.8 | 79.2 | 79.2 | 79.6 |
| 25° | 75.7 | 76.7 | 79.6 | 81.8 | 82.1 | 81.2 | 78.6 | 75.4 | 73.5 | 74.5 | 74.8 |
| 27.5° | 70.9 | 70.9 | 72.2 | 73.5 | 73.2 | 72.2 | 71.3 | 68.7 | 68.4 | 69.3 | 70.3 |
| 30° | 65.8 | 64.2 | 63.6 | 62.6 | 62.3 | 62.0 | 63.0 | 63.0 | 63.6 | 64.9 | 65.8 |
| 32.5° | 61.4 | 58.2 | 55.3 | 52.4 | 50.8 | 52.1 | 54.6 | 56.9 | 59.1 | 61.0 | 62.0 |
| 35° | 56.2 | 51.1 | 46.3 | 42.5 | 39.9 | 41.9 | 46.0 | 50.2 | 54.0 | 56.6 | 58.2 |
| 37.5° | 51.1 | 43.8 | 38.0 | 33.2 | 31.3 | 32.9 | 37.4 | 43.1 | 48.9 | 52.1 | 54.3 |
| 40° | 45.7 | 36.4 | 29.7 | 25.9 | 24.0 | 25.6 | 30.0 | 35.8 | 43.5 | 47.6 | 50.5 |
| 42.5° | 40.3 | 30.0 | 24.0 | 20.1 | 19.2 | 20.1 | 23.6 | 29.4 | 37.7 | 42.8 | 46.7 |
| 45° | 34.8 | 24.9 | 19.2 | 16.3 | 15.3 | 16.3 | 19.2 | 24.0 | 32.3 | 38.0 | 42.5 |
| 47.5° | 30.0 | 21.1 | 16.0 | 13.4 | 12.8 | 13.7 | 16.0 | 20.1 | 27.2 | 32.9 | 38.0 |
| 50° | 26.2 | 18.5 | 13.7 | 11.5 | 10.9 | 11.8 | 13.7 | 16.9 | 23.0 | 28.1 | 33.6 |
| 52.5° | 23.6 | 17.3 | 12.1 | 9.9 | 9.6 | 10.2 | 11.8 | 14.4 | 19.5 | 24.0 | 29.1 |
| 55° | 23.0 | 17.3 | 11.2 | 8.9 | 8.6 | 9.3 | 10.5 | 12.5 | 16.9 | 20.8 | 25.2 |
| 57.5° | 23.6 | 18.5 | 10.5 | 7.7 | 7.3 | 8.0 | 9.3 | 10.9 | 14.7 | 17.9 | 22.0 |
| 60° | 23.6 | 18.9 | 9.3 | 6.1 | 5.8 | 6.4 | 7.7 | 9.6 | 13.1 | 15.7 | 19.2 |
| 62.5° | 21.4 | 17.3 | 7.7 | 4.8 | 4.2 | 4.8 | 6.4 | 8.0 | 11.5 | 14.1 | 16.9 |
| 65° | 18.5 | 14.7 | 6.4 | 3.5 | 2.9 | 3.5 | 5.1 | 6.7 | 9.9 | 12.1 | 15.3 |
| 67.5° | 15.0 | 11.2 | 4.8 | 2.6 | 1.9 | 2.6 | 3.8 | 5.4 | 8.3 | 10.5 | 13.7 |
| 70° | 11.2 | 8.0 | 3.8 | 2.2 | 1.9 | 2.2 | 3.5 | 5.1 | 7.3 | 9.6 | 12.8 |
| 72.5° | 8.3 | 5.4 | 3.2 | 2.2 | 1.6 | 2.2 | 3.2 | 4.8 | 7.0 | 9.3 | 12.1 |
| 75° | 7.0 | 4.5 | 2.9 | 1.9 | 1.6 | 1.9 | 2.9 | 4.5 | 6.4 | 8.6 | 11.5 |
| 77.5° | 6.7 | 4.2 | 2.6 | 1.6 | 1.3 | 1.6 | 2.6 | 3.8 | 5.8 | 8.0 | 11.2 |
| 80° | 5.8 | 3.5 | 2.2 | 1.3 | 1.0 | 1.3 | 2.2 | 3.2 | 4.5 | 6.1 | 8.6 |
| 82.5° | 4.5 | 2.9 | 1.6 | 0.6 | 0.3 | 0.6 | 1.6 | 1.9 | 2.9 | 3.5 | 5.1 |
| 85° | 2.9 | 1.6 | 0.6 | 0.0 | 0.0 | 0.0 | 0.6 | 1.3 | 1.3 | 1.6 | 2.6 |
| 87.5° | 1.3 | 0.3 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.3 | 0.6 | 1.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P630510
 CATALOG NUMBER: GWS-SA1D-827-U-SLR-W-HSS

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 359° | 360° |
|-------|-------|-------|-------|-------|-------|-------|-------|--------|--------|--------|
| 0° | 143.8 | 143.8 | 143.8 | 143.8 | 143.8 | 143.8 | 143.8 | 143.8 | 143.8 | 143.8 |
| 2.5° | 134.8 | 135.2 | 135.8 | 136.8 | 139.0 | 140.9 | 142.8 | 145.4 | 146.7 | 146.7 |
| 5° | 122.1 | 122.4 | 122.7 | 124.0 | 127.2 | 129.7 | 133.9 | 139.0 | 141.6 | 142.2 |
| 7.5° | 112.2 | 112.8 | 113.4 | 114.4 | 117.6 | 121.1 | 126.5 | 136.1 | 140.9 | 141.9 |
| 10° | 106.4 | 107.4 | 108.6 | 110.6 | 113.4 | 117.3 | 126.5 | 143.8 | 151.8 | 153.4 |
| 12.5° | 101.9 | 103.5 | 104.8 | 107.0 | 110.6 | 116.6 | 135.2 | 165.5 | 179.6 | 183.4 |
| 15° | 97.5 | 99.4 | 101.3 | 103.5 | 107.4 | 118.9 | 151.8 | 204.5 | 227.8 | 230.7 |
| 17.5° | 93.0 | 95.2 | 97.8 | 100.3 | 105.1 | 124.3 | 178.0 | 258.5 | 291.1 | 297.5 |
| 20° | 87.9 | 90.8 | 94.3 | 97.5 | 102.9 | 132.9 | 214.4 | 322.7 | 363.6 | 377.4 |
| 22.5° | 82.4 | 86.0 | 90.1 | 94.3 | 100.3 | 143.5 | 258.5 | 391.8 | 449.0 | 457.9 |
| 25° | 78.0 | 81.5 | 85.3 | 89.5 | 96.2 | 156.3 | 311.9 | 477.4 | 529.5 | 538.1 |
| 27.5° | 73.8 | 77.3 | 80.8 | 84.7 | 92.0 | 172.9 | 376.1 | 568.5 | 622.8 | 631.7 |
| 30° | 69.3 | 73.5 | 77.0 | 80.8 | 88.2 | 193.3 | 450.2 | 669.4 | 720.9 | 729.2 |
| 32.5° | 65.5 | 69.7 | 73.2 | 77.0 | 85.3 | 215.7 | 528.2 | 758.9 | 800.8 | 800.8 |
| 35° | 62.3 | 66.8 | 69.3 | 74.5 | 83.1 | 230.1 | 602.0 | 844.2 | 875.9 | 874.6 |
| 37.5° | 58.8 | 64.2 | 66.1 | 69.7 | 80.2 | 231.7 | 671.4 | 934.3 | 957.7 | 949.4 |
| 40° | 55.3 | 61.0 | 63.9 | 65.8 | 77.0 | 218.6 | 747.4 | 1017.1 | 1036.9 | 1026.1 |
| 42.5° | 52.1 | 56.6 | 60.7 | 63.0 | 75.1 | 195.6 | 808.4 | 1105.6 | 1129.3 | 1119.7 |
| 45° | 48.9 | 52.7 | 55.3 | 59.4 | 76.4 | 179.6 | 860.9 | 1208.8 | 1250.4 | 1243.3 |
| 47.5° | 45.7 | 48.9 | 50.5 | 56.9 | 85.0 | 172.2 | 892.8 | 1368.6 | 1446.9 | 1441.1 |
| 50° | 42.2 | 46.0 | 46.0 | 56.2 | 97.8 | 174.8 | 920.6 | 1600.0 | 1721.1 | 1719.1 |
| 52.5° | 38.7 | 42.8 | 42.2 | 61.0 | 107.7 | 186.6 | 952.2 | 1804.1 | 2014.7 | 2032.3 |
| 55° | 35.1 | 39.0 | 39.6 | 70.6 | 113.4 | 196.8 | 829.9 | 1890.1 | 2265.6 | 2327.2 |
| 57.5° | 31.3 | 33.6 | 41.2 | 78.0 | 111.5 | 226.6 | 568.5 | 1905.8 | 2425.7 | 2558.0 |
| 60° | 27.2 | 29.1 | 46.7 | 76.4 | 105.4 | 209.3 | 357.9 | 1765.2 | 2403.0 | 2570.7 |
| 62.5° | 23.6 | 26.8 | 49.2 | 67.4 | 107.4 | 181.5 | 228.2 | 1504.4 | 2186.6 | 2378.0 |
| 65° | 20.8 | 25.9 | 44.7 | 61.0 | 108.6 | 123.0 | 154.0 | 1223.9 | 1975.4 | 2157.6 |
| 67.5° | 18.5 | 28.8 | 36.7 | 54.3 | 93.3 | 86.6 | 105.8 | 951.0 | 1661.0 | 1824.3 |
| 70° | 16.9 | 29.4 | 30.0 | 46.7 | 72.2 | 55.6 | 69.7 | 640.0 | 1144.9 | 1331.5 |
| 72.5° | 15.3 | 21.7 | 22.7 | 37.4 | 46.7 | 33.9 | 45.1 | 366.2 | 834.6 | 961.8 |
| 75° | 14.7 | 14.7 | 15.7 | 24.3 | 25.9 | 24.6 | 29.1 | 218.6 | 598.5 | 691.5 |
| 77.5° | 13.7 | 11.2 | 9.9 | 15.7 | 14.1 | 17.6 | 17.3 | 97.1 | 259.5 | 280.6 |
| 80° | 10.9 | 8.0 | 6.7 | 9.9 | 9.6 | 11.8 | 10.2 | 8.0 | 11.8 | 11.5 |
| 82.5° | 6.7 | 5.1 | 4.8 | 6.1 | 5.4 | 6.1 | 4.8 | 1.3 | 1.3 | 1.3 |
| 85° | 3.2 | 2.9 | 2.6 | 2.6 | 2.9 | 2.6 | 1.9 | 0.6 | 0.3 | 0.3 |
| 87.5° | 1.6 | 1.6 | 1.3 | 1.0 | 1.3 | 1.3 | 1.0 | 0.3 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions


Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9


| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength




Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_9 = -1.5$




Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)