

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P630527

Luminaire Tested: GWS-SA1D-827-U-T3R-W-HSS

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P630527
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA1D-827-U-T3R-W-HSS
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III ROADWAY OPTICS WITH HOUSE SIDE SHIELD
Light Source: (16) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3489.5 lumens
Efficiency: N/A
Efficacy: 78.8 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B1 - U0 - G1


Input Watts (W): 44.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P630527
 CATALOG NUMBER: GWS-SA1D-827-U-T3R-W-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 6.6 fc
 Type III - Medium - N/A

REPORT NUMBER: P630527
CATALOG NUMBER: GWS-SA1D-827-U-T3R-W-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 56-Deg Lateral - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P630527
 CATALOG NUMBER: GWS-SA1D-827-U-T3R-W-HSS

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 313.4 | 0.0 | 313.4 |
| | % Fixture | 9.0 | 0.0 | 9.0 |
| Street Side | Lumens | 3176.1 | 0.0 | 3176.1 |
| | % Fixture | 91.0 | 0.0 | 91.0 |
| Total | Lumens | 3489.5 | 0.0 | 3489.5 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 54.0 | 1.5 |
| 10°-20° | 121.5 | 3.5 |
| 20°-30° | 192.5 | 5.5 |
| 30°-40° | 331.9 | 9.5 |
| 40°-50° | 560.4 | 16.1 |
| 50°-60° | 823.5 | 23.6 |
| 60°-70° | 976.3 | 28.0 |
| 70°-80° | 416.3 | 11.9 |
| 80°-90° | 13.1 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 3489.5 | 100.0 |
| 0°-180° | 3489.5 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P630527

CATALOG NUMBER: GWS-SA1D-827-U-T3R-W-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 243.2 | 7.0 | | | |
| FM (30°-60°) | 1580.8 | 45.3 | | | |
| FH (60°-80°) | 1340.3 | 38.4 | | | G1/1800 |
| FVH (80°-90°) | 11.7 | 0.3 | | | G1/100 |
| BL (0°-30°) | 124.8 | 3.6 | B1/500 | | |
| BM (30°-60°) | 135.0 | 3.9 | B0/220 | | |
| BH (60°-80°) | 52.3 | 1.5 | B0/110 | | G0/110 |
| BVH (80°-90°) | 1.3 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G1
 Type III Medium





REPORT NUMBER: P630527

CATALOG NUMBER: GWS-SA1D-827-U-T3R-W-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 56° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 629.2 | 629.2 | 629.2 | 629.2 | 629.2 | 629.2 | 629.2 | 629.2 | 629.2 | 629.2 | 629.2 |
| 2.5° | 585.7 | 584.8 | 585.4 | 590.2 | 599.2 | 603.3 | 610.3 | 611.6 | 617.4 | 624.7 | 627.6 |
| 5° | 547.7 | 544.5 | 546.1 | 552.8 | 563.0 | 574.5 | 587.7 | 591.2 | 605.5 | 621.8 | 634.0 |
| 7.5° | 512.9 | 509.4 | 513.2 | 523.7 | 538.1 | 550.6 | 570.1 | 572.3 | 595.3 | 624.1 | 646.1 |
| 10° | 458.2 | 459.2 | 466.9 | 485.4 | 507.4 | 533.3 | 559.5 | 562.7 | 591.2 | 631.4 | 665.6 |
| 12.5° | 416.4 | 414.1 | 422.4 | 443.5 | 474.5 | 512.2 | 551.5 | 555.7 | 591.5 | 642.6 | 690.5 |
| 15° | 396.9 | 396.2 | 399.8 | 415.1 | 445.1 | 489.5 | 544.2 | 549.6 | 595.6 | 652.8 | 714.2 |
| 17.5° | 397.5 | 396.6 | 396.2 | 405.2 | 427.6 | 472.6 | 536.2 | 543.2 | 599.2 | 664.0 | 739.1 |
| 20° | 425.3 | 420.8 | 412.9 | 408.7 | 422.1 | 461.7 | 530.8 | 538.8 | 604.3 | 675.8 | 765.6 |
| 22.5° | 483.5 | 485.1 | 463.7 | 441.3 | 434.9 | 463.0 | 530.1 | 539.4 | 615.5 | 694.4 | 798.2 |
| 25° | 599.8 | 597.2 | 557.6 | 507.4 | 472.6 | 477.7 | 541.3 | 552.5 | 637.5 | 720.9 | 828.9 |
| 27.5° | 745.5 | 747.7 | 693.4 | 613.5 | 540.7 | 508.1 | 561.8 | 573.0 | 663.1 | 737.5 | 849.4 |
| 30° | 904.3 | 902.1 | 843.9 | 755.4 | 637.2 | 558.6 | 582.2 | 592.1 | 675.8 | 746.5 | 870.5 |
| 32.5° | 1054.5 | 1049.4 | 991.9 | 899.2 | 760.2 | 638.1 | 610.3 | 616.1 | 692.8 | 766.0 | 898.9 |
| 35° | 1182.7 | 1182.3 | 1132.2 | 1033.4 | 886.7 | 737.8 | 658.6 | 663.4 | 724.4 | 797.0 | 940.8 |
| 37.5° | 1314.9 | 1310.5 | 1254.2 | 1164.1 | 1016.8 | 847.1 | 732.4 | 730.5 | 774.3 | 842.7 | 992.2 |
| 40° | 1423.6 | 1420.7 | 1377.6 | 1291.0 | 1152.0 | 967.9 | 821.9 | 816.1 | 833.4 | 905.9 | 1063.8 |
| 42.5° | 1504.1 | 1504.4 | 1491.0 | 1438.3 | 1295.1 | 1107.6 | 934.4 | 925.4 | 925.1 | 1001.5 | 1158.4 |
| 45° | 1565.2 | 1569.3 | 1589.4 | 1581.4 | 1464.2 | 1270.2 | 1078.5 | 1069.2 | 1053.6 | 1125.5 | 1266.7 |
| 47.5° | 1593.6 | 1599.0 | 1659.7 | 1691.7 | 1612.1 | 1431.6 | 1250.1 | 1230.6 | 1199.9 | 1290.3 | 1387.8 |
| 50° | 1590.7 | 1600.3 | 1685.0 | 1782.1 | 1746.3 | 1595.2 | 1437.0 | 1427.7 | 1377.6 | 1464.8 | 1507.6 |
| 52.5° | 1525.5 | 1546.0 | 1686.6 | 1837.1 | 1849.5 | 1746.0 | 1630.3 | 1613.1 | 1588.8 | 1647.0 | 1620.1 |
| 55° | 1348.5 | 1373.4 | 1619.2 | 1854.7 | 1930.1 | 1877.7 | 1819.5 | 1805.5 | 1765.2 | 1818.9 | 1718.2 |
| 57.5° | 1252.3 | 1273.7 | 1477.3 | 1846.0 | 1998.5 | 1999.4 | 1987.9 | 1976.4 | 1943.2 | 1988.9 | 1833.3 |
| 60° | 1194.5 | 1215.9 | 1401.5 | 1814.4 | 2060.5 | 2127.9 | 2146.1 | 2144.8 | 2096.9 | 2182.2 | 1968.1 |
| 62.5° | 1109.8 | 1139.2 | 1322.6 | 1732.3 | 2104.5 | 2254.4 | 2309.4 | 2300.8 | 2247.4 | 2383.5 | 2101.7 |
| 65° | 938.8 | 964.4 | 1160.9 | 1596.8 | 2078.7 | 2359.2 | 2486.4 | 2490.9 | 2429.2 | 2573.0 | 2207.1 |
| 67.5° | 658.3 | 677.1 | 872.4 | 1312.4 | 1902.9 | 2393.7 | 2667.6 | 2667.3 | 2562.1 | 2670.2 | 2160.5 |
| 70° | 381.5 | 407.4 | 515.4 | 811.3 | 1480.5 | 2236.8 | 2694.8 | 2704.0 | 2508.1 | 2467.2 | 1787.9 |
| 72.5° | 147.6 | 169.0 | 292.1 | 431.1 | 772.0 | 1713.4 | 2318.0 | 2345.2 | 2099.1 | 1903.2 | 1244.3 |
| 75° | 44.1 | 49.2 | 137.4 | 229.4 | 310.0 | 827.6 | 1569.3 | 1577.0 | 1439.9 | 1187.1 | 637.8 |
| 77.5° | 32.9 | 36.4 | 60.1 | 116.0 | 108.6 | 250.8 | 812.0 | 886.7 | 764.4 | 424.0 | 175.8 |
| 80° | 22.4 | 26.5 | 42.8 | 56.6 | 40.3 | 66.8 | 228.2 | 250.5 | 233.3 | 95.2 | 44.1 |
| 82.5° | 9.9 | 12.8 | 30.4 | 28.4 | 14.7 | 19.2 | 70.3 | 74.8 | 48.3 | 28.8 | 15.3 |
| 85° | 1.0 | 1.3 | 11.5 | 12.5 | 5.4 | 4.5 | 14.7 | 14.7 | 10.5 | 9.9 | 6.4 |
| 87.5° | 0.0 | 0.0 | 0.3 | 0.6 | 0.6 | 1.0 | 1.3 | 1.6 | 1.9 | 2.6 | 3.2 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P630527
 CATALOG NUMBER: GWS-SA1D-827-U-T3R-W-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 629.2 | 629.2 | 629.2 | 629.2 | 629.2 | 629.2 | 629.2 | 629.2 | 629.2 | 629.2 | 629.2 |
| 2.5° | 634.9 | 631.1 | 635.9 | 639.7 | 640.7 | 633.7 | 629.5 | 623.4 | 622.2 | 622.5 | 620.9 |
| 5° | 643.6 | 641.7 | 645.2 | 641.0 | 630.2 | 609.7 | 592.1 | 572.6 | 562.1 | 556.0 | 555.4 |
| 7.5° | 659.5 | 658.6 | 654.8 | 635.9 | 602.0 | 556.7 | 512.9 | 470.1 | 443.5 | 433.9 | 432.3 |
| 10° | 683.2 | 681.3 | 665.6 | 620.9 | 548.7 | 461.4 | 387.9 | 326.6 | 289.2 | 278.3 | 264.9 |
| 12.5° | 710.4 | 706.5 | 672.3 | 588.6 | 468.1 | 347.3 | 255.6 | 186.9 | 154.7 | 145.1 | 145.1 |
| 15° | 736.6 | 728.3 | 668.5 | 535.2 | 369.1 | 225.9 | 142.8 | 108.0 | 98.1 | 95.5 | 95.5 |
| 17.5° | 763.4 | 747.4 | 653.5 | 462.4 | 255.0 | 133.6 | 95.2 | 88.5 | 87.2 | 87.6 | 87.9 |
| 20° | 788.6 | 763.7 | 627.0 | 374.8 | 162.7 | 93.3 | 85.3 | 83.7 | 83.1 | 83.7 | 83.4 |
| 22.5° | 816.1 | 778.7 | 586.7 | 279.3 | 105.8 | 84.0 | 81.2 | 79.9 | 79.2 | 80.2 | 80.2 |
| 25° | 843.3 | 789.6 | 533.3 | 187.9 | 84.0 | 78.3 | 76.7 | 75.4 | 74.8 | 75.1 | 75.1 |
| 27.5° | 857.3 | 785.5 | 463.3 | 119.8 | 75.4 | 72.5 | 70.9 | 69.3 | 68.4 | 68.1 | 68.4 |
| 30° | 866.9 | 772.7 | 377.7 | 85.3 | 68.4 | 64.9 | 63.3 | 62.0 | 59.4 | 57.8 | 58.5 |
| 32.5° | 882.0 | 759.9 | 284.7 | 71.6 | 62.6 | 57.2 | 54.6 | 51.4 | 47.9 | 46.3 | 46.3 |
| 35° | 899.8 | 742.3 | 199.7 | 64.5 | 56.6 | 50.8 | 46.0 | 40.6 | 36.4 | 35.2 | 35.2 |
| 37.5° | 923.5 | 725.7 | 132.9 | 59.8 | 51.4 | 45.4 | 38.7 | 32.3 | 27.8 | 27.2 | 26.8 |
| 40° | 959.0 | 711.6 | 93.6 | 56.2 | 47.0 | 39.6 | 31.6 | 24.9 | 21.7 | 20.8 | 20.8 |
| 42.5° | 1005.0 | 697.3 | 74.1 | 52.7 | 43.1 | 34.2 | 25.2 | 19.8 | 17.3 | 16.6 | 16.3 |
| 45° | 1061.9 | 680.3 | 64.5 | 49.5 | 39.3 | 28.4 | 20.1 | 16.6 | 14.7 | 14.1 | 14.1 |
| 47.5° | 1123.5 | 657.3 | 60.1 | 45.4 | 34.8 | 23.0 | 16.9 | 14.4 | 13.4 | 13.1 | 12.8 |
| 50° | 1184.2 | 626.3 | 56.2 | 41.5 | 29.7 | 18.9 | 14.7 | 13.1 | 12.5 | 12.1 | 12.1 |
| 52.5° | 1237.3 | 590.2 | 51.4 | 37.1 | 24.3 | 16.3 | 13.1 | 12.1 | 11.5 | 10.9 | 10.5 |
| 55° | 1282.7 | 550.9 | 45.4 | 32.0 | 19.8 | 14.4 | 12.1 | 11.2 | 10.5 | 9.9 | 9.6 |
| 57.5° | 1341.1 | 528.5 | 36.4 | 25.9 | 16.3 | 12.8 | 11.2 | 10.2 | 9.6 | 8.6 | 8.6 |
| 60° | 1406.0 | 512.2 | 27.2 | 20.5 | 14.1 | 11.8 | 10.2 | 9.3 | 8.6 | 7.7 | 7.7 |
| 62.5° | 1458.1 | 488.0 | 21.4 | 16.6 | 12.1 | 10.5 | 9.3 | 8.3 | 7.7 | 6.7 | 6.7 |
| 65° | 1477.9 | 437.8 | 17.6 | 13.1 | 9.9 | 9.3 | 8.3 | 7.7 | 6.7 | 5.8 | 5.8 |
| 67.5° | 1388.4 | 337.4 | 14.7 | 10.5 | 8.3 | 8.0 | 7.3 | 7.0 | 5.8 | 5.1 | 4.8 |
| 70° | 1099.6 | 205.8 | 12.1 | 8.6 | 7.0 | 6.7 | 6.7 | 6.1 | 5.1 | 4.8 | 4.5 |
| 72.5° | 753.5 | 106.1 | 9.9 | 7.0 | 6.1 | 6.1 | 5.8 | 5.4 | 4.8 | 4.5 | 4.5 |
| 75° | 391.4 | 35.5 | 7.7 | 5.4 | 4.8 | 5.1 | 5.1 | 4.8 | 4.5 | 4.5 | 4.2 |
| 77.5° | 112.2 | 16.0 | 5.8 | 4.2 | 3.8 | 3.8 | 4.2 | 4.2 | 4.2 | 3.8 | 3.8 |
| 80° | 29.1 | 9.3 | 4.2 | 3.2 | 3.2 | 3.2 | 3.2 | 3.5 | 3.8 | 3.5 | 3.5 |
| 82.5° | 11.8 | 5.1 | 2.9 | 2.6 | 2.6 | 2.6 | 2.6 | 2.9 | 3.2 | 3.2 | 3.2 |
| 85° | 7.3 | 2.6 | 2.2 | 2.2 | 2.2 | 1.9 | 1.9 | 2.2 | 2.2 | 2.6 | 2.6 |
| 87.5° | 4.5 | 1.9 | 1.9 | 1.9 | 1.9 | 1.6 | 1.6 | 1.6 | 1.6 | 1.6 | 1.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions


Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_g = -1.5$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)