

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P635457

Luminaire Tested: GWS-SA3D-827-U-SLL-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P635457
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-37)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA3D-827-U-SLL-W
Description: GALLEON WALL SLIM LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT ELIMINATOR LEFT OPTICS
Light Source: (48) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12124.7 lumens
Efficiency: N/A
Efficacy: 100.4 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification: Type III - Short
BUG Rating: B2 - U0 - G2


Input Watts (W): 120.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P635457
 CATALOG NUMBER: GWS-SA3D-827-U-SLL-W

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 5 fc
 Type III - Short - N/A

REPORT NUMBER: P635457
CATALOG NUMBER: GWS-SA3D-827-U-SLL-W

Luminous Intensity Polar Plot



— Vertical Plane Through 315-Deg Lateral - - - Horizontal Cone Through 62.5-Deg Vertical

REPORT NUMBER: P635457

CATALOG NUMBER: GWS-SA3D-827-U-SLL-W

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 2899.0 | 0.0 | 2899.0 |
| | % Fixture | 23.9 | 0.0 | 23.9 |
| Street Side | Lumens | 9225.7 | 0.0 | 9225.7 |
| | % Fixture | 76.1 | 0.0 | 76.1 |
| Total | Lumens | 12124.7 | 0.0 | 12124.7 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 148.9 | 1.2 |
| 10°-20° | 484.0 | 4.0 |
| 20°-30° | 761.9 | 6.3 |
| 30°-40° | 1044.4 | 8.6 |
| 40°-50° | 1629.6 | 13.4 |
| 50°-60° | 2809.7 | 23.2 |
| 60°-70° | 3256.0 | 26.9 |
| 70°-80° | 1718.7 | 14.2 |
| 80°-90° | 271.5 | 2.2 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 12124.7 | 100.0 |
| 0°-180° | 12124.7 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P635457


CATALOG NUMBER: GWS-SA3D-827-U-SLL-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 801.9 | 6.6 | | | |
| FM (30°-60°) | 4002.8 | 33.0 | | | |
| FH (60°-80°) | 4211.4 | 34.7 | | | G2/5000 |
| FVH (80°-90°) | 209.6 | 1.7 | | | G2/225 |
| BL (0°-30°) | 593.0 | 4.9 | B2/1000 | | |
| BM (30°-60°) | 1480.8 | 12.2 | B2/2500 | | |
| BH (60°-80°) | 763.3 | 6.3 | B2/1000 | | G2/1000 |
| BVH (80°-90°) | 61.9 | 0.5 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G2

Type III Short





REPORT NUMBER: P635457
 CATALOG NUMBER: GWS-SA3D-827-U-SLL-W

CANDELA DISTRIBUTION (FULL):

| | 0° | 2° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1511.7 | 1511.7 | 1511.7 | 1511.7 | 1511.7 | 1511.7 | 1511.7 | 1511.7 | 1511.7 | 1511.7 | 1511.7 |
| 2.5° | 1642.5 | 1636.0 | 1626.7 | 1595.2 | 1575.7 | 1553.4 | 1530.2 | 1503.4 | 1472.7 | 1451.4 | 1430.1 |
| 5° | 1781.6 | 1771.4 | 1749.1 | 1674.0 | 1622.1 | 1565.5 | 1518.2 | 1464.4 | 1411.5 | 1375.4 | 1339.2 |
| 7.5° | 1915.1 | 1902.1 | 1867.8 | 1752.8 | 1668.4 | 1586.8 | 1515.4 | 1437.5 | 1358.7 | 1304.9 | 1262.2 |
| 10° | 2048.7 | 2021.8 | 1978.2 | 1828.0 | 1716.7 | 1622.1 | 1540.4 | 1444.9 | 1340.1 | 1266.9 | 1221.4 |
| 12.5° | 2150.7 | 2125.7 | 2078.4 | 1896.6 | 1764.9 | 1646.2 | 1554.4 | 1466.3 | 1377.2 | 1299.3 | 1252.9 |
| 15° | 2246.2 | 2213.8 | 2160.0 | 1960.6 | 1804.8 | 1645.2 | 1526.5 | 1449.6 | 1436.6 | 1417.1 | 1356.8 |
| 17.5° | 2314.8 | 2285.2 | 2229.5 | 2012.5 | 1827.0 | 1616.5 | 1449.6 | 1404.1 | 1462.5 | 1521.9 | 1464.4 |
| 20° | 2375.1 | 2340.8 | 2284.2 | 2048.7 | 1831.7 | 1552.5 | 1355.9 | 1356.8 | 1448.6 | 1530.2 | 1516.3 |
| 22.5° | 2426.1 | 2388.1 | 2338.0 | 2089.5 | 1829.8 | 1463.5 | 1274.3 | 1329.9 | 1421.7 | 1485.7 | 1487.6 |
| 25° | 2489.2 | 2457.7 | 2415.9 | 2149.8 | 1829.8 | 1372.6 | 1214.9 | 1297.5 | 1376.3 | 1430.1 | 1428.2 |
| 27.5° | 2566.2 | 2544.8 | 2510.5 | 2241.6 | 1846.5 | 1296.5 | 1181.5 | 1255.7 | 1317.9 | 1364.2 | 1363.3 |
| 30° | 2652.4 | 2633.0 | 2607.0 | 2339.0 | 1875.2 | 1240.0 | 1163.0 | 1203.8 | 1249.2 | 1286.3 | 1286.3 |
| 32.5° | 2740.5 | 2733.1 | 2705.3 | 2416.9 | 1853.0 | 1222.3 | 1147.2 | 1151.9 | 1176.0 | 1206.6 | 1203.8 |
| 35° | 2863.0 | 2855.5 | 2820.3 | 2477.1 | 1756.5 | 1197.3 | 1122.2 | 1099.0 | 1101.8 | 1121.3 | 1127.7 |
| 37.5° | 3041.9 | 3030.8 | 2978.9 | 2547.6 | 1610.9 | 1134.2 | 1081.4 | 1043.4 | 1035.0 | 1043.4 | 1055.4 |
| 40° | 3258.0 | 3241.3 | 3170.9 | 2643.2 | 1443.1 | 1048.9 | 1017.4 | 985.9 | 971.9 | 974.7 | 988.6 |
| 42.5° | 3528.8 | 3493.6 | 3392.5 | 2744.2 | 1277.1 | 973.8 | 946.0 | 926.5 | 910.7 | 908.9 | 935.8 |
| 45° | 3968.4 | 3872.0 | 3711.5 | 2834.2 | 1137.0 | 933.9 | 882.0 | 868.1 | 855.1 | 862.5 | 894.0 |
| 47.5° | 4736.3 | 4558.3 | 4245.7 | 2911.2 | 1051.7 | 934.8 | 831.0 | 816.1 | 815.2 | 830.0 | 865.3 |
| 50° | 5791.8 | 5534.9 | 5052.6 | 2963.1 | 1007.2 | 946.0 | 800.4 | 776.3 | 793.9 | 808.7 | 842.1 |
| 52.5° | 6802.6 | 6410.3 | 5836.3 | 2962.2 | 987.7 | 947.8 | 808.7 | 739.2 | 793.9 | 797.6 | 829.1 |
| 55° | 7666.1 | 6955.7 | 6047.7 | 2658.0 | 959.9 | 940.4 | 841.2 | 710.4 | 783.7 | 797.6 | 822.6 |
| 57.5° | 8352.4 | 7302.5 | 6032.0 | 2147.0 | 1044.3 | 899.6 | 860.6 | 703.9 | 754.0 | 799.4 | 828.2 |
| 60° | 8276.3 | 7143.9 | 5643.4 | 1317.9 | 1035.9 | 827.3 | 857.9 | 716.0 | 703.9 | 774.4 | 821.7 |
| 62.5° | 7770.9 | 6575.4 | 4974.7 | 914.4 | 972.9 | 785.5 | 812.4 | 737.3 | 657.5 | 738.2 | 790.2 |
| 65° | 7063.3 | 5841.8 | 4145.6 | 701.1 | 805.9 | 787.4 | 735.4 | 722.5 | 616.7 | 680.7 | 736.4 |
| 67.5° | 6127.5 | 4932.0 | 3272.9 | 555.5 | 562.0 | 681.7 | 667.7 | 641.8 | 578.7 | 629.7 | 679.8 |
| 70° | 4606.5 | 3599.3 | 2251.8 | 447.0 | 425.7 | 569.4 | 600.0 | 576.9 | 541.6 | 556.5 | 609.3 |
| 72.5° | 3246.0 | 2350.1 | 1233.5 | 354.3 | 328.3 | 437.7 | 521.2 | 517.5 | 478.6 | 489.7 | 541.6 |
| 75° | 2412.2 | 1662.9 | 770.7 | 280.1 | 267.1 | 313.5 | 436.8 | 447.9 | 415.5 | 428.5 | 468.3 |
| 77.5° | 1605.4 | 1076.7 | 428.5 | 207.7 | 207.7 | 229.1 | 325.5 | 377.5 | 353.3 | 363.5 | 391.4 |
| 80° | 885.7 | 548.1 | 214.2 | 136.3 | 140.0 | 157.7 | 237.4 | 271.7 | 272.7 | 297.7 | 305.1 |
| 82.5° | 280.1 | 174.4 | 95.5 | 79.8 | 75.1 | 90.0 | 153.0 | 194.8 | 181.8 | 231.9 | 213.3 |
| 85° | 64.0 | 40.8 | 17.6 | 17.6 | 19.5 | 29.7 | 58.4 | 103.9 | 132.6 | 159.5 | 115.9 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.9 | 40.8 | 60.3 | 53.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P635457
 CATALOG NUMBER: GWS-SA3D-827-U-SLL-W

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1511.7 | 1511.7 | 1511.7 | 1511.7 | 1511.7 | 1511.7 | 1511.7 | 1511.7 | 1511.7 | 1511.7 | 1511.7 |
| 2.5° | 1417.1 | 1398.6 | 1393.0 | 1377.2 | 1375.4 | 1360.5 | 1355.0 | 1355.0 | 1361.5 | 1361.5 | 1367.9 |
| 5° | 1324.4 | 1301.2 | 1288.2 | 1269.6 | 1265.0 | 1253.9 | 1246.5 | 1247.4 | 1255.7 | 1261.3 | 1272.4 |
| 7.5° | 1242.7 | 1227.0 | 1217.7 | 1209.4 | 1207.5 | 1205.6 | 1197.3 | 1196.4 | 1199.2 | 1207.5 | 1215.9 |
| 10° | 1208.4 | 1197.3 | 1200.1 | 1206.6 | 1216.8 | 1222.3 | 1214.9 | 1211.2 | 1208.4 | 1214.0 | 1221.4 |
| 12.5° | 1241.8 | 1230.7 | 1236.3 | 1247.4 | 1261.3 | 1266.9 | 1264.1 | 1263.1 | 1265.9 | 1287.3 | 1303.0 |
| 15° | 1315.1 | 1293.8 | 1286.3 | 1291.0 | 1302.1 | 1307.7 | 1304.9 | 1308.6 | 1326.2 | 1381.9 | 1421.7 |
| 17.5° | 1406.0 | 1354.0 | 1324.4 | 1316.0 | 1320.6 | 1325.3 | 1325.3 | 1334.6 | 1365.2 | 1446.8 | 1496.9 |
| 20° | 1455.1 | 1387.4 | 1337.3 | 1316.9 | 1318.8 | 1323.4 | 1323.4 | 1336.4 | 1370.7 | 1457.9 | 1490.4 |
| 22.5° | 1442.1 | 1380.0 | 1318.8 | 1296.5 | 1297.5 | 1301.2 | 1301.2 | 1312.3 | 1342.9 | 1419.9 | 1434.7 |
| 25° | 1391.1 | 1336.4 | 1276.1 | 1256.7 | 1258.5 | 1265.0 | 1263.1 | 1269.6 | 1292.8 | 1355.9 | 1364.2 |
| 27.5° | 1329.9 | 1281.7 | 1222.3 | 1207.5 | 1215.9 | 1228.8 | 1217.7 | 1218.6 | 1240.0 | 1292.8 | 1293.8 |
| 30° | 1264.1 | 1224.2 | 1171.3 | 1160.2 | 1176.0 | 1182.5 | 1172.3 | 1172.3 | 1193.6 | 1229.8 | 1228.8 |
| 32.5° | 1192.7 | 1167.6 | 1129.6 | 1117.5 | 1135.2 | 1145.4 | 1132.4 | 1134.2 | 1150.9 | 1175.0 | 1165.8 |
| 35° | 1125.9 | 1112.9 | 1095.3 | 1086.9 | 1098.1 | 1107.3 | 1099.0 | 1102.7 | 1118.5 | 1125.0 | 1112.0 |
| 37.5° | 1061.9 | 1060.0 | 1061.9 | 1061.9 | 1064.7 | 1067.5 | 1061.9 | 1071.2 | 1085.1 | 1076.7 | 1061.9 |
| 40° | 1006.3 | 1013.7 | 1031.3 | 1026.7 | 1023.9 | 1026.7 | 1022.9 | 1038.7 | 1052.6 | 1037.8 | 1020.2 |
| 42.5° | 959.9 | 973.8 | 1000.7 | 1000.7 | 995.1 | 997.0 | 995.1 | 1014.6 | 1024.8 | 1004.4 | 984.9 |
| 45° | 920.0 | 940.4 | 974.7 | 979.4 | 970.1 | 970.1 | 973.8 | 997.9 | 1001.6 | 973.8 | 953.4 |
| 47.5° | 892.2 | 917.2 | 956.2 | 964.5 | 950.6 | 949.7 | 959.9 | 985.9 | 985.9 | 953.4 | 930.2 |
| 50° | 872.7 | 900.5 | 946.9 | 958.0 | 944.1 | 940.4 | 957.1 | 982.1 | 976.6 | 937.6 | 914.4 |
| 52.5° | 859.7 | 888.5 | 946.0 | 961.7 | 952.5 | 948.8 | 965.4 | 983.1 | 969.2 | 927.4 | 903.3 |
| 55° | 851.4 | 882.9 | 948.8 | 961.7 | 951.5 | 945.0 | 961.7 | 977.5 | 970.1 | 921.9 | 898.7 |
| 57.5° | 856.0 | 887.5 | 945.0 | 951.5 | 939.5 | 928.4 | 947.8 | 970.1 | 967.3 | 923.7 | 900.5 |
| 60° | 848.6 | 877.3 | 924.6 | 926.5 | 906.1 | 888.5 | 917.2 | 950.6 | 950.6 | 917.2 | 896.8 |
| 62.5° | 814.3 | 843.0 | 884.8 | 886.6 | 863.4 | 844.0 | 877.3 | 917.2 | 916.3 | 889.4 | 868.1 |
| 65° | 757.7 | 784.6 | 831.9 | 836.5 | 813.3 | 792.9 | 827.3 | 864.4 | 867.1 | 843.0 | 824.5 |
| 67.5° | 695.6 | 719.7 | 754.9 | 773.5 | 754.0 | 732.7 | 764.2 | 799.4 | 798.5 | 769.8 | 750.3 |
| 70° | 621.4 | 643.6 | 676.1 | 691.9 | 679.8 | 659.4 | 688.1 | 706.7 | 698.3 | 684.4 | 671.5 |
| 72.5° | 548.1 | 569.4 | 600.0 | 600.0 | 587.1 | 567.6 | 575.9 | 609.3 | 619.5 | 609.3 | 601.0 |
| 75° | 471.1 | 489.7 | 511.0 | 515.6 | 486.9 | 451.7 | 490.6 | 519.4 | 531.4 | 526.8 | 516.6 |
| 77.5° | 392.3 | 406.2 | 437.7 | 429.4 | 375.6 | 357.1 | 388.6 | 431.3 | 439.6 | 436.8 | 422.9 |
| 80° | 302.3 | 310.7 | 344.1 | 327.4 | 285.6 | 273.6 | 287.5 | 320.9 | 322.7 | 313.5 | 295.8 |
| 82.5° | 203.1 | 214.2 | 236.5 | 204.0 | 203.1 | 192.0 | 180.8 | 184.6 | 201.3 | 199.4 | 187.3 |
| 85° | 103.9 | 109.4 | 130.8 | 122.4 | 104.8 | 90.9 | 86.3 | 91.8 | 82.5 | 75.1 | 64.9 |
| 87.5° | 43.6 | 47.3 | 64.9 | 36.2 | 11.1 | 0.0 | 0.0 | 5.6 | 8.3 | 12.1 | 13.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P635457
 CATALOG NUMBER: GWS-SA3D-827-U-SLL-W

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|---------|
| 0° | 1511.7 | 1511.7 | 1511.7 | 1511.7 | 1511.7 | 1511.7 | 1511.7 | 1511.7 | 1511.7 | 1511.7 | 1511.7 |
| 2.5° | 1382.8 | 1393.0 | 1418.0 | 1449.6 | 1480.2 | 1511.7 | 1546.0 | 1567.3 | 1593.3 | 1626.7 | 1627.6 |
| 5° | 1286.3 | 1309.5 | 1345.7 | 1393.9 | 1444.0 | 1501.5 | 1568.3 | 1623.9 | 1690.7 | 1743.6 | 1764.9 |
| 7.5° | 1227.0 | 1260.4 | 1305.8 | 1367.0 | 1432.9 | 1504.3 | 1591.5 | 1685.1 | 1794.6 | 1865.0 | 1906.8 |
| 10° | 1232.5 | 1283.6 | 1329.0 | 1380.9 | 1440.3 | 1517.3 | 1629.5 | 1753.8 | 1888.2 | 1981.0 | 2032.9 |
| 12.5° | 1331.8 | 1385.6 | 1377.2 | 1374.4 | 1414.3 | 1508.0 | 1660.1 | 1823.3 | 1987.5 | 2080.2 | 2142.3 |
| 15° | 1457.0 | 1477.4 | 1398.6 | 1339.2 | 1363.3 | 1474.6 | 1676.8 | 1885.5 | 2070.0 | 2183.2 | 2244.4 |
| 17.5° | 1521.0 | 1480.2 | 1384.6 | 1295.6 | 1289.1 | 1423.6 | 1685.1 | 1948.5 | 2162.7 | 2275.9 | 2340.8 |
| 20° | 1491.3 | 1431.9 | 1351.3 | 1266.9 | 1220.5 | 1354.0 | 1680.5 | 1998.6 | 2247.1 | 2373.3 | 2426.1 |
| 22.5° | 1427.3 | 1375.4 | 1312.3 | 1231.6 | 1164.8 | 1278.0 | 1668.4 | 2048.7 | 2322.3 | 2449.3 | 2495.7 |
| 25° | 1357.7 | 1318.8 | 1266.9 | 1196.4 | 1133.3 | 1211.2 | 1660.1 | 2115.5 | 2408.5 | 2530.0 | 2559.7 |
| 27.5° | 1288.2 | 1259.4 | 1216.8 | 1162.1 | 1125.9 | 1164.8 | 1662.9 | 2202.6 | 2519.8 | 2634.8 | 2622.8 |
| 30° | 1219.6 | 1194.5 | 1164.8 | 1140.7 | 1125.0 | 1153.7 | 1655.4 | 2295.4 | 2642.2 | 2748.9 | 2677.5 |
| 32.5° | 1154.6 | 1131.5 | 1112.9 | 1116.6 | 1125.9 | 1158.4 | 1617.4 | 2379.8 | 2754.4 | 2845.3 | 2736.8 |
| 35° | 1099.0 | 1074.9 | 1074.9 | 1087.9 | 1122.2 | 1142.6 | 1519.1 | 2445.6 | 2878.7 | 2969.6 | 2821.2 |
| 37.5° | 1047.1 | 1025.7 | 1039.6 | 1061.0 | 1093.4 | 1099.9 | 1393.0 | 2509.6 | 3059.6 | 3144.9 | 2952.0 |
| 40° | 1001.6 | 980.3 | 1005.3 | 1032.2 | 1048.9 | 1046.1 | 1265.0 | 2598.6 | 3272.9 | 3361.0 | 3125.4 |
| 42.5° | 965.4 | 946.0 | 968.2 | 1002.5 | 1005.3 | 1008.1 | 1171.3 | 2684.0 | 3520.5 | 3632.7 | 3424.0 |
| 45° | 935.8 | 921.9 | 933.0 | 967.3 | 967.3 | 1010.0 | 1112.9 | 2755.4 | 3893.3 | 4091.8 | 3972.2 |
| 47.5° | 912.6 | 904.2 | 909.8 | 920.9 | 939.5 | 1043.4 | 1075.8 | 2810.1 | 4572.2 | 4961.7 | 4841.1 |
| 50° | 899.6 | 891.3 | 898.7 | 875.5 | 931.1 | 1060.0 | 1063.8 | 2851.8 | 5467.2 | 6077.4 | 5928.1 |
| 52.5° | 888.5 | 885.7 | 890.3 | 836.5 | 949.7 | 1048.9 | 1054.5 | 2796.2 | 6067.2 | 7175.5 | 7322.9 |
| 55° | 884.8 | 886.6 | 864.4 | 807.8 | 971.9 | 1011.8 | 1026.7 | 2398.3 | 6230.4 | 8122.4 | 9037.7 |
| 57.5° | 886.6 | 881.1 | 824.5 | 810.6 | 972.9 | 937.6 | 1066.5 | 1711.1 | 5993.0 | 8534.1 | 10715.4 |
| 60° | 880.1 | 852.3 | 776.3 | 835.6 | 930.2 | 850.4 | 1037.8 | 1115.7 | 5367.0 | 8217.9 | 10812.8 |
| 62.5° | 851.4 | 810.6 | 734.5 | 849.5 | 854.2 | 798.5 | 942.3 | 859.7 | 4532.3 | 7540.9 | 9874.3 |
| 65° | 809.6 | 754.9 | 699.3 | 820.8 | 777.2 | 774.4 | 708.6 | 689.1 | 3644.8 | 6734.9 | 8983.9 |
| 67.5° | 741.0 | 686.3 | 673.3 | 754.9 | 699.3 | 686.3 | 569.4 | 571.3 | 2908.4 | 5876.2 | 8089.0 |
| 70° | 663.1 | 608.4 | 618.6 | 682.6 | 622.3 | 570.4 | 460.9 | 475.8 | 2206.3 | 4895.9 | 6882.4 |
| 72.5° | 612.1 | 538.8 | 539.8 | 601.0 | 547.2 | 461.9 | 379.3 | 392.3 | 1400.4 | 3690.2 | 5471.8 |
| 75° | 516.6 | 474.8 | 454.4 | 486.9 | 464.6 | 359.8 | 319.0 | 316.3 | 830.0 | 2645.0 | 4097.4 |
| 77.5° | 431.3 | 398.8 | 388.6 | 401.6 | 346.9 | 266.2 | 256.9 | 252.3 | 470.2 | 1694.4 | 2684.9 |
| 80° | 312.5 | 304.2 | 303.3 | 309.8 | 267.1 | 195.7 | 195.7 | 196.6 | 253.2 | 920.0 | 1513.6 |
| 82.5° | 198.5 | 217.0 | 192.0 | 213.3 | 181.8 | 139.1 | 129.8 | 147.5 | 145.6 | 392.3 | 638.1 |
| 85° | 82.5 | 113.1 | 105.7 | 112.2 | 86.3 | 76.0 | 81.6 | 88.1 | 84.4 | 151.2 | 248.5 |
| 87.5° | 15.8 | 18.5 | 20.4 | 19.5 | 19.5 | 24.1 | 26.9 | 32.5 | 32.5 | 43.6 | 75.1 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P635457

CATALOG NUMBER: GWS-SA3D-827-U-SLL-W

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 358° | 360° |
|-------|---------|--------|---------|---------|---------|---------|---------|---------|--------|--------|
| 0° | 1511.7 | 1511.7 | 1511.7 | 1511.7 | 1511.7 | 1511.7 | 1511.7 | 1511.7 | 1511.7 | 1511.7 |
| 2.5° | 1662.9 | 1689.8 | 1684.2 | 1696.3 | 1680.5 | 1686.1 | 1654.5 | 1646.2 | 1640.6 | 1642.5 |
| 5° | 1833.5 | 1888.2 | 1898.4 | 1918.8 | 1904.9 | 1904.9 | 1849.3 | 1807.5 | 1792.7 | 1781.6 |
| 7.5° | 2006.9 | 2085.8 | 2137.7 | 2143.3 | 2135.9 | 2121.0 | 2040.3 | 1965.2 | 1938.3 | 1915.1 |
| 10° | 2160.9 | 2255.5 | 2313.9 | 2341.7 | 2327.8 | 2304.6 | 2204.5 | 2101.5 | 2069.1 | 2048.7 |
| 12.5° | 2278.7 | 2362.1 | 2401.1 | 2419.6 | 2417.8 | 2409.4 | 2327.8 | 2216.5 | 2182.2 | 2150.7 |
| 15° | 2354.7 | 2396.5 | 2381.6 | 2380.7 | 2393.7 | 2427.1 | 2402.0 | 2314.8 | 2275.0 | 2246.2 |
| 17.5° | 2403.9 | 2364.0 | 2298.2 | 2267.5 | 2295.4 | 2374.2 | 2431.7 | 2382.5 | 2346.4 | 2314.8 |
| 20° | 2421.5 | 2279.6 | 2184.1 | 2127.5 | 2160.0 | 2274.0 | 2415.9 | 2431.7 | 2401.1 | 2375.1 |
| 22.5° | 2401.1 | 2176.7 | 2046.8 | 1980.0 | 2011.6 | 2147.9 | 2369.6 | 2471.6 | 2451.2 | 2426.1 |
| 25° | 2351.0 | 2069.1 | 1913.3 | 1853.0 | 1887.3 | 2026.4 | 2287.0 | 2508.7 | 2509.6 | 2489.2 |
| 27.5° | 2288.9 | 1969.8 | 1819.6 | 1763.0 | 1796.4 | 1926.3 | 2206.3 | 2541.1 | 2573.6 | 2566.2 |
| 30° | 2225.8 | 1910.5 | 1775.1 | 1735.2 | 1760.2 | 1875.2 | 2123.8 | 2574.5 | 2639.4 | 2652.4 |
| 32.5° | 2197.1 | 1939.2 | 1879.9 | 1897.5 | 1865.0 | 1904.9 | 2094.1 | 2621.8 | 2719.2 | 2740.5 |
| 35° | 2235.1 | 2194.3 | 2344.5 | 2414.1 | 2299.1 | 2147.9 | 2132.1 | 2693.2 | 2831.4 | 2863.0 |
| 37.5° | 2419.6 | 2740.5 | 2965.0 | 3209.8 | 3010.4 | 2677.5 | 2320.4 | 2814.7 | 2991.9 | 3041.9 |
| 40° | 2821.2 | 3217.2 | 3622.5 | 3938.8 | 3637.4 | 3189.4 | 2678.4 | 2995.6 | 3212.6 | 3258.0 |
| 42.5° | 3199.6 | 3664.2 | 4222.6 | 4631.5 | 4240.2 | 3607.7 | 3064.2 | 3299.8 | 3503.8 | 3528.8 |
| 45° | 3570.6 | 4102.9 | 4948.7 | 5517.2 | 4985.8 | 4005.5 | 3458.4 | 3813.6 | 3967.5 | 3968.4 |
| 47.5° | 4005.5 | 4597.2 | 5859.5 | 6669.1 | 5975.4 | 4446.1 | 3828.4 | 4626.9 | 4841.1 | 4736.3 |
| 50° | 4525.8 | 5088.8 | 6797.1 | 8009.2 | 7182.0 | 4987.7 | 4298.6 | 5618.3 | 5910.5 | 5791.8 |
| 52.5° | 5222.3 | 5630.4 | 7830.2 | 9316.0 | 8497.0 | 5604.4 | 4980.3 | 6927.8 | 7024.3 | 6802.6 |
| 55° | 6202.6 | 6412.2 | 9156.4 | 10929.7 | 9965.2 | 6364.0 | 5977.2 | 8571.2 | 8301.4 | 7666.1 |
| 57.5° | 8434.9 | 7649.4 | 10859.2 | 12770.6 | 11626.2 | 7744.0 | 8162.2 | 10383.4 | 9423.5 | 8352.4 |
| 60° | 10302.7 | 9151.8 | 12434.9 | 14597.6 | 13049.8 | 9265.0 | 10213.7 | 10698.7 | 9381.8 | 8276.3 |
| 62.5° | 9673.0 | 9534.8 | 13003.4 | 14798.9 | 13535.7 | 10013.4 | 9832.5 | 9903.9 | 8769.7 | 7770.9 |
| 65° | 8486.8 | 8795.7 | 12496.1 | 13844.6 | 12996.9 | 9342.9 | 8894.0 | 9169.4 | 8069.5 | 7063.3 |
| 67.5° | 7786.6 | 8013.9 | 11593.7 | 12317.1 | 12017.5 | 8617.6 | 8164.1 | 7964.7 | 6982.6 | 6127.5 |
| 70° | 7070.7 | 7258.9 | 10326.9 | 10400.1 | 10490.1 | 7412.0 | 6675.6 | 6082.0 | 5204.7 | 4606.5 |
| 72.5° | 6109.9 | 6120.1 | 8725.2 | 8300.4 | 8471.1 | 5800.1 | 5373.5 | 4547.2 | 3788.5 | 3246.0 |
| 75° | 5125.9 | 4845.8 | 6906.5 | 5802.0 | 6144.2 | 4511.9 | 4461.8 | 3426.8 | 2857.4 | 2412.2 |
| 77.5° | 3908.2 | 3580.8 | 5045.2 | 3815.4 | 4315.3 | 3004.8 | 3354.5 | 2324.1 | 2010.7 | 1605.4 |
| 80° | 2623.7 | 2419.6 | 2787.8 | 2153.5 | 2823.1 | 2070.9 | 2187.8 | 1316.9 | 1141.7 | 885.7 |
| 82.5° | 1383.7 | 1181.5 | 1723.2 | 1277.1 | 1702.7 | 1137.9 | 820.8 | 407.1 | 346.9 | 280.1 |
| 85° | 536.1 | 620.4 | 844.9 | 454.4 | 660.3 | 406.2 | 237.4 | 101.1 | 84.4 | 64.0 |
| 87.5° | 103.9 | 160.4 | 88.1 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions


Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_9 = -1.5$




Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)