

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P635464

Luminaire Tested: GWS-SA3D-827-U-T2-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P635464
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA3D-827-U-T2-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II OPTICS W/ FACTORY INSALLED GLARE SHIELD, WH
Light Source: (48) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10785.6 lumens
Efficiency: N/A
Efficacy: 89.3 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B2 - U0 - G2


Input Watts (W): 120.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P635464
 CATALOG NUMBER: GWS-SA3D-827-U-T2-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 7.1 fc
 Type II - Short - N/A

REPORT NUMBER: P635464
CATALOG NUMBER: GWS-SA3D-827-U-T2-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 75-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P635464

CATALOG NUMBER: GWS-SA3D-827-U-T2-W-GRSWH

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 2917.7 | 0.0 | 2917.7 |
| | % Fixture | 27.1 | 0.0 | 27.1 |
| Street Side | Lumens | 7867.9 | 0.0 | 7867.9 |
| | % Fixture | 72.9 | 0.0 | 72.9 |
| Total | Lumens | 10785.6 | 0.0 | 10785.6 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 202.1 | 1.9 |
| 10°-20° | 643.5 | 6.0 |
| 20°-30° | 1141.3 | 10.6 |
| 30°-40° | 1747.1 | 16.2 |
| 40°-50° | 2432.7 | 22.6 |
| 50°-60° | 2787.4 | 25.8 |
| 60°-70° | 1432.2 | 13.3 |
| 70°-80° | 360.6 | 3.3 |
| 80°-90° | 38.5 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 10785.6 | 100.0 |
| 0°-180° | 10785.6 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P635464


CATALOG NUMBER: GWS-SA3D-827-U-T2-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1211.8 | 11.2 | | | |
| FM (30°-60°) | 5432.8 | 50.4 | | | |
| FH (60°-80°) | 1209.0 | 11.2 | | | G1/1800 |
| FVH (80°-90°) | 14.3 | 0.1 | | | G1/100 |
| BL (0°-30°) | 775.1 | 7.2 | B2/1000 | | |
| BM (30°-60°) | 1534.5 | 14.2 | B2/2500 | | |
| BH (60°-80°) | 583.9 | 5.4 | B2/1000 | | G2/1000 |
| BVH (80°-90°) | 24.3 | 0.2 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G2

Type II Short





REPORT NUMBER: P635464

CATALOG NUMBER: GWS-SA3D-827-U-T2-W-GRSWH

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 74° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2019.9 | 2019.9 | 2019.9 | 2019.9 | 2019.9 | 2019.9 | 2019.9 | 2019.9 | 2019.9 | 2019.9 | 2019.9 |
| 2.5° | 2170.1 | 2175.7 | 2170.1 | 2179.4 | 2160.8 | 2152.5 | 2132.1 | 2101.5 | 2077.4 | 2073.7 | 2046.8 |
| 5° | 2338.9 | 2351.0 | 2343.5 | 2339.8 | 2314.8 | 2296.3 | 2265.6 | 2204.4 | 2154.4 | 2146.9 | 2094.1 |
| 7.5° | 2447.4 | 2455.8 | 2455.8 | 2458.5 | 2449.3 | 2427.9 | 2395.5 | 2323.1 | 2252.7 | 2241.5 | 2161.8 |
| 10° | 2483.6 | 2490.1 | 2502.1 | 2525.3 | 2543.9 | 2550.4 | 2529.0 | 2459.5 | 2373.2 | 2362.1 | 2250.8 |
| 12.5° | 2491.9 | 2499.4 | 2517.9 | 2560.6 | 2611.6 | 2657.9 | 2661.6 | 2610.6 | 2514.2 | 2502.1 | 2353.7 |
| 15° | 2507.7 | 2515.1 | 2540.2 | 2593.0 | 2668.1 | 2757.2 | 2811.9 | 2776.6 | 2670.0 | 2657.0 | 2470.6 |
| 17.5° | 2505.8 | 2514.2 | 2551.3 | 2621.8 | 2722.9 | 2851.8 | 2957.5 | 2972.3 | 2862.0 | 2839.7 | 2603.2 |
| 20° | 2501.2 | 2508.6 | 2548.5 | 2634.8 | 2760.0 | 2937.1 | 3128.1 | 3205.1 | 3086.4 | 3066.0 | 2758.1 |
| 22.5° | 2538.3 | 2546.6 | 2577.3 | 2648.7 | 2779.4 | 3002.9 | 3285.8 | 3471.3 | 3352.6 | 3323.8 | 2936.2 |
| 25° | 2621.8 | 2633.8 | 2652.4 | 2701.5 | 2814.7 | 3061.4 | 3447.2 | 3772.7 | 3651.2 | 3616.9 | 3130.0 |
| 27.5° | 2750.7 | 2765.5 | 2791.5 | 2814.7 | 2893.5 | 3135.5 | 3607.6 | 4110.3 | 3988.8 | 3952.6 | 3334.9 |
| 30° | 2908.3 | 2927.8 | 2961.2 | 2977.0 | 3030.8 | 3245.0 | 3781.9 | 4458.0 | 4387.5 | 4337.5 | 3565.9 |
| 32.5° | 3126.3 | 3153.2 | 3184.7 | 3189.3 | 3221.8 | 3411.0 | 3954.4 | 4803.0 | 4802.1 | 4766.9 | 3828.3 |
| 35° | 3410.1 | 3438.8 | 3445.3 | 3451.8 | 3467.6 | 3639.1 | 4163.1 | 5117.4 | 5238.9 | 5198.1 | 4114.0 |
| 37.5° | 3719.8 | 3761.5 | 3771.7 | 3743.0 | 3765.3 | 3913.6 | 4397.7 | 5369.7 | 5619.1 | 5575.5 | 4390.3 |
| 40° | 4050.9 | 4067.6 | 4095.4 | 4050.0 | 4077.8 | 4228.0 | 4627.7 | 5531.0 | 5902.9 | 5856.6 | 4608.3 |
| 42.5° | 4288.3 | 4318.9 | 4360.6 | 4344.0 | 4359.7 | 4497.0 | 4789.1 | 5608.9 | 6105.1 | 6058.7 | 4765.0 |
| 45° | 4546.1 | 4555.4 | 4582.3 | 4578.6 | 4587.9 | 4715.8 | 4905.0 | 5643.2 | 6285.9 | 6244.2 | 4898.5 |
| 47.5° | 4770.6 | 4784.5 | 4802.1 | 4781.7 | 4761.3 | 4844.8 | 4999.6 | 5672.9 | 6494.6 | 6444.5 | 5038.6 |
| 50° | 4986.6 | 4998.7 | 5020.0 | 4960.7 | 4884.6 | 4906.0 | 5046.0 | 5713.7 | 6690.3 | 6655.0 | 5148.9 |
| 52.5° | 5026.5 | 5039.5 | 5139.7 | 5151.7 | 5054.3 | 4979.2 | 5127.6 | 5803.7 | 6805.3 | 6783.0 | 5188.8 |
| 55° | 4524.8 | 4548.0 | 4747.4 | 4976.4 | 5216.6 | 5192.5 | 5258.4 | 5851.0 | 6850.7 | 6856.3 | 5260.2 |
| 57.5° | 3512.1 | 3545.5 | 3836.7 | 4151.1 | 4656.5 | 5074.7 | 5275.1 | 5838.9 | 6835.0 | 6865.6 | 5333.5 |
| 60° | 2303.7 | 2323.1 | 2668.1 | 3020.6 | 3544.5 | 4123.2 | 4721.4 | 5621.9 | 6694.9 | 6738.5 | 5314.9 |
| 62.5° | 1391.1 | 1413.4 | 1690.7 | 1957.7 | 2266.6 | 2653.3 | 3202.3 | 4518.3 | 5611.7 | 5709.1 | 4256.8 |
| 65° | 971.0 | 1000.7 | 1243.6 | 1463.4 | 1570.1 | 1490.3 | 1622.0 | 2523.5 | 3496.3 | 3537.1 | 2601.4 |
| 67.5° | 703.9 | 724.3 | 923.7 | 1185.2 | 1303.0 | 1052.6 | 802.2 | 1117.5 | 1522.8 | 1537.6 | 1073.0 |
| 70° | 460.9 | 484.1 | 664.9 | 902.4 | 1063.7 | 853.2 | 600.0 | 604.7 | 640.8 | 648.3 | 623.2 |
| 72.5° | 253.2 | 267.1 | 410.8 | 599.1 | 628.8 | 510.1 | 468.3 | 502.7 | 527.7 | 527.7 | 534.2 |
| 75° | 130.8 | 142.8 | 167.9 | 197.5 | 238.3 | 279.1 | 337.6 | 388.6 | 415.5 | 417.3 | 414.5 |
| 77.5° | 66.8 | 71.4 | 90.0 | 97.4 | 106.7 | 124.3 | 161.4 | 206.8 | 230.9 | 240.2 | 238.3 |
| 80° | 31.5 | 33.4 | 38.0 | 44.5 | 54.7 | 69.6 | 87.2 | 103.9 | 118.7 | 120.6 | 130.8 |
| 82.5° | 16.7 | 18.5 | 20.4 | 24.1 | 29.7 | 37.1 | 51.0 | 61.2 | 70.5 | 72.3 | 80.7 |
| 85° | 6.5 | 7.4 | 8.3 | 9.3 | 13.0 | 15.8 | 21.3 | 28.7 | 35.2 | 35.2 | 41.7 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.9 | 1.9 | 3.7 | 4.6 | 6.5 | 6.5 | 11.1 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P635464

CATALOG NUMBER: GWS-SA3D-827-U-T2-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2019.9 | 2019.9 | 2019.9 | 2019.9 | 2019.9 | 2019.9 | 2019.9 | 2019.9 | 2019.9 | 2019.9 | 2019.9 |
| 2.5° | 2040.3 | 2013.4 | 2001.3 | 1981.9 | 1966.1 | 1948.5 | 1934.6 | 1924.4 | 1917.9 | 1914.2 | 1910.5 |
| 5° | 2073.7 | 2032.9 | 2000.4 | 1961.5 | 1934.6 | 1908.6 | 1887.3 | 1872.4 | 1865.0 | 1859.4 | 1855.7 |
| 7.5° | 2125.6 | 2070.9 | 2009.7 | 1949.4 | 1902.1 | 1860.4 | 1833.5 | 1817.7 | 1807.5 | 1803.8 | 1801.0 |
| 10° | 2197.0 | 2121.0 | 2019.9 | 1924.4 | 1853.9 | 1808.4 | 1789.9 | 1782.5 | 1783.4 | 1781.5 | 1780.6 |
| 12.5° | 2277.7 | 2173.8 | 2017.1 | 1879.8 | 1801.9 | 1775.0 | 1776.0 | 1788.0 | 1801.9 | 1805.7 | 1806.6 |
| 15° | 2364.9 | 2225.8 | 1990.2 | 1822.3 | 1761.1 | 1763.9 | 1788.0 | 1816.8 | 1842.7 | 1853.0 | 1854.8 |
| 17.5° | 2459.5 | 2269.4 | 1941.1 | 1759.3 | 1727.8 | 1757.4 | 1801.9 | 1849.2 | 1887.3 | 1904.0 | 1908.6 |
| 20° | 2565.2 | 2306.5 | 1871.5 | 1697.1 | 1696.2 | 1745.4 | 1810.3 | 1872.4 | 1920.7 | 1942.9 | 1946.6 |
| 22.5° | 2677.4 | 2329.6 | 1786.2 | 1639.6 | 1663.8 | 1729.6 | 1803.8 | 1868.7 | 1919.7 | 1942.0 | 1946.6 |
| 25° | 2790.6 | 2337.1 | 1692.5 | 1586.8 | 1630.4 | 1704.6 | 1772.3 | 1824.2 | 1872.4 | 1891.9 | 1895.6 |
| 27.5° | 2896.3 | 2315.7 | 1603.5 | 1541.3 | 1599.8 | 1667.5 | 1712.9 | 1740.7 | 1774.1 | 1789.0 | 1791.7 |
| 30° | 3003.9 | 2273.1 | 1528.4 | 1505.2 | 1565.5 | 1616.5 | 1636.9 | 1638.7 | 1651.7 | 1651.7 | 1653.6 |
| 32.5° | 3112.4 | 2210.0 | 1462.5 | 1469.9 | 1522.8 | 1556.2 | 1559.0 | 1537.6 | 1521.9 | 1495.9 | 1495.0 |
| 35° | 3237.6 | 2146.0 | 1408.7 | 1430.1 | 1472.7 | 1493.1 | 1484.8 | 1444.0 | 1405.9 | 1363.3 | 1361.4 |
| 37.5° | 3353.5 | 2080.2 | 1363.3 | 1389.2 | 1416.1 | 1431.0 | 1411.5 | 1362.4 | 1330.8 | 1287.2 | 1280.7 |
| 40° | 3449.0 | 2020.8 | 1319.7 | 1346.6 | 1359.6 | 1372.6 | 1341.0 | 1301.1 | 1305.8 | 1281.7 | 1280.7 |
| 42.5° | 3504.7 | 1963.3 | 1278.9 | 1299.3 | 1307.6 | 1316.9 | 1289.1 | 1259.4 | 1284.5 | 1265.9 | 1266.8 |
| 45° | 3545.5 | 1913.2 | 1241.8 | 1249.2 | 1269.6 | 1283.5 | 1257.6 | 1224.2 | 1229.7 | 1158.3 | 1141.6 |
| 47.5° | 3591.8 | 1885.4 | 1206.6 | 1199.1 | 1235.3 | 1259.4 | 1219.5 | 1171.3 | 1137.9 | 1067.4 | 1060.9 |
| 50° | 3641.0 | 1875.2 | 1169.5 | 1149.1 | 1192.6 | 1215.8 | 1169.5 | 1109.2 | 1065.6 | 1027.6 | 1023.9 |
| 52.5° | 3657.7 | 1874.3 | 1123.1 | 1088.8 | 1132.4 | 1164.8 | 1125.9 | 1064.7 | 1012.7 | 975.6 | 973.8 |
| 55° | 3723.5 | 1901.2 | 1063.7 | 1006.2 | 1047.0 | 1113.8 | 1085.1 | 997.0 | 955.2 | 938.5 | 936.7 |
| 57.5° | 3800.5 | 1905.8 | 970.1 | 916.3 | 972.8 | 1051.7 | 1015.5 | 939.5 | 894.0 | 873.6 | 871.8 |
| 60° | 3769.0 | 1791.7 | 869.9 | 847.6 | 909.8 | 993.2 | 959.9 | 894.0 | 841.2 | 821.7 | 819.8 |
| 62.5° | 2872.2 | 1265.0 | 796.6 | 788.3 | 842.1 | 908.9 | 902.4 | 833.7 | 783.7 | 769.7 | 767.9 |
| 65° | 1727.8 | 888.5 | 726.2 | 725.2 | 763.3 | 827.2 | 835.6 | 779.9 | 727.1 | 707.6 | 707.6 |
| 67.5° | 854.1 | 679.8 | 646.4 | 641.8 | 665.9 | 711.3 | 746.6 | 701.1 | 656.6 | 638.1 | 635.3 |
| 70° | 603.7 | 599.1 | 588.0 | 575.0 | 579.6 | 598.2 | 613.0 | 575.0 | 527.7 | 509.1 | 505.4 |
| 72.5° | 522.1 | 523.1 | 515.6 | 505.4 | 501.7 | 488.7 | 475.8 | 447.9 | 419.2 | 399.7 | 401.6 |
| 75° | 405.3 | 407.1 | 411.8 | 408.1 | 397.9 | 383.9 | 370.0 | 334.8 | 311.6 | 293.1 | 289.3 |
| 77.5° | 236.5 | 245.8 | 260.6 | 256.9 | 258.7 | 239.3 | 233.7 | 199.4 | 178.1 | 165.1 | 162.3 |
| 80° | 133.5 | 139.1 | 145.6 | 150.2 | 144.7 | 136.3 | 124.3 | 105.7 | 99.2 | 90.0 | 88.1 |
| 82.5° | 80.7 | 86.2 | 89.0 | 92.7 | 90.9 | 79.8 | 70.5 | 58.4 | 52.9 | 48.2 | 47.3 |
| 85° | 40.8 | 44.5 | 47.3 | 49.2 | 43.6 | 36.2 | 32.5 | 26.0 | 22.3 | 19.5 | 19.5 |
| 87.5° | 10.2 | 11.1 | 13.0 | 11.1 | 10.2 | 4.6 | 3.7 | 0.9 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26


| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_9 = -1.5$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)