

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P637913

Luminaire Tested: GWS-SA4D-827-U-AFL-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P637913
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-47)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA4D-827-U-AFL-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND AUTOMOTIVE FRONTLINE OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH
Light Source: (64) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 16331.6 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B3 - U0 - G1


Input Watts (W): 162.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P637913
 CATALOG NUMBER: GWS-SA4D-827-U-AFL-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 9.5 fc
 Type II - Short - N/A

REPORT NUMBER: P637913
CATALOG NUMBER: GWS-SA4D-827-U-AFL-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 51-Deg Lateral - - - Horizontal Cone Through 52.5-Deg Vertical

REPORT NUMBER: P637913

CATALOG NUMBER: GWS-SA4D-827-U-AFL-W-GRSWH


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 3182.1 | 0.0 | 3182.1 |
| | % Fixture | 19.5 | 0.0 | 19.5 |
| Street Side | Lumens | 13149.5 | 0.0 | 13149.5 |
| | % Fixture | 80.5 | 0.0 | 80.5 |
| Total | Lumens | 16331.6 | 0.0 | 16331.6 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 453.8 | 2.8 |
| 10°-20° | 1179.1 | 7.2 |
| 20°-30° | 1917.0 | 11.7 |
| 30°-40° | 3038.1 | 18.6 |
| 40°-50° | 4582.1 | 28.1 |
| 50°-60° | 3963.8 | 24.3 |
| 60°-70° | 898.6 | 5.5 |
| 70°-80° | 265.0 | 1.6 |
| 80°-90° | 34.1 | 0.2 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 16331.6 | 100.0 |
| 0°-180° | 16331.6 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P637913


CATALOG NUMBER: GWS-SA4D-827-U-AFL-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 2437.5 | 14.9 | | | |
| FM (30°-60°) | 9991.9 | 61.2 | | | |
| FH (60°-80°) | 707.2 | 4.3 | | | G1/1800 |
| FVH (80°-90°) | 12.9 | 0.1 | | | G1/100 |
| BL (0°-30°) | 1112.3 | 6.8 | B3/2500 | | |
| BM (30°-60°) | 1592.1 | 9.7 | B2/2500 | | |
| BH (60°-80°) | 456.4 | 2.8 | B1/500 | | G1/500 |
| BVH (80°-90°) | 21.3 | 0.1 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G1

Type II Short





REPORT NUMBER: P637913

CATALOG NUMBER: GWS-SA4D-827-U-AFL-W-GRSWH

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 51° | 55° | 65° | 75° | 85° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|--------|
| 0° | 4862.7 | 4862.7 | 4862.7 | 4862.7 | 4862.7 | 4862.7 | 4862.7 | 4862.7 | 4862.7 | 4862.7 | 4862.7 |
| 2.5° | 5419.0 | 5449.9 | 5402.2 | 5384.1 | 5354.4 | 5302.8 | 5243.4 | 5226.7 | 5098.9 | 5015.0 | 4920.8 |
| 5° | 5963.6 | 5980.3 | 5941.6 | 5902.9 | 5829.3 | 5737.7 | 5622.9 | 5598.3 | 5366.0 | 5173.8 | 4973.7 |
| 7.5° | 6084.9 | 6078.4 | 6112.0 | 6133.9 | 6124.9 | 6088.7 | 5986.8 | 5939.0 | 5661.6 | 5357.0 | 5061.5 |
| 10° | 5604.8 | 5568.7 | 5692.5 | 5839.7 | 6016.5 | 6220.4 | 6208.8 | 6204.9 | 5963.6 | 5603.5 | 5173.8 |
| 12.5° | 4968.6 | 4950.5 | 5051.2 | 5235.7 | 5569.9 | 6021.6 | 6190.7 | 6322.3 | 6235.9 | 5838.4 | 5298.9 |
| 15° | 4604.6 | 4598.2 | 4666.6 | 4799.5 | 5065.3 | 5635.8 | 5997.1 | 6257.8 | 6469.4 | 6090.0 | 5431.9 |
| 17.5° | 4538.8 | 4542.7 | 4565.9 | 4642.1 | 4833.0 | 5302.8 | 5720.9 | 6084.9 | 6651.4 | 6366.2 | 5598.3 |
| 20° | 4731.1 | 4756.9 | 4716.9 | 4728.5 | 4831.8 | 5182.8 | 5532.5 | 5910.6 | 6767.6 | 6643.7 | 5777.7 |
| 22.5° | 5158.3 | 5149.2 | 5061.5 | 5009.9 | 5011.1 | 5256.3 | 5511.9 | 5829.3 | 6843.7 | 6913.4 | 5940.3 |
| 25° | 5642.2 | 5631.9 | 5527.4 | 5412.5 | 5340.2 | 5456.4 | 5660.3 | 5915.8 | 6912.1 | 7159.9 | 6070.7 |
| 27.5° | 6213.9 | 6181.7 | 6065.5 | 5918.4 | 5758.4 | 5808.7 | 5946.8 | 6149.4 | 7017.9 | 7402.5 | 6157.1 |
| 30° | 6767.6 | 6805.0 | 6638.5 | 6464.3 | 6295.2 | 6264.3 | 6344.3 | 6527.5 | 7233.4 | 7686.4 | 6260.4 |
| 32.5° | 7501.9 | 7489.0 | 7304.4 | 7077.3 | 6836.0 | 6812.7 | 6876.0 | 7043.7 | 7620.6 | 8078.7 | 6417.8 |
| 35° | 8391.1 | 8393.6 | 8131.7 | 7824.5 | 7481.2 | 7419.3 | 7525.1 | 7687.7 | 8197.5 | 8610.4 | 6666.9 |
| 37.5° | 9315.1 | 9311.2 | 9082.8 | 8734.3 | 8265.9 | 8178.1 | 8299.4 | 8420.7 | 8918.9 | 9334.4 | 7054.1 |
| 40° | 9962.9 | 9988.7 | 9881.6 | 9698.4 | 9254.4 | 9040.2 | 9147.3 | 9231.2 | 9703.5 | 10186.2 | 7563.8 |
| 42.5° | 10330.7 | 10369.4 | 10392.7 | 10502.4 | 10268.8 | 10040.4 | 10001.6 | 10045.5 | 10404.3 | 10977.3 | 8042.6 |
| 45° | 10409.4 | 10461.1 | 10630.1 | 11036.6 | 11127.0 | 11062.5 | 10936.0 | 10830.2 | 10927.0 | 11538.7 | 8356.2 |
| 47.5° | 10062.3 | 10152.6 | 10514.0 | 11225.1 | 11752.9 | 11955.5 | 11814.8 | 11653.5 | 11228.9 | 11683.2 | 8323.9 |
| 50° | 8686.6 | 8792.4 | 9606.7 | 10840.5 | 11841.9 | 12580.1 | 12593.0 | 12354.3 | 11192.8 | 11266.4 | 7918.7 |
| 52.5° | 6877.3 | 6949.5 | 7415.4 | 9189.9 | 10968.2 | 12554.3 | 13070.5 | 12815.0 | 11018.6 | 10745.0 | 7411.5 |
| 55° | 4110.4 | 4226.5 | 4661.4 | 6062.9 | 8544.6 | 11127.0 | 12226.5 | 12350.4 | 10933.4 | 10307.5 | 7065.7 |
| 57.5° | 1387.3 | 1444.1 | 1859.7 | 2677.9 | 5035.7 | 8147.1 | 9446.7 | 9950.0 | 9925.5 | 9639.0 | 6390.7 |
| 60° | 660.8 | 673.7 | 757.5 | 1015.7 | 2015.8 | 4257.5 | 5591.9 | 6172.6 | 6701.7 | 6754.7 | 3976.1 |
| 62.5° | 503.3 | 511.1 | 553.6 | 609.1 | 810.5 | 1793.8 | 2563.0 | 3006.9 | 3212.1 | 2756.6 | 1448.0 |
| 65° | 420.7 | 427.2 | 459.4 | 494.3 | 551.1 | 776.9 | 983.4 | 1134.4 | 1022.1 | 796.3 | 690.4 |
| 67.5° | 351.0 | 356.2 | 380.7 | 418.1 | 456.8 | 520.1 | 545.9 | 561.4 | 588.5 | 660.8 | 634.9 |
| 70° | 274.9 | 280.0 | 305.9 | 338.1 | 375.5 | 391.0 | 415.6 | 431.0 | 485.2 | 578.2 | 575.6 |
| 72.5° | 211.6 | 218.1 | 232.3 | 252.9 | 283.9 | 299.4 | 326.5 | 344.6 | 375.5 | 450.4 | 481.4 |
| 75° | 154.9 | 158.7 | 171.6 | 178.1 | 182.0 | 178.1 | 205.2 | 225.8 | 267.1 | 295.5 | 303.3 |
| 77.5° | 63.2 | 71.0 | 68.4 | 68.4 | 81.3 | 98.1 | 112.3 | 125.2 | 153.6 | 170.4 | 171.6 |
| 80° | 25.8 | 28.4 | 33.6 | 37.4 | 45.2 | 58.1 | 67.1 | 72.3 | 85.2 | 95.5 | 103.2 |
| 82.5° | 15.5 | 16.8 | 19.4 | 20.6 | 25.8 | 33.6 | 38.7 | 42.6 | 52.9 | 63.2 | 67.1 |
| 85° | 7.7 | 7.7 | 9.0 | 10.3 | 12.9 | 15.5 | 18.1 | 20.6 | 27.1 | 33.6 | 37.4 |
| 87.5° | 1.3 | 1.3 | 1.3 | 2.6 | 3.9 | 5.2 | 6.5 | 7.7 | 9.0 | 10.3 | 12.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P637913
 CATALOG NUMBER: GWS-SA4D-827-U-AFL-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 4862.7 | 4862.7 | 4862.7 | 4862.7 | 4862.7 | 4862.7 | 4862.7 | 4862.7 | 4862.7 | 4862.7 | 4862.7 |
| 2.5° | 4865.3 | 4795.6 | 4714.3 | 4649.8 | 4574.9 | 4519.5 | 4440.7 | 4391.7 | 4345.2 | 4306.5 | 4278.1 |
| 5° | 4870.5 | 4753.0 | 4584.0 | 4434.3 | 4279.4 | 4132.3 | 3981.3 | 3858.7 | 3749.0 | 3657.4 | 3649.6 |
| 7.5° | 4900.2 | 4731.1 | 4466.5 | 4204.6 | 3902.6 | 3610.9 | 3319.3 | 3081.8 | 2901.1 | 2806.9 | 2787.6 |
| 10° | 4950.5 | 4728.5 | 4346.5 | 3928.4 | 3413.5 | 2943.7 | 2597.8 | 2417.2 | 2312.6 | 2275.2 | 2262.3 |
| 12.5° | 5003.4 | 4722.1 | 4192.9 | 3538.6 | 2823.7 | 2412.0 | 2222.3 | 2200.4 | 2219.7 | 2222.3 | 2221.0 |
| 15° | 5067.9 | 4718.2 | 3999.4 | 3081.8 | 2392.7 | 2165.5 | 2178.4 | 2224.9 | 2270.0 | 2280.4 | 2280.4 |
| 17.5° | 5146.6 | 4709.2 | 3736.1 | 2635.3 | 2122.9 | 2117.8 | 2186.2 | 2248.1 | 2290.7 | 2298.4 | 2298.4 |
| 20° | 5229.2 | 4685.9 | 3412.2 | 2271.3 | 2013.2 | 2088.1 | 2161.6 | 2209.4 | 2239.1 | 2249.4 | 2250.7 |
| 22.5° | 5286.0 | 4624.0 | 3039.2 | 2001.6 | 1944.8 | 2031.3 | 2084.2 | 2133.3 | 2133.3 | 2107.4 | 2099.7 |
| 25° | 5297.6 | 4491.1 | 2635.3 | 1817.1 | 1863.5 | 1943.5 | 1997.7 | 1969.4 | 1916.4 | 1895.8 | 1894.5 |
| 27.5° | 5255.1 | 4297.5 | 2236.5 | 1685.4 | 1765.5 | 1845.5 | 1836.4 | 1795.1 | 1771.9 | 1751.3 | 1759.0 |
| 30° | 5203.4 | 4065.2 | 1890.6 | 1577.0 | 1651.9 | 1730.6 | 1699.6 | 1685.4 | 1668.7 | 1645.4 | 1650.6 |
| 32.5° | 5168.6 | 3805.8 | 1624.8 | 1493.1 | 1575.7 | 1588.6 | 1610.6 | 1609.3 | 1593.8 | 1549.9 | 1547.4 |
| 35° | 5178.9 | 3543.8 | 1446.7 | 1424.7 | 1512.5 | 1507.3 | 1548.6 | 1540.9 | 1433.8 | 1373.1 | 1369.3 |
| 37.5° | 5261.5 | 3292.2 | 1342.2 | 1370.5 | 1411.8 | 1444.1 | 1480.2 | 1387.3 | 1349.9 | 1311.2 | 1313.8 |
| 40° | 5419.0 | 3058.6 | 1285.4 | 1340.9 | 1351.2 | 1398.9 | 1315.1 | 1313.8 | 1297.0 | 1262.1 | 1260.9 |
| 42.5° | 5597.0 | 2861.1 | 1246.7 | 1326.7 | 1312.5 | 1321.5 | 1232.5 | 1242.8 | 1241.5 | 1219.6 | 1213.1 |
| 45° | 5705.5 | 2679.1 | 1215.7 | 1273.8 | 1277.6 | 1187.3 | 1160.2 | 1171.8 | 1178.3 | 1166.6 | 1165.4 |
| 47.5° | 5593.2 | 2470.1 | 1183.4 | 1192.5 | 1226.0 | 1126.6 | 1093.1 | 1094.4 | 1106.0 | 1107.3 | 1102.1 |
| 50° | 5278.3 | 2236.5 | 1144.7 | 1122.8 | 1100.8 | 1063.4 | 1032.4 | 1026.0 | 1037.6 | 1049.2 | 1053.1 |
| 52.5° | 4871.8 | 2013.2 | 1080.2 | 1046.6 | 995.0 | 995.0 | 980.8 | 960.2 | 975.6 | 991.1 | 996.3 |
| 55° | 4573.7 | 1848.0 | 988.5 | 951.1 | 894.3 | 913.7 | 911.1 | 893.0 | 913.7 | 925.3 | 929.2 |
| 57.5° | 3963.2 | 1485.4 | 869.8 | 858.2 | 810.5 | 833.7 | 838.8 | 815.6 | 805.3 | 807.9 | 811.7 |
| 60° | 2352.6 | 958.9 | 784.6 | 783.4 | 740.8 | 767.9 | 783.4 | 760.1 | 729.2 | 733.0 | 738.2 |
| 62.5° | 1055.7 | 733.0 | 677.5 | 672.4 | 671.1 | 705.9 | 722.7 | 700.8 | 656.9 | 660.8 | 665.9 |
| 65° | 664.6 | 633.7 | 588.5 | 588.5 | 609.1 | 638.8 | 651.7 | 633.7 | 583.3 | 576.9 | 582.0 |
| 67.5° | 616.9 | 589.8 | 543.3 | 534.3 | 544.6 | 569.1 | 570.4 | 535.6 | 505.9 | 500.7 | 500.7 |
| 70° | 553.6 | 533.0 | 487.8 | 469.8 | 465.9 | 464.6 | 460.7 | 451.7 | 432.3 | 427.2 | 429.7 |
| 72.5° | 458.1 | 443.9 | 415.6 | 396.2 | 385.9 | 384.6 | 369.1 | 361.3 | 344.6 | 342.0 | 340.7 |
| 75° | 303.3 | 307.1 | 307.1 | 304.6 | 295.5 | 291.7 | 274.9 | 267.1 | 247.8 | 240.0 | 238.7 |
| 77.5° | 179.4 | 183.3 | 188.4 | 189.7 | 188.4 | 188.4 | 172.9 | 163.9 | 144.5 | 134.2 | 131.6 |
| 80° | 109.7 | 112.3 | 114.9 | 118.7 | 113.6 | 109.7 | 95.5 | 86.5 | 77.4 | 71.0 | 69.7 |
| 82.5° | 71.0 | 73.6 | 74.9 | 77.4 | 74.9 | 69.7 | 58.1 | 52.9 | 46.5 | 41.3 | 40.0 |
| 85° | 40.0 | 41.3 | 43.9 | 43.9 | 40.0 | 36.1 | 29.7 | 25.8 | 21.9 | 19.4 | 19.4 |
| 87.5° | 14.2 | 14.2 | 14.2 | 15.5 | 12.9 | 11.6 | 7.7 | 5.2 | 3.9 | 3.9 | 3.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions


Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_9 = -1.5$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)