

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P640422

Luminaire Tested: GWS-SA5D-827-U-T3-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P640422
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-25)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA5D-827-U-T3-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (5) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH
Light Source: (80) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 18848.5 lumens
Efficiency: N/A
Efficacy: 92.1 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B3 - U0 - G3


Input Watts (W): 204.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P640422
 CATALOG NUMBER: GWS-SA5D-827-U-T3-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 6.2 fc
 Type II - Short - N/A

REPORT NUMBER: P640422
CATALOG NUMBER: GWS-SA5D-827-U-T3-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 47-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P640422
 CATALOG NUMBER: GWS-SA5D-827-U-T3-W-GRSWH


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 5965.5 | 0.0 | 5965.5 |
| | % Fixture | 31.6 | 0.0 | 31.6 |
| Street Side | Lumens | 12883.0 | 0.0 | 12883.0 |
| | % Fixture | 68.4 | 0.0 | 68.4 |
| Total | Lumens | 18848.5 | 0.0 | 18848.5 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 344.8 | 1.8 |
| 10°-20° | 1134.0 | 6.0 |
| 20°-30° | 2041.8 | 10.8 |
| 30°-40° | 3083.9 | 16.4 |
| 40°-50° | 4152.8 | 22.0 |
| 50°-60° | 4990.2 | 26.5 |
| 60°-70° | 2430.3 | 12.9 |
| 70°-80° | 598.7 | 3.2 |
| 80°-90° | 72.0 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 18848.5 | 100.0 |
| 0°-180° | 18848.5 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P640422


CATALOG NUMBER: GWS-SA5D-827-U-T3-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1893.2 | 10.0 | | | |
| FM (30°-60°) | 8959.7 | 47.5 | | | |
| FH (60°-80°) | 2003.0 | 10.6 | | | G2/5000 |
| FVH (80°-90°) | 27.0 | 0.1 | | | G1/100 |
| BL (0°-30°) | 1627.3 | 8.6 | B3/2500 | | |
| BM (30°-60°) | 3267.3 | 17.3 | B3/5000 | | |
| BH (60°-80°) | 1026.0 | 5.4 | B3/2500 | | G3/2500 |
| BVH (80°-90°) | 44.9 | 0.2 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G3

Type II Short





REPORT NUMBER: P640422

CATALOG NUMBER: GWS-SA5D-827-U-T3-W-GRSWH

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 47° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|---------|---------|--------|--------|--------|--------|
| 0° | 3495.5 | 3495.5 | 3495.5 | 3495.5 | 3495.5 | 3495.5 | 3495.5 | 3495.5 | 3495.5 | 3495.5 | 3495.5 |
| 2.5° | 3489.1 | 3487.6 | 3487.6 | 3497.1 | 3497.1 | 3500.2 | 3505.0 | 3509.7 | 3511.3 | 3503.4 | 3486.0 |
| 5° | 3527.1 | 3527.1 | 3527.1 | 3535.1 | 3535.1 | 3538.2 | 3544.6 | 3546.1 | 3544.6 | 3531.9 | 3514.5 |
| 7.5° | 3587.3 | 3587.3 | 3588.9 | 3598.4 | 3606.3 | 3611.0 | 3622.1 | 3620.5 | 3615.8 | 3595.2 | 3573.1 |
| 10° | 3685.5 | 3690.2 | 3695.0 | 3706.0 | 3721.9 | 3732.9 | 3740.9 | 3740.9 | 3734.5 | 3702.9 | 3674.4 |
| 12.5° | 3824.8 | 3831.1 | 3835.8 | 3845.3 | 3858.0 | 3877.0 | 3894.4 | 3894.4 | 3886.5 | 3846.9 | 3804.2 |
| 15° | 3987.8 | 3994.2 | 3992.6 | 3995.7 | 4019.5 | 4046.4 | 4060.6 | 4070.1 | 4073.3 | 4017.9 | 3951.4 |
| 17.5° | 4174.6 | 4181.0 | 4174.6 | 4165.1 | 4168.3 | 4211.0 | 4236.4 | 4271.2 | 4291.8 | 4217.4 | 4111.3 |
| 20° | 4344.0 | 4337.7 | 4337.7 | 4344.0 | 4353.5 | 4405.8 | 4443.8 | 4500.7 | 4526.1 | 4435.8 | 4271.2 |
| 22.5° | 4522.9 | 4537.2 | 4530.8 | 4530.8 | 4568.8 | 4655.9 | 4701.8 | 4776.2 | 4803.1 | 4686.0 | 4464.3 |
| 25° | 4754.0 | 4766.7 | 4763.5 | 4766.7 | 4811.0 | 4934.5 | 4980.4 | 5118.2 | 5145.1 | 4977.3 | 4678.1 |
| 27.5° | 5007.3 | 5027.9 | 5037.4 | 5034.3 | 5105.5 | 5267.0 | 5324.0 | 5515.5 | 5564.6 | 5303.4 | 4906.0 |
| 30° | 5336.6 | 5358.8 | 5366.7 | 5363.5 | 5447.4 | 5667.5 | 5732.4 | 5950.9 | 6020.5 | 5689.7 | 5195.7 |
| 32.5° | 5718.2 | 5740.3 | 5764.1 | 5773.6 | 5881.2 | 6106.0 | 6199.4 | 6425.8 | 6525.5 | 6136.1 | 5545.6 |
| 35° | 6096.5 | 6115.5 | 6161.4 | 6235.8 | 6383.1 | 6612.6 | 6694.9 | 6918.1 | 7014.7 | 6599.9 | 5968.3 |
| 37.5° | 6514.5 | 6527.1 | 6566.7 | 6669.6 | 6881.7 | 7100.2 | 7182.5 | 7396.2 | 7407.3 | 7048.0 | 6446.4 |
| 40° | 6972.0 | 6972.0 | 6964.1 | 7065.4 | 7287.0 | 7507.1 | 7578.3 | 7701.8 | 7636.9 | 7393.1 | 6911.8 |
| 42.5° | 7359.8 | 7353.5 | 7359.8 | 7454.8 | 7619.5 | 7798.3 | 7860.1 | 7836.3 | 7754.0 | 7657.4 | 7332.9 |
| 45° | 7709.7 | 7714.4 | 7771.4 | 7844.3 | 7929.7 | 8035.8 | 8072.2 | 7937.7 | 7863.3 | 7869.6 | 7670.1 |
| 47.5° | 7947.2 | 7951.9 | 8084.9 | 8206.8 | 8259.0 | 8292.3 | 8276.4 | 8089.6 | 8051.6 | 8122.9 | 7929.7 |
| 50° | 7978.8 | 8004.1 | 8233.7 | 8483.8 | 8613.6 | 8618.4 | 8574.1 | 8346.1 | 8335.0 | 8415.8 | 8069.1 |
| 52.5° | 7985.1 | 8010.5 | 8297.0 | 8748.2 | 9085.4 | 9156.6 | 9106.0 | 8868.5 | 8753.0 | 8672.2 | 8240.0 |
| 55° | 7961.4 | 7989.9 | 8306.5 | 8925.5 | 9571.4 | 9856.4 | 9861.1 | 9525.5 | 9156.6 | 9102.8 | 8727.6 |
| 57.5° | 7029.0 | 7040.0 | 7530.8 | 8474.3 | 9552.4 | 10359.8 | 10421.5 | 9965.6 | 9544.5 | 9493.8 | 9118.6 |
| 60° | 4896.5 | 4940.9 | 5474.4 | 6720.3 | 8024.7 | 9447.9 | 9647.4 | 9514.4 | 9232.6 | 8863.8 | 7823.7 |
| 62.5° | 2452.2 | 2490.2 | 3025.3 | 4203.1 | 5534.5 | 6658.5 | 6872.2 | 7013.1 | 7079.6 | 6683.8 | 5327.1 |
| 65° | 1055.9 | 1084.4 | 1416.9 | 2195.8 | 3133.0 | 3676.0 | 3750.4 | 3919.8 | 4334.5 | 3867.5 | 2870.2 |
| 67.5° | 706.1 | 725.1 | 894.5 | 1339.3 | 1845.9 | 1880.7 | 1869.6 | 1906.1 | 1996.3 | 1648.0 | 1296.6 |
| 70° | 541.4 | 557.3 | 671.2 | 981.5 | 1326.6 | 1135.1 | 1074.9 | 975.2 | 1059.1 | 1079.7 | 1051.2 |
| 72.5° | 392.6 | 405.3 | 490.8 | 669.7 | 831.1 | 725.1 | 715.6 | 766.2 | 880.2 | 911.9 | 894.5 |
| 75° | 253.3 | 259.6 | 311.9 | 367.3 | 429.0 | 465.4 | 484.4 | 576.2 | 691.8 | 715.6 | 695.0 |
| 77.5° | 169.4 | 174.1 | 204.2 | 235.9 | 243.8 | 245.4 | 251.7 | 292.9 | 372.0 | 416.4 | 411.6 |
| 80° | 88.7 | 88.7 | 99.7 | 99.7 | 114.0 | 136.1 | 142.5 | 169.4 | 205.8 | 228.0 | 229.5 |
| 82.5° | 34.8 | 36.4 | 42.7 | 47.5 | 57.0 | 69.7 | 74.4 | 88.7 | 107.7 | 123.5 | 137.7 |
| 85° | 14.2 | 15.8 | 17.4 | 20.6 | 25.3 | 31.7 | 33.2 | 38.0 | 50.7 | 63.3 | 71.2 |
| 87.5° | 0.0 | 0.0 | 1.6 | 1.6 | 3.2 | 4.7 | 4.7 | 6.3 | 7.9 | 14.2 | 19.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P640422

CATALOG NUMBER: GWS-SA5D-827-U-T3-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3495.5 | 3495.5 | 3495.5 | 3495.5 | 3495.5 | 3495.5 | 3495.5 | 3495.5 | 3495.5 | 3495.5 | 3495.5 |
| 2.5° | 3506.6 | 3486.0 | 3506.6 | 3512.9 | 3530.3 | 3536.6 | 3525.6 | 3524.0 | 3524.0 | 3508.1 | 3503.4 |
| 5° | 3530.3 | 3511.3 | 3531.9 | 3541.4 | 3566.7 | 3582.6 | 3585.7 | 3598.4 | 3606.3 | 3600.0 | 3598.4 |
| 7.5° | 3588.9 | 3565.1 | 3587.3 | 3601.5 | 3634.8 | 3660.1 | 3671.2 | 3699.7 | 3720.3 | 3717.1 | 3715.5 |
| 10° | 3691.8 | 3660.1 | 3685.5 | 3709.2 | 3745.6 | 3775.7 | 3777.3 | 3793.1 | 3813.7 | 3807.4 | 3804.2 |
| 12.5° | 3810.5 | 3780.4 | 3808.9 | 3832.7 | 3875.4 | 3888.1 | 3867.5 | 3861.2 | 3864.3 | 3856.4 | 3850.1 |
| 15° | 3956.2 | 3913.4 | 3938.7 | 3965.7 | 3989.4 | 3975.2 | 3930.8 | 3913.4 | 3911.8 | 3900.8 | 3894.4 |
| 17.5° | 4101.8 | 4048.0 | 4067.0 | 4081.2 | 4070.1 | 4025.8 | 3970.4 | 3940.3 | 3926.1 | 3903.9 | 3897.6 |
| 20° | 4245.9 | 4177.8 | 4174.6 | 4163.5 | 4112.9 | 4032.2 | 3957.7 | 3897.6 | 3861.2 | 3831.1 | 3820.0 |
| 22.5° | 4410.5 | 4315.5 | 4268.0 | 4217.4 | 4106.6 | 3975.2 | 3862.8 | 3777.3 | 3718.7 | 3680.7 | 3668.0 |
| 25° | 4587.8 | 4453.3 | 4355.1 | 4253.8 | 4043.2 | 3853.3 | 3696.5 | 3579.4 | 3509.7 | 3468.6 | 3454.3 |
| 27.5° | 4763.5 | 4578.3 | 4431.1 | 4258.5 | 3916.6 | 3677.5 | 3467.0 | 3308.7 | 3239.0 | 3205.8 | 3194.7 |
| 30° | 5001.0 | 4744.5 | 4521.3 | 4196.8 | 3750.4 | 3433.7 | 3170.9 | 3011.1 | 2965.1 | 2941.4 | 2931.9 |
| 32.5° | 5274.9 | 4955.1 | 4641.6 | 4067.0 | 3538.2 | 3148.8 | 2871.7 | 2760.9 | 2729.3 | 2683.4 | 2681.8 |
| 35° | 5635.8 | 5255.9 | 4755.6 | 3875.4 | 3270.7 | 2843.2 | 2642.2 | 2563.0 | 2506.0 | 2433.2 | 2426.9 |
| 37.5° | 6056.9 | 5631.1 | 4817.4 | 3631.6 | 2958.8 | 2591.5 | 2471.2 | 2382.6 | 2290.7 | 2194.2 | 2181.5 |
| 40° | 6492.3 | 6069.6 | 4822.1 | 3343.5 | 2653.3 | 2425.3 | 2324.0 | 2208.4 | 2094.4 | 1986.8 | 1972.5 |
| 42.5° | 6949.8 | 6478.0 | 4738.2 | 3011.1 | 2403.1 | 2281.2 | 2178.3 | 2032.7 | 1904.5 | 1831.6 | 1823.7 |
| 45° | 7358.2 | 6807.3 | 4548.2 | 2661.2 | 2217.9 | 2160.9 | 2029.5 | 1872.8 | 1804.7 | 1752.5 | 1741.4 |
| 47.5° | 7679.6 | 7025.8 | 4291.8 | 2347.7 | 2067.5 | 2037.4 | 1866.5 | 1785.7 | 1733.5 | 1686.0 | 1674.9 |
| 50° | 7837.9 | 7074.9 | 3957.7 | 2092.9 | 1928.2 | 1891.8 | 1774.7 | 1712.9 | 1678.1 | 1640.1 | 1630.6 |
| 52.5° | 8034.2 | 7130.3 | 3669.6 | 1879.1 | 1792.1 | 1743.0 | 1698.7 | 1649.6 | 1624.3 | 1600.5 | 1592.6 |
| 55° | 8485.4 | 7339.2 | 3517.6 | 1708.2 | 1662.3 | 1640.1 | 1633.8 | 1592.6 | 1584.7 | 1568.9 | 1554.6 |
| 57.5° | 8669.0 | 7204.7 | 3158.3 | 1568.9 | 1559.4 | 1562.5 | 1578.3 | 1540.4 | 1532.4 | 1513.4 | 1503.9 |
| 60° | 6972.0 | 5445.9 | 2138.8 | 1448.5 | 1473.9 | 1494.4 | 1510.3 | 1472.3 | 1461.2 | 1458.0 | 1445.4 |
| 62.5° | 4467.5 | 3349.8 | 1492.9 | 1336.1 | 1374.1 | 1399.5 | 1409.0 | 1372.5 | 1364.6 | 1390.0 | 1391.5 |
| 65° | 2325.6 | 1825.3 | 1211.1 | 1215.8 | 1247.5 | 1285.5 | 1304.5 | 1291.8 | 1288.6 | 1315.6 | 1317.1 |
| 67.5° | 1187.3 | 1116.1 | 1055.9 | 1073.3 | 1098.7 | 1147.7 | 1192.1 | 1247.5 | 1266.5 | 1269.6 | 1271.2 |
| 70° | 1011.6 | 979.9 | 949.9 | 960.9 | 987.9 | 1014.8 | 1057.5 | 1084.4 | 1052.8 | 1044.8 | 1041.7 |
| 72.5° | 861.2 | 837.5 | 823.2 | 835.9 | 850.1 | 845.4 | 832.7 | 845.4 | 850.1 | 851.7 | 853.3 |
| 75° | 669.7 | 652.2 | 641.2 | 642.7 | 642.7 | 625.3 | 601.6 | 587.3 | 571.5 | 558.8 | 558.8 |
| 77.5° | 410.0 | 413.2 | 424.3 | 422.7 | 421.1 | 414.8 | 391.0 | 378.4 | 340.4 | 329.3 | 329.3 |
| 80° | 234.3 | 239.0 | 250.1 | 253.3 | 253.3 | 245.4 | 221.6 | 207.4 | 190.0 | 182.1 | 180.5 |
| 82.5° | 142.5 | 148.8 | 155.1 | 158.3 | 159.9 | 150.4 | 129.8 | 118.7 | 109.2 | 101.3 | 101.3 |
| 85° | 74.4 | 77.6 | 83.9 | 85.5 | 80.7 | 71.2 | 60.2 | 55.4 | 45.9 | 44.3 | 44.3 |
| 87.5° | 20.6 | 22.2 | 25.3 | 20.6 | 19.0 | 14.2 | 7.9 | 6.3 | 3.2 | 1.6 | 1.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26


| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_g = -1.5$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)