

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P643918

Luminaire Tested: GWS-SA6F-830-U-SL3-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P643918
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-32)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SAGF-830-U-SL3-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (6) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III SPILL LIGHT ELIMINATOR OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (96) 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 23124.9 lumens
Efficiency: N/A
Efficacy: 62.1 lumens/watt
Luminous Opening: Rectangular (W 2' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B3 - U0 - G2


Input Watts (W): 372.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P643918
 CATALOG NUMBER: GWS-SA6F-830-U-SL3-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 16.2 fc
 Type II - Short - N/A

REPORT NUMBER: P643918
CATALOG NUMBER: GWS-SA6F-830-U-SL3-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 53-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P643918
 CATALOG NUMBER: GWS-SA6F-830-U-SL3-W-GRSBK

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3819.9	0.0	3819.9
	% Fixture	16.5	0.0	16.5
Street Side	Lumens	19305.0	0.0	19305.0
	% Fixture	83.5	0.0	83.5
Total	Lumens	23124.9	0.0	23124.9
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	867.9	3.8
10°-20°	1905.3	8.2
20°-30°	2482.2	10.7
30°-40°	3600.4	15.6
40°-50°	5195.1	22.5
50°-60°	6283.1	27.2
60°-70°	2560.7	11.1
70°-80°	230.1	1.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	23124.9	100.0
0°-180°	23124.9	100.0

Coefficient of Utilization



REPORT NUMBER: P643918


CATALOG NUMBER: GWS-SA6F-830-U-SL3-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	3472.6	15.0			
FM (30°-60°)	13305.6	57.5			
FH (60°-80°)	2526.8	10.9			G2/5000
FVH (80°-90°)	0.0	0.0			G0/10
BL (0°-30°)	1782.8	7.7	B3/2500		
BM (30°-60°)	1773.0	7.7	B2/2500		
BH (60°-80°)	264.1	1.1	B1/500		G1/500
BVH (80°-90°)	0.0	0.0			G0/10
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G2

Type II Short





REPORT NUMBER: P643918

CATALOG NUMBER: GWS-SA6F-830-U-SL3-W-GRSBK

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	53°	55°	65°	75°	85°
0°	10143.9	10143.9	10143.9	10143.9	10143.9	10143.9	10143.9	10143.9	10143.9	10143.9	10143.9
2.5°	10002.2	10024.9	10064.5	10115.6	10149.6	10166.6	10166.6	10214.8	10183.6	10158.1	10129.7
5°	9574.2	9596.9	9650.7	9732.9	9815.1	9874.6	9942.7	9993.7	10013.5	10013.5	9965.3
7.5°	8970.5	9001.7	9035.7	9149.1	9327.6	9460.8	9577.0	9650.7	9758.4	9792.4	9724.4
10°	8321.5	8352.6	8429.2	8585.0	8789.1	8987.5	9185.9	9279.4	9463.7	9560.0	9483.5
12.5°	7771.6	7785.8	7887.8	8074.9	8335.6	8607.7	8848.6	8945.0	9205.8	9350.3	9259.6
15°	7318.1	7326.6	7428.7	7635.6	7936.0	8270.4	8573.7	8672.9	8993.2	9211.4	9075.4
17.5°	6975.2	6978.0	7065.9	7289.8	7604.4	7975.7	8335.6	8457.5	8871.3	9134.9	8930.8
20°	6802.3	6793.8	6856.1	7051.7	7349.3	7720.6	8145.7	8295.9	8803.3	9123.6	8820.3
22.5°	6805.1	6785.3	6810.8	6949.7	7201.9	7550.5	8026.7	8196.7	8809.0	9171.7	8726.8
25°	6966.7	6938.3	6944.0	7017.7	7196.2	7513.7	8043.7	8225.1	8922.3	9333.3	8692.7
27.5°	7238.8	7207.6	7207.6	7244.4	7340.8	7629.9	8256.3	8463.2	9225.6	9647.9	8763.6
30°	7590.2	7559.0	7547.7	7584.5	7663.9	7930.3	8729.6	8945.0	9744.3	10163.7	8990.3
32.5°	7992.7	7955.8	7975.7	8026.7	8103.2	8471.7	9339.0	9625.2	10393.3	10858.1	9398.5
35°	8417.8	8386.6	8477.3	8587.9	8706.9	9222.8	10180.7	10430.2	11189.7	11722.6	10022.0
37.5°	8823.1	8809.0	8998.8	9231.3	9477.8	10124.1	11036.7	11229.4	11872.8	12663.6	10784.4
40°	9228.4	9225.6	9551.5	9959.7	10353.6	11022.5	11685.7	11844.5	12289.5	13394.8	11515.7
42.5°	9681.9	9681.9	10132.6	10676.7	11201.1	11782.1	12161.9	12232.8	12476.5	13817.1	12065.5
45°	10115.6	10141.1	10662.6	11294.6	11915.3	12374.5	12490.7	12496.4	12553.0	14066.5	12521.9
47.5°	10458.5	10481.2	11104.7	11833.1	12502.0	12825.1	12842.1	12816.6	12754.3	14304.6	12873.3
50°	10736.3	10770.3	11422.2	12193.1	12904.5	13258.8	13389.2	13363.6	13204.9	14559.7	13119.9
52.5°	10872.3	10920.5	11532.7	12371.6	13352.3	14001.4	14364.1	14423.7	13879.5	14701.4	13355.1
55°	9783.9	9854.8	10418.8	11566.7	13601.7	15149.2	15718.9	15707.6	14610.7	15123.7	13927.7
57.5°	7389.0	7383.3	7851.0	9106.6	11617.7	15214.4	16552.2	16529.5	15293.8	15614.1	14514.4
60°	5030.9	4996.8	5121.5	5728.1	8123.1	12394.3	15064.2	15370.3	14809.1	14423.7	12323.5
62.5°	4140.9	4109.7	4070.0	3902.8	4665.2	7720.6	10407.5	10872.3	10798.6	10024.9	7729.1
65°	3389.8	3415.3	3525.8	3455.0	3245.3	3959.5	5402.1	5677.1	5189.6	4367.6	2701.1
67.5°	2499.8	2511.2	2655.7	3029.8	2916.5	2635.9	2542.4	2587.7	1516.3	697.2	450.7
70°	1476.7	1485.2	1618.4	2120.0	2366.6	2023.7	1717.6	1692.1	600.9	187.1	204.1
72.5°	836.1	819.1	844.6	1009.0	1289.6	1074.2	884.3	804.9	181.4	104.9	104.9
75°	396.8	385.5	331.6	311.8	283.4	181.4	113.4	96.4	45.3	42.5	42.5
77.5°	2.8	8.5	5.7	8.5	8.5	5.7	2.8	2.8	8.5	8.5	11.3
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P643918
 CATALOG NUMBER: GWS-SA6F-830-U-SL3-W-GRSBK

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	10143.9	10143.9	10143.9	10143.9	10143.9	10143.9	10143.9	10143.9	10143.9	10143.9	10143.9
2.5°	10078.7	9993.7	9973.8	9968.2	9888.8	9803.8	9715.9	9681.9	9630.9	9599.7	9625.2
5°	9888.8	9766.9	9659.2	9560.0	9384.3	9191.6	9024.4	8916.7	8814.6	8746.6	8763.6
7.5°	9619.6	9460.8	9214.3	8962.0	8638.9	8349.8	8026.7	7828.3	7644.1	7542.0	7590.2
10°	9333.3	9123.6	8729.6	8301.6	7794.3	7340.8	6878.8	6501.8	6283.6	6076.7	6099.4
12.5°	9052.7	8774.9	8185.4	7536.4	6895.8	6226.9	5529.7	5008.2	4651.1	4393.1	4353.5
15°	8791.9	8434.8	7655.4	6799.4	5926.5	5036.5	4146.6	3401.1	2987.3	2732.2	2715.2
17.5°	8559.5	8117.4	7105.5	6028.5	4934.5	3795.1	2771.9	2213.6	1975.5	1865.0	1853.6
20°	8335.6	7797.1	6544.4	5246.3	3851.8	2664.2	1913.1	1655.2	1578.7	1533.3	1539.0
22.5°	8120.2	7448.5	5954.8	4379.0	2888.1	1870.6	1482.3	1383.1	1374.6	1380.3	1383.1
25°	7938.8	7128.2	5348.3	3542.9	2060.5	1425.6	1238.6	1210.2	1235.7	1272.6	1278.3
27.5°	7845.3	6867.5	4755.9	2701.1	1490.8	1159.2	1074.2	1085.5	1130.9	1170.6	1176.2
30°	7870.8	6671.9	4143.7	1958.5	1147.9	977.8	949.5	972.2	1017.5	1054.4	1060.0
32.5°	8052.2	6572.7	3517.3	1425.6	943.8	853.1	841.8	858.8	898.5	926.8	929.6
35°	8412.2	6595.4	2922.1	1091.2	810.6	759.6	756.8	768.1	787.9	807.8	810.6
37.5°	8942.2	6779.6	2335.4	907.0	734.1	697.2	685.9	685.9	700.1	708.6	714.2
40°	9511.9	7057.4	1870.6	802.1	680.2	640.5	617.9	609.4	620.7	632.0	634.9
42.5°	9982.3	7335.1	1519.2	728.4	637.7	583.9	555.5	549.9	564.0	583.9	589.5
45°	10342.3	7550.5	1266.9	668.9	589.5	530.0	498.8	498.8	524.3	558.4	564.0
47.5°	10671.1	7723.4	1079.9	615.0	544.2	481.8	450.7	456.3	498.8	544.2	552.7
50°	10895.0	7862.3	941.0	566.9	507.3	442.1	413.8	425.1	476.2	530.0	538.5
52.5°	11135.9	8032.4	850.3	524.3	473.3	411.0	385.5	394.0	450.7	510.2	521.5
55°	11802.0	8602.0	847.5	467.7	413.8	368.5	357.1	360.0	416.6	484.7	498.8
57.5°	12346.1	9103.7	904.1	394.0	345.8	323.1	317.4	320.3	371.3	447.8	464.8
60°	10214.8	7074.4	748.3	325.9	289.1	283.4	274.9	280.6	328.8	396.8	411.0
62.5°	6045.5	4044.5	357.1	249.4	246.6	240.9	232.4	243.7	289.1	348.6	357.1
65°	2066.2	1198.9	226.7	204.1	209.7	201.2	192.7	204.1	243.7	277.8	280.6
67.5°	396.8	317.4	181.4	170.1	172.9	155.9	153.1	164.4	187.1	192.7	189.9
70°	206.9	184.2	138.9	138.9	133.2	110.5	110.5	121.9	121.9	113.4	110.5
72.5°	107.7	102.0	90.7	102.0	85.0	68.0	68.0	73.7	68.0	56.7	56.7
75°	42.5	42.5	39.7	51.0	36.8	31.2	28.3	34.0	25.5	19.8	19.8
77.5°	11.3	11.3	11.3	14.2	8.5	8.5	5.7	5.7	2.8	0.0	0.0
80°	0.0	2.8	0.0	2.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)