

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P634527

Luminaire Tested: GWS-SA3B-830-U-T1-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P634527
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA3B-830-U-T1-W
Description: GALLEON WALL SLIM LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE I OPTICS
Light Source: (48) 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8247.7 lumens
Efficiency: N/A
Efficacy: 120.8 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification: Type I - Medium
BUG Rating: B3 - U0 - G3


Input Watts (W): 68.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P634527
 CATALOG NUMBER: GWS-SA3B-830-U-T1-W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 15.1 fc
 Type I - Medium - N/A

REPORT NUMBER: P634527
CATALOG NUMBER: GWS-SA3B-830-U-T1-W

Luminous Intensity Polar Plot



— Vertical Plane Through 89-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P634527

CATALOG NUMBER: GWS-SA3B-830-U-T1-W


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4087.7	0.0	4087.7
	% Fixture	49.6	0.0	49.6
Street Side	Lumens	4160.0	0.0	4160.0
	% Fixture	50.4	0.0	50.4
Total	Lumens	8247.7	0.0	8247.7
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.9	1.7
10°-20°	452.1	5.5
20°-30°	764.3	9.3
30°-40°	1048.9	12.7
40°-50°	1337.6	16.2
50°-60°	1678.3	20.3
60°-70°	2024.1	24.5
70°-80°	732.3	8.9
80°-90°	71.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	8247.7	100.0
0°-180°	8247.7	100.0

Coefficient of Utilization



REPORT NUMBER: P634527


CATALOG NUMBER: GWS-SA3B-830-U-T1-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	668.0	8.1			
FM (30°-60°)	2018.4	24.5			
FH (60°-80°)	1436.0	17.4			G1/1800
FVH (80°-90°)	37.6	0.5			G1/100
BL (0°-30°)	687.3	8.3	B2/1000		
BM (30°-60°)	2046.4	24.8	B2/2500		
BH (60°-80°)	1320.3	16.0	B3/2500		G3/2500
BVH (80°-90°)	33.6	0.4			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3

Type I Medium





REPORT NUMBER: P634527
 CATALOG NUMBER: GWS-SA3B-830-U-T1-W

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	89°	
0°	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3
2.5°	1388.5	1387.3	1384.3	1393.2	1391.4	1392.0	1395.6	1393.2	1389.0	1381.9	1381.9	1392.0
5°	1427.6	1427.0	1420.4	1425.8	1419.9	1415.7	1415.1	1409.2	1404.4	1396.7	1396.7	1407.4
7.5°	1465.5	1464.9	1459.5	1469.0	1464.3	1459.5	1454.2	1442.4	1431.1	1419.9	1419.9	1431.7
10°	1494.5	1493.9	1492.7	1506.3	1507.5	1509.3	1506.9	1486.8	1467.2	1453.6	1453.6	1465.5
12.5°	1511.1	1512.8	1515.8	1540.7	1553.1	1565.0	1567.9	1551.4	1518.8	1499.2	1499.2	1513.4
15°	1499.8	1503.4	1518.2	1563.2	1597.6	1624.2	1635.5	1621.8	1579.8	1547.2	1547.2	1563.2
17.5°	1445.9	1448.9	1477.9	1546.6	1622.4	1684.0	1702.4	1694.1	1647.3	1607.6	1607.6	1623.0
20°	1371.3	1377.8	1409.2	1505.1	1618.3	1725.5	1774.7	1771.7	1720.8	1659.8	1659.8	1678.1
22.5°	1303.8	1311.5	1344.6	1450.7	1590.4	1736.2	1847.5	1855.2	1787.7	1711.9	1711.9	1726.7
25°	1227.9	1235.0	1277.7	1386.1	1542.5	1727.9	1909.7	1944.7	1863.5	1771.7	1771.7	1785.3
27.5°	1150.3	1155.7	1197.7	1313.2	1479.7	1712.5	1958.9	2043.0	1938.2	1813.2	1813.2	1822.6
30°	1082.2	1089.3	1127.8	1240.4	1411.0	1681.7	1999.2	2147.8	2024.0	1860.0	1860.0	1867.7
32.5°	1016.5	1022.4	1064.4	1168.7	1338.1	1634.3	2035.3	2271.1	2151.4	1947.0	1947.0	1947.0
35°	933.5	944.2	991.6	1100.0	1269.4	1571.5	2061.4	2414.4	2325.5	2075.6	2075.6	2076.2
37.5°	857.1	863.0	912.8	1022.4	1197.1	1500.4	2063.7	2563.1	2545.9	2239.1	2239.1	2240.2
40°	770.0	777.7	831.1	939.5	1114.2	1425.8	2041.2	2701.7	2776.9	2407.3	2407.3	2400.8
42.5°	681.8	693.0	744.0	850.0	1024.8	1334.6	1981.4	2833.8	3070.1	2602.2	2602.2	2586.2
45°	596.5	603.6	654.5	754.6	922.3	1225.6	1885.4	2960.5	3418.4	2898.3	2898.3	2875.2
47.5°	500.5	503.5	556.2	652.2	816.3	1104.1	1748.0	3073.7	3801.1	3290.5	3290.5	3250.8
50°	415.2	419.4	460.8	543.2	686.5	960.2	1576.8	3140.0	4288.6	3825.4	3825.4	3756.7
52.5°	335.9	340.0	373.2	438.9	567.5	796.1	1364.8	3124.6	4783.2	4489.4	4489.4	4389.3
55°	271.3	274.3	296.8	348.3	446.6	633.2	1114.2	2986.6	5332.3	5356.6	5356.6	5141.0
57.5°	229.2	230.4	245.8	277.2	348.9	488.1	860.1	2660.8	5908.0	6463.1	6463.1	6108.9
60°	205.0	205.5	212.7	232.2	275.4	372.6	630.3	2141.9	6504.5	7847.4	7847.4	7361.7
62.5°	189.6	189.6	195.5	206.7	228.6	286.7	463.2	1538.3	6932.8	9353.7	9353.7	8871.0
65°	174.7	174.7	178.9	188.4	200.2	234.0	347.7	992.2	7143.1	10613.0	10613.0	10505.8
67.5°	155.8	156.4	159.3	169.4	180.1	195.5	263.6	671.1	6706.5	10961.3	10961.3	11503.9
70°	138.0	138.6	142.8	149.3	158.2	168.8	206.1	462.6	4881.5	9129.2	9129.2	10286.1
72.5°	118.5	120.8	123.8	130.9	136.2	143.9	168.2	299.7	2840.3	5872.5	5872.5	6799.5
75°	97.1	100.1	103.7	110.8	114.3	117.3	138.6	213.8	1366.5	2975.9	2975.9	3388.8
77.5°	75.2	78.2	82.3	88.9	91.2	94.8	106.0	154.6	654.5	1319.2	1319.2	1422.2
80°	50.3	51.5	55.1	62.8	66.9	69.3	78.2	105.4	284.3	529.6	529.6	524.8
82.5°	30.8	31.4	32.6	37.3	39.1	41.5	50.9	64.6	135.6	601.8	601.8	690.1
85°	11.3	10.7	10.1	13.0	15.4	17.8	23.7	32.6	59.2	413.5	413.5	462.6
87.5°	0.0	0.0	0.0	0.6	1.2	1.2	2.4	4.7	14.2	154.6	154.6	106.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P634527
 CATALOG NUMBER: GWS-SA3B-830-U-T1-W

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3
2.5°	1389.0	1382.5	1390.8	1396.7	1409.8	1414.5	1415.7	1411.6	1411.6	1404.4	1405.6
5°	1405.0	1400.9	1414.5	1424.6	1443.5	1450.7	1455.4	1452.4	1454.2	1449.5	1450.7
7.5°	1429.3	1425.8	1449.5	1469.0	1488.6	1496.9	1501.0	1498.6	1499.2	1493.3	1495.1
10°	1463.1	1464.3	1492.7	1518.2	1544.2	1552.5	1554.3	1547.2	1541.3	1530.6	1531.2
12.5°	1509.3	1515.2	1555.5	1583.9	1610.6	1622.4	1609.4	1583.3	1559.1	1540.7	1538.3
15°	1559.6	1570.3	1628.4	1664.5	1693.5	1687.6	1649.1	1590.4	1542.5	1515.2	1509.9
17.5°	1620.1	1636.1	1708.9	1752.2	1777.0	1739.1	1658.6	1570.9	1504.0	1467.2	1460.1
20°	1676.9	1702.4	1794.2	1850.5	1853.4	1768.1	1654.4	1531.2	1447.1	1402.1	1392.6
22.5°	1729.1	1761.6	1883.7	1955.3	1916.8	1781.2	1628.9	1474.9	1378.4	1325.7	1317.4
25°	1785.9	1832.1	1987.9	2054.8	1980.2	1775.8	1575.6	1405.0	1295.5	1241.6	1235.6
27.5°	1825.0	1883.1	2092.8	2156.7	2032.3	1745.6	1506.9	1328.6	1219.6	1168.7	1160.4
30°	1870.0	1944.1	2208.3	2267.5	2064.3	1701.2	1433.5	1257.5	1149.1	1094.1	1088.1
32.5°	1951.8	2044.8	2351.6	2384.8	2074.4	1646.1	1363.0	1188.8	1075.7	1020.6	1012.3
35°	2083.3	2192.3	2553.0	2515.7	2066.7	1585.7	1296.1	1108.3	1000.5	948.9	940.6
37.5°	2249.1	2384.8	2777.5	2633.6	2045.4	1519.4	1216.7	1040.7	932.9	880.8	876.1
40°	2403.7	2570.8	3029.3	2735.4	2002.1	1437.6	1140.3	970.3	860.1	805.0	794.3
42.5°	2597.4	2819.6	3320.7	2823.7	1931.0	1339.9	1054.4	883.2	768.9	719.1	706.1
45°	2891.8	3167.9	3659.5	2908.4	1825.0	1219.6	946.6	777.2	668.8	617.8	607.7
47.5°	3259.1	3603.2	4026.8	2958.8	1663.9	1092.9	824.5	665.2	556.8	499.3	494.6
50°	3775.0	4236.5	4420.7	2949.9	1483.8	942.4	687.1	531.9	441.3	399.8	393.3
52.5°	4403.5	5031.4	4846.6	2843.3	1292.5	771.2	535.5	417.6	350.1	320.5	315.1
55°	5191.9	5983.3	5295.0	2614.6	1050.8	590.6	420.6	329.3	283.1	265.4	263.0
57.5°	6168.1	7215.9	5726.8	2229.6	790.2	450.8	324.0	271.9	250.0	239.3	238.7
60°	7456.4	8524.4	6101.7	1732.6	565.7	344.7	267.7	242.9	225.7	218.6	218.0
62.5°	8988.2	9712.7	6335.1	1180.0	425.3	274.8	235.8	220.4	210.3	206.1	205.5
65°	10562.7	10463.8	6223.8	773.0	322.8	233.4	211.5	203.2	194.3	190.1	190.1
67.5°	11492.7	10305.0	5369.0	536.7	255.9	205.0	190.7	183.0	168.2	164.7	164.7
70°	10179.4	8350.3	3519.1	392.7	207.3	179.5	165.9	155.2	149.3	145.7	145.1
72.5°	6732.6	5433.6	1871.2	272.5	173.0	152.8	140.4	136.2	129.1	125.6	125.0
75°	3350.9	2853.9	959.0	196.7	143.9	122.6	117.3	115.5	109.6	104.8	103.7
77.5°	1396.7	1270.6	447.2	142.8	109.6	98.9	94.2	94.2	87.7	82.3	80.0
80°	526.6	469.1	211.5	97.7	81.2	73.5	70.5	68.1	62.8	56.3	52.7
82.5°	704.3	460.3	103.7	61.0	53.3	47.4	43.2	41.5	38.5	35.5	33.2
85°	456.1	327.0	46.8	31.4	26.7	20.1	17.8	16.6	14.8	13.0	11.8
87.5°	93.0	109.6	14.2	5.9	3.6	1.8	1.8	0.6	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)