

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P639957

Luminaire Tested: GWS-SA5C-830-U-SL2-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P639957
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-27)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA5C-830-U-SL2-W
Description: GALLEON WALL SLIM LUMINAIRE. (5) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II SPILL LIGHT ELIMINATOR OPTICS
Light Source: (80) 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 18588.9 lumens
Efficiency: N/A
Efficacy: 118.0 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B3 - U0 - G3

Input Watts (W): 157.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P639957

CATALOG NUMBER: GWS-SA5C-830-U-SL2-W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 6.6 fc
 Type II - Short - N/A

REPORT NUMBER: P639957
CATALOG NUMBER: GWS-SA5C-830-U-SL2-W

Luminous Intensity Polar Plot



— Vertical Plane Through 66-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical



REPORT NUMBER: P639957

CATALOG NUMBER: GWS-SA5C-830-U-SL2-W

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3772.1	0.0	3772.1
	% Fixture	20.3	0.0	20.3
Street Side	Lumens	14816.8	0.0	14816.8
	% Fixture	79.7	0.0	79.7
Total	Lumens	18588.9	0.0	18588.9
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	360.5	1.9
10°-20°	886.0	4.8
20°-30°	1217.8	6.6
30°-40°	1664.9	9.0
40°-50°	2522.8	13.6
50°-60°	3921.7	21.1
60°-70°	4774.6	25.7
70°-80°	2908.5	15.6
80°-90°	332.2	1.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	18588.9	100.0
0°-180°	18588.9	100.0

Coefficient of Utilization



REPORT NUMBER: P639957


CATALOG NUMBER: GWS-SA5C-830-U-SL2-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1456.5	7.8			
FM (30°-60°)	6776.4	36.5			
FH (60°-80°)	6307.7	33.9			G3/7500
FVH (80°-90°)	276.2	1.5			G3/500
BL (0°-30°)	1007.7	5.4	B3/2500		
BM (30°-60°)	1333.0	7.2	B2/2500		
BH (60°-80°)	1375.4	7.4	B3/2500		G3/2500
BVH (80°-90°)	56.0	0.3			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3

Type II Short





REPORT NUMBER: P639957
 CATALOG NUMBER: GWS-SA5C-830-U-SL2-W

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	66°	75°	85°
0°	4107.6	4107.6	4107.6	4107.6	4107.6	4107.6	4107.6	4107.6	4107.6	4107.6	4107.6
2.5°	3847.2	3860.8	3852.7	3904.2	3906.9	3972.0	4008.6	4039.8	4042.5	4083.2	4110.3
5°	3584.2	3592.3	3592.3	3641.1	3673.7	3760.5	3844.5	3934.0	3940.8	4038.5	4113.0
7.5°	3371.3	3379.4	3374.0	3439.1	3481.1	3577.4	3684.5	3821.5	3835.0	3992.4	4122.5
10°	3204.5	3201.7	3215.3	3275.0	3329.2	3444.5	3563.8	3719.8	3740.1	3939.5	4133.4
12.5°	3090.5	3093.3	3101.4	3163.8	3222.1	3336.0	3459.4	3628.9	3650.6	3878.4	4128.0
15°	3036.3	3030.9	3037.7	3094.6	3150.2	3250.6	3378.0	3553.0	3574.7	3824.2	4129.3
17.5°	3024.1	3020.0	3018.7	3059.4	3101.4	3195.0	3317.0	3494.7	3517.7	3788.9	4137.5
20°	3062.1	3056.6	3041.7	3059.4	3077.0	3155.6	3273.6	3452.6	3478.4	3765.9	4153.7
22.5°	3166.5	3157.0	3133.9	3112.2	3089.2	3136.7	3246.5	3421.4	3447.2	3751.0	4170.0
25°	3325.2	3317.0	3292.6	3243.8	3159.7	3151.6	3241.1	3407.9	3433.6	3740.1	4176.8
27.5°	3543.5	3531.3	3506.9	3436.4	3299.4	3207.2	3261.4	3406.5	3430.9	3727.9	4170.0
30°	3802.5	3794.4	3780.8	3695.4	3512.3	3325.2	3307.5	3417.4	3436.4	3721.1	4156.4
32.5°	4065.6	4057.4	4068.3	4027.6	3802.5	3520.4	3407.9	3447.2	3460.8	3719.8	4144.2
35°	4297.5	4307.0	4385.6	4392.4	4171.4	3784.9	3566.5	3516.4	3519.1	3746.9	4149.7
37.5°	4540.2	4576.8	4679.9	4768.0	4583.6	4134.7	3802.5	3646.5	3643.8	3816.1	4183.6
40°	4861.6	4877.9	5009.4	5174.9	5059.6	4614.8	4137.5	3859.5	3840.5	3957.1	4274.4
42.5°	5174.9	5214.2	5424.4	5614.2	5576.3	5155.9	4559.2	4178.1	4144.2	4206.6	4461.6
45°	5573.6	5611.5	5847.5	6091.6	6160.8	5767.5	5098.9	4631.1	4597.2	4582.3	4804.7
47.5°	5972.3	6011.6	6223.1	6575.7	6818.5	6532.3	5801.4	5229.1	5173.5	5115.2	5322.7
50°	6240.8	6286.9	6488.9	6912.0	7481.6	7487.0	6634.0	6012.9	5942.4	5850.2	6052.3
52.5°	6231.3	6261.1	6453.7	6941.9	7958.9	8584.1	7748.7	7011.0	6954.1	6753.4	6929.7
55°	5741.7	5786.5	5980.4	6590.6	8010.5	9624.2	9386.9	8188.1	8086.4	7727.0	7921.0
57.5°	4758.5	4796.5	4991.8	5744.4	7553.5	10157.2	11467.2	9688.0	9548.3	8787.5	9011.3
60°	3592.3	3546.2	3638.4	4297.5	6460.4	10170.7	13303.3	11722.1	11488.9	9921.2	10108.4
62.5°	2695.9	2649.8	2670.2	2855.9	4380.2	9348.9	14350.2	14504.8	14119.7	11201.4	11164.8
65°	2130.4	2104.7	2163.0	2290.4	2553.5	7119.5	14358.4	17514.0	17271.3	12684.9	12248.3
67.5°	1735.8	1719.5	1779.2	2015.2	2070.8	3825.6	12874.8	18918.9	19013.8	14309.5	13253.1
70°	1398.1	1373.7	1467.3	1777.8	1925.7	2314.9	9222.8	18202.9	18356.1	15277.8	12969.7
72.5°	965.5	966.9	1014.4	1440.2	1859.2	1998.9	5216.9	15157.1	15489.3	14400.4	11402.1
75°	650.9	656.4	669.9	950.6	1712.8	1939.2	2780.0	11475.3	11709.9	11902.5	9424.9
77.5°	393.3	396.0	427.2	575.0	1181.2	1810.4	1883.6	8318.3	8502.7	7846.4	5842.1
80°	227.8	237.3	265.8	385.1	797.4	1360.2	1457.8	5100.3	5309.1	3487.9	1856.5
82.5°	100.4	107.1	145.1	223.8	465.1	1156.8	1137.8	2015.2	1985.3	972.3	644.1
85°	17.6	21.7	31.2	70.5	170.9	610.2	882.8	889.6	836.7	368.9	267.2
87.5°	0.0	0.0	0.0	0.0	0.0	4.1	132.9	238.7	237.3	104.4	92.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P639957
 CATALOG NUMBER: GWS-SA5C-830-U-SL2-W

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	4107.6	4107.6	4107.6	4107.6	4107.6	4107.6	4107.6	4107.6	4107.6	4107.6	4107.6
2.5°	4128.0	4091.3	4123.9	4128.0	4121.2	4115.8	4075.1	4039.8	4035.7	3997.8	3997.8
5°	4142.9	4109.0	4125.2	4094.1	4045.2	3995.1	3908.3	3848.6	3821.5	3772.7	3772.7
7.5°	4163.2	4128.0	4109.0	4031.7	3917.8	3807.9	3668.2	3551.6	3504.2	3435.0	3432.3
10°	4182.2	4137.5	4072.4	3921.8	3740.1	3565.2	3361.8	3196.3	3083.8	3001.0	3001.0
12.5°	4180.8	4122.5	3993.7	3771.3	3520.4	3266.8	2995.6	2746.1	2596.9	2468.1	2460.0
15°	4178.1	4098.1	3893.4	3596.4	3264.1	2912.9	2544.0	2218.6	1997.5	1871.4	1860.6
17.5°	4175.4	4066.9	3780.8	3397.0	2952.2	2473.5	1986.7	1634.1	1449.7	1372.4	1375.1
20°	4175.4	4031.7	3660.1	3167.8	2592.9	1947.4	1457.8	1201.5	1155.4	1159.5	1163.5
22.5°	4163.2	3988.3	3525.9	2918.3	2192.8	1432.0	1075.4	988.6	1013.0	1051.0	1056.4
25°	4134.7	3916.4	3369.9	2641.7	1716.8	1042.8	877.4	861.1	905.9	953.3	966.9
27.5°	4090.0	3833.7	3195.0	2317.6	1263.9	838.1	771.6	770.3	805.5	840.8	853.0
30°	4042.5	3741.5	3010.5	1956.8	915.4	729.6	703.8	703.8	721.4	743.1	740.4
32.5°	3986.9	3647.9	2812.5	1581.2	745.9	668.6	660.4	656.4	659.1	667.2	667.2
35°	3939.5	3565.2	2609.1	1183.9	668.6	634.7	626.5	617.0	613.0	607.5	610.2
37.5°	3921.8	3500.1	2398.9	892.3	630.6	610.2	596.7	583.1	573.6	570.9	569.6
40°	3950.3	3473.0	2188.7	735.0	603.5	584.5	569.6	551.9	543.8	543.8	543.8
42.5°	4061.5	3493.3	1974.5	664.5	584.5	562.8	541.1	524.8	522.1	524.8	526.2
45°	4264.9	3572.0	1752.1	629.2	568.2	541.1	515.3	503.1	503.1	505.8	505.8
47.5°	4628.4	3778.1	1532.4	607.5	551.9	523.5	496.3	484.1	482.8	485.5	485.5
50°	5257.6	4149.7	1334.4	592.6	539.7	509.9	482.8	466.5	462.4	461.1	461.1
52.5°	6050.9	4793.8	1208.3	581.8	524.8	495.0	467.9	446.2	438.0	434.0	434.0
55°	7009.7	5652.2	1208.3	573.6	505.8	477.3	446.2	424.5	412.3	406.8	406.8
57.5°	8095.9	6651.7	1417.1	566.8	490.9	457.0	423.1	401.4	387.8	379.7	379.7
60°	9201.1	7708.1	1933.8	557.4	477.3	431.2	397.3	377.0	359.4	349.9	348.5
62.5°	10347.0	8871.6	2614.6	562.8	467.9	406.8	370.2	347.2	332.2	322.8	321.4
65°	11396.6	9979.5	3209.9	604.8	469.2	385.1	339.0	318.7	306.5	294.3	292.9
67.5°	12287.6	10591.1	2792.2	690.3	497.7	359.4	307.8	287.5	276.6	268.5	267.2
70°	11663.8	9658.1	1583.9	743.1	537.0	332.2	272.6	259.0	248.2	242.7	241.4
72.5°	9974.1	8177.3	1059.1	656.4	489.6	297.0	240.0	229.2	221.0	214.3	212.9
75°	8079.6	6484.9	809.6	538.4	381.1	241.4	206.1	198.0	189.9	183.1	181.7
77.5°	4780.2	3746.9	596.7	425.8	268.5	188.5	170.9	164.1	156.0	150.5	149.2
80°	1525.6	1301.9	378.4	292.9	177.6	145.1	131.5	126.1	118.0	111.2	109.8
82.5°	581.8	503.1	200.7	149.2	118.0	99.0	88.1	82.7	77.3	70.5	69.2
85°	257.7	241.4	111.2	80.0	63.7	48.8	43.4	40.7	33.9	28.5	27.1
87.5°	90.9	90.9	47.5	23.1	13.6	6.8	4.1	1.4	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)