

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P642925

Luminaire Tested: GWS-SA6D-830-U-SL2-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P642925
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-29)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA6D-830-U-SL2-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (6) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II SPILL LIGHT ELIMINATOR OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH
Light Source: (96) 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 24236.7 lumens
Efficiency: N/A
Efficacy: 98.6 lumens/watt
Luminous Opening: Rectangular (W 2' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B3 - U0 - G3


Input Watts (W): 245.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P642925
 CATALOG NUMBER: GWS-SA6D-830-U-SL2-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 12.4 fc
 Type II - Short - N/A

REPORT NUMBER: P642925
CATALOG NUMBER: GWS-SA6D-830-U-SL2-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 53-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P642925

CATALOG NUMBER: GWS-SA6D-830-U-SL2-W-GRSWH

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	7577.9	0.0	7577.9
	% Fixture	31.3	0.0	31.3
Street Side	Lumens	16658.8	0.0	16658.8
	% Fixture	68.7	0.0	68.7
Total	Lumens	24236.7	0.0	24236.7
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	699.9	2.9
10°-20°	1836.2	7.6
20°-30°	2705.3	11.2
30°-40°	3786.7	15.6
40°-50°	4977.9	20.5
50°-60°	5836.6	24.1
60°-70°	3438.4	14.2
70°-80°	855.4	3.5
80°-90°	100.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	24236.7	100.0
0°-180°	24236.7	100.0

Coefficient of Utilization



REPORT NUMBER: P642925


CATALOG NUMBER: GWS-SA6D-830-U-SL2-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	2946.7	12.2			
FM (30°-60°)	10843.7	44.7			
FH (60°-80°)	2834.8	11.7			G2/5000
FVH (80°-90°)	33.6	0.1			G1/100
BL (0°-30°)	2294.6	9.5	B3/2500		
BM (30°-60°)	3757.5	15.5	B3/5000		
BH (60°-80°)	1459.0	6.0	B3/2500		G3/2500
BVH (80°-90°)	66.8	0.3			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3

Type II Short





REPORT NUMBER: P642925

CATALOG NUMBER: GWS-SA6D-830-U-SL2-W-GRSWH

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	53°	55°	65°	75°	85°
0°	7739.4	7739.4	7739.4	7739.4	7739.4	7739.4	7739.4	7739.4	7739.4	7739.4	7739.4
2.5°	7294.7	7315.1	7319.2	7382.4	7386.5	7478.3	7539.5	7527.3	7590.5	7668.0	7729.2
5°	6945.9	6947.9	6968.3	7043.8	7084.6	7205.0	7307.0	7307.0	7429.4	7588.5	7725.2
7.5°	6658.3	6656.2	6674.6	6758.2	6825.6	6970.4	7109.1	7125.4	7296.8	7529.3	7751.7
10°	6391.1	6405.3	6425.7	6527.7	6613.4	6792.9	6958.1	6984.7	7200.9	7488.5	7788.4
12.5°	6219.7	6221.7	6252.3	6366.6	6476.7	6668.5	6841.9	6874.5	7123.4	7449.8	7814.9
15°	6109.5	6111.6	6144.2	6270.7	6399.2	6593.0	6770.5	6807.2	7078.5	7443.6	7865.9
17.5°	6060.6	6058.5	6089.1	6215.6	6356.4	6558.3	6748.0	6792.9	7098.9	7490.6	7955.7
20°	6060.6	6062.6	6078.9	6193.2	6336.0	6550.2	6770.5	6825.6	7178.5	7596.6	8094.4
22.5°	6146.3	6154.4	6162.6	6240.1	6352.3	6562.4	6829.6	6903.1	7349.8	7774.1	8275.9
25°	6313.5	6315.6	6323.7	6387.0	6438.0	6597.1	6927.5	7037.7	7617.0	8033.2	8504.4
27.5°	6537.9	6566.5	6574.6	6615.4	6615.4	6682.8	7080.5	7239.7	7978.1	8406.5	8796.1
30°	6852.1	6862.3	6876.5	6921.4	6872.5	6843.9	7304.9	7508.9	8396.3	8857.3	9147.0
32.5°	7127.5	7149.9	7227.4	7300.9	7213.1	7123.4	7635.4	7876.1	8798.1	9326.5	9520.3
35°	7362.0	7417.1	7566.0	7729.2	7668.0	7578.3	8074.0	8324.9	9128.6	9663.1	9850.7
37.5°	7645.6	7688.4	7892.4	8157.6	8212.7	8169.9	8608.4	8787.9	9348.9	9748.7	10030.3
40°	7933.2	7998.5	8261.7	8628.8	8838.9	8869.5	9102.1	9222.5	9424.4	9581.5	9995.6
42.5°	8227.0	8339.2	8700.2	9128.6	9501.9	9571.3	9518.2	9569.2	9399.9	9351.0	9834.4
45°	8586.0	8718.6	9126.6	9673.3	10164.9	10273.0	9926.2	9879.3	9395.8	9263.2	9734.5
47.5°	9010.3	9142.9	9532.5	10169.0	10797.3	10876.8	10344.4	10258.7	9538.6	9397.9	9869.1
50°	9385.6	9477.4	9826.3	10538.2	11386.8	11433.7	10805.4	10701.4	9893.6	9771.2	10289.3
52.5°	9004.2	8994.0	9361.2	10238.3	11692.8	12257.8	11515.3	11415.4	10579.0	10391.3	10940.1
55°	7639.5	7523.2	7851.6	8714.5	10838.1	12990.2	12788.2	12588.3	11492.9	11015.5	11550.0
57.5°	5585.3	5552.6	5632.2	6442.0	8681.9	11856.0	13567.5	13549.1	12282.3	11586.7	12157.9
60°	4367.5	4318.5	4106.3	4128.8	5917.8	9261.2	11774.4	12315.0	12771.9	11929.4	12582.2
62.5°	3877.9	3841.2	3731.0	3427.1	3525.0	6209.5	8630.9	9126.6	11160.4	10536.2	10807.5
65°	3210.8	3200.6	3292.4	3280.2	2953.8	3429.1	4871.3	5371.1	7017.3	7105.0	7017.3
67.5°	2333.7	2315.3	2547.9	3006.8	2843.6	2588.7	2715.1	2888.5	3598.4	3231.2	2908.9
70°	1517.7	1491.2	1625.8	2172.5	2545.8	2256.1	1956.3	1927.7	1978.7	1230.1	1330.0
72.5°	1017.9	987.3	985.3	1195.4	1538.1	1519.7	1515.7	1501.4	1340.2	971.0	1077.1
75°	567.1	542.6	536.5	516.1	550.8	561.0	597.7	618.1	669.1	736.4	816.0
77.5°	95.9	93.8	118.3	151.0	208.1	267.2	330.5	348.8	430.4	510.0	561.0
80°	53.0	55.1	71.4	87.7	116.3	159.1	204.0	216.2	265.2	308.0	348.8
82.5°	28.6	28.6	36.7	46.9	63.2	83.6	110.2	120.4	153.0	179.5	208.1
85°	10.2	10.2	14.3	18.4	26.5	34.7	42.8	49.0	67.3	91.8	104.0
87.5°	0.0	0.0	0.0	0.0	2.0	4.1	8.2	8.2	10.2	18.4	26.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P642925

CATALOG NUMBER: GWS-SA6D-830-U-SL2-W-GRSWH

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	7739.4	7739.4	7739.4	7739.4	7739.4	7739.4	7739.4	7739.4	7739.4	7739.4	7739.4
2.5°	7780.2	7725.2	7800.6	7835.3	7847.5	7855.7	7802.7	7766.0	7753.7	7715.0	7692.5
5°	7808.8	7772.1	7843.5	7843.5	7792.5	7739.4	7631.3	7555.8	7502.8	7439.6	7429.4
7.5°	7857.7	7831.2	7870.0	7790.4	7661.9	7519.1	7331.5	7184.6	7066.3	6988.7	6990.8
10°	7923.0	7890.4	7859.8	7682.3	7447.7	7184.6	6896.9	6682.8	6486.9	6397.2	6348.2
12.5°	7965.9	7918.9	7790.4	7496.7	7151.9	6799.0	6393.1	6074.9	5791.3	5662.8	5652.6
15°	8018.9	7933.2	7676.2	7256.0	6776.6	6295.2	5773.0	5330.3	4946.8	4746.9	4736.7
17.5°	8088.3	7947.5	7539.5	6980.6	6380.9	5671.0	5014.1	4457.2	4049.2	3894.2	3920.7
20°	8186.2	7963.8	7384.5	6674.6	5889.2	4961.1	4143.1	3631.0	3474.0	3463.8	3443.4
22.5°	8296.3	7974.0	7213.1	6331.9	5293.6	4204.3	3423.0	3204.7	3202.7	3253.7	3265.9
25°	8420.8	7982.2	7019.3	5932.1	4649.0	3449.5	3027.2	2962.0	3013.0	3108.8	3121.1
27.5°	8579.9	7998.5	6784.8	5493.5	3963.6	2980.3	2809.0	2792.6	2853.8	2943.6	2939.5
30°	8814.5	8057.7	6535.9	4989.6	3259.8	2758.0	2676.4	2678.4	2702.9	2745.7	2751.8
32.5°	9053.1	8149.5	6293.1	4422.5	2855.9	2631.5	2594.8	2590.7	2590.7	2609.0	2613.1
35°	9279.6	8253.5	6030.0	3831.0	2660.0	2558.1	2533.6	2521.3	2515.2	2511.1	2505.0
37.5°	9406.0	8304.5	5773.0	3247.5	2556.0	2509.1	2484.6	2468.3	2445.9	2429.5	2425.5
40°	9351.0	8245.3	5475.1	2811.0	2492.8	2462.2	2433.6	2411.2	2380.6	2366.3	2358.1
42.5°	9167.4	8061.7	5150.8	2605.0	2441.8	2411.2	2376.5	2339.8	2319.4	2307.1	2305.1
45°	8973.6	7839.4	4759.1	2484.6	2392.8	2356.1	2315.3	2274.5	2252.1	2245.9	2243.9
47.5°	8967.5	7729.2	4343.0	2388.7	2333.7	2296.9	2245.9	2205.1	2180.7	2172.5	2164.3
50°	9236.7	7841.4	3873.8	2305.1	2272.5	2233.7	2176.6	2131.7	2101.1	2090.9	2088.9
52.5°	9795.7	8263.7	3453.6	2221.5	2190.9	2146.0	2099.1	2054.2	2017.5	1999.1	1997.1
55°	10399.5	8800.2	3192.5	2135.8	2095.0	2056.2	2013.4	1964.4	1923.6	1895.1	1891.0
57.5°	11023.7	9385.6	3112.9	2027.7	1997.1	1970.6	1919.6	1866.5	1819.6	1793.1	1787.0
60°	11537.8	9889.5	3261.8	1913.4	1897.1	1862.4	1815.5	1764.5	1731.9	1711.5	1707.4
62.5°	9659.0	8051.5	2633.5	1789.0	1789.0	1752.3	1699.2	1662.5	1640.1	1625.8	1621.7
65°	6129.9	4985.5	1797.2	1664.6	1662.5	1613.6	1568.7	1544.2	1534.0	1511.6	1507.5
67.5°	2670.2	2278.6	1536.1	1538.1	1529.9	1476.9	1432.0	1413.7	1393.3	1368.8	1366.7
70°	1385.1	1411.6	1374.9	1397.3	1383.1	1319.8	1277.0	1248.4	1205.6	1181.1	1183.2
72.5°	1117.9	1146.4	1187.2	1221.9	1191.3	1140.3	1073.0	1038.3	983.2	956.7	958.8
75°	852.7	883.3	922.0	958.8	934.3	871.0	828.2	793.5	730.3	699.7	705.8
77.5°	587.5	603.8	650.7	648.7	640.5	622.2	558.9	518.1	452.9	416.1	420.2
80°	365.1	375.3	397.8	408.0	403.9	379.4	328.4	297.8	259.1	236.6	238.7
82.5°	220.3	226.4	246.8	248.9	246.8	228.5	189.7	167.3	142.8	130.6	130.6
85°	112.2	116.3	128.5	128.5	116.3	97.9	87.7	77.5	63.2	57.1	57.1
87.5°	30.6	30.6	38.8	32.6	26.5	24.5	12.2	10.2	4.1	2.0	2.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)