

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P385914

Luminaire Tested: **GWC-SA1C-730-U-SLL-HSS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P385914  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: GWC-SA1C-730-U-SLL-HSS  
Description: GALLEON WALL LUMINAIRE  
(1) 70 CRI, 3000K, 1050mA LIGHTSQUARE WITH 16 LEDS AND SPILL LIGHT  
ELIMINATOR LEFT OPTICS WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5100 lumens  
Efficiency: N/A  
Efficacy: 86.4 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type III - Medium  
BUG Rating: B1 - U0 - G1


Input Watts (W): 59  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P385914  
 CATALOG NUMBER: GWC-SA1C-730-U-SLL-HSS

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 22.2 fc  
 Type III - Medium - N/A

REPORT NUMBER: P385914  
CATALOG NUMBER: GWC-SA1C-730-U-SLL-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 75-Deg Lateral    - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P385914

CATALOG NUMBER: GWC-SA1C-730-U-SLL-HSS


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	765.3	0.0	765.3
	% Fixture	15.0	0.0	15.0
<b>Street Side</b>	Lumens	4334.7	0.0	4334.7
	% Fixture	85.0	0.0	85.0
<b>Total</b>	Lumens	5100.0	0.0	5100.0
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	129.8	2.5
10°-20°	255.5	5.0
20°-30°	361.5	7.1
30°-40°	531.5	10.4
40°-50°	764.0	15.0
50°-60°	1075.5	21.1
60°-70°	1256.1	24.6
70°-80°	640.8	12.6
80°-90°	85.1	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5100.0	100.0
0°-180°	5100.0	100.0

**Coefficient of Utilization**



REPORT NUMBER: P385914


CATALOG NUMBER: GWC-SA1C-730-U-SLL-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	546.7	10.7			
FM (30°-60°)	2007.3	39.4			
FH (60°-80°)	1698.2	33.3			G1/1800
FVH (80°-90°)	82.5	1.6			G1/100
BL (0°-30°)	200.1	3.9	B1/500		
BM (30°-60°)	363.8	7.1	B1/1000		
BH (60°-80°)	198.8	3.9	B1/500		G1/500
BVH (80°-90°)	2.6	0.1			G0/10
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B1-U0-G1**

Type III Medium





REPORT NUMBER: P385914

CATALOG NUMBER: GWC-SA1C-730-U-SLL-HSS

**CANDELA DISTRIBUTION (FULL):**

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	1711.0	1711.0	1711.0	1711.0	1711.0	1711.0	1711.0	1711.0	1711.0	1711.0	1711.0
2.5°	1854.7	1857.6	1872.6	1907.4	1945.3	1948.2	1973.8	1947.5	1938.5	1896.0	1852.1
5°	1868.7	1879.8	1931.3	2033.5	2122.2	2150.7	2171.0	2119.3	2064.9	1961.0	1850.1
7.5°	1755.9	1774.5	1855.4	2047.3	2205.7	2275.8	2289.1	2208.2	2075.0	1904.0	1737.3
10°	1611.4	1632.7	1730.3	1966.1	2183.8	2303.8	2322.2	2216.1	2024.8	1811.7	1615.3
12.5°	1494.5	1519.4	1619.2	1874.8	2108.1	2241.0	2277.3	2189.3	1981.3	1746.2	1531.9
15°	1440.6	1469.1	1574.0	1815.8	2024.3	2128.9	2158.9	2120.9	1957.1	1735.8	1512.6
17.5°	1471.5	1502.5	1610.7	1820.9	1945.5	1990.2	2014.4	2029.9	1957.1	1798.4	1569.1
20°	1598.4	1631.7	1746.2	1872.3	1880.3	1863.6	1889.5	1943.9	1979.9	1917.3	1704.9
22.5°	1773.8	1812.9	1942.2	1960.5	1848.4	1785.4	1788.8	1874.0	2021.2	2068.0	1893.4
25°	1987.6	2035.4	2166.8	2092.0	1861.7	1738.7	1737.5	1816.5	2061.5	2219.0	2103.3
27.5°	2199.9	2252.6	2368.1	2252.4	1916.6	1730.3	1727.9	1799.1	2100.9	2353.4	2332.6
30°	2378.0	2429.2	2528.8	2368.6	1975.7	1750.1	1738.5	1817.7	2124.3	2440.6	2499.8
32.5°	2523.0	2564.0	2644.5	2448.5	2039.0	1788.5	1763.4	1867.5	2164.2	2514.3	2653.4
35°	2682.4	2725.7	2757.8	2524.6	2110.1	1843.8	1807.8	1946.5	2225.6	2589.2	2821.8
37.5°	2864.3	2907.3	2903.5	2594.2	2200.2	1935.4	1912.5	2071.7	2321.0	2663.3	3009.8
40°	3042.4	3086.4	3054.9	2670.3	2306.0	2086.4	2069.5	2259.6	2448.8	2758.3	3230.1
42.5°	3209.1	3256.7	3189.5	2742.3	2432.1	2276.8	2305.8	2501.7	2608.7	2875.2	3420.0
45°	3343.4	3392.0	3302.3	2812.4	2565.0	2507.7	2595.0	2769.9	2801.0	2974.0	3548.3
47.5°	3441.0	3486.9	3380.6	2882.4	2735.1	2790.2	2942.1	3051.1	2974.7	3059.8	3639.4
50°	3503.3	3539.1	3403.6	2970.1	2958.3	3119.7	3303.8	3356.9	3138.3	3137.1	3750.0
52.5°	3543.0	3559.2	3420.5	3061.7	3191.2	3478.5	3658.0	3674.6	3306.7	3222.1	3899.1
55°	3679.5	3692.5	3540.3	3172.6	3383.8	3792.8	3978.3	3962.9	3497.3	3388.6	4075.0
57.5°	3912.4	3926.1	3787.9	3332.1	3539.6	3987.0	4210.5	4238.3	3720.8	3622.4	4263.4
60°	4029.3	4054.9	4005.6	3534.0	3690.6	4111.2	4368.7	4457.4	4000.1	3930.7	4446.0
62.5°	3923.2	3960.4	4031.9	3758.0	3840.6	4179.6	4418.0	4535.9	4286.1	4290.0	4558.6
65°	3711.6	3741.3	3862.6	3880.7	3927.6	4171.1	4296.3	4426.2	4461.3	4620.0	4552.6
67.5°	3456.0	3467.1	3570.0	3890.4	3801.5	3916.9	3930.5	4026.6	4322.8	4736.9	4369.7
70°	3088.0	3094.1	3184.0	3566.9	3266.8	3292.2	3272.1	3291.7	3716.4	4452.1	3908.0
72.5°	2485.3	2500.5	2628.3	2962.2	2379.9	2306.7	2464.3	2455.6	2862.2	3761.4	2902.5
75°	1829.8	1856.2	2049.2	2386.0	1670.4	1510.9	1625.9	1656.6	2034.7	2909.5	1815.1
77.5°	1281.2	1300.7	1487.7	1754.0	1208.9	1080.4	1038.9	1075.3	1343.0	2104.8	914.4
80°	738.1	745.3	864.7	1012.8	814.7	932.1	844.4	869.5	804.7	936.4	393.3
82.5°	482.9	484.2	530.8	602.8	507.3	589.5	436.3	557.8	495.0	376.2	128.0
85°	260.9	262.4	307.8	427.9	287.3	162.4	95.4	195.9	306.1	86.2	35.0
87.5°	28.7	26.3	92.8	155.6	79.7	14.7	5.1	22.0	49.0	5.6	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P385914  
 CATALOG NUMBER: GWC-SA1C-730-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1711.0	1711.0	1711.0	1711.0	1711.0	1711.0	1711.0	1711.0	1711.0	1711.0	1711.0
2.5°	1829.6	1809.5	1759.5	1706.6	1664.1	1624.2	1584.1	1535.1	1497.2	1489.4	1476.9
5°	1790.4	1726.9	1622.1	1516.7	1431.9	1324.9	1257.0	1204.1	1152.4	1149.3	1138.9
7.5°	1653.7	1570.1	1422.5	1276.8	1157.5	1055.5	952.6	883.7	829.6	810.5	799.2
10°	1522.3	1428.3	1244.0	1077.7	971.2	881.1	808.6	736.6	671.4	626.5	606.2
12.5°	1430.5	1326.6	1123.4	980.1	903.8	818.3	729.9	640.0	564.8	510.7	477.6
15°	1395.0	1284.1	1083.1	941.5	847.3	739.0	626.0	523.3	439.9	390.9	361.2
17.5°	1437.2	1308.2	1079.9	894.4	762.7	628.1	503.2	382.0	303.4	266.2	247.1
20°	1544.5	1385.1	1078.7	836.6	662.2	496.7	340.9	251.3	203.7	182.9	173.9
22.5°	1696.2	1483.1	1088.4	779.6	557.6	354.9	235.3	184.6	160.2	149.1	144.0
25°	1891.4	1620.8	1115.7	727.9	459.3	264.8	183.4	154.6	137.5	128.8	125.1
27.5°	2099.4	1779.3	1158.2	683.0	379.3	211.2	157.0	132.4	120.1	114.0	110.6
30°	2271.0	1962.9	1201.2	633.0	321.3	184.1	143.7	120.8	106.5	102.7	99.5
32.5°	2421.0	2101.9	1231.6	587.8	283.4	163.6	130.0	108.0	98.3	90.8	87.5
35°	2576.3	2217.6	1230.7	556.1	257.3	148.1	118.4	96.6	85.0	76.3	73.7
37.5°	2744.5	2348.3	1209.7	529.1	245.9	135.8	111.9	90.6	79.0	70.3	66.9
40°	2941.4	2485.5	1188.2	503.7	242.8	125.9	107.3	85.8	73.4	65.0	61.6
42.5°	3133.2	2609.2	1169.3	484.9	229.3	125.6	103.2	82.1	69.1	60.9	57.0
45°	3286.6	2724.4	1165.7	473.5	215.0	130.0	101.0	79.7	65.7	57.5	53.9
47.5°	3414.2	2849.6	1188.9	465.6	201.5	118.6	106.3	78.0	62.6	54.6	50.5
50°	3565.9	3003.2	1243.5	452.5	187.2	106.8	121.8	78.5	59.9	51.7	47.4
52.5°	3777.6	3215.8	1323.7	430.5	167.7	95.9	119.8	79.0	57.0	48.6	44.2
55°	4014.8	3481.4	1409.9	394.0	140.4	81.7	102.7	75.6	51.5	45.2	41.1
57.5°	4264.1	3722.2	1461.2	350.6	111.6	70.5	82.1	68.9	45.4	40.6	37.9
60°	4303.3	3813.8	1437.7	297.2	88.7	61.4	60.9	70.1	40.6	35.8	33.8
62.5°	4205.9	3698.8	1324.4	249.6	74.2	53.9	50.0	61.1	36.7	31.9	30.0
65°	4018.7	3387.9	1140.8	224.9	68.9	46.1	41.6	43.0	32.1	27.8	26.1
67.5°	3758.2	2972.8	936.7	210.9	68.1	39.6	35.5	32.6	27.8	24.2	22.7
70°	3225.8	2476.6	747.2	203.2	66.2	33.3	30.0	26.6	23.2	20.5	19.3
72.5°	2374.1	1754.9	581.3	194.7	66.7	26.6	26.1	22.0	18.6	15.9	15.5
75°	1371.8	1002.6	381.2	157.8	63.5	20.5	21.7	15.5	13.0	11.1	11.1
77.5°	731.1	611.5	145.2	65.7	23.2	13.0	12.3	9.2	8.2	6.8	6.5
80°	318.7	269.1	43.7	18.4	12.8	7.0	4.6	4.1	3.6	2.9	2.7
82.5°	112.8	97.4	14.3	8.9	5.6	0.0	0.0	0.0	0.0	0.0	0.0
85°	25.6	18.4	0.0	2.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P385914  
 CATALOG NUMBER: GWC-SA1C-730-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	1711.0	1711.0	1711.0	1711.0	1711.0	1711.0	1711.0	1711.0	1711.0	1711.0	1711.0
2.5°	1451.3	1445.9	1414.5	1415.7	1421.3	1429.3	1410.4	1419.1	1442.6	1465.0	1473.5
5°	1122.2	1123.4	1104.3	1116.2	1126.8	1134.0	1103.6	1104.1	1122.7	1148.1	1161.3
7.5°	790.7	788.8	789.8	818.0	838.1	823.6	834.9	795.6	798.0	816.1	802.6
10°	587.8	561.2	546.2	567.5	589.5	581.5	561.9	549.1	558.1	578.1	576.7
12.5°	461.9	423.8	401.3	386.1	404.2	389.2	388.7	377.6	365.5	367.7	399.8
15°	347.4	319.6	293.1	268.7	268.2	263.1	237.2	208.3	205.8	207.3	224.0
17.5°	238.9	229.5	218.6	197.6	192.1	170.8	145.7	134.1	128.3	130.9	136.5
20°	167.9	164.3	165.5	154.1	146.2	125.9	111.1	106.5	105.6	108.2	110.9
22.5°	139.2	132.6	131.9	126.8	118.9	104.1	96.2	93.5	92.3	94.7	96.6
25°	121.8	115.2	112.6	109.4	101.0	90.8	86.0	83.6	82.4	83.8	85.0
27.5°	107.3	101.2	98.8	96.6	88.4	81.2	77.3	75.1	74.2	74.7	75.9
30°	96.4	91.1	87.9	85.3	78.3	73.2	69.8	67.6	66.7	66.7	67.9
32.5°	85.0	82.1	79.2	75.9	69.3	66.0	62.6	60.2	59.2	59.4	60.4
35°	70.8	69.8	70.5	67.4	61.8	58.9	55.6	52.9	52.2	52.4	53.4
37.5°	62.8	58.5	61.1	59.4	56.3	52.4	48.1	45.7	44.5	45.2	45.7
40°	57.7	52.4	50.5	52.2	51.7	45.4	41.6	39.1	38.2	38.4	38.9
42.5°	53.4	47.1	42.8	42.5	45.4	39.6	35.5	33.3	32.1	32.1	32.6
45°	49.3	42.5	37.2	33.1	38.2	33.6	29.7	27.8	26.3	26.3	26.6
47.5°	46.1	38.7	32.4	27.1	28.7	27.5	24.4	22.5	21.0	21.0	21.3
50°	43.2	34.8	28.0	22.7	21.5	22.7	19.8	17.6	16.7	16.4	16.9
52.5°	40.1	30.9	23.9	19.3	16.9	17.2	15.5	14.0	12.8	12.8	13.3
55°	37.0	27.8	20.8	16.4	14.0	12.8	12.3	11.4	10.4	10.4	10.9
57.5°	33.8	24.4	17.6	13.5	11.1	10.1	10.1	9.4	8.7	8.7	9.2
60°	30.9	21.0	14.5	11.1	8.7	8.5	8.7	8.0	7.5	7.5	8.0
62.5°	27.5	17.9	11.8	9.2	7.0	6.8	7.5	7.0	6.5	6.5	7.0
65°	23.4	15.2	9.4	7.0	5.3	5.3	6.3	5.8	5.3	5.3	5.8
67.5°	19.8	12.8	7.2	5.1	3.9	4.1	5.3	4.8	4.6	4.6	5.1
70°	16.4	9.9	5.1	3.1	2.2	3.1	4.1	4.1	4.1	4.1	4.6
72.5°	12.3	6.8	2.9	1.2	1.0	2.2	3.4	3.9	3.6	3.6	4.3
75°	8.0	3.9	1.0	0.0	0.0	1.2	2.7	3.1	3.1	2.9	3.6
77.5°	4.6	1.2	0.0	0.0	0.0	0.0	1.7	1.4	1.2	1.0	1.7
80°	1.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P385914  
 CATALOG NUMBER: GWC-SA1C-730-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	1711.0	1711.0	1711.0	1711.0	1711.0	1711.0	1711.0	1711.0	1711.0	1711.0
2.5°	1507.5	1536.0	1576.2	1618.7	1684.1	1736.1	1787.1	1830.8	1847.7	1854.7
5°	1193.2	1235.0	1293.7	1369.1	1487.2	1593.5	1701.3	1809.8	1856.9	1868.7
7.5°	856.2	909.6	984.3	1078.7	1217.1	1354.9	1505.4	1664.6	1737.5	1755.9
10°	633.7	698.9	784.5	884.0	1016.1	1157.7	1321.8	1503.7	1587.0	1611.4
12.5°	449.6	537.8	652.3	773.3	887.9	1014.2	1180.2	1380.7	1468.2	1494.5
15°	264.1	349.3	484.9	647.0	793.6	921.7	1090.3	1317.6	1414.0	1440.6
17.5°	151.5	194.0	296.4	477.1	676.2	853.5	1062.0	1333.4	1446.9	1471.5
20°	115.7	129.3	170.8	307.3	539.0	786.6	1062.0	1422.3	1562.1	1598.4
22.5°	101.2	111.1	128.0	183.4	396.7	714.9	1074.4	1550.8	1733.7	1773.8
25°	89.9	98.8	113.3	137.9	270.6	629.6	1103.6	1708.5	1935.6	1987.6
27.5°	80.5	88.9	102.0	120.8	185.1	526.7	1143.0	1893.6	2158.4	2199.9
30°	72.0	80.0	91.8	105.1	142.8	410.0	1176.6	2068.0	2333.3	2378.0
32.5°	64.0	71.3	81.9	91.8	116.9	303.2	1180.2	2206.2	2478.5	2523.0
35°	56.5	63.1	72.7	80.5	96.9	239.4	1123.9	2326.1	2623.7	2682.4
37.5°	49.3	55.6	64.0	69.8	85.3	195.2	1037.9	2459.7	2810.0	2864.3
40°	42.5	48.1	56.8	60.6	80.7	150.0	944.4	2599.8	2992.6	3042.4
42.5°	36.2	41.6	50.0	57.5	70.8	112.1	843.4	2731.2	3156.9	3209.1
45°	30.2	35.8	44.2	60.9	58.7	83.8	735.4	2818.4	3286.6	3343.4
47.5°	24.4	30.7	42.3	58.0	46.9	61.6	649.9	2901.1	3385.0	3441.0
50°	19.6	25.9	47.6	51.7	38.4	47.1	614.1	2975.0	3449.5	3503.3
52.5°	15.9	21.7	44.9	39.6	32.1	38.9	633.5	3094.8	3509.1	3543.0
55°	13.3	17.2	27.1	27.5	27.3	33.1	657.4	3266.8	3663.5	3679.5
57.5°	11.6	13.8	18.8	21.3	23.0	29.5	657.9	3513.7	3902.5	3912.4
60°	9.9	12.1	15.7	17.2	19.8	26.3	633.9	3600.0	3996.4	4029.3
62.5°	8.7	10.6	13.0	14.3	16.7	23.7	577.9	3475.1	3867.4	3923.2
65°	7.7	9.7	10.9	12.1	14.7	21.3	485.6	3225.3	3653.4	3711.6
67.5°	6.8	8.5	9.7	10.9	13.3	18.8	357.6	2935.1	3407.7	3456.0
70°	6.0	7.5	8.7	9.7	11.6	15.9	217.0	2490.6	3068.0	3088.0
72.5°	5.8	6.8	8.0	8.7	10.1	14.0	109.9	1830.3	2452.7	2485.3
75°	5.1	6.0	7.2	7.7	8.9	12.1	44.7	1202.2	1777.4	1829.8
77.5°	4.1	5.6	6.5	7.0	7.7	9.9	22.7	768.3	1247.3	1281.2
80°	1.4	4.1	5.6	5.8	6.5	7.2	15.0	420.6	723.6	738.1
82.5°	0.0	2.7	4.3	4.1	4.6	5.6	9.7	200.0	477.6	482.9
85°	0.0	1.2	3.4	2.7	1.9	3.9	3.4	43.7	250.5	260.9
87.5°	0.0	0.0	0.2	1.2	1.0	1.4	0.5	0.2	22.7	28.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245982

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



--- HS    — SS

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



u



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)