

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P387064

Luminaire Tested: **GWC-SA2D-735-U-SLR-HSS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P387064  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-28)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: GWC-SA2D-735-U-SLR-HSS  
Description: GALLEON WALL LUMINAIRE  
(2) 70 CRI, 3500K, 1200mA LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT  
ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11276.5 lumens  
Efficiency: N/A  
Efficacy: 87.4 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')  
IES Classification: Type IV - Medium  
BUG Rating: B1 - U0 - G2


Input Watts (W): 129  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P387064  
 CATALOG NUMBER: GWC-SA2D-735-U-SLR-HSS

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 9.2 fc  
 Type IV - Medium - N/A

REPORT NUMBER: P387064  
CATALOG NUMBER: GWC-SA2D-735-U-SLR-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 345-Deg Lateral    - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P387064

CATALOG NUMBER: GWC-SA2D-735-U-SLR-HSS


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1364.8	0.0	1364.8
	% Fixture	12.1	0.0	12.1
<b>Street Side</b>	Lumens	9911.7	0.0	9911.7
	% Fixture	87.9	0.0	87.9
<b>Total</b>	Lumens	11276.5	0.0	11276.5
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	281.9	2.5
10°-20°	561.2	5.0
20°-30°	796.8	7.1
30°-40°	1177.0	10.4
40°-50°	1697.5	15.1
50°-60°	2382.9	21.1
60°-70°	2777.8	24.6
70°-80°	1420.1	12.6
80°-90°	181.4	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	11276.5	100.0
0°-180°	11276.5	100.0

**Coefficient of Utilization**




REPORT NUMBER: P387064

CATALOG NUMBER: GWC-SA2D-735-U-SLR-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1236.8	11.0			
FM (30°-60°)	4639.3	41.1			
FH (60°-80°)	3865.2	34.3			G2/5000
FVH (80°-90°)	170.3	1.5			G2/225
BL (0°-30°)	403.1	3.6	B1/500		
BM (30°-60°)	618.0	5.5	B1/1000		
BH (60°-80°)	332.7	2.9	B1/500		G1/500
BVH (80°-90°)	11.0	0.1			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B1-U0-G2**  
 Type IV Medium





REPORT NUMBER: P387064

CATALOG NUMBER: GWC-SA2D-735-U-SLR-HSS

**CANDELA DISTRIBUTION (FULL):**

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3
2.5°	4022.1	3991.1	3957.0	3845.3	3741.7	3623.1	3526.4	3459.0	3374.7	3265.1	3237.3
5°	3993.3	3960.2	3852.8	3604.4	3387.0	3175.4	2971.3	2851.6	2703.1	2552.5	2515.1
7.5°	3703.2	3668.5	3513.5	3173.3	2880.6	2575.0	2310.0	2146.0	1978.2	1840.4	1767.2
10°	3401.4	3363.4	3189.3	2776.4	2415.7	2139.6	1945.1	1788.6	1629.9	1482.5	1364.9
12.5°	3193.6	3143.9	2954.8	2486.8	2172.6	1985.1	1803.5	1616.0	1401.3	1243.1	1113.8
15°	3106.5	3049.8	2850.0	2375.2	2086.7	1866.6	1629.9	1399.7	1148.0	966.9	848.4
17.5°	3173.8	3100.1	2885.8	2367.6	1978.7	1679.1	1379.9	1109.6	836.6	653.3	568.9
20°	3402.5	3305.7	3033.9	2365.5	1847.9	1456.2	1077.0	771.4	551.3	443.4	399.1
22.5°	3762.6	3634.8	3246.5	2382.6	1712.7	1222.3	777.8	524.1	414.0	357.9	331.8
25°	4197.4	4049.4	3552.6	2443.0	1594.2	994.7	565.2	414.0	349.4	308.2	286.3
27.5°	4610.8	4490.7	3939.3	2530.1	1502.2	811.0	458.9	351.0	298.6	271.4	253.7
30°	5023.8	4872.6	4336.2	2633.7	1391.6	686.5	403.4	320.0	267.6	238.8	227.6
32.5°	5324.0	5198.5	4647.2	2708.5	1273.5	605.3	360.6	292.7	250.0	220.7	204.0
35°	5677.1	5535.0	4913.8	2725.1	1197.7	554.0	324.3	263.4	216.9	190.7	173.1
37.5°	6058.6	5881.7	5221.4	2688.7	1138.5	528.9	297.0	250.0	202.4	175.8	157.1
40°	6480.6	6280.8	5516.9	2636.4	1080.2	520.3	276.2	239.8	191.3	164.0	144.8
42.5°	6925.1	6689.5	5772.8	2581.4	1043.3	490.9	274.0	229.7	182.7	153.3	134.1
45°	7298.5	7059.7	6035.6	2563.2	1017.2	458.9	283.1	222.7	176.8	144.8	126.1
47.5°	7596.0	7370.1	6304.8	2603.8	1002.2	429.5	258.1	231.8	173.6	137.3	119.1
50°	7951.3	7695.4	6684.2	2725.1	980.3	400.1	233.4	265.5	173.6	132.5	113.3
52.5°	8396.9	8143.6	7107.3	2913.1	936.5	359.5	210.0	266.0	175.2	126.1	105.8
55°	8957.2	8773.5	7711.5	3119.4	866.5	299.7	181.7	228.6	168.8	114.3	98.8
57.5°	9494.6	9344.5	8262.3	3260.4	773.0	234.0	158.1	184.3	154.4	100.4	88.1
59°	9641.6	9477.5	8464.2	3266.7	703.0	204.0	146.4	152.3	151.1	94.0	81.7
60°	9641.6	9467.4	8522.4	3232.5	652.3	187.5	138.9	135.6	157.6	89.7	78.0
62.5°	9466.9	9222.2	8333.3	3001.3	532.1	159.7	121.3	112.2	141.6	80.7	69.0
65°	9103.7	8747.4	7689.0	2583.0	474.4	146.4	104.7	91.9	98.3	71.0	60.4
67.5°	8497.9	8014.9	6760.0	2086.7	451.4	142.6	90.3	78.0	74.2	60.9	52.9
70°	7431.0	6895.2	5632.3	1640.6	431.7	141.0	75.9	65.7	59.8	51.3	44.9
72.5°	5408.5	4849.6	3998.6	1282.6	419.9	144.2	60.9	55.0	49.1	40.1	34.8
75°	3093.7	2727.7	2247.5	847.2	357.9	137.8	47.0	45.9	35.2	28.8	24.0
77.5°	1598.4	1549.8	1346.8	325.3	171.4	60.4	31.0	26.7	20.9	17.7	14.5
80°	689.7	682.2	590.3	94.0	45.4	33.6	17.7	11.2	9.6	7.5	5.9
82.5°	238.2	238.2	210.0	31.6	20.3	16.5	2.2	0.0	0.0	0.0	0.0
85°	48.1	53.9	38.0	0.0	7.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P387064

CATALOG NUMBER: GWC-SA2D-735-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3
2.5°	3203.7	3139.1	3134.8	3094.2	3043.4	3020.4	3007.1	3030.7	3059.5	3062.7	3105.9
5°	2486.8	2418.9	2447.2	2375.2	2389.5	2375.2	2351.7	2355.9	2368.8	2328.7	2378.4
7.5°	1746.3	1695.0	1727.6	1708.5	1734.1	1744.3	1729.8	1708.5	1645.4	1637.9	1681.2
10°	1316.3	1258.1	1223.4	1187.0	1195.0	1211.6	1206.3	1190.8	1150.7	1152.8	1194.5
12.5°	1057.8	992.6	923.7	834.5	812.6	824.9	812.6	803.5	765.0	768.2	805.1
15°	802.4	749.0	676.8	605.3	566.3	570.0	535.8	511.8	487.7	458.9	481.3
17.5°	541.7	509.2	487.7	466.4	419.9	409.2	365.9	319.5	301.3	287.9	297.6
20°	383.6	365.9	357.4	356.3	329.6	316.3	274.0	245.2	236.2	233.4	239.4
22.5°	320.5	307.7	295.4	288.5	275.1	259.6	227.6	213.1	206.8	203.6	207.8
25°	278.9	269.2	256.5	244.7	239.4	222.7	199.8	189.1	184.9	181.7	183.7
27.5°	247.9	239.4	224.3	216.9	212.6	198.2	178.4	169.8	166.2	165.1	164.6
30°	223.3	215.3	201.4	192.9	185.3	172.6	160.8	152.3	148.5	147.5	146.4
32.5°	198.8	192.3	183.3	174.7	166.6	154.9	144.8	137.8	132.0	130.9	130.4
35°	167.8	161.3	156.5	156.0	148.5	137.3	129.8	120.7	115.9	114.3	114.9
37.5°	149.1	140.5	129.8	133.6	131.4	123.4	113.3	104.2	99.4	98.3	98.3
40°	137.3	128.2	115.9	109.5	115.9	114.3	98.3	89.2	84.5	83.9	82.8
42.5°	126.1	117.0	103.1	92.4	95.6	100.4	84.9	76.4	71.6	70.5	69.0
45°	118.1	108.4	93.0	80.7	74.2	84.5	72.6	62.0	59.3	57.1	56.1
47.5°	110.6	101.5	83.9	70.0	59.3	60.9	58.2	50.7	47.5	45.4	44.9
50°	104.2	94.6	75.9	59.8	49.1	44.9	47.0	40.1	37.4	35.2	34.2
52.5°	96.7	87.6	67.4	51.9	41.1	35.2	35.8	31.6	28.8	27.2	26.7
55°	90.8	81.7	60.4	45.4	36.4	28.8	25.6	24.6	23.0	21.9	21.3
57.5°	82.8	74.2	53.5	38.4	31.0	23.5	19.7	19.7	19.3	18.1	17.7
59°	78.0	70.5	49.1	34.8	28.3	20.3	17.7	18.1	17.7	16.5	16.1
60°	74.2	67.4	45.9	32.0	26.7	18.7	16.1	17.1	16.5	15.5	14.9
62.5°	65.7	60.9	39.5	26.7	23.5	14.9	13.3	14.5	14.5	13.9	13.3
65°	57.7	52.3	33.6	22.5	21.9	12.8	10.7	12.8	13.3	12.3	11.2
67.5°	50.3	44.9	29.4	18.1	20.3	10.1	8.0	10.7	14.5	11.2	10.1
70°	42.7	37.4	23.0	14.5	21.3	7.0	6.4	9.6	17.1	12.3	9.6
72.5°	33.2	28.8	16.1	10.7	23.0	4.8	4.8	8.0	19.3	13.3	9.1
75°	23.0	18.7	9.6	6.4	18.7	3.2	3.2	7.5	18.1	12.3	8.5
77.5°	13.3	10.1	3.2	0.6	9.6	0.0	0.6	5.4	12.8	7.5	3.8
80°	4.8	2.2	0.0	0.0	5.9	0.0	0.0	0.0	1.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P387064  
 CATALOG NUMBER: GWC-SA2D-735-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3
2.5°	3117.2	3189.3	3254.0	3351.7	3467.6	3601.2	3716.1	3839.4	3955.3	4003.4	4036.6
5°	2388.5	2477.7	2581.9	2725.6	2916.8	3152.4	3373.1	3622.6	3890.7	4024.8	4150.9
7.5°	1688.7	1779.5	1908.8	2061.6	2292.9	2573.4	2861.8	3206.3	3569.7	3781.7	3990.6
10°	1214.3	1326.0	1446.7	1655.6	1890.6	2156.7	2453.7	2838.3	3243.3	3478.3	3730.0
12.5°	826.5	953.6	1136.3	1370.3	1646.5	1907.2	2165.2	2532.2	3002.3	3235.3	3505.0
15°	495.7	566.3	759.7	1030.5	1369.2	1694.0	1976.6	2344.7	2845.8	3131.1	3411.5
17.5°	305.6	338.2	443.4	665.7	1021.4	1432.2	1819.5	2281.1	2868.3	3215.5	3515.7
20°	243.6	256.5	290.1	393.2	676.8	1143.8	1642.7	2268.3	3051.4	3478.9	3801.0
22.5°	211.6	223.9	246.3	285.8	425.7	856.4	1474.9	2280.0	3314.3	3873.6	4249.7
25°	186.5	197.1	218.5	251.1	312.0	603.1	1295.5	2332.4	3656.8	4363.5	4763.1
27.5°	166.6	175.8	195.5	225.5	267.6	420.9	1092.0	2396.0	4062.8	4864.6	5258.8
30°	148.5	156.5	174.2	202.0	232.4	323.7	868.7	2439.2	4469.3	5258.8	5613.1
32.5°	133.0	138.9	154.9	178.4	202.0	258.1	660.3	2432.3	4771.1	5586.9	5867.8
35°	117.0	122.9	136.8	157.1	175.8	213.1	519.3	2302.5	5033.9	5927.2	6159.5
37.5°	99.4	106.8	120.2	138.4	151.1	187.5	419.9	2146.0	5300.5	6316.1	6484.9
40°	84.5	91.9	103.6	123.4	131.4	177.9	322.7	1955.3	5600.2	6751.0	6841.8
42.5°	70.0	76.9	89.2	106.3	123.9	153.3	238.8	1737.3	5888.2	7122.8	7167.1
45°	56.6	63.6	76.4	93.5	132.5	127.1	184.9	1503.8	6120.5	7432.1	7446.5
47.5°	44.9	51.3	64.6	88.1	123.4	101.5	132.0	1320.6	6315.5	7673.5	7635.6
50°	34.8	40.1	53.9	101.0	107.9	83.9	99.9	1259.7	6490.3	7823.1	7724.8
52.5°	27.2	32.0	44.3	94.6	83.9	69.4	83.9	1316.8	6729.5	7947.1	7775.0
55°	21.9	26.7	34.8	53.9	57.1	58.8	71.6	1370.3	7142.5	8237.6	8071.6
57.5°	18.1	23.0	28.3	38.0	43.3	49.7	63.6	1376.1	7629.2	8720.6	8563.5
59°	16.5	20.9	25.6	33.6	38.0	45.4	59.8	1344.1	7800.6	8896.3	8817.8
60°	15.5	19.7	24.0	31.0	35.2	42.7	57.7	1313.6	7808.1	8890.0	8926.3
62.5°	13.3	17.7	21.3	26.2	29.9	36.4	51.9	1200.9	7491.9	8598.8	8861.1
65°	11.7	15.5	19.3	22.5	25.6	32.6	47.0	995.3	6951.8	8129.2	8415.0
67.5°	10.7	13.3	17.7	19.7	23.0	28.8	41.7	709.4	6277.1	7554.9	7740.3
70°	9.6	12.8	16.1	18.1	20.9	25.1	35.8	407.6	5300.5	6714.0	6846.0
72.5°	9.1	12.3	14.5	17.1	18.7	22.5	32.6	191.8	3881.1	5378.5	5723.1
75°	8.0	11.2	13.3	16.1	17.7	20.3	27.8	91.9	2581.4	3892.3	4283.9
77.5°	4.8	9.1	12.3	14.5	15.5	17.7	23.0	52.9	1647.5	2694.1	3173.3
80°	0.0	3.2	9.1	12.3	13.3	14.9	17.7	41.7	881.4	1539.1	1847.3
82.5°	0.0	0.0	6.4	9.6	9.1	10.1	13.3	26.2	397.5	1005.9	1133.7
85°	0.0	0.0	2.2	7.5	6.4	4.8	9.1	9.1	87.1	509.2	635.2
87.5°	0.0	0.0	0.0	0.6	3.2	2.2	3.8	1.0	0.6	38.0	153.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P387064

CATALOG NUMBER: GWC-SA2D-735-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3
2.5°	4152.5	4192.0	4258.8	4290.3	4274.8	4209.1	4130.6	4050.5	4003.4	4022.1
5°	4407.8	4611.4	4728.9	4767.9	4702.7	4555.3	4362.5	4108.2	4017.9	3993.3
7.5°	4407.8	4790.9	5033.5	5076.1	4930.9	4641.8	4280.2	3883.3	3751.3	3703.2
10°	4252.9	4774.3	5112.5	5180.3	4977.3	4545.2	4060.6	3607.6	3451.1	3401.4
12.5°	4078.2	4639.7	4996.0	5089.5	4922.8	4449.0	3908.3	3421.2	3236.9	3193.6
15°	3970.8	4474.1	4769.0	4836.8	4766.3	4392.9	3872.0	3365.0	3148.2	3106.5
17.5°	4009.3	4345.9	4452.2	4491.7	4539.2	4373.2	3970.8	3487.9	3213.3	3173.8
20°	4154.1	4210.7	4155.7	4205.4	4333.6	4392.3	4206.4	3784.9	3455.4	3402.5
22.5°	4399.8	4140.8	3986.3	4006.1	4162.1	4455.9	4566.5	4209.1	3828.8	3762.6
25°	4686.2	4197.4	3892.3	3874.7	4035.0	4539.8	4895.6	4670.7	4270.6	4197.4
27.5°	5046.2	4324.5	3873.1	3855.5	3990.6	4618.3	5169.1	5126.9	4735.9	4610.8
30°	5324.0	4449.5	3930.2	3889.7	4035.0	4672.8	5388.6	5514.2	5106.6	5023.8
32.5°	5523.3	4596.9	4023.2	3964.4	4160.0	4766.9	5558.0	5869.0	5449.6	5324.0
35°	5675.0	4757.2	4173.4	4076.6	4332.0	4909.5	5716.7	6246.6	5814.5	5677.1
37.5°	5817.1	4982.2	4407.8	4292.5	4601.8	5139.2	5884.5	6675.1	6222.5	6058.6
40°	6015.3	5236.9	4769.5	4666.9	5055.3	5452.2	6093.8	7121.6	6686.8	6480.6
42.5°	6213.5	5510.5	5139.7	5167.5	5621.1	5832.6	6364.1	7594.0	7145.2	6925.1
45°	6394.6	5792.6	5667.0	5795.2	6146.2	6249.9	6632.9	7867.0	7511.1	7298.5
47.5°	6555.9	6145.1	6191.1	6532.5	6743.4	6627.5	6833.7	8102.6	7783.5	7596.0
50°	6743.4	6601.3	6881.8	7364.8	7431.0	6969.5	7016.4	8381.4	8102.0	7951.3
52.5°	6948.6	7082.2	7646.9	8072.6	8051.3	7340.7	7200.2	8693.9	8538.4	8396.9
55°	7181.5	7470.5	8320.5	8735.0	8716.8	7755.3	7504.7	9080.1	9085.4	8957.2
57.5°	7527.2	7805.0	8777.8	9270.9	9301.3	8233.9	8020.7	9512.9	9580.1	9494.6
59°	7775.0	8021.9	8958.9	9494.6	9618.6	8604.1	8397.9	9764.0	9719.6	9641.6
60°	7958.8	8159.7	9048.6	9611.7	9803.0	8855.2	8676.2	9911.4	9736.2	9641.6
62.5°	8413.4	8459.9	9210.5	9744.1	10015.0	9412.9	9459.4	10162.5	9621.3	9466.9
65°	8625.5	8649.6	9208.3	9506.9	9809.9	9847.3	10170.0	10170.0	9340.9	9103.7
67.5°	8536.8	8420.9	8751.6	8720.6	9023.0	9589.2	10437.0	9797.0	8804.5	8497.9
70°	7815.7	7369.5	7222.6	7236.0	7467.3	8340.8	9908.2	8699.7	7789.5	7431.0
72.5°	6503.0	5433.0	5070.3	5484.3	5544.7	6410.1	8443.8	6551.7	5744.5	5408.5
75°	5230.5	3829.8	3240.1	3677.1	3779.6	4691.0	6531.9	4080.4	3355.4	3093.7
77.5°	3757.7	2749.1	2324.9	2294.5	2426.9	2975.1	4634.9	2053.5	1712.7	1598.4
80°	2134.8	1809.4	1948.3	1838.2	1905.0	1860.2	2202.0	900.7	737.8	689.7
82.5°	1288.6	1069.5	1158.2	964.3	1220.2	1062.5	848.4	288.5	250.5	238.2
85°	838.2	584.4	304.6	204.0	420.5	679.0	189.7	78.5	60.4	48.1
87.5°	289.1	149.1	14.9	6.4	44.9	126.6	7.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245982

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



--- HS — SS

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



u



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)