

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P386615

Luminaire Tested: **GWC-SA2B-735-U-SLL**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P386615
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-26)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GWC-SA2B-735-U-SLL
Description: GALLEON WALL LUMINAIRE
(2) 70 CRI, 3500K, 800mA LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT
ELIMINATOR LEFT OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9845.8 lumens
Efficiency: N/A
Efficacy: 114.5 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B1 - U0 - G3


Input Watts (W): 86
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P386615
 CATALOG NUMBER: GWC-SA2B-735-U-SLL

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 37.7 fc
 Type III - Medium - N/A

REPORT NUMBER: P386615
CATALOG NUMBER: GWC-SA2B-735-U-SLL

Luminous Intensity Polar Plot



— Vertical Plane Through 75-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical



REPORT NUMBER: P386615

CATALOG NUMBER: GWC-SA2B-735-U-SLL


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 1734.1 | 0.0 | 1734.1 |
| | % Fixture | 17.6 | 0.0 | 17.6 |
| Street Side | Lumens | 8111.7 | 0.0 | 8111.7 |
| | % Fixture | 82.4 | 0.0 | 82.4 |
| Total | Lumens | 9845.8 | 0.0 | 9845.8 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 231.5 | 2.4 |
| 10°-20° | 480.9 | 4.9 |
| 20°-30° | 684.0 | 6.9 |
| 30°-40° | 985.6 | 10.0 |
| 40°-50° | 1389.0 | 14.1 |
| 50°-60° | 1930.9 | 19.6 |
| 60°-70° | 2335.1 | 23.7 |
| 70°-80° | 1435.3 | 14.6 |
| 80°-90° | 373.5 | 3.8 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 9845.8 | 100.0 |
| 0°-180° | 9845.8 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P386615


CATALOG NUMBER: GWC-SA2B-735-U-SLL

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 977.6 | 9.9 | | | |
| FM (30°-60°) | 3518.4 | 35.7 | | | |
| FH (60°-80°) | 3284.2 | 33.4 | | | G2/5000 |
| FVH (80°-90°) | 331.5 | 3.4 | | | G3/500 |
| BL (0°-30°) | 418.8 | 4.3 | B1/500 | | |
| BM (30°-60°) | 787.1 | 8.0 | B1/1000 | | |
| BH (60°-80°) | 486.2 | 4.9 | B1/500 | | G1/500 |
| BVH (80°-90°) | 42.0 | 0.4 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G3

Type III Medium





REPORT NUMBER: P386615

CATALOG NUMBER: GWC-SA2B-735-U-SLL

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 10° | 15° | 20° | 25° | 30° | 35° | 40° | 45° | 50° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 |
| 2.5° | 3197.1 | 3239.3 | 3268.4 | 3297.2 | 3319.6 | 3341.6 | 3373.9 | 3406.2 | 3412.5 | 3418.4 | 3405.8 |
| 5° | 3178.3 | 3281.0 | 3368.4 | 3455.4 | 3536.1 | 3616.8 | 3665.2 | 3713.6 | 3723.5 | 3733.3 | 3703.0 |
| 7.5° | 2974.8 | 3126.3 | 3277.8 | 3429.4 | 3568.4 | 3707.3 | 3792.0 | 3876.2 | 3895.5 | 3914.4 | 3864.8 |
| 10° | 2743.3 | 2919.6 | 3105.8 | 3292.0 | 3475.1 | 3658.1 | 3780.6 | 3903.0 | 3927.4 | 3951.7 | 3890.0 |
| 12.5° | 2567.4 | 2759.8 | 2958.6 | 3157.4 | 3350.7 | 3543.6 | 3670.3 | 3797.1 | 3827.4 | 3857.7 | 3812.8 |
| 15° | 2499.6 | 2710.6 | 2897.7 | 3084.6 | 3253.0 | 3421.2 | 3525.1 | 3628.6 | 3641.2 | 3653.4 | 3646.4 |
| 17.5° | 2567.4 | 2800.0 | 2969.2 | 3138.1 | 3229.8 | 3321.1 | 3362.9 | 3404.3 | 3418.0 | 3431.4 | 3449.5 |
| 20° | 2765.4 | 3016.5 | 3135.8 | 3254.6 | 3250.7 | 3246.4 | 3226.3 | 3205.9 | 3202.3 | 3198.7 | 3249.9 |
| 22.5° | 3048.0 | 3339.6 | 3387.3 | 3434.5 | 3324.0 | 3213.3 | 3146.0 | 3078.3 | 3064.9 | 3051.2 | 3105.4 |
| 25° | 3379.8 | 3690.4 | 3681.8 | 3672.7 | 3462.1 | 3251.1 | 3122.7 | 2994.4 | 2979.5 | 2964.5 | 3010.9 |
| 27.5° | 3740.8 | 4037.6 | 3981.0 | 3924.2 | 3638.1 | 3351.9 | 3165.7 | 2979.5 | 2964.5 | 2949.6 | 2990.5 |
| 30° | 4023.0 | 4292.3 | 4201.3 | 4110.4 | 3786.4 | 3462.5 | 3241.3 | 3020.1 | 2995.6 | 2970.8 | 3021.2 |
| 32.5° | 4261.9 | 4491.1 | 4369.0 | 4247.0 | 3906.9 | 3566.8 | 3327.4 | 3088.2 | 3049.9 | 3011.8 | 3079.1 |
| 35° | 4510.8 | 4689.5 | 4517.8 | 4345.8 | 4014.4 | 3682.5 | 3429.4 | 3175.9 | 3129.0 | 3082.2 | 3174.8 |
| 37.5° | 4790.6 | 4939.1 | 4692.6 | 4445.8 | 4135.2 | 3824.6 | 3582.2 | 3339.3 | 3291.3 | 3243.3 | 3361.3 |
| 40° | 5086.3 | 5209.9 | 4881.2 | 4552.5 | 4267.5 | 3982.5 | 3793.6 | 3604.2 | 3558.5 | 3512.5 | 3655.7 |
| 42.5° | 5344.9 | 5435.1 | 5056.8 | 4678.5 | 4426.9 | 4174.9 | 4041.9 | 3908.4 | 3908.1 | 3907.3 | 4052.5 |
| 45° | 5539.8 | 5618.0 | 5203.2 | 4787.9 | 4582.4 | 4376.5 | 4307.2 | 4238.0 | 4293.5 | 4349.0 | 4480.4 |
| 47.5° | 5701.6 | 5754.6 | 5326.0 | 4897.0 | 4760.4 | 4623.7 | 4633.9 | 4644.2 | 4757.2 | 4870.2 | 4954.8 |
| 50° | 5886.5 | 5843.7 | 5437.4 | 5030.7 | 4988.7 | 4946.6 | 5038.6 | 5130.3 | 5260.2 | 5389.8 | 5447.3 |
| 52.5° | 6086.9 | 5973.1 | 5588.5 | 5203.6 | 5250.8 | 5298.1 | 5485.4 | 5672.8 | 5803.9 | 5935.0 | 5956.6 |
| 55° | 6447.1 | 6272.7 | 5866.5 | 5459.9 | 5550.8 | 5641.3 | 5916.5 | 6191.3 | 6293.6 | 6396.0 | 6403.8 |
| 57.5° | 6853.0 | 6698.3 | 6255.8 | 5813.3 | 5910.9 | 6008.6 | 6326.3 | 6643.5 | 6754.1 | 6864.3 | 6849.0 |
| 60° | 7009.2 | 7016.7 | 6625.5 | 6233.7 | 6332.2 | 6430.5 | 6740.0 | 7049.4 | 7176.5 | 7303.3 | 7269.4 |
| 62.5° | 6851.8 | 7036.3 | 6827.3 | 6617.9 | 6707.3 | 6796.2 | 7099.4 | 7402.4 | 7532.8 | 7663.1 | 7604.0 |
| 65° | 6540.4 | 6723.4 | 6817.1 | 6910.8 | 6940.3 | 6969.8 | 7252.9 | 7535.5 | 7635.5 | 7735.1 | 7705.2 |
| 67.5° | 6144.4 | 6292.4 | 6638.0 | 6983.3 | 6923.8 | 6864.3 | 6997.0 | 7129.7 | 7232.4 | 7335.2 | 7318.3 |
| 70° | 5685.8 | 5862.1 | 6323.1 | 6784.0 | 6492.0 | 6199.5 | 6144.8 | 6090.1 | 6201.0 | 6311.7 | 6243.2 |
| 72.5° | 4863.4 | 5129.6 | 5621.2 | 6112.5 | 5574.4 | 5036.3 | 4849.3 | 4662.3 | 4802.8 | 4943.4 | 4834.3 |
| 75° | 3673.5 | 4026.6 | 4569.8 | 5112.7 | 4470.6 | 3828.6 | 3579.0 | 3329.4 | 3450.3 | 3571.1 | 3496.3 |
| 77.5° | 2554.8 | 2997.6 | 3532.6 | 4067.5 | 3414.9 | 2761.8 | 2576.4 | 2390.6 | 2426.8 | 2462.6 | 2450.0 |
| 80° | 1741.9 | 2033.1 | 2406.4 | 2779.1 | 2344.5 | 1910.0 | 1924.5 | 1938.7 | 1921.8 | 1904.4 | 1929.6 |
| 82.5° | 1092.3 | 1297.5 | 1585.6 | 1873.3 | 1642.7 | 1412.0 | 1544.3 | 1676.5 | 1611.6 | 1546.2 | 1570.7 |
| 85° | 615.3 | 740.4 | 1022.2 | 1303.8 | 1215.2 | 1126.2 | 1203.7 | 1281.0 | 1180.2 | 1079.4 | 1123.9 |
| 87.5° | 117.3 | 195.2 | 565.7 | 935.7 | 849.5 | 763.3 | 663.3 | 563.3 | 429.9 | 296.4 | 433.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386615
 CATALOG NUMBER: GWC-SA2B-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 0° | 5° | 10° | 15° | 20° | 25° | 30° | 35° | 40° | 45° | 50° |
|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386615

CATALOG NUMBER: GWC-SA2B-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 55° | 60° | 65° | 70° | 75° | 80° | 85° | 90° | 95° | 100° | 105° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 |
| 2.5° | 3393.2 | 3386.5 | 3379.8 | 3355.8 | 3331.4 | 3295.2 | 3265.2 | 3213.3 | 3185.0 | 3142.1 | 3099.2 |
| 5° | 3672.3 | 3629.8 | 3587.3 | 3514.1 | 3440.4 | 3358.6 | 3264.5 | 3160.2 | 3081.4 | 2979.1 | 2876.7 |
| 7.5° | 3815.2 | 3716.0 | 3616.4 | 3475.9 | 3334.9 | 3208.2 | 3059.4 | 2920.9 | 2802.8 | 2669.7 | 2536.6 |
| 10° | 3828.2 | 3679.4 | 3530.2 | 3347.5 | 3164.5 | 3010.6 | 2839.3 | 2685.4 | 2543.7 | 2390.9 | 2237.8 |
| 12.5° | 3767.5 | 3609.3 | 3450.7 | 3249.6 | 3048.0 | 2873.2 | 2689.0 | 2516.5 | 2359.5 | 2191.4 | 2022.9 |
| 15° | 3639.2 | 3512.9 | 3386.1 | 3197.6 | 3009.0 | 2832.6 | 2654.0 | 2449.7 | 2272.1 | 2100.1 | 1927.6 |
| 17.5° | 3467.2 | 3407.4 | 3347.2 | 3210.9 | 3074.4 | 2921.6 | 2748.4 | 2508.7 | 2300.9 | 2113.8 | 1926.9 |
| 20° | 3300.7 | 3322.7 | 3344.4 | 3290.0 | 3235.7 | 3113.3 | 2962.2 | 2693.0 | 2427.6 | 2183.2 | 1938.3 |
| 22.5° | 3159.4 | 3265.2 | 3370.7 | 3412.9 | 3454.6 | 3381.0 | 3262.9 | 2951.6 | 2600.4 | 2281.1 | 1961.9 |
| 25° | 3057.1 | 3232.6 | 3408.1 | 3548.3 | 3688.1 | 3655.4 | 3564.4 | 3265.7 | 2829.5 | 2422.5 | 2015.1 |
| 27.5° | 3031.4 | 3246.7 | 3462.1 | 3679.4 | 3896.3 | 3926.6 | 3901.4 | 3596.8 | 3102.7 | 2598.1 | 2093.0 |
| 30° | 3071.6 | 3289.7 | 3507.3 | 3771.9 | 4036.0 | 4156.9 | 4190.7 | 3872.7 | 3414.9 | 2802.8 | 2190.2 |
| 32.5° | 3146.4 | 3360.1 | 3573.9 | 3862.0 | 4149.8 | 4332.5 | 4440.3 | 4125.0 | 3632.5 | 2957.0 | 2281.1 |
| 35° | 3267.2 | 3467.2 | 3667.2 | 3967.2 | 4267.1 | 4503.3 | 4700.1 | 4385.6 | 3825.9 | 3064.9 | 2303.6 |
| 37.5° | 3479.0 | 3651.0 | 3823.1 | 4100.2 | 4376.9 | 4683.2 | 4978.8 | 4672.5 | 4034.9 | 3168.9 | 2302.5 |
| 40° | 3799.1 | 3920.7 | 4041.9 | 4276.1 | 4509.9 | 4895.4 | 5294.5 | 4992.6 | 4265.9 | 3281.4 | 2296.9 |
| 42.5° | 4197.8 | 4260.4 | 4322.6 | 4508.0 | 4693.4 | 5117.0 | 5581.1 | 5305.5 | 4486.4 | 3386.1 | 2285.9 |
| 45° | 4611.6 | 4628.1 | 4644.6 | 4761.5 | 4878.0 | 5292.5 | 5776.3 | 5540.5 | 4678.8 | 3477.1 | 2274.8 |
| 47.5° | 5039.0 | 4982.4 | 4925.6 | 4972.1 | 5018.5 | 5427.2 | 5915.6 | 5718.8 | 4872.2 | 3577.9 | 2283.1 |
| 50° | 5504.8 | 5346.8 | 5189.0 | 5164.6 | 5140.2 | 5561.8 | 6079.9 | 5945.6 | 5104.4 | 3724.7 | 2344.9 |
| 52.5° | 5977.8 | 5717.7 | 5457.5 | 5361.0 | 5264.2 | 5722.4 | 6297.5 | 6227.8 | 5435.8 | 3952.2 | 2468.2 |
| 55° | 6411.6 | 6080.6 | 5749.6 | 5619.6 | 5489.7 | 5968.1 | 6563.3 | 6642.4 | 5860.6 | 4243.1 | 2625.2 |
| 57.5° | 6833.2 | 6458.1 | 6083.0 | 5962.5 | 5842.1 | 6329.0 | 6899.8 | 7014.4 | 6289.6 | 4522.1 | 2754.3 |
| 60° | 7235.6 | 6864.3 | 6492.7 | 6396.3 | 6299.5 | 6777.7 | 7263.5 | 7180.1 | 6510.8 | 4652.9 | 2794.5 |
| 62.5° | 7544.9 | 7249.8 | 6954.5 | 6903.7 | 6852.6 | 7231.6 | 7543.0 | 7115.5 | 6370.3 | 4524.1 | 2677.9 |
| 65° | 7675.2 | 7507.2 | 7338.7 | 7386.4 | 7433.6 | 7574.9 | 7612.7 | 6926.5 | 5928.7 | 4163.6 | 2398.5 |
| 67.5° | 7300.9 | 7335.2 | 7369.5 | 7569.4 | 7769.0 | 7671.7 | 7405.6 | 6554.2 | 5300.1 | 3652.6 | 2005.2 |
| 70° | 6174.3 | 6379.8 | 6584.9 | 7058.0 | 7530.8 | 7315.1 | 6851.0 | 5885.8 | 4543.5 | 3064.1 | 1584.4 |
| 72.5° | 4724.9 | 4956.0 | 5186.7 | 5888.9 | 6590.8 | 6392.0 | 5823.6 | 4834.3 | 3642.8 | 2446.9 | 1250.6 |
| 75° | 3421.2 | 3682.1 | 3942.7 | 4717.4 | 5492.1 | 5216.2 | 4356.1 | 3461.3 | 2766.9 | 1867.8 | 968.3 |
| 77.5° | 2437.1 | 2611.8 | 2786.6 | 3551.8 | 4316.7 | 3867.2 | 2899.5 | 2329.2 | 1915.0 | 1298.2 | 681.0 |
| 80° | 1954.9 | 1901.3 | 1847.8 | 2274.1 | 2700.4 | 2625.6 | 1917.9 | 1495.9 | 1325.4 | 870.0 | 414.5 |
| 82.5° | 1594.6 | 1464.0 | 1333.3 | 1534.0 | 1734.8 | 1723.8 | 1330.9 | 1097.5 | 986.5 | 604.6 | 222.8 |
| 85° | 1167.9 | 1115.6 | 1063.2 | 1240.8 | 1418.3 | 1266.8 | 901.4 | 697.5 | 769.2 | 445.2 | 121.3 |
| 87.5° | 569.6 | 650.7 | 731.4 | 940.8 | 1149.8 | 863.3 | 273.6 | 135.4 | 187.4 | 123.2 | 58.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386615
 CATALOG NUMBER: GWC-SA2B-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 55° | 60° | 65° | 70° | 75° | 80° | 85° | 90° | 95° | 100° | 105° |
|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386615

CATALOG NUMBER: GWC-SA2B-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 110° | 115° | 120° | 125° | 130° | 135° | 140° | 145° | 150° | 155° | 160° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 |
| 2.5° | 3067.3 | 3035.0 | 2998.4 | 2961.8 | 2920.0 | 2877.9 | 2853.1 | 2828.0 | 2800.8 | 2773.7 | 2742.9 |
| 5° | 2809.1 | 2741.3 | 2664.6 | 2587.8 | 2511.8 | 2435.8 | 2394.9 | 2354.0 | 2310.7 | 2267.0 | 2229.2 |
| 7.5° | 2438.2 | 2339.5 | 2233.1 | 2126.5 | 2032.0 | 1937.1 | 1878.5 | 1819.4 | 1765.9 | 1712.0 | 1666.7 |
| 10° | 2111.9 | 1986.0 | 1879.3 | 1772.2 | 1701.0 | 1629.7 | 1575.7 | 1521.8 | 1469.9 | 1417.5 | 1367.5 |
| 12.5° | 1897.0 | 1771.0 | 1703.3 | 1635.6 | 1576.6 | 1517.5 | 1455.3 | 1392.7 | 1321.4 | 1249.9 | 1197.4 |
| 15° | 1813.1 | 1698.6 | 1623.4 | 1547.8 | 1468.6 | 1389.2 | 1312.8 | 1236.4 | 1152.2 | 1068.0 | 1008.5 |
| 17.5° | 1776.9 | 1626.9 | 1521.8 | 1416.3 | 1312.1 | 1207.7 | 1119.1 | 1030.5 | 938.5 | 846.3 | 786.1 |
| 20° | 1738.7 | 1539.1 | 1398.2 | 1256.9 | 1123.0 | 989.2 | 888.9 | 788.4 | 706.2 | 623.9 | 577.9 |
| 22.5° | 1704.1 | 1445.8 | 1269.1 | 1092.0 | 933.8 | 775.5 | 677.0 | 578.3 | 527.8 | 477.5 | 459.0 |
| 25° | 1689.9 | 1364.4 | 1147.1 | 929.8 | 762.9 | 595.6 | 525.5 | 455.4 | 436.2 | 416.4 | 407.0 |
| 27.5° | 1692.3 | 1291.6 | 1044.3 | 796.7 | 646.4 | 496.0 | 448.0 | 399.9 | 388.2 | 375.9 | 370.0 |
| 30° | 1701.3 | 1212.4 | 947.5 | 682.6 | 558.6 | 434.6 | 403.5 | 372.0 | 359.4 | 346.8 | 339.3 |
| 32.5° | 1711.6 | 1141.6 | 872.7 | 603.5 | 502.3 | 400.7 | 375.1 | 349.2 | 337.0 | 324.7 | 317.2 |
| 35° | 1693.8 | 1083.7 | 821.5 | 559.4 | 466.0 | 372.4 | 350.8 | 328.7 | 315.4 | 301.9 | 294.9 |
| 37.5° | 1663.9 | 1025.4 | 781.8 | 537.7 | 442.5 | 346.8 | 331.0 | 314.9 | 301.2 | 287.0 | 280.3 |
| 40° | 1636.8 | 976.2 | 752.3 | 527.8 | 429.5 | 330.7 | 317.2 | 303.9 | 289.7 | 275.1 | 267.3 |
| 42.5° | 1614.7 | 943.2 | 723.1 | 503.0 | 417.7 | 331.9 | 312.9 | 293.7 | 279.8 | 266.1 | 257.5 |
| 45° | 1598.2 | 921.5 | 700.3 | 479.1 | 406.7 | 334.2 | 310.2 | 286.1 | 272.4 | 258.2 | 248.0 |
| 47.5° | 1596.6 | 910.1 | 684.2 | 458.2 | 385.8 | 312.9 | 303.1 | 293.3 | 273.2 | 252.7 | 241.0 |
| 50° | 1618.3 | 891.6 | 665.3 | 438.5 | 365.7 | 292.9 | 306.2 | 319.2 | 285.0 | 250.3 | 235.4 |
| 52.5° | 1663.6 | 858.9 | 635.3 | 411.7 | 341.3 | 270.5 | 291.3 | 311.8 | 282.3 | 252.3 | 233.1 |
| 55° | 1718.2 | 810.9 | 590.0 | 368.8 | 309.0 | 248.8 | 267.3 | 285.4 | 266.9 | 248.0 | 224.8 |
| 57.5° | 1752.5 | 750.3 | 533.0 | 315.7 | 272.8 | 229.9 | 240.5 | 250.7 | 243.3 | 235.8 | 212.2 |
| 60° | 1732.1 | 669.6 | 468.9 | 267.6 | 241.0 | 214.2 | 212.2 | 209.8 | 220.9 | 231.8 | 204.7 |
| 62.5° | 1632.0 | 586.2 | 412.1 | 238.1 | 218.0 | 197.6 | 193.2 | 188.5 | 206.7 | 224.4 | 195.7 |
| 65° | 1463.2 | 527.8 | 376.3 | 224.8 | 202.3 | 179.9 | 175.2 | 170.4 | 175.9 | 181.5 | 168.1 |
| 67.5° | 1248.6 | 492.1 | 355.8 | 219.6 | 192.5 | 165.0 | 159.4 | 153.9 | 152.7 | 151.5 | 146.8 |
| 70° | 1027.4 | 470.0 | 342.5 | 214.9 | 181.9 | 148.4 | 143.3 | 138.2 | 136.6 | 134.6 | 131.0 |
| 72.5° | 858.9 | 467.3 | 340.9 | 214.6 | 173.2 | 131.9 | 127.1 | 122.4 | 120.4 | 118.1 | 115.4 |
| 75° | 703.4 | 438.5 | 323.6 | 208.6 | 161.4 | 113.8 | 109.4 | 105.1 | 103.5 | 101.5 | 99.2 |
| 77.5° | 521.9 | 363.0 | 272.0 | 181.1 | 138.2 | 95.3 | 90.9 | 86.2 | 85.9 | 85.0 | 83.0 |
| 80° | 338.6 | 262.6 | 194.5 | 126.3 | 100.8 | 74.8 | 71.2 | 67.4 | 67.7 | 68.1 | 66.5 |
| 82.5° | 188.2 | 153.1 | 118.9 | 84.6 | 68.9 | 53.2 | 51.6 | 49.6 | 50.8 | 51.6 | 49.6 |
| 85° | 99.2 | 77.1 | 63.8 | 50.4 | 39.7 | 29.1 | 29.1 | 28.7 | 30.3 | 31.8 | 30.3 |
| 87.5° | 42.9 | 27.1 | 23.2 | 18.9 | 10.6 | 2.0 | 2.3 | 2.3 | 3.2 | 3.9 | 3.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386615
 CATALOG NUMBER: GWC-SA2B-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 110° | 115° | 120° | 125° | 130° | 135° | 140° | 145° | 150° | 155° | 160° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386615

CATALOG NUMBER: GWC-SA2B-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 165° | 170° | 175° | 180° | 185° | 190° | 195° | 200° | 205° | 210° | 215° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 |
| 2.5° | 2711.8 | 2683.1 | 2654.0 | 2622.0 | 2628.0 | 2603.5 | 2579.2 | 2563.8 | 2548.5 | 2543.7 | 2539.0 |
| 5° | 2191.4 | 2158.7 | 2125.7 | 2096.2 | 2121.7 | 2104.4 | 2087.1 | 2084.7 | 2082.0 | 2082.0 | 2081.6 |
| 7.5° | 1621.4 | 1586.4 | 1550.9 | 1526.5 | 1551.8 | 1548.6 | 1545.5 | 1562.4 | 1579.3 | 1593.1 | 1606.5 |
| 10° | 1317.5 | 1275.0 | 1232.1 | 1195.8 | 1189.6 | 1171.5 | 1153.0 | 1157.0 | 1160.4 | 1175.5 | 1190.4 |
| 12.5° | 1145.1 | 1094.3 | 1043.6 | 1001.0 | 981.8 | 951.8 | 921.5 | 902.7 | 883.7 | 885.7 | 887.3 |
| 15° | 948.7 | 899.5 | 849.9 | 813.2 | 801.0 | 777.8 | 754.6 | 731.0 | 707.0 | 697.1 | 686.9 |
| 17.5° | 725.5 | 686.1 | 646.4 | 622.0 | 622.0 | 615.3 | 608.5 | 596.8 | 584.6 | 574.7 | 564.5 |
| 20° | 531.8 | 510.9 | 489.7 | 479.5 | 482.6 | 483.0 | 483.0 | 488.9 | 494.8 | 491.7 | 488.5 |
| 22.5° | 440.1 | 432.6 | 425.2 | 420.8 | 422.4 | 422.7 | 423.2 | 428.6 | 433.8 | 437.8 | 441.2 |
| 25° | 397.2 | 392.5 | 387.8 | 386.2 | 389.7 | 390.1 | 390.1 | 393.6 | 397.2 | 401.1 | 405.1 |
| 27.5° | 363.7 | 361.8 | 359.8 | 357.1 | 360.5 | 360.5 | 360.2 | 364.1 | 367.7 | 371.2 | 374.3 |
| 30° | 331.9 | 332.6 | 333.0 | 332.3 | 334.6 | 336.2 | 337.3 | 340.2 | 342.5 | 345.2 | 348.0 |
| 32.5° | 309.4 | 308.2 | 307.1 | 306.2 | 311.4 | 314.1 | 316.9 | 319.7 | 322.0 | 323.2 | 324.4 |
| 35° | 287.7 | 285.0 | 282.3 | 280.3 | 285.0 | 288.6 | 292.1 | 297.2 | 301.9 | 302.7 | 303.5 |
| 37.5° | 273.2 | 269.6 | 266.1 | 263.8 | 265.8 | 267.3 | 268.9 | 274.4 | 279.8 | 283.0 | 285.8 |
| 40° | 259.4 | 255.9 | 252.3 | 250.3 | 251.6 | 251.9 | 252.3 | 255.0 | 257.5 | 263.3 | 268.9 |
| 42.5° | 248.4 | 244.1 | 239.7 | 237.4 | 238.1 | 239.0 | 239.4 | 239.0 | 238.5 | 244.1 | 249.6 |
| 45° | 237.4 | 232.7 | 227.9 | 225.2 | 225.5 | 225.5 | 225.5 | 224.8 | 223.6 | 226.3 | 229.1 |
| 47.5° | 228.7 | 223.2 | 217.7 | 214.9 | 214.2 | 213.3 | 212.6 | 212.2 | 211.4 | 213.3 | 214.9 |
| 50° | 220.0 | 214.2 | 207.9 | 204.7 | 202.7 | 202.0 | 201.1 | 200.7 | 200.0 | 202.0 | 203.5 |
| 52.5° | 213.3 | 206.3 | 199.2 | 194.1 | 192.1 | 190.9 | 189.8 | 190.1 | 190.1 | 190.9 | 191.4 |
| 55° | 201.5 | 195.2 | 188.5 | 185.0 | 181.5 | 180.6 | 179.9 | 181.1 | 181.9 | 181.9 | 181.9 |
| 57.5° | 188.5 | 182.6 | 176.3 | 174.0 | 170.9 | 170.9 | 170.4 | 172.0 | 173.2 | 174.0 | 174.8 |
| 60° | 177.2 | 170.4 | 163.7 | 161.8 | 160.6 | 160.2 | 159.8 | 161.8 | 163.4 | 165.0 | 166.6 |
| 62.5° | 166.6 | 159.4 | 152.4 | 150.0 | 149.6 | 150.0 | 150.0 | 151.9 | 153.5 | 155.1 | 156.7 |
| 65° | 154.7 | 147.6 | 140.2 | 137.8 | 138.6 | 139.8 | 140.9 | 142.5 | 143.6 | 145.2 | 146.8 |
| 67.5° | 141.8 | 135.8 | 129.5 | 127.1 | 127.6 | 129.1 | 130.7 | 131.9 | 132.6 | 134.2 | 135.8 |
| 70° | 127.6 | 122.4 | 117.3 | 115.7 | 115.4 | 117.3 | 118.9 | 119.7 | 120.4 | 122.4 | 124.0 |
| 72.5° | 112.2 | 107.8 | 103.5 | 102.4 | 102.8 | 103.9 | 105.1 | 106.2 | 107.1 | 109.1 | 110.7 |
| 75° | 96.5 | 92.5 | 88.6 | 87.7 | 88.6 | 89.7 | 90.9 | 91.7 | 92.5 | 94.9 | 96.9 |
| 77.5° | 81.1 | 76.7 | 72.1 | 71.7 | 72.8 | 74.0 | 74.8 | 76.0 | 77.1 | 80.3 | 83.4 |
| 80° | 64.9 | 60.2 | 55.1 | 54.7 | 55.9 | 57.1 | 58.2 | 59.5 | 60.6 | 64.5 | 68.1 |
| 82.5° | 47.6 | 42.1 | 36.6 | 35.8 | 39.7 | 41.0 | 42.1 | 44.1 | 45.7 | 49.2 | 52.8 |
| 85° | 28.7 | 23.2 | 17.8 | 17.3 | 20.9 | 22.8 | 24.8 | 27.1 | 29.1 | 32.3 | 35.4 |
| 87.5° | 3.2 | 1.6 | 0.0 | 0.0 | 0.4 | 2.0 | 3.6 | 5.5 | 7.5 | 10.6 | 13.3 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386615
 CATALOG NUMBER: GWC-SA2B-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 165° | 170° | 175° | 180° | 185° | 190° | 195° | 200° | 205° | 210° | 215° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386615

CATALOG NUMBER: GWC-SA2B-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 220° | 225° | 230° | 235° | 240° | 245° | 250° | 255° | 260° | 265° | 270° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 |
| 2.5° | 2521.7 | 2504.0 | 2522.1 | 2539.7 | 2547.3 | 2554.8 | 2535.4 | 2515.8 | 2546.5 | 2576.8 | 2584.6 |
| 5° | 2065.8 | 2049.7 | 2061.9 | 2073.7 | 2047.3 | 2021.0 | 2018.2 | 2015.1 | 2037.9 | 2060.7 | 2064.2 |
| 7.5° | 1601.4 | 1596.2 | 1607.7 | 1619.0 | 1585.6 | 1551.8 | 1535.3 | 1518.7 | 1524.2 | 1529.7 | 1529.0 |
| 10° | 1193.9 | 1197.1 | 1211.3 | 1225.1 | 1199.0 | 1173.0 | 1161.7 | 1150.2 | 1162.8 | 1175.0 | 1186.5 |
| 12.5° | 894.4 | 901.1 | 916.0 | 930.6 | 919.9 | 909.0 | 910.1 | 911.3 | 925.9 | 940.1 | 952.6 |
| 15° | 694.8 | 702.7 | 713.3 | 723.5 | 723.9 | 723.9 | 734.1 | 744.0 | 742.8 | 741.7 | 750.3 |
| 17.5° | 575.1 | 585.3 | 586.6 | 587.7 | 588.1 | 588.5 | 587.7 | 586.9 | 581.0 | 575.1 | 581.8 |
| 20° | 492.4 | 496.0 | 499.1 | 501.9 | 498.3 | 494.4 | 484.5 | 474.8 | 470.8 | 466.9 | 473.2 |
| 22.5° | 448.0 | 454.3 | 451.1 | 447.5 | 440.5 | 433.0 | 425.5 | 417.7 | 417.3 | 416.4 | 420.0 |
| 25° | 410.6 | 415.7 | 410.1 | 404.7 | 399.5 | 394.5 | 389.3 | 384.2 | 383.8 | 383.4 | 385.0 |
| 27.5° | 379.5 | 384.2 | 379.0 | 374.0 | 369.7 | 365.3 | 361.4 | 357.4 | 356.7 | 355.8 | 356.2 |
| 30° | 352.7 | 357.1 | 352.7 | 348.0 | 344.9 | 341.3 | 338.6 | 335.7 | 335.4 | 335.0 | 335.0 |
| 32.5° | 328.7 | 333.0 | 329.9 | 326.7 | 324.0 | 321.2 | 319.2 | 317.2 | 315.4 | 313.4 | 309.0 |
| 35° | 307.8 | 312.2 | 310.2 | 307.8 | 304.6 | 301.5 | 298.0 | 294.0 | 289.0 | 283.4 | 281.1 |
| 37.5° | 290.1 | 294.4 | 292.4 | 290.6 | 286.1 | 281.8 | 275.5 | 268.9 | 267.3 | 265.3 | 264.9 |
| 40° | 275.9 | 282.7 | 278.7 | 274.4 | 267.6 | 261.0 | 257.9 | 254.7 | 253.9 | 253.1 | 252.3 |
| 42.5° | 260.2 | 270.5 | 263.3 | 256.3 | 250.0 | 243.7 | 242.8 | 242.1 | 241.7 | 241.3 | 241.3 |
| 45° | 240.5 | 251.6 | 244.4 | 237.0 | 233.4 | 229.9 | 229.9 | 229.9 | 230.2 | 230.2 | 231.1 |
| 47.5° | 222.0 | 228.7 | 225.2 | 221.6 | 219.6 | 217.7 | 218.0 | 218.5 | 219.6 | 220.5 | 222.4 |
| 50° | 206.3 | 208.6 | 209.4 | 209.8 | 208.6 | 207.4 | 208.3 | 208.6 | 209.8 | 210.6 | 212.2 |
| 52.5° | 194.8 | 198.4 | 198.4 | 198.0 | 198.0 | 198.0 | 198.8 | 199.6 | 200.7 | 202.0 | 203.5 |
| 55° | 187.4 | 192.5 | 190.9 | 189.4 | 189.8 | 189.8 | 190.5 | 191.4 | 192.5 | 193.2 | 195.7 |
| 57.5° | 180.3 | 185.8 | 184.2 | 182.6 | 182.6 | 182.6 | 183.1 | 183.5 | 184.6 | 185.4 | 186.9 |
| 60° | 172.0 | 177.5 | 175.9 | 174.0 | 174.4 | 174.8 | 175.2 | 175.2 | 175.9 | 176.3 | 176.3 |
| 62.5° | 162.1 | 167.7 | 166.1 | 164.1 | 165.3 | 166.1 | 166.1 | 166.1 | 166.9 | 167.3 | 166.1 |
| 65° | 151.9 | 157.1 | 155.5 | 153.9 | 155.5 | 156.7 | 157.4 | 157.8 | 157.4 | 157.1 | 155.8 |
| 67.5° | 140.9 | 146.1 | 144.5 | 142.5 | 144.5 | 146.1 | 147.6 | 148.8 | 147.6 | 146.5 | 144.9 |
| 70° | 129.1 | 134.2 | 132.3 | 130.3 | 132.3 | 134.2 | 135.8 | 137.3 | 135.8 | 134.2 | 133.9 |
| 72.5° | 116.5 | 122.4 | 120.1 | 117.7 | 120.1 | 122.4 | 123.2 | 124.0 | 122.8 | 121.7 | 120.8 |
| 75° | 102.8 | 108.7 | 106.7 | 104.3 | 106.2 | 108.2 | 108.7 | 109.1 | 109.1 | 108.7 | 106.2 |
| 77.5° | 88.2 | 92.9 | 91.7 | 90.6 | 91.7 | 92.9 | 92.9 | 92.9 | 93.3 | 93.3 | 90.2 |
| 80° | 70.8 | 73.6 | 74.0 | 74.4 | 74.8 | 75.2 | 74.8 | 74.4 | 73.6 | 72.8 | 70.8 |
| 82.5° | 52.8 | 52.8 | 55.9 | 58.6 | 58.6 | 58.2 | 57.9 | 57.1 | 55.5 | 53.5 | 49.2 |
| 85° | 33.4 | 31.5 | 36.6 | 41.3 | 41.3 | 41.0 | 40.1 | 39.0 | 35.8 | 32.3 | 28.7 |
| 87.5° | 11.5 | 9.5 | 14.6 | 19.7 | 20.1 | 20.1 | 19.3 | 18.5 | 15.3 | 11.8 | 9.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386615
 CATALOG NUMBER: GWC-SA2B-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 220° | 225° | 230° | 235° | 240° | 245° | 250° | 255° | 260° | 265° | 270° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386615

CATALOG NUMBER: GWC-SA2B-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 275° | 280° | 285° | 290° | 295° | 300° | 305° | 310° | 315° | 320° | 325° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 |
| 2.5° | 2596.5 | 2601.6 | 2606.3 | 2644.9 | 2683.1 | 2727.9 | 2772.8 | 2807.1 | 2840.9 | 2876.0 | 2911.0 |
| 5° | 2076.4 | 2082.7 | 2089.0 | 2135.9 | 2182.4 | 2245.0 | 2307.5 | 2361.4 | 2415.4 | 2478.8 | 2542.2 |
| 7.5° | 1539.1 | 1552.9 | 1566.3 | 1616.3 | 1665.9 | 1733.2 | 1800.2 | 1870.6 | 1940.7 | 2023.4 | 2106.0 |
| 10° | 1208.9 | 1234.8 | 1260.5 | 1311.6 | 1362.8 | 1429.3 | 1495.4 | 1569.1 | 1642.7 | 1724.2 | 1805.2 |
| 12.5° | 978.6 | 1013.2 | 1047.5 | 1108.9 | 1170.3 | 1249.9 | 1329.0 | 1410.8 | 1492.3 | 1563.9 | 1635.6 |
| 15° | 773.1 | 810.9 | 848.3 | 913.3 | 978.2 | 1065.6 | 1152.5 | 1242.0 | 1330.9 | 1416.7 | 1502.6 |
| 17.5° | 603.1 | 634.2 | 664.9 | 720.0 | 774.7 | 859.4 | 944.0 | 1037.7 | 1131.3 | 1236.1 | 1340.3 |
| 20° | 486.5 | 499.6 | 512.5 | 552.3 | 591.6 | 660.5 | 729.1 | 824.7 | 920.3 | 1045.5 | 1170.7 |
| 22.5° | 426.3 | 433.0 | 439.3 | 458.6 | 477.5 | 521.9 | 566.1 | 650.7 | 734.9 | 871.6 | 1007.7 |
| 25° | 390.1 | 395.2 | 400.4 | 413.0 | 425.5 | 446.8 | 468.0 | 527.5 | 586.9 | 721.2 | 855.0 |
| 27.5° | 357.4 | 365.3 | 372.8 | 378.7 | 384.2 | 398.8 | 413.0 | 451.9 | 490.8 | 616.1 | 740.8 |
| 30° | 333.8 | 336.6 | 339.3 | 348.4 | 357.1 | 372.0 | 386.9 | 414.1 | 441.2 | 547.2 | 652.7 |
| 32.5° | 306.2 | 310.2 | 314.1 | 323.6 | 333.0 | 346.8 | 360.5 | 382.6 | 404.3 | 494.8 | 585.0 |
| 35° | 281.4 | 285.4 | 289.3 | 298.8 | 307.8 | 322.8 | 337.3 | 355.8 | 374.0 | 452.7 | 531.4 |
| 37.5° | 266.1 | 270.1 | 274.0 | 282.3 | 290.1 | 305.1 | 319.7 | 334.2 | 348.4 | 421.2 | 494.0 |
| 40° | 253.1 | 257.0 | 261.0 | 268.9 | 276.4 | 290.9 | 305.1 | 317.2 | 329.4 | 397.6 | 465.7 |
| 42.5° | 241.7 | 246.0 | 250.3 | 258.2 | 265.8 | 278.7 | 291.7 | 307.8 | 323.6 | 377.1 | 430.2 |
| 45° | 232.2 | 236.5 | 240.5 | 249.2 | 257.9 | 270.5 | 283.0 | 305.5 | 327.9 | 366.5 | 405.1 |
| 47.5° | 223.6 | 228.3 | 232.7 | 242.1 | 251.6 | 267.3 | 282.7 | 301.5 | 320.1 | 358.2 | 396.4 |
| 50° | 215.3 | 220.9 | 226.3 | 237.8 | 248.8 | 275.1 | 301.2 | 303.9 | 306.2 | 351.5 | 396.4 |
| 52.5° | 207.4 | 213.7 | 220.0 | 234.2 | 248.0 | 278.7 | 309.4 | 299.6 | 289.3 | 338.9 | 388.5 |
| 55° | 199.6 | 205.1 | 210.2 | 227.5 | 244.8 | 267.3 | 289.7 | 276.7 | 263.3 | 315.4 | 367.3 |
| 57.5° | 188.9 | 194.8 | 200.4 | 218.9 | 237.4 | 253.1 | 268.5 | 256.6 | 244.4 | 288.6 | 332.3 |
| 60° | 177.9 | 184.6 | 191.4 | 214.9 | 238.1 | 235.4 | 232.2 | 229.9 | 227.1 | 258.6 | 290.1 |
| 62.5° | 168.1 | 175.2 | 182.2 | 213.0 | 243.7 | 224.8 | 205.9 | 207.9 | 209.4 | 232.7 | 255.9 |
| 65° | 158.3 | 165.3 | 172.0 | 187.4 | 202.7 | 195.2 | 187.8 | 190.9 | 193.7 | 216.5 | 239.4 |
| 67.5° | 147.2 | 153.5 | 159.4 | 164.6 | 169.7 | 170.4 | 171.3 | 174.4 | 177.5 | 204.7 | 231.5 |
| 70° | 135.0 | 140.2 | 145.2 | 148.8 | 151.9 | 153.5 | 154.7 | 158.7 | 162.6 | 192.1 | 221.6 |
| 72.5° | 121.3 | 125.6 | 129.5 | 132.6 | 135.8 | 137.0 | 137.8 | 141.8 | 145.6 | 177.2 | 208.6 |
| 75° | 106.2 | 109.8 | 113.0 | 115.7 | 118.5 | 120.1 | 121.7 | 124.4 | 127.1 | 161.4 | 195.2 |
| 77.5° | 89.7 | 93.3 | 96.5 | 98.8 | 100.8 | 102.4 | 103.5 | 107.1 | 110.7 | 139.3 | 167.7 |
| 80° | 70.1 | 74.4 | 78.3 | 80.3 | 81.9 | 82.3 | 82.3 | 85.4 | 88.6 | 109.1 | 129.1 |
| 82.5° | 49.6 | 54.3 | 58.6 | 60.2 | 61.8 | 61.8 | 61.8 | 65.4 | 68.9 | 82.7 | 96.0 |
| 85° | 29.1 | 34.3 | 39.0 | 40.6 | 42.1 | 42.9 | 43.3 | 44.9 | 46.0 | 55.9 | 65.4 |
| 87.5° | 9.0 | 13.3 | 17.3 | 18.1 | 18.9 | 20.5 | 22.1 | 22.5 | 22.5 | 29.1 | 35.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386615
 CATALOG NUMBER: GWC-SA2B-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 275° | 280° | 285° | 290° | 295° | 300° | 305° | 310° | 315° | 320° | 325° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386615
 CATALOG NUMBER: GWC-SA2B-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 330° | 335° | 340° | 345° | 350° | 355° | 360° |
|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 | 2999.6 |
| 2.5° | 2951.1 | 2991.3 | 3038.2 | 3084.6 | 3124.3 | 3164.1 | 3197.1 |
| 5° | 2622.9 | 2703.6 | 2802.3 | 2900.8 | 2988.6 | 3076.3 | 3178.3 |
| 7.5° | 2210.3 | 2314.7 | 2442.5 | 2570.5 | 2694.5 | 2818.1 | 2974.8 |
| 10° | 1911.6 | 2017.4 | 2152.8 | 2287.9 | 2427.2 | 2566.1 | 2743.3 |
| 12.5° | 1721.8 | 1807.6 | 1938.7 | 2069.8 | 2233.5 | 2396.9 | 2567.4 |
| 15° | 1596.6 | 1690.3 | 1817.8 | 1945.4 | 2124.5 | 2303.6 | 2499.6 |
| 17.5° | 1463.2 | 1585.6 | 1749.0 | 1912.3 | 2124.5 | 2336.3 | 2567.4 |
| 20° | 1323.4 | 1475.8 | 1687.5 | 1899.4 | 2185.1 | 2470.5 | 2765.4 |
| 22.5° | 1184.1 | 1360.4 | 1632.0 | 1903.3 | 2276.8 | 2650.0 | 3048.0 |
| 25° | 1058.5 | 1262.0 | 1598.2 | 1933.9 | 2410.3 | 2886.2 | 3379.8 |
| 27.5° | 963.3 | 1185.2 | 1584.4 | 1983.2 | 2579.6 | 3175.9 | 3740.8 |
| 30° | 878.6 | 1104.5 | 1567.8 | 2031.2 | 2742.6 | 3453.4 | 4023.0 |
| 32.5° | 805.4 | 1025.8 | 1536.0 | 2045.8 | 2856.3 | 3666.8 | 4261.9 |
| 35° | 747.9 | 964.4 | 1482.5 | 2000.5 | 2927.5 | 3854.5 | 4510.8 |
| 37.5° | 698.3 | 902.7 | 1421.5 | 1940.2 | 2990.9 | 4041.6 | 4790.6 |
| 40° | 651.1 | 836.5 | 1369.1 | 1901.3 | 3078.3 | 4255.3 | 5086.3 |
| 42.5° | 606.2 | 782.1 | 1327.0 | 1871.7 | 3159.4 | 4446.6 | 5344.9 |
| 45° | 572.7 | 740.4 | 1289.6 | 1838.3 | 3211.7 | 4585.2 | 5539.8 |
| 47.5° | 556.2 | 715.6 | 1269.5 | 1823.0 | 3264.1 | 4704.9 | 5701.6 |
| 50° | 553.9 | 711.3 | 1292.3 | 1873.3 | 3377.5 | 4881.2 | 5886.5 |
| 52.5° | 553.5 | 718.4 | 1358.1 | 1997.7 | 3588.1 | 5178.0 | 6086.9 |
| 55° | 545.2 | 722.8 | 1436.4 | 2149.7 | 3870.7 | 5591.3 | 6447.1 |
| 57.5° | 520.0 | 707.7 | 1517.1 | 2326.0 | 4169.5 | 6012.5 | 6853.0 |
| 60° | 481.1 | 671.6 | 1583.6 | 2495.3 | 4370.2 | 6244.8 | 7009.2 |
| 62.5° | 432.2 | 608.2 | 1605.7 | 2602.8 | 4364.7 | 6126.6 | 6851.8 |
| 65° | 390.5 | 541.7 | 1533.3 | 2524.4 | 4143.9 | 5762.9 | 6540.4 |
| 67.5° | 353.5 | 475.1 | 1352.2 | 2228.8 | 3746.7 | 5264.2 | 6144.4 |
| 70° | 326.7 | 431.5 | 1118.7 | 1806.1 | 3249.6 | 4692.6 | 5685.8 |
| 72.5° | 309.8 | 410.6 | 912.1 | 1413.2 | 2637.0 | 3860.4 | 4863.4 |
| 75° | 286.6 | 377.9 | 715.6 | 1053.0 | 2018.2 | 2983.4 | 3673.5 |
| 77.5° | 243.3 | 318.5 | 539.3 | 760.2 | 1480.9 | 2201.3 | 2554.8 |
| 80° | 187.8 | 246.0 | 370.8 | 495.6 | 1019.1 | 1542.7 | 1741.9 |
| 82.5° | 133.9 | 171.6 | 224.8 | 277.9 | 677.0 | 1075.8 | 1092.3 |
| 85° | 82.7 | 100.0 | 128.7 | 157.4 | 448.0 | 738.5 | 615.3 |
| 87.5° | 44.5 | 53.2 | 68.1 | 82.7 | 143.3 | 203.9 | 117.3 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386615

CATALOG NUMBER: GWC-SA2B-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 330° | 335° | 340° | 345° | 350° | 355° | 360° |
|--------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245982

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





--- HS — SS

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



u



| | | | | | | | | | | | |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





| | | | | | | | | | | | |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





| | | | | | | | | | | | |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





| | | | | | | | | | | | |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





| | | | | | | | | | | | |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





| | | | | | | | | | | | |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





| | | | | | | | |
|------|-----|-----|-----|-----|-----|-----|-----|
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
|------|-----|-----|-----|-----|-----|-----|-----|

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)