

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P385747

Luminaire Tested: **GWC-SA1B-750-U-SLL**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P385747
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-26)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GWC-SA1B-750-U-SLL
Description: GALLEON WALL LUMINAIRE
(1) 70 CRI, 5000K, 800mA LIGHTSQUARE WITH 16 LEDS AND SPILL LIGHT
ELIMINATOR LEFT OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5365 lumens
Efficiency: N/A
Efficacy: 121.9 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B1 - U0 - G2

Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




REPORT NUMBER: P385747

CATALOG NUMBER: GWC-SA1B-750-U-SLL

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 20.6 fc
 Type III - Medium - N/A

REPORT NUMBER: P385747
CATALOG NUMBER: GWC-SA1B-750-U-SLL

Luminous Intensity Polar Plot



— Vertical Plane Through 75-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P385747

CATALOG NUMBER: GWC-SA1B-750-U-SLL


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 944.9 | 0.0 | 944.9 |
| | % Fixture | 17.6 | 0.0 | 17.6 |
| Street Side | Lumens | 4420.1 | 0.0 | 4420.1 |
| | % Fixture | 82.4 | 0.0 | 82.4 |
| Total | Lumens | 5365.0 | 0.0 | 5365.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 126.1 | 2.4 |
| 10°-20° | 262.1 | 4.9 |
| 20°-30° | 372.7 | 6.9 |
| 30°-40° | 537.1 | 10.0 |
| 40°-50° | 756.9 | 14.1 |
| 50°-60° | 1052.2 | 19.6 |
| 60°-70° | 1272.4 | 23.7 |
| 70°-80° | 782.1 | 14.6 |
| 80°-90° | 203.5 | 3.8 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 5365.0 | 100.0 |
| 0°-180° | 5365.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P385747

CATALOG NUMBER: GWC-SA1B-750-U-SLL

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 532.7 | 9.9 | | | |
| FM (30°-60°) | 1917.2 | 35.7 | | | |
| FH (60°-80°) | 1789.6 | 33.4 | | | G1/1800 |
| FVH (80°-90°) | 180.7 | 3.4 | | | G2/225 |
| BL (0°-30°) | 228.2 | 4.3 | B1/500 | | |
| BM (30°-60°) | 428.9 | 8.0 | B1/1000 | | |
| BH (60°-80°) | 264.9 | 4.9 | B1/500 | | G1/500 |
| BVH (80°-90°) | 22.9 | 0.4 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G2
 Type III Medium





REPORT NUMBER: P385747

CATALOG NUMBER: GWC-SA1B-750-U-SLL

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 10° | 15° | 20° | 25° | 30° | 35° | 40° | 45° | 50° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 |
| 2.5° | 1742.2 | 1765.1 | 1781.0 | 1796.6 | 1808.9 | 1820.9 | 1838.5 | 1856.0 | 1859.5 | 1862.7 | 1855.8 |
| 5° | 1731.9 | 1787.8 | 1835.5 | 1882.9 | 1926.8 | 1970.8 | 1997.2 | 2023.6 | 2028.9 | 2034.3 | 2017.8 |
| 7.5° | 1621.0 | 1703.5 | 1786.1 | 1868.7 | 1944.4 | 2020.1 | 2066.3 | 2112.2 | 2122.7 | 2133.0 | 2105.9 |
| 10° | 1494.8 | 1590.9 | 1692.4 | 1793.8 | 1893.6 | 1993.3 | 2060.0 | 2126.7 | 2140.0 | 2153.3 | 2119.7 |
| 12.5° | 1399.0 | 1503.8 | 1612.2 | 1720.5 | 1825.8 | 1930.9 | 2000.0 | 2069.0 | 2085.6 | 2102.1 | 2077.6 |
| 15° | 1362.1 | 1477.0 | 1578.9 | 1680.8 | 1772.6 | 1864.2 | 1920.8 | 1977.2 | 1984.1 | 1990.8 | 1986.9 |
| 17.5° | 1399.0 | 1525.7 | 1618.0 | 1710.0 | 1760.0 | 1809.7 | 1832.5 | 1855.0 | 1862.5 | 1869.8 | 1879.6 |
| 20° | 1506.8 | 1643.7 | 1708.7 | 1773.5 | 1771.3 | 1769.0 | 1758.0 | 1746.9 | 1744.9 | 1743.0 | 1770.9 |
| 22.5° | 1660.9 | 1819.8 | 1845.8 | 1871.5 | 1811.2 | 1750.9 | 1714.3 | 1677.4 | 1670.1 | 1662.6 | 1692.2 |
| 25° | 1841.7 | 2010.9 | 2006.2 | 2001.3 | 1886.5 | 1771.5 | 1701.6 | 1631.7 | 1623.5 | 1615.4 | 1640.7 |
| 27.5° | 2038.4 | 2200.1 | 2169.2 | 2138.3 | 1982.4 | 1826.4 | 1725.0 | 1623.5 | 1615.4 | 1607.2 | 1629.5 |
| 30° | 2192.2 | 2338.9 | 2289.3 | 2239.8 | 2063.3 | 1886.7 | 1766.2 | 1645.6 | 1632.3 | 1618.8 | 1646.3 |
| 32.5° | 2322.4 | 2447.2 | 2380.7 | 2314.2 | 2128.9 | 1943.6 | 1813.1 | 1682.7 | 1661.9 | 1641.1 | 1677.8 |
| 35° | 2457.9 | 2555.3 | 2461.8 | 2368.1 | 2187.4 | 2006.6 | 1868.7 | 1730.6 | 1705.0 | 1679.5 | 1729.9 |
| 37.5° | 2610.4 | 2691.3 | 2557.0 | 2422.5 | 2253.3 | 2084.1 | 1951.9 | 1819.6 | 1793.4 | 1767.2 | 1831.6 |
| 40° | 2771.5 | 2838.9 | 2659.8 | 2480.7 | 2325.4 | 2170.1 | 2067.1 | 1963.9 | 1939.1 | 1914.0 | 1992.0 |
| 42.5° | 2912.4 | 2961.6 | 2755.4 | 2549.3 | 2412.2 | 2275.0 | 2202.5 | 2129.7 | 2129.5 | 2129.1 | 2208.3 |
| 45° | 3018.6 | 3061.3 | 2835.2 | 2608.9 | 2497.0 | 2384.8 | 2347.0 | 2309.3 | 2339.5 | 2369.8 | 2441.4 |
| 47.5° | 3106.8 | 3135.7 | 2902.2 | 2668.4 | 2593.9 | 2519.5 | 2525.1 | 2530.6 | 2592.2 | 2653.8 | 2699.9 |
| 50° | 3207.6 | 3184.2 | 2962.9 | 2741.3 | 2718.3 | 2695.4 | 2745.6 | 2795.5 | 2866.3 | 2936.9 | 2968.2 |
| 52.5° | 3316.8 | 3254.8 | 3045.2 | 2835.4 | 2861.2 | 2886.9 | 2989.0 | 3091.1 | 3162.6 | 3234.0 | 3245.8 |
| 55° | 3513.0 | 3418.0 | 3196.7 | 2975.1 | 3024.6 | 3074.0 | 3223.9 | 3373.6 | 3429.4 | 3485.2 | 3489.4 |
| 57.5° | 3734.2 | 3649.9 | 3408.8 | 3167.7 | 3220.9 | 3274.1 | 3447.2 | 3620.1 | 3680.4 | 3740.4 | 3732.0 |
| 60° | 3819.3 | 3823.4 | 3610.2 | 3396.8 | 3450.4 | 3504.0 | 3672.6 | 3841.2 | 3910.5 | 3979.6 | 3961.1 |
| 62.5° | 3733.5 | 3834.1 | 3720.2 | 3606.1 | 3654.8 | 3703.3 | 3868.5 | 4033.6 | 4104.6 | 4175.6 | 4143.5 |
| 65° | 3563.9 | 3663.6 | 3714.7 | 3765.7 | 3781.8 | 3797.9 | 3952.1 | 4106.1 | 4160.6 | 4214.9 | 4198.6 |
| 67.5° | 3348.1 | 3428.7 | 3617.1 | 3805.2 | 3772.8 | 3740.4 | 3812.7 | 3885.0 | 3941.0 | 3996.9 | 3987.7 |
| 70° | 3098.2 | 3194.3 | 3445.5 | 3696.7 | 3537.5 | 3378.1 | 3348.3 | 3318.5 | 3379.0 | 3439.3 | 3401.9 |
| 72.5° | 2650.1 | 2795.1 | 3063.0 | 3330.7 | 3037.5 | 2744.3 | 2642.4 | 2540.5 | 2617.1 | 2693.7 | 2634.2 |
| 75° | 2001.7 | 2194.1 | 2490.1 | 2785.9 | 2436.1 | 2086.2 | 1950.2 | 1814.2 | 1880.1 | 1945.9 | 1905.2 |
| 77.5° | 1392.1 | 1633.4 | 1924.9 | 2216.4 | 1860.8 | 1504.9 | 1403.9 | 1302.6 | 1322.4 | 1341.9 | 1335.0 |
| 80° | 949.2 | 1107.9 | 1311.2 | 1514.4 | 1277.5 | 1040.7 | 1048.7 | 1056.4 | 1047.2 | 1037.7 | 1051.5 |
| 82.5° | 595.2 | 707.0 | 864.0 | 1020.8 | 895.1 | 769.4 | 841.5 | 913.5 | 878.2 | 842.5 | 855.8 |
| 85° | 335.3 | 403.5 | 557.1 | 710.4 | 662.2 | 613.7 | 655.9 | 698.0 | 643.1 | 588.2 | 612.4 |
| 87.5° | 63.9 | 106.4 | 308.2 | 509.9 | 462.9 | 415.9 | 361.4 | 306.9 | 234.2 | 161.5 | 235.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P385747
 CATALOG NUMBER: GWC-SA1B-750-U-SLL

CANDELA DISTRIBUTION (continued):

| | 0° | 5° | 10° | 15° | 20° | 25° | 30° | 35° | 40° | 45° | 50° |
|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P385747

CATALOG NUMBER: GWC-SA1B-750-U-SLL

CANDELA DISTRIBUTION (continued):

| | 55° | 60° | 65° | 70° | 75° | 80° | 85° | 90° | 95° | 100° | 105° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 |
| 2.5° | 1849.0 | 1845.3 | 1841.7 | 1828.6 | 1815.3 | 1795.6 | 1779.3 | 1750.9 | 1735.5 | 1712.1 | 1688.7 |
| 5° | 2001.0 | 1977.9 | 1954.7 | 1914.8 | 1874.7 | 1830.1 | 1778.8 | 1722.0 | 1679.1 | 1623.3 | 1567.5 |
| 7.5° | 2078.9 | 2024.9 | 1970.6 | 1894.0 | 1817.2 | 1748.2 | 1667.1 | 1591.6 | 1527.2 | 1454.7 | 1382.2 |
| 10° | 2086.0 | 2004.9 | 1923.6 | 1824.1 | 1724.3 | 1640.5 | 1547.2 | 1463.3 | 1386.1 | 1302.9 | 1219.4 |
| 12.5° | 2053.0 | 1966.7 | 1880.3 | 1770.7 | 1660.9 | 1565.6 | 1465.2 | 1371.3 | 1285.7 | 1194.1 | 1102.3 |
| 15° | 1983.0 | 1914.2 | 1845.1 | 1742.4 | 1639.6 | 1543.5 | 1446.1 | 1334.8 | 1238.1 | 1144.3 | 1050.4 |
| 17.5° | 1889.3 | 1856.7 | 1823.9 | 1749.7 | 1675.2 | 1592.0 | 1497.6 | 1367.0 | 1253.7 | 1151.9 | 1050.0 |
| 20° | 1798.6 | 1810.6 | 1822.4 | 1792.8 | 1763.2 | 1696.5 | 1614.1 | 1467.4 | 1322.8 | 1189.6 | 1056.2 |
| 22.5° | 1721.6 | 1779.3 | 1836.7 | 1859.7 | 1882.4 | 1842.3 | 1778.0 | 1608.3 | 1417.0 | 1243.0 | 1069.1 |
| 25° | 1665.8 | 1761.5 | 1857.1 | 1933.5 | 2009.6 | 1991.8 | 1942.3 | 1779.5 | 1541.8 | 1320.0 | 1098.0 |
| 27.5° | 1651.8 | 1769.2 | 1886.5 | 2004.9 | 2123.1 | 2139.6 | 2125.9 | 1959.9 | 1690.7 | 1415.7 | 1140.5 |
| 30° | 1673.7 | 1792.6 | 1911.2 | 2055.3 | 2199.2 | 2265.1 | 2283.5 | 2110.2 | 1860.8 | 1527.2 | 1193.5 |
| 32.5° | 1714.5 | 1831.0 | 1947.4 | 2104.4 | 2261.2 | 2360.8 | 2419.5 | 2247.7 | 1979.4 | 1611.3 | 1243.0 |
| 35° | 1780.3 | 1889.3 | 1998.3 | 2161.7 | 2325.2 | 2453.9 | 2561.1 | 2389.7 | 2084.7 | 1670.1 | 1255.2 |
| 37.5° | 1895.7 | 1989.5 | 2083.2 | 2234.2 | 2385.0 | 2551.9 | 2713.0 | 2546.1 | 2198.6 | 1726.7 | 1254.6 |
| 40° | 2070.1 | 2136.4 | 2202.5 | 2330.1 | 2457.5 | 2667.5 | 2885.0 | 2720.5 | 2324.5 | 1788.1 | 1251.6 |
| 42.5° | 2287.4 | 2321.5 | 2355.4 | 2456.4 | 2557.5 | 2788.3 | 3041.1 | 2891.0 | 2444.6 | 1845.1 | 1245.6 |
| 45° | 2512.8 | 2521.8 | 2530.9 | 2594.6 | 2658.1 | 2883.9 | 3147.5 | 3019.1 | 2549.5 | 1894.7 | 1239.6 |
| 47.5° | 2745.8 | 2714.9 | 2684.0 | 2709.3 | 2734.6 | 2957.3 | 3223.5 | 3116.2 | 2654.8 | 1949.6 | 1244.1 |
| 50° | 2999.5 | 2913.5 | 2827.5 | 2814.2 | 2800.9 | 3030.6 | 3312.9 | 3239.8 | 2781.4 | 2029.6 | 1277.8 |
| 52.5° | 3257.4 | 3115.6 | 2973.8 | 2921.2 | 2868.5 | 3118.2 | 3431.5 | 3393.6 | 2962.0 | 2153.6 | 1344.9 |
| 55° | 3493.7 | 3313.3 | 3133.0 | 3062.2 | 2991.4 | 3252.0 | 3576.3 | 3619.4 | 3193.4 | 2312.1 | 1430.5 |
| 57.5° | 3723.5 | 3519.0 | 3314.6 | 3249.0 | 3183.4 | 3448.7 | 3759.7 | 3822.1 | 3427.2 | 2464.1 | 1500.8 |
| 60° | 3942.7 | 3740.4 | 3537.9 | 3485.4 | 3432.6 | 3693.2 | 3957.9 | 3912.4 | 3547.8 | 2535.4 | 1522.7 |
| 62.5° | 4111.3 | 3950.4 | 3789.5 | 3761.9 | 3734.0 | 3940.5 | 4110.2 | 3877.3 | 3471.2 | 2465.2 | 1459.2 |
| 65° | 4182.3 | 4090.7 | 3998.9 | 4024.8 | 4050.6 | 4127.6 | 4148.2 | 3774.3 | 3230.5 | 2268.7 | 1306.9 |
| 67.5° | 3978.3 | 3996.9 | 4015.6 | 4124.6 | 4233.3 | 4180.3 | 4035.3 | 3571.4 | 2888.0 | 1990.3 | 1092.7 |
| 70° | 3364.4 | 3476.4 | 3588.1 | 3845.9 | 4103.6 | 3986.0 | 3733.1 | 3207.2 | 2475.7 | 1669.7 | 863.4 |
| 72.5° | 2574.6 | 2700.5 | 2826.2 | 3208.9 | 3591.3 | 3483.0 | 3173.3 | 2634.2 | 1985.0 | 1333.3 | 681.5 |
| 75° | 1864.2 | 2006.4 | 2148.4 | 2570.5 | 2992.7 | 2842.3 | 2373.6 | 1886.1 | 1507.7 | 1017.8 | 527.7 |
| 77.5° | 1328.0 | 1423.2 | 1518.4 | 1935.4 | 2352.2 | 2107.2 | 1580.0 | 1269.2 | 1043.5 | 707.4 | 371.1 |
| 80° | 1065.2 | 1036.0 | 1006.9 | 1239.2 | 1471.5 | 1430.7 | 1045.0 | 815.1 | 722.2 | 474.0 | 225.9 |
| 82.5° | 868.9 | 797.7 | 726.5 | 835.9 | 945.3 | 939.3 | 725.2 | 598.0 | 537.5 | 329.5 | 121.4 |
| 85° | 636.4 | 607.9 | 579.4 | 676.1 | 772.8 | 690.3 | 491.2 | 380.1 | 419.1 | 242.6 | 66.1 |
| 87.5° | 310.4 | 354.6 | 398.5 | 512.6 | 626.5 | 470.4 | 149.1 | 73.8 | 102.1 | 67.1 | 32.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P385747
 CATALOG NUMBER: GWC-SA1B-750-U-SLL

CANDELA DISTRIBUTION (continued):

| | 55° | 60° | 65° | 70° | 75° | 80° | 85° | 90° | 95° | 100° | 105° |
|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P385747

CATALOG NUMBER: GWC-SA1B-750-U-SLL

CANDELA DISTRIBUTION (continued):

| | 110° | 115° | 120° | 125° | 130° | 135° | 140° | 145° | 150° | 155° | 160° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 |
| 2.5° | 1671.4 | 1653.8 | 1633.8 | 1613.9 | 1591.1 | 1568.2 | 1554.7 | 1541.0 | 1526.2 | 1511.4 | 1494.6 |
| 5° | 1530.7 | 1493.8 | 1451.9 | 1410.1 | 1368.7 | 1327.3 | 1305.0 | 1282.7 | 1259.1 | 1235.3 | 1214.7 |
| 7.5° | 1328.6 | 1274.8 | 1216.8 | 1158.7 | 1107.2 | 1055.5 | 1023.6 | 991.4 | 962.2 | 932.9 | 908.2 |
| 10° | 1150.8 | 1082.1 | 1024.0 | 965.7 | 926.8 | 888.0 | 858.6 | 829.2 | 800.9 | 772.4 | 745.2 |
| 12.5° | 1033.7 | 965.0 | 928.1 | 891.2 | 859.1 | 826.9 | 793.0 | 758.9 | 720.1 | 681.0 | 652.5 |
| 15° | 988.0 | 925.6 | 884.6 | 843.4 | 800.3 | 757.0 | 715.3 | 673.7 | 627.8 | 581.9 | 549.5 |
| 17.5° | 968.2 | 886.5 | 829.2 | 771.8 | 714.9 | 658.1 | 609.8 | 561.6 | 511.4 | 461.2 | 428.4 |
| 20° | 947.4 | 838.7 | 761.9 | 684.9 | 612.0 | 539.0 | 484.3 | 429.6 | 384.8 | 340.0 | 314.9 |
| 22.5° | 928.6 | 787.9 | 691.5 | 595.0 | 508.8 | 422.6 | 368.9 | 315.1 | 287.6 | 260.2 | 250.1 |
| 25° | 920.8 | 743.4 | 625.0 | 506.6 | 415.7 | 324.5 | 286.4 | 248.2 | 237.7 | 226.9 | 221.8 |
| 27.5° | 922.1 | 703.8 | 569.1 | 434.1 | 352.2 | 270.3 | 244.1 | 217.9 | 211.5 | 204.8 | 201.6 |
| 30° | 927.1 | 660.7 | 516.3 | 371.9 | 304.4 | 236.8 | 219.9 | 202.7 | 195.8 | 189.0 | 184.9 |
| 32.5° | 932.6 | 622.0 | 475.5 | 328.8 | 273.7 | 218.4 | 204.4 | 190.3 | 183.6 | 177.0 | 172.9 |
| 35° | 923.0 | 590.5 | 447.7 | 304.8 | 254.0 | 202.9 | 191.1 | 179.1 | 171.8 | 164.5 | 160.7 |
| 37.5° | 906.7 | 558.8 | 426.0 | 293.0 | 241.1 | 189.0 | 180.4 | 171.6 | 164.1 | 156.4 | 152.7 |
| 40° | 891.9 | 532.0 | 409.9 | 287.6 | 234.0 | 180.2 | 172.9 | 165.6 | 157.9 | 149.9 | 145.6 |
| 42.5° | 879.9 | 513.9 | 394.0 | 274.1 | 227.6 | 180.8 | 170.5 | 160.0 | 152.5 | 145.0 | 140.3 |
| 45° | 870.9 | 502.1 | 381.6 | 261.0 | 221.6 | 182.1 | 169.0 | 155.9 | 148.4 | 140.7 | 135.1 |
| 47.5° | 870.0 | 495.9 | 372.8 | 249.7 | 210.2 | 170.5 | 165.2 | 159.8 | 148.9 | 137.7 | 131.3 |
| 50° | 881.8 | 485.8 | 362.5 | 239.0 | 199.3 | 159.6 | 166.9 | 174.0 | 155.3 | 136.4 | 128.3 |
| 52.5° | 906.5 | 468.0 | 346.2 | 224.4 | 186.0 | 147.4 | 158.7 | 169.9 | 153.8 | 137.5 | 127.0 |
| 55° | 936.3 | 441.9 | 321.5 | 201.0 | 168.4 | 135.6 | 145.6 | 155.5 | 145.4 | 135.1 | 122.5 |
| 57.5° | 954.9 | 408.8 | 290.4 | 172.0 | 148.6 | 125.3 | 131.1 | 136.6 | 132.6 | 128.5 | 115.6 |
| 60° | 943.8 | 364.9 | 255.5 | 145.9 | 131.3 | 116.7 | 115.6 | 114.3 | 120.3 | 126.3 | 111.5 |
| 62.5° | 889.3 | 319.4 | 224.6 | 129.8 | 118.8 | 107.7 | 105.3 | 102.7 | 112.6 | 122.3 | 106.6 |
| 65° | 797.3 | 287.6 | 205.1 | 122.5 | 110.3 | 98.0 | 95.5 | 92.9 | 95.9 | 98.9 | 91.6 |
| 67.5° | 680.4 | 268.1 | 193.9 | 119.7 | 104.9 | 89.9 | 86.9 | 83.9 | 83.2 | 82.6 | 80.0 |
| 70° | 559.8 | 256.1 | 186.6 | 117.1 | 99.1 | 80.9 | 78.1 | 75.3 | 74.4 | 73.4 | 71.4 |
| 72.5° | 468.0 | 254.6 | 185.8 | 116.9 | 94.4 | 71.9 | 69.3 | 66.7 | 65.6 | 64.3 | 62.8 |
| 75° | 383.3 | 239.0 | 176.3 | 113.7 | 87.9 | 62.0 | 59.6 | 57.3 | 56.4 | 55.3 | 54.1 |
| 77.5° | 284.4 | 197.8 | 148.2 | 98.7 | 75.3 | 51.9 | 49.5 | 47.0 | 46.8 | 46.3 | 45.3 |
| 80° | 184.5 | 143.1 | 106.0 | 68.9 | 54.9 | 40.8 | 38.8 | 36.7 | 36.9 | 37.1 | 36.3 |
| 82.5° | 102.5 | 83.4 | 64.8 | 46.1 | 37.5 | 29.0 | 28.1 | 27.0 | 27.7 | 28.1 | 27.0 |
| 85° | 54.1 | 42.0 | 34.7 | 27.5 | 21.7 | 15.9 | 15.9 | 15.7 | 16.5 | 17.4 | 16.5 |
| 87.5° | 23.4 | 14.8 | 12.7 | 10.3 | 5.8 | 1.1 | 1.3 | 1.3 | 1.7 | 2.1 | 1.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P385747
 CATALOG NUMBER: GWC-SA1B-750-U-SLL

CANDELA DISTRIBUTION (continued):

| | 110° | 115° | 120° | 125° | 130° | 135° | 140° | 145° | 150° | 155° | 160° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P385747
 CATALOG NUMBER: GWC-SA1B-750-U-SLL

CANDELA DISTRIBUTION (continued):

| | 165° | 170° | 175° | 180° | 185° | 190° | 195° | 200° | 205° | 210° | 215° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 |
| 2.5° | 1477.7 | 1462.0 | 1446.1 | 1428.8 | 1432.0 | 1418.7 | 1405.4 | 1397.0 | 1388.7 | 1386.1 | 1383.5 |
| 5° | 1194.1 | 1176.3 | 1158.3 | 1142.2 | 1156.1 | 1146.7 | 1137.3 | 1136.0 | 1134.5 | 1134.5 | 1134.3 |
| 7.5° | 883.5 | 864.4 | 845.1 | 831.8 | 845.5 | 843.8 | 842.1 | 851.3 | 860.6 | 868.1 | 875.4 |
| 10° | 717.9 | 694.8 | 671.4 | 651.6 | 648.2 | 638.3 | 628.3 | 630.4 | 632.3 | 640.5 | 648.6 |
| 12.5° | 624.0 | 596.3 | 568.6 | 545.5 | 535.0 | 518.7 | 502.1 | 491.8 | 481.5 | 482.6 | 483.5 |
| 15° | 516.9 | 490.1 | 463.1 | 443.2 | 436.5 | 423.8 | 411.2 | 398.3 | 385.2 | 379.9 | 374.3 |
| 17.5° | 395.3 | 373.9 | 352.2 | 338.9 | 338.9 | 335.3 | 331.6 | 325.2 | 318.5 | 313.2 | 307.6 |
| 20° | 289.8 | 278.4 | 266.8 | 261.3 | 263.0 | 263.2 | 263.2 | 266.4 | 269.6 | 267.9 | 266.2 |
| 22.5° | 239.8 | 235.7 | 231.7 | 229.3 | 230.2 | 230.4 | 230.6 | 233.6 | 236.4 | 238.5 | 240.5 |
| 25° | 216.4 | 213.9 | 211.3 | 210.4 | 212.4 | 212.6 | 212.6 | 214.5 | 216.4 | 218.6 | 220.7 |
| 27.5° | 198.2 | 197.1 | 196.1 | 194.5 | 196.5 | 196.5 | 196.3 | 198.4 | 200.3 | 202.3 | 204.0 |
| 30° | 180.8 | 181.3 | 181.5 | 181.0 | 182.3 | 183.2 | 183.8 | 185.3 | 186.6 | 188.1 | 189.6 |
| 32.5° | 168.6 | 168.0 | 167.3 | 166.9 | 169.7 | 171.2 | 172.7 | 174.2 | 175.5 | 176.1 | 176.7 |
| 35° | 156.8 | 155.3 | 153.8 | 152.7 | 155.3 | 157.2 | 159.2 | 161.9 | 164.5 | 164.9 | 165.4 |
| 37.5° | 148.9 | 146.9 | 145.0 | 143.7 | 144.8 | 145.6 | 146.5 | 149.5 | 152.5 | 154.2 | 155.7 |
| 40° | 141.4 | 139.4 | 137.5 | 136.4 | 137.1 | 137.3 | 137.5 | 139.0 | 140.3 | 143.5 | 146.5 |
| 42.5° | 135.3 | 133.0 | 130.6 | 129.3 | 129.8 | 130.2 | 130.4 | 130.2 | 130.0 | 133.0 | 136.0 |
| 45° | 129.3 | 126.8 | 124.2 | 122.7 | 122.9 | 122.9 | 122.9 | 122.5 | 121.8 | 123.3 | 124.8 |
| 47.5° | 124.6 | 121.6 | 118.6 | 117.1 | 116.7 | 116.3 | 115.8 | 115.6 | 115.2 | 116.3 | 117.1 |
| 50° | 119.9 | 116.7 | 113.3 | 111.5 | 110.5 | 110.0 | 109.6 | 109.4 | 109.0 | 110.0 | 110.9 |
| 52.5° | 116.3 | 112.4 | 108.5 | 105.7 | 104.7 | 104.0 | 103.4 | 103.6 | 103.6 | 104.0 | 104.2 |
| 55° | 109.8 | 106.4 | 102.7 | 100.8 | 98.9 | 98.5 | 98.0 | 98.7 | 99.1 | 99.1 | 99.1 |
| 57.5° | 102.7 | 99.5 | 96.1 | 94.8 | 93.1 | 93.1 | 92.9 | 93.7 | 94.4 | 94.8 | 95.2 |
| 60° | 96.5 | 92.9 | 89.2 | 88.2 | 87.5 | 87.3 | 87.1 | 88.2 | 89.0 | 89.9 | 90.7 |
| 62.5° | 90.7 | 86.9 | 83.0 | 81.7 | 81.5 | 81.7 | 81.7 | 82.8 | 83.7 | 84.5 | 85.4 |
| 65° | 84.3 | 80.4 | 76.4 | 75.1 | 75.5 | 76.1 | 76.8 | 77.6 | 78.3 | 79.1 | 80.0 |
| 67.5° | 77.2 | 74.0 | 70.6 | 69.3 | 69.5 | 70.4 | 71.2 | 71.9 | 72.3 | 73.1 | 74.0 |
| 70° | 69.5 | 66.7 | 63.9 | 63.1 | 62.8 | 63.9 | 64.8 | 65.2 | 65.6 | 66.7 | 67.6 |
| 72.5° | 61.1 | 58.8 | 56.4 | 55.8 | 56.0 | 56.6 | 57.3 | 57.9 | 58.3 | 59.4 | 60.3 |
| 75° | 52.6 | 50.4 | 48.3 | 47.8 | 48.3 | 48.9 | 49.5 | 50.0 | 50.4 | 51.7 | 52.8 |
| 77.5° | 44.2 | 41.8 | 39.3 | 39.0 | 39.7 | 40.3 | 40.8 | 41.4 | 42.0 | 43.8 | 45.5 |
| 80° | 35.4 | 32.8 | 30.0 | 29.8 | 30.5 | 31.1 | 31.7 | 32.4 | 33.0 | 35.2 | 37.1 |
| 82.5° | 26.0 | 23.0 | 19.9 | 19.5 | 21.7 | 22.3 | 23.0 | 24.0 | 24.9 | 26.8 | 28.7 |
| 85° | 15.7 | 12.7 | 9.7 | 9.4 | 11.4 | 12.4 | 13.5 | 14.8 | 15.9 | 17.6 | 19.3 |
| 87.5° | 1.7 | 0.9 | 0.0 | 0.0 | 0.2 | 1.1 | 1.9 | 3.0 | 4.1 | 5.8 | 7.3 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P385747

CATALOG NUMBER: GWC-SA1B-750-U-SLL

CANDELA DISTRIBUTION (continued):

| | 165° | 170° | 175° | 180° | 185° | 190° | 195° | 200° | 205° | 210° | 215° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P385747
 CATALOG NUMBER: GWC-SA1B-750-U-SLL

CANDELA DISTRIBUTION (continued):

| | 220° | 225° | 230° | 235° | 240° | 245° | 250° | 255° | 260° | 265° | 270° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 |
| 2.5° | 1374.1 | 1364.4 | 1374.3 | 1383.9 | 1388.0 | 1392.1 | 1381.6 | 1370.9 | 1387.6 | 1404.1 | 1408.4 |
| 5° | 1125.7 | 1116.9 | 1123.5 | 1130.0 | 1115.6 | 1101.2 | 1099.7 | 1098.0 | 1110.5 | 1122.9 | 1124.8 |
| 7.5° | 872.6 | 869.8 | 876.0 | 882.2 | 864.0 | 845.5 | 836.5 | 827.5 | 830.5 | 833.5 | 833.1 |
| 10° | 650.6 | 652.3 | 660.0 | 667.5 | 653.4 | 639.2 | 633.0 | 626.8 | 633.6 | 640.3 | 646.5 |
| 12.5° | 487.3 | 491.0 | 499.1 | 507.1 | 501.3 | 495.3 | 495.9 | 496.6 | 504.5 | 512.2 | 519.1 |
| 15° | 378.6 | 382.9 | 388.7 | 394.2 | 394.5 | 394.5 | 400.0 | 405.4 | 404.8 | 404.1 | 408.8 |
| 17.5° | 313.4 | 319.0 | 319.6 | 320.2 | 320.5 | 320.7 | 320.2 | 319.8 | 316.6 | 313.4 | 317.0 |
| 20° | 268.3 | 270.3 | 272.0 | 273.5 | 271.6 | 269.4 | 264.0 | 258.7 | 256.5 | 254.4 | 257.8 |
| 22.5° | 244.1 | 247.5 | 245.8 | 243.9 | 240.0 | 235.9 | 231.9 | 227.6 | 227.4 | 226.9 | 228.9 |
| 25° | 223.7 | 226.5 | 223.5 | 220.5 | 217.7 | 214.9 | 212.1 | 209.3 | 209.1 | 208.9 | 209.8 |
| 27.5° | 206.8 | 209.3 | 206.6 | 203.8 | 201.4 | 199.1 | 196.9 | 194.8 | 194.3 | 193.9 | 194.1 |
| 30° | 192.2 | 194.5 | 192.2 | 189.6 | 187.9 | 186.0 | 184.5 | 183.0 | 182.8 | 182.5 | 182.5 |
| 32.5° | 179.1 | 181.5 | 179.7 | 178.0 | 176.5 | 175.0 | 174.0 | 172.9 | 171.8 | 170.7 | 168.4 |
| 35° | 167.7 | 170.1 | 169.0 | 167.7 | 166.0 | 164.3 | 162.4 | 160.2 | 157.4 | 154.4 | 153.2 |
| 37.5° | 158.1 | 160.4 | 159.4 | 158.3 | 155.9 | 153.6 | 150.1 | 146.5 | 145.6 | 144.6 | 144.4 |
| 40° | 150.4 | 154.0 | 151.9 | 149.5 | 145.9 | 142.2 | 140.5 | 138.8 | 138.4 | 137.9 | 137.5 |
| 42.5° | 141.8 | 147.4 | 143.5 | 139.6 | 136.2 | 132.8 | 132.3 | 131.9 | 131.7 | 131.5 | 131.5 |
| 45° | 131.1 | 137.1 | 133.2 | 129.1 | 127.2 | 125.3 | 125.3 | 125.3 | 125.5 | 125.5 | 125.9 |
| 47.5° | 121.0 | 124.6 | 122.7 | 120.8 | 119.7 | 118.6 | 118.8 | 119.0 | 119.7 | 120.1 | 121.2 |
| 50° | 112.4 | 113.7 | 114.1 | 114.3 | 113.7 | 113.0 | 113.5 | 113.7 | 114.3 | 114.8 | 115.6 |
| 52.5° | 106.2 | 108.1 | 108.1 | 107.9 | 107.9 | 107.9 | 108.3 | 108.8 | 109.4 | 110.0 | 110.9 |
| 55° | 102.1 | 104.9 | 104.0 | 103.2 | 103.4 | 103.4 | 103.8 | 104.2 | 104.9 | 105.3 | 106.6 |
| 57.5° | 98.2 | 101.2 | 100.4 | 99.5 | 99.5 | 99.5 | 99.7 | 100.0 | 100.6 | 101.0 | 101.9 |
| 60° | 93.7 | 96.7 | 95.9 | 94.8 | 95.0 | 95.2 | 95.5 | 95.5 | 95.9 | 96.1 | 96.1 |
| 62.5° | 88.4 | 91.4 | 90.5 | 89.4 | 90.1 | 90.5 | 90.5 | 90.5 | 90.9 | 91.2 | 90.5 |
| 65° | 82.8 | 85.6 | 84.7 | 83.9 | 84.7 | 85.4 | 85.8 | 86.0 | 85.8 | 85.6 | 84.9 |
| 67.5° | 76.8 | 79.6 | 78.7 | 77.6 | 78.7 | 79.6 | 80.4 | 81.1 | 80.4 | 79.8 | 78.9 |
| 70° | 70.4 | 73.1 | 72.1 | 71.0 | 72.1 | 73.1 | 74.0 | 74.9 | 74.0 | 73.1 | 72.9 |
| 72.5° | 63.5 | 66.7 | 65.4 | 64.1 | 65.4 | 66.7 | 67.1 | 67.6 | 66.9 | 66.3 | 65.9 |
| 75° | 56.0 | 59.2 | 58.1 | 56.8 | 57.9 | 59.0 | 59.2 | 59.4 | 59.4 | 59.2 | 57.9 |
| 77.5° | 48.0 | 50.6 | 50.0 | 49.3 | 50.0 | 50.6 | 50.6 | 50.6 | 50.8 | 50.8 | 49.1 |
| 80° | 38.6 | 40.1 | 40.3 | 40.5 | 40.8 | 41.0 | 40.8 | 40.5 | 40.1 | 39.7 | 38.6 |
| 82.5° | 28.7 | 28.7 | 30.5 | 32.0 | 32.0 | 31.7 | 31.5 | 31.1 | 30.2 | 29.2 | 26.8 |
| 85° | 18.2 | 17.2 | 19.9 | 22.5 | 22.5 | 22.3 | 21.9 | 21.2 | 19.5 | 17.6 | 15.7 |
| 87.5° | 6.2 | 5.1 | 7.9 | 10.7 | 10.9 | 10.9 | 10.5 | 10.1 | 8.4 | 6.4 | 4.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P385747
 CATALOG NUMBER: GWC-SA1B-750-U-SLL

CANDELA DISTRIBUTION (continued):

| | 220° | 225° | 230° | 235° | 240° | 245° | 250° | 255° | 260° | 265° | 270° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P385747
 CATALOG NUMBER: GWC-SA1B-750-U-SLL

CANDELA DISTRIBUTION (continued):

| | 275° | 280° | 285° | 290° | 295° | 300° | 305° | 310° | 315° | 320° | 325° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 |
| 2.5° | 1414.8 | 1417.6 | 1420.2 | 1441.2 | 1462.0 | 1486.5 | 1510.9 | 1529.6 | 1548.0 | 1567.1 | 1586.2 |
| 5° | 1131.5 | 1134.9 | 1138.3 | 1163.9 | 1189.2 | 1223.3 | 1257.4 | 1286.8 | 1316.2 | 1350.7 | 1385.2 |
| 7.5° | 838.7 | 846.2 | 853.5 | 880.7 | 907.8 | 944.4 | 980.9 | 1019.3 | 1057.5 | 1102.5 | 1147.6 |
| 10° | 658.7 | 672.9 | 686.8 | 714.7 | 742.6 | 778.8 | 814.9 | 855.0 | 895.1 | 939.5 | 983.7 |
| 12.5° | 533.2 | 552.1 | 570.8 | 604.2 | 637.7 | 681.0 | 724.1 | 768.8 | 813.2 | 852.2 | 891.2 |
| 15° | 421.3 | 441.9 | 462.2 | 497.6 | 533.0 | 580.6 | 628.0 | 676.7 | 725.2 | 772.0 | 818.7 |
| 17.5° | 328.6 | 345.6 | 362.3 | 392.3 | 422.1 | 468.2 | 514.4 | 565.4 | 616.5 | 673.5 | 730.4 |
| 20° | 265.1 | 272.2 | 279.3 | 300.9 | 322.4 | 359.9 | 397.2 | 449.4 | 501.5 | 569.7 | 637.9 |
| 22.5° | 232.3 | 235.9 | 239.4 | 249.9 | 260.2 | 284.4 | 308.4 | 354.6 | 400.5 | 474.9 | 549.1 |
| 25° | 212.6 | 215.4 | 218.1 | 225.0 | 231.9 | 243.5 | 255.0 | 287.4 | 319.8 | 393.0 | 465.9 |
| 27.5° | 194.8 | 199.1 | 203.1 | 206.3 | 209.3 | 217.3 | 225.0 | 246.2 | 267.5 | 335.7 | 403.7 |
| 30° | 181.9 | 183.4 | 184.9 | 189.8 | 194.5 | 202.7 | 210.9 | 225.7 | 240.5 | 298.2 | 355.6 |
| 32.5° | 166.9 | 169.0 | 171.2 | 176.3 | 181.5 | 189.0 | 196.5 | 208.5 | 220.3 | 269.6 | 318.7 |
| 35° | 153.4 | 155.5 | 157.7 | 162.8 | 167.7 | 175.9 | 183.8 | 193.9 | 203.8 | 246.7 | 289.6 |
| 37.5° | 145.0 | 147.1 | 149.3 | 153.8 | 158.1 | 166.2 | 174.2 | 182.1 | 189.8 | 229.5 | 269.2 |
| 40° | 137.9 | 140.1 | 142.2 | 146.5 | 150.6 | 158.5 | 166.2 | 172.9 | 179.5 | 216.6 | 253.8 |
| 42.5° | 131.7 | 134.1 | 136.4 | 140.7 | 144.8 | 151.9 | 158.9 | 167.7 | 176.3 | 205.5 | 234.4 |
| 45° | 126.6 | 128.9 | 131.1 | 135.8 | 140.5 | 147.4 | 154.2 | 166.5 | 178.7 | 199.7 | 220.7 |
| 47.5° | 121.8 | 124.4 | 126.8 | 131.9 | 137.1 | 145.6 | 154.0 | 164.3 | 174.4 | 195.2 | 216.0 |
| 50° | 117.3 | 120.3 | 123.3 | 129.6 | 135.6 | 149.9 | 164.1 | 165.6 | 166.9 | 191.5 | 216.0 |
| 52.5° | 113.0 | 116.5 | 119.9 | 127.6 | 135.1 | 151.9 | 168.6 | 163.2 | 157.7 | 184.7 | 211.7 |
| 55° | 108.8 | 111.8 | 114.5 | 124.0 | 133.4 | 145.6 | 157.9 | 150.8 | 143.5 | 171.8 | 200.1 |
| 57.5° | 103.0 | 106.2 | 109.2 | 119.3 | 129.3 | 137.9 | 146.3 | 139.9 | 133.2 | 157.2 | 181.0 |
| 60° | 97.0 | 100.6 | 104.2 | 117.1 | 129.8 | 128.3 | 126.6 | 125.3 | 123.8 | 140.9 | 158.1 |
| 62.5° | 91.6 | 95.5 | 99.3 | 116.0 | 132.8 | 122.5 | 112.2 | 113.3 | 114.1 | 126.8 | 139.4 |
| 65° | 86.2 | 90.1 | 93.7 | 102.1 | 110.5 | 106.4 | 102.3 | 104.0 | 105.5 | 118.0 | 130.4 |
| 67.5° | 80.2 | 83.7 | 86.9 | 89.7 | 92.4 | 92.9 | 93.3 | 95.0 | 96.7 | 111.5 | 126.1 |
| 70° | 73.6 | 76.4 | 79.1 | 81.1 | 82.8 | 83.7 | 84.3 | 86.4 | 88.6 | 104.7 | 120.8 |
| 72.5° | 66.1 | 68.4 | 70.6 | 72.3 | 74.0 | 74.6 | 75.1 | 77.2 | 79.4 | 96.5 | 113.7 |
| 75° | 57.9 | 59.8 | 61.6 | 63.1 | 64.6 | 65.4 | 66.3 | 67.8 | 69.3 | 87.9 | 106.4 |
| 77.5° | 48.9 | 50.8 | 52.6 | 53.8 | 54.9 | 55.8 | 56.4 | 58.3 | 60.3 | 75.9 | 91.4 |
| 80° | 38.2 | 40.5 | 42.7 | 43.8 | 44.6 | 44.8 | 44.8 | 46.5 | 48.3 | 59.4 | 70.4 |
| 82.5° | 27.0 | 29.6 | 32.0 | 32.8 | 33.7 | 33.7 | 33.7 | 35.6 | 37.5 | 45.0 | 52.3 |
| 85° | 15.9 | 18.7 | 21.2 | 22.1 | 23.0 | 23.4 | 23.6 | 24.5 | 25.1 | 30.5 | 35.6 |
| 87.5° | 4.9 | 7.3 | 9.4 | 9.9 | 10.3 | 11.2 | 12.0 | 12.2 | 12.2 | 15.9 | 19.5 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P385747
 CATALOG NUMBER: GWC-SA1B-750-U-SLL

CANDELA DISTRIBUTION (continued):

| | 275° | 280° | 285° | 290° | 295° | 300° | 305° | 310° | 315° | 320° | 325° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P385747
 CATALOG NUMBER: GWC-SA1B-750-U-SLL

CANDELA DISTRIBUTION (continued):

| | 330° | 335° | 340° | 345° | 350° | 355° | 360° |
|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 | 1634.5 |
| 2.5° | 1608.1 | 1630.0 | 1655.5 | 1680.8 | 1702.5 | 1724.1 | 1742.2 |
| 5° | 1429.2 | 1473.2 | 1527.0 | 1580.6 | 1628.5 | 1676.3 | 1731.9 |
| 7.5° | 1204.4 | 1261.2 | 1331.0 | 1400.7 | 1468.2 | 1535.6 | 1621.0 |
| 10° | 1041.6 | 1099.3 | 1173.1 | 1246.7 | 1322.6 | 1398.3 | 1494.8 |
| 12.5° | 938.2 | 985.0 | 1056.4 | 1127.8 | 1217.1 | 1306.1 | 1399.0 |
| 15° | 870.0 | 921.1 | 990.6 | 1060.0 | 1157.6 | 1255.2 | 1362.1 |
| 17.5° | 797.3 | 864.0 | 953.0 | 1042.0 | 1157.6 | 1273.0 | 1399.0 |
| 20° | 721.1 | 804.2 | 919.6 | 1035.0 | 1190.7 | 1346.2 | 1506.8 |
| 22.5° | 645.2 | 741.3 | 889.3 | 1037.1 | 1240.7 | 1444.0 | 1660.9 |
| 25° | 576.8 | 687.7 | 870.9 | 1053.8 | 1313.4 | 1572.7 | 1841.7 |
| 27.5° | 524.9 | 645.9 | 863.4 | 1080.6 | 1405.6 | 1730.6 | 2038.4 |
| 30° | 478.8 | 601.9 | 854.3 | 1106.8 | 1494.4 | 1881.8 | 2192.2 |
| 32.5° | 438.9 | 559.0 | 837.0 | 1114.7 | 1556.4 | 1998.0 | 2322.4 |
| 35° | 407.5 | 525.5 | 807.8 | 1090.1 | 1595.2 | 2100.4 | 2457.9 |
| 37.5° | 380.5 | 491.8 | 774.6 | 1057.3 | 1629.8 | 2202.2 | 2610.4 |
| 40° | 354.8 | 455.8 | 746.0 | 1036.0 | 1677.4 | 2318.7 | 2771.5 |
| 42.5° | 330.3 | 426.2 | 723.1 | 1019.9 | 1721.6 | 2423.0 | 2912.4 |
| 45° | 312.1 | 403.5 | 702.7 | 1001.7 | 1750.1 | 2498.5 | 3018.6 |
| 47.5° | 303.1 | 390.0 | 691.8 | 993.3 | 1778.6 | 2563.7 | 3106.8 |
| 50° | 301.8 | 387.6 | 704.2 | 1020.8 | 1840.4 | 2659.8 | 3207.6 |
| 52.5° | 301.6 | 391.5 | 740.0 | 1088.6 | 1955.1 | 2821.5 | 3316.8 |
| 55° | 297.1 | 393.8 | 782.7 | 1171.4 | 2109.2 | 3046.7 | 3513.0 |
| 57.5° | 283.4 | 385.7 | 826.7 | 1267.5 | 2272.0 | 3276.2 | 3734.2 |
| 60° | 262.1 | 365.9 | 862.9 | 1359.7 | 2381.4 | 3402.8 | 3819.3 |
| 62.5° | 235.5 | 331.4 | 874.9 | 1418.3 | 2378.4 | 3338.4 | 3733.5 |
| 65° | 212.8 | 295.1 | 835.5 | 1375.6 | 2258.0 | 3140.2 | 3563.9 |
| 67.5° | 192.6 | 258.9 | 736.8 | 1214.5 | 2041.6 | 2868.5 | 3348.1 |
| 70° | 178.0 | 235.1 | 609.6 | 984.1 | 1770.7 | 2557.0 | 3098.2 |
| 72.5° | 168.8 | 223.7 | 497.0 | 770.0 | 1436.9 | 2103.6 | 2650.1 |
| 75° | 156.2 | 205.9 | 390.0 | 573.8 | 1099.7 | 1625.7 | 2001.7 |
| 77.5° | 132.6 | 173.5 | 293.9 | 414.2 | 806.9 | 1199.5 | 1392.1 |
| 80° | 102.3 | 134.1 | 202.1 | 270.1 | 555.3 | 840.6 | 949.2 |
| 82.5° | 72.9 | 93.5 | 122.5 | 151.4 | 368.9 | 586.2 | 595.2 |
| 85° | 45.0 | 54.5 | 70.1 | 85.8 | 244.1 | 402.4 | 335.3 |
| 87.5° | 24.2 | 29.0 | 37.1 | 45.0 | 78.1 | 111.1 | 63.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P385747

CATALOG NUMBER: GWC-SA1B-750-U-SLL

CANDELA DISTRIBUTION (continued):

| | 330° | 335° | 340° | 345° | 350° | 355° | 360° |
|--------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245982

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





--- HS — SS



u



| | | | | | | | | | | | |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





| | | | | | | | | | | | | |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





| | | | | | | | | | | | |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





| | | | | | | | | | | | |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





| | | | | | | | | | | | |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





| | | | | | | | | | | | |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





| | | | | | | | |
|------|-----|-----|-----|-----|-----|-----|-----|
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
|------|-----|-----|-----|-----|-----|-----|-----|

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)