

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P386643

Luminaire Tested: **GWC-SA2B-750-U-SLL**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P386643
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-26)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GWC-SA2B-750-U-SLL
Description: GALLEON WALL LUMINAIRE
(2) 70 CRI, 5000K, 800mA LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT
ELIMINATOR LEFT OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10482 lumens
Efficiency: N/A
Efficacy: 121.9 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B2 - U0 - G3


Input Watts (W): 86
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P386643
 CATALOG NUMBER: GWC-SA2B-750-U-SLL

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 10 fc
 Type III - Medium - N/A

REPORT NUMBER: P386643
CATALOG NUMBER: GWC-SA2B-750-U-SLL

Luminous Intensity Polar Plot



— Vertical Plane Through 75-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical



REPORT NUMBER: P386643

CATALOG NUMBER: GWC-SA2B-750-U-SLL


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 1846.1 | 0.0 | 1846.1 |
| | % Fixture | 17.6 | 0.0 | 17.6 |
| Street Side | Lumens | 8635.9 | 0.0 | 8635.9 |
| | % Fixture | 82.4 | 0.0 | 82.4 |
| Total | Lumens | 10482.0 | 0.0 | 10482.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 246.5 | 2.4 |
| 10°-20° | 512.0 | 4.9 |
| 20°-30° | 728.2 | 6.9 |
| 30°-40° | 1049.3 | 10.0 |
| 40°-50° | 1478.7 | 14.1 |
| 50°-60° | 2055.7 | 19.6 |
| 60°-70° | 2486.0 | 23.7 |
| 70°-80° | 1528.1 | 14.6 |
| 80°-90° | 397.6 | 3.8 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 10482.0 | 100.0 |
| 0°-180° | 10482.0 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P386643


CATALOG NUMBER: GWC-SA2B-750-U-SLL

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1040.8 | 9.9 | | | |
| FM (30°-60°) | 3745.7 | 35.7 | | | |
| FH (60°-80°) | 3496.4 | 33.4 | | | G2/5000 |
| FVH (80°-90°) | 353.0 | 3.4 | | | G3/500 |
| BL (0°-30°) | 445.9 | 4.3 | B1/500 | | |
| BM (30°-60°) | 838.0 | 8.0 | B1/1000 | | |
| BH (60°-80°) | 517.6 | 4.9 | B2/1000 | | G2/1000 |
| BVH (80°-90°) | 44.7 | 0.4 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G3

Type III Medium





REPORT NUMBER: P386643

CATALOG NUMBER: GWC-SA2B-750-U-SLL

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 10° | 15° | 20° | 25° | 30° | 35° | 40° | 45° | 50° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 |
| 2.5° | 3403.8 | 3448.6 | 3479.6 | 3510.2 | 3534.1 | 3557.6 | 3591.9 | 3626.3 | 3633.0 | 3639.3 | 3625.9 |
| 5° | 3383.7 | 3493.0 | 3586.1 | 3678.7 | 3764.6 | 3850.5 | 3902.1 | 3953.6 | 3964.1 | 3974.6 | 3942.3 |
| 7.5° | 3167.0 | 3328.3 | 3489.7 | 3651.0 | 3799.0 | 3946.9 | 4037.0 | 4126.7 | 4147.2 | 4167.3 | 4114.5 |
| 10° | 2920.6 | 3108.3 | 3306.5 | 3504.8 | 3699.6 | 3894.5 | 4024.8 | 4155.2 | 4181.2 | 4207.1 | 4141.3 |
| 12.5° | 2733.2 | 2938.2 | 3149.8 | 3361.4 | 3567.2 | 3772.6 | 3907.5 | 4042.4 | 4074.7 | 4107.0 | 4059.2 |
| 15° | 2661.2 | 2885.8 | 3084.8 | 3283.9 | 3463.3 | 3642.2 | 3752.9 | 3863.1 | 3876.5 | 3889.5 | 3881.9 |
| 17.5° | 2733.2 | 2980.9 | 3161.1 | 3340.9 | 3438.6 | 3535.8 | 3580.2 | 3624.2 | 3638.9 | 3653.1 | 3672.4 |
| 20° | 2944.0 | 3211.4 | 3338.4 | 3465.0 | 3460.8 | 3456.2 | 3434.8 | 3413.0 | 3409.2 | 3405.4 | 3459.9 |
| 22.5° | 3244.9 | 3555.5 | 3606.2 | 3656.5 | 3538.7 | 3421.0 | 3349.3 | 3277.2 | 3263.0 | 3248.3 | 3306.1 |
| 25° | 3598.2 | 3928.9 | 3919.7 | 3910.0 | 3685.8 | 3461.2 | 3324.6 | 3187.9 | 3172.0 | 3156.1 | 3205.5 |
| 27.5° | 3982.5 | 4298.5 | 4238.2 | 4177.8 | 3873.1 | 3568.5 | 3370.2 | 3172.0 | 3156.1 | 3140.2 | 3183.8 |
| 30° | 4283.0 | 4569.6 | 4472.8 | 4376.0 | 4031.1 | 3686.2 | 3450.7 | 3215.2 | 3189.2 | 3162.8 | 3216.4 |
| 32.5° | 4537.4 | 4781.3 | 4651.4 | 4521.5 | 4159.4 | 3797.3 | 3542.5 | 3287.7 | 3247.0 | 3206.4 | 3278.0 |
| 35° | 4802.2 | 4992.5 | 4809.8 | 4626.6 | 4273.8 | 3920.5 | 3651.0 | 3381.1 | 3331.3 | 3281.4 | 3379.9 |
| 37.5° | 5100.2 | 5258.2 | 4995.9 | 4733.1 | 4402.4 | 4071.8 | 3813.6 | 3555.1 | 3503.9 | 3452.8 | 3578.5 |
| 40° | 5414.9 | 5546.5 | 5196.6 | 4846.7 | 4543.2 | 4239.8 | 4038.7 | 3837.1 | 3788.5 | 3739.5 | 3892.0 |
| 42.5° | 5690.3 | 5786.2 | 5383.5 | 4980.8 | 4713.0 | 4444.8 | 4303.1 | 4161.0 | 4160.6 | 4159.8 | 4314.4 |
| 45° | 5897.7 | 5981.1 | 5539.4 | 5097.3 | 4878.5 | 4659.3 | 4585.6 | 4511.8 | 4570.9 | 4630.0 | 4770.0 |
| 47.5° | 6070.0 | 6126.5 | 5670.2 | 5213.4 | 5067.9 | 4922.5 | 4933.4 | 4944.3 | 5064.6 | 5184.9 | 5275.0 |
| 50° | 6266.9 | 6221.2 | 5788.8 | 5355.8 | 5311.0 | 5266.2 | 5364.2 | 5461.9 | 5600.2 | 5738.0 | 5799.2 |
| 52.5° | 6480.2 | 6359.1 | 5949.7 | 5539.8 | 5590.1 | 5640.4 | 5839.9 | 6039.4 | 6178.9 | 6318.5 | 6341.5 |
| 55° | 6863.7 | 6678.0 | 6245.6 | 5812.6 | 5909.4 | 6005.8 | 6298.8 | 6591.3 | 6700.3 | 6809.2 | 6817.6 |
| 57.5° | 7295.8 | 7131.1 | 6660.0 | 6189.0 | 6292.9 | 6396.8 | 6735.0 | 7072.8 | 7190.6 | 7307.9 | 7291.6 |
| 60° | 7462.1 | 7470.1 | 7053.5 | 6636.6 | 6741.3 | 6846.1 | 7175.5 | 7504.9 | 7640.2 | 7775.2 | 7739.2 |
| 62.5° | 7294.5 | 7491.1 | 7268.5 | 7045.6 | 7140.7 | 7235.4 | 7558.1 | 7880.8 | 8019.5 | 8158.2 | 8095.4 |
| 65° | 6963.0 | 7157.9 | 7257.6 | 7357.4 | 7388.8 | 7420.2 | 7721.6 | 8022.5 | 8128.9 | 8234.9 | 8203.1 |
| 67.5° | 6541.4 | 6699.0 | 7066.9 | 7434.5 | 7371.2 | 7307.9 | 7449.1 | 7590.4 | 7699.8 | 7809.1 | 7791.1 |
| 70° | 6053.2 | 6240.9 | 6731.7 | 7222.4 | 6911.5 | 6600.1 | 6541.8 | 6483.6 | 6601.8 | 6719.5 | 6646.6 |
| 72.5° | 5177.7 | 5461.0 | 5984.5 | 6507.5 | 5934.6 | 5361.7 | 5162.6 | 4963.6 | 5113.2 | 5262.8 | 5146.7 |
| 75° | 3910.9 | 4286.8 | 4865.1 | 5443.0 | 4759.5 | 4076.0 | 3810.3 | 3544.6 | 3673.2 | 3801.9 | 3722.3 |
| 77.5° | 2719.8 | 3191.3 | 3760.8 | 4330.4 | 3635.5 | 2940.3 | 2742.9 | 2545.1 | 2583.6 | 2621.8 | 2608.4 |
| 80° | 1854.4 | 2164.5 | 2561.8 | 2958.7 | 2496.0 | 2033.4 | 2048.9 | 2064.0 | 2045.9 | 2027.5 | 2054.3 |
| 82.5° | 1162.9 | 1381.3 | 1688.1 | 1994.4 | 1748.8 | 1503.2 | 1644.1 | 1784.9 | 1715.7 | 1646.1 | 1672.1 |
| 85° | 655.0 | 788.3 | 1088.4 | 1388.0 | 1293.7 | 1199.0 | 1281.5 | 1363.7 | 1256.4 | 1149.1 | 1196.5 |
| 87.5° | 124.9 | 207.9 | 602.2 | 996.2 | 904.4 | 812.6 | 706.1 | 599.7 | 457.6 | 315.6 | 461.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386643
 CATALOG NUMBER: GWC-SA2B-750-U-SLL

CANDELA DISTRIBUTION (continued):

| | 0° | 5° | 10° | 15° | 20° | 25° | 30° | 35° | 40° | 45° | 50° |
|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386643

CATALOG NUMBER: GWC-SA2B-750-U-SLL

CANDELA DISTRIBUTION (continued):

| | 55° | 60° | 65° | 70° | 75° | 80° | 85° | 90° | 95° | 100° | 105° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 |
| 2.5° | 3612.5 | 3605.3 | 3598.2 | 3572.7 | 3546.7 | 3508.1 | 3476.3 | 3421.0 | 3390.8 | 3345.1 | 3299.4 |
| 5° | 3909.6 | 3864.3 | 3819.1 | 3741.1 | 3662.8 | 3575.6 | 3475.4 | 3364.4 | 3280.6 | 3171.6 | 3062.6 |
| 7.5° | 4061.7 | 3956.1 | 3850.1 | 3700.5 | 3550.4 | 3415.5 | 3257.1 | 3109.6 | 2983.9 | 2842.2 | 2700.6 |
| 10° | 4075.6 | 3917.1 | 3758.3 | 3563.9 | 3369.0 | 3205.1 | 3022.8 | 2859.0 | 2708.1 | 2545.5 | 2382.5 |
| 12.5° | 4011.0 | 3842.5 | 3673.7 | 3459.5 | 3244.9 | 3058.9 | 2862.7 | 2679.2 | 2512.0 | 2333.0 | 2153.7 |
| 15° | 3874.4 | 3739.9 | 3604.9 | 3404.2 | 3203.4 | 3015.7 | 2825.4 | 2607.9 | 2418.9 | 2235.8 | 2052.2 |
| 17.5° | 3691.3 | 3627.6 | 3563.4 | 3418.4 | 3273.0 | 3110.4 | 2926.0 | 2670.8 | 2449.5 | 2250.5 | 2051.4 |
| 20° | 3514.0 | 3537.5 | 3560.5 | 3502.7 | 3444.8 | 3314.5 | 3153.6 | 2866.9 | 2584.5 | 2324.2 | 2063.6 |
| 22.5° | 3363.5 | 3476.3 | 3588.6 | 3633.4 | 3677.8 | 3599.5 | 3473.8 | 3142.3 | 2768.4 | 2428.6 | 2088.7 |
| 25° | 3254.6 | 3441.5 | 3628.4 | 3777.6 | 3926.4 | 3891.6 | 3794.8 | 3476.7 | 3012.3 | 2579.0 | 2145.3 |
| 27.5° | 3227.3 | 3456.6 | 3685.8 | 3917.1 | 4148.1 | 4180.3 | 4153.5 | 3829.1 | 3303.2 | 2765.9 | 2228.2 |
| 30° | 3270.1 | 3502.3 | 3734.0 | 4015.6 | 4296.8 | 4425.5 | 4461.5 | 4122.9 | 3635.5 | 2983.9 | 2331.8 |
| 32.5° | 3349.7 | 3577.3 | 3804.8 | 4111.6 | 4417.9 | 4612.4 | 4727.2 | 4391.5 | 3867.3 | 3148.1 | 2428.6 |
| 35° | 3478.4 | 3691.3 | 3904.2 | 4223.5 | 4542.8 | 4794.3 | 5003.8 | 4669.0 | 4073.0 | 3263.0 | 2452.5 |
| 37.5° | 3703.8 | 3887.0 | 4070.1 | 4365.1 | 4659.8 | 4985.8 | 5300.5 | 4974.5 | 4295.6 | 3373.6 | 2451.2 |
| 40° | 4044.5 | 4174.0 | 4303.1 | 4552.5 | 4801.4 | 5211.7 | 5636.6 | 5315.2 | 4541.6 | 3493.5 | 2445.3 |
| 42.5° | 4469.1 | 4535.7 | 4601.9 | 4799.3 | 4996.7 | 5447.6 | 5941.7 | 5648.4 | 4776.3 | 3604.9 | 2433.6 |
| 45° | 4909.5 | 4927.1 | 4944.7 | 5069.2 | 5193.2 | 5634.5 | 6149.6 | 5898.6 | 4981.2 | 3701.7 | 2421.9 |
| 47.5° | 5364.6 | 5304.3 | 5243.9 | 5293.4 | 5342.9 | 5777.9 | 6297.9 | 6088.4 | 5187.0 | 3809.0 | 2430.7 |
| 50° | 5860.4 | 5692.4 | 5524.3 | 5498.3 | 5472.3 | 5921.2 | 6472.7 | 6329.8 | 5434.2 | 3965.3 | 2496.5 |
| 52.5° | 6364.2 | 6087.1 | 5810.1 | 5707.5 | 5604.4 | 6092.2 | 6704.4 | 6630.3 | 5787.1 | 4207.6 | 2627.6 |
| 55° | 6826.0 | 6473.5 | 6121.1 | 5982.8 | 5844.5 | 6353.7 | 6987.3 | 7071.6 | 6239.3 | 4517.3 | 2794.8 |
| 57.5° | 7274.8 | 6875.4 | 6476.0 | 6347.8 | 6219.6 | 6738.0 | 7345.6 | 7467.6 | 6696.1 | 4814.4 | 2932.3 |
| 60° | 7703.1 | 7307.9 | 6912.3 | 6809.6 | 6706.5 | 7215.7 | 7732.9 | 7644.0 | 6931.6 | 4953.5 | 2975.0 |
| 62.5° | 8032.5 | 7718.2 | 7403.9 | 7349.8 | 7295.3 | 7698.9 | 8030.4 | 7575.3 | 6782.0 | 4816.5 | 2851.0 |
| 65° | 8171.2 | 7992.3 | 7812.9 | 7863.6 | 7913.9 | 8064.4 | 8104.6 | 7374.1 | 6311.8 | 4432.6 | 2553.5 |
| 67.5° | 7772.7 | 7809.1 | 7845.6 | 8058.5 | 8271.0 | 8167.5 | 7884.2 | 6977.7 | 5642.5 | 3888.6 | 2134.8 |
| 70° | 6573.3 | 6792.0 | 7010.4 | 7514.1 | 8017.4 | 7787.8 | 7293.7 | 6266.1 | 4837.0 | 3262.1 | 1686.8 |
| 72.5° | 5030.2 | 5276.2 | 5521.8 | 6269.4 | 7016.7 | 6805.0 | 6199.9 | 5146.7 | 3878.2 | 2605.0 | 1331.4 |
| 75° | 3642.2 | 3920.1 | 4197.5 | 5022.3 | 5847.0 | 5553.2 | 4637.5 | 3685.0 | 2945.7 | 1988.5 | 1030.9 |
| 77.5° | 2594.5 | 2780.6 | 2966.7 | 3781.4 | 4595.6 | 4117.0 | 3086.9 | 2479.7 | 2038.8 | 1382.1 | 725.0 |
| 80° | 2081.2 | 2024.2 | 1967.2 | 2421.0 | 2874.9 | 2795.3 | 2041.8 | 1592.5 | 1411.0 | 926.2 | 441.3 |
| 82.5° | 1697.7 | 1558.6 | 1419.4 | 1633.2 | 1846.9 | 1835.2 | 1416.9 | 1168.4 | 1050.2 | 643.7 | 237.2 |
| 85° | 1243.4 | 1187.7 | 1131.9 | 1320.9 | 1509.9 | 1348.6 | 959.7 | 742.6 | 818.9 | 474.0 | 129.1 |
| 87.5° | 606.4 | 692.7 | 778.7 | 1001.6 | 1224.1 | 919.0 | 291.3 | 144.2 | 199.5 | 131.2 | 62.4 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386643

CATALOG NUMBER: GWC-SA2B-750-U-SLL

CANDELA DISTRIBUTION (continued):

| | 55° | 60° | 65° | 70° | 75° | 80° | 85° | 90° | 95° | 100° | 105° |
|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386643

CATALOG NUMBER: GWC-SA2B-750-U-SLL

CANDELA DISTRIBUTION (continued):

| | 110° | 115° | 120° | 125° | 130° | 135° | 140° | 145° | 150° | 155° | 160° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 |
| 2.5° | 3265.5 | 3231.1 | 3192.1 | 3153.2 | 3108.7 | 3063.9 | 3037.5 | 3010.7 | 2981.8 | 2952.8 | 2920.2 |
| 5° | 2990.6 | 2918.5 | 2836.8 | 2755.0 | 2674.2 | 2593.3 | 2549.7 | 2506.1 | 2460.0 | 2413.5 | 2373.3 |
| 7.5° | 2595.8 | 2490.6 | 2377.4 | 2263.9 | 2163.3 | 2062.3 | 1999.9 | 1937.0 | 1880.0 | 1822.6 | 1774.4 |
| 10° | 2248.4 | 2114.3 | 2000.7 | 1886.7 | 1810.8 | 1735.0 | 1677.6 | 1620.2 | 1564.8 | 1509.1 | 1455.9 |
| 12.5° | 2019.5 | 1885.4 | 1813.4 | 1741.3 | 1678.4 | 1615.6 | 1549.3 | 1482.7 | 1406.9 | 1330.6 | 1274.8 |
| 15° | 1930.3 | 1808.3 | 1728.3 | 1647.8 | 1563.6 | 1478.9 | 1397.6 | 1316.3 | 1226.6 | 1137.0 | 1073.7 |
| 17.5° | 1891.7 | 1732.1 | 1620.2 | 1507.9 | 1396.8 | 1285.7 | 1191.4 | 1097.2 | 999.1 | 901.0 | 836.9 |
| 20° | 1851.1 | 1638.6 | 1488.6 | 1338.1 | 1195.6 | 1053.1 | 946.3 | 839.4 | 751.8 | 664.2 | 615.2 |
| 22.5° | 1814.2 | 1539.3 | 1351.1 | 1162.5 | 994.1 | 825.6 | 720.8 | 615.6 | 562.0 | 508.3 | 488.6 |
| 25° | 1799.1 | 1452.5 | 1221.2 | 989.9 | 812.2 | 634.1 | 559.5 | 484.9 | 464.3 | 443.4 | 433.3 |
| 27.5° | 1801.6 | 1375.0 | 1111.8 | 848.2 | 688.1 | 528.0 | 476.9 | 425.8 | 413.2 | 400.2 | 393.9 |
| 30° | 1811.3 | 1290.8 | 1008.7 | 726.7 | 594.7 | 462.7 | 429.6 | 396.0 | 382.6 | 369.2 | 361.2 |
| 32.5° | 1822.2 | 1215.3 | 929.1 | 642.4 | 534.7 | 426.6 | 399.4 | 371.7 | 358.7 | 345.7 | 337.8 |
| 35° | 1803.3 | 1153.7 | 874.6 | 595.5 | 496.2 | 396.4 | 373.4 | 349.9 | 335.7 | 321.4 | 313.9 |
| 37.5° | 1771.5 | 1091.7 | 832.3 | 572.5 | 471.0 | 369.2 | 352.4 | 335.3 | 320.6 | 305.5 | 298.4 |
| 40° | 1742.5 | 1039.3 | 800.9 | 562.0 | 457.2 | 352.0 | 337.8 | 323.5 | 308.4 | 292.9 | 284.6 |
| 42.5° | 1719.1 | 1004.1 | 769.9 | 535.6 | 444.6 | 353.3 | 333.2 | 312.6 | 298.0 | 283.3 | 274.1 |
| 45° | 1701.5 | 981.1 | 745.5 | 510.0 | 432.9 | 355.8 | 330.2 | 304.7 | 290.0 | 274.9 | 264.0 |
| 47.5° | 1699.8 | 968.9 | 728.4 | 487.8 | 410.7 | 333.2 | 322.7 | 312.2 | 290.8 | 269.0 | 256.5 |
| 50° | 1722.8 | 949.2 | 708.2 | 466.9 | 389.3 | 311.8 | 326.0 | 339.9 | 303.4 | 266.5 | 250.6 |
| 52.5° | 1771.0 | 914.4 | 676.4 | 438.4 | 363.3 | 287.9 | 310.1 | 331.9 | 300.5 | 268.6 | 248.1 |
| 55° | 1829.3 | 863.3 | 628.2 | 392.7 | 329.0 | 264.9 | 284.6 | 303.8 | 284.1 | 264.0 | 239.3 |
| 57.5° | 1865.7 | 798.8 | 567.4 | 336.1 | 290.4 | 244.7 | 256.1 | 267.0 | 259.0 | 251.0 | 225.9 |
| 60° | 1844.0 | 712.9 | 499.1 | 285.0 | 256.5 | 228.0 | 225.9 | 223.4 | 235.1 | 246.8 | 217.9 |
| 62.5° | 1737.5 | 624.0 | 438.8 | 253.5 | 232.2 | 210.4 | 205.8 | 200.7 | 220.0 | 238.9 | 208.3 |
| 65° | 1557.7 | 562.0 | 400.6 | 239.3 | 215.4 | 191.5 | 186.5 | 181.5 | 187.3 | 193.2 | 178.9 |
| 67.5° | 1329.3 | 523.9 | 378.8 | 233.8 | 204.9 | 175.6 | 169.7 | 163.9 | 162.6 | 161.3 | 156.3 |
| 70° | 1093.8 | 500.4 | 364.6 | 228.8 | 193.6 | 158.0 | 152.5 | 147.1 | 145.4 | 143.3 | 139.6 |
| 72.5° | 914.4 | 497.4 | 362.9 | 228.4 | 184.4 | 140.4 | 135.4 | 130.3 | 128.2 | 125.7 | 122.8 |
| 75° | 748.9 | 466.9 | 344.5 | 222.1 | 171.8 | 121.1 | 116.5 | 111.9 | 110.2 | 108.1 | 105.6 |
| 77.5° | 555.7 | 386.4 | 289.6 | 192.8 | 147.1 | 101.4 | 96.8 | 91.8 | 91.4 | 90.5 | 88.4 |
| 80° | 360.4 | 279.5 | 207.0 | 134.5 | 107.3 | 79.6 | 75.9 | 71.7 | 72.1 | 72.5 | 70.8 |
| 82.5° | 200.3 | 163.0 | 126.6 | 90.1 | 73.3 | 56.6 | 54.9 | 52.8 | 54.1 | 54.9 | 52.8 |
| 85° | 105.6 | 82.1 | 67.9 | 53.6 | 42.3 | 31.0 | 31.0 | 30.6 | 32.3 | 33.9 | 32.3 |
| 87.5° | 45.7 | 28.9 | 24.7 | 20.1 | 11.3 | 2.1 | 2.5 | 2.5 | 3.4 | 4.2 | 3.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386643
 CATALOG NUMBER: GWC-SA2B-750-U-SLL

CANDELA DISTRIBUTION (continued):

| | 110° | 115° | 120° | 125° | 130° | 135° | 140° | 145° | 150° | 155° | 160° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386643

CATALOG NUMBER: GWC-SA2B-750-U-SLL

CANDELA DISTRIBUTION (continued):

| | 165° | 170° | 175° | 180° | 185° | 190° | 195° | 200° | 205° | 210° | 215° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 |
| 2.5° | 2887.0 | 2856.5 | 2825.4 | 2791.5 | 2797.8 | 2771.8 | 2745.8 | 2729.5 | 2713.1 | 2708.1 | 2703.1 |
| 5° | 2333.0 | 2298.2 | 2263.0 | 2231.6 | 2258.8 | 2240.4 | 2222.0 | 2219.4 | 2216.5 | 2216.5 | 2216.1 |
| 7.5° | 1726.2 | 1688.9 | 1651.2 | 1625.2 | 1652.0 | 1648.7 | 1645.3 | 1663.3 | 1681.3 | 1696.0 | 1710.3 |
| 10° | 1402.7 | 1357.4 | 1311.7 | 1273.2 | 1266.5 | 1247.2 | 1227.5 | 1231.7 | 1235.4 | 1251.4 | 1267.3 |
| 12.5° | 1219.1 | 1165.0 | 1111.0 | 1065.7 | 1045.2 | 1013.3 | 981.1 | 961.0 | 940.8 | 942.9 | 944.6 |
| 15° | 1010.0 | 957.6 | 904.8 | 865.8 | 852.8 | 828.1 | 803.4 | 778.2 | 752.7 | 742.2 | 731.3 |
| 17.5° | 772.4 | 730.5 | 688.1 | 662.1 | 662.1 | 655.0 | 647.9 | 635.3 | 622.3 | 611.9 | 601.0 |
| 20° | 566.2 | 544.0 | 521.3 | 510.4 | 513.8 | 514.2 | 514.2 | 520.5 | 526.8 | 523.4 | 520.1 |
| 22.5° | 468.5 | 460.6 | 452.6 | 448.0 | 449.7 | 450.1 | 450.5 | 456.4 | 461.8 | 466.0 | 469.8 |
| 25° | 422.9 | 417.8 | 412.8 | 411.1 | 414.9 | 415.3 | 415.3 | 419.1 | 422.9 | 427.0 | 431.2 |
| 27.5° | 387.2 | 385.1 | 383.0 | 380.1 | 383.9 | 383.9 | 383.5 | 387.6 | 391.4 | 395.2 | 398.5 |
| 30° | 353.3 | 354.1 | 354.5 | 353.7 | 356.2 | 357.9 | 359.2 | 362.1 | 364.6 | 367.5 | 370.5 |
| 32.5° | 329.4 | 328.1 | 326.9 | 326.0 | 331.5 | 334.4 | 337.4 | 340.3 | 342.8 | 344.1 | 345.3 |
| 35° | 306.3 | 303.4 | 300.5 | 298.4 | 303.4 | 307.2 | 311.0 | 316.4 | 321.4 | 322.3 | 323.1 |
| 37.5° | 290.8 | 287.1 | 283.3 | 280.8 | 282.9 | 284.6 | 286.2 | 292.1 | 298.0 | 301.3 | 304.3 |
| 40° | 276.2 | 272.4 | 268.6 | 266.5 | 267.8 | 268.2 | 268.6 | 271.6 | 274.1 | 280.4 | 286.2 |
| 42.5° | 264.4 | 259.8 | 255.2 | 252.7 | 253.5 | 254.4 | 254.8 | 254.4 | 254.0 | 259.8 | 265.7 |
| 45° | 252.7 | 247.7 | 242.6 | 239.7 | 240.1 | 240.1 | 240.1 | 239.3 | 238.0 | 241.0 | 243.9 |
| 47.5° | 243.5 | 237.6 | 231.8 | 228.8 | 228.0 | 227.1 | 226.3 | 225.9 | 225.0 | 227.1 | 228.8 |
| 50° | 234.3 | 228.0 | 221.3 | 217.9 | 215.8 | 215.0 | 214.1 | 213.7 | 212.9 | 215.0 | 216.7 |
| 52.5° | 227.1 | 219.6 | 212.1 | 206.6 | 204.5 | 203.3 | 202.0 | 202.4 | 202.4 | 203.3 | 203.7 |
| 55° | 214.6 | 207.9 | 200.7 | 197.0 | 193.2 | 192.4 | 191.5 | 192.8 | 193.6 | 193.6 | 193.6 |
| 57.5° | 200.7 | 194.5 | 187.7 | 185.2 | 181.9 | 181.9 | 181.5 | 183.1 | 184.4 | 185.2 | 186.1 |
| 60° | 188.6 | 181.5 | 174.3 | 172.2 | 171.0 | 170.6 | 170.1 | 172.2 | 173.9 | 175.6 | 177.3 |
| 62.5° | 177.3 | 169.7 | 162.2 | 159.7 | 159.3 | 159.7 | 159.7 | 161.8 | 163.4 | 165.1 | 166.8 |
| 65° | 164.7 | 157.2 | 149.2 | 146.7 | 147.5 | 148.8 | 150.0 | 151.7 | 153.0 | 154.6 | 156.3 |
| 67.5° | 150.9 | 144.6 | 137.9 | 135.4 | 135.8 | 137.5 | 139.1 | 140.4 | 141.2 | 142.9 | 144.6 |
| 70° | 135.8 | 130.3 | 124.9 | 123.2 | 122.8 | 124.9 | 126.6 | 127.4 | 128.2 | 130.3 | 132.0 |
| 72.5° | 119.4 | 114.8 | 110.2 | 109.0 | 109.4 | 110.6 | 111.9 | 113.2 | 114.0 | 116.1 | 117.8 |
| 75° | 102.7 | 98.5 | 94.3 | 93.5 | 94.3 | 95.6 | 96.8 | 97.6 | 98.5 | 101.0 | 103.1 |
| 77.5° | 86.3 | 81.7 | 76.7 | 76.3 | 77.5 | 78.8 | 79.6 | 80.9 | 82.1 | 85.5 | 88.8 |
| 80° | 69.1 | 64.1 | 58.7 | 58.3 | 59.5 | 60.8 | 62.0 | 63.3 | 64.5 | 68.7 | 72.5 |
| 82.5° | 50.7 | 44.8 | 39.0 | 38.1 | 42.3 | 43.6 | 44.8 | 46.9 | 48.6 | 52.4 | 56.2 |
| 85° | 30.6 | 24.7 | 18.9 | 18.4 | 22.2 | 24.3 | 26.4 | 28.9 | 31.0 | 34.4 | 37.7 |
| 87.5° | 3.4 | 1.7 | 0.0 | 0.0 | 0.4 | 2.1 | 3.8 | 5.9 | 8.0 | 11.3 | 14.2 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386643
 CATALOG NUMBER: GWC-SA2B-750-U-SLL

CANDELA DISTRIBUTION (continued):

| | 165° | 170° | 175° | 180° | 185° | 190° | 195° | 200° | 205° | 210° | 215° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386643

CATALOG NUMBER: GWC-SA2B-750-U-SLL

CANDELA DISTRIBUTION (continued):

| | 220° | 225° | 230° | 235° | 240° | 245° | 250° | 255° | 260° | 265° | 270° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 |
| 2.5° | 2684.6 | 2665.8 | 2685.0 | 2703.9 | 2711.9 | 2719.8 | 2699.3 | 2678.3 | 2711.0 | 2743.3 | 2751.7 |
| 5° | 2199.3 | 2182.2 | 2195.1 | 2207.7 | 2179.6 | 2151.6 | 2148.6 | 2145.3 | 2169.6 | 2193.9 | 2197.7 |
| 7.5° | 1704.8 | 1699.4 | 1711.5 | 1723.7 | 1688.1 | 1652.0 | 1634.4 | 1616.8 | 1622.7 | 1628.5 | 1627.7 |
| 10° | 1271.1 | 1274.4 | 1289.5 | 1304.2 | 1276.5 | 1248.9 | 1236.7 | 1224.6 | 1238.0 | 1251.0 | 1263.1 |
| 12.5° | 952.2 | 959.3 | 975.2 | 990.7 | 979.4 | 967.7 | 968.9 | 970.2 | 985.7 | 1000.8 | 1014.2 |
| 15° | 739.7 | 748.1 | 759.4 | 770.3 | 770.7 | 770.7 | 781.6 | 792.1 | 790.8 | 789.5 | 798.8 |
| 17.5° | 612.3 | 623.2 | 624.4 | 625.7 | 626.1 | 626.5 | 625.7 | 624.8 | 618.6 | 612.3 | 619.4 |
| 20° | 524.3 | 528.0 | 531.4 | 534.3 | 530.6 | 526.4 | 515.9 | 505.4 | 501.2 | 497.0 | 503.7 |
| 22.5° | 476.9 | 483.6 | 480.3 | 476.5 | 469.0 | 461.0 | 453.0 | 444.6 | 444.2 | 443.4 | 447.2 |
| 25° | 437.1 | 442.5 | 436.7 | 430.8 | 425.4 | 419.9 | 414.5 | 409.0 | 408.6 | 408.2 | 409.9 |
| 27.5° | 404.0 | 409.0 | 403.6 | 398.1 | 393.5 | 388.9 | 384.7 | 380.5 | 379.7 | 378.8 | 379.3 |
| 30° | 375.5 | 380.1 | 375.5 | 370.5 | 367.1 | 363.3 | 360.4 | 357.5 | 357.1 | 356.6 | 356.6 |
| 32.5° | 349.9 | 354.5 | 351.2 | 347.8 | 344.9 | 342.0 | 339.9 | 337.8 | 335.7 | 333.6 | 329.0 |
| 35° | 327.7 | 332.3 | 330.2 | 327.7 | 324.4 | 321.0 | 317.2 | 313.1 | 307.6 | 301.7 | 299.2 |
| 37.5° | 308.9 | 313.5 | 311.4 | 309.3 | 304.7 | 300.1 | 293.4 | 286.2 | 284.6 | 282.5 | 282.0 |
| 40° | 293.8 | 300.9 | 296.7 | 292.1 | 285.0 | 277.9 | 274.5 | 271.1 | 270.3 | 269.5 | 268.6 |
| 42.5° | 277.0 | 287.9 | 280.4 | 272.8 | 266.1 | 259.4 | 258.6 | 257.7 | 257.3 | 256.9 | 256.9 |
| 45° | 256.1 | 267.8 | 260.2 | 252.3 | 248.5 | 244.7 | 244.7 | 244.7 | 245.2 | 245.2 | 246.0 |
| 47.5° | 236.4 | 243.5 | 239.7 | 235.9 | 233.8 | 231.8 | 232.2 | 232.6 | 233.8 | 234.7 | 236.8 |
| 50° | 219.6 | 222.1 | 223.0 | 223.4 | 222.1 | 220.9 | 221.7 | 222.1 | 223.4 | 224.2 | 225.9 |
| 52.5° | 207.4 | 211.2 | 211.2 | 210.8 | 210.8 | 210.8 | 211.6 | 212.5 | 213.7 | 215.0 | 216.7 |
| 55° | 199.5 | 204.9 | 203.3 | 201.6 | 202.0 | 202.0 | 202.8 | 203.7 | 204.9 | 205.8 | 208.3 |
| 57.5° | 191.9 | 197.8 | 196.1 | 194.5 | 194.5 | 194.5 | 194.9 | 195.3 | 196.5 | 197.4 | 199.1 |
| 60° | 183.1 | 189.0 | 187.3 | 185.2 | 185.7 | 186.1 | 186.5 | 186.5 | 187.3 | 187.7 | 187.7 |
| 62.5° | 172.7 | 178.5 | 176.9 | 174.8 | 176.0 | 176.9 | 176.9 | 176.9 | 177.7 | 178.1 | 176.9 |
| 65° | 161.8 | 167.2 | 165.5 | 163.9 | 165.5 | 166.8 | 167.6 | 168.1 | 167.6 | 167.2 | 166.0 |
| 67.5° | 150.0 | 155.5 | 153.8 | 151.7 | 153.8 | 155.5 | 157.2 | 158.4 | 157.2 | 155.9 | 154.2 |
| 70° | 137.5 | 142.9 | 140.8 | 138.7 | 140.8 | 142.9 | 144.6 | 146.3 | 144.6 | 142.9 | 142.5 |
| 72.5° | 124.0 | 130.3 | 127.8 | 125.3 | 127.8 | 130.3 | 131.2 | 132.0 | 130.8 | 129.5 | 128.7 |
| 75° | 109.4 | 115.7 | 113.6 | 111.1 | 113.2 | 115.2 | 115.7 | 116.1 | 116.1 | 115.7 | 113.2 |
| 77.5° | 93.9 | 98.9 | 97.6 | 96.4 | 97.6 | 98.9 | 98.9 | 98.9 | 99.3 | 99.3 | 96.0 |
| 80° | 75.4 | 78.4 | 78.8 | 79.2 | 79.6 | 80.0 | 79.6 | 79.2 | 78.4 | 77.5 | 75.4 |
| 82.5° | 56.2 | 56.2 | 59.5 | 62.4 | 62.4 | 62.0 | 61.6 | 60.8 | 59.1 | 57.0 | 52.4 |
| 85° | 35.6 | 33.5 | 39.0 | 44.0 | 44.0 | 43.6 | 42.7 | 41.5 | 38.1 | 34.4 | 30.6 |
| 87.5° | 12.2 | 10.1 | 15.5 | 21.0 | 21.4 | 21.4 | 20.5 | 19.7 | 16.3 | 12.6 | 9.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386643
 CATALOG NUMBER: GWC-SA2B-750-U-SLL

CANDELA DISTRIBUTION (continued):

| | 220° | 225° | 230° | 235° | 240° | 245° | 250° | 255° | 260° | 265° | 270° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386643

CATALOG NUMBER: GWC-SA2B-750-U-SLL

CANDELA DISTRIBUTION (continued):

| | 275° | 280° | 285° | 290° | 295° | 300° | 305° | 310° | 315° | 320° | 325° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 |
| 2.5° | 2764.3 | 2769.7 | 2774.7 | 2815.8 | 2856.5 | 2904.2 | 2952.0 | 2988.5 | 3024.5 | 3061.8 | 3099.1 |
| 5° | 2210.6 | 2217.4 | 2224.1 | 2273.9 | 2323.4 | 2390.0 | 2456.6 | 2514.1 | 2571.5 | 2638.9 | 2706.4 |
| 7.5° | 1638.6 | 1653.3 | 1667.5 | 1720.7 | 1773.5 | 1845.2 | 1916.5 | 1991.5 | 2066.1 | 2154.1 | 2242.1 |
| 10° | 1287.0 | 1314.7 | 1341.9 | 1396.4 | 1450.9 | 1521.7 | 1592.1 | 1670.5 | 1748.8 | 1835.6 | 1921.9 |
| 12.5° | 1041.8 | 1078.7 | 1115.2 | 1180.5 | 1245.9 | 1330.6 | 1414.8 | 1502.0 | 1588.7 | 1665.0 | 1741.3 |
| 15° | 823.1 | 863.3 | 903.1 | 972.3 | 1041.4 | 1134.4 | 1227.1 | 1322.2 | 1416.9 | 1508.3 | 1599.6 |
| 17.5° | 642.0 | 675.1 | 707.8 | 766.5 | 824.7 | 914.9 | 1005.0 | 1104.7 | 1204.4 | 1315.9 | 1427.0 |
| 20° | 518.0 | 531.8 | 545.6 | 588.0 | 629.9 | 703.2 | 776.1 | 878.0 | 979.8 | 1113.1 | 1246.3 |
| 22.5° | 453.9 | 461.0 | 467.7 | 488.2 | 508.3 | 555.7 | 602.6 | 692.7 | 782.4 | 927.8 | 1072.8 |
| 25° | 415.3 | 420.8 | 426.2 | 439.6 | 453.0 | 475.7 | 498.3 | 561.6 | 624.8 | 767.8 | 910.2 |
| 27.5° | 380.5 | 388.9 | 396.9 | 403.2 | 409.0 | 424.5 | 439.6 | 481.1 | 522.6 | 655.9 | 788.7 |
| 30° | 355.4 | 358.3 | 361.2 | 370.9 | 380.1 | 396.0 | 412.0 | 440.9 | 469.8 | 582.5 | 694.8 |
| 32.5° | 326.0 | 330.2 | 334.4 | 344.5 | 354.5 | 369.2 | 383.9 | 407.3 | 430.4 | 526.8 | 622.8 |
| 35° | 299.6 | 303.8 | 308.0 | 318.1 | 327.7 | 343.6 | 359.2 | 378.8 | 398.1 | 481.9 | 565.8 |
| 37.5° | 283.3 | 287.5 | 291.7 | 300.5 | 308.9 | 324.8 | 340.3 | 355.8 | 370.9 | 448.4 | 525.9 |
| 40° | 269.5 | 273.7 | 277.9 | 286.2 | 294.2 | 309.7 | 324.8 | 337.8 | 350.8 | 423.3 | 495.8 |
| 42.5° | 257.3 | 261.9 | 266.5 | 274.9 | 282.9 | 296.7 | 310.5 | 327.7 | 344.5 | 401.5 | 458.1 |
| 45° | 247.3 | 251.9 | 256.1 | 265.3 | 274.5 | 287.9 | 301.3 | 325.2 | 349.1 | 390.2 | 431.2 |
| 47.5° | 238.0 | 243.1 | 247.7 | 257.7 | 267.8 | 284.6 | 300.9 | 321.0 | 340.7 | 381.4 | 422.0 |
| 50° | 229.2 | 235.1 | 241.0 | 253.1 | 264.9 | 292.9 | 320.6 | 323.5 | 326.0 | 374.2 | 422.0 |
| 52.5° | 220.9 | 227.6 | 234.3 | 249.4 | 264.0 | 296.7 | 329.4 | 318.9 | 308.0 | 360.8 | 413.6 |
| 55° | 212.5 | 218.3 | 223.8 | 242.2 | 260.7 | 284.6 | 308.4 | 294.6 | 280.4 | 335.7 | 391.0 |
| 57.5° | 201.2 | 207.4 | 213.3 | 233.0 | 252.7 | 269.5 | 285.8 | 273.2 | 260.2 | 307.2 | 353.7 |
| 60° | 189.4 | 196.5 | 203.7 | 228.8 | 253.5 | 250.6 | 247.3 | 244.7 | 241.8 | 275.3 | 308.9 |
| 62.5° | 178.9 | 186.5 | 194.0 | 226.7 | 259.4 | 239.3 | 219.2 | 221.3 | 223.0 | 247.7 | 272.4 |
| 65° | 168.5 | 176.0 | 183.1 | 199.5 | 215.8 | 207.9 | 199.9 | 203.3 | 206.2 | 230.5 | 254.8 |
| 67.5° | 156.7 | 163.4 | 169.7 | 175.2 | 180.6 | 181.5 | 182.3 | 185.7 | 189.0 | 217.9 | 246.4 |
| 70° | 143.7 | 149.2 | 154.6 | 158.4 | 161.8 | 163.4 | 164.7 | 168.9 | 173.1 | 204.5 | 235.9 |
| 72.5° | 129.1 | 133.7 | 137.9 | 141.2 | 144.6 | 145.8 | 146.7 | 150.9 | 155.1 | 188.6 | 222.1 |
| 75° | 113.2 | 116.9 | 120.3 | 123.2 | 126.1 | 127.8 | 129.5 | 132.4 | 135.4 | 171.8 | 207.9 |
| 77.5° | 95.6 | 99.3 | 102.7 | 105.2 | 107.3 | 109.0 | 110.2 | 114.0 | 117.8 | 148.4 | 178.5 |
| 80° | 74.6 | 79.2 | 83.4 | 85.5 | 87.2 | 87.6 | 87.6 | 90.9 | 94.3 | 116.1 | 137.5 |
| 82.5° | 52.8 | 57.8 | 62.4 | 64.1 | 65.8 | 65.8 | 65.8 | 69.6 | 73.3 | 88.0 | 102.3 |
| 85° | 31.0 | 36.5 | 41.5 | 43.2 | 44.8 | 45.7 | 46.1 | 47.8 | 49.0 | 59.5 | 69.6 |
| 87.5° | 9.6 | 14.2 | 18.4 | 19.3 | 20.1 | 21.8 | 23.5 | 23.9 | 23.9 | 31.0 | 38.1 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386643
 CATALOG NUMBER: GWC-SA2B-750-U-SLL

CANDELA DISTRIBUTION (continued):

| | 275° | 280° | 285° | 290° | 295° | 300° | 305° | 310° | 315° | 320° | 325° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386643

CATALOG NUMBER: GWC-SA2B-750-U-SLL

CANDELA DISTRIBUTION (continued):

| | 330° | 335° | 340° | 345° | 350° | 355° | 360° |
|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 | 3193.4 |
| 2.5° | 3141.8 | 3184.6 | 3234.5 | 3283.9 | 3326.2 | 3368.6 | 3403.8 |
| 5° | 2792.3 | 2878.2 | 2983.4 | 3088.2 | 3181.7 | 3275.1 | 3383.7 |
| 7.5° | 2353.1 | 2464.2 | 2600.4 | 2736.6 | 2868.6 | 3000.2 | 3167.0 |
| 10° | 2035.1 | 2147.8 | 2291.9 | 2435.7 | 2584.0 | 2732.0 | 2920.6 |
| 12.5° | 1833.1 | 1924.4 | 2064.0 | 2203.5 | 2377.9 | 2551.8 | 2733.2 |
| 15° | 1699.8 | 1799.5 | 1935.3 | 2071.1 | 2261.8 | 2452.5 | 2661.2 |
| 17.5° | 1557.7 | 1688.1 | 1862.0 | 2035.9 | 2261.8 | 2487.2 | 2733.2 |
| 20° | 1408.9 | 1571.1 | 1796.6 | 2022.1 | 2326.3 | 2630.1 | 2944.0 |
| 22.5° | 1260.6 | 1448.3 | 1737.5 | 2026.3 | 2424.0 | 2821.2 | 3244.9 |
| 25° | 1126.9 | 1343.6 | 1701.5 | 2058.9 | 2566.0 | 3072.7 | 3598.2 |
| 27.5° | 1025.5 | 1261.9 | 1686.8 | 2111.3 | 2746.2 | 3381.1 | 3982.5 |
| 30° | 935.4 | 1175.9 | 1669.2 | 2162.5 | 2919.7 | 3676.6 | 4283.0 |
| 32.5° | 857.4 | 1092.1 | 1635.3 | 2178.0 | 3040.8 | 3903.7 | 4537.4 |
| 35° | 796.3 | 1026.7 | 1578.3 | 2129.8 | 3116.7 | 4103.6 | 4802.2 |
| 37.5° | 743.4 | 961.0 | 1513.3 | 2065.6 | 3184.2 | 4302.7 | 5100.2 |
| 40° | 693.2 | 890.5 | 1457.6 | 2024.2 | 3277.2 | 4530.3 | 5414.9 |
| 42.5° | 645.4 | 832.7 | 1412.7 | 1992.7 | 3363.5 | 4733.9 | 5690.3 |
| 45° | 609.8 | 788.3 | 1372.9 | 1957.1 | 3419.3 | 4881.4 | 5897.7 |
| 47.5° | 592.2 | 761.9 | 1351.5 | 1940.8 | 3475.0 | 5008.8 | 6070.0 |
| 50° | 589.6 | 757.3 | 1375.8 | 1994.4 | 3595.7 | 5196.6 | 6266.9 |
| 52.5° | 589.2 | 764.8 | 1445.8 | 2126.8 | 3819.9 | 5512.6 | 6480.2 |
| 55° | 580.4 | 769.4 | 1529.2 | 2288.6 | 4120.8 | 5952.6 | 6863.7 |
| 57.5° | 553.6 | 753.5 | 1615.1 | 2476.3 | 4438.9 | 6401.0 | 7295.8 |
| 60° | 512.1 | 715.0 | 1686.0 | 2656.5 | 4652.6 | 6648.3 | 7462.1 |
| 62.5° | 460.1 | 647.5 | 1709.4 | 2771.0 | 4646.8 | 6522.6 | 7294.5 |
| 65° | 415.7 | 576.7 | 1632.3 | 2687.6 | 4411.7 | 6135.3 | 6963.0 |
| 67.5° | 376.3 | 505.8 | 1439.5 | 2372.8 | 3988.8 | 5604.4 | 6541.4 |
| 70° | 347.8 | 459.3 | 1191.0 | 1922.7 | 3459.5 | 4995.9 | 6053.2 |
| 72.5° | 329.8 | 437.1 | 971.0 | 1504.5 | 2807.4 | 4109.9 | 5177.7 |
| 75° | 305.1 | 402.3 | 761.9 | 1121.0 | 2148.6 | 3176.2 | 3910.9 |
| 77.5° | 259.0 | 339.0 | 574.1 | 809.2 | 1576.6 | 2343.5 | 2719.8 |
| 80° | 199.9 | 261.9 | 394.8 | 527.6 | 1085.0 | 1642.4 | 1854.4 |
| 82.5° | 142.5 | 182.7 | 239.3 | 295.9 | 720.8 | 1145.3 | 1162.9 |
| 85° | 88.0 | 106.4 | 137.0 | 167.6 | 476.9 | 786.2 | 655.0 |
| 87.5° | 47.4 | 56.6 | 72.5 | 88.0 | 152.5 | 217.1 | 124.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386643
 CATALOG NUMBER: GWC-SA2B-750-U-SLL

CANDELA DISTRIBUTION (continued):

| | 330° | 335° | 340° | 345° | 350° | 355° | 360° |
|--------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245982

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



--- HS — SS

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



u



| | | | | | | | | | | | |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





| | | | | | | | | | | | | |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





| | | | | | | | | | | | |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





| | | | | | | | | | | | |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





| | | | | | | | | | | | |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





| | | | | | | | | | | | |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





| | | | | | | | |
|------|-----|-----|-----|-----|-----|-----|-----|
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
|------|-----|-----|-----|-----|-----|-----|-----|

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)