

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P387119

Luminaire Tested: **GWC-SA2D-760-U-SLL**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P387119
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-26)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GWC-SA2D-760-U-SLL
Description: GALLEON WALL LUMINAIRE
(2) 70 CRI, 5700K, 1200mA LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT
ELIMINATOR LEFT OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14231 lumens
Efficiency: N/A
Efficacy: 110.3 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B2 - U0 - G3

Input Watts (W): 129
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




REPORT NUMBER: P387119

CATALOG NUMBER: GWC-SA2D-760-U-SLL

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 13.6 fc
 Type III - Medium - N/A

REPORT NUMBER: P387119
CATALOG NUMBER: GWC-SA2D-760-U-SLL

Luminous Intensity Polar Plot



— Vertical Plane Through 75-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P387119

CATALOG NUMBER: GWC-SA2D-760-U-SLL


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 2506.4 | 0.0 | 2506.4 |
| | % Fixture | 17.6 | 0.0 | 17.6 |
| Street Side | Lumens | 11724.6 | 0.0 | 11724.6 |
| | % Fixture | 82.4 | 0.0 | 82.4 |
| Total | Lumens | 14231.0 | 0.0 | 14231.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 334.6 | 2.4 |
| 10°-20° | 695.1 | 4.9 |
| 20°-30° | 988.6 | 6.9 |
| 30°-40° | 1424.6 | 10.0 |
| 40°-50° | 2007.6 | 14.1 |
| 50°-60° | 2790.9 | 19.6 |
| 60°-70° | 3375.1 | 23.7 |
| 70°-80° | 2074.6 | 14.6 |
| 80°-90° | 539.8 | 3.8 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 14231.0 | 100.0 |
| 0°-180° | 14231.0 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P387119


CATALOG NUMBER: GWC-SA2D-760-U-SLL

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1413.0 | 9.9 | | | |
| FM (30°-60°) | 5085.4 | 35.7 | | | |
| FH (60°-80°) | 4747.0 | 33.4 | | | G2/5000 |
| FVH (80°-90°) | 479.2 | 3.4 | | | G3/500 |
| BL (0°-30°) | 605.3 | 4.3 | B2/1000 | | |
| BM (30°-60°) | 1137.7 | 8.0 | B2/2500 | | |
| BH (60°-80°) | 702.7 | 4.9 | B2/1000 | | G2/1000 |
| BVH (80°-90°) | 60.7 | 0.4 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G3

Type III Medium





REPORT NUMBER: P387119

CATALOG NUMBER: GWC-SA2D-760-U-SLL

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 10° | 15° | 20° | 25° | 30° | 35° | 40° | 45° | 50° |
|--------|---------|---------|--------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 |
| 2.5° | 4621.2 | 4682.0 | 4724.1 | 4765.7 | 4798.1 | 4830.0 | 4876.6 | 4923.3 | 4932.4 | 4940.9 | 4922.7 |
| 5° | 4593.9 | 4742.4 | 4868.7 | 4994.4 | 5111.0 | 5227.7 | 5297.7 | 5367.6 | 5381.9 | 5396.1 | 5352.3 |
| 7.5° | 4299.7 | 4518.7 | 4737.8 | 4956.9 | 5157.7 | 5358.5 | 5480.9 | 5602.6 | 5630.5 | 5657.8 | 5586.1 |
| 10° | 3965.1 | 4220.0 | 4489.2 | 4758.3 | 5022.9 | 5287.4 | 5464.4 | 5641.3 | 5676.6 | 5711.9 | 5622.5 |
| 12.5° | 3710.8 | 3989.0 | 4276.4 | 4563.7 | 4843.1 | 5121.9 | 5305.1 | 5488.3 | 5532.1 | 5575.9 | 5511.0 |
| 15° | 3613.0 | 3917.9 | 4188.2 | 4458.4 | 4702.0 | 4944.9 | 5095.1 | 5244.8 | 5263.0 | 5280.6 | 5270.4 |
| 17.5° | 3710.8 | 4047.1 | 4291.7 | 4535.8 | 4668.4 | 4800.4 | 4860.7 | 4920.4 | 4940.4 | 4959.7 | 4985.9 |
| 20° | 3997.0 | 4360.0 | 4532.4 | 4704.2 | 4698.5 | 4692.3 | 4663.3 | 4633.7 | 4628.6 | 4623.4 | 4697.4 |
| 22.5° | 4405.5 | 4827.1 | 4896.0 | 4964.3 | 4804.4 | 4644.5 | 4547.2 | 4449.3 | 4430.0 | 4410.1 | 4488.6 |
| 25° | 4885.2 | 5334.1 | 5321.6 | 5308.5 | 5004.1 | 4699.1 | 4513.6 | 4328.1 | 4306.5 | 4284.9 | 4352.0 |
| 27.5° | 5406.9 | 5835.9 | 5754.0 | 5672.0 | 5258.4 | 4844.8 | 4575.6 | 4306.5 | 4284.9 | 4263.3 | 4322.5 |
| 30° | 5814.9 | 6204.0 | 6072.6 | 5941.2 | 5472.9 | 5004.6 | 4684.9 | 4365.1 | 4329.9 | 4294.0 | 4366.8 |
| 32.5° | 6160.2 | 6491.4 | 6315.0 | 6138.6 | 5647.0 | 5155.4 | 4809.5 | 4463.6 | 4408.4 | 4353.2 | 4450.5 |
| 35° | 6519.8 | 6778.1 | 6530.1 | 6281.4 | 5802.3 | 5322.7 | 4956.9 | 4590.4 | 4522.7 | 4455.0 | 4588.7 |
| 37.5° | 6924.3 | 7138.8 | 6782.7 | 6425.9 | 5977.0 | 5528.1 | 5177.6 | 4826.6 | 4757.1 | 4687.7 | 4858.4 |
| 40° | 7351.6 | 7530.3 | 7055.2 | 6580.1 | 6168.2 | 5756.3 | 5483.2 | 5209.5 | 5143.5 | 5076.9 | 5284.0 |
| 42.5° | 7725.5 | 7855.7 | 7309.0 | 6762.2 | 6398.6 | 6034.5 | 5842.2 | 5649.3 | 5648.7 | 5647.6 | 5857.5 |
| 45° | 8007.1 | 8120.3 | 7520.6 | 6920.4 | 6623.4 | 6325.8 | 6225.7 | 6125.5 | 6205.7 | 6286.0 | 6476.0 |
| 47.5° | 8240.9 | 8317.8 | 7698.1 | 7078.0 | 6880.5 | 6683.1 | 6697.9 | 6712.7 | 6876.0 | 7039.3 | 7161.6 |
| 50° | 8508.4 | 8446.3 | 7859.2 | 7271.4 | 7210.5 | 7149.7 | 7282.8 | 7415.4 | 7603.1 | 7790.3 | 7873.4 |
| 52.5° | 8798.0 | 8633.5 | 8077.6 | 7521.2 | 7589.5 | 7657.7 | 7928.6 | 8199.4 | 8388.9 | 8578.3 | 8609.6 |
| 55° | 9318.6 | 9066.5 | 8479.3 | 7891.6 | 8023.0 | 8153.9 | 8551.6 | 8948.7 | 9096.7 | 9244.6 | 9256.0 |
| 57.5° | 9905.2 | 9681.6 | 9042.0 | 8402.5 | 8543.6 | 8684.7 | 9143.9 | 9602.5 | 9762.4 | 9921.7 | 9899.5 |
| 60° | 10131.1 | 10141.9 | 9576.3 | 9010.2 | 9152.4 | 9294.7 | 9741.9 | 10189.1 | 10372.9 | 10556.1 | 10507.1 |
| 62.5° | 9903.5 | 10170.3 | 9868.2 | 9565.5 | 9694.7 | 9823.2 | 10261.3 | 10699.5 | 10887.8 | 11076.1 | 10990.8 |
| 65° | 9453.4 | 9718.0 | 9853.4 | 9988.8 | 10031.5 | 10074.2 | 10483.2 | 10891.8 | 11036.3 | 11180.2 | 11137.0 |
| 67.5° | 8881.0 | 9095.0 | 9594.5 | 10093.5 | 10007.6 | 9921.7 | 10113.4 | 10305.2 | 10453.7 | 10602.2 | 10577.7 |
| 70° | 8218.2 | 8473.1 | 9139.3 | 9805.6 | 9383.4 | 8960.7 | 8881.6 | 8802.5 | 8963.0 | 9122.8 | 9023.8 |
| 72.5° | 7029.6 | 7414.2 | 8124.9 | 8834.9 | 8057.2 | 7279.4 | 7009.1 | 6738.9 | 6942.0 | 7145.1 | 6987.5 |
| 75° | 5309.6 | 5820.0 | 6605.2 | 7389.8 | 6461.8 | 5533.8 | 5173.1 | 4812.3 | 4987.0 | 5161.7 | 5053.6 |
| 77.5° | 3692.6 | 4332.7 | 5105.9 | 5879.2 | 4935.8 | 3991.9 | 3723.9 | 3455.3 | 3507.7 | 3559.5 | 3541.3 |
| 80° | 2517.7 | 2938.7 | 3478.1 | 4016.9 | 3388.8 | 2760.6 | 2781.7 | 2802.2 | 2777.7 | 2752.7 | 2789.1 |
| 82.5° | 1578.9 | 1875.3 | 2291.8 | 2707.7 | 2374.3 | 2040.9 | 2232.1 | 2423.2 | 2329.4 | 2234.9 | 2270.2 |
| 85° | 889.3 | 1070.2 | 1477.6 | 1884.4 | 1756.4 | 1627.8 | 1739.9 | 1851.4 | 1705.8 | 1560.1 | 1624.4 |
| 87.5° | 169.6 | 282.2 | 817.6 | 1352.4 | 1227.8 | 1103.2 | 958.7 | 814.2 | 621.3 | 428.4 | 625.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P387119

CATALOG NUMBER: GWC-SA2D-760-U-SLL

CANDELA DISTRIBUTION (continued):

| | 0° | 5° | 10° | 15° | 20° | 25° | 30° | 35° | 40° | 45° | 50° |
|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P387119

CATALOG NUMBER: GWC-SA2D-760-U-SLL

CANDELA DISTRIBUTION (continued):

| | 55° | 60° | 65° | 70° | 75° | 80° | 85° | 90° | 95° | 100° | 105° |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|--------|--------|--------|
| 0° | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 |
| 2.5° | 4904.5 | 4894.8 | 4885.2 | 4850.5 | 4815.2 | 4762.8 | 4719.6 | 4644.5 | 4603.5 | 4541.5 | 4479.5 |
| 5° | 5307.9 | 5246.5 | 5185.0 | 5079.2 | 4972.8 | 4854.4 | 4718.5 | 4567.7 | 4453.9 | 4306.0 | 4158.0 |
| 7.5° | 5514.4 | 5371.1 | 5227.1 | 5024.0 | 4820.3 | 4637.1 | 4422.0 | 4221.7 | 4051.1 | 3858.7 | 3666.4 |
| 10° | 5533.2 | 5318.1 | 5102.5 | 4838.5 | 4573.9 | 4351.5 | 4104.0 | 3881.5 | 3676.7 | 3455.9 | 3234.6 |
| 12.5° | 5445.6 | 5216.9 | 4987.6 | 4696.8 | 4405.5 | 4152.9 | 3886.6 | 3637.4 | 3410.4 | 3167.4 | 2923.9 |
| 15° | 5260.1 | 5077.5 | 4894.3 | 4621.7 | 4349.2 | 4094.3 | 3836.0 | 3540.7 | 3284.1 | 3035.4 | 2786.2 |
| 17.5° | 5011.5 | 4925.0 | 4837.9 | 4641.1 | 4443.6 | 4222.9 | 3972.5 | 3626.0 | 3325.6 | 3055.4 | 2785.1 |
| 20° | 4770.8 | 4802.7 | 4834.0 | 4755.4 | 4676.9 | 4500.0 | 4281.5 | 3892.3 | 3508.8 | 3155.5 | 2801.6 |
| 22.5° | 4566.5 | 4719.6 | 4872.1 | 4933.0 | 4993.3 | 4886.9 | 4716.2 | 4266.1 | 3758.6 | 3297.2 | 2835.7 |
| 25° | 4418.6 | 4672.4 | 4926.1 | 5128.7 | 5330.7 | 5283.4 | 5152.0 | 4720.2 | 4089.7 | 3501.4 | 2912.6 |
| 27.5° | 4381.6 | 4692.9 | 5004.1 | 5318.1 | 5631.7 | 5675.5 | 5639.0 | 5198.7 | 4484.6 | 3755.2 | 3025.2 |
| 30° | 4439.7 | 4754.9 | 5069.5 | 5451.9 | 5833.6 | 6008.3 | 6057.2 | 5597.5 | 4935.8 | 4051.1 | 3165.7 |
| 32.5° | 4547.8 | 4856.7 | 5165.7 | 5582.2 | 5998.1 | 6262.1 | 6418.0 | 5962.2 | 5250.4 | 4274.1 | 3297.2 |
| 35° | 4722.4 | 5011.5 | 5300.5 | 5734.1 | 6167.6 | 6509.0 | 6793.5 | 6338.9 | 5529.8 | 4430.0 | 3329.6 |
| 37.5° | 5028.5 | 5277.2 | 5525.8 | 5926.4 | 6326.4 | 6769.0 | 7196.3 | 6753.7 | 5831.9 | 4580.2 | 3327.9 |
| 40° | 5491.1 | 5666.9 | 5842.2 | 6180.7 | 6518.7 | 7075.7 | 7652.6 | 7216.2 | 6165.9 | 4742.9 | 3319.9 |
| 42.5° | 6067.5 | 6157.9 | 6247.8 | 6515.8 | 6783.8 | 7396.0 | 8066.8 | 7668.6 | 6484.5 | 4894.3 | 3304.0 |
| 45° | 6665.5 | 6689.4 | 6713.3 | 6882.2 | 7050.7 | 7649.8 | 8349.0 | 8008.2 | 6762.8 | 5025.7 | 3288.1 |
| 47.5° | 7283.4 | 7201.4 | 7119.5 | 7186.6 | 7253.8 | 7844.4 | 8550.5 | 8266.0 | 7042.1 | 5171.4 | 3300.0 |
| 50° | 7956.5 | 7728.3 | 7500.1 | 7464.9 | 7429.6 | 8039.0 | 8787.7 | 8593.7 | 7377.8 | 5383.6 | 3389.3 |
| 52.5° | 8640.4 | 8264.3 | 7888.2 | 7748.8 | 7608.8 | 8271.1 | 9102.4 | 9001.7 | 7856.9 | 5712.4 | 3567.4 |
| 55° | 9267.4 | 8788.9 | 8310.4 | 8122.6 | 7934.8 | 8626.1 | 9486.4 | 9600.8 | 8470.8 | 6132.9 | 3794.5 |
| 57.5° | 9876.7 | 9334.5 | 8792.3 | 8618.2 | 8444.1 | 9147.9 | 9972.9 | 10138.5 | 9091.0 | 6536.3 | 3981.1 |
| 60° | 10458.2 | 9921.7 | 9384.6 | 9245.2 | 9105.2 | 9796.5 | 10498.6 | 10378.0 | 9410.7 | 6725.2 | 4039.1 |
| 62.5° | 10905.4 | 10478.7 | 10052.0 | 9978.6 | 9904.6 | 10452.5 | 10902.6 | 10284.7 | 9207.6 | 6539.2 | 3870.7 |
| 65° | 11093.8 | 10850.8 | 10607.3 | 10676.1 | 10744.4 | 10948.7 | 11003.3 | 10011.6 | 8569.2 | 6018.0 | 3466.7 |
| 67.5° | 10552.7 | 10602.2 | 10651.7 | 10940.7 | 11229.2 | 11088.6 | 10704.0 | 9473.3 | 7660.6 | 5279.5 | 2898.3 |
| 70° | 8924.3 | 9221.3 | 9517.7 | 10201.6 | 10884.9 | 10573.1 | 9902.3 | 8507.2 | 6567.0 | 4428.9 | 2290.1 |
| 72.5° | 6829.3 | 7163.3 | 7496.7 | 8511.8 | 9526.2 | 9238.9 | 8417.3 | 6987.5 | 5265.2 | 3536.7 | 1807.6 |
| 75° | 4944.9 | 5322.1 | 5698.8 | 6818.5 | 7938.3 | 7539.4 | 6296.2 | 5002.9 | 3999.3 | 2699.8 | 1399.7 |
| 77.5° | 3522.5 | 3775.1 | 4027.7 | 5133.8 | 6239.3 | 5589.5 | 4191.0 | 3366.6 | 2768.0 | 1876.5 | 984.3 |
| 80° | 2825.5 | 2748.1 | 2670.7 | 3286.9 | 3903.1 | 3795.0 | 2772.0 | 2162.1 | 1915.7 | 1257.4 | 599.1 |
| 82.5° | 2304.9 | 2116.0 | 1927.1 | 2217.3 | 2507.4 | 2491.5 | 1923.7 | 1586.3 | 1425.8 | 873.9 | 322.0 |
| 85° | 1688.1 | 1612.5 | 1536.8 | 1793.4 | 2050.0 | 1830.9 | 1302.9 | 1008.2 | 1111.8 | 643.5 | 175.2 |
| 87.5° | 823.3 | 940.5 | 1057.1 | 1359.8 | 1662.0 | 1247.7 | 395.4 | 195.7 | 270.8 | 178.1 | 84.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P387119

CATALOG NUMBER: GWC-SA2D-760-U-SLL

CANDELA DISTRIBUTION (continued):

| | 55° | 60° | 65° | 70° | 75° | 80° | 85° | 90° | 95° | 100° | 105° |
|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P387119

CATALOG NUMBER: GWC-SA2D-760-U-SLL

CANDELA DISTRIBUTION (continued):

| | 110° | 115° | 120° | 125° | 130° | 135° | 140° | 145° | 150° | 155° | 160° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 |
| 2.5° | 4433.4 | 4386.7 | 4333.8 | 4280.9 | 4220.6 | 4159.7 | 4123.9 | 4087.5 | 4048.2 | 4009.0 | 3964.6 |
| 5° | 4060.2 | 3962.3 | 3851.3 | 3740.4 | 3630.6 | 3520.8 | 3461.6 | 3402.4 | 3339.8 | 3276.7 | 3222.1 |
| 7.5° | 3524.2 | 3381.4 | 3227.8 | 3073.6 | 2937.0 | 2799.9 | 2715.1 | 2629.8 | 2552.4 | 2474.4 | 2409.0 |
| 10° | 3052.5 | 2870.4 | 2716.3 | 2561.5 | 2458.5 | 2355.5 | 2277.6 | 2199.6 | 2124.5 | 2048.9 | 1976.6 |
| 12.5° | 2741.9 | 2559.8 | 2461.9 | 2364.1 | 2278.7 | 2193.4 | 2103.5 | 2013.0 | 1910.0 | 1806.5 | 1730.8 |
| 15° | 2620.7 | 2455.1 | 2346.4 | 2237.2 | 2122.8 | 2007.9 | 1897.5 | 1787.1 | 1665.4 | 1543.6 | 1457.7 |
| 17.5° | 2568.3 | 2351.5 | 2199.6 | 2047.1 | 1896.4 | 1745.6 | 1617.6 | 1489.6 | 1356.4 | 1223.3 | 1136.2 |
| 20° | 2513.1 | 2224.7 | 2021.0 | 1816.7 | 1623.3 | 1429.8 | 1284.7 | 1139.6 | 1020.7 | 901.8 | 835.2 |
| 22.5° | 2463.1 | 2089.8 | 1834.4 | 1578.3 | 1349.6 | 1120.9 | 978.6 | 835.8 | 763.0 | 690.2 | 663.4 |
| 25° | 2442.6 | 1972.0 | 1658.0 | 1343.9 | 1102.7 | 860.8 | 759.6 | 658.3 | 630.4 | 602.0 | 588.3 |
| 27.5° | 2446.0 | 1866.8 | 1509.5 | 1151.6 | 934.2 | 716.9 | 647.5 | 578.1 | 561.0 | 543.4 | 534.8 |
| 30° | 2459.1 | 1752.4 | 1369.5 | 986.6 | 807.4 | 628.1 | 583.2 | 537.7 | 519.5 | 501.3 | 490.5 |
| 32.5° | 2473.9 | 1650.0 | 1261.4 | 872.2 | 726.0 | 579.2 | 542.2 | 504.7 | 487.0 | 469.4 | 458.6 |
| 35° | 2448.3 | 1566.4 | 1187.4 | 808.5 | 673.7 | 538.2 | 507.0 | 475.1 | 455.7 | 436.4 | 426.2 |
| 37.5° | 2405.0 | 1482.2 | 1130.0 | 777.2 | 639.5 | 501.3 | 478.5 | 455.2 | 435.3 | 414.8 | 405.1 |
| 40° | 2365.8 | 1411.0 | 1087.3 | 763.0 | 620.7 | 477.9 | 458.6 | 439.2 | 418.8 | 397.7 | 386.3 |
| 42.5° | 2333.9 | 1363.2 | 1045.2 | 727.1 | 603.7 | 479.6 | 452.3 | 424.5 | 404.5 | 384.6 | 372.1 |
| 45° | 2310.0 | 1332.0 | 1012.2 | 692.4 | 587.7 | 483.1 | 448.3 | 413.6 | 393.7 | 373.2 | 358.5 |
| 47.5° | 2307.7 | 1315.5 | 988.9 | 662.3 | 557.6 | 452.3 | 438.1 | 423.9 | 394.9 | 365.3 | 348.2 |
| 50° | 2339.0 | 1288.7 | 961.6 | 633.8 | 528.6 | 423.3 | 442.7 | 461.4 | 411.9 | 361.9 | 340.2 |
| 52.5° | 2404.5 | 1241.5 | 918.3 | 595.1 | 493.3 | 390.9 | 421.0 | 450.6 | 408.0 | 364.7 | 336.8 |
| 55° | 2483.5 | 1172.1 | 852.9 | 533.1 | 446.6 | 359.6 | 386.3 | 412.5 | 385.8 | 358.5 | 324.9 |
| 57.5° | 2533.0 | 1084.5 | 770.4 | 456.3 | 394.3 | 332.3 | 347.6 | 362.4 | 351.6 | 340.8 | 306.7 |
| 60° | 2503.5 | 967.8 | 677.6 | 386.9 | 348.2 | 309.5 | 306.7 | 303.3 | 319.2 | 335.1 | 295.9 |
| 62.5° | 2358.9 | 847.2 | 595.7 | 344.2 | 315.2 | 285.6 | 279.4 | 272.5 | 298.7 | 324.3 | 282.8 |
| 65° | 2114.9 | 763.0 | 543.9 | 324.9 | 292.4 | 260.0 | 253.2 | 246.4 | 254.3 | 262.3 | 242.9 |
| 67.5° | 1804.8 | 711.2 | 514.3 | 317.5 | 278.2 | 238.4 | 230.4 | 222.5 | 220.8 | 219.1 | 212.2 |
| 70° | 1485.0 | 679.3 | 495.0 | 310.7 | 262.9 | 214.5 | 207.1 | 199.7 | 197.4 | 194.6 | 189.5 |
| 72.5° | 1241.5 | 675.4 | 492.7 | 310.1 | 250.3 | 190.6 | 183.8 | 176.9 | 174.1 | 170.7 | 166.7 |
| 75° | 1016.7 | 633.8 | 467.7 | 301.6 | 233.3 | 164.4 | 158.2 | 151.9 | 149.6 | 146.8 | 143.4 |
| 77.5° | 754.5 | 524.6 | 393.2 | 261.7 | 199.7 | 137.7 | 131.4 | 124.6 | 124.0 | 122.9 | 120.1 |
| 80° | 489.3 | 379.5 | 281.1 | 182.6 | 145.7 | 108.1 | 103.0 | 97.3 | 97.9 | 98.4 | 96.2 |
| 82.5° | 272.0 | 221.3 | 171.8 | 122.3 | 99.6 | 76.8 | 74.5 | 71.7 | 73.4 | 74.5 | 71.7 |
| 85° | 143.4 | 111.5 | 92.2 | 72.8 | 57.5 | 42.1 | 42.1 | 41.5 | 43.8 | 46.1 | 43.8 |
| 87.5° | 62.0 | 39.3 | 33.6 | 27.3 | 15.4 | 2.8 | 3.4 | 3.4 | 4.6 | 5.7 | 5.1 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P387119
 CATALOG NUMBER: GWC-SA2D-760-U-SLL

CANDELA DISTRIBUTION (continued):

| | 110° | 115° | 120° | 125° | 130° | 135° | 140° | 145° | 150° | 155° | 160° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P387119

CATALOG NUMBER: GWC-SA2D-760-U-SLL

CANDELA DISTRIBUTION (continued):

| | 165° | 170° | 175° | 180° | 185° | 190° | 195° | 200° | 205° | 210° | 215° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 |
| 2.5° | 3919.6 | 3878.1 | 3836.0 | 3789.9 | 3798.4 | 3763.2 | 3727.9 | 3705.7 | 3683.5 | 3676.7 | 3669.8 |
| 5° | 3167.4 | 3120.2 | 3072.4 | 3029.8 | 3066.7 | 3041.7 | 3016.7 | 3013.3 | 3009.3 | 3009.3 | 3008.7 |
| 7.5° | 2343.6 | 2292.9 | 2241.7 | 2206.5 | 2242.9 | 2238.3 | 2233.8 | 2258.2 | 2282.7 | 2302.6 | 2322.0 |
| 10° | 1904.3 | 1842.9 | 1780.9 | 1728.5 | 1719.4 | 1693.3 | 1666.5 | 1672.2 | 1677.3 | 1698.9 | 1720.6 |
| 12.5° | 1655.1 | 1581.7 | 1508.3 | 1446.9 | 1419.0 | 1375.8 | 1332.0 | 1304.6 | 1277.3 | 1280.2 | 1282.5 |
| 15° | 1371.2 | 1300.1 | 1228.4 | 1175.5 | 1157.9 | 1124.3 | 1090.7 | 1056.6 | 1021.9 | 1007.6 | 992.9 |
| 17.5° | 1048.6 | 991.7 | 934.2 | 899.0 | 899.0 | 889.3 | 879.6 | 862.6 | 844.9 | 830.7 | 815.9 |
| 20° | 768.7 | 738.5 | 707.8 | 693.0 | 697.6 | 698.1 | 698.1 | 706.7 | 715.2 | 710.6 | 706.1 |
| 22.5° | 636.1 | 625.3 | 614.5 | 608.2 | 610.5 | 611.1 | 611.6 | 619.6 | 627.0 | 632.7 | 637.8 |
| 25° | 574.1 | 567.3 | 560.4 | 558.2 | 563.3 | 563.8 | 563.8 | 569.0 | 574.1 | 579.8 | 585.5 |
| 27.5° | 525.7 | 522.9 | 520.0 | 516.1 | 521.2 | 521.2 | 520.6 | 526.3 | 531.4 | 536.5 | 541.1 |
| 30° | 479.6 | 480.8 | 481.3 | 480.2 | 483.6 | 485.9 | 487.6 | 491.6 | 495.0 | 499.0 | 503.0 |
| 32.5° | 447.2 | 445.5 | 443.8 | 442.7 | 450.1 | 454.0 | 458.0 | 462.0 | 465.4 | 467.1 | 468.8 |
| 35° | 415.9 | 411.9 | 408.0 | 405.1 | 411.9 | 417.1 | 422.2 | 429.6 | 436.4 | 437.5 | 438.7 |
| 37.5° | 394.9 | 389.7 | 384.6 | 381.2 | 384.1 | 386.3 | 388.6 | 396.6 | 404.5 | 409.1 | 413.1 |
| 40° | 375.0 | 369.8 | 364.7 | 361.9 | 363.6 | 364.1 | 364.7 | 368.7 | 372.1 | 380.6 | 388.6 |
| 42.5° | 359.0 | 352.8 | 346.5 | 343.1 | 344.2 | 345.4 | 345.9 | 345.4 | 344.8 | 352.8 | 360.7 |
| 45° | 343.1 | 336.3 | 329.4 | 325.5 | 326.0 | 326.0 | 326.0 | 324.9 | 323.2 | 327.2 | 331.1 |
| 47.5° | 330.6 | 322.6 | 314.6 | 310.7 | 309.5 | 308.4 | 307.2 | 306.7 | 305.5 | 308.4 | 310.7 |
| 50° | 318.1 | 309.5 | 300.4 | 295.9 | 293.0 | 291.9 | 290.7 | 290.2 | 289.0 | 291.9 | 294.2 |
| 52.5° | 308.4 | 298.1 | 287.9 | 280.5 | 277.7 | 275.9 | 274.2 | 274.8 | 274.8 | 275.9 | 276.5 |
| 55° | 291.3 | 282.2 | 272.5 | 267.4 | 262.3 | 261.2 | 260.0 | 261.7 | 262.9 | 262.9 | 262.9 |
| 57.5° | 272.5 | 264.0 | 254.9 | 251.5 | 246.9 | 246.9 | 246.4 | 248.6 | 250.3 | 251.5 | 252.6 |
| 60° | 256.0 | 246.4 | 236.7 | 233.8 | 232.1 | 231.6 | 231.0 | 233.8 | 236.1 | 238.4 | 240.7 |
| 62.5° | 240.7 | 230.4 | 220.2 | 216.8 | 216.2 | 216.8 | 216.8 | 219.6 | 221.9 | 224.2 | 226.4 |
| 65° | 223.6 | 213.4 | 202.6 | 199.1 | 200.3 | 202.0 | 203.7 | 206.0 | 207.7 | 209.9 | 212.2 |
| 67.5° | 204.8 | 196.3 | 187.2 | 183.8 | 184.3 | 186.6 | 188.9 | 190.6 | 191.7 | 194.0 | 196.3 |
| 70° | 184.3 | 176.9 | 169.6 | 167.3 | 166.7 | 169.6 | 171.8 | 173.0 | 174.1 | 176.9 | 179.2 |
| 72.5° | 162.2 | 155.9 | 149.6 | 147.9 | 148.5 | 150.2 | 151.9 | 153.6 | 154.8 | 157.6 | 159.9 |
| 75° | 139.4 | 133.7 | 128.0 | 126.9 | 128.0 | 129.7 | 131.4 | 132.6 | 133.7 | 137.1 | 140.0 |
| 77.5° | 117.2 | 110.9 | 104.1 | 103.6 | 105.3 | 107.0 | 108.1 | 109.8 | 111.5 | 116.1 | 120.6 |
| 80° | 93.9 | 87.1 | 79.7 | 79.1 | 80.8 | 82.5 | 84.2 | 85.9 | 87.6 | 93.3 | 98.4 |
| 82.5° | 68.8 | 60.9 | 52.9 | 51.8 | 57.5 | 59.2 | 60.9 | 63.7 | 66.0 | 71.1 | 76.2 |
| 85° | 41.5 | 33.6 | 25.6 | 25.0 | 30.2 | 33.0 | 35.8 | 39.3 | 42.1 | 46.7 | 51.2 |
| 87.5° | 4.6 | 2.3 | 0.0 | 0.0 | 0.6 | 2.8 | 5.1 | 8.0 | 10.8 | 15.4 | 19.3 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P387119

CATALOG NUMBER: GWC-SA2D-760-U-SLL

CANDELA DISTRIBUTION (continued):

| | 165° | 170° | 175° | 180° | 185° | 190° | 195° | 200° | 205° | 210° | 215° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P387119

CATALOG NUMBER: GWC-SA2D-760-U-SLL

CANDELA DISTRIBUTION (continued):

| | 220° | 225° | 230° | 235° | 240° | 245° | 250° | 255° | 260° | 265° | 270° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 |
| 2.5° | 3644.8 | 3619.2 | 3645.4 | 3671.0 | 3681.8 | 3692.6 | 3664.7 | 3636.3 | 3680.7 | 3724.5 | 3735.8 |
| 5° | 2985.9 | 2962.6 | 2980.3 | 2997.3 | 2959.2 | 2921.1 | 2917.1 | 2912.6 | 2945.6 | 2978.6 | 2983.7 |
| 7.5° | 2314.6 | 2307.2 | 2323.7 | 2340.2 | 2291.8 | 2242.9 | 2219.0 | 2195.1 | 2203.0 | 2211.0 | 2209.9 |
| 10° | 1725.7 | 1730.2 | 1750.7 | 1770.6 | 1733.1 | 1695.5 | 1679.0 | 1662.5 | 1680.7 | 1698.4 | 1714.9 |
| 12.5° | 1292.7 | 1302.4 | 1324.0 | 1345.0 | 1329.7 | 1313.7 | 1315.5 | 1317.2 | 1338.2 | 1358.7 | 1376.9 |
| 15° | 1004.2 | 1015.6 | 1031.0 | 1045.8 | 1046.3 | 1046.3 | 1061.1 | 1075.4 | 1073.6 | 1071.9 | 1084.5 |
| 17.5° | 831.3 | 846.1 | 847.8 | 849.5 | 850.0 | 850.6 | 849.5 | 848.3 | 839.8 | 831.3 | 840.9 |
| 20° | 711.8 | 716.9 | 721.5 | 725.4 | 720.3 | 714.6 | 700.4 | 686.2 | 680.5 | 674.8 | 683.9 |
| 22.5° | 647.5 | 656.6 | 652.0 | 646.9 | 636.7 | 625.9 | 615.1 | 603.7 | 603.1 | 602.0 | 607.1 |
| 25° | 593.4 | 600.8 | 592.9 | 584.9 | 577.5 | 570.1 | 562.7 | 555.3 | 554.7 | 554.2 | 556.5 |
| 27.5° | 548.5 | 555.3 | 547.9 | 540.5 | 534.3 | 528.0 | 522.3 | 516.6 | 515.5 | 514.3 | 514.9 |
| 30° | 509.8 | 516.1 | 509.8 | 503.0 | 498.4 | 493.3 | 489.3 | 485.3 | 484.8 | 484.2 | 484.2 |
| 32.5° | 475.1 | 481.3 | 476.8 | 472.2 | 468.3 | 464.3 | 461.4 | 458.6 | 455.7 | 452.9 | 446.6 |
| 35° | 444.9 | 451.2 | 448.3 | 444.9 | 440.4 | 435.8 | 430.7 | 425.0 | 417.6 | 409.7 | 406.2 |
| 37.5° | 419.3 | 425.6 | 422.7 | 419.9 | 413.6 | 407.4 | 398.3 | 388.6 | 386.3 | 383.5 | 382.9 |
| 40° | 398.8 | 408.5 | 402.8 | 396.6 | 386.9 | 377.2 | 372.7 | 368.1 | 367.0 | 365.8 | 364.7 |
| 42.5° | 376.1 | 390.9 | 380.6 | 370.4 | 361.3 | 352.2 | 351.1 | 349.9 | 349.3 | 348.8 | 348.8 |
| 45° | 347.6 | 363.6 | 353.3 | 342.5 | 337.4 | 332.3 | 332.3 | 332.3 | 332.8 | 332.8 | 334.0 |
| 47.5° | 320.9 | 330.6 | 325.5 | 320.3 | 317.5 | 314.6 | 315.2 | 315.8 | 317.5 | 318.6 | 321.5 |
| 50° | 298.1 | 301.6 | 302.7 | 303.3 | 301.6 | 299.8 | 301.0 | 301.6 | 303.3 | 304.4 | 306.7 |
| 52.5° | 281.6 | 286.8 | 286.8 | 286.2 | 286.2 | 286.2 | 287.3 | 288.5 | 290.2 | 291.9 | 294.2 |
| 55° | 270.8 | 278.2 | 275.9 | 273.7 | 274.2 | 274.2 | 275.4 | 276.5 | 278.2 | 279.4 | 282.8 |
| 57.5° | 260.6 | 268.6 | 266.3 | 264.0 | 264.0 | 264.0 | 264.6 | 265.1 | 266.8 | 268.0 | 270.3 |
| 60° | 248.6 | 256.6 | 254.3 | 251.5 | 252.1 | 252.6 | 253.2 | 253.2 | 254.3 | 254.9 | 254.9 |
| 62.5° | 234.4 | 242.4 | 240.1 | 237.3 | 239.0 | 240.1 | 240.1 | 240.1 | 241.2 | 241.8 | 240.1 |
| 65° | 219.6 | 227.0 | 224.7 | 222.5 | 224.7 | 226.4 | 227.6 | 228.2 | 227.6 | 227.0 | 225.3 |
| 67.5° | 203.7 | 211.1 | 208.8 | 206.0 | 208.8 | 211.1 | 213.4 | 215.1 | 213.4 | 211.7 | 209.4 |
| 70° | 186.6 | 194.0 | 191.2 | 188.3 | 191.2 | 194.0 | 196.3 | 198.6 | 196.3 | 194.0 | 193.4 |
| 72.5° | 168.4 | 176.9 | 173.5 | 170.1 | 173.5 | 176.9 | 178.1 | 179.2 | 177.5 | 175.8 | 174.7 |
| 75° | 148.5 | 157.0 | 154.2 | 150.8 | 153.6 | 156.5 | 157.0 | 157.6 | 157.6 | 157.0 | 153.6 |
| 77.5° | 127.4 | 134.3 | 132.6 | 130.9 | 132.6 | 134.3 | 134.3 | 134.3 | 134.8 | 134.8 | 130.3 |
| 80° | 102.4 | 106.4 | 107.0 | 107.5 | 108.1 | 108.7 | 108.1 | 107.5 | 106.4 | 105.3 | 102.4 |
| 82.5° | 76.2 | 76.2 | 80.8 | 84.8 | 84.8 | 84.2 | 83.6 | 82.5 | 80.2 | 77.4 | 71.1 |
| 85° | 48.4 | 45.5 | 52.9 | 59.7 | 59.7 | 59.2 | 58.0 | 56.3 | 51.8 | 46.7 | 41.5 |
| 87.5° | 16.5 | 13.7 | 21.1 | 28.4 | 29.0 | 29.0 | 27.9 | 26.7 | 22.2 | 17.1 | 13.1 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P387119
 CATALOG NUMBER: GWC-SA2D-760-U-SLL

CANDELA DISTRIBUTION (continued):

| | 220° | 225° | 230° | 235° | 240° | 245° | 250° | 255° | 260° | 265° | 270° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P387119

CATALOG NUMBER: GWC-SA2D-760-U-SLL

CANDELA DISTRIBUTION (continued):

| | 275° | 280° | 285° | 290° | 295° | 300° | 305° | 310° | 315° | 320° | 325° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 |
| 2.5° | 3752.9 | 3760.3 | 3767.1 | 3822.9 | 3878.1 | 3943.0 | 4007.8 | 4057.3 | 4106.2 | 4156.9 | 4207.5 |
| 5° | 3001.3 | 3010.4 | 3019.5 | 3087.2 | 3154.4 | 3244.8 | 3335.3 | 3413.2 | 3491.2 | 3582.8 | 3674.4 |
| 7.5° | 2224.7 | 2244.6 | 2263.9 | 2336.2 | 2407.9 | 2505.2 | 2601.9 | 2703.7 | 2805.0 | 2924.5 | 3044.0 |
| 10° | 1747.3 | 1784.9 | 1821.8 | 1895.8 | 1969.8 | 2065.9 | 2161.5 | 2267.9 | 2374.3 | 2492.1 | 2609.3 |
| 12.5° | 1414.5 | 1464.5 | 1514.0 | 1602.8 | 1691.5 | 1806.5 | 1920.8 | 2039.2 | 2157.0 | 2260.5 | 2364.1 |
| 15° | 1117.5 | 1172.1 | 1226.1 | 1320.0 | 1413.9 | 1540.2 | 1665.9 | 1795.1 | 1923.7 | 2047.7 | 2171.8 |
| 17.5° | 871.7 | 916.6 | 961.0 | 1040.6 | 1119.7 | 1242.1 | 1364.4 | 1499.8 | 1635.2 | 1786.6 | 1937.3 |
| 20° | 703.2 | 722.0 | 740.8 | 798.3 | 855.2 | 954.7 | 1053.7 | 1192.0 | 1330.2 | 1511.2 | 1692.1 |
| 22.5° | 616.2 | 625.9 | 635.0 | 662.8 | 690.2 | 754.5 | 818.2 | 940.5 | 1062.3 | 1259.7 | 1456.6 |
| 25° | 563.8 | 571.2 | 578.6 | 596.8 | 615.1 | 645.8 | 676.5 | 762.4 | 848.3 | 1042.4 | 1235.8 |
| 27.5° | 516.6 | 528.0 | 538.8 | 547.3 | 555.3 | 576.4 | 596.8 | 653.2 | 709.5 | 890.4 | 1070.8 |
| 30° | 482.5 | 486.5 | 490.5 | 503.5 | 516.1 | 537.7 | 559.3 | 598.6 | 637.8 | 790.9 | 943.3 |
| 32.5° | 442.7 | 448.3 | 454.0 | 467.7 | 481.3 | 501.3 | 521.2 | 553.0 | 584.3 | 715.2 | 845.5 |
| 35° | 406.8 | 412.5 | 418.2 | 431.8 | 444.9 | 466.6 | 487.6 | 514.3 | 540.5 | 654.3 | 768.1 |
| 37.5° | 384.6 | 390.3 | 396.0 | 408.0 | 419.3 | 441.0 | 462.0 | 483.1 | 503.5 | 608.8 | 714.1 |
| 40° | 365.8 | 371.5 | 377.2 | 388.6 | 399.4 | 420.5 | 441.0 | 458.6 | 476.2 | 574.7 | 673.1 |
| 42.5° | 349.3 | 355.6 | 361.9 | 373.2 | 384.1 | 402.8 | 421.6 | 444.9 | 467.7 | 545.1 | 621.9 |
| 45° | 335.7 | 342.0 | 347.6 | 360.2 | 372.7 | 390.9 | 409.1 | 441.5 | 474.0 | 529.7 | 585.5 |
| 47.5° | 323.2 | 330.0 | 336.3 | 349.9 | 363.6 | 386.3 | 408.5 | 435.8 | 462.6 | 517.8 | 573.0 |
| 50° | 311.2 | 319.2 | 327.2 | 343.7 | 359.6 | 397.7 | 435.3 | 439.2 | 442.7 | 508.1 | 573.0 |
| 52.5° | 299.8 | 308.9 | 318.1 | 338.5 | 358.5 | 402.8 | 447.2 | 433.0 | 418.2 | 489.9 | 561.6 |
| 55° | 288.5 | 296.4 | 303.8 | 328.9 | 353.9 | 386.3 | 418.8 | 400.0 | 380.6 | 455.7 | 530.8 |
| 57.5° | 273.1 | 281.6 | 289.6 | 316.3 | 343.1 | 365.8 | 388.0 | 371.0 | 353.3 | 417.1 | 480.2 |
| 60° | 257.2 | 266.8 | 276.5 | 310.7 | 344.2 | 340.2 | 335.7 | 332.3 | 328.3 | 373.8 | 419.3 |
| 62.5° | 242.9 | 253.2 | 263.4 | 307.8 | 352.2 | 324.9 | 297.6 | 300.4 | 302.7 | 336.3 | 369.8 |
| 65° | 228.7 | 239.0 | 248.6 | 270.8 | 293.0 | 282.2 | 271.4 | 275.9 | 279.9 | 312.9 | 345.9 |
| 67.5° | 212.8 | 221.9 | 230.4 | 237.8 | 245.2 | 246.4 | 247.5 | 252.1 | 256.6 | 295.9 | 334.6 |
| 70° | 195.2 | 202.6 | 209.9 | 215.1 | 219.6 | 221.9 | 223.6 | 229.3 | 235.0 | 277.7 | 320.3 |
| 72.5° | 175.2 | 181.5 | 187.2 | 191.7 | 196.3 | 198.0 | 199.1 | 204.8 | 210.5 | 256.0 | 301.6 |
| 75° | 153.6 | 158.7 | 163.3 | 167.3 | 171.3 | 173.5 | 175.8 | 179.8 | 183.8 | 233.3 | 282.2 |
| 77.5° | 129.7 | 134.8 | 139.4 | 142.8 | 145.7 | 147.9 | 149.6 | 154.8 | 159.9 | 201.4 | 242.4 |
| 80° | 101.3 | 107.5 | 113.2 | 116.1 | 118.3 | 118.9 | 118.9 | 123.5 | 128.0 | 157.6 | 186.6 |
| 82.5° | 71.7 | 78.5 | 84.8 | 87.1 | 89.3 | 89.3 | 89.3 | 94.4 | 99.6 | 119.5 | 138.8 |
| 85° | 42.1 | 49.5 | 56.3 | 58.6 | 60.9 | 62.0 | 62.6 | 64.9 | 66.6 | 80.8 | 94.4 |
| 87.5° | 13.1 | 19.3 | 25.0 | 26.2 | 27.3 | 29.6 | 31.9 | 32.4 | 32.4 | 42.1 | 51.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P387119
 CATALOG NUMBER: GWC-SA2D-760-U-SLL

CANDELA DISTRIBUTION (continued):

| | 275° | 280° | 285° | 290° | 295° | 300° | 305° | 310° | 315° | 320° | 325° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P387119
 CATALOG NUMBER: GWC-SA2D-760-U-SLL

CANDELA DISTRIBUTION (continued):

| | 330° | 335° | 340° | 345° | 350° | 355° | 360° |
|--------|--------|--------|--------|--------|--------|--------|---------|
| 0° | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 | 4335.5 |
| 2.5° | 4265.6 | 4323.6 | 4391.3 | 4458.4 | 4515.9 | 4573.4 | 4621.2 |
| 5° | 3791.0 | 3907.7 | 4050.5 | 4192.7 | 4319.6 | 4446.5 | 4593.9 |
| 7.5° | 3194.8 | 3345.5 | 3530.5 | 3715.4 | 3894.6 | 4073.2 | 4299.7 |
| 10° | 2762.9 | 2916.0 | 3111.7 | 3306.8 | 3508.3 | 3709.1 | 3965.1 |
| 12.5° | 2488.7 | 2612.7 | 2802.2 | 2991.6 | 3228.3 | 3464.4 | 3710.8 |
| 15° | 2307.7 | 2443.2 | 2627.5 | 2811.8 | 3070.7 | 3329.6 | 3613.0 |
| 17.5° | 2114.9 | 2291.8 | 2527.9 | 2764.0 | 3070.7 | 3376.8 | 3710.8 |
| 20° | 1912.9 | 2133.1 | 2439.2 | 2745.3 | 3158.3 | 3570.8 | 3997.0 |
| 22.5° | 1711.5 | 1966.4 | 2358.9 | 2751.0 | 3290.9 | 3830.3 | 4405.5 |
| 25° | 1530.0 | 1824.1 | 2310.0 | 2795.3 | 3483.8 | 4171.7 | 4885.2 |
| 27.5° | 1392.3 | 1713.2 | 2290.1 | 2866.5 | 3728.5 | 4590.4 | 5406.9 |
| 30° | 1269.9 | 1596.5 | 2266.2 | 2935.9 | 3964.0 | 4991.6 | 5814.9 |
| 32.5° | 1164.1 | 1482.7 | 2220.1 | 2956.9 | 4128.4 | 5299.9 | 6160.2 |
| 35° | 1081.0 | 1394.0 | 2142.7 | 2891.5 | 4231.4 | 5571.3 | 6519.8 |
| 37.5° | 1009.4 | 1304.6 | 2054.5 | 2804.4 | 4323.0 | 5841.6 | 6924.3 |
| 40° | 941.1 | 1209.1 | 1978.9 | 2748.1 | 4449.3 | 6150.6 | 7351.6 |
| 42.5° | 876.2 | 1130.5 | 1918.0 | 2705.4 | 4566.5 | 6427.1 | 7725.5 |
| 45° | 827.8 | 1070.2 | 1863.9 | 2657.1 | 4642.2 | 6627.3 | 8007.1 |
| 47.5° | 804.0 | 1034.4 | 1834.9 | 2634.9 | 4717.9 | 6800.3 | 8240.9 |
| 50° | 800.5 | 1028.1 | 1867.9 | 2707.7 | 4881.8 | 7055.2 | 8508.4 |
| 52.5° | 800.0 | 1038.4 | 1962.9 | 2887.5 | 5186.1 | 7484.2 | 8798.0 |
| 55° | 788.0 | 1044.6 | 2076.2 | 3107.1 | 5594.7 | 8081.6 | 9318.6 |
| 57.5° | 751.6 | 1023.0 | 2192.8 | 3362.0 | 6026.5 | 8690.4 | 9905.2 |
| 60° | 695.3 | 970.7 | 2289.0 | 3606.7 | 6316.7 | 9026.1 | 10131.1 |
| 62.5° | 624.7 | 879.1 | 2320.8 | 3762.0 | 6308.7 | 8855.4 | 9903.5 |
| 65° | 564.4 | 782.9 | 2216.1 | 3648.8 | 5989.5 | 8329.7 | 9453.4 |
| 67.5° | 510.9 | 686.7 | 1954.4 | 3221.5 | 5415.4 | 7608.8 | 8881.0 |
| 70° | 472.2 | 623.6 | 1617.0 | 2610.4 | 4696.8 | 6782.7 | 8218.2 |
| 72.5° | 447.8 | 593.4 | 1318.3 | 2042.6 | 3811.5 | 5579.9 | 7029.6 |
| 75° | 414.2 | 546.2 | 1034.4 | 1522.0 | 2917.1 | 4312.2 | 5309.6 |
| 77.5° | 351.6 | 460.3 | 779.5 | 1098.7 | 2140.5 | 3181.7 | 3692.6 |
| 80° | 271.4 | 355.6 | 536.0 | 716.3 | 1473.1 | 2229.8 | 2517.7 |
| 82.5° | 193.4 | 248.1 | 324.9 | 401.7 | 978.6 | 1555.0 | 1578.9 |
| 85° | 119.5 | 144.5 | 186.1 | 227.6 | 647.5 | 1067.4 | 889.3 |
| 87.5° | 64.3 | 76.8 | 98.4 | 119.5 | 207.1 | 294.7 | 169.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P387119
 CATALOG NUMBER: GWC-SA2D-760-U-SLL

CANDELA DISTRIBUTION (continued):

| | 330° | 335° | 340° | 345° | 350° | 355° | 360° |
|--------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245982

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





--- HS — SS



u



| | | | | | | | | | | | |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





| | | | | | | | | | | | | |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





| | | | | | | | | | | | |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





| | | | | | | | | | | | |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





| | | | | | | | | | | | |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





| | | | | | | | | | | | |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





| | | | | | | | |
|------|-----|-----|-----|-----|-----|-----|-----|
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
|------|-----|-----|-----|-----|-----|-----|-----|

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)