

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P227912

Luminaire Tested: **ISC-AF-1200-LED-E1-T4FT-7050**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P227912  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29760)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: ISC-AF-1200-LED-E1-T4FT-7050  
Description: IMPACT ELITE LED CYLINDER LUMINAIRE  
LIGHT SQUARE WITH ACCULED OPTICS-TYPE IV FORWARD THROW  
Light Source: (16) 5000K CCT, 70 CRI LEDs  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6509 lumens  
Efficiency: N/A  
Efficacy: 98.6 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type IV - Short - Non-Cutoff  
BUG Rating: B1 - U0 - G2


Input Watts (W): 66  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



REPORT NUMBER: P227912  
 CATALOG NUMBER: ISC-AF-1200-LED-E1-T4FT-7050

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 10 fc  
 Type IV - Short - Non-Cutoff

REPORT NUMBER: P227912  
CATALOG NUMBER: ISC-AF-1200-LED-E1-T4FT-7050

### Luminous Intensity Polar Plot



— Vertical Plane Through 35-Deg Lateral    - - - Horizontal Cone Through 75-Deg Vertical

REPORT NUMBER: P227912

CATALOG NUMBER: ISC-AF-1200-LED-E1-T4FT-7050

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1306.4	0.0	1306.4
	% Fixture	20.1	0.0	20.1
<b>Street Side</b>	Lumens	5202.6	0.0	5202.6
	% Fixture	79.9	0.0	79.9
<b>Total</b>	Lumens	6509.0	0.0	6509.0
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	91.8	1.4
10°-20°	242.2	3.7
20°-30°	383.2	5.9
30°-40°	618.5	9.5
40°-50°	915.1	14.1
50°-60°	1176.6	18.1
60°-70°	1456.8	22.4
70°-80°	1468.1	22.6
80°-90°	156.7	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6509.0	100.0
0°-180°	6509.0	100.0



REPORT NUMBER: P227912


CATALOG NUMBER: ISC-AF-1200-LED-E1-T4FT-7050

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	361.9	5.6			
FM	(30°-60°)	2066.9	31.8			
FH	(60°-80°)	2644.2	40.6			G2/5000
FVH	(80°-90°)	129.6	2.0			G2/225
BL	(0°-30°)	355.3	5.5	B1/500		
BM	(30°-60°)	643.3	9.9	B1/1000		
BH	(60°-80°)	280.7	4.3	B1/500		G1/500
BVH	(80°-90°)	27.1	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B1-U0-G2**

Type IV Short





REPORT NUMBER: P227912

CATALOG NUMBER: ISC-AF-1200-LED-E1-T4FT-7050

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	37°	45°	55°	65°	75°	85°
0°	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8
2.5°	949.6	947.4	945.2	945.2	949.6	949.6	951.7	953.9	956.1	962.6	971.3
5°	923.5	921.3	919.1	921.3	927.8	927.8	934.4	938.7	943.0	953.9	964.8
7.5°	888.7	888.7	886.6	895.2	901.8	899.6	908.3	912.6	923.5	934.4	951.7
10°	843.1	843.1	843.1	854.0	864.8	864.8	871.3	882.2	890.9	906.1	927.8
12.5°	804.0	801.8	801.8	810.5	823.5	825.7	836.6	851.8	862.7	882.2	906.1
15°	790.9	786.6	775.7	775.7	782.3	782.3	799.6	821.4	838.7	858.3	886.6
17.5°	793.1	786.6	758.4	749.7	749.7	751.8	769.2	793.1	814.8	838.7	875.7
20°	812.7	801.8	749.7	730.1	725.8	727.9	743.1	767.0	793.1	825.7	867.0
22.5°	897.4	880.0	782.3	738.8	719.2	719.2	727.9	754.0	786.6	830.1	882.2
25°	1093.0	1064.7	890.9	812.7	754.0	747.5	732.3	758.4	797.5	849.6	925.7
27.5°	1292.9	1264.6	1025.6	940.9	849.6	830.1	773.6	780.1	823.5	893.1	990.9
30°	1460.2	1436.3	1195.1	1097.3	975.6	953.9	867.0	825.7	869.2	953.9	1088.6
32.5°	1473.2	1462.4	1377.6	1277.7	1129.9	1099.5	984.3	919.1	940.9	1036.5	1195.1
35°	1594.9	1586.2	1540.6	1445.0	1297.2	1262.5	1140.8	1040.8	1034.3	1127.7	1316.8
37.5°	1714.4	1703.6	1673.2	1608.0	1471.1	1442.8	1347.2	1186.4	1140.8	1234.2	1436.3
40°	1827.4	1812.2	1773.1	1736.2	1636.2	1636.2	1534.1	1325.5	1242.9	1327.7	1536.3
42.5°	2036.0	1988.2	1883.9	1855.7	1827.4	1827.4	1677.5	1421.1	1325.5	1429.8	1631.9
45°	2235.9	2190.3	2049.1	1992.6	2007.8	1999.1	1792.7	1475.4	1399.4	1525.4	1723.1
47.5°	2394.6	2353.3	2209.9	2170.8	2214.2	2179.4	1888.3	1518.9	1492.8	1627.5	1799.2
50°	2535.8	2438.0	2299.0	2351.1	2405.4	2346.8	1973.0	1584.1	1586.2	1736.2	1910.0
52.5°	2342.4	2331.5	2362.0	2483.7	2535.8	2470.6	2049.1	1666.6	1686.2	1875.2	2036.0
55°	2109.9	2107.7	2285.9	2522.8	2585.8	2524.9	2099.0	1766.6	1790.5	2046.9	2194.7
57.5°	2064.3	2042.5	2164.2	2440.2	2555.4	2511.9	2125.1	1860.0	1890.4	2264.2	2351.1
60°	2212.0	2170.8	2151.2	2351.1	2490.2	2468.4	2157.7	1970.8	2012.1	2511.9	2496.7
62.5°	2533.6	2477.1	2338.1	2357.6	2483.7	2466.3	2235.9	2101.2	2149.0	2759.6	2579.3
65°	2959.5	2918.2	2696.6	2538.0	2585.8	2561.9	2377.2	2266.4	2292.4	2937.8	2485.8
67.5°	3426.7	3370.2	3129.0	2911.7	2850.9	2805.2	2601.0	2461.9	2368.5	2911.7	2235.9
70°	3954.7	3893.9	3685.3	3461.5	3357.2	3307.2	2992.1	2631.4	2340.2	2624.9	1764.4
72.5°	4604.4	4521.9	4406.7	4430.6	4413.2	4274.1	3615.7	2687.9	2133.8	1953.5	1053.9
75°	4126.4	4032.9	4052.5	4650.1	5475.8	5469.3	4337.2	2548.8	1590.6	921.3	456.3
77.5°	1479.8	1636.2	2414.1	3483.2	4591.4	4584.9	3357.2	1594.9	682.3	393.3	276.0
80°	371.6	378.1	599.7	1429.8	2681.4	2659.7	1903.5	601.9	284.7	239.0	189.0
82.5°	119.5	128.2	219.5	493.3	1147.3	1121.2	591.0	197.7	178.2	154.3	115.2
85°	39.1	39.1	78.2	169.5	378.1	362.9	119.5	71.7	97.8	80.4	52.2
87.5°	0.0	0.0	2.2	4.3	8.7	4.3	0.0	4.3	13.0	15.2	10.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P227912

CATALOG NUMBER: ISC-AF-1200-LED-E1-T4FT-7050

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8	977.8
2.5°	977.8	975.6	984.3	990.9	993.0	999.5	1006.1	1010.4	1008.2	1006.1	1006.1
5°	975.6	977.8	993.0	1006.1	1016.9	1027.8	1036.5	1040.8	1038.7	1038.7	1038.7
7.5°	962.6	971.3	988.7	1010.4	1025.6	1032.1	1034.3	1027.8	1023.4	1016.9	1016.9
10°	940.9	953.9	982.2	1006.1	1012.6	1003.9	990.9	977.8	960.4	949.6	949.6
12.5°	923.5	938.7	973.5	993.0	984.3	962.6	934.4	912.6	895.2	882.2	880.0
15°	908.3	927.8	964.8	969.1	949.6	912.6	875.7	851.8	832.2	823.5	823.5
17.5°	897.4	923.5	956.1	943.0	903.9	856.1	821.4	801.8	786.6	777.9	775.7
20°	899.6	932.2	947.4	910.5	854.0	804.0	771.4	760.5	749.7	745.3	745.3
22.5°	923.5	953.9	945.2	882.2	808.3	751.8	730.1	727.9	723.6	719.2	717.1
25°	975.6	997.4	951.7	854.0	760.5	704.0	693.2	699.7	697.5	693.2	693.2
27.5°	1047.3	1051.7	962.6	825.7	708.4	658.4	658.4	669.3	664.9	658.4	662.7
30°	1134.3	1110.4	967.0	780.1	647.5	614.9	621.5	628.0	623.6	614.9	614.9
32.5°	1227.7	1171.2	967.0	721.4	588.9	575.8	578.0	580.2	571.5	560.6	560.6
35°	1319.0	1229.9	956.1	651.9	543.2	536.7	534.5	543.2	536.7	521.5	521.5
37.5°	1405.9	1275.5	927.8	580.2	508.5	506.3	512.8	508.5	499.8	478.0	473.7
40°	1466.7	1305.9	871.3	521.5	480.2	493.3	488.9	465.0	452.0	436.8	436.8
42.5°	1521.0	1321.1	801.8	475.9	460.7	478.0	460.7	430.2	412.9	410.7	412.9
45°	1571.0	1334.2	734.4	438.9	436.8	460.7	438.9	406.3	386.8	386.8	389.0
47.5°	1618.8	1347.2	667.1	404.2	408.5	434.6	421.5	389.0	369.4	356.4	356.4
50°	1694.9	1377.6	569.3	367.2	375.9	412.9	408.5	371.6	349.8	330.3	325.9
52.5°	1786.1	1429.8	462.8	328.1	352.0	393.3	393.3	356.4	332.5	306.4	302.0
55°	1907.8	1486.3	371.6	299.9	328.1	371.6	378.1	349.8	315.1	291.2	286.8
57.5°	2029.5	1505.8	299.9	271.6	297.7	349.8	367.2	336.8	295.5	278.1	276.0
60°	2114.3	1442.8	252.1	247.7	276.0	323.8	352.0	321.6	282.5	265.1	265.1
62.5°	2101.2	1251.6	226.0	232.5	258.6	304.2	339.0	308.6	273.8	262.9	260.8
65°	1916.5	945.2	204.3	219.5	243.4	284.7	325.9	302.0	269.4	258.6	254.2
67.5°	1614.5	628.0	189.0	206.4	228.2	269.4	315.1	293.3	256.4	249.9	245.5
70°	1169.0	367.2	173.8	193.4	212.9	252.1	299.9	276.0	241.2	236.8	226.0
72.5°	632.3	230.3	156.5	176.0	193.4	230.3	276.0	254.2	221.6	204.3	197.7
75°	289.0	167.3	139.1	156.5	169.5	202.1	247.7	223.8	197.7	176.0	171.7
77.5°	193.4	126.0	117.3	134.7	141.2	169.5	219.5	178.2	154.3	139.1	134.7
80°	132.5	93.4	95.6	110.8	108.6	134.7	165.1	143.4	121.7	126.0	115.2
82.5°	84.7	65.2	73.9	78.2	76.1	102.1	128.2	108.6	91.3	76.1	65.2
85°	36.9	34.8	43.5	45.6	45.6	56.5	67.4	54.3	41.3	30.4	30.4
87.5°	2.2	4.3	4.3	6.5	4.3	2.2	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)