

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P437507

Luminaire Tested: ISC-SA1D-735-U-T3-HSS

Issue Date: 12/9/2020

Test Information

Test Method: LM-79-2019
Report Number: P437507
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-074-9)
Test Lab: INNOVATION CENTER
Issue Date: 12/9/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: MCGRAW-EDISON
Catalog Number: ISC-SA1D-735-U-T3-HSS
Description: IMPACT ELITE LED CYLINDER LUMINAIRE
(1) 70 CRI, 3500K, 800mA LIGHTSQUARE WITH 16 LEDS AND TYPE III OPTICS WITH HOUSE SIDE
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3973.0 lumens
Efficiency: N/A
Efficacy: 87.9 lumens/watt
Spacing Criteria (0/90/45): 2.48 / 3.57 / 2.91
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 45.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P437507

CATALOG NUMBER: ISC-SA1D-735-U-T3-HSS

Luminous Intensity Polar Plot





TEST NUMBER: P437507

CATALOG NUMBER: ISC-SA1D-735-U-T3-HSS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	107	101	96	92	104	99	94	90	95	91	87	91	88	85	87	84	82	80
2	94	84	76	69	92	82	75	68	79	72	67	75	70	65	72	68	64	61
3	83	71	61	53	81	69	60	52	66	58	51	63	56	50	60	54	49	47
4	74	60	49	41	72	58	48	41	56	47	40	53	46	39	51	44	39	36
5	67	51	41	33	64	50	40	32	48	39	32	46	38	31	44	37	31	29
6	60	45	34	26	58	44	34	26	42	33	26	40	32	26	38	31	25	23
7	55	39	29	22	53	38	29	22	37	28	21	35	27	21	34	26	21	19
8	51	35	25	18	49	34	25	18	33	24	18	31	24	18	30	23	18	16
9	47	32	22	16	45	31	22	16	30	21	16	28	21	15	27	20	15	13
10	44	29	20	14	42	28	19	14	27	19	14	26	19	13	25	18	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	20352	20352	20352	20352	20352
5°	18840	19678	20681	20179	20179
10°	17873	19399	22192	19989	17619
15°	17964	19947	24440	17273	8117
20°	21306	21484	27519	9145	5682
25°	32214	24665	30651	5615	5064
30°	45466	33037	35159	4624	3659
35°	57334	46133	43889	3869	2444
40°	72302	63051	57711	3046	1742
45°	95555	89892	81519	2356	1181
50°	124842	132626	110307	1815	777
55°	151684	191972	141070	1456	728
60°	165334	258756	175512	999	499
65°	114083	278108	191266	784	194
70°	30238	194633	142440	730	0
75°	8384	54148	40607	316	0
80°	5281	14902	6248	967	0
85°	0	2865	2865	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 57°
 Vertical Angle: 67.5°
 Luminance: 362282 cd/sqm

TEST NUMBER: P437507

CATALOG NUMBER: ISC-SA1D-735-U-T3-HSS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.0	1.1
10°-20°	118.9	3.0
20°-30°	205.3	5.2
30°-40°	363.7	9.2
40°-50°	659.6	16.6
50°-60°	1111.1	28.0
60°-70°	1142.5	28.8
70°-80°	316.6	8.0
80°-90°	11.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	368.2	9.3
0°-40°	731.9	18.4
0°-60°	2502.7	63.0
0°-90°	3973.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3973.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	473	473	473	473	473	
5°	436	455	478	467	467	41
15°	403	448	548	388	182	119
25°	678	519	645	118	107	322
35°	1091	878	835	74	46	695
45°	1569	1476	1339	39	19	1221
55°	2021	2557	1879	19	10	1774
65°	1120	2730	1877	8	2	1077
75°	50	326	244	2	0	79
85°	0	6	6	0	0	6
90°	0	0	0	0	0	



TEST NUMBER: P437507

CATALOG NUMBER: ISC-SA1D-735-U-T3-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	57°	65°	75°	85°
0°	472.7	472.7	472.7	472.7	472.7	472.7	472.7	472.7	472.7	472.7	472.7
2.5°	459.2	459.2	463.0	465.0	465.0	466.9	468.9	470.8	470.8	470.8	474.7
5°	435.9	434.0	437.9	441.7	447.5	455.3	461.1	465.0	470.8	476.6	478.5
7.5°	414.6	414.6	418.5	424.3	435.9	447.5	459.2	465.0	474.7	486.3	490.2
10°	408.8	406.9	412.7	418.5	430.1	443.7	461.1	468.9	482.4	497.9	503.7
12.5°	404.9	404.9	406.9	416.5	428.2	445.6	466.9	472.7	494.0	511.5	525.0
15°	403.0	403.0	406.9	414.6	428.2	447.5	476.6	486.3	511.5	536.7	548.3
17.5°	418.5	416.5	414.6	418.5	432.0	453.4	492.1	501.8	532.8	563.8	577.4
20°	465.0	463.0	457.2	443.7	443.7	468.9	511.5	523.1	563.8	594.8	602.5
22.5°	552.2	558.0	536.7	501.8	476.6	488.2	536.7	550.2	596.7	629.7	629.7
25°	678.1	670.3	651.0	592.9	542.5	519.2	558.0	571.5	627.7	666.5	658.7
27.5°	809.8	811.8	784.7	718.8	637.4	575.4	581.2	596.7	660.7	705.2	687.8
30°	914.5	906.7	893.2	838.9	749.8	664.5	625.8	635.5	697.5	747.8	732.3
32.5°	1007.5	1003.6	986.1	939.6	860.2	769.2	699.4	701.3	749.8	811.8	792.4
35°	1090.8	1094.6	1086.9	1034.6	962.9	877.7	798.2	804.0	840.8	904.8	866.0
37.5°	1195.4	1195.4	1181.8	1133.4	1079.1	993.9	918.3	920.3	939.6	992.0	943.5
40°	1286.4	1290.3	1288.4	1251.6	1199.3	1121.8	1030.7	1030.7	1036.5	1098.5	1073.3
42.5°	1410.4	1416.3	1414.3	1379.4	1338.8	1282.6	1205.1	1199.3	1195.4	1272.9	1245.8
45°	1569.3	1582.9	1588.7	1546.1	1509.3	1476.3	1416.3	1393.0	1402.7	1474.4	1453.1
47.5°	1720.4	1735.9	1763.1	1741.7	1724.3	1724.3	1642.9	1639.1	1623.6	1706.9	1648.7
50°	1863.8	1865.7	1904.5	1937.4	1989.7	1980.0	1925.8	1902.5	1879.3	1935.5	1830.9
52.5°	1945.2	1968.4	2018.8	2113.7	2228.0	2274.5	2218.3	2204.8	2158.3	2150.5	2007.2
55°	2020.7	2020.7	2100.2	2264.8	2458.6	2557.4	2510.9	2495.4	2402.4	2375.3	2189.3
57.5°	2045.9	2038.2	2144.7	2354.0	2644.6	2817.0	2826.7	2791.8	2662.0	2578.7	2375.3
60°	1920.0	1906.4	2018.8	2295.8	2695.0	3004.9	3109.6	3086.3	2886.8	2776.3	2571.0
62.5°	1557.7	1575.1	1718.5	2018.8	2516.7	2985.6	3297.5	3283.9	3053.4	2910.0	2648.5
65°	1119.8	1090.8	1218.6	1551.9	2065.3	2729.8	3340.1	3349.8	3156.1	2954.6	2584.5
67.5°	627.7	600.6	707.2	961.0	1468.6	2239.7	3165.7	3220.0	3082.4	2844.1	2309.4
70°	240.2	255.7	329.4	474.7	866.0	1546.1	2724.0	2801.5	2702.7	2373.3	1720.4
72.5°	85.2	96.9	135.6	211.2	401.0	833.1	1904.5	2020.7	1991.7	1648.7	984.2
75°	50.4	52.3	69.7	102.7	176.3	325.5	1075.3	1172.1	1125.6	815.7	406.9
77.5°	34.9	34.9	44.6	62.0	100.7	129.8	420.4	476.6	490.2	294.5	120.1
80°	21.3	23.2	31.0	40.7	58.1	60.1	129.8	153.1	143.4	104.6	42.6
82.5°	9.7	9.7	17.4	27.1	29.1	25.2	40.7	44.6	52.3	46.5	19.4
85°	0.0	0.0	5.8	9.7	7.7	5.8	13.6	13.6	17.4	21.3	9.7
87.5°	0.0	0.0	0.0	0.0	1.9	1.9	1.9	1.9	1.9	3.9	1.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P437507

CATALOG NUMBER: ISC-SA1D-735-U-T3-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	472.7	472.7	472.7	472.7	472.7	472.7	472.7	472.7	472.7	472.7	472.7
2.5°	474.7	476.6	474.7	472.7	472.7	470.8	470.8	470.8	470.8	470.8	470.8
5°	478.5	480.5	478.5	474.7	470.8	466.9	463.0	463.0	463.0	463.0	466.9
7.5°	490.2	490.2	486.3	478.5	468.9	465.0	457.2	455.3	451.4	449.5	451.4
10°	507.6	507.6	499.9	488.2	472.7	457.2	443.7	424.3	412.7	404.9	403.0
12.5°	525.0	523.1	513.4	497.9	472.7	437.9	393.3	344.9	315.8	294.5	290.6
15°	548.3	546.4	530.9	503.7	461.1	387.5	300.3	234.4	199.6	184.1	182.1
17.5°	573.5	569.6	548.3	507.6	424.3	292.6	197.6	153.1	139.5	135.6	135.6
20°	600.6	594.8	561.9	501.8	350.7	199.6	137.6	127.9	125.9	124.0	124.0
22.5°	621.9	612.2	571.5	472.7	261.6	137.6	122.1	120.1	118.2	116.2	116.2
25°	645.2	629.7	579.3	408.8	172.4	118.2	114.3	112.4	108.5	106.6	106.6
27.5°	672.3	649.0	590.9	321.6	120.1	106.6	102.7	100.7	94.9	91.1	91.1
30°	707.2	678.1	596.7	234.4	100.7	93.0	89.1	85.2	77.5	73.6	73.6
32.5°	763.3	738.2	585.1	156.9	91.1	83.3	77.5	69.7	62.0	58.1	56.2
35°	835.0	800.2	544.4	110.4	81.4	73.6	63.9	54.2	48.4	46.5	46.5
37.5°	914.5	868.0	482.4	89.1	73.6	63.9	54.2	44.6	38.7	36.8	36.8
40°	1026.8	955.1	397.2	77.5	63.9	54.2	44.6	36.8	32.9	31.0	31.0
42.5°	1174.1	1065.6	300.3	71.7	58.1	46.5	36.8	31.0	27.1	25.2	25.2
45°	1338.8	1181.8	218.9	63.9	50.4	38.7	29.1	25.2	21.3	19.4	19.4
47.5°	1503.4	1265.1	151.1	58.1	42.6	32.9	25.2	19.4	15.5	15.5	13.6
50°	1646.8	1309.7	108.5	50.4	38.7	27.1	19.4	15.5	13.6	11.6	11.6
52.5°	1772.7	1329.1	83.3	44.6	32.9	23.2	15.5	13.6	11.6	11.6	11.6
55°	1879.3	1313.6	65.9	38.7	29.1	19.4	13.6	11.6	9.7	9.7	9.7
57.5°	1983.9	1267.1	52.3	32.9	23.2	13.6	11.6	9.7	7.7	7.7	7.7
60°	2038.2	1207.0	42.6	27.1	19.4	11.6	9.7	7.7	7.7	5.8	5.8
62.5°	2001.4	1085.0	34.9	23.2	13.6	9.7	7.7	5.8	5.8	3.9	3.9
65°	1877.4	930.0	27.1	17.4	9.7	7.7	5.8	5.8	3.9	1.9	1.9
67.5°	1582.9	728.5	21.3	13.6	7.7	5.8	3.9	3.9	1.9	0.0	0.0
70°	1131.5	480.5	17.4	9.7	5.8	5.8	3.9	1.9	0.0	0.0	0.0
72.5°	652.9	232.5	13.6	5.8	3.9	3.9	1.9	1.9	0.0	0.0	0.0
75°	244.1	81.4	11.6	5.8	3.9	1.9	1.9	1.9	0.0	0.0	0.0
77.5°	81.4	32.9	9.7	7.7	5.8	1.9	1.9	0.0	0.0	0.0	0.0
80°	25.2	15.5	3.9	3.9	3.9	3.9	1.9	0.0	0.0	0.0	0.0
82.5°	13.6	7.7	1.9	1.9	1.9	1.9	0.0	0.0	0.0	0.0	0.0
85°	5.8	3.9	1.9	1.9	1.9	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	1.9	1.9	1.9	1.9	1.9	1.9	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-121-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 03/04/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: **IFLD-S-SA2A-735-U-T2**
 Description: STREETWORKS INF FLOOD

PROGRAMMED @ 615mA.

Spectral Parameters

CCT (K):	3388	CRI (Ra):	73.1	R9:	-34.6
CIE u':	0.2371	R1:	68.9	R10:	57.8
CIE v':	0.5177	R2:	81.1	R11:	68.6
Duv:	0.0032	R3:	93.1	R12:	53.9
CIE x:	0.4153	R4:	71.6	R13:	70.9
CIE y:	0.4030	R5:	69.4	R14:	96.2
CIE z:	0.1817	R6:	75.0		
Peak Wavelength (nm):	590	R7:	79.5		
Dominant Wavelength (nm):	580	R8:	46.4		
Purity:	45.7				
Rf:	76.9				
Rg:	94.4				



Test Conditions

Stabilization Time: 81M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0/30%
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-7

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	1/31/2021	7/31/2021
Power Meter	IN0071	12/1/2020	12/1/2021
AC Power Source	IN0063	12/1/2020	12/1/2021
DC Power Source	IN0208	12/1/2020	12/1/2021
Sphere Thermometer	IN0085	12/1/2020	12/1/2021
Room Thermometer	IN0046	12/1/2020	12/1/2021

REPORT NUMBER: SP1-2101-121-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-7

Photopic Flux vs. Wavelength



#####

λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)
360	2672	0.0	490	34553	4.9	620	136720	35.6	750	5870	0.0	880	4216	0.0
365	2252	0.0	495	44336	8.0	625	126308	27.9	755	5421	0.0	885	4132	0.0
370	2217	0.0	500	54643	12.1	630	114625	20.7	760	5097	0.0	890	3992	0.0
375	2697	0.0	505	64676	18.1	635	103216	15.5	765	4626	0.0	895	3214	0.0
380	3039	0.0	510	73825	25.4	640	92605	11.1	770	3782	0.0	900	2580	0.0
385	2655	0.0	515	81872	33.9	645	83234	8.0	775	3506	0.0	905	1776	0.0
390	2357	0.0	520	88574	43.0	650	73263	5.4	780	3507	0.0	910	3995	0.0
395	2186	0.0	525	93289	50.1	655	64627	3.7	785	3267	0.0	915	4288	0.0
400	2015	0.0	530	98393	57.9	660	56614	2.4	790	2849	0.0	920	2446	0.0
405	2234	0.0	535	103269	64.0	665	49537	1.6	795	3037	0.0	925	3009	0.0
410	3412	0.0	540	107316	69.9	670	42866	0.9	800	2716	0.0	930	3026	0.0
415	6135	0.0	545	113101	75.3	675	36708	0.6	805	2648	0.0	935	4734	0.0
420	12146	0.0	550	120690	82.0	680	31814	0.4	810	3187	0.0	940	3719	0.0
425	23983	0.1	555	128583	87.8	685	27485	0.2	815	2931	0.0	945	1480	0.0
430	42142	0.3	560	137796	93.6	690	23698	0.1	820	2717	0.0	950	3450	0.0
435	68228	0.8	565	146577	97.5	695	20309	0.1	825	2236	0.0	955	5051	0.0
440	99323	1.6	570	154581	100.5	700	17890	0.1	830	2628	0.0	960	3176	0.0
445	115584	2.4	575	162633	101.2	705	15500	0.0	835	3140	0.0	965	5178	0.0
450	94997	2.5	580	168101	99.9	710	13699	0.0	840	3675	0.0	970	6385	0.0
455	61433	2.1	585	173145	96.2	715	12398	0.0	845	3283	0.0	975	3810	0.0
460	43373	1.8	590	174675	90.3	720	11147	0.0	850	3055	0.0	980	4322	0.0
465	32472	1.7	595	173724	82.3	725	9761	0.0	855	2932	0.0	985	4200	0.0
470	24257	1.5	600	171241	73.8	730	8651	0.0	860	3382	0.0	990	4661	0.0
475	21690	1.7	605	165134	64.0	735	7730	0.0	865	2605	0.0	995	6746	0.0
480	23173	2.2	610	156652	53.8	740	6847	0.0	870	3325	0.0	1000	4150	0.0
485	27564	3.3	615	147879	44.6	745	6124	0.0	875	3325	0.0			

REPORT NUMBER: SP1-2101-121-7

Scotopic Flux vs. Wavelength



Scotopic Lumens: 12126

S/P: 1.36

λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)
360	2672	0.0	490	34553	53.2	620	136720	1.7	750	5870	0.0	880	4216	0.0
365	2252	0.0	495	44336	71.7	625	126308	1.1	755	5421	0.0	885	4132	0.0
370	2217	0.0	500	54643	91.4	630	114625	0.6	760	5097	0.0	890	3992	0.0
375	2697	0.0	505	64676	110.0	635	103216	0.4	765	4626	0.0	895	3214	0.0
380	3039	0.0	510	73825	125.1	640	92605	0.2	770	3782	0.0	900	2580	0.0
385	2655	0.0	515	81872	135.7	645	83234	0.1	775	3506	0.0	905	1776	0.0
390	2357	0.0	520	88574	140.8	650	73263	0.1	780	3507	0.0	910	3995	0.0
395	2186	0.0	525	93289	139.6	655	64627	0.1	785	3267	0.0	915	4288	0.0
400	2015	0.0	530	98393	135.7	660	56614	0.0	790	2849	0.0	920	2446	0.0
405	2234	0.1	535	103269	128.7	665	49537	0.0	795	3037	0.0	925	3009	0.0
410	3412	0.2	540	107316	118.6	670	42866	0.0	800	2716	0.0	930	3026	0.0
415	6135	0.6	545	113101	108.4	675	36708	0.0	805	2648	0.0	935	4734	0.0
420	12146	2.0	550	120690	98.7	680	31814	0.0	810	3187	0.0	940	3719	0.0
425	23983	5.9	555	128583	87.9	685	27485	0.0	815	2931	0.0	945	1480	0.0
430	42142	14.3	560	137796	77.0	690	23698	0.0	820	2717	0.0	950	3450	0.0
435	68228	30.5	565	146577	65.8	695	20309	0.0	825	2236	0.0	955	5051	0.0
440	99323	55.5	570	154581	54.6	700	17890	0.0	830	2628	0.0	960	3176	0.0
445	115584	77.4	575	162633	44.3	705	15500	0.0	835	3140	0.0	965	5178	0.0
450	94997	73.6	580	168101	34.6	710	13699	0.0	840	3675	0.0	970	6385	0.0
455	61433	53.7	585	173145	26.5	715	12398	0.0	845	3283	0.0	975	3810	0.0
460	43373	41.9	590	174675	19.5	720	11147	0.0	850	3055	0.0	980	4322	0.0
465	32472	34.3	595	173724	13.9	725	9761	0.0	855	2932	0.0	985	4200	0.0
470	24257	27.9	600	171241	9.7	730	8651	0.0	860	3382	0.0	990	4661	0.0
475	21690	27.1	605	165134	6.5	735	7730	0.0	865	2605	0.0	995	6746	0.0
480	23173	31.3	610	156652	4.2	740	6847	0.0	870	3325	0.0	1000	4150	0.0
485	27564	40.0	615	147879	2.7	745	6124	0.0	875	3325	0.0			

REPORT NUMBER: SP1-2101-121-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: 4490.7 M/P: 0.5

λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)	λ (nm)	Power (µW/nm)	Lumens (φ/nm)
360	2672	0.0	490	34553	28.8	620	136720	0.1	750	5870	0.0	880	4216	0.0
365	2252	0.0	495	44336	36.6	625	126308	0.1	755	5421	0.0	885	4132	0.0
370	2217	0.0	500	54643	43.9	630	114625	0.0	760	5097	0.0	890	3992	0.0
375	2697	0.0	505	64676	49.6	635	103216	0.0	765	4626	0.0	895	3214	0.0
380	3039	0.0	510	73825	53.0	640	92605	0.0	770	3782	0.0	900	2580	0.0
385	2655	0.0	515	81872	53.5	645	83234	0.0	775	3506	0.0	905	1776	0.0
390	2357	0.0	520	88574	51.6	650	73263	0.0	780	3507	0.0	910	3995	0.0
395	2186	0.0	525	93289	47.3	655	64627	0.0	785	3267	0.0	915	4288	0.0
400	2015	0.0	530	98393	42.5	660	56614	0.0	790	2849	0.0	920	2446	0.0
405	2234	0.0	535	103269	37.2	665	49537	0.0	795	3037	0.0	925	3009	0.0
410	3412	0.1	540	107316	31.4	670	42866	0.0	800	2716	0.0	930	3026	0.0
415	6135	0.4	545	113101	26.3	675	36708	0.0	805	2648	0.0	935	4734	0.0
420	12146	1.4	550	120690	21.7	680	31814	0.0	810	3187	0.0	940	3719	0.0
425	23983	3.7	555	128583	17.3	685	27485	0.0	815	2931	0.0	945	1480	0.0
430	42142	8.9	560	137796	13.6	690	23698	0.0	820	2717	0.0	950	3450	0.0
435	68228	18.2	565	146577	10.3	695	20309	0.0	825	2236	0.0	955	5051	0.0
440	99323	33.2	570	154581	7.6	700	17890	0.0	830	2628	0.0	960	3176	0.0
445	115584	45.6	575	162633	5.4	705	15500	0.0	835	3140	0.0	965	5178	0.0
450	94997	43.8	580	168101	3.8	710	13699	0.0	840	3675	0.0	970	6385	0.0
455	61433	32.2	585	173145	2.6	715	12398	0.0	845	3283	0.0	975	3810	0.0
460	43373	25.6	590	174675	1.7	720	11147	0.0	850	3055	0.0	980	4322	0.0
465	32472	21.2	595	173724	1.1	725	9761	0.0	855	2932	0.0	985	4200	0.0
470	24257	17.4	600	171241	0.7	730	8651	0.0	860	3382	0.0	990	4661	0.0
475	21690	16.6	605	165134	0.5	735	7730	0.0	865	2605	0.0	995	6746	0.0
480	23173	18.6	610	156652	0.3	740	6847	0.0	870	3325	0.0	1000	4150	0.0
485	27564	22.7	615	147879	0.2	745	6124	0.0	875	3325	0.0			

Summary

$R_f = 76.9$
 $R_g = 94.4$
 $CIE R_a = 73.1$
 $R_g = -34.6$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 68	CES51 = 90	CES76 = 63
CES02 = 62	CES27 = 88	CES52 = 89	CES77 = 80
CES03 = 31	CES28 = 87	CES53 = 80	CES78 = 65
CES04 = 70	CES29 = 67	CES54 = 84	CES79 = 87
CES05 = 48	CES30 = 74	CES55 = 84	CES80 = 86
CES06 = 51	CES31 = 71	CES56 = 75	CES81 = 75
CES07 = 40	CES32 = 67	CES57 = 74	CES82 = 94
CES08 = 39	CES33 = 74	CES58 = 76	CES83 = 91
CES09 = 29	CES34 = 78	CES59 = 87	CES84 = 89
CES10 = 75	CES35 = 89	CES60 = 93	CES85 = 80
CES11 = 58	CES36 = 98	CES61 = 86	CES86 = 66
CES12 = 64	CES37 = 86	CES62 = 89	CES87 = 79
CES13 = 43	CES38 = 82	CES63 = 77	CES88 = 79
CES14 = 74	CES39 = 95	CES64 = 74	CES89 = 70
CES15 = 71	CES40 = 91	CES65 = 68	CES90 = 77
CES16 = 47	CES41 = 89	CES66 = 71	CES91 = 88
CES17 = 50	CES42 = 88	CES67 = 69	CES92 = 60
CES18 = 56	CES43 = 82	CES68 = 74	CES93 = 77
CES19 = 72	CES44 = 99	CES69 = 82	CES94 = 52
CES20 = 65	CES45 = 87	CES70 = 67	CES95 = 69
CES21 = 86	CES46 = 82	CES71 = 66	CES96 = 78
CES22 = 79	CES47 = 82	CES72 = 88	CES97 = 85
CES23 = 92	CES48 = 72	CES73 = 59	CES98 = 76
CES24 = 91	CES49 = 82	CES74 = 97	CES99 = 63
CES25 = 72	CES50 = 88	CES75 = 66	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)