

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P437352

Luminaire Tested: **ISC-SA1C-740-U-SLR**

Issue Date: 12/9/2020

Test Information

Test Method: LM-79-08
Report Number: P437352
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-074-22)
Test Lab: INNOVATION CENTER
Issue Date: 12/9/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: ISC-SA1C-740-U-SLR
Description: IMPACT ELITE LED CYLINDER LUMINAIRE
(1) 70 CRI, 4000K, 615mA LIGHTSQUARE WITH 16 LEDS AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4033 lumens
Efficiency: N/A
Efficacy: 117.9 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G1


Input Watts (W): 34.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P437352
 CATALOG NUMBER: ISC-SA1C-740-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 2.1 fc
 Type IV - Short - N/A

REPORT NUMBER: P437352
CATALOG NUMBER: ISC-SA1C-740-U-SLR

Luminous Intensity Polar Plot



— Vertical Plane Through 355-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P437352
 CATALOG NUMBER: ISC-SA1C-740-U-SLR

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 727.0 | 0.0 | 727.0 |
| | % Fixture | 18.0 | 0.0 | 18.0 |
| Street Side | Lumens | 3305.9 | 0.0 | 3305.9 |
| | % Fixture | 82.0 | 0.0 | 82.0 |
| Total | Lumens | 4033.0 | 0.0 | 4033.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 97.4 | 2.4 |
| 10°-20° | 201.2 | 5.0 |
| 20°-30° | 286.7 | 7.1 |
| 30°-40° | 409.8 | 10.2 |
| 40°-50° | 572.3 | 14.2 |
| 50°-60° | 796.0 | 19.7 |
| 60°-70° | 969.7 | 24.0 |
| 70°-80° | 597.2 | 14.8 |
| 80°-90° | 102.6 | 2.5 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 4033.0 | 100.0 |
| 0°-180° | 4033.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P437352
 CATALOG NUMBER: ISC-SA1C-740-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 403.2 | 10.0 | | | |
| FM (30°-60°) | 1464.5 | 36.3 | | | |
| FH (60°-80°) | 1355.8 | 33.6 | | | G1/1800 |
| FVH (80°-90°) | 82.4 | 2.0 | | | G1/100 |
| BL (0°-30°) | 182.1 | 4.5 | B1/500 | | |
| BM (30°-60°) | 313.7 | 7.8 | B1/1000 | | |
| BH (60°-80°) | 211.1 | 5.2 | B1/500 | | G1/500 |
| BVH (80°-90°) | 20.2 | 0.5 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G1
 Type IV Short





REPORT NUMBER: P437352
 CATALOG NUMBER: ISC-SA1C-740-U-SLR

CANDELA DISTRIBUTION (FULL):

| | 0° | 1° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1290.4 | 1290.4 | 1290.4 | 1290.4 | 1290.4 | 1290.4 | 1290.4 | 1290.4 | 1290.4 | 1290.4 | 1290.4 |
| 2.5° | 1323.1 | 1323.1 | 1306.7 | 1265.9 | 1228.3 | 1189.1 | 1176.1 | 1140.1 | 1117.3 | 1096.0 | 1104.2 |
| 5° | 1246.3 | 1241.4 | 1212.0 | 1127.1 | 1061.7 | 998.0 | 958.8 | 900.0 | 893.5 | 841.2 | 838.0 |
| 7.5° | 1143.4 | 1140.1 | 1096.0 | 999.7 | 924.5 | 824.9 | 766.1 | 715.4 | 671.3 | 640.3 | 630.5 |
| 10° | 1073.2 | 1061.7 | 1007.8 | 890.2 | 780.8 | 708.9 | 676.2 | 632.1 | 594.6 | 555.4 | 522.7 |
| 12.5° | 1027.4 | 1014.4 | 960.5 | 831.4 | 725.2 | 676.2 | 630.5 | 578.2 | 527.6 | 481.9 | 449.2 |
| 15° | 1035.6 | 1014.4 | 953.9 | 816.7 | 705.6 | 635.4 | 571.7 | 509.6 | 450.8 | 400.2 | 359.4 |
| 17.5° | 1094.4 | 1068.3 | 1001.3 | 826.5 | 674.6 | 581.5 | 494.9 | 423.1 | 351.2 | 298.9 | 266.2 |
| 20° | 1197.3 | 1159.7 | 1074.8 | 854.3 | 651.7 | 530.9 | 416.5 | 321.8 | 246.6 | 210.7 | 200.9 |
| 22.5° | 1323.1 | 1290.4 | 1174.4 | 877.2 | 627.2 | 473.7 | 330.0 | 231.9 | 194.4 | 176.4 | 171.5 |
| 25° | 1453.8 | 1417.8 | 1288.8 | 914.7 | 607.6 | 421.4 | 259.7 | 184.6 | 166.6 | 158.4 | 155.2 |
| 27.5° | 1587.7 | 1551.8 | 1401.5 | 975.2 | 584.8 | 365.9 | 209.1 | 161.7 | 148.6 | 142.1 | 142.1 |
| 30° | 1682.4 | 1653.0 | 1502.8 | 1029.1 | 558.6 | 321.8 | 184.6 | 150.3 | 138.8 | 132.3 | 130.7 |
| 32.5° | 1788.6 | 1747.8 | 1597.5 | 1065.0 | 539.0 | 287.5 | 168.2 | 140.5 | 130.7 | 122.5 | 122.5 |
| 35° | 1907.9 | 1862.1 | 1685.7 | 1100.9 | 519.4 | 271.2 | 156.8 | 133.9 | 124.1 | 116.0 | 114.3 |
| 37.5° | 2038.5 | 1979.7 | 1775.5 | 1132.0 | 498.2 | 263.0 | 150.3 | 127.4 | 117.6 | 111.1 | 107.8 |
| 40° | 2182.3 | 2120.2 | 1894.8 | 1158.1 | 483.5 | 253.2 | 145.4 | 122.5 | 112.7 | 104.5 | 102.9 |
| 42.5° | 2303.1 | 2247.6 | 1978.1 | 1174.4 | 477.0 | 240.1 | 143.7 | 117.6 | 109.4 | 99.6 | 96.4 |
| 45° | 2365.2 | 2317.8 | 2079.4 | 1179.3 | 473.7 | 231.9 | 135.6 | 117.6 | 106.2 | 96.4 | 91.5 |
| 47.5° | 2419.1 | 2384.8 | 2152.9 | 1203.8 | 465.5 | 223.8 | 125.8 | 124.1 | 104.5 | 91.5 | 86.6 |
| 50° | 2510.6 | 2474.7 | 2267.2 | 1249.6 | 455.7 | 214.0 | 116.0 | 119.2 | 104.5 | 88.2 | 83.3 |
| 52.5° | 2620.0 | 2610.2 | 2417.5 | 1321.4 | 441.0 | 200.9 | 106.2 | 112.7 | 104.5 | 86.6 | 80.0 |
| 55° | 2780.1 | 2765.4 | 2616.8 | 1414.6 | 423.1 | 182.9 | 96.4 | 102.9 | 102.9 | 81.7 | 75.1 |
| 57.5° | 2915.7 | 2917.3 | 2799.7 | 1479.9 | 406.7 | 153.5 | 89.8 | 88.2 | 98.0 | 76.8 | 70.2 |
| 60° | 2977.8 | 2977.8 | 2858.5 | 1504.4 | 385.5 | 129.0 | 84.9 | 78.4 | 101.3 | 71.9 | 65.3 |
| 62.5° | 3017.0 | 2984.3 | 2776.8 | 1481.5 | 361.0 | 116.0 | 76.8 | 71.9 | 81.7 | 67.0 | 60.4 |
| 65° | 3005.5 | 2943.4 | 2613.5 | 1365.6 | 325.1 | 112.7 | 71.9 | 65.3 | 65.3 | 62.1 | 57.2 |
| 67.5° | 2902.6 | 2806.2 | 2373.4 | 1169.5 | 287.5 | 111.1 | 65.3 | 60.4 | 58.8 | 55.5 | 52.3 |
| 70° | 2623.3 | 2554.7 | 2087.5 | 953.9 | 263.0 | 111.1 | 60.4 | 53.9 | 52.3 | 49.0 | 47.4 |
| 72.5° | 2144.7 | 2043.4 | 1666.1 | 715.4 | 243.4 | 111.1 | 55.5 | 47.4 | 45.7 | 44.1 | 42.5 |
| 75° | 1465.2 | 1349.2 | 1171.2 | 439.4 | 191.1 | 96.4 | 49.0 | 39.2 | 39.2 | 37.6 | 35.9 |
| 77.5° | 808.5 | 782.4 | 659.9 | 231.9 | 119.2 | 58.8 | 37.6 | 31.0 | 32.7 | 31.0 | 29.4 |
| 80° | 468.8 | 441.0 | 392.0 | 112.7 | 68.6 | 34.3 | 22.9 | 22.9 | 24.5 | 24.5 | 22.9 |
| 82.5° | 227.0 | 197.6 | 202.5 | 45.7 | 24.5 | 14.7 | 9.8 | 11.4 | 13.1 | 16.3 | 16.3 |
| 85° | 8.2 | 8.2 | 16.3 | 3.3 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 3.3 | 4.9 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P437352
 CATALOG NUMBER: ISC-SA1C-740-U-SLR

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1290.4 | 1290.4 | 1290.4 | 1290.4 | 1290.4 | 1290.4 | 1290.4 | 1290.4 | 1290.4 | 1290.4 | 1290.4 |
| 2.5° | 1078.1 | 1078.1 | 1084.6 | 1112.4 | 1089.5 | 1086.2 | 1092.8 | 1104.2 | 1109.1 | 1132.0 | 1130.3 |
| 5° | 831.4 | 826.5 | 846.1 | 872.3 | 887.0 | 895.1 | 908.2 | 937.6 | 926.2 | 944.1 | 940.9 |
| 7.5° | 614.2 | 622.3 | 614.2 | 643.6 | 666.4 | 700.7 | 726.9 | 720.3 | 722.0 | 707.3 | 728.5 |
| 10° | 501.5 | 498.2 | 478.6 | 488.4 | 501.5 | 522.7 | 540.7 | 543.9 | 560.3 | 534.1 | 552.1 |
| 12.5° | 428.0 | 414.9 | 395.3 | 385.5 | 382.2 | 398.6 | 403.5 | 411.6 | 421.4 | 429.6 | 432.9 |
| 15° | 343.0 | 333.2 | 320.2 | 305.5 | 302.2 | 302.2 | 313.6 | 325.1 | 338.1 | 341.4 | 352.8 |
| 17.5° | 256.4 | 251.5 | 246.6 | 246.6 | 246.6 | 246.6 | 256.4 | 261.3 | 267.9 | 277.7 | 276.1 |
| 20° | 194.4 | 194.4 | 196.0 | 204.2 | 209.1 | 212.3 | 218.9 | 220.5 | 218.9 | 220.5 | 220.5 |
| 22.5° | 171.5 | 169.9 | 174.8 | 178.0 | 186.2 | 194.4 | 197.6 | 196.0 | 191.1 | 187.8 | 191.1 |
| 25° | 155.2 | 156.8 | 158.4 | 163.3 | 169.9 | 178.0 | 179.7 | 178.0 | 173.1 | 173.1 | 173.1 |
| 27.5° | 142.1 | 143.7 | 147.0 | 151.9 | 158.4 | 165.0 | 166.6 | 163.3 | 158.4 | 160.1 | 158.4 |
| 30° | 132.3 | 135.6 | 137.2 | 142.1 | 147.0 | 153.5 | 153.5 | 150.3 | 147.0 | 147.0 | 147.0 |
| 32.5° | 120.9 | 124.1 | 127.4 | 132.3 | 138.8 | 142.1 | 142.1 | 140.5 | 137.2 | 135.6 | 135.6 |
| 35° | 114.3 | 114.3 | 117.6 | 124.1 | 127.4 | 130.7 | 132.3 | 130.7 | 127.4 | 124.1 | 122.5 |
| 37.5° | 107.8 | 107.8 | 109.4 | 112.7 | 119.2 | 122.5 | 124.1 | 120.9 | 117.6 | 114.3 | 114.3 |
| 40° | 101.3 | 101.3 | 102.9 | 104.5 | 111.1 | 116.0 | 116.0 | 111.1 | 107.8 | 109.4 | 107.8 |
| 42.5° | 96.4 | 96.4 | 98.0 | 98.0 | 101.3 | 109.4 | 107.8 | 104.5 | 102.9 | 102.9 | 101.3 |
| 45° | 91.5 | 89.8 | 91.5 | 91.5 | 93.1 | 101.3 | 101.3 | 96.4 | 96.4 | 98.0 | 96.4 |
| 47.5° | 86.6 | 84.9 | 86.6 | 86.6 | 88.2 | 93.1 | 93.1 | 91.5 | 91.5 | 91.5 | 93.1 |
| 50° | 81.7 | 81.7 | 81.7 | 81.7 | 83.3 | 84.9 | 88.2 | 86.6 | 86.6 | 86.6 | 88.2 |
| 52.5° | 76.8 | 76.8 | 76.8 | 78.4 | 78.4 | 81.7 | 83.3 | 81.7 | 83.3 | 83.3 | 83.3 |
| 55° | 73.5 | 71.9 | 71.9 | 75.1 | 75.1 | 78.4 | 80.0 | 78.4 | 80.0 | 80.0 | 80.0 |
| 57.5° | 68.6 | 68.6 | 68.6 | 70.2 | 71.9 | 75.1 | 78.4 | 75.1 | 76.8 | 76.8 | 78.4 |
| 60° | 63.7 | 63.7 | 63.7 | 67.0 | 68.6 | 71.9 | 73.5 | 71.9 | 73.5 | 73.5 | 73.5 |
| 62.5° | 58.8 | 60.4 | 60.4 | 62.1 | 63.7 | 68.6 | 70.2 | 68.6 | 70.2 | 70.2 | 70.2 |
| 65° | 55.5 | 55.5 | 57.2 | 58.8 | 60.4 | 63.7 | 65.3 | 65.3 | 65.3 | 67.0 | 65.3 |
| 67.5° | 50.6 | 50.6 | 52.3 | 53.9 | 55.5 | 60.4 | 60.4 | 60.4 | 62.1 | 60.4 | 60.4 |
| 70° | 45.7 | 45.7 | 47.4 | 49.0 | 50.6 | 55.5 | 55.5 | 55.5 | 57.2 | 53.9 | 53.9 |
| 72.5° | 40.8 | 40.8 | 42.5 | 44.1 | 47.4 | 52.3 | 50.6 | 50.6 | 50.6 | 49.0 | 49.0 |
| 75° | 35.9 | 35.9 | 37.6 | 39.2 | 40.8 | 47.4 | 45.7 | 44.1 | 44.1 | 42.5 | 42.5 |
| 77.5° | 29.4 | 29.4 | 31.0 | 34.3 | 35.9 | 40.8 | 39.2 | 37.6 | 35.9 | 35.9 | 35.9 |
| 80° | 22.9 | 24.5 | 26.1 | 27.8 | 29.4 | 32.7 | 31.0 | 29.4 | 27.8 | 27.8 | 27.8 |
| 82.5° | 16.3 | 18.0 | 19.6 | 21.2 | 22.9 | 22.9 | 22.9 | 22.9 | 21.2 | 19.6 | 19.6 |
| 85° | 6.5 | 9.8 | 13.1 | 13.1 | 14.7 | 13.1 | 14.7 | 13.1 | 11.4 | 11.4 | 9.8 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 1.6 | 3.3 | 4.9 | 4.9 | 4.9 | 4.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P437352
 CATALOG NUMBER: ISC-SA1C-740-U-SLR

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1290.4 | 1290.4 | 1290.4 | 1290.4 | 1290.4 | 1290.4 | 1290.4 | 1290.4 | 1290.4 | 1290.4 | 1290.4 |
| 2.5° | 1143.4 | 1169.5 | 1184.2 | 1210.4 | 1238.1 | 1275.7 | 1306.7 | 1350.8 | 1390.1 | 1398.2 | 1408.0 |
| 5° | 947.4 | 981.7 | 998.0 | 1040.5 | 1105.8 | 1146.7 | 1212.0 | 1280.6 | 1365.6 | 1391.7 | 1426.0 |
| 7.5° | 712.2 | 738.3 | 780.8 | 818.4 | 895.1 | 963.7 | 1051.9 | 1151.6 | 1251.2 | 1308.4 | 1363.9 |
| 10° | 542.3 | 575.0 | 620.7 | 664.8 | 739.9 | 808.5 | 913.1 | 1024.2 | 1151.6 | 1203.8 | 1262.6 |
| 12.5° | 450.8 | 477.0 | 522.7 | 583.1 | 653.4 | 718.7 | 797.1 | 918.0 | 1051.9 | 1118.9 | 1190.8 |
| 15° | 364.3 | 392.0 | 449.2 | 516.2 | 584.8 | 658.3 | 733.4 | 849.4 | 1012.7 | 1081.3 | 1149.9 |
| 17.5° | 290.8 | 315.3 | 364.3 | 436.1 | 511.3 | 592.9 | 684.4 | 831.4 | 1020.9 | 1105.8 | 1185.9 |
| 20° | 225.4 | 246.6 | 284.2 | 349.6 | 426.3 | 522.7 | 640.3 | 824.9 | 1069.9 | 1189.1 | 1269.2 |
| 22.5° | 194.4 | 202.5 | 223.8 | 269.5 | 347.9 | 460.6 | 599.5 | 829.8 | 1148.3 | 1301.8 | 1393.3 |
| 25° | 173.1 | 179.7 | 187.8 | 215.6 | 277.7 | 396.9 | 563.5 | 839.6 | 1231.6 | 1429.3 | 1533.8 |
| 27.5° | 160.1 | 163.3 | 168.2 | 181.3 | 227.0 | 344.7 | 527.6 | 852.7 | 1344.3 | 1558.3 | 1659.6 |
| 30° | 147.0 | 147.0 | 151.9 | 165.0 | 199.3 | 307.1 | 501.5 | 878.8 | 1455.4 | 1669.4 | 1769.0 |
| 32.5° | 133.9 | 133.9 | 142.1 | 153.5 | 181.3 | 276.1 | 475.3 | 887.0 | 1538.7 | 1767.4 | 1847.4 |
| 35° | 122.5 | 125.8 | 132.3 | 145.4 | 169.9 | 253.2 | 450.8 | 872.3 | 1599.1 | 1850.7 | 1932.4 |
| 37.5° | 116.0 | 117.6 | 125.8 | 137.2 | 155.2 | 231.9 | 426.3 | 852.7 | 1680.8 | 1961.8 | 2025.5 |
| 40° | 107.8 | 111.1 | 119.2 | 130.7 | 145.4 | 215.6 | 398.6 | 831.4 | 1752.7 | 2085.9 | 2118.6 |
| 42.5° | 102.9 | 106.2 | 112.7 | 124.1 | 138.8 | 196.0 | 372.4 | 815.1 | 1829.4 | 2192.1 | 2214.9 |
| 45° | 98.0 | 101.3 | 109.4 | 119.2 | 138.8 | 181.3 | 346.3 | 803.6 | 1904.6 | 2273.7 | 2291.7 |
| 47.5° | 93.1 | 96.4 | 104.5 | 117.6 | 137.2 | 173.1 | 328.3 | 792.2 | 1952.0 | 2344.0 | 2348.9 |
| 50° | 89.8 | 93.1 | 102.9 | 120.9 | 132.3 | 169.9 | 320.2 | 803.6 | 2032.0 | 2399.5 | 2384.8 |
| 52.5° | 84.9 | 89.8 | 101.3 | 125.8 | 125.8 | 166.6 | 313.6 | 844.5 | 2131.6 | 2481.2 | 2443.6 |
| 55° | 83.3 | 86.6 | 98.0 | 120.9 | 114.3 | 158.4 | 313.6 | 875.5 | 2263.9 | 2642.9 | 2580.8 |
| 57.5° | 78.4 | 81.7 | 94.7 | 112.7 | 104.5 | 145.4 | 310.4 | 926.2 | 2451.8 | 2820.9 | 2765.4 |
| 60° | 73.5 | 78.4 | 91.5 | 101.3 | 94.7 | 129.0 | 295.7 | 981.7 | 2580.8 | 2917.3 | 2927.1 |
| 62.5° | 70.2 | 75.1 | 91.5 | 88.2 | 86.6 | 112.7 | 272.8 | 1016.0 | 2567.8 | 2886.3 | 2979.4 |
| 65° | 65.3 | 70.2 | 83.3 | 80.0 | 81.7 | 101.3 | 243.4 | 999.7 | 2396.2 | 2755.6 | 2918.9 |
| 67.5° | 60.4 | 65.3 | 71.9 | 71.9 | 75.1 | 98.0 | 212.3 | 904.9 | 2210.0 | 2597.2 | 2785.0 |
| 70° | 55.5 | 58.8 | 62.1 | 65.3 | 68.6 | 96.4 | 187.8 | 775.9 | 1996.1 | 2445.3 | 2593.9 |
| 72.5° | 49.0 | 50.6 | 53.9 | 57.2 | 63.7 | 91.5 | 178.0 | 630.5 | 1700.4 | 2116.9 | 2347.2 |
| 75° | 42.5 | 44.1 | 47.4 | 50.6 | 55.5 | 86.6 | 163.3 | 478.6 | 1401.5 | 1672.6 | 1896.4 |
| 77.5° | 35.9 | 37.6 | 40.8 | 42.5 | 47.4 | 76.8 | 140.5 | 346.3 | 1091.1 | 1205.5 | 1386.8 |
| 80° | 27.8 | 29.4 | 32.7 | 32.7 | 39.2 | 57.2 | 109.4 | 241.7 | 766.1 | 854.3 | 949.0 |
| 82.5° | 19.6 | 21.2 | 22.9 | 24.5 | 29.4 | 39.2 | 71.9 | 145.4 | 519.4 | 586.4 | 570.1 |
| 85° | 11.4 | 13.1 | 13.1 | 16.3 | 18.0 | 26.1 | 40.8 | 75.1 | 339.8 | 267.9 | 264.6 |
| 87.5° | 4.9 | 4.9 | 4.9 | 6.5 | 6.5 | 9.8 | 13.1 | 14.7 | 32.7 | 11.4 | 8.2 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P437352

CATALOG NUMBER: ISC-SA1C-740-U-SLR

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 359° | 360° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1290.4 | 1290.4 | 1290.4 | 1290.4 | 1290.4 | 1290.4 | 1290.4 | 1290.4 | 1290.4 | 1290.4 |
| 2.5° | 1422.7 | 1434.2 | 1442.3 | 1439.1 | 1434.2 | 1406.4 | 1378.6 | 1349.2 | 1323.1 | 1323.1 |
| 5° | 1481.5 | 1528.9 | 1548.5 | 1532.2 | 1496.2 | 1439.1 | 1367.2 | 1292.0 | 1256.1 | 1246.3 |
| 7.5° | 1450.5 | 1540.3 | 1587.7 | 1566.5 | 1519.1 | 1414.6 | 1305.1 | 1207.1 | 1153.2 | 1143.4 |
| 10° | 1388.4 | 1506.0 | 1559.9 | 1553.4 | 1501.1 | 1380.3 | 1247.9 | 1136.9 | 1079.7 | 1073.2 |
| 12.5° | 1316.5 | 1430.9 | 1499.5 | 1502.8 | 1468.5 | 1362.3 | 1223.4 | 1091.1 | 1040.5 | 1027.4 |
| 15° | 1272.4 | 1372.1 | 1419.5 | 1408.0 | 1417.8 | 1347.6 | 1233.2 | 1109.1 | 1047.0 | 1035.6 |
| 17.5° | 1274.1 | 1316.5 | 1328.0 | 1310.0 | 1347.6 | 1344.3 | 1288.8 | 1174.4 | 1105.8 | 1094.4 |
| 20° | 1316.5 | 1280.6 | 1244.7 | 1241.4 | 1290.4 | 1355.8 | 1377.0 | 1283.9 | 1205.5 | 1197.3 |
| 22.5° | 1390.1 | 1270.8 | 1195.7 | 1184.2 | 1246.3 | 1367.2 | 1461.9 | 1417.8 | 1344.3 | 1323.1 |
| 25° | 1471.7 | 1280.6 | 1164.6 | 1149.9 | 1205.5 | 1375.4 | 1553.4 | 1555.0 | 1473.4 | 1453.8 |
| 27.5° | 1559.9 | 1311.6 | 1164.6 | 1148.3 | 1207.1 | 1388.4 | 1613.8 | 1679.2 | 1604.0 | 1587.7 |
| 30° | 1638.3 | 1355.8 | 1176.1 | 1158.1 | 1226.7 | 1401.5 | 1654.7 | 1790.2 | 1705.3 | 1682.4 |
| 32.5° | 1685.7 | 1393.3 | 1203.8 | 1171.2 | 1261.0 | 1427.6 | 1692.2 | 1885.0 | 1819.6 | 1788.6 |
| 35° | 1723.3 | 1437.4 | 1249.6 | 1207.1 | 1311.6 | 1470.1 | 1723.3 | 1987.9 | 1925.8 | 1907.9 |
| 37.5° | 1751.0 | 1489.7 | 1296.9 | 1256.1 | 1378.6 | 1527.3 | 1767.4 | 2097.3 | 2077.7 | 2038.5 |
| 40° | 1796.8 | 1522.4 | 1381.9 | 1367.2 | 1494.6 | 1617.1 | 1819.6 | 2192.1 | 2205.1 | 2182.3 |
| 42.5° | 1837.6 | 1586.1 | 1502.8 | 1519.1 | 1643.2 | 1716.7 | 1889.9 | 2262.3 | 2332.5 | 2303.1 |
| 45° | 1870.3 | 1674.3 | 1654.7 | 1708.6 | 1814.7 | 1844.1 | 1929.1 | 2311.3 | 2384.8 | 2365.2 |
| 47.5° | 1916.0 | 1790.2 | 1857.2 | 1927.5 | 2015.7 | 1976.5 | 1969.9 | 2363.6 | 2438.7 | 2419.1 |
| 50° | 1981.4 | 1925.8 | 2059.8 | 2151.2 | 2208.4 | 2084.3 | 2020.6 | 2410.9 | 2522.0 | 2510.6 |
| 52.5° | 2048.3 | 2082.6 | 2265.6 | 2350.5 | 2388.1 | 2218.2 | 2092.4 | 2486.1 | 2620.0 | 2620.0 |
| 55° | 2172.5 | 2236.2 | 2484.5 | 2538.4 | 2589.0 | 2339.1 | 2188.8 | 2598.8 | 2771.9 | 2780.1 |
| 57.5° | 2353.8 | 2401.1 | 2651.1 | 2713.1 | 2726.2 | 2474.7 | 2340.7 | 2755.6 | 2901.0 | 2915.7 |
| 60° | 2541.6 | 2564.5 | 2816.0 | 2871.6 | 2827.5 | 2649.4 | 2518.8 | 2938.5 | 2985.9 | 2977.8 |
| 62.5° | 2749.1 | 2722.9 | 2930.4 | 2969.6 | 2958.1 | 2803.0 | 2742.5 | 3105.2 | 3048.0 | 3017.0 |
| 65° | 2914.0 | 2816.0 | 2989.2 | 2997.4 | 3003.9 | 2909.1 | 2971.2 | 3180.3 | 3074.1 | 3005.5 |
| 67.5° | 3013.7 | 2830.7 | 2869.9 | 2832.4 | 2858.5 | 2881.4 | 3126.4 | 3149.3 | 2963.0 | 2902.6 |
| 70° | 2990.8 | 2623.3 | 2446.9 | 2404.4 | 2406.0 | 2566.1 | 3026.8 | 2954.9 | 2709.9 | 2623.3 |
| 72.5° | 2780.1 | 2205.1 | 1948.7 | 1891.5 | 1903.0 | 1917.7 | 2544.9 | 2579.2 | 2190.4 | 2144.7 |
| 75° | 2340.7 | 1698.8 | 1403.1 | 1390.1 | 1373.7 | 1437.4 | 2035.3 | 1885.0 | 1453.8 | 1465.2 |
| 77.5° | 1909.5 | 1251.2 | 1030.7 | 963.7 | 953.9 | 963.7 | 1388.4 | 1076.4 | 844.5 | 808.5 |
| 80° | 1377.0 | 833.1 | 769.3 | 754.6 | 708.9 | 570.1 | 726.9 | 692.6 | 477.0 | 468.8 |
| 82.5° | 906.6 | 575.0 | 588.0 | 490.0 | 460.6 | 361.0 | 441.0 | 352.8 | 238.5 | 227.0 |
| 85° | 470.4 | 298.9 | 246.6 | 107.8 | 120.9 | 101.3 | 96.4 | 78.4 | 8.2 | 8.2 |
| 87.5° | 16.3 | 6.5 | 4.9 | 4.9 | 3.3 | 1.6 | 1.6 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-121-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 03/05/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: **IFLD-S-SA2A-740-U-T3R-HSS**
 Description: STREETWORKS INF FLOOD

SHIELD, DRIVER PROGRAMMED @ 615mA.

Spectral Parameters

| | | | | | |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K): | 3905 | CRI (Ra): | 71.2 | R9: | -29.7 |
| CIE u': | 0.2273 | R1: | 68.9 | R10: | 46.2 |
| CIE v': | 0.5024 | R2: | 77.0 | R11: | 68.8 |
| Duv: | -0.0008 | R3: | 84.0 | R12: | 45.6 |
| CIE x: | 0.3841 | R4: | 71.6 | R13: | 69.5 |
| CIE y: | 0.3774 | R5: | 68.9 | R14: | 90.7 |
| CIE z: | 0.2385 | R6: | 68.3 | | |
| Peak Wavelength (nm): | 443 | R7: | 78.7 | | |
| Dominant Wavelength (nm): | 579 | R8: | 52.2 | | |
| Purity: | 28.7 | | | | |
| Rf: | 71.7 | | | | |
| Rg: | 96.9 | | | | |



Test Conditions

Stabilization Time: 211M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.8/312%
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-2

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 1/31/2021 | 7/31/2021 |
| Power Meter | IN0071 | 12/1/2020 | 12/1/2021 |
| AC Power Source | IN0063 | 12/1/2020 | 12/1/2021 |
| DC Power Source | IN0208 | 12/1/2020 | 12/1/2021 |
| Sphere Thermometer | IN0085 | 12/1/2020 | 12/1/2021 |
| Room Thermometer | IN0046 | 12/1/2020 | 12/1/2021 |

REPORT NUMBER: SP1-2101-121-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 3905K
 CIE x = 0.3841
 CIE y = 0.3774
 Duv = -0.0008

Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-2

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 2.7 | 620 | 97577 | 25.4 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 4.8 | 625 | 90158 | 19.9 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 8.0 | 630 | 82240 | 14.9 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 13.3 | 635 | 74361 | 11.2 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 20.2 | 640 | 66994 | 8.0 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 28.5 | 645 | 60405 | 5.8 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 37.4 | 650 | 53806 | 3.9 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 44.9 | 655 | 47610 | 2.7 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 52.6 | 660 | 42018 | 1.8 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.0 | 535 | 94097 | 58.4 | 665 | 36742 | 1.2 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.0 | 540 | 96845 | 63.1 | 670 | 32105 | 0.7 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.0 | 545 | 100829 | 67.1 | 675 | 27946 | 0.5 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 0.1 | 550 | 105648 | 71.8 | 680 | 24146 | 0.3 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 0.2 | 555 | 110017 | 75.1 | 685 | 21191 | 0.2 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 0.5 | 560 | 114586 | 77.9 | 690 | 18544 | 0.1 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 1.2 | 565 | 118987 | 79.1 | 695 | 16058 | 0.1 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 2.1 | 570 | 122326 | 79.5 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 2.9 | 575 | 125968 | 78.4 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 2.7 | 580 | 127613 | 75.8 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 2.0 | 585 | 129466 | 71.9 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 1.5 | 590 | 128813 | 66.6 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 1.3 | 595 | 126387 | 59.9 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 1.0 | 600 | 123477 | 53.2 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 1.1 | 605 | 118718 | 46.0 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 1.2 | 610 | 112091 | 38.5 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 1.7 | 615 | 105039 | 31.7 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-2

Scotopic Flux vs. Wavelength



Scotopic Lumens: 10425.8 S/P: 1.47

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 29.3 | 620 | 97577 | 1.2 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 43.0 | 625 | 90158 | 0.8 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 60.8 | 630 | 82240 | 0.5 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 81.1 | 635 | 74361 | 0.3 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 99.6 | 640 | 66994 | 0.2 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 113.9 | 645 | 60405 | 0.1 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 122.6 | 650 | 53806 | 0.1 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 125.0 | 655 | 47610 | 0.0 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 123.1 | 660 | 42018 | 0.0 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.1 | 535 | 94097 | 117.3 | 665 | 36742 | 0.0 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.2 | 540 | 96845 | 107.0 | 670 | 32105 | 0.0 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.9 | 545 | 100829 | 96.7 | 675 | 27946 | 0.0 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 3.0 | 550 | 105648 | 86.4 | 680 | 24146 | 0.0 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 9.3 | 555 | 110017 | 75.2 | 685 | 21191 | 0.0 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 23.0 | 560 | 114586 | 64.0 | 690 | 18544 | 0.0 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 45.7 | 565 | 118987 | 53.4 | 695 | 16058 | 0.0 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 75.5 | 570 | 122326 | 43.2 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 93.8 | 575 | 125968 | 34.3 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 79.3 | 580 | 127613 | 26.3 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 51.3 | 585 | 129466 | 19.8 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 35.6 | 590 | 128813 | 14.3 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 26.0 | 595 | 126387 | 10.1 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 19.3 | 600 | 123477 | 7.0 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 16.8 | 605 | 118718 | 4.7 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 17.7 | 610 | 112091 | 3.0 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 21.4 | 615 | 105039 | 1.9 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: 3927.2 M/P: 0.55

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 15.8 | 620 | 97577 | 0.1 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 22.0 | 625 | 90158 | 0.0 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 29.2 | 630 | 82240 | 0.0 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 36.6 | 635 | 74361 | 0.0 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 42.2 | 640 | 66994 | 0.0 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 44.9 | 645 | 60405 | 0.0 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 44.9 | 650 | 53806 | 0.0 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 42.4 | 655 | 47610 | 0.0 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 38.6 | 660 | 42018 | 0.0 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.0 | 535 | 94097 | 33.9 | 665 | 36742 | 0.0 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.2 | 540 | 96845 | 28.3 | 670 | 32105 | 0.0 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.6 | 545 | 100829 | 23.4 | 675 | 27946 | 0.0 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 2.1 | 550 | 105648 | 19.0 | 680 | 24146 | 0.0 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 5.9 | 555 | 110017 | 14.8 | 685 | 21191 | 0.0 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 14.3 | 560 | 114586 | 11.3 | 690 | 18544 | 0.0 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 27.3 | 565 | 118987 | 8.4 | 695 | 16058 | 0.0 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 45.1 | 570 | 122326 | 6.0 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 55.3 | 575 | 125968 | 4.2 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 47.2 | 580 | 127613 | 2.9 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 30.8 | 585 | 129466 | 1.9 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 21.7 | 590 | 128813 | 1.3 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 16.1 | 595 | 126387 | 0.8 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 12.0 | 600 | 123477 | 0.5 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 10.3 | 605 | 118718 | 0.3 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 10.5 | 610 | 112091 | 0.2 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 12.1 | 615 | 105039 | 0.1 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

Summary

$R_f = 71.7$
 $R_g = 96.9$
 CIE $R_a = 71.2$
 $R_g = -29.7$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 55 | CES51 = 86 | CES76 = 45 |
| CES02 = 61 | CES27 = 80 | CES52 = 87 | CES77 = 68 |
| CES03 = 30 | CES28 = 79 | CES53 = 74 | CES78 = 49 |
| CES04 = 70 | CES29 = 51 | CES54 = 81 | CES79 = 77 |
| CES05 = 47 | CES30 = 60 | CES55 = 80 | CES80 = 75 |
| CES06 = 50 | CES31 = 56 | CES56 = 69 | CES81 = 75 |
| CES07 = 40 | CES32 = 52 | CES57 = 67 | CES82 = 90 |
| CES08 = 39 | CES33 = 62 | CES58 = 69 | CES83 = 85 |
| CES09 = 29 | CES34 = 65 | CES59 = 86 | CES84 = 87 |
| CES10 = 74 | CES35 = 81 | CES60 = 91 | CES85 = 83 |
| CES11 = 57 | CES36 = 92 | CES61 = 85 | CES86 = 72 |
| CES12 = 63 | CES37 = 74 | CES62 = 81 | CES87 = 77 |
| CES13 = 42 | CES38 = 69 | CES63 = 72 | CES88 = 77 |
| CES14 = 74 | CES39 = 92 | CES64 = 69 | CES89 = 72 |
| CES15 = 71 | CES40 = 86 | CES65 = 64 | CES90 = 75 |
| CES16 = 46 | CES41 = 84 | CES66 = 63 | CES91 = 91 |
| CES17 = 49 | CES42 = 75 | CES67 = 60 | CES92 = 66 |
| CES18 = 56 | CES43 = 70 | CES68 = 67 | CES93 = 80 |
| CES19 = 72 | CES44 = 98 | CES69 = 77 | CES94 = 56 |
| CES20 = 65 | CES45 = 80 | CES70 = 57 | CES95 = 72 |
| CES21 = 86 | CES46 = 77 | CES71 = 53 | CES96 = 78 |
| CES22 = 78 | CES47 = 74 | CES72 = 84 | CES97 = 83 |
| CES23 = 92 | CES48 = 66 | CES73 = 47 | CES98 = 73 |
| CES24 = 91 | CES49 = 76 | CES74 = 96 | CES99 = 63 |
| CES25 = 72 | CES50 = 85 | CES75 = 52 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)