

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P437542

Luminaire Tested: **ISC-SA1D-750-U-SLR**

Issue Date: 12/9/2020

Test Information

Test Method: LM-79-08
Report Number: P437542
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-074-22)
Test Lab: INNOVATION CENTER
Issue Date: 12/9/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: ISC-SA1D-750-U-SLR
Description: IMPACT ELITE LED CYLINDER LUMINAIRE
(1) 70 CRI, 5000K, 800mA LIGHTSQUARE WITH 16 LEDS AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5046 lumens
Efficiency: N/A
Efficacy: 111.6 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 45.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P437542
 CATALOG NUMBER: ISC-SA1D-750-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 2.6 fc
 Type IV - Short - N/A

REPORT NUMBER: P437542
CATALOG NUMBER: ISC-SA1D-750-U-SLR

Luminous Intensity Polar Plot



— Vertical Plane Through 355-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P437542
 CATALOG NUMBER: ISC-SA1D-750-U-SLR


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 909.7 | 0.0 | 909.7 |
| | % Fixture | 18.0 | 0.0 | 18.0 |
| Street Side | Lumens | 4136.3 | 0.0 | 4136.3 |
| | % Fixture | 82.0 | 0.0 | 82.0 |
| Total | Lumens | 5046.0 | 0.0 | 5046.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 121.9 | 2.4 |
| 10°-20° | 251.7 | 5.0 |
| 20°-30° | 358.7 | 7.1 |
| 30°-40° | 512.8 | 10.2 |
| 40°-50° | 716.1 | 14.2 |
| 50°-60° | 996.0 | 19.7 |
| 60°-70° | 1213.3 | 24.0 |
| 70°-80° | 747.2 | 14.8 |
| 80°-90° | 128.4 | 2.5 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 5046.0 | 100.0 |
| 0°-180° | 5046.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P437542
 CATALOG NUMBER: ISC-SA1D-750-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 504.5 | 10.0 | | | |
| FM (30°-60°) | 1832.3 | 36.3 | | | |
| FH (60°-80°) | 1696.3 | 33.6 | | | G1/1800 |
| FVH (80°-90°) | 103.1 | 2.0 | | | G2/225 |
| BL (0°-30°) | 227.8 | 4.5 | B1/500 | | |
| BM (30°-60°) | 392.5 | 7.8 | B1/1000 | | |
| BH (60°-80°) | 264.2 | 5.2 | B1/500 | | G1/500 |
| BVH (80°-90°) | 25.2 | 0.5 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G2
 Type IV Short





REPORT NUMBER: P437542
 CATALOG NUMBER: ISC-SA1D-750-U-SLR

CANDELA DISTRIBUTION (FULL):

| | 0° | 1° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1614.5 | 1614.5 | 1614.5 | 1614.5 | 1614.5 | 1614.5 | 1614.5 | 1614.5 | 1614.5 | 1614.5 | 1614.5 |
| 2.5° | 1655.4 | 1655.4 | 1635.0 | 1583.9 | 1536.9 | 1487.8 | 1471.5 | 1426.5 | 1397.9 | 1371.3 | 1381.6 |
| 5° | 1559.4 | 1553.2 | 1516.4 | 1410.2 | 1328.4 | 1248.7 | 1199.7 | 1126.1 | 1117.9 | 1052.5 | 1048.4 |
| 7.5° | 1430.6 | 1426.5 | 1371.3 | 1250.8 | 1156.7 | 1032.1 | 958.5 | 895.1 | 840.0 | 801.1 | 788.9 |
| 10° | 1342.7 | 1328.4 | 1261.0 | 1113.8 | 976.9 | 887.0 | 846.1 | 790.9 | 743.9 | 694.9 | 654.0 |
| 12.5° | 1285.5 | 1269.1 | 1201.7 | 1040.3 | 907.4 | 846.1 | 788.9 | 723.5 | 660.1 | 602.9 | 562.0 |
| 15° | 1295.7 | 1269.1 | 1193.5 | 1021.9 | 882.9 | 795.0 | 715.3 | 637.6 | 564.1 | 500.7 | 449.6 |
| 17.5° | 1369.3 | 1336.6 | 1252.8 | 1034.1 | 844.1 | 727.6 | 619.2 | 529.3 | 439.4 | 374.0 | 333.1 |
| 20° | 1498.0 | 1451.0 | 1344.8 | 1068.9 | 815.4 | 664.2 | 521.1 | 402.6 | 308.6 | 263.6 | 251.4 |
| 22.5° | 1655.4 | 1614.5 | 1469.4 | 1097.5 | 784.8 | 592.7 | 412.8 | 290.2 | 243.2 | 220.7 | 214.6 |
| 25° | 1818.9 | 1773.9 | 1612.5 | 1144.5 | 760.3 | 527.3 | 325.0 | 230.9 | 208.5 | 198.2 | 194.2 |
| 27.5° | 1986.5 | 1941.5 | 1753.5 | 1220.1 | 731.7 | 457.8 | 261.6 | 202.3 | 186.0 | 177.8 | 177.8 |
| 30° | 2105.0 | 2068.2 | 1880.2 | 1287.5 | 699.0 | 402.6 | 230.9 | 188.0 | 173.7 | 165.5 | 163.5 |
| 32.5° | 2237.9 | 2186.8 | 1998.8 | 1332.5 | 674.4 | 359.7 | 210.5 | 175.8 | 163.5 | 153.3 | 153.3 |
| 35° | 2387.1 | 2329.8 | 2109.1 | 1377.5 | 649.9 | 339.3 | 196.2 | 167.6 | 155.3 | 145.1 | 143.1 |
| 37.5° | 2550.6 | 2477.0 | 2221.5 | 1416.3 | 623.3 | 329.0 | 188.0 | 159.4 | 147.1 | 139.0 | 134.9 |
| 40° | 2730.4 | 2652.7 | 2370.7 | 1449.0 | 604.9 | 316.8 | 181.9 | 153.3 | 141.0 | 130.8 | 128.8 |
| 42.5° | 2881.6 | 2812.2 | 2474.9 | 1469.4 | 596.8 | 300.4 | 179.8 | 147.1 | 136.9 | 124.7 | 120.6 |
| 45° | 2959.3 | 2900.0 | 2601.7 | 1475.6 | 592.7 | 290.2 | 169.6 | 147.1 | 132.8 | 120.6 | 114.4 |
| 47.5° | 3026.7 | 2983.8 | 2693.6 | 1506.2 | 582.5 | 280.0 | 157.4 | 155.3 | 130.8 | 114.4 | 108.3 |
| 50° | 3141.2 | 3096.2 | 2836.7 | 1563.4 | 570.2 | 267.7 | 145.1 | 149.2 | 130.8 | 110.4 | 104.2 |
| 52.5° | 3278.1 | 3265.9 | 3024.7 | 1653.4 | 551.8 | 251.4 | 132.8 | 141.0 | 130.8 | 108.3 | 100.1 |
| 55° | 3478.4 | 3460.0 | 3274.0 | 1769.9 | 529.3 | 228.9 | 120.6 | 128.8 | 128.8 | 102.2 | 94.0 |
| 57.5° | 3648.0 | 3650.1 | 3502.9 | 1851.6 | 508.9 | 192.1 | 112.4 | 110.4 | 122.6 | 96.1 | 87.9 |
| 60° | 3725.7 | 3725.7 | 3576.5 | 1882.3 | 482.3 | 161.5 | 106.3 | 98.1 | 126.7 | 89.9 | 81.7 |
| 62.5° | 3774.7 | 3733.9 | 3474.3 | 1853.7 | 451.7 | 145.1 | 96.1 | 89.9 | 102.2 | 83.8 | 75.6 |
| 65° | 3760.4 | 3682.8 | 3269.9 | 1708.5 | 406.7 | 141.0 | 89.9 | 81.7 | 81.7 | 77.7 | 71.5 |
| 67.5° | 3631.7 | 3511.1 | 2969.5 | 1463.3 | 359.7 | 139.0 | 81.7 | 75.6 | 73.6 | 69.5 | 65.4 |
| 70° | 3282.2 | 3196.4 | 2611.9 | 1193.5 | 329.0 | 139.0 | 75.6 | 67.4 | 65.4 | 61.3 | 59.3 |
| 72.5° | 2683.4 | 2556.7 | 2084.6 | 895.1 | 304.5 | 139.0 | 69.5 | 59.3 | 57.2 | 55.2 | 53.1 |
| 75° | 1833.2 | 1688.1 | 1465.3 | 549.8 | 239.1 | 120.6 | 61.3 | 49.0 | 49.0 | 47.0 | 45.0 |
| 77.5° | 1011.6 | 978.9 | 825.7 | 290.2 | 149.2 | 73.6 | 47.0 | 38.8 | 40.9 | 38.8 | 36.8 |
| 80° | 586.5 | 551.8 | 490.5 | 141.0 | 85.8 | 42.9 | 28.6 | 28.6 | 30.7 | 30.7 | 28.6 |
| 82.5° | 284.1 | 247.3 | 253.4 | 57.2 | 30.7 | 18.4 | 12.3 | 14.3 | 16.3 | 20.4 | 20.4 |
| 85° | 10.2 | 10.2 | 20.4 | 4.1 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 4.1 | 6.1 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P437542
 CATALOG NUMBER: ISC-SA1D-750-U-SLR

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1614.5 | 1614.5 | 1614.5 | 1614.5 | 1614.5 | 1614.5 | 1614.5 | 1614.5 | 1614.5 | 1614.5 | 1614.5 |
| 2.5° | 1348.9 | 1348.9 | 1357.0 | 1391.8 | 1363.2 | 1359.1 | 1367.2 | 1381.6 | 1387.7 | 1416.3 | 1414.3 |
| 5° | 1040.3 | 1034.1 | 1058.6 | 1091.3 | 1109.7 | 1120.0 | 1136.3 | 1173.1 | 1158.8 | 1181.3 | 1177.2 |
| 7.5° | 768.4 | 778.7 | 768.4 | 805.2 | 833.8 | 876.8 | 909.5 | 901.3 | 903.3 | 884.9 | 911.5 |
| 10° | 627.4 | 623.3 | 598.8 | 611.1 | 627.4 | 654.0 | 676.5 | 680.6 | 701.0 | 668.3 | 690.8 |
| 12.5° | 535.5 | 519.1 | 494.6 | 482.3 | 478.2 | 498.7 | 504.8 | 515.0 | 527.3 | 537.5 | 541.6 |
| 15° | 429.2 | 416.9 | 400.6 | 382.2 | 378.1 | 378.1 | 392.4 | 406.7 | 423.0 | 427.1 | 441.4 |
| 17.5° | 320.9 | 314.7 | 308.6 | 308.6 | 308.6 | 308.6 | 320.9 | 327.0 | 335.2 | 347.4 | 345.4 |
| 20° | 243.2 | 243.2 | 245.2 | 255.5 | 261.6 | 265.7 | 273.9 | 275.9 | 273.9 | 275.9 | 275.9 |
| 22.5° | 214.6 | 212.5 | 218.7 | 222.8 | 233.0 | 243.2 | 247.3 | 245.2 | 239.1 | 235.0 | 239.1 |
| 25° | 194.2 | 196.2 | 198.2 | 204.4 | 212.5 | 222.8 | 224.8 | 222.8 | 216.6 | 216.6 | 216.6 |
| 27.5° | 177.8 | 179.8 | 183.9 | 190.1 | 198.2 | 206.4 | 208.5 | 204.4 | 198.2 | 200.3 | 198.2 |
| 30° | 165.5 | 169.6 | 171.7 | 177.8 | 183.9 | 192.1 | 192.1 | 188.0 | 183.9 | 183.9 | 183.9 |
| 32.5° | 151.2 | 155.3 | 159.4 | 165.5 | 173.7 | 177.8 | 177.8 | 175.8 | 171.7 | 169.6 | 169.6 |
| 35° | 143.1 | 143.1 | 147.1 | 155.3 | 159.4 | 163.5 | 165.5 | 163.5 | 159.4 | 155.3 | 153.3 |
| 37.5° | 134.9 | 134.9 | 136.9 | 141.0 | 149.2 | 153.3 | 155.3 | 151.2 | 147.1 | 143.1 | 143.1 |
| 40° | 126.7 | 126.7 | 128.8 | 130.8 | 139.0 | 145.1 | 145.1 | 139.0 | 134.9 | 136.9 | 134.9 |
| 42.5° | 120.6 | 120.6 | 122.6 | 122.6 | 126.7 | 136.9 | 134.9 | 130.8 | 128.8 | 128.8 | 126.7 |
| 45° | 114.4 | 112.4 | 114.4 | 114.4 | 116.5 | 126.7 | 126.7 | 120.6 | 120.6 | 122.6 | 120.6 |
| 47.5° | 108.3 | 106.3 | 108.3 | 108.3 | 110.4 | 116.5 | 116.5 | 114.4 | 114.4 | 114.4 | 116.5 |
| 50° | 102.2 | 102.2 | 102.2 | 102.2 | 104.2 | 106.3 | 110.4 | 108.3 | 108.3 | 108.3 | 110.4 |
| 52.5° | 96.1 | 96.1 | 96.1 | 98.1 | 98.1 | 102.2 | 104.2 | 102.2 | 104.2 | 104.2 | 104.2 |
| 55° | 92.0 | 89.9 | 89.9 | 94.0 | 94.0 | 98.1 | 100.1 | 98.1 | 100.1 | 100.1 | 100.1 |
| 57.5° | 85.8 | 85.8 | 85.8 | 87.9 | 89.9 | 94.0 | 98.1 | 94.0 | 96.1 | 96.1 | 98.1 |
| 60° | 79.7 | 79.7 | 79.7 | 83.8 | 85.8 | 89.9 | 92.0 | 89.9 | 92.0 | 92.0 | 92.0 |
| 62.5° | 73.6 | 75.6 | 75.6 | 77.7 | 79.7 | 85.8 | 87.9 | 85.8 | 87.9 | 87.9 | 87.9 |
| 65° | 69.5 | 69.5 | 71.5 | 73.6 | 75.6 | 79.7 | 81.7 | 81.7 | 81.7 | 83.8 | 81.7 |
| 67.5° | 63.4 | 63.4 | 65.4 | 67.4 | 69.5 | 75.6 | 75.6 | 75.6 | 77.7 | 75.6 | 75.6 |
| 70° | 57.2 | 57.2 | 59.3 | 61.3 | 63.4 | 69.5 | 69.5 | 69.5 | 71.5 | 67.4 | 67.4 |
| 72.5° | 51.1 | 51.1 | 53.1 | 55.2 | 59.3 | 65.4 | 63.4 | 63.4 | 63.4 | 61.3 | 61.3 |
| 75° | 45.0 | 45.0 | 47.0 | 49.0 | 51.1 | 59.3 | 57.2 | 55.2 | 55.2 | 53.1 | 53.1 |
| 77.5° | 36.8 | 36.8 | 38.8 | 42.9 | 45.0 | 51.1 | 49.0 | 47.0 | 45.0 | 45.0 | 45.0 |
| 80° | 28.6 | 30.7 | 32.7 | 34.7 | 36.8 | 40.9 | 38.8 | 36.8 | 34.7 | 34.7 | 34.7 |
| 82.5° | 20.4 | 22.5 | 24.5 | 26.6 | 28.6 | 28.6 | 28.6 | 28.6 | 26.6 | 24.5 | 24.5 |
| 85° | 8.2 | 12.3 | 16.3 | 16.3 | 18.4 | 16.3 | 18.4 | 16.3 | 14.3 | 14.3 | 12.3 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 2.0 | 4.1 | 6.1 | 6.1 | 6.1 | 6.1 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P437542
 CATALOG NUMBER: ISC-SA1D-750-U-SLR

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1614.5 | 1614.5 | 1614.5 | 1614.5 | 1614.5 | 1614.5 | 1614.5 | 1614.5 | 1614.5 | 1614.5 | 1614.5 |
| 2.5° | 1430.6 | 1463.3 | 1481.7 | 1514.4 | 1549.1 | 1596.1 | 1635.0 | 1690.2 | 1739.2 | 1749.4 | 1761.7 |
| 5° | 1185.4 | 1228.3 | 1248.7 | 1301.8 | 1383.6 | 1434.7 | 1516.4 | 1602.3 | 1708.5 | 1741.2 | 1784.2 |
| 7.5° | 891.1 | 923.8 | 976.9 | 1023.9 | 1120.0 | 1205.8 | 1316.2 | 1440.8 | 1565.5 | 1637.0 | 1706.5 |
| 10° | 678.5 | 719.4 | 776.6 | 831.8 | 925.8 | 1011.6 | 1142.4 | 1281.4 | 1440.8 | 1506.2 | 1579.8 |
| 12.5° | 564.1 | 596.8 | 654.0 | 729.6 | 817.5 | 899.2 | 997.3 | 1148.6 | 1316.2 | 1399.9 | 1489.9 |
| 15° | 455.7 | 490.5 | 562.0 | 645.8 | 731.7 | 823.6 | 917.6 | 1062.7 | 1267.1 | 1352.9 | 1438.8 |
| 17.5° | 363.8 | 394.4 | 455.7 | 545.7 | 639.7 | 741.9 | 856.3 | 1040.3 | 1277.3 | 1383.6 | 1483.7 |
| 20° | 282.0 | 308.6 | 355.6 | 437.4 | 533.4 | 654.0 | 801.1 | 1032.1 | 1338.6 | 1487.8 | 1588.0 |
| 22.5° | 243.2 | 253.4 | 280.0 | 337.2 | 435.3 | 576.3 | 750.0 | 1038.2 | 1436.7 | 1628.8 | 1743.3 |
| 25° | 216.6 | 224.8 | 235.0 | 269.8 | 347.4 | 496.6 | 705.1 | 1050.5 | 1541.0 | 1788.3 | 1919.0 |
| 27.5° | 200.3 | 204.4 | 210.5 | 226.9 | 284.1 | 431.2 | 660.1 | 1066.8 | 1682.0 | 1949.7 | 2076.4 |
| 30° | 183.9 | 183.9 | 190.1 | 206.4 | 249.3 | 384.2 | 627.4 | 1099.5 | 1821.0 | 2088.7 | 2213.3 |
| 32.5° | 167.6 | 167.6 | 177.8 | 192.1 | 226.9 | 345.4 | 594.7 | 1109.7 | 1925.2 | 2211.3 | 2311.4 |
| 35° | 153.3 | 157.4 | 165.5 | 181.9 | 212.5 | 316.8 | 564.1 | 1091.3 | 2000.8 | 2315.5 | 2417.7 |
| 37.5° | 145.1 | 147.1 | 157.4 | 171.7 | 194.2 | 290.2 | 533.4 | 1066.8 | 2103.0 | 2454.5 | 2534.2 |
| 40° | 134.9 | 139.0 | 149.2 | 163.5 | 181.9 | 269.8 | 498.7 | 1040.3 | 2192.9 | 2609.8 | 2650.7 |
| 42.5° | 128.8 | 132.8 | 141.0 | 155.3 | 173.7 | 245.2 | 466.0 | 1019.8 | 2289.0 | 2742.7 | 2771.3 |
| 45° | 122.6 | 126.7 | 136.9 | 149.2 | 173.7 | 226.9 | 433.3 | 1005.5 | 2383.0 | 2844.9 | 2867.3 |
| 47.5° | 116.5 | 120.6 | 130.8 | 147.1 | 171.7 | 216.6 | 410.8 | 991.2 | 2442.2 | 2932.7 | 2938.9 |
| 50° | 112.4 | 116.5 | 128.8 | 151.2 | 165.5 | 212.5 | 400.6 | 1005.5 | 2542.4 | 3002.2 | 2983.8 |
| 52.5° | 106.3 | 112.4 | 126.7 | 157.4 | 157.4 | 208.5 | 392.4 | 1056.6 | 2667.0 | 3104.4 | 3057.4 |
| 55° | 104.2 | 108.3 | 122.6 | 151.2 | 143.1 | 198.2 | 392.4 | 1095.4 | 2832.6 | 3306.7 | 3229.1 |
| 57.5° | 98.1 | 102.2 | 118.5 | 141.0 | 130.8 | 181.9 | 388.3 | 1158.8 | 3067.6 | 3529.5 | 3460.0 |
| 60° | 92.0 | 98.1 | 114.4 | 126.7 | 118.5 | 161.5 | 369.9 | 1228.3 | 3229.1 | 3650.1 | 3662.3 |
| 62.5° | 87.9 | 94.0 | 114.4 | 110.4 | 108.3 | 141.0 | 341.3 | 1271.2 | 3212.7 | 3611.2 | 3727.7 |
| 65° | 81.7 | 87.9 | 104.2 | 100.1 | 102.2 | 126.7 | 304.5 | 1250.8 | 2998.1 | 3447.7 | 3652.1 |
| 67.5° | 75.6 | 81.7 | 89.9 | 89.9 | 94.0 | 122.6 | 265.7 | 1132.2 | 2765.1 | 3249.5 | 3484.5 |
| 70° | 69.5 | 73.6 | 77.7 | 81.7 | 85.8 | 120.6 | 235.0 | 970.8 | 2497.4 | 3059.4 | 3245.4 |
| 72.5° | 61.3 | 63.4 | 67.4 | 71.5 | 79.7 | 114.4 | 222.8 | 788.9 | 2127.5 | 2648.7 | 2936.8 |
| 75° | 53.1 | 55.2 | 59.3 | 63.4 | 69.5 | 108.3 | 204.4 | 598.8 | 1753.5 | 2092.8 | 2372.8 |
| 77.5° | 45.0 | 47.0 | 51.1 | 53.1 | 59.3 | 96.1 | 175.8 | 433.3 | 1365.2 | 1508.3 | 1735.1 |
| 80° | 34.7 | 36.8 | 40.9 | 40.9 | 49.0 | 71.5 | 136.9 | 302.5 | 958.5 | 1068.9 | 1187.4 |
| 82.5° | 24.5 | 26.6 | 28.6 | 30.7 | 36.8 | 49.0 | 89.9 | 181.9 | 649.9 | 733.7 | 713.3 |
| 85° | 14.3 | 16.3 | 16.3 | 20.4 | 22.5 | 32.7 | 51.1 | 94.0 | 425.1 | 335.2 | 331.1 |
| 87.5° | 6.1 | 6.1 | 6.1 | 8.2 | 8.2 | 12.3 | 16.3 | 18.4 | 40.9 | 14.3 | 10.2 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P437542

CATALOG NUMBER: ISC-SA1D-750-U-SLR

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 359° | 360° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1614.5 | 1614.5 | 1614.5 | 1614.5 | 1614.5 | 1614.5 | 1614.5 | 1614.5 | 1614.5 | 1614.5 |
| 2.5° | 1780.1 | 1794.4 | 1804.6 | 1800.5 | 1794.4 | 1759.6 | 1724.9 | 1688.1 | 1655.4 | 1655.4 |
| 5° | 1853.7 | 1912.9 | 1937.4 | 1917.0 | 1872.0 | 1800.5 | 1710.6 | 1616.6 | 1571.6 | 1559.4 |
| 7.5° | 1814.8 | 1927.2 | 1986.5 | 1959.9 | 1900.7 | 1769.9 | 1632.9 | 1510.3 | 1442.9 | 1430.6 |
| 10° | 1737.2 | 1884.3 | 1951.7 | 1943.6 | 1878.2 | 1726.9 | 1561.4 | 1422.4 | 1350.9 | 1342.7 |
| 12.5° | 1647.2 | 1790.3 | 1876.1 | 1880.2 | 1837.3 | 1704.5 | 1530.7 | 1365.2 | 1301.8 | 1285.5 |
| 15° | 1592.1 | 1716.7 | 1776.0 | 1761.7 | 1773.9 | 1686.1 | 1543.0 | 1387.7 | 1310.0 | 1295.7 |
| 17.5° | 1594.1 | 1647.2 | 1661.5 | 1639.1 | 1686.1 | 1682.0 | 1612.5 | 1469.4 | 1383.6 | 1369.3 |
| 20° | 1647.2 | 1602.3 | 1557.3 | 1553.2 | 1614.5 | 1696.3 | 1722.9 | 1606.4 | 1508.3 | 1498.0 |
| 22.5° | 1739.2 | 1590.0 | 1496.0 | 1481.7 | 1559.4 | 1710.6 | 1829.1 | 1773.9 | 1682.0 | 1655.4 |
| 25° | 1841.4 | 1602.3 | 1457.2 | 1438.8 | 1508.3 | 1720.8 | 1943.6 | 1945.6 | 1843.4 | 1818.9 |
| 27.5° | 1951.7 | 1641.1 | 1457.2 | 1436.7 | 1510.3 | 1737.2 | 2019.2 | 2100.9 | 2006.9 | 1986.5 |
| 30° | 2049.8 | 1696.3 | 1471.5 | 1449.0 | 1534.8 | 1753.5 | 2070.3 | 2239.9 | 2133.6 | 2105.0 |
| 32.5° | 2109.1 | 1743.3 | 1506.2 | 1465.3 | 1577.7 | 1786.2 | 2117.3 | 2358.4 | 2276.7 | 2237.9 |
| 35° | 2156.1 | 1798.5 | 1563.4 | 1510.3 | 1641.1 | 1839.3 | 2156.1 | 2487.2 | 2409.5 | 2387.1 |
| 37.5° | 2190.9 | 1863.9 | 1622.7 | 1571.6 | 1724.9 | 1910.9 | 2211.3 | 2624.1 | 2599.6 | 2550.6 |
| 40° | 2248.1 | 1904.7 | 1729.0 | 1710.6 | 1870.0 | 2023.3 | 2276.7 | 2742.7 | 2759.0 | 2730.4 |
| 42.5° | 2299.2 | 1984.4 | 1880.2 | 1900.7 | 2056.0 | 2147.9 | 2364.6 | 2830.5 | 2918.4 | 2881.6 |
| 45° | 2340.1 | 2094.8 | 2070.3 | 2137.7 | 2270.6 | 2307.4 | 2413.6 | 2891.9 | 2983.8 | 2959.3 |
| 47.5° | 2397.3 | 2239.9 | 2323.7 | 2411.6 | 2521.9 | 2472.9 | 2464.7 | 2957.3 | 3051.3 | 3026.7 |
| 50° | 2479.0 | 2409.5 | 2577.1 | 2691.6 | 2763.1 | 2607.8 | 2528.1 | 3016.5 | 3155.5 | 3141.2 |
| 52.5° | 2562.8 | 2605.7 | 2834.6 | 2940.9 | 2987.9 | 2775.4 | 2618.0 | 3110.5 | 3278.1 | 3278.1 |
| 55° | 2718.1 | 2797.8 | 3108.5 | 3175.9 | 3239.3 | 2926.6 | 2738.6 | 3251.6 | 3468.2 | 3478.4 |
| 57.5° | 2945.0 | 3004.3 | 3317.0 | 3394.6 | 3411.0 | 3096.2 | 2928.6 | 3447.7 | 3629.6 | 3648.0 |
| 60° | 3180.0 | 3208.6 | 3523.4 | 3592.9 | 3537.7 | 3314.9 | 3151.4 | 3676.6 | 3735.9 | 3725.7 |
| 62.5° | 3439.6 | 3406.9 | 3666.4 | 3715.5 | 3701.2 | 3507.0 | 3431.4 | 3885.1 | 3813.6 | 3774.7 |
| 65° | 3646.0 | 3523.4 | 3740.0 | 3750.2 | 3758.4 | 3639.9 | 3717.5 | 3979.1 | 3846.3 | 3760.4 |
| 67.5° | 3770.7 | 3541.8 | 3590.8 | 3543.8 | 3576.5 | 3605.1 | 3911.7 | 3940.3 | 3707.3 | 3631.7 |
| 70° | 3742.0 | 3282.2 | 3061.5 | 3008.4 | 3010.4 | 3210.7 | 3787.0 | 3697.1 | 3390.5 | 3282.2 |
| 72.5° | 3478.4 | 2759.0 | 2438.2 | 2366.6 | 2380.9 | 2399.3 | 3184.1 | 3227.0 | 2740.6 | 2683.4 |
| 75° | 2928.6 | 2125.5 | 1755.6 | 1739.2 | 1718.8 | 1798.5 | 2546.5 | 2358.4 | 1818.9 | 1833.2 |
| 77.5° | 2389.1 | 1565.5 | 1289.6 | 1205.8 | 1193.5 | 1205.8 | 1737.2 | 1346.8 | 1056.6 | 1011.6 |
| 80° | 1722.9 | 1042.3 | 962.6 | 944.2 | 887.0 | 713.3 | 909.5 | 866.5 | 596.8 | 586.5 |
| 82.5° | 1134.3 | 719.4 | 735.7 | 613.1 | 576.3 | 451.7 | 551.8 | 441.4 | 298.4 | 284.1 |
| 85° | 588.6 | 374.0 | 308.6 | 134.9 | 151.2 | 126.7 | 120.6 | 98.1 | 10.2 | 10.2 |
| 87.5° | 20.4 | 8.2 | 6.1 | 6.1 | 4.1 | 2.0 | 2.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-4-R4

Test Date: 10/02/2019

Luminaire Tested: SA1C-750-U-5WQ

Data in this report applies to families of products SA1C-760-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-4-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: MCGRAW-EDISON
 Catalog Number: **SA1C-750-U-5WQ**
 Description: MCGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K): | 4884 | CRI (Ra): | 73.5 | R9: | -28.4 |
| CIE u': | 0.2101 | R1: | 70.5 | R10: | 48.6 |
| CIE v': | 0.4904 | R2: | 77.7 | R11: | 73.2 |
| Duv: | 0.0037 | R3: | 84.6 | R12: | 50.7 |
| CIE x: | 0.3493 | R4: | 74.7 | R13: | 71.2 |
| CIE y: | 0.3624 | R5: | 71.9 | R14: | 91.4 |
| CIE z: | 0.2884 | R6: | 70.7 | | |
| Peak Wavelength (nm): | 444 | R7: | 81.2 | | |
| Dominant Wavelength (nm): | 571 | R8: | 56.9 | | |
| Purity: | 13.7 | | | | |
| Rf: | 74.9 | | | | |
| Rg: | 96.3 | | | | |



Test Conditions

Stabilization Time: 240M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0./44%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-4-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-4-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-4-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 13493.5 S/P: 1.77

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 5378.9 M/P: 0.71

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Summary

$R_f = 74.9$
 $R_g = 96.3$
 CIE $R_a = 73.5$
 $R_g = -28.4$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 61 | CES51 = 90 | CES76 = 52 |
| CES02 = 60 | CES27 = 84 | CES52 = 91 | CES77 = 71 |
| CES03 = 30 | CES28 = 81 | CES53 = 79 | CES78 = 54 |
| CES04 = 69 | CES29 = 58 | CES54 = 83 | CES79 = 80 |
| CES05 = 46 | CES30 = 67 | CES55 = 83 | CES80 = 77 |
| CES06 = 50 | CES31 = 63 | CES56 = 73 | CES81 = 77 |
| CES07 = 39 | CES32 = 59 | CES57 = 72 | CES82 = 90 |
| CES08 = 38 | CES33 = 69 | CES58 = 73 | CES83 = 86 |
| CES09 = 29 | CES34 = 69 | CES59 = 88 | CES84 = 88 |
| CES10 = 73 | CES35 = 83 | CES60 = 93 | CES85 = 84 |
| CES11 = 56 | CES36 = 95 | CES61 = 88 | CES86 = 75 |
| CES12 = 61 | CES37 = 78 | CES62 = 85 | CES87 = 78 |
| CES13 = 41 | CES38 = 76 | CES63 = 77 | CES88 = 79 |
| CES14 = 74 | CES39 = 93 | CES64 = 74 | CES89 = 75 |
| CES15 = 70 | CES40 = 86 | CES65 = 67 | CES90 = 77 |
| CES16 = 46 | CES41 = 87 | CES66 = 69 | CES91 = 89 |
| CES17 = 49 | CES42 = 78 | CES67 = 67 | CES92 = 66 |
| CES18 = 55 | CES43 = 75 | CES68 = 73 | CES93 = 80 |
| CES19 = 71 | CES44 = 99 | CES69 = 81 | CES94 = 57 |
| CES20 = 64 | CES45 = 83 | CES70 = 63 | CES95 = 71 |
| CES21 = 85 | CES46 = 81 | CES71 = 60 | CES96 = 78 |
| CES22 = 77 | CES47 = 80 | CES72 = 86 | CES97 = 85 |
| CES23 = 91 | CES48 = 72 | CES73 = 53 | CES98 = 75 |
| CES24 = 90 | CES49 = 81 | CES74 = 96 | CES99 = 62 |
| CES25 = 71 | CES50 = 89 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Measure Comparisons



(END OF REPORT)