

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P437745

Luminaire Tested: **ISC-SA1E-827-U-SL3**

Issue Date: 12/9/2020

Test Information

Test Method: LM-79-08
Report Number: P437745
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-074-16)
Test Lab: INNOVATION CENTER
Issue Date: 12/9/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: ISC-SA1E-827-U-SL3
Description: IMPACT ELITE LED CYLINDER LUMINAIRE
(1) 80 CRI, 2700K, 1050mA LIGHTSQUARE WITH 16 LEDS AND TYPE III SPILL
LIGHT ELIMINATOR OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5208 lumens
Efficiency: N/A
Efficacy: 89.5 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B1 - U0 - G2


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P437745
 CATALOG NUMBER: ISC-SA1E-827-U-SL3

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 2.4 fc
 Type III - Medium - N/A

REPORT NUMBER: P437745
CATALOG NUMBER: ISC-SA1E-827-U-SL3

Luminous Intensity Polar Plot



— Vertical Plane Through 59-Deg Lateral - - - Horizontal Cone Through 72.5-Deg Vertical

REPORT NUMBER: P437745
 CATALOG NUMBER: ISC-SA1E-827-U-SL3


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 850.1 | 0.0 | 850.1 |
| | % Fixture | 16.3 | 0.0 | 16.3 |
| Street Side | Lumens | 4357.9 | 0.0 | 4357.9 |
| | % Fixture | 83.7 | 0.0 | 83.7 |
| Total | Lumens | 5208.0 | 0.0 | 5208.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

Coefficient of Utilization

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 126.9 | 2.4 |
| 10°-20° | 285.0 | 5.5 |
| 20°-30° | 367.3 | 7.1 |
| 30°-40° | 469.9 | 9.0 |
| 40°-50° | 652.1 | 12.5 |
| 50°-60° | 961.1 | 18.5 |
| 60°-70° | 1293.2 | 24.8 |
| 70°-80° | 940.7 | 18.1 |
| 80°-90° | 111.9 | 2.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 5208.0 | 100.0 |
| 0°-180° | 5208.0 | 100.0 |




REPORT NUMBER: P437745
 CATALOG NUMBER: ISC-SA1E-827-U-SL3

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 502.3 | 9.6 | | | |
| FM (30°-60°) | 1770.5 | 34.0 | | | |
| FH (60°-80°) | 1985.3 | 38.1 | | | G2/5000 |
| FVH (80°-90°) | 99.8 | 1.9 | | | G1/100 |
| BL (0°-30°) | 276.9 | 5.3 | B1/500 | | |
| BM (30°-60°) | 312.5 | 6.0 | B1/1000 | | |
| BH (60°-80°) | 248.6 | 4.8 | B1/500 | | G1/500 |
| BVH (80°-90°) | 12.1 | 0.2 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G2
 Type III Medium





REPORT NUMBER: P437745

CATALOG NUMBER: ISC-SA1E-827-U-SL3

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 59° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1478.1 | 1478.1 | 1478.1 | 1478.1 | 1478.1 | 1478.1 | 1478.1 | 1478.1 | 1478.1 | 1478.1 | 1478.1 |
| 2.5° | 1470.5 | 1470.5 | 1476.2 | 1480.0 | 1474.3 | 1480.0 | 1478.1 | 1476.2 | 1478.1 | 1478.1 | 1474.3 |
| 5° | 1409.8 | 1417.4 | 1417.4 | 1419.3 | 1432.6 | 1442.1 | 1445.9 | 1449.7 | 1451.6 | 1453.5 | 1449.7 |
| 7.5° | 1335.8 | 1339.6 | 1343.4 | 1360.5 | 1368.1 | 1388.9 | 1402.2 | 1409.8 | 1417.4 | 1421.2 | 1409.8 |
| 10° | 1254.2 | 1259.9 | 1271.3 | 1284.6 | 1303.6 | 1332.0 | 1354.8 | 1368.1 | 1379.5 | 1385.1 | 1371.9 |
| 12.5° | 1185.9 | 1187.8 | 1199.2 | 1220.1 | 1242.8 | 1282.7 | 1311.1 | 1326.3 | 1341.5 | 1352.9 | 1337.7 |
| 15° | 1123.3 | 1125.2 | 1134.7 | 1159.3 | 1185.9 | 1229.6 | 1271.3 | 1294.1 | 1314.9 | 1333.9 | 1313.0 |
| 17.5° | 1074.0 | 1079.7 | 1083.4 | 1104.3 | 1136.6 | 1184.0 | 1239.0 | 1261.8 | 1294.1 | 1322.5 | 1296.0 |
| 20° | 1045.5 | 1043.6 | 1045.5 | 1058.8 | 1092.9 | 1140.4 | 1204.9 | 1237.1 | 1275.1 | 1314.9 | 1278.9 |
| 22.5° | 1028.4 | 1032.2 | 1030.3 | 1036.0 | 1056.9 | 1104.3 | 1168.8 | 1214.4 | 1258.0 | 1309.2 | 1263.7 |
| 25° | 1028.4 | 1034.1 | 1032.2 | 1030.3 | 1037.9 | 1070.2 | 1138.5 | 1184.0 | 1239.0 | 1309.2 | 1246.6 |
| 27.5° | 1047.4 | 1049.3 | 1045.5 | 1039.8 | 1039.8 | 1051.2 | 1111.9 | 1153.7 | 1229.6 | 1307.3 | 1237.1 |
| 30° | 1064.5 | 1068.3 | 1068.3 | 1064.5 | 1058.8 | 1053.1 | 1092.9 | 1136.6 | 1220.1 | 1318.7 | 1229.6 |
| 32.5° | 1087.2 | 1091.0 | 1098.6 | 1102.4 | 1094.8 | 1077.8 | 1098.6 | 1134.7 | 1222.0 | 1343.4 | 1231.5 |
| 35° | 1115.7 | 1119.5 | 1130.9 | 1149.9 | 1144.2 | 1115.7 | 1119.5 | 1151.8 | 1237.1 | 1370.0 | 1239.0 |
| 37.5° | 1138.5 | 1144.2 | 1168.8 | 1201.1 | 1203.0 | 1172.6 | 1170.7 | 1193.5 | 1265.6 | 1411.7 | 1265.6 |
| 40° | 1161.2 | 1168.8 | 1204.9 | 1258.0 | 1269.4 | 1252.3 | 1240.9 | 1258.0 | 1316.8 | 1472.4 | 1309.2 |
| 42.5° | 1191.6 | 1199.2 | 1246.6 | 1313.0 | 1341.5 | 1333.9 | 1326.3 | 1351.0 | 1394.6 | 1554.0 | 1377.6 |
| 45° | 1223.9 | 1239.0 | 1299.8 | 1373.8 | 1425.0 | 1430.7 | 1438.3 | 1453.5 | 1487.6 | 1667.9 | 1474.3 |
| 47.5° | 1282.7 | 1296.0 | 1366.2 | 1442.1 | 1508.5 | 1538.8 | 1552.1 | 1571.1 | 1592.0 | 1772.2 | 1592.0 |
| 50° | 1362.4 | 1388.9 | 1451.6 | 1525.6 | 1603.4 | 1662.2 | 1696.3 | 1696.3 | 1719.1 | 1897.5 | 1721.0 |
| 52.5° | 1481.9 | 1506.6 | 1544.5 | 1614.7 | 1707.7 | 1800.7 | 1848.1 | 1855.7 | 1848.1 | 2017.0 | 1851.9 |
| 55° | 1582.5 | 1607.1 | 1643.2 | 1694.4 | 1812.1 | 1956.3 | 2037.9 | 2032.2 | 2005.6 | 2144.1 | 1980.9 |
| 57.5° | 1694.4 | 1713.4 | 1745.7 | 1787.4 | 1918.3 | 2117.6 | 2237.1 | 2231.4 | 2182.1 | 2273.2 | 2121.4 |
| 60° | 1741.9 | 1768.4 | 1827.3 | 1912.6 | 2083.4 | 2324.4 | 2464.8 | 2447.7 | 2337.7 | 2411.7 | 2246.6 |
| 62.5° | 1599.6 | 1648.9 | 1768.4 | 1941.1 | 2275.1 | 2669.7 | 2762.7 | 2707.7 | 2557.8 | 2563.5 | 2415.5 |
| 65° | 1278.9 | 1252.3 | 1434.5 | 1721.0 | 2290.2 | 3096.7 | 3218.1 | 3098.5 | 2832.9 | 2757.0 | 2607.1 |
| 67.5° | 730.5 | 741.9 | 829.2 | 1138.5 | 1886.1 | 3271.2 | 4007.4 | 3796.8 | 3263.6 | 3058.7 | 2838.6 |
| 70° | 495.2 | 506.6 | 544.6 | 675.5 | 1083.4 | 2924.0 | 4650.7 | 4692.4 | 3929.6 | 3326.2 | 2846.2 |
| 72.5° | 387.1 | 389.0 | 428.8 | 531.3 | 656.5 | 1836.7 | 4421.1 | 4891.6 | 4385.0 | 3335.7 | 2610.9 |
| 75° | 296.0 | 297.9 | 334.0 | 453.5 | 590.1 | 889.9 | 3366.1 | 4102.3 | 4113.7 | 3068.2 | 2132.7 |
| 77.5° | 187.8 | 197.3 | 239.1 | 362.4 | 554.1 | 590.1 | 2144.1 | 2889.8 | 2965.7 | 2273.2 | 1115.7 |
| 80° | 91.1 | 94.9 | 119.5 | 231.5 | 487.6 | 521.8 | 1277.0 | 1922.1 | 1666.0 | 886.1 | 339.6 |
| 82.5° | 37.9 | 39.8 | 56.9 | 100.6 | 311.2 | 442.1 | 639.4 | 988.6 | 643.2 | 241.0 | 110.1 |
| 85° | 7.6 | 9.5 | 13.3 | 24.7 | 100.6 | 216.3 | 261.8 | 256.2 | 155.6 | 74.0 | 41.7 |
| 87.5° | 0.0 | 0.0 | 0.0 | 1.9 | 1.9 | 3.8 | 3.8 | 3.8 | 3.8 | 3.8 | 3.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P437745

CATALOG NUMBER: ISC-SA1E-827-U-SL3

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1478.1 | 1478.1 | 1478.1 | 1478.1 | 1478.1 | 1478.1 | 1478.1 | 1478.1 | 1478.1 | 1478.1 | 1478.1 |
| 2.5° | 1472.4 | 1472.4 | 1457.2 | 1445.9 | 1432.6 | 1423.1 | 1413.6 | 1402.2 | 1400.3 | 1406.0 | 1411.7 |
| 5° | 1442.1 | 1434.5 | 1409.8 | 1387.0 | 1360.5 | 1330.1 | 1311.1 | 1286.5 | 1273.2 | 1278.9 | 1275.1 |
| 7.5° | 1402.2 | 1390.8 | 1345.3 | 1307.3 | 1254.2 | 1206.8 | 1174.5 | 1138.5 | 1113.8 | 1104.3 | 1098.6 |
| 10° | 1360.5 | 1337.7 | 1277.0 | 1208.7 | 1138.5 | 1068.3 | 1009.4 | 952.5 | 924.1 | 922.2 | 891.8 |
| 12.5° | 1320.6 | 1290.3 | 1204.9 | 1106.2 | 1009.4 | 914.6 | 827.3 | 764.7 | 686.9 | 664.1 | 671.7 |
| 15° | 1288.4 | 1246.6 | 1127.1 | 1001.9 | 876.6 | 757.1 | 643.2 | 550.3 | 482.0 | 457.3 | 447.8 |
| 17.5° | 1258.0 | 1199.2 | 1055.0 | 905.1 | 747.6 | 597.7 | 459.2 | 389.0 | 347.2 | 332.1 | 332.1 |
| 20° | 1223.9 | 1155.6 | 977.2 | 796.9 | 605.3 | 444.0 | 339.6 | 305.5 | 292.2 | 290.3 | 288.4 |
| 22.5° | 1197.3 | 1111.9 | 897.5 | 683.1 | 472.5 | 337.7 | 280.8 | 265.6 | 265.6 | 267.5 | 267.5 |
| 25° | 1165.0 | 1062.6 | 812.1 | 561.6 | 364.3 | 271.3 | 248.6 | 242.9 | 248.6 | 254.3 | 254.3 |
| 27.5° | 1142.3 | 1018.9 | 734.3 | 447.8 | 282.7 | 235.3 | 223.9 | 225.8 | 233.4 | 241.0 | 241.0 |
| 30° | 1123.3 | 977.2 | 652.7 | 352.9 | 235.3 | 208.7 | 206.8 | 210.6 | 218.2 | 225.8 | 223.9 |
| 32.5° | 1104.3 | 944.9 | 563.5 | 278.9 | 203.0 | 191.6 | 189.7 | 195.4 | 201.1 | 203.0 | 206.8 |
| 35° | 1096.7 | 918.4 | 474.4 | 229.6 | 184.1 | 178.4 | 178.4 | 180.3 | 182.2 | 184.1 | 184.1 |
| 37.5° | 1102.4 | 897.5 | 394.7 | 195.4 | 172.7 | 170.8 | 168.9 | 167.0 | 167.0 | 167.0 | 168.9 |
| 40° | 1125.2 | 889.9 | 326.4 | 176.5 | 163.2 | 163.2 | 159.4 | 153.7 | 151.8 | 153.7 | 151.8 |
| 42.5° | 1170.7 | 905.1 | 269.4 | 165.1 | 155.6 | 153.7 | 148.0 | 144.2 | 142.3 | 142.3 | 140.4 |
| 45° | 1242.8 | 931.7 | 231.5 | 157.5 | 149.9 | 144.2 | 138.5 | 134.7 | 132.8 | 134.7 | 134.7 |
| 47.5° | 1337.7 | 981.0 | 204.9 | 149.9 | 144.2 | 134.7 | 127.1 | 125.2 | 125.2 | 129.0 | 129.0 |
| 50° | 1451.6 | 1047.4 | 189.7 | 146.1 | 138.5 | 127.1 | 119.5 | 117.6 | 119.5 | 123.3 | 125.2 |
| 52.5° | 1573.0 | 1130.9 | 186.0 | 144.2 | 132.8 | 119.5 | 113.8 | 112.0 | 113.8 | 117.6 | 119.5 |
| 55° | 1694.4 | 1222.0 | 195.4 | 144.2 | 127.1 | 113.8 | 110.1 | 104.4 | 106.3 | 110.1 | 112.0 |
| 57.5° | 1823.5 | 1320.6 | 223.9 | 140.4 | 123.3 | 110.1 | 104.4 | 98.7 | 98.7 | 102.5 | 102.5 |
| 60° | 1962.0 | 1432.6 | 277.0 | 140.4 | 119.5 | 106.3 | 96.8 | 91.1 | 91.1 | 91.1 | 93.0 |
| 62.5° | 2115.7 | 1567.3 | 339.6 | 142.3 | 121.4 | 102.5 | 89.2 | 81.6 | 81.6 | 83.5 | 81.6 |
| 65° | 2343.4 | 1768.4 | 356.7 | 144.2 | 125.2 | 98.7 | 83.5 | 75.9 | 74.0 | 74.0 | 74.0 |
| 67.5° | 2483.8 | 1791.2 | 277.0 | 140.4 | 130.9 | 98.7 | 77.8 | 68.3 | 66.4 | 64.5 | 64.5 |
| 70° | 2381.3 | 1573.0 | 197.3 | 134.7 | 130.9 | 98.7 | 74.0 | 62.6 | 58.8 | 55.0 | 55.0 |
| 72.5° | 2060.6 | 1248.5 | 161.3 | 127.1 | 121.4 | 93.0 | 68.3 | 56.9 | 51.2 | 47.4 | 47.4 |
| 75° | 1650.8 | 886.1 | 136.6 | 117.6 | 102.5 | 74.0 | 56.9 | 47.4 | 43.6 | 41.7 | 41.7 |
| 77.5° | 804.5 | 436.4 | 106.3 | 102.5 | 81.6 | 55.0 | 45.5 | 39.8 | 37.9 | 34.2 | 34.2 |
| 80° | 235.3 | 161.3 | 79.7 | 81.6 | 51.2 | 37.9 | 34.2 | 32.3 | 30.4 | 26.6 | 28.5 |
| 82.5° | 108.2 | 91.1 | 56.9 | 51.2 | 32.3 | 22.8 | 22.8 | 20.9 | 19.0 | 17.1 | 17.1 |
| 85° | 43.6 | 45.5 | 30.4 | 24.7 | 15.2 | 11.4 | 9.5 | 9.5 | 7.6 | 7.6 | 7.6 |
| 87.5° | 3.8 | 5.7 | 5.7 | 3.8 | 3.8 | 1.9 | 0.0 | 0.0 | 0.0 | 1.9 | 1.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) | λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) | λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) | λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) | λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) |
|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_9 = -1.5$



Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)