

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P438488

Luminaire Tested: **IST-SA1D-727-U-SL4**

Issue Date: 12/10/2020

Test Information

Test Method: LM-79-08
Report Number: P438488
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-074-18)
Test Lab: INNOVATION CENTER
Issue Date: 12/10/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: IST-SA1D-727-U-SL4
Description: IMPACT ELITE LED TRAPEZOID LUMINAIRE
(1) 70 CRI, 2700K, 800mA LIGHTSQUARE WITH 16 LEDS AND TYPE IV SPILL LIGHT
ELIMINATOR OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4611 lumens
Efficiency: N/A
Efficacy: 102.0 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 45.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P438488
 CATALOG NUMBER: IST-SA1D-727-U-SL4

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1.3 fc
 Type IV - Short - N/A

REPORT NUMBER: P438488
CATALOG NUMBER: IST-SA1D-727-U-SL4

Luminous Intensity Polar Plot



— Vertical Plane Through 36-Deg Lateral - - - Horizontal Cone Through 75-Deg Vertical

REPORT NUMBER: P438488
 CATALOG NUMBER: IST-SA1D-727-U-SL4

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 680.5 | 0.0 | 680.5 |
| | % Fixture | 14.8 | 0.0 | 14.8 |
| Street Side | Lumens | 3930.5 | 0.0 | 3930.5 |
| | % Fixture | 85.2 | 0.0 | 85.2 |
| Total | Lumens | 4611.0 | 0.0 | 4611.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 74.2 | 1.6 |
| 10°-20° | 191.9 | 4.2 |
| 20°-30° | 296.7 | 6.4 |
| 30°-40° | 429.7 | 9.3 |
| 40°-50° | 621.5 | 13.5 |
| 50°-60° | 862.1 | 18.7 |
| 60°-70° | 1088.6 | 23.6 |
| 70°-80° | 935.0 | 20.3 |
| 80°-90° | 111.4 | 2.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 4611.0 | 100.0 |
| 0°-180° | 4611.0 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P438488


CATALOG NUMBER: IST-SA1D-727-U-SL4

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 370.3 | 8.0 | | | |
| FM (30°-60°) | 1587.1 | 34.4 | | | |
| FH (60°-80°) | 1872.1 | 40.6 | | | G2/5000 |
| FVH (80°-90°) | 101.1 | 2.2 | | | G2/225 |
| BL (0°-30°) | 192.4 | 4.2 | B1/500 | | |
| BM (30°-60°) | 326.3 | 7.1 | B1/1000 | | |
| BH (60°-80°) | 151.5 | 3.3 | B1/500 | | G1/500 |
| BVH (80°-90°) | 10.3 | 0.2 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P438488

CATALOG NUMBER: IST-SA1D-727-U-SL4

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 36° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 841.3 | 841.3 | 841.3 | 841.3 | 841.3 | 841.3 | 841.3 | 841.3 | 841.3 | 841.3 | 841.3 |
| 2.5° | 865.3 | 865.3 | 865.3 | 863.6 | 860.2 | 858.5 | 855.0 | 851.6 | 849.9 | 843.0 | 841.3 |
| 5° | 865.3 | 867.1 | 865.3 | 863.6 | 860.2 | 856.7 | 853.3 | 846.4 | 841.3 | 832.7 | 824.1 |
| 7.5° | 856.7 | 858.5 | 858.5 | 856.7 | 853.3 | 851.6 | 848.1 | 839.5 | 832.7 | 820.6 | 806.8 |
| 10° | 843.0 | 846.4 | 846.4 | 848.1 | 849.9 | 849.9 | 846.4 | 839.5 | 829.2 | 815.4 | 793.1 |
| 12.5° | 825.8 | 834.4 | 839.5 | 844.7 | 851.6 | 851.6 | 853.3 | 843.0 | 834.4 | 815.4 | 793.1 |
| 15° | 820.6 | 825.8 | 836.1 | 851.6 | 858.5 | 853.3 | 860.2 | 855.0 | 844.7 | 825.8 | 798.2 |
| 17.5° | 818.9 | 824.1 | 841.3 | 860.2 | 870.5 | 873.9 | 873.9 | 867.1 | 855.0 | 836.1 | 801.7 |
| 20° | 825.8 | 832.7 | 855.0 | 879.1 | 894.6 | 894.6 | 892.9 | 884.3 | 868.8 | 846.4 | 808.6 |
| 22.5° | 848.1 | 849.9 | 875.7 | 904.9 | 916.9 | 913.5 | 916.9 | 901.5 | 884.3 | 861.9 | 817.2 |
| 25° | 877.4 | 880.8 | 901.5 | 935.9 | 942.8 | 944.5 | 939.3 | 922.1 | 903.2 | 880.8 | 827.5 |
| 27.5° | 916.9 | 922.1 | 937.6 | 970.3 | 975.4 | 972.0 | 965.1 | 944.5 | 925.6 | 904.9 | 848.1 |
| 30° | 963.4 | 966.8 | 985.8 | 999.5 | 1004.7 | 1001.2 | 996.1 | 973.7 | 958.2 | 939.3 | 879.1 |
| 32.5° | 1008.1 | 1009.8 | 1030.5 | 1044.3 | 1035.7 | 1035.7 | 1028.8 | 1006.4 | 994.4 | 990.9 | 918.7 |
| 35° | 1054.6 | 1058.0 | 1076.9 | 1083.8 | 1070.1 | 1071.8 | 1070.1 | 1051.1 | 1054.6 | 1061.5 | 978.9 |
| 37.5° | 1097.6 | 1102.7 | 1125.1 | 1126.8 | 1121.7 | 1116.5 | 1121.7 | 1111.3 | 1118.2 | 1145.8 | 1049.4 |
| 40° | 1135.4 | 1142.3 | 1169.8 | 1175.0 | 1173.3 | 1173.3 | 1176.7 | 1175.0 | 1200.8 | 1245.5 | 1135.4 |
| 42.5° | 1166.4 | 1175.0 | 1207.7 | 1221.5 | 1231.8 | 1236.9 | 1249.0 | 1252.4 | 1290.3 | 1362.5 | 1235.2 |
| 45° | 1197.4 | 1206.0 | 1250.7 | 1273.1 | 1297.1 | 1298.9 | 1323.0 | 1335.0 | 1405.5 | 1470.9 | 1343.6 |
| 47.5° | 1233.5 | 1243.8 | 1285.1 | 1329.8 | 1357.4 | 1362.5 | 1407.3 | 1431.3 | 1517.4 | 1601.7 | 1445.1 |
| 50° | 1283.4 | 1286.8 | 1319.5 | 1395.2 | 1429.6 | 1438.2 | 1488.1 | 1538.0 | 1632.6 | 1716.9 | 1534.6 |
| 52.5° | 1345.3 | 1341.9 | 1357.4 | 1453.7 | 1507.0 | 1519.1 | 1599.9 | 1649.8 | 1763.4 | 1840.8 | 1605.1 |
| 55° | 1396.9 | 1393.5 | 1415.9 | 1520.8 | 1605.1 | 1608.5 | 1704.9 | 1753.0 | 1883.8 | 1932.0 | 1665.3 |
| 57.5° | 1457.1 | 1450.3 | 1472.6 | 1601.7 | 1716.9 | 1718.6 | 1830.5 | 1885.5 | 1992.2 | 2012.8 | 1704.9 |
| 60° | 1507.0 | 1507.0 | 1536.3 | 1680.8 | 1840.8 | 1859.7 | 1961.2 | 2004.2 | 2097.1 | 2071.3 | 1723.8 |
| 62.5° | 1553.5 | 1562.1 | 1603.4 | 1785.7 | 1987.0 | 2002.5 | 2105.7 | 2122.9 | 2205.5 | 2116.0 | 1703.2 |
| 65° | 1608.5 | 1622.3 | 1701.4 | 1911.3 | 2160.8 | 2171.1 | 2257.1 | 2281.2 | 2313.9 | 2114.3 | 1613.7 |
| 67.5° | 1667.0 | 1689.4 | 1794.3 | 2052.4 | 2351.7 | 2379.3 | 2472.2 | 2448.1 | 2386.1 | 2047.2 | 1426.2 |
| 70° | 1746.2 | 1773.7 | 1923.4 | 2239.9 | 2613.2 | 2647.6 | 2769.8 | 2621.8 | 2348.3 | 1808.1 | 1156.1 |
| 72.5° | 1806.4 | 1842.5 | 2047.2 | 2482.5 | 2967.6 | 3020.9 | 2991.7 | 2625.3 | 2105.7 | 1441.7 | 774.2 |
| 75° | 1584.4 | 1639.5 | 1949.2 | 2522.0 | 3119.0 | 3143.1 | 2830.0 | 2219.3 | 1491.5 | 744.9 | 333.7 |
| 77.5° | 1157.8 | 1154.4 | 1424.5 | 1959.5 | 2556.4 | 2492.8 | 2147.0 | 1443.4 | 708.8 | 270.1 | 168.6 |
| 80° | 581.5 | 559.1 | 770.7 | 1044.3 | 1379.7 | 1422.7 | 1269.6 | 750.1 | 280.4 | 144.5 | 101.5 |
| 82.5° | 215.0 | 220.2 | 282.1 | 426.6 | 693.3 | 703.6 | 512.7 | 318.3 | 153.1 | 75.7 | 53.3 |
| 85° | 82.6 | 86.0 | 92.9 | 92.9 | 129.0 | 142.8 | 132.5 | 127.3 | 51.6 | 25.8 | 29.2 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 1.7 | 1.7 | 1.7 | 1.7 | 1.7 | 1.7 | 1.7 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P438488
 CATALOG NUMBER: IST-SA1D-727-U-SL4

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 841.3 | 841.3 | 841.3 | 841.3 | 841.3 | 841.3 | 841.3 | 841.3 | 841.3 | 841.3 | 841.3 |
| 2.5° | 836.1 | 832.7 | 825.8 | 813.7 | 806.8 | 801.7 | 794.8 | 787.9 | 786.2 | 784.5 | 793.1 |
| 5° | 815.4 | 810.3 | 793.1 | 777.6 | 760.4 | 746.6 | 732.9 | 720.8 | 713.9 | 712.2 | 715.7 |
| 7.5° | 794.8 | 787.9 | 762.1 | 731.2 | 701.9 | 677.8 | 653.7 | 641.7 | 622.8 | 622.8 | 624.5 |
| 10° | 782.8 | 770.7 | 734.6 | 688.1 | 650.3 | 607.3 | 578.0 | 548.8 | 536.8 | 528.1 | 524.7 |
| 12.5° | 775.9 | 757.0 | 708.8 | 657.2 | 598.7 | 541.9 | 502.3 | 466.2 | 447.3 | 433.5 | 433.5 |
| 15° | 777.6 | 757.0 | 691.6 | 624.5 | 548.8 | 480.0 | 430.1 | 390.5 | 366.4 | 352.7 | 349.2 |
| 17.5° | 775.9 | 750.1 | 670.9 | 583.2 | 498.9 | 426.6 | 366.4 | 325.1 | 301.1 | 292.5 | 290.7 |
| 20° | 779.3 | 744.9 | 646.9 | 545.4 | 450.7 | 373.3 | 311.4 | 273.5 | 259.8 | 252.9 | 251.2 |
| 22.5° | 781.0 | 734.6 | 622.8 | 504.1 | 399.1 | 323.4 | 271.8 | 246.0 | 235.7 | 230.5 | 228.8 |
| 25° | 784.5 | 732.9 | 595.2 | 466.2 | 356.1 | 285.6 | 246.0 | 223.6 | 218.5 | 215.0 | 215.0 |
| 27.5° | 798.2 | 732.9 | 571.2 | 418.0 | 311.4 | 254.6 | 223.6 | 209.9 | 206.4 | 204.7 | 204.7 |
| 30° | 815.4 | 736.3 | 548.8 | 378.5 | 277.0 | 230.5 | 208.2 | 197.8 | 196.1 | 194.4 | 194.4 |
| 32.5° | 844.7 | 748.4 | 523.0 | 340.6 | 247.7 | 213.3 | 196.1 | 187.5 | 184.1 | 184.1 | 184.1 |
| 35° | 884.3 | 769.0 | 497.2 | 306.2 | 223.6 | 196.1 | 184.1 | 175.5 | 173.8 | 175.5 | 175.5 |
| 37.5° | 941.0 | 793.1 | 474.8 | 275.3 | 204.7 | 182.4 | 172.0 | 166.9 | 165.2 | 165.2 | 166.9 |
| 40° | 1011.6 | 836.1 | 452.5 | 251.2 | 191.0 | 170.3 | 163.4 | 158.3 | 156.6 | 158.3 | 158.3 |
| 42.5° | 1089.0 | 882.5 | 433.5 | 227.1 | 177.2 | 161.7 | 153.1 | 149.7 | 148.0 | 149.7 | 151.4 |
| 45° | 1175.0 | 930.7 | 418.0 | 209.9 | 166.9 | 153.1 | 146.2 | 144.5 | 142.8 | 142.8 | 144.5 |
| 47.5° | 1247.3 | 982.3 | 406.0 | 197.8 | 158.3 | 146.2 | 141.1 | 137.6 | 135.9 | 134.2 | 135.9 |
| 50° | 1314.4 | 1021.9 | 402.6 | 191.0 | 153.1 | 139.3 | 134.2 | 130.7 | 129.0 | 127.3 | 129.0 |
| 52.5° | 1364.2 | 1042.5 | 402.6 | 185.8 | 148.0 | 134.2 | 129.0 | 125.6 | 123.9 | 120.4 | 122.1 |
| 55° | 1398.6 | 1052.9 | 397.4 | 182.4 | 142.8 | 129.0 | 122.1 | 120.4 | 118.7 | 115.3 | 115.3 |
| 57.5° | 1419.3 | 1051.1 | 378.5 | 180.6 | 141.1 | 122.1 | 117.0 | 115.3 | 113.5 | 110.1 | 110.1 |
| 60° | 1415.9 | 1018.5 | 344.1 | 173.8 | 137.6 | 117.0 | 110.1 | 110.1 | 110.1 | 106.7 | 106.7 |
| 62.5° | 1366.0 | 927.3 | 287.3 | 163.4 | 134.2 | 111.8 | 103.2 | 106.7 | 108.4 | 104.9 | 104.9 |
| 65° | 1231.8 | 787.9 | 237.4 | 149.7 | 125.6 | 106.7 | 98.1 | 103.2 | 106.7 | 104.9 | 103.2 |
| 67.5° | 1037.4 | 624.5 | 196.1 | 135.9 | 117.0 | 99.8 | 91.2 | 98.1 | 99.8 | 99.8 | 99.8 |
| 70° | 801.7 | 449.0 | 161.7 | 118.7 | 104.9 | 89.5 | 82.6 | 86.0 | 87.7 | 87.7 | 89.5 |
| 72.5° | 474.8 | 268.4 | 132.5 | 101.5 | 89.5 | 77.4 | 72.3 | 74.0 | 72.3 | 72.3 | 72.3 |
| 75° | 234.0 | 166.9 | 106.7 | 86.0 | 75.7 | 65.4 | 60.2 | 56.8 | 56.8 | 56.8 | 55.1 |
| 77.5° | 142.8 | 123.9 | 87.7 | 68.8 | 60.2 | 49.9 | 46.4 | 43.0 | 43.0 | 43.0 | 43.0 |
| 80° | 101.5 | 96.3 | 67.1 | 51.6 | 41.3 | 36.1 | 34.4 | 32.7 | 32.7 | 31.0 | 31.0 |
| 82.5° | 63.7 | 72.3 | 49.9 | 34.4 | 27.5 | 25.8 | 24.1 | 22.4 | 20.6 | 18.9 | 18.9 |
| 85° | 36.1 | 46.4 | 29.2 | 18.9 | 15.5 | 12.0 | 10.3 | 10.3 | 8.6 | 8.6 | 6.9 |
| 87.5° | 1.7 | 3.4 | 3.4 | 3.4 | 3.4 | 1.7 | 1.7 | 1.7 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-1-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-727-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.TESTED IN
 SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2741
 CIE u': 0.2605
 CIE v': 0.5272
 Duv: 0.0005
 CIE x: 0.4573
 CIE y: 0.4113
 CIE z: 0.1313
 Peak Wavelength (nm): 602
 Dominant Wavelength (nm): 583
 Purity: 61.2

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 | | |
| R1: | 69.2 | R9: | -16.1 |
| R2: | 79.4 | R10: | 51.4 |
| R3: | 87.8 | R11: | 63.1 |
| R4: | 69.4 | R12: | 42.0 |
| R5: | 66.4 | R13: | 70.2 |
| R6: | 69.8 | R14: | 92.4 |
| R7: | 79.8 | | |
| R8: | 50.1 | | |

Rf: 69.9
 Rg: 98.3



Test Conditions

Stabilization Time: 56M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.3./42%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

Photopic Flux vs. Wavelength



Photopic Lumens: 6211.7

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4


TM-30-18

Summary

$R_f = 69.9$
 $R_g = 98.3$
 CIE $R_a = 71.5$
 $R_9 = -16.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)