

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P438659

Luminaire Tested: **IST-SA1E-727-U-SL4**

Issue Date: 12/10/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P438659  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-074-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 12/10/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: IST-SA1E-727-U-SL4  
Description: IMPACT ELITE LED TRAPEZOID LUMINAIRE  
(1) 70 CRI, 2700K, 1050mA LIGHTSQUARE WITH 16 LEDS AND TYPE IV SPILL  
LIGHT ELIMINATOR OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5771 lumens  
Efficiency: N/A  
Efficacy: 99.2 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B1 - U0 - G2  
  
Input Watts (W): 58.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P438659  
 CATALOG NUMBER: IST-SA1E-727-U-SL4

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1.7 fc  
 Type IV - Short - N/A

REPORT NUMBER: P438659  
CATALOG NUMBER: IST-SA1E-727-U-SL4

### Luminous Intensity Polar Plot



— Vertical Plane Through 36-Deg Lateral      - - - Horizontal Cone Through 75-Deg Vertical

REPORT NUMBER: P438659  
 CATALOG NUMBER: IST-SA1E-727-U-SL4


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 851.7    | 0.0    | 851.7  |
|                    | % Fixture | 14.8     | 0.0    | 14.8   |
| <b>Street Side</b> | Lumens    | 4919.3   | 0.0    | 4919.3 |
|                    | % Fixture | 85.2     | 0.0    | 85.2   |
| <b>Total</b>       | Lumens    | 5771.0   | 0.0    | 5771.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 92.8   | 1.6       |
| 10°-20°   | 240.1  | 4.2       |
| 20°-30°   | 371.3  | 6.4       |
| 30°-40°   | 537.8  | 9.3       |
| 40°-50°   | 777.9  | 13.5      |
| 50°-60°   | 1079.0 | 18.7      |
| 60°-70°   | 1362.4 | 23.6      |
| 70°-80°   | 1170.2 | 20.3      |
| 80°-90°   | 139.4  | 2.4       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 5771.0 | 100.0     |
| 0°-180°   | 5771.0 | 100.0     |

**Coefficient of Utilization**




REPORT NUMBER: P438659  
 CATALOG NUMBER: IST-SA1E-727-U-SL4

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 463.5  | 8.0       |                         |      |         |
| FM (30°-60°)   | 1986.3 | 34.4      |                         |      |         |
| FH (60°-80°)   | 2343.0 | 40.6      |                         |      | G2/5000 |
| FVH (80°-90°)  | 126.5  | 2.2       |                         |      | G2/225  |
| BL (0°-30°)    | 240.9  | 4.2       | B1/500                  |      |         |
| BM (30°-60°)   | 408.4  | 7.1       | B1/1000                 |      |         |
| BH (60°-80°)   | 189.6  | 3.3       | B1/500                  |      | G1/500  |
| BVH (80°-90°)  | 12.9   | 0.2       |                         |      | G1/100  |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B1-U0-G2**  
 Type IV Short





REPORT NUMBER: P438659  
 CATALOG NUMBER: IST-SA1E-727-U-SL4

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 36°    | 45°    | 55°    | 65°    | 75°    | 85°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1052.9 | 1052.9 | 1052.9 | 1052.9 | 1052.9 | 1052.9 | 1052.9 | 1052.9 | 1052.9 | 1052.9 | 1052.9 |
| 2.5°  | 1083.0 | 1083.0 | 1083.0 | 1080.9 | 1076.6 | 1074.4 | 1070.1 | 1065.8 | 1063.7 | 1055.0 | 1052.9 |
| 5°    | 1083.0 | 1085.2 | 1083.0 | 1080.9 | 1076.6 | 1072.3 | 1068.0 | 1059.3 | 1052.9 | 1042.1 | 1031.4 |
| 7.5°  | 1072.3 | 1074.4 | 1074.4 | 1072.3 | 1068.0 | 1065.8 | 1061.5 | 1050.7 | 1042.1 | 1027.1 | 1009.8 |
| 10°   | 1055.0 | 1059.3 | 1059.3 | 1061.5 | 1063.7 | 1063.7 | 1059.3 | 1050.7 | 1037.8 | 1020.6 | 992.6  |
| 12.5° | 1033.5 | 1044.3 | 1050.7 | 1057.2 | 1065.8 | 1065.8 | 1068.0 | 1055.0 | 1044.3 | 1020.6 | 992.6  |
| 15°   | 1027.1 | 1033.5 | 1046.4 | 1065.8 | 1074.4 | 1068.0 | 1076.6 | 1070.1 | 1057.2 | 1033.5 | 999.1  |
| 17.5° | 1024.9 | 1031.4 | 1052.9 | 1076.6 | 1089.5 | 1093.8 | 1093.8 | 1085.2 | 1070.1 | 1046.4 | 1003.4 |
| 20°   | 1033.5 | 1042.1 | 1070.1 | 1100.3 | 1119.6 | 1119.6 | 1117.5 | 1106.7 | 1087.3 | 1059.3 | 1012.0 |
| 22.5° | 1061.5 | 1063.7 | 1096.0 | 1132.6 | 1147.6 | 1143.3 | 1147.6 | 1128.3 | 1106.7 | 1078.7 | 1022.7 |
| 25°   | 1098.1 | 1102.4 | 1128.3 | 1171.3 | 1179.9 | 1182.1 | 1175.6 | 1154.1 | 1130.4 | 1102.4 | 1035.7 |
| 27.5° | 1147.6 | 1154.1 | 1173.5 | 1214.4 | 1220.8 | 1216.5 | 1207.9 | 1182.1 | 1158.4 | 1132.6 | 1061.5 |
| 30°   | 1205.8 | 1210.1 | 1233.8 | 1251.0 | 1257.4 | 1253.1 | 1246.7 | 1218.7 | 1199.3 | 1175.6 | 1100.3 |
| 32.5° | 1261.7 | 1263.9 | 1289.7 | 1307.0 | 1296.2 | 1296.2 | 1287.6 | 1259.6 | 1244.5 | 1240.2 | 1149.8 |
| 35°   | 1319.9 | 1324.2 | 1347.9 | 1356.5 | 1339.3 | 1341.4 | 1339.3 | 1315.6 | 1319.9 | 1328.5 | 1225.1 |
| 37.5° | 1373.7 | 1380.2 | 1408.2 | 1410.3 | 1403.9 | 1397.4 | 1403.9 | 1390.9 | 1399.5 | 1434.0 | 1313.4 |
| 40°   | 1421.1 | 1429.7 | 1464.1 | 1470.6 | 1468.4 | 1468.4 | 1472.8 | 1470.6 | 1502.9 | 1558.9 | 1421.1 |
| 42.5° | 1459.8 | 1470.6 | 1511.5 | 1528.7 | 1541.7 | 1548.1 | 1563.2 | 1567.5 | 1614.9 | 1705.3 | 1546.0 |
| 45°   | 1498.6 | 1509.4 | 1565.3 | 1593.3 | 1623.5 | 1625.6 | 1655.8 | 1670.8 | 1759.1 | 1840.9 | 1681.6 |
| 47.5° | 1543.8 | 1556.7 | 1608.4 | 1664.4 | 1698.8 | 1705.3 | 1761.3 | 1791.4 | 1899.1 | 2004.6 | 1808.6 |
| 50°   | 1606.2 | 1610.6 | 1651.5 | 1746.2 | 1789.3 | 1800.0 | 1862.5 | 1924.9 | 2043.3 | 2148.8 | 1920.6 |
| 52.5° | 1683.8 | 1679.5 | 1698.8 | 1819.4 | 1886.2 | 1901.2 | 2002.4 | 2064.9 | 2207.0 | 2303.9 | 2008.9 |
| 55°   | 1748.4 | 1744.1 | 1772.0 | 1903.4 | 2008.9 | 2013.2 | 2133.8 | 2194.1 | 2357.7 | 2418.0 | 2084.2 |
| 57.5° | 1823.7 | 1815.1 | 1843.1 | 2004.6 | 2148.8 | 2151.0 | 2291.0 | 2359.9 | 2493.3 | 2519.2 | 2133.8 |
| 60°   | 1886.2 | 1886.2 | 1922.8 | 2103.6 | 2303.9 | 2327.6 | 2454.6 | 2508.4 | 2624.7 | 2592.4 | 2157.5 |
| 62.5° | 1944.3 | 1955.1 | 2006.7 | 2235.0 | 2486.9 | 2506.3 | 2635.5 | 2657.0 | 2760.3 | 2648.4 | 2131.6 |
| 65°   | 2013.2 | 2030.4 | 2129.5 | 2392.1 | 2704.4 | 2717.3 | 2824.9 | 2855.1 | 2896.0 | 2646.2 | 2019.7 |
| 67.5° | 2086.4 | 2114.4 | 2245.7 | 2568.7 | 2943.4 | 2977.8 | 3094.1 | 3063.9 | 2986.4 | 2562.2 | 1785.0 |
| 70°   | 2185.4 | 2219.9 | 2407.2 | 2803.4 | 3270.6 | 3313.7 | 3466.6 | 3281.4 | 2939.0 | 2263.0 | 1446.9 |
| 72.5° | 2260.8 | 2306.0 | 2562.2 | 3107.0 | 3714.2 | 3780.9 | 3744.3 | 3285.7 | 2635.5 | 1804.3 | 968.9  |
| 75°   | 1983.1 | 2052.0 | 2439.5 | 3156.5 | 3903.7 | 3933.8 | 3541.9 | 2777.6 | 1866.8 | 932.3  | 417.7  |
| 77.5° | 1449.1 | 1444.8 | 1782.8 | 2452.4 | 3199.6 | 3119.9 | 2687.1 | 1806.5 | 887.1  | 338.0  | 211.0  |
| 80°   | 727.8  | 699.8  | 964.6  | 1307.0 | 1726.8 | 1780.7 | 1589.0 | 938.8  | 351.0  | 180.9  | 127.0  |
| 82.5° | 269.1  | 275.6  | 353.1  | 534.0  | 867.7  | 880.6  | 641.6  | 398.3  | 191.6  | 94.7   | 66.7   |
| 85°   | 103.4  | 107.7  | 116.3  | 116.3  | 161.5  | 178.7  | 165.8  | 159.3  | 64.6   | 32.3   | 36.6   |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 2.2    | 2.2    | 2.2    | 2.2    | 2.2    | 2.2    | 2.2    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P438659  
 CATALOG NUMBER: IST-SA1E-727-U-SL4

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1052.9 | 1052.9 | 1052.9 | 1052.9 | 1052.9 | 1052.9 | 1052.9 | 1052.9 | 1052.9 | 1052.9 | 1052.9 |
| 2.5°  | 1046.4 | 1042.1 | 1033.5 | 1018.4 | 1009.8 | 1003.4 | 994.8  | 986.1  | 984.0  | 981.8  | 992.6  |
| 5°    | 1020.6 | 1014.1 | 992.6  | 973.2  | 951.7  | 934.5  | 917.2  | 902.2  | 893.6  | 891.4  | 895.7  |
| 7.5°  | 994.8  | 986.1  | 953.8  | 915.1  | 878.5  | 848.3  | 818.2  | 803.1  | 779.4  | 779.4  | 781.6  |
| 10°   | 979.7  | 964.6  | 919.4  | 861.3  | 813.9  | 760.1  | 723.5  | 686.9  | 671.8  | 661.0  | 656.7  |
| 12.5° | 971.1  | 947.4  | 887.1  | 822.5  | 749.3  | 678.2  | 628.7  | 583.5  | 559.8  | 542.6  | 542.6  |
| 15°   | 973.2  | 947.4  | 865.6  | 781.6  | 686.9  | 600.7  | 538.3  | 488.8  | 458.6  | 441.4  | 437.1  |
| 17.5° | 971.1  | 938.8  | 839.7  | 729.9  | 624.4  | 534.0  | 458.6  | 406.9  | 376.8  | 366.0  | 363.9  |
| 20°   | 975.4  | 932.3  | 809.6  | 682.5  | 564.1  | 467.2  | 389.7  | 342.4  | 325.1  | 316.5  | 314.4  |
| 22.5° | 977.5  | 919.4  | 779.4  | 630.9  | 499.5  | 404.8  | 340.2  | 307.9  | 295.0  | 288.5  | 286.4  |
| 25°   | 981.8  | 917.2  | 745.0  | 583.5  | 445.7  | 357.4  | 307.9  | 279.9  | 273.4  | 269.1  | 269.1  |
| 27.5° | 999.1  | 917.2  | 714.8  | 523.2  | 389.7  | 318.7  | 279.9  | 262.7  | 258.4  | 256.2  | 256.2  |
| 30°   | 1020.6 | 921.5  | 686.9  | 473.7  | 346.7  | 288.5  | 260.5  | 247.6  | 245.5  | 243.3  | 243.3  |
| 32.5° | 1057.2 | 936.6  | 654.6  | 426.3  | 310.1  | 267.0  | 245.5  | 234.7  | 230.4  | 230.4  | 230.4  |
| 35°   | 1106.7 | 962.5  | 622.3  | 383.3  | 279.9  | 245.5  | 230.4  | 219.6  | 217.5  | 219.6  | 219.6  |
| 37.5° | 1177.8 | 992.6  | 594.3  | 344.5  | 256.2  | 228.2  | 215.3  | 208.9  | 206.7  | 206.7  | 208.9  |
| 40°   | 1266.1 | 1046.4 | 566.3  | 314.4  | 239.0  | 213.2  | 204.5  | 198.1  | 195.9  | 198.1  | 198.1  |
| 42.5° | 1362.9 | 1104.6 | 542.6  | 284.2  | 221.8  | 202.4  | 191.6  | 187.3  | 185.2  | 187.3  | 189.5  |
| 45°   | 1470.6 | 1164.9 | 523.2  | 262.7  | 208.9  | 191.6  | 183.0  | 180.9  | 178.7  | 178.7  | 180.9  |
| 47.5° | 1561.0 | 1229.4 | 508.1  | 247.6  | 198.1  | 183.0  | 176.6  | 172.3  | 170.1  | 167.9  | 170.1  |
| 50°   | 1645.0 | 1279.0 | 503.8  | 239.0  | 191.6  | 174.4  | 167.9  | 163.6  | 161.5  | 159.3  | 161.5  |
| 52.5° | 1707.4 | 1304.8 | 503.8  | 232.5  | 185.2  | 167.9  | 161.5  | 157.2  | 155.0  | 150.7  | 152.9  |
| 55°   | 1750.5 | 1317.7 | 497.4  | 228.2  | 178.7  | 161.5  | 152.9  | 150.7  | 148.6  | 144.3  | 144.3  |
| 57.5° | 1776.3 | 1315.6 | 473.7  | 226.1  | 176.6  | 152.9  | 146.4  | 144.3  | 142.1  | 137.8  | 137.8  |
| 60°   | 1772.0 | 1274.7 | 430.6  | 217.5  | 172.3  | 146.4  | 137.8  | 137.8  | 137.8  | 133.5  | 133.5  |
| 62.5° | 1709.6 | 1160.5 | 359.6  | 204.5  | 167.9  | 140.0  | 129.2  | 133.5  | 135.6  | 131.3  | 131.3  |
| 65°   | 1541.7 | 986.1  | 297.1  | 187.3  | 157.2  | 133.5  | 122.7  | 129.2  | 133.5  | 131.3  | 129.2  |
| 67.5° | 1298.3 | 781.6  | 245.5  | 170.1  | 146.4  | 124.9  | 114.1  | 122.7  | 124.9  | 124.9  | 124.9  |
| 70°   | 1003.4 | 562.0  | 202.4  | 148.6  | 131.3  | 112.0  | 103.4  | 107.7  | 109.8  | 109.8  | 112.0  |
| 72.5° | 594.3  | 335.9  | 165.8  | 127.0  | 112.0  | 96.9   | 90.4   | 92.6   | 90.4   | 90.4   | 90.4   |
| 75°   | 292.8  | 208.9  | 133.5  | 107.7  | 94.7   | 81.8   | 75.4   | 71.1   | 71.1   | 71.1   | 68.9   |
| 77.5° | 178.7  | 155.0  | 109.8  | 86.1   | 75.4   | 62.4   | 58.1   | 53.8   | 53.8   | 53.8   | 53.8   |
| 80°   | 127.0  | 120.6  | 84.0   | 64.6   | 51.7   | 45.2   | 43.1   | 40.9   | 40.9   | 38.8   | 38.8   |
| 82.5° | 79.7   | 90.4   | 62.4   | 43.1   | 34.5   | 32.3   | 30.1   | 28.0   | 25.8   | 23.7   | 23.7   |
| 85°   | 45.2   | 58.1   | 36.6   | 23.7   | 19.4   | 15.1   | 12.9   | 12.9   | 10.8   | 10.8   | 8.6    |
| 87.5° | 2.2    | 4.3    | 4.3    | 4.3    | 4.3    | 2.2    | 2.2    | 2.2    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

---

**Test Information**

Test Method: LM-79-2008  
 Report Number: SP1-1908-441-1-R4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/28/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGRAW-EDISON  
 Catalog Number: **SA1C-727-U-5WQ**  
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

\*\*\*THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.\*\*\*TESTED IN  
 SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

**Spectral Parameters**

CCT (K): 2741  
 CIE u': 0.2605  
 CIE v': 0.5272  
 Duv: 0.0005  
 CIE x: 0.4573  
 CIE y: 0.4113  
 CIE z: 0.1313  
 Peak Wavelength (nm): 602  
 Dominant Wavelength (nm): 583  
 Purity: 61.2

|           |      |      |       |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 |      |       |
| R1:       | 69.2 | R9:  | -16.1 |
| R2:       | 79.4 | R10: | 51.4  |
| R3:       | 87.8 | R11: | 63.1  |
| R4:       | 69.4 | R12: | 42.0  |
| R5:       | 66.4 | R13: | 70.2  |
| R6:       | 69.8 | R14: | 92.4  |
| R7:       | 79.8 |      |       |
| R8:       | 50.1 |      |       |

Rf: 69.9  
 Rg: 98.3



**Test Conditions**

Stabilization Time: 56M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.3./42%  
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/28/2019        | 12/28/2019           |
| Power Meter                    | IN0071                | 12/5/2018        | 12/5/2019            |
| AC Power Source                | IN0063                | 12/5/2018        | 12/5/2019            |
| DC Power Source                | IN0208                | 12/5/2018        | 12/5/2019            |
| Sphere Thermometer             | IN0085                | 12/5/2018        | 12/5/2019            |
| Room Thermometer               | IN0046                | 12/5/2018        | 12/5/2019            |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

**Photopic Flux vs. Wavelength**



**Photopic Lumens: 6211.7**

| $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360            | 2044                              | 0.0                         | 490            | 7179                              | 1.0                         | 620            | 118034                            | 30.7                        | 750            | 8362                              | 0.0                         | 880            | 3128                              | 0.0                         |
| 365            | 2016                              | 0.0                         | 495            | 10476                             | 1.9                         | 625            | 111884                            | 24.7                        | 755            | 7635                              | 0.0                         | 885            | 3110                              | 0.0                         |
| 370            | 2020                              | 0.0                         | 500            | 15549                             | 3.4                         | 630            | 106119                            | 19.2                        | 760            | 6582                              | 0.0                         | 890            | 2632                              | 0.0                         |
| 375            | 2137                              | 0.0                         | 505            | 22477                             | 6.3                         | 635            | 99706                             | 15.0                        | 765            | 5777                              | 0.0                         | 895            | 2709                              | 0.0                         |
| 380            | 2046                              | 0.0                         | 510            | 30417                             | 10.4                        | 640            | 92142                             | 11.0                        | 770            | 5474                              | 0.0                         | 900            | 2016                              | 0.0                         |
| 385            | 1925                              | 0.0                         | 515            | 39274                             | 16.3                        | 645            | 84987                             | 8.2                         | 775            | 4977                              | 0.0                         | 905            | 1748                              | 0.0                         |
| 390            | 1893                              | 0.0                         | 520            | 47282                             | 22.9                        | 650            | 78016                             | 5.7                         | 780            | 4723                              | 0.0                         | 910            | 2046                              | 0.0                         |
| 395            | 1695                              | 0.0                         | 525            | 55413                             | 29.7                        | 655            | 71541                             | 4.1                         | 785            | 4219                              | 0.0                         | 915            | 1844                              | 0.0                         |
| 400            | 1633                              | 0.0                         | 530            | 62377                             | 36.7                        | 660            | 64863                             | 2.7                         | 790            | 3969                              | 0.0                         | 920            | 2734                              | 0.0                         |
| 405            | 2065                              | 0.0                         | 535            | 68520                             | 42.5                        | 665            | 58485                             | 1.9                         | 795            | 4122                              | 0.0                         | 925            | 2307                              | 0.0                         |
| 410            | 3449                              | 0.0                         | 540            | 73435                             | 47.8                        | 670            | 51641                             | 1.1                         | 800            | 2864                              | 0.0                         | 930            | 2039                              | 0.0                         |
| 415            | 7117                              | 0.0                         | 545            | 78677                             | 52.4                        | 675            | 46030                             | 0.8                         | 805            | 3151                              | 0.0                         | 935            | 1784                              | 0.0                         |
| 420            | 13992                             | 0.0                         | 550            | 83331                             | 56.6                        | 680            | 40590                             | 0.5                         | 810            | 3022                              | 0.0                         | 940            | 2464                              | 0.0                         |
| 425            | 25176                             | 0.1                         | 555            | 89120                             | 60.9                        | 685            | 35691                             | 0.3                         | 815            | 3471                              | 0.0                         | 945            | 2794                              | 0.0                         |
| 430            | 38151                             | 0.3                         | 560            | 94613                             | 64.3                        | 690            | 31631                             | 0.2                         | 820            | 2749                              | 0.0                         | 950            | 3090                              | 0.0                         |
| 435            | 49673                             | 0.6                         | 565            | 99818                             | 66.4                        | 695            | 27437                             | 0.1                         | 825            | 2729                              | 0.0                         | 955            | 1866                              | 0.0                         |
| 440            | 57273                             | 0.9                         | 570            | 106526                            | 69.3                        | 700            | 24589                             | 0.1                         | 830            | 2282                              | 0.0                         | 960            | 3110                              | 0.0                         |
| 445            | 54802                             | 1.1                         | 575            | 111610                            | 69.4                        | 705            | 21832                             | 0.0                         | 835            | 3140                              | 0.0                         | 965            | 3880                              | 0.0                         |
| 450            | 39184                             | 1.0                         | 580            | 117163                            | 69.6                        | 710            | 19500                             | 0.0                         | 840            | 2365                              | 0.0                         | 970            | 3243                              | 0.0                         |
| 455            | 22506                             | 0.8                         | 585            | 122201                            | 67.9                        | 715            | 17870                             | 0.0                         | 845            | 3024                              | 0.0                         | 975            | 2014                              | 0.0                         |
| 460            | 13692                             | 0.6                         | 590            | 125662                            | 65.0                        | 720            | 15924                             | 0.0                         | 850            | 2510                              | 0.0                         | 980            | 1688                              | 0.0                         |
| 465            | 9446                              | 0.5                         | 595            | 127415                            | 60.4                        | 725            | 14268                             | 0.0                         | 855            | 2739                              | 0.0                         | 985            | 2827                              | 0.0                         |
| 470            | 6698                              | 0.4                         | 600            | 129155                            | 55.7                        | 730            | 12438                             | 0.0                         | 860            | 3515                              | 0.0                         | 990            | 4172                              | 0.0                         |
| 475            | 5328                              | 0.4                         | 605            | 128057                            | 49.6                        | 735            | 11255                             | 0.0                         | 865            | 3600                              | 0.0                         | 995            | 3177                              | 0.0                         |
| 480            | 5081                              | 0.5                         | 610            | 126031                            | 43.3                        | 740            | 9951                              | 0.0                         | 870            | 3609                              | 0.0                         | 1000           | 3241                              | 0.0                         |
| 485            | 5579                              | 0.7                         | 615            | 123059                            | 37.1                        | 745            | 8870                              | 0.0                         | 875            | 3208                              | 0.0                         |                |                                   |                             |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2044          | 0.0           | 490    | 7179          | 6.0           | 620    | 118034        | 0.1           | 750    | 8362          | 0.0           | 880    | 3128          | 0.0           |
| 365    | 2016          | 0.0           | 495    | 10476         | 8.6           | 625    | 111884        | 0.1           | 755    | 7635          | 0.0           | 885    | 3110          | 0.0           |
| 370    | 2020          | 0.0           | 500    | 15549         | 12.5          | 630    | 106119        | 0.0           | 760    | 6582          | 0.0           | 890    | 2632          | 0.0           |
| 375    | 2137          | 0.0           | 505    | 22477         | 17.3          | 635    | 99706         | 0.0           | 765    | 5777          | 0.0           | 895    | 2709          | 0.0           |
| 380    | 2046          | 0.0           | 510    | 30417         | 21.8          | 640    | 92142         | 0.0           | 770    | 5474          | 0.0           | 900    | 2016          | 0.0           |
| 385    | 1925          | 0.0           | 515    | 39274         | 25.7          | 645    | 84987         | 0.0           | 775    | 4977          | 0.0           | 905    | 1748          | 0.0           |
| 390    | 1893          | 0.0           | 520    | 47282         | 27.5          | 650    | 78016         | 0.0           | 780    | 4723          | 0.0           | 910    | 2046          | 0.0           |
| 395    | 1695          | 0.0           | 525    | 55413         | 28.1          | 655    | 71541         | 0.0           | 785    | 4219          | 0.0           | 915    | 1844          | 0.0           |
| 400    | 1633          | 0.0           | 530    | 62377         | 27.0          | 660    | 64863         | 0.0           | 790    | 3969          | 0.0           | 920    | 2734          | 0.0           |
| 405    | 2065          | 0.0           | 535    | 68520         | 24.7          | 665    | 58485         | 0.0           | 795    | 4122          | 0.0           | 925    | 2307          | 0.0           |
| 410    | 3449          | 0.1           | 540    | 73435         | 21.5          | 670    | 51641         | 0.0           | 800    | 2864          | 0.0           | 930    | 2039          | 0.0           |
| 415    | 7117          | 0.5           | 545    | 78677         | 18.3          | 675    | 46030         | 0.0           | 805    | 3151          | 0.0           | 935    | 1784          | 0.0           |
| 420    | 13992         | 1.6           | 550    | 83331         | 15.0          | 680    | 40590         | 0.0           | 810    | 3022          | 0.0           | 940    | 2464          | 0.0           |
| 425    | 25176         | 3.9           | 555    | 89120         | 12.0          | 685    | 35691         | 0.0           | 815    | 3471          | 0.0           | 945    | 2794          | 0.0           |
| 430    | 38151         | 8.1           | 560    | 94613         | 9.3           | 690    | 31631         | 0.0           | 820    | 2749          | 0.0           | 950    | 3090          | 0.0           |
| 435    | 49673         | 13.3          | 565    | 99818         | 7.0           | 695    | 27437         | 0.0           | 825    | 2729          | 0.0           | 955    | 1866          | 0.0           |
| 440    | 57273         | 19.1          | 570    | 106526        | 5.2           | 700    | 24589         | 0.0           | 830    | 2282          | 0.0           | 960    | 3110          | 0.0           |
| 445    | 54802         | 21.6          | 575    | 111610        | 3.7           | 705    | 21832         | 0.0           | 835    | 3140          | 0.0           | 965    | 3880          | 0.0           |
| 450    | 39184         | 18.1          | 580    | 117163        | 2.6           | 710    | 19500         | 0.0           | 840    | 2365          | 0.0           | 970    | 3243          | 0.0           |
| 455    | 22506         | 11.8          | 585    | 122201        | 1.8           | 715    | 17870         | 0.0           | 845    | 3024          | 0.0           | 975    | 2014          | 0.0           |
| 460    | 13692         | 8.1           | 590    | 125662        | 1.2           | 720    | 15924         | 0.0           | 850    | 2510          | 0.0           | 980    | 1688          | 0.0           |
| 465    | 9446          | 6.2           | 595    | 127415        | 0.8           | 725    | 14268         | 0.0           | 855    | 2739          | 0.0           | 985    | 2827          | 0.0           |
| 470    | 6698          | 4.8           | 600    | 129155        | 0.5           | 730    | 12438         | 0.0           | 860    | 3515          | 0.0           | 990    | 4172          | 0.0           |
| 475    | 5328          | 4.1           | 605    | 128057        | 0.4           | 735    | 11255         | 0.0           | 865    | 3600          | 0.0           | 995    | 3177          | 0.0           |
| 480    | 5081          | 4.1           | 610    | 126031        | 0.2           | 740    | 9951          | 0.0           | 870    | 3609          | 0.0           | 1000   | 3241          | 0.0           |
| 485    | 5579          | 4.6           | 615    | 123059        | 0.1           | 745    | 8870          | 0.0           | 875    | 3208          | 0.0           |        |               |               |

REPORT NUMBER: SP1-1908-441-1-R4

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 2145.7 M/P: 0.35**

| $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360            | 2044                              | 0.0                         | 490            | 7179                              | 11.1                        | 620            | 118034                            | 1.5                         | 750            | 8362                              | 0.0                         | 880            | 3128                              | 0.0                         |
| 365            | 2016                              | 0.0                         | 495            | 10476                             | 16.9                        | 625            | 111884                            | 0.9                         | 755            | 7635                              | 0.0                         | 885            | 3110                              | 0.0                         |
| 370            | 2020                              | 0.0                         | 500            | 15549                             | 26.0                        | 630            | 106119                            | 0.6                         | 760            | 6582                              | 0.0                         | 890            | 2632                              | 0.0                         |
| 375            | 2137                              | 0.0                         | 505            | 22477                             | 38.2                        | 635            | 99706                             | 0.4                         | 765            | 5777                              | 0.0                         | 895            | 2709                              | 0.0                         |
| 380            | 2046                              | 0.0                         | 510            | 30417                             | 51.6                        | 640            | 92142                             | 0.2                         | 770            | 5474                              | 0.0                         | 900            | 2016                              | 0.0                         |
| 385            | 1925                              | 0.0                         | 515            | 39274                             | 65.1                        | 645            | 84987                             | 0.1                         | 775            | 4977                              | 0.0                         | 905            | 1748                              | 0.0                         |
| 390            | 1893                              | 0.0                         | 520            | 47282                             | 75.2                        | 650            | 78016                             | 0.1                         | 780            | 4723                              | 0.0                         | 910            | 2046                              | 0.0                         |
| 395            | 1695                              | 0.0                         | 525            | 55413                             | 82.9                        | 655            | 71541                             | 0.1                         | 785            | 4219                              | 0.0                         | 915            | 1844                              | 0.0                         |
| 400            | 1633                              | 0.0                         | 530            | 62377                             | 86.0                        | 660            | 64863                             | 0.0                         | 790            | 3969                              | 0.0                         | 920            | 2734                              | 0.0                         |
| 405            | 2065                              | 0.1                         | 535            | 68520                             | 85.4                        | 665            | 58485                             | 0.0                         | 795            | 4122                              | 0.0                         | 925            | 2307                              | 0.0                         |
| 410            | 3449                              | 0.2                         | 540            | 73435                             | 81.1                        | 670            | 51641                             | 0.0                         | 800            | 2864                              | 0.0                         | 930            | 2039                              | 0.0                         |
| 415            | 7117                              | 0.7                         | 545            | 78677                             | 75.4                        | 675            | 46030                             | 0.0                         | 805            | 3151                              | 0.0                         | 935            | 1784                              | 0.0                         |
| 420            | 13992                             | 2.3                         | 550            | 83331                             | 68.1                        | 680            | 40590                             | 0.0                         | 810            | 3022                              | 0.0                         | 940            | 2464                              | 0.0                         |
| 425            | 25176                             | 6.2                         | 555            | 89120                             | 60.9                        | 685            | 35691                             | 0.0                         | 815            | 3471                              | 0.0                         | 945            | 2794                              | 0.0                         |
| 430            | 38151                             | 13.0                        | 560            | 94613                             | 52.9                        | 690            | 31631                             | 0.0                         | 820            | 2749                              | 0.0                         | 950            | 3090                              | 0.0                         |
| 435            | 49673                             | 22.2                        | 565            | 99818                             | 44.8                        | 695            | 27437                             | 0.0                         | 825            | 2729                              | 0.0                         | 955            | 1866                              | 0.0                         |
| 440            | 57273                             | 32.0                        | 570            | 106526                            | 37.6                        | 700            | 24589                             | 0.0                         | 830            | 2282                              | 0.0                         | 960            | 3110                              | 0.0                         |
| 445            | 54802                             | 36.7                        | 575            | 111610                            | 30.4                        | 705            | 21832                             | 0.0                         | 835            | 3140                              | 0.0                         | 965            | 3880                              | 0.0                         |
| 450            | 39184                             | 30.4                        | 580            | 117163                            | 24.1                        | 710            | 19500                             | 0.0                         | 840            | 2365                              | 0.0                         | 970            | 3243                              | 0.0                         |
| 455            | 22506                             | 19.7                        | 585            | 122201                            | 18.7                        | 715            | 17870                             | 0.0                         | 845            | 3024                              | 0.0                         | 975            | 2014                              | 0.0                         |
| 460            | 13692                             | 13.2                        | 590            | 125662                            | 14.0                        | 720            | 15924                             | 0.0                         | 850            | 2510                              | 0.0                         | 980            | 1688                              | 0.0                         |
| 465            | 9446                              | 10.0                        | 595            | 127415                            | 10.2                        | 725            | 14268                             | 0.0                         | 855            | 2739                              | 0.0                         | 985            | 2827                              | 0.0                         |
| 470            | 6698                              | 7.7                         | 600            | 129155                            | 7.3                         | 730            | 12438                             | 0.0                         | 860            | 3515                              | 0.0                         | 990            | 4172                              | 0.0                         |
| 475            | 5328                              | 6.7                         | 605            | 128057                            | 5.0                         | 735            | 11255                             | 0.0                         | 865            | 3600                              | 0.0                         | 995            | 3177                              | 0.0                         |
| 480            | 5081                              | 6.9                         | 610            | 126031                            | 3.4                         | 740            | 9951                              | 0.0                         | 870            | 3609                              | 0.0                         | 1000           | 3241                              | 0.0                         |
| 485            | 5579                              | 8.1                         | 615            | 123059                            | 2.3                         | 745            | 8870                              | 0.0                         | 875            | 3208                              | 0.0                         |                |                                   |                             |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

**Summary**

$R_f = 69.9$   
 $R_g = 98.3$   
 $CIE R_a = 71.5$   
 $R_9 = -16.1$



**Color Vector Graphics**





REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 |            |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)