

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P438814

Luminaire Tested: **ISW-SA1F-722-U-SLR-HSS**

Issue Date: 12/10/2020

Test Information

Test Method: LM-79-08
Report Number: P438814
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-074-23)
Test Lab: INNOVATION CENTER
Issue Date: 12/10/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: ISW-SA1F-722-U-SLR-HSS
Description: IMPACT ELITE LED WEDGE LUMINAIRE
(1) 70 CRI, 2200K, 1200mA LIGHTSQUARE WITH 16 LEDS AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4294 lumens
Efficiency: N/A
Efficacy: 65.1 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G1


Input Watts (W): 66
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P438814
 CATALOG NUMBER: ISW-SA1F-722-U-SLR-HSS

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 2.3 fc
 Type IV - Short - N/A

REPORT NUMBER: P438814
CATALOG NUMBER: ISW-SA1F-722-U-SLR-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 345-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P438814

CATALOG NUMBER: ISW-SA1F-722-U-SLR-HSS


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 462.9 | 0.0 | 462.9 |
| | % Fixture | 10.8 | 0.0 | 10.8 |
| Street Side | Lumens | 3831.1 | 0.0 | 3831.1 |
| | % Fixture | 89.2 | 0.0 | 89.2 |
| Total | Lumens | 4294.0 | 0.0 | 4294.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 107.6 | 2.5 |
| 10°-20° | 209.4 | 4.9 |
| 20°-30° | 305.4 | 7.1 |
| 30°-40° | 453.9 | 10.6 |
| 40°-50° | 665.4 | 15.5 |
| 50°-60° | 957.5 | 22.3 |
| 60°-70° | 1074.1 | 25.0 |
| 70°-80° | 471.3 | 11.0 |
| 80°-90° | 49.6 | 1.2 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 4294.0 | 100.0 |
| 0°-180° | 4294.0 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P438814


CATALOG NUMBER: ISW-SA1F-722-U-SLR-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 472.1 | 11.0 | | | |
| FM (30°-60°) | 1866.0 | 43.5 | | | |
| FH (60°-80°) | 1448.1 | 33.7 | | | G1/1800 |
| FVH (80°-90°) | 44.8 | 1.0 | | | G1/100 |
| BL (0°-30°) | 150.2 | 3.5 | B1/500 | | |
| BM (30°-60°) | 210.7 | 4.9 | B0/220 | | |
| BH (60°-80°) | 97.3 | 2.3 | B0/110 | | G0/110 |
| BVH (80°-90°) | 4.8 | 0.1 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G1

Type IV Short





REPORT NUMBER: P438814
 CATALOG NUMBER: ISW-SA1F-722-U-SLR-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 1° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1449.1 | 1449.1 | 1449.1 | 1449.1 | 1449.1 | 1449.1 | 1449.1 | 1449.1 | 1449.1 | 1449.1 | 1449.1 |
| 2.5° | 1533.6 | 1533.6 | 1510.9 | 1457.4 | 1407.9 | 1348.1 | 1315.1 | 1284.2 | 1251.2 | 1228.5 | 1193.5 |
| 5° | 1461.5 | 1447.0 | 1414.1 | 1315.1 | 1210.0 | 1139.9 | 1086.3 | 991.5 | 946.1 | 913.2 | 898.7 |
| 7.5° | 1341.9 | 1333.7 | 1280.1 | 1164.6 | 1038.9 | 925.5 | 853.4 | 775.1 | 713.2 | 688.5 | 645.2 |
| 10° | 1259.5 | 1251.2 | 1183.2 | 1026.5 | 880.2 | 797.7 | 740.0 | 684.4 | 624.6 | 564.8 | 519.5 |
| 12.5° | 1218.2 | 1201.8 | 1135.8 | 958.5 | 832.8 | 752.4 | 686.4 | 618.4 | 544.2 | 478.2 | 424.6 |
| 15° | 1228.5 | 1201.8 | 1127.5 | 946.1 | 797.7 | 698.8 | 614.3 | 515.3 | 441.1 | 362.8 | 313.3 |
| 17.5° | 1300.7 | 1271.8 | 1181.1 | 956.5 | 752.4 | 626.6 | 515.3 | 404.0 | 305.1 | 232.9 | 208.2 |
| 20° | 1434.7 | 1403.8 | 1280.1 | 979.1 | 723.5 | 554.5 | 397.8 | 278.3 | 202.0 | 169.0 | 154.6 |
| 22.5° | 1605.8 | 1564.5 | 1418.2 | 1016.2 | 690.5 | 482.3 | 301.0 | 197.9 | 154.6 | 134.0 | 123.7 |
| 25° | 1785.1 | 1743.9 | 1581.0 | 1071.9 | 669.9 | 420.5 | 232.9 | 154.6 | 125.7 | 113.4 | 107.2 |
| 27.5° | 1947.9 | 1896.4 | 1727.4 | 1154.3 | 645.2 | 364.9 | 193.8 | 134.0 | 113.4 | 98.9 | 94.8 |
| 30° | 2096.4 | 2036.6 | 1873.7 | 1224.4 | 610.2 | 315.4 | 167.0 | 123.7 | 105.1 | 92.8 | 86.6 |
| 32.5° | 2222.1 | 2174.7 | 1993.3 | 1273.9 | 581.3 | 288.6 | 148.4 | 109.3 | 90.7 | 80.4 | 76.3 |
| 35° | 2372.6 | 2327.2 | 2108.7 | 1315.1 | 562.7 | 276.2 | 136.0 | 103.1 | 84.5 | 74.2 | 66.0 |
| 37.5° | 2576.7 | 2510.7 | 2236.5 | 1352.2 | 542.1 | 265.9 | 125.7 | 96.9 | 80.4 | 68.0 | 61.8 |
| 40° | 2760.1 | 2688.0 | 2384.9 | 1379.0 | 531.8 | 257.7 | 123.7 | 92.8 | 76.3 | 63.9 | 57.7 |
| 42.5° | 2923.0 | 2857.0 | 2504.5 | 1389.3 | 523.6 | 243.2 | 121.6 | 90.7 | 76.3 | 61.8 | 53.6 |
| 45° | 3026.0 | 2966.2 | 2646.7 | 1416.1 | 523.6 | 232.9 | 113.4 | 90.7 | 74.2 | 59.8 | 51.5 |
| 47.5° | 3120.8 | 3063.1 | 2770.4 | 1445.0 | 515.3 | 224.7 | 103.1 | 98.9 | 74.2 | 57.7 | 47.4 |
| 50° | 3259.0 | 3213.6 | 2927.1 | 1531.6 | 500.9 | 212.3 | 92.8 | 96.9 | 76.3 | 55.7 | 47.4 |
| 52.5° | 3434.2 | 3413.5 | 3157.9 | 1649.1 | 480.3 | 189.6 | 82.5 | 90.7 | 76.3 | 53.6 | 45.3 |
| 55° | 3627.9 | 3619.7 | 3399.1 | 1756.2 | 455.6 | 162.8 | 76.3 | 82.5 | 74.2 | 49.5 | 41.2 |
| 57.5° | 3745.4 | 3745.4 | 3555.8 | 1816.0 | 434.9 | 129.9 | 68.0 | 68.0 | 72.1 | 45.3 | 37.1 |
| 60° | 3788.7 | 3743.4 | 3537.2 | 1809.8 | 399.9 | 107.2 | 61.8 | 55.7 | 76.3 | 39.2 | 33.0 |
| 62.5° | 3784.6 | 3685.6 | 3364.1 | 1710.9 | 352.5 | 98.9 | 53.6 | 47.4 | 55.7 | 35.0 | 28.9 |
| 65° | 3673.3 | 3553.7 | 3100.2 | 1490.3 | 317.4 | 98.9 | 45.3 | 39.2 | 37.1 | 30.9 | 22.7 |
| 67.5° | 3366.1 | 3294.0 | 2714.8 | 1263.6 | 292.7 | 98.9 | 39.2 | 33.0 | 28.9 | 24.7 | 20.6 |
| 70° | 2859.1 | 2764.2 | 2187.1 | 975.0 | 274.2 | 98.9 | 33.0 | 28.9 | 26.8 | 20.6 | 16.5 |
| 72.5° | 1863.4 | 1809.8 | 1337.8 | 669.9 | 224.7 | 96.9 | 28.9 | 26.8 | 24.7 | 18.6 | 14.4 |
| 75° | 1014.2 | 937.9 | 735.9 | 239.1 | 160.8 | 70.1 | 24.7 | 22.7 | 18.6 | 16.5 | 12.4 |
| 77.5° | 439.1 | 422.6 | 375.2 | 63.9 | 47.4 | 20.6 | 14.4 | 14.4 | 12.4 | 12.4 | 8.2 |
| 80° | 57.7 | 43.3 | 49.5 | 18.6 | 16.5 | 10.3 | 8.2 | 6.2 | 6.2 | 6.2 | 4.1 |
| 82.5° | 2.1 | 2.1 | 0.0 | 2.1 | 6.2 | 4.1 | 0.0 | 0.0 | 2.1 | 2.1 | 2.1 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P438814
 CATALOG NUMBER: ISW-SA1F-722-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1449.1 | 1449.1 | 1449.1 | 1449.1 | 1449.1 | 1449.1 | 1449.1 | 1449.1 | 1449.1 | 1449.1 | 1449.1 |
| 2.5° | 1210.0 | 1185.3 | 1166.7 | 1166.7 | 1191.4 | 1177.0 | 1193.5 | 1183.2 | 1212.1 | 1226.5 | 1222.4 |
| 5° | 867.8 | 878.1 | 867.8 | 884.3 | 911.1 | 925.5 | 933.8 | 954.4 | 952.3 | 960.6 | 975.0 |
| 7.5° | 628.7 | 628.7 | 632.8 | 628.7 | 653.4 | 680.2 | 694.7 | 688.5 | 684.4 | 676.1 | 690.5 |
| 10° | 505.0 | 482.3 | 455.6 | 455.6 | 459.7 | 474.1 | 476.2 | 465.9 | 451.4 | 424.6 | 432.9 |
| 12.5° | 395.8 | 379.3 | 362.8 | 327.8 | 325.7 | 317.4 | 315.4 | 286.5 | 263.8 | 255.6 | 255.6 |
| 15° | 290.6 | 280.3 | 261.8 | 245.3 | 228.8 | 220.6 | 206.1 | 171.1 | 148.4 | 146.4 | 148.4 |
| 17.5° | 193.8 | 187.6 | 181.4 | 181.4 | 175.2 | 160.8 | 146.4 | 123.7 | 113.4 | 109.3 | 111.3 |
| 20° | 144.3 | 142.2 | 136.0 | 138.1 | 138.1 | 125.7 | 111.3 | 101.0 | 96.9 | 96.9 | 98.9 |
| 22.5° | 119.6 | 117.5 | 111.3 | 111.3 | 111.3 | 105.1 | 94.8 | 88.6 | 86.6 | 86.6 | 86.6 |
| 25° | 103.1 | 101.0 | 96.9 | 94.8 | 94.8 | 90.7 | 82.5 | 78.3 | 76.3 | 76.3 | 76.3 |
| 27.5° | 92.8 | 90.7 | 86.6 | 82.5 | 82.5 | 78.3 | 74.2 | 68.0 | 68.0 | 68.0 | 68.0 |
| 30° | 82.5 | 80.4 | 78.3 | 74.2 | 72.1 | 68.0 | 63.9 | 61.8 | 59.8 | 59.8 | 59.8 |
| 32.5° | 74.2 | 72.1 | 70.1 | 68.0 | 63.9 | 59.8 | 55.7 | 53.6 | 51.5 | 51.5 | 51.5 |
| 35° | 63.9 | 59.8 | 57.7 | 59.8 | 57.7 | 51.5 | 49.5 | 45.3 | 43.3 | 43.3 | 43.3 |
| 37.5° | 57.7 | 53.6 | 49.5 | 47.4 | 47.4 | 47.4 | 43.3 | 39.2 | 37.1 | 35.0 | 37.1 |
| 40° | 53.6 | 49.5 | 45.3 | 41.2 | 39.2 | 41.2 | 37.1 | 33.0 | 30.9 | 28.9 | 30.9 |
| 42.5° | 49.5 | 45.3 | 39.2 | 35.0 | 30.9 | 35.0 | 30.9 | 26.8 | 24.7 | 22.7 | 24.7 |
| 45° | 47.4 | 43.3 | 37.1 | 30.9 | 26.8 | 26.8 | 26.8 | 22.7 | 18.6 | 18.6 | 18.6 |
| 47.5° | 45.3 | 41.2 | 33.0 | 26.8 | 22.7 | 20.6 | 20.6 | 16.5 | 14.4 | 12.4 | 12.4 |
| 50° | 43.3 | 39.2 | 30.9 | 22.7 | 18.6 | 16.5 | 16.5 | 12.4 | 10.3 | 10.3 | 10.3 |
| 52.5° | 41.2 | 37.1 | 28.9 | 20.6 | 16.5 | 12.4 | 10.3 | 8.2 | 8.2 | 6.2 | 6.2 |
| 55° | 37.1 | 33.0 | 24.7 | 18.6 | 14.4 | 10.3 | 8.2 | 6.2 | 6.2 | 4.1 | 6.2 |
| 57.5° | 35.0 | 30.9 | 22.7 | 16.5 | 12.4 | 8.2 | 6.2 | 4.1 | 4.1 | 4.1 | 4.1 |
| 60° | 30.9 | 26.8 | 18.6 | 12.4 | 8.2 | 6.2 | 4.1 | 4.1 | 4.1 | 2.1 | 2.1 |
| 62.5° | 24.7 | 22.7 | 16.5 | 10.3 | 6.2 | 4.1 | 2.1 | 2.1 | 2.1 | 2.1 | 2.1 |
| 65° | 22.7 | 20.6 | 14.4 | 8.2 | 4.1 | 2.1 | 2.1 | 2.1 | 2.1 | 2.1 | 2.1 |
| 67.5° | 18.6 | 16.5 | 10.3 | 6.2 | 2.1 | 2.1 | 0.0 | 2.1 | 2.1 | 0.0 | 0.0 |
| 70° | 14.4 | 14.4 | 8.2 | 4.1 | 2.1 | 0.0 | 0.0 | 2.1 | 2.1 | 0.0 | 0.0 |
| 72.5° | 12.4 | 12.4 | 8.2 | 2.1 | 0.0 | 0.0 | 0.0 | 2.1 | 2.1 | 2.1 | 0.0 |
| 75° | 10.3 | 10.3 | 8.2 | 4.1 | 0.0 | 0.0 | 0.0 | 2.1 | 2.1 | 2.1 | 2.1 |
| 77.5° | 8.2 | 6.2 | 4.1 | 2.1 | 0.0 | 0.0 | 0.0 | 2.1 | 2.1 | 2.1 | 2.1 |
| 80° | 4.1 | 4.1 | 2.1 | 0.0 | 0.0 | 0.0 | 0.0 | 2.1 | 2.1 | 2.1 | 2.1 |
| 82.5° | 2.1 | 2.1 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 2.1 | 4.1 | 4.1 | 2.1 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 2.1 | 4.1 | 4.1 | 4.1 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 2.1 | 4.1 | 4.1 | 4.1 | 4.1 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P438814
 CATALOG NUMBER: ISW-SA1F-722-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1449.1 | 1449.1 | 1449.1 | 1449.1 | 1449.1 | 1449.1 | 1449.1 | 1449.1 | 1449.1 | 1449.1 | 1449.1 |
| 2.5° | 1232.7 | 1265.7 | 1302.8 | 1325.4 | 1374.9 | 1418.2 | 1469.7 | 1515.1 | 1568.7 | 1597.5 | 1607.8 |
| 5° | 989.4 | 1008.0 | 1055.4 | 1117.2 | 1172.9 | 1251.2 | 1341.9 | 1442.9 | 1552.2 | 1603.7 | 1640.8 |
| 7.5° | 682.3 | 698.8 | 766.8 | 824.5 | 917.3 | 1018.3 | 1142.0 | 1280.1 | 1422.3 | 1494.5 | 1560.4 |
| 10° | 445.2 | 467.9 | 525.6 | 606.0 | 723.5 | 847.2 | 972.9 | 1117.2 | 1282.1 | 1366.7 | 1455.3 |
| 12.5° | 257.7 | 284.5 | 354.5 | 459.7 | 575.1 | 707.0 | 836.9 | 995.6 | 1179.1 | 1271.8 | 1362.5 |
| 15° | 148.4 | 158.7 | 199.9 | 292.7 | 422.6 | 583.4 | 735.9 | 907.0 | 1121.4 | 1224.4 | 1331.6 |
| 17.5° | 111.3 | 117.5 | 129.9 | 169.0 | 270.0 | 447.3 | 661.7 | 880.2 | 1127.5 | 1265.7 | 1360.5 |
| 20° | 98.9 | 103.1 | 109.3 | 123.7 | 171.1 | 317.4 | 571.0 | 861.6 | 1187.3 | 1364.6 | 1480.0 |
| 22.5° | 88.6 | 92.8 | 98.9 | 109.3 | 129.9 | 214.4 | 476.2 | 859.6 | 1286.3 | 1510.9 | 1640.8 |
| 25° | 78.3 | 82.5 | 88.6 | 98.9 | 115.4 | 154.6 | 369.0 | 853.4 | 1409.9 | 1671.7 | 1834.6 |
| 27.5° | 68.0 | 72.1 | 78.3 | 88.6 | 103.1 | 127.8 | 280.3 | 834.8 | 1558.4 | 1844.9 | 2018.0 |
| 30° | 59.8 | 63.9 | 70.1 | 78.3 | 92.8 | 111.3 | 214.4 | 803.9 | 1686.2 | 1999.5 | 2141.7 |
| 32.5° | 51.5 | 55.7 | 61.8 | 70.1 | 82.5 | 96.9 | 173.2 | 738.0 | 1785.1 | 2121.1 | 2242.7 |
| 35° | 43.3 | 47.4 | 53.6 | 61.8 | 72.1 | 82.5 | 142.2 | 630.8 | 1886.1 | 2246.8 | 2364.3 |
| 37.5° | 37.1 | 41.2 | 45.3 | 53.6 | 63.9 | 74.2 | 117.5 | 562.7 | 1960.3 | 2403.5 | 2518.9 |
| 40° | 30.9 | 35.0 | 41.2 | 47.4 | 55.7 | 70.1 | 94.8 | 472.0 | 2034.5 | 2554.0 | 2661.2 |
| 42.5° | 24.7 | 28.9 | 35.0 | 43.3 | 51.5 | 61.8 | 76.3 | 389.6 | 2108.7 | 2690.0 | 2791.0 |
| 45° | 18.6 | 22.7 | 28.9 | 39.2 | 51.5 | 53.6 | 61.8 | 331.9 | 2127.3 | 2817.8 | 2904.4 |
| 47.5° | 14.4 | 16.5 | 22.7 | 33.0 | 49.5 | 47.4 | 51.5 | 288.6 | 2162.3 | 2918.8 | 3015.7 |
| 50° | 10.3 | 12.4 | 18.6 | 30.9 | 43.3 | 39.2 | 45.3 | 272.1 | 2211.8 | 2997.2 | 3048.7 |
| 52.5° | 8.2 | 10.3 | 14.4 | 26.8 | 35.0 | 35.0 | 41.2 | 288.6 | 2275.7 | 3089.9 | 3133.2 |
| 55° | 6.2 | 8.2 | 12.4 | 18.6 | 26.8 | 30.9 | 39.2 | 311.3 | 2399.4 | 3252.8 | 3244.5 |
| 57.5° | 4.1 | 6.2 | 10.3 | 14.4 | 20.6 | 26.8 | 37.1 | 346.3 | 2525.1 | 3436.2 | 3444.5 |
| 60° | 4.1 | 6.2 | 8.2 | 12.4 | 18.6 | 22.7 | 33.0 | 350.4 | 2504.5 | 3463.0 | 3584.6 |
| 62.5° | 2.1 | 4.1 | 8.2 | 10.3 | 14.4 | 18.6 | 28.9 | 294.8 | 2306.6 | 3333.2 | 3510.4 |
| 65° | 2.1 | 4.1 | 6.2 | 10.3 | 12.4 | 16.5 | 22.7 | 187.6 | 2007.7 | 3102.3 | 3337.3 |
| 67.5° | 2.1 | 4.1 | 6.2 | 8.2 | 10.3 | 14.4 | 18.6 | 96.9 | 1702.7 | 2863.2 | 3089.9 |
| 70° | 2.1 | 4.1 | 6.2 | 8.2 | 10.3 | 12.4 | 16.5 | 47.4 | 1290.4 | 2413.8 | 2706.5 |
| 72.5° | 2.1 | 4.1 | 6.2 | 8.2 | 8.2 | 10.3 | 14.4 | 33.0 | 828.7 | 1814.0 | 2096.4 |
| 75° | 2.1 | 4.1 | 4.1 | 6.2 | 8.2 | 10.3 | 12.4 | 22.7 | 535.9 | 1220.3 | 1589.3 |
| 77.5° | 2.1 | 4.1 | 4.1 | 6.2 | 8.2 | 10.3 | 14.4 | 20.6 | 391.7 | 836.9 | 1098.7 |
| 80° | 2.1 | 4.1 | 4.1 | 6.2 | 8.2 | 8.2 | 10.3 | 14.4 | 210.3 | 554.5 | 698.8 |
| 82.5° | 4.1 | 4.1 | 6.2 | 6.2 | 6.2 | 8.2 | 10.3 | 10.3 | 109.3 | 354.5 | 472.0 |
| 85° | 4.1 | 4.1 | 6.2 | 6.2 | 8.2 | 8.2 | 8.2 | 10.3 | 47.4 | 148.4 | 235.0 |
| 87.5° | 4.1 | 6.2 | 6.2 | 6.2 | 8.2 | 8.2 | 8.2 | 8.2 | 6.2 | 8.2 | 8.2 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P438814

CATALOG NUMBER: ISW-SA1F-722-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 359° | 360° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1449.1 | 1449.1 | 1449.1 | 1449.1 | 1449.1 | 1449.1 | 1449.1 | 1449.1 | 1449.1 | 1449.1 |
| 2.5° | 1638.8 | 1665.5 | 1677.9 | 1667.6 | 1659.4 | 1634.6 | 1599.6 | 1564.5 | 1535.7 | 1533.6 |
| 5° | 1725.3 | 1783.0 | 1828.4 | 1805.7 | 1774.8 | 1702.7 | 1614.0 | 1515.1 | 1478.0 | 1461.5 |
| 7.5° | 1706.8 | 1832.5 | 1908.8 | 1888.2 | 1826.3 | 1690.3 | 1552.2 | 1422.3 | 1362.5 | 1341.9 |
| 10° | 1622.3 | 1791.3 | 1892.3 | 1886.1 | 1828.4 | 1667.6 | 1496.5 | 1339.9 | 1276.0 | 1259.5 |
| 12.5° | 1543.9 | 1710.9 | 1807.8 | 1811.9 | 1791.3 | 1642.9 | 1469.7 | 1302.8 | 1226.5 | 1218.2 |
| 15° | 1502.7 | 1644.9 | 1702.7 | 1715.0 | 1723.3 | 1640.8 | 1494.5 | 1327.5 | 1247.1 | 1228.5 |
| 17.5° | 1510.9 | 1579.0 | 1593.4 | 1583.1 | 1638.8 | 1642.9 | 1564.5 | 1414.1 | 1323.4 | 1300.7 |
| 20° | 1560.4 | 1535.7 | 1488.3 | 1498.6 | 1560.4 | 1651.1 | 1669.7 | 1566.6 | 1463.5 | 1434.7 |
| 22.5° | 1655.2 | 1533.6 | 1438.8 | 1430.6 | 1510.9 | 1665.5 | 1783.0 | 1729.4 | 1622.3 | 1605.8 |
| 25° | 1795.4 | 1564.5 | 1418.2 | 1401.7 | 1471.8 | 1680.0 | 1898.5 | 1900.5 | 1816.0 | 1785.1 |
| 27.5° | 1931.5 | 1614.0 | 1416.1 | 1399.6 | 1471.8 | 1698.5 | 1976.8 | 2069.6 | 1980.9 | 1947.9 |
| 30° | 2009.8 | 1671.7 | 1449.1 | 1418.2 | 1498.6 | 1715.0 | 2028.3 | 2203.6 | 2125.2 | 2096.4 |
| 32.5° | 2081.9 | 1733.6 | 1484.2 | 1447.0 | 1550.1 | 1760.4 | 2075.8 | 2325.2 | 2257.1 | 2222.1 |
| 35° | 2141.7 | 1805.7 | 1550.1 | 1492.4 | 1626.4 | 1826.3 | 2133.5 | 2459.2 | 2415.9 | 2372.6 |
| 37.5° | 2199.4 | 1877.9 | 1642.9 | 1609.9 | 1754.2 | 1921.2 | 2209.7 | 2599.3 | 2619.9 | 2576.7 |
| 40° | 2281.9 | 1960.3 | 1801.6 | 1774.8 | 1941.8 | 2065.4 | 2302.5 | 2739.5 | 2807.5 | 2760.1 |
| 42.5° | 2360.2 | 2065.4 | 1962.4 | 1987.1 | 2168.5 | 2232.4 | 2407.6 | 2867.3 | 2943.6 | 2923.0 |
| 45° | 2432.4 | 2195.3 | 2195.3 | 2255.1 | 2413.8 | 2415.9 | 2488.0 | 2955.9 | 3036.3 | 3026.0 |
| 47.5° | 2527.2 | 2356.1 | 2436.5 | 2601.4 | 2685.9 | 2574.6 | 2574.6 | 3040.5 | 3149.7 | 3120.8 |
| 50° | 2619.9 | 2570.5 | 2756.0 | 2906.5 | 2980.7 | 2766.3 | 2663.2 | 3153.8 | 3283.7 | 3259.0 |
| 52.5° | 2720.9 | 2778.7 | 3054.9 | 3203.3 | 3246.6 | 2984.8 | 2797.2 | 3267.2 | 3434.2 | 3434.2 |
| 55° | 2883.8 | 2955.9 | 3370.3 | 3493.9 | 3555.8 | 3166.2 | 2968.3 | 3428.0 | 3617.6 | 3627.9 |
| 57.5° | 3050.8 | 3127.0 | 3547.5 | 3704.2 | 3784.6 | 3434.2 | 3188.9 | 3642.4 | 3747.5 | 3745.4 |
| 60° | 3226.0 | 3306.4 | 3685.6 | 3840.2 | 3957.7 | 3708.3 | 3450.7 | 3838.2 | 3809.3 | 3788.7 |
| 62.5° | 3442.4 | 3442.4 | 3737.2 | 3809.3 | 3951.6 | 3881.5 | 3745.4 | 3949.5 | 3832.0 | 3784.6 |
| 65° | 3547.5 | 3514.6 | 3588.8 | 3535.2 | 3698.0 | 3832.0 | 3970.1 | 3953.6 | 3751.6 | 3673.3 |
| 67.5° | 3491.9 | 3291.9 | 3164.1 | 3083.7 | 3118.8 | 3349.6 | 3871.2 | 3757.8 | 3425.9 | 3366.1 |
| 70° | 3110.5 | 2632.3 | 2512.8 | 2384.9 | 2316.9 | 2556.0 | 3345.5 | 3318.7 | 2914.7 | 2859.1 |
| 72.5° | 2535.4 | 1900.5 | 1612.0 | 1741.8 | 1675.9 | 1945.9 | 2741.6 | 2341.7 | 1912.9 | 1863.4 |
| 75° | 2104.6 | 1414.1 | 1051.3 | 1053.3 | 1063.6 | 1278.0 | 2003.6 | 1391.4 | 1051.3 | 1014.2 |
| 77.5° | 1523.3 | 995.6 | 849.3 | 760.6 | 768.9 | 816.3 | 1043.0 | 593.7 | 484.4 | 439.1 |
| 80° | 929.7 | 616.3 | 686.4 | 610.2 | 589.5 | 453.5 | 449.4 | 86.6 | 57.7 | 57.7 |
| 82.5° | 507.1 | 391.7 | 364.9 | 131.9 | 204.1 | 247.4 | 204.1 | 4.1 | 2.1 | 2.1 |
| 85° | 257.7 | 156.7 | 74.2 | 22.7 | 26.8 | 22.7 | 4.1 | 0.0 | 0.0 | 0.0 |
| 87.5° | 8.2 | 6.2 | 6.2 | 4.1 | 4.1 | 2.1 | 2.1 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Test Information

Test Method: LM-79-2008 Report
 Number: SP1-1908-441-10-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: MCGRAW-EDISON
 Catalog Number: **SA1C-722-U-5WQ**
 Description: MCGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2237
 CIE u': 0.2876
 CIE v': 0.5346
 Duv: -0.0006
 CIE x: 0.5005
 CIE y: 0.4134
 CIE z: 0.0860
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 587
 Purity: 74.5
 Rf: 69.8
 Rg: 99.2

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 72.0 | | |
| R1: | 68.9 | R9: | -17.4 |
| R2: | 83.0 | R10: | 61.3 |
| R3: | 95.2 | R11: | 59.8 |
| R4: | 66.2 | R12: | 50.5 |
| R5: | 65.9 | R13: | 71.1 |
| R6: | 76.3 | R14: | 96.9 |
| R7: | 76.7 | | |
| R8: | 43.8 | | |



Test Conditions

Stabilization Time: 71M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.7/41%
 Sphere Temperature (°C): 25.6

REPORT NUMBER: SP1-1908-441-10-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-10-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2200K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-10-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 1768 | NR | 490 | 5206 | NR | 620 | 130919 | NR | 750 | 8553 | NR | 880 | 2713 | NR |
| 365 | 1569 | NR | 495 | 7286 | NR | 625 | 125335 | NR | 755 | 7696 | NR | 885 | 2316 | NR |
| 370 | 1594 | NR | 500 | 10654 | NR | 630 | 118388 | NR | 760 | 6978 | NR | 890 | 2539 | NR |
| 375 | 1744 | NR | 505 | 15189 | NR | 635 | 111855 | NR | 765 | 6377 | NR | 895 | 1933 | NR |
| 380 | 1659 | NR | 510 | 20541 | NR | 640 | 104062 | NR | 770 | 5600 | NR | 900 | 2216 | NR |
| 385 | 1504 | NR | 515 | 26492 | NR | 645 | 96365 | NR | 775 | 5000 | NR | 905 | 2067 | NR |
| 390 | 1541 | NR | 520 | 32294 | NR | 650 | 88651 | NR | 780 | 4709 | NR | 910 | 1959 | NR |
| 395 | 1355 | NR | 525 | 38123 | NR | 655 | 81152 | NR | 785 | 4305 | NR | 915 | 1874 | NR |
| 400 | 1243 | NR | 530 | 43232 | NR | 660 | 73523 | NR | 790 | 4040 | NR | 920 | 1484 | NR |
| 405 | 1417 | NR | 535 | 48012 | NR | 665 | 66123 | NR | 795 | 3642 | NR | 925 | 1914 | NR |
| 410 | 2147 | NR | 540 | 52623 | NR | 670 | 58677 | NR | 800 | 3594 | NR | 930 | 1948 | NR |
| 415 | 3837 | NR | 545 | 57516 | NR | 675 | 52349 | NR | 805 | 3190 | NR | 935 | 2079 | NR |
| 420 | 7159 | NR | 550 | 62613 | NR | 680 | 46159 | NR | 810 | 3241 | NR | 940 | 2263 | NR |
| 425 | 12599 | NR | 555 | 68554 | NR | 685 | 40525 | NR | 815 | 2732 | NR | 945 | 1688 | NR |
| 430 | 19019 | NR | 560 | 75325 | NR | 690 | 35615 | NR | 820 | 2612 | NR | 950 | 1560 | NR |
| 435 | 24875 | NR | 565 | 82533 | NR | 695 | 31158 | NR | 825 | 2966 | NR | 955 | 2826 | NR |
| 440 | 29103 | NR | 570 | 90909 | NR | 700 | 27409 | NR | 830 | 2574 | NR | 960 | 1477 | NR |
| 445 | 29901 | NR | 575 | 99621 | NR | 705 | 24204 | NR | 835 | 2633 | NR | 965 | 1568 | NR |
| 450 | 24862 | NR | 580 | 108484 | NR | 710 | 21558 | NR | 840 | 2526 | NR | 970 | 2030 | NR |
| 455 | 15942 | NR | 585 | 116679 | NR | 715 | 19222 | NR | 845 | 2631 | NR | 975 | 1986 | NR |
| 460 | 9916 | NR | 590 | 123752 | NR | 720 | 17310 | NR | 850 | 2079 | NR | 980 | 2540 | NR |
| 465 | 7051 | NR | 595 | 129324 | NR | 725 | 15280 | NR | 855 | 2309 | NR | 985 | 1139 | NR |
| 470 | 5227 | NR | 600 | 134082 | NR | 730 | 13282 | NR | 860 | 2528 | NR | 990 | 2018 | NR |
| 475 | 4257 | NR | 605 | 135698 | NR | 735 | 11753 | NR | 865 | 2121 | NR | 995 | 3445 | NR |
| 480 | 4052 | NR | 610 | 135144 | NR | 740 | 10654 | NR | 870 | 2751 | NR | 1000 | 3704 | NR |
| 485 | 4298 | NR | 615 | 134180 | NR | 745 | 9451 | NR | 875 | 2317 | NR | | | |

REPORT NUMBER: SP1-1908-441-10-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 4696.9

S/P: 0.85

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 1768 | NR | 490 | 5206 | NR | 620 | 130919 | NR | 750 | 8553 | NR | 880 | 2713 | NR |
| 365 | 1569 | NR | 495 | 7286 | NR | 625 | 125335 | NR | 755 | 7696 | NR | 885 | 2316 | NR |
| 370 | 1594 | NR | 500 | 10654 | NR | 630 | 118388 | NR | 760 | 6978 | NR | 890 | 2539 | NR |
| 375 | 1744 | NR | 505 | 15189 | NR | 635 | 111855 | NR | 765 | 6377 | NR | 895 | 1933 | NR |
| 380 | 1659 | NR | 510 | 20541 | NR | 640 | 104062 | NR | 770 | 5600 | NR | 900 | 2216 | NR |
| 385 | 1504 | NR | 515 | 26492 | NR | 645 | 96365 | NR | 775 | 5000 | NR | 905 | 2067 | NR |
| 390 | 1541 | NR | 520 | 32294 | NR | 650 | 88651 | NR | 780 | 4709 | NR | 910 | 1959 | NR |
| 395 | 1355 | NR | 525 | 38123 | NR | 655 | 81152 | NR | 785 | 4305 | NR | 915 | 1874 | NR |
| 400 | 1243 | NR | 530 | 43232 | NR | 660 | 73523 | NR | 790 | 4040 | NR | 920 | 1484 | NR |
| 405 | 1417 | NR | 535 | 48012 | NR | 665 | 66123 | NR | 795 | 3642 | NR | 925 | 1914 | NR |
| 410 | 2147 | NR | 540 | 52623 | NR | 670 | 58677 | NR | 800 | 3594 | NR | 930 | 1948 | NR |
| 415 | 3837 | NR | 545 | 57516 | NR | 675 | 52349 | NR | 805 | 3190 | NR | 935 | 2079 | NR |
| 420 | 7159 | NR | 550 | 62613 | NR | 680 | 46159 | NR | 810 | 3241 | NR | 940 | 2263 | NR |
| 425 | 12599 | NR | 555 | 68554 | NR | 685 | 40525 | NR | 815 | 2732 | NR | 945 | 1688 | NR |
| 430 | 19019 | NR | 560 | 75325 | NR | 690 | 35615 | NR | 820 | 2612 | NR | 950 | 1560 | NR |
| 435 | 24875 | NR | 565 | 82533 | NR | 695 | 31158 | NR | 825 | 2966 | NR | 955 | 2826 | NR |
| 440 | 29103 | NR | 570 | 90909 | NR | 700 | 27409 | NR | 830 | 2574 | NR | 960 | 1477 | NR |
| 445 | 29901 | NR | 575 | 99621 | NR | 705 | 24204 | NR | 835 | 2633 | NR | 965 | 1568 | NR |
| 450 | 24862 | NR | 580 | 108484 | NR | 710 | 21558 | NR | 840 | 2526 | NR | 970 | 2030 | NR |
| 455 | 15942 | NR | 585 | 116679 | NR | 715 | 19222 | NR | 845 | 2631 | NR | 975 | 1986 | NR |
| 460 | 9916 | NR | 590 | 123752 | NR | 720 | 17310 | NR | 850 | 2079 | NR | 980 | 2540 | NR |
| 465 | 7051 | NR | 595 | 129324 | NR | 725 | 15280 | NR | 855 | 2309 | NR | 985 | 1139 | NR |
| 470 | 5227 | NR | 600 | 134082 | NR | 730 | 13282 | NR | 860 | 2528 | NR | 990 | 2018 | NR |
| 475 | 4257 | NR | 605 | 135698 | NR | 735 | 11753 | NR | 865 | 2121 | NR | 995 | 3445 | NR |
| 480 | 4052 | NR | 610 | 135144 | NR | 740 | 10654 | NR | 870 | 2751 | NR | 1000 | 3704 | NR |
| 485 | 4298 | NR | 615 | 134180 | NR | 745 | 9451 | NR | 875 | 2317 | NR | | | |

REPORT NUMBER: SP1-1908-441-10-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 1470.8 M/P: 0.27

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 1768 | NR | 490 | 5206 | NR | 620 | 130919 | NR | 750 | 8553 | NR | 880 | 2713 | NR |
| 365 | 1569 | NR | 495 | 7286 | NR | 625 | 125335 | NR | 755 | 7696 | NR | 885 | 2316 | NR |
| 370 | 1594 | NR | 500 | 10654 | NR | 630 | 118388 | NR | 760 | 6978 | NR | 890 | 2539 | NR |
| 375 | 1744 | NR | 505 | 15189 | NR | 635 | 111855 | NR | 765 | 6377 | NR | 895 | 1933 | NR |
| 380 | 1659 | NR | 510 | 20541 | NR | 640 | 104062 | NR | 770 | 5600 | NR | 900 | 2216 | NR |
| 385 | 1504 | NR | 515 | 26492 | NR | 645 | 96365 | NR | 775 | 5000 | NR | 905 | 2067 | NR |
| 390 | 1541 | NR | 520 | 32294 | NR | 650 | 88651 | NR | 780 | 4709 | NR | 910 | 1959 | NR |
| 395 | 1355 | NR | 525 | 38123 | NR | 655 | 81152 | NR | 785 | 4305 | NR | 915 | 1874 | NR |
| 400 | 1243 | NR | 530 | 43232 | NR | 660 | 73523 | NR | 790 | 4040 | NR | 920 | 1484 | NR |
| 405 | 1417 | NR | 535 | 48012 | NR | 665 | 66123 | NR | 795 | 3642 | NR | 925 | 1914 | NR |
| 410 | 2147 | NR | 540 | 52623 | NR | 670 | 58677 | NR | 800 | 3594 | NR | 930 | 1948 | NR |
| 415 | 3837 | NR | 545 | 57516 | NR | 675 | 52349 | NR | 805 | 3190 | NR | 935 | 2079 | NR |
| 420 | 7159 | NR | 550 | 62613 | NR | 680 | 46159 | NR | 810 | 3241 | NR | 940 | 2263 | NR |
| 425 | 12599 | NR | 555 | 68554 | NR | 685 | 40525 | NR | 815 | 2732 | NR | 945 | 1688 | NR |
| 430 | 19019 | NR | 560 | 75325 | NR | 690 | 35615 | NR | 820 | 2612 | NR | 950 | 1560 | NR |
| 435 | 24875 | NR | 565 | 82533 | NR | 695 | 31158 | NR | 825 | 2966 | NR | 955 | 2826 | NR |
| 440 | 29103 | NR | 570 | 90909 | NR | 700 | 27409 | NR | 830 | 2574 | NR | 960 | 1477 | NR |
| 445 | 29901 | NR | 575 | 99621 | NR | 705 | 24204 | NR | 835 | 2633 | NR | 965 | 1568 | NR |
| 450 | 24862 | NR | 580 | 108484 | NR | 710 | 21558 | NR | 840 | 2526 | NR | 970 | 2030 | NR |
| 455 | 15942 | NR | 585 | 116679 | NR | 715 | 19222 | NR | 845 | 2631 | NR | 975 | 1986 | NR |
| 460 | 9916 | NR | 590 | 123752 | NR | 720 | 17310 | NR | 850 | 2079 | NR | 980 | 2540 | NR |
| 465 | 7051 | NR | 595 | 129324 | NR | 725 | 15280 | NR | 855 | 2309 | NR | 985 | 1139 | NR |
| 470 | 5227 | NR | 600 | 134082 | NR | 730 | 13282 | NR | 860 | 2528 | NR | 990 | 2018 | NR |
| 475 | 4257 | NR | 605 | 135698 | NR | 735 | 11753 | NR | 865 | 2121 | NR | 995 | 3445 | NR |
| 480 | 4052 | NR | 610 | 135144 | NR | 740 | 10654 | NR | 870 | 2751 | NR | 1000 | 3704 | NR |
| 485 | 4298 | NR | 615 | 134180 | NR | 745 | 9451 | NR | 875 | 2317 | NR | | | |

REPORT NUMBER: SP1-1908-441-10-R4




TM-30-18

Summary

$R_f = 69.8$
 $R_g = 99.2$
 CIE $R_a = 72.0$
 $R_9 = -17.4$



Color Vector Graphics




REPORT NUMBER: SP1-1908-441-10-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)



| | | | |
|------------|------------|------------|------------|
| CES01 = 87 | CES26 = 56 | CES51 = 74 | CES76 = 56 |
| CES02 = 65 | CES27 = 76 | CES52 = 76 | CES77 = 81 |
| CES03 = 32 | CES28 = 83 | CES53 = 65 | CES78 = 63 |
| CES04 = 72 | CES29 = 46 | CES54 = 78 | CES79 = 84 |
| CES05 = 52 | CES30 = 48 | CES55 = 75 | CES80 = 84 |
| CES06 = 52 | CES31 = 51 | CES56 = 65 | CES81 = 63 |
| CES07 = 44 | CES32 = 51 | CES57 = 62 | CES82 = 92 |
| CES08 = 42 | CES33 = 53 | CES58 = 66 | CES83 = 83 |
| CES09 = 29 | CES34 = 70 | CES59 = 84 | CES84 = 92 |
| CES10 = 78 | CES35 = 85 | CES60 = 90 | CES85 = 81 |
| CES11 = 61 | CES36 = 78 | CES61 = 84 | CES86 = 56 |
| CES12 = 68 | CES37 = 80 | CES62 = 70 | CES87 = 78 |
| CES13 = 45 | CES38 = 53 | CES63 = 68 | CES88 = 72 |
| CES14 = 75 | CES39 = 90 | CES64 = 69 | CES89 = 62 |
| CES15 = 72 | CES40 = 84 | CES65 = 67 | CES90 = 67 |
| CES16 = 49 | CES41 = 75 | CES66 = 64 | CES91 = 90 |
| CES17 = 51 | CES42 = 79 | CES67 = 63 | CES92 = 67 |
| CES18 = 57 | CES43 = 64 | CES68 = 69 | CES93 = 79 |
| CES19 = 74 | CES44 = 98 | CES69 = 80 | CES94 = 52 |
| CES20 = 68 | CES45 = 73 | CES70 = 63 | CES95 = 76 |
| CES21 = 89 | CES46 = 67 | CES71 = 63 | CES96 = 78 |
| CES22 = 81 | CES47 = 60 | CES72 = 87 | CES97 = 77 |
| CES23 = 92 | CES48 = 48 | CES73 = 56 | CES98 = 71 |
| CES24 = 92 | CES49 = 64 | CES74 = 87 | CES99 = 65 |
| CES25 = 74 | CES50 = 74 | CES75 = 66 | |



REPORT NUMBER: SP1-1908-441-10-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-10-R4

TM-30-18

Measure Comparisons



(END OF REPORT)