

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P438373

Luminaire Tested: **ISW-SA1C-740-U-SL4-HSS**

Issue Date: 12/10/2020

Test Information

Test Method: LM-79-08
Report Number: P438373
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-074-19)
Test Lab: INNOVATION CENTER
Issue Date: 12/10/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: ISW-SA1C-740-U-SL4-HSS
Description: IMPACT ELITE LED WEDGE LUMINAIRE
(1) 70 CRI, 4000K, 615mA LIGHTSQUARE WITH 16 LEDS AND TYPE IV SPILL LIGHT
ELIMINATOR OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3694 lumens
Efficiency: N/A
Efficacy: 108.0 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B0 - U0 - G1


Input Watts (W): 34.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P438373
 CATALOG NUMBER: ISW-SA1C-740-U-SL4-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1.2 fc
 Type IV - Short - N/A

REPORT NUMBER: P438373
CATALOG NUMBER: ISW-SA1C-740-U-SL4-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 36-Deg Lateral - - - Horizontal Cone Through 72.5-Deg Vertical

REPORT NUMBER: P438373

CATALOG NUMBER: ISW-SA1C-740-U-SL4-HSS


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 288.2 | 0.0 | 288.2 |
| | % Fixture | 7.8 | 0.0 | 7.8 |
| Street Side | Lumens | 3405.8 | 0.0 | 3405.8 |
| | % Fixture | 92.2 | 0.0 | 92.2 |
| Total | Lumens | 3694.0 | 0.0 | 3694.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 55.4 | 1.5 |
| 10°-20° | 139.1 | 3.8 |
| 20°-30° | 227.2 | 6.1 |
| 30°-40° | 345.4 | 9.3 |
| 40°-50° | 528.1 | 14.3 |
| 50°-60° | 750.9 | 20.3 |
| 60°-70° | 952.3 | 25.8 |
| 70°-80° | 652.0 | 17.7 |
| 80°-90° | 43.7 | 1.2 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 3694.0 | 100.0 |
| 0°-180° | 3694.0 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P438373


CATALOG NUMBER: ISW-SA1C-740-U-SL4-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 319.9 | 8.7 | | | |
| FM (30°-60°) | 1473.3 | 39.9 | | | |
| FH (60°-80°) | 1569.5 | 42.5 | | | G1/1800 |
| FVH (80°-90°) | 43.0 | 1.2 | | | G1/100 |
| BL (0°-30°) | 101.7 | 2.8 | B0/110 | | |
| BM (30°-60°) | 151.1 | 4.1 | B0/220 | | |
| BH (60°-80°) | 34.7 | 0.9 | B0/110 | | G0/110 |
| BVH (80°-90°) | 0.6 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B0-U0-G1

Type IV Short





REPORT NUMBER: P438373
 CATALOG NUMBER: ISW-SA1C-740-U-SL4-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 36° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 648.7 | 648.7 | 648.7 | 648.7 | 648.7 | 648.7 | 648.7 | 648.7 | 648.7 | 648.7 | 648.7 |
| 2.5° | 726.8 | 721.9 | 718.6 | 715.4 | 705.6 | 707.3 | 697.5 | 687.7 | 673.1 | 666.6 | 656.9 |
| 5° | 744.6 | 743.0 | 741.4 | 736.5 | 728.4 | 731.6 | 721.9 | 712.1 | 691.0 | 671.5 | 650.3 |
| 7.5° | 741.4 | 744.6 | 743.0 | 739.8 | 733.3 | 734.9 | 726.8 | 717.0 | 699.1 | 673.1 | 643.8 |
| 10° | 734.9 | 736.5 | 736.5 | 734.9 | 733.3 | 733.3 | 726.8 | 718.6 | 702.4 | 679.6 | 642.2 |
| 12.5° | 721.9 | 725.1 | 730.0 | 733.3 | 734.9 | 736.5 | 731.6 | 725.1 | 710.5 | 686.1 | 647.1 |
| 15° | 717.0 | 720.3 | 730.0 | 739.8 | 744.6 | 746.3 | 741.4 | 733.3 | 720.3 | 699.1 | 655.2 |
| 17.5° | 717.0 | 720.3 | 736.5 | 751.2 | 760.9 | 762.5 | 756.0 | 747.9 | 731.6 | 710.5 | 665.0 |
| 20° | 726.8 | 730.0 | 749.5 | 775.5 | 780.4 | 783.7 | 773.9 | 762.5 | 744.6 | 723.5 | 676.4 |
| 22.5° | 743.0 | 747.9 | 772.3 | 796.7 | 806.4 | 808.1 | 796.7 | 775.5 | 759.3 | 738.1 | 686.1 |
| 25° | 770.7 | 782.0 | 804.8 | 830.8 | 832.4 | 834.1 | 816.2 | 795.0 | 775.5 | 754.4 | 697.5 |
| 27.5° | 809.7 | 819.4 | 838.9 | 868.2 | 858.5 | 858.5 | 843.8 | 816.2 | 796.7 | 777.2 | 717.0 |
| 30° | 860.1 | 866.6 | 889.3 | 900.7 | 887.7 | 889.3 | 871.5 | 845.5 | 829.2 | 809.7 | 746.3 |
| 32.5° | 907.2 | 912.1 | 936.5 | 938.1 | 923.5 | 921.9 | 908.9 | 878.0 | 865.0 | 858.5 | 786.9 |
| 35° | 951.1 | 957.6 | 977.1 | 975.5 | 960.9 | 959.3 | 952.8 | 925.1 | 925.1 | 931.6 | 847.1 |
| 37.5° | 983.7 | 999.9 | 1024.3 | 1017.8 | 1008.0 | 1008.0 | 1003.2 | 982.0 | 998.3 | 1022.7 | 926.7 |
| 40° | 1025.9 | 1035.7 | 1068.2 | 1063.3 | 1064.9 | 1064.9 | 1066.6 | 1053.6 | 1082.8 | 1123.5 | 1019.4 |
| 42.5° | 1048.7 | 1068.2 | 1107.2 | 1113.7 | 1128.4 | 1128.4 | 1141.4 | 1138.1 | 1193.4 | 1245.4 | 1126.7 |
| 45° | 1084.5 | 1105.6 | 1147.9 | 1172.3 | 1190.1 | 1198.3 | 1221.0 | 1238.9 | 1317.0 | 1382.0 | 1240.5 |
| 47.5° | 1130.0 | 1147.9 | 1183.6 | 1229.2 | 1261.7 | 1274.7 | 1320.2 | 1349.5 | 1453.5 | 1520.2 | 1347.8 |
| 50° | 1191.8 | 1195.0 | 1221.0 | 1289.3 | 1346.2 | 1354.3 | 1425.9 | 1474.7 | 1591.7 | 1653.5 | 1424.3 |
| 52.5° | 1258.4 | 1251.9 | 1266.6 | 1359.2 | 1438.9 | 1453.5 | 1534.8 | 1609.6 | 1726.7 | 1739.7 | 1455.2 |
| 55° | 1310.4 | 1310.4 | 1321.8 | 1435.6 | 1542.9 | 1551.1 | 1664.9 | 1744.6 | 1850.2 | 1790.1 | 1474.7 |
| 57.5° | 1377.1 | 1370.6 | 1388.5 | 1513.7 | 1673.0 | 1679.5 | 1811.2 | 1873.0 | 1918.5 | 1822.6 | 1471.4 |
| 60° | 1425.9 | 1434.0 | 1461.7 | 1614.5 | 1808.0 | 1837.2 | 1947.8 | 1967.3 | 1990.1 | 1834.0 | 1461.7 |
| 62.5° | 1494.2 | 1492.5 | 1546.2 | 1726.7 | 1983.6 | 2003.1 | 2079.5 | 2047.0 | 2045.3 | 1853.5 | 1448.6 |
| 65° | 1551.1 | 1564.1 | 1645.4 | 1861.6 | 2170.5 | 2183.5 | 2209.6 | 2167.3 | 2121.8 | 1874.6 | 1334.8 |
| 67.5° | 1638.9 | 1664.9 | 1767.3 | 2038.8 | 2370.5 | 2385.1 | 2407.9 | 2315.2 | 2142.9 | 1725.0 | 1112.1 |
| 70° | 1738.1 | 1772.2 | 1938.0 | 2274.6 | 2585.1 | 2601.4 | 2606.3 | 2329.9 | 1941.3 | 1354.3 | 754.4 |
| 72.5° | 1638.9 | 1694.2 | 1986.8 | 2404.7 | 2741.2 | 2742.8 | 2546.1 | 2058.3 | 1487.7 | 739.8 | 266.6 |
| 75° | 1055.2 | 1125.1 | 1645.4 | 2133.1 | 2360.8 | 2386.8 | 1996.6 | 1438.9 | 694.2 | 165.8 | 74.8 |
| 77.5° | 357.7 | 382.1 | 808.1 | 1346.2 | 1583.6 | 1593.4 | 1313.7 | 728.4 | 219.5 | 66.7 | 40.6 |
| 80° | 206.5 | 204.9 | 282.9 | 588.6 | 790.2 | 821.1 | 661.7 | 291.0 | 102.4 | 34.1 | 27.6 |
| 82.5° | 48.8 | 50.4 | 148.0 | 214.6 | 313.8 | 282.9 | 139.8 | 175.6 | 47.2 | 19.5 | 24.4 |
| 85° | 0.0 | 0.0 | 24.4 | 52.0 | 37.4 | 43.9 | 13.0 | 53.7 | 8.1 | 8.1 | 16.3 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 1.6 | 1.6 | 1.6 | 1.6 | 1.6 | 1.6 | 1.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P438373
 CATALOG NUMBER: ISW-SA1C-740-U-SL4-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 648.7 | 648.7 | 648.7 | 648.7 | 648.7 | 648.7 | 648.7 | 648.7 | 648.7 | 648.7 | 648.7 |
| 2.5° | 647.1 | 639.0 | 622.7 | 609.7 | 591.8 | 577.2 | 562.6 | 556.0 | 544.7 | 541.4 | 543.0 |
| 5° | 637.3 | 624.3 | 593.4 | 562.6 | 528.4 | 495.9 | 461.7 | 442.2 | 434.1 | 419.5 | 416.2 |
| 7.5° | 626.0 | 606.4 | 562.6 | 512.1 | 453.6 | 406.5 | 359.3 | 326.8 | 297.5 | 286.2 | 281.3 |
| 10° | 621.1 | 596.7 | 534.9 | 458.5 | 378.8 | 302.4 | 243.9 | 201.6 | 175.6 | 165.8 | 162.6 |
| 12.5° | 621.1 | 591.8 | 508.9 | 406.5 | 300.8 | 213.0 | 159.3 | 134.9 | 126.8 | 125.2 | 123.6 |
| 15° | 627.6 | 590.2 | 484.5 | 351.2 | 227.6 | 148.0 | 121.9 | 118.7 | 117.1 | 117.1 | 118.7 |
| 17.5° | 630.8 | 586.9 | 458.5 | 297.5 | 167.5 | 118.7 | 113.8 | 113.8 | 113.8 | 113.8 | 113.8 |
| 20° | 639.0 | 585.3 | 429.2 | 240.6 | 126.8 | 110.6 | 108.9 | 108.9 | 108.9 | 108.9 | 110.6 |
| 22.5° | 640.6 | 585.3 | 393.5 | 185.3 | 112.2 | 105.7 | 104.1 | 104.1 | 104.1 | 105.7 | 105.7 |
| 25° | 650.3 | 582.1 | 359.3 | 141.5 | 105.7 | 99.2 | 99.2 | 97.6 | 99.2 | 99.2 | 99.2 |
| 27.5° | 663.4 | 583.7 | 317.0 | 117.1 | 99.2 | 94.3 | 92.7 | 92.7 | 92.7 | 92.7 | 92.7 |
| 30° | 678.0 | 586.9 | 273.1 | 104.1 | 92.7 | 89.4 | 87.8 | 86.2 | 86.2 | 86.2 | 86.2 |
| 32.5° | 705.6 | 590.2 | 226.0 | 94.3 | 86.2 | 82.9 | 81.3 | 79.7 | 79.7 | 79.7 | 79.7 |
| 35° | 747.9 | 608.1 | 185.3 | 87.8 | 79.7 | 76.4 | 74.8 | 73.2 | 73.2 | 73.2 | 71.5 |
| 37.5° | 804.8 | 635.7 | 146.3 | 81.3 | 73.2 | 69.9 | 68.3 | 66.7 | 65.0 | 65.0 | 65.0 |
| 40° | 873.1 | 665.0 | 121.9 | 73.2 | 66.7 | 63.4 | 61.8 | 60.2 | 58.5 | 56.9 | 56.9 |
| 42.5° | 954.4 | 700.7 | 97.6 | 66.7 | 60.2 | 56.9 | 55.3 | 53.7 | 50.4 | 48.8 | 50.4 |
| 45° | 1045.4 | 734.9 | 82.9 | 61.8 | 55.3 | 52.0 | 50.4 | 47.2 | 43.9 | 42.3 | 42.3 |
| 47.5° | 1125.1 | 743.0 | 73.2 | 55.3 | 50.4 | 47.2 | 45.5 | 40.6 | 37.4 | 34.1 | 34.1 |
| 50° | 1178.8 | 728.4 | 65.0 | 50.4 | 45.5 | 43.9 | 40.6 | 34.1 | 29.3 | 27.6 | 26.0 |
| 52.5° | 1185.3 | 689.4 | 56.9 | 45.5 | 42.3 | 39.0 | 34.1 | 29.3 | 24.4 | 21.1 | 21.1 |
| 55° | 1178.8 | 624.3 | 50.4 | 42.3 | 37.4 | 34.1 | 29.3 | 22.8 | 17.9 | 16.3 | 14.6 |
| 57.5° | 1157.6 | 556.0 | 45.5 | 37.4 | 34.1 | 29.3 | 22.8 | 17.9 | 13.0 | 11.4 | 9.8 |
| 60° | 1118.6 | 473.1 | 40.6 | 34.1 | 29.3 | 24.4 | 17.9 | 13.0 | 8.1 | 6.5 | 6.5 |
| 62.5° | 1045.4 | 382.1 | 35.8 | 29.3 | 24.4 | 19.5 | 14.6 | 8.1 | 4.9 | 3.3 | 3.3 |
| 65° | 900.7 | 286.2 | 30.9 | 24.4 | 19.5 | 16.3 | 9.8 | 4.9 | 1.6 | 0.0 | 0.0 |
| 67.5° | 700.7 | 193.5 | 24.4 | 19.5 | 16.3 | 13.0 | 8.1 | 1.6 | 0.0 | 0.0 | 0.0 |
| 70° | 413.0 | 102.4 | 19.5 | 14.6 | 13.0 | 9.8 | 4.9 | 1.6 | 0.0 | 0.0 | 0.0 |
| 72.5° | 118.7 | 40.6 | 14.6 | 11.4 | 9.8 | 6.5 | 3.3 | 1.6 | 0.0 | 0.0 | 0.0 |
| 75° | 48.8 | 24.4 | 9.8 | 8.1 | 8.1 | 4.9 | 1.6 | 1.6 | 0.0 | 0.0 | 0.0 |
| 77.5° | 32.5 | 17.9 | 6.5 | 4.9 | 4.9 | 3.3 | 1.6 | 0.0 | 0.0 | 0.0 | 0.0 |
| 80° | 26.0 | 9.8 | 3.3 | 3.3 | 3.3 | 1.6 | 1.6 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 22.8 | 6.5 | 1.6 | 1.6 | 1.6 | 1.6 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 11.4 | 3.3 | 1.6 | 1.6 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 1.6 | 1.6 | 1.6 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-121-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 03/05/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: **IFLD-S-SA2A-740-U-T3R-HSS**
 Description: STREETWORKS INF FLOOD

SHIELD, DRIVER PROGRAMMED @ 615mA.

Spectral Parameters

| | | | | | |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K): | 3905 | CRI (Ra): | 71.2 | R9: | -29.7 |
| CIE u': | 0.2273 | R1: | 68.9 | R10: | 46.2 |
| CIE v': | 0.5024 | R2: | 77.0 | R11: | 68.8 |
| Duv: | -0.0008 | R3: | 84.0 | R12: | 45.6 |
| CIE x: | 0.3841 | R4: | 71.6 | R13: | 69.5 |
| CIE y: | 0.3774 | R5: | 68.9 | R14: | 90.7 |
| CIE z: | 0.2385 | R6: | 68.3 | | |
| Peak Wavelength (nm): | 443 | R7: | 78.7 | | |
| Dominant Wavelength (nm): | 579 | R8: | 52.2 | | |
| Purity: | 28.7 | | | | |
| Rf: | 71.7 | | | | |
| Rg: | 96.9 | | | | |



Test Conditions

Stabilization Time: 211M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.8/312%
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-2

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 1/31/2021 | 7/31/2021 |
| Power Meter | IN0071 | 12/1/2020 | 12/1/2021 |
| AC Power Source | IN0063 | 12/1/2020 | 12/1/2021 |
| DC Power Source | IN0208 | 12/1/2020 | 12/1/2021 |
| Sphere Thermometer | IN0085 | 12/1/2020 | 12/1/2021 |
| Room Thermometer | IN0046 | 12/1/2020 | 12/1/2021 |

REPORT NUMBER: SP1-2101-121-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-2

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 2.7 | 620 | 97577 | 25.4 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 4.8 | 625 | 90158 | 19.9 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 8.0 | 630 | 82240 | 14.9 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 13.3 | 635 | 74361 | 11.2 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 20.2 | 640 | 66994 | 8.0 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 28.5 | 645 | 60405 | 5.8 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 37.4 | 650 | 53806 | 3.9 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 44.9 | 655 | 47610 | 2.7 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 52.6 | 660 | 42018 | 1.8 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.0 | 535 | 94097 | 58.4 | 665 | 36742 | 1.2 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.0 | 540 | 96845 | 63.1 | 670 | 32105 | 0.7 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.0 | 545 | 100829 | 67.1 | 675 | 27946 | 0.5 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 0.1 | 550 | 105648 | 71.8 | 680 | 24146 | 0.3 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 0.2 | 555 | 110017 | 75.1 | 685 | 21191 | 0.2 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 0.5 | 560 | 114586 | 77.9 | 690 | 18544 | 0.1 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 1.2 | 565 | 118987 | 79.1 | 695 | 16058 | 0.1 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 2.1 | 570 | 122326 | 79.5 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 2.9 | 575 | 125968 | 78.4 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 2.7 | 580 | 127613 | 75.8 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 2.0 | 585 | 129466 | 71.9 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 1.5 | 590 | 128813 | 66.6 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 1.3 | 595 | 126387 | 59.9 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 1.0 | 600 | 123477 | 53.2 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 1.1 | 605 | 118718 | 46.0 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 1.2 | 610 | 112091 | 38.5 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 1.7 | 615 | 105039 | 31.7 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-2

Scotopic Flux vs. Wavelength



Scotopic Lumens: 10425.8 S/P: 1.47

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 29.3 | 620 | 97577 | 1.2 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 43.0 | 625 | 90158 | 0.8 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 60.8 | 630 | 82240 | 0.5 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 81.1 | 635 | 74361 | 0.3 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 99.6 | 640 | 66994 | 0.2 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 113.9 | 645 | 60405 | 0.1 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 122.6 | 650 | 53806 | 0.1 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 125.0 | 655 | 47610 | 0.0 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 123.1 | 660 | 42018 | 0.0 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.1 | 535 | 94097 | 117.3 | 665 | 36742 | 0.0 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.2 | 540 | 96845 | 107.0 | 670 | 32105 | 0.0 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.9 | 545 | 100829 | 96.7 | 675 | 27946 | 0.0 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 3.0 | 550 | 105648 | 86.4 | 680 | 24146 | 0.0 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 9.3 | 555 | 110017 | 75.2 | 685 | 21191 | 0.0 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 23.0 | 560 | 114586 | 64.0 | 690 | 18544 | 0.0 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 45.7 | 565 | 118987 | 53.4 | 695 | 16058 | 0.0 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 75.5 | 570 | 122326 | 43.2 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 93.8 | 575 | 125968 | 34.3 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 79.3 | 580 | 127613 | 26.3 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 51.3 | 585 | 129466 | 19.8 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 35.6 | 590 | 128813 | 14.3 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 26.0 | 595 | 126387 | 10.1 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 19.3 | 600 | 123477 | 7.0 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 16.8 | 605 | 118718 | 4.7 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 17.7 | 610 | 112091 | 3.0 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 21.4 | 615 | 105039 | 1.9 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: 3927.2 M/P: 0.55

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 15.8 | 620 | 97577 | 0.1 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 22.0 | 625 | 90158 | 0.0 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 29.2 | 630 | 82240 | 0.0 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 36.6 | 635 | 74361 | 0.0 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 42.2 | 640 | 66994 | 0.0 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 44.9 | 645 | 60405 | 0.0 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 44.9 | 650 | 53806 | 0.0 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 42.4 | 655 | 47610 | 0.0 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 38.6 | 660 | 42018 | 0.0 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.0 | 535 | 94097 | 33.9 | 665 | 36742 | 0.0 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.2 | 540 | 96845 | 28.3 | 670 | 32105 | 0.0 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.6 | 545 | 100829 | 23.4 | 675 | 27946 | 0.0 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 2.1 | 550 | 105648 | 19.0 | 680 | 24146 | 0.0 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 5.9 | 555 | 110017 | 14.8 | 685 | 21191 | 0.0 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 14.3 | 560 | 114586 | 11.3 | 690 | 18544 | 0.0 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 27.3 | 565 | 118987 | 8.4 | 695 | 16058 | 0.0 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 45.1 | 570 | 122326 | 6.0 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 55.3 | 575 | 125968 | 4.2 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 47.2 | 580 | 127613 | 2.9 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 30.8 | 585 | 129466 | 1.9 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 21.7 | 590 | 128813 | 1.3 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 16.1 | 595 | 126387 | 0.8 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 12.0 | 600 | 123477 | 0.5 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 10.3 | 605 | 118718 | 0.3 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 10.5 | 610 | 112091 | 0.2 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 12.1 | 615 | 105039 | 0.1 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

Summary

$R_f = 71.7$
 $R_g = 96.9$
 CIE $R_a = 71.2$
 $R_g = -29.7$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 55 | CES51 = 86 | CES76 = 45 |
| CES02 = 61 | CES27 = 80 | CES52 = 87 | CES77 = 68 |
| CES03 = 30 | CES28 = 79 | CES53 = 74 | CES78 = 49 |
| CES04 = 70 | CES29 = 51 | CES54 = 81 | CES79 = 77 |
| CES05 = 47 | CES30 = 60 | CES55 = 80 | CES80 = 75 |
| CES06 = 50 | CES31 = 56 | CES56 = 69 | CES81 = 75 |
| CES07 = 40 | CES32 = 52 | CES57 = 67 | CES82 = 90 |
| CES08 = 39 | CES33 = 62 | CES58 = 69 | CES83 = 85 |
| CES09 = 29 | CES34 = 65 | CES59 = 86 | CES84 = 87 |
| CES10 = 74 | CES35 = 81 | CES60 = 91 | CES85 = 83 |
| CES11 = 57 | CES36 = 92 | CES61 = 85 | CES86 = 72 |
| CES12 = 63 | CES37 = 74 | CES62 = 81 | CES87 = 77 |
| CES13 = 42 | CES38 = 69 | CES63 = 72 | CES88 = 77 |
| CES14 = 74 | CES39 = 92 | CES64 = 69 | CES89 = 72 |
| CES15 = 71 | CES40 = 86 | CES65 = 64 | CES90 = 75 |
| CES16 = 46 | CES41 = 84 | CES66 = 63 | CES91 = 91 |
| CES17 = 49 | CES42 = 75 | CES67 = 60 | CES92 = 66 |
| CES18 = 56 | CES43 = 70 | CES68 = 67 | CES93 = 80 |
| CES19 = 72 | CES44 = 98 | CES69 = 77 | CES94 = 56 |
| CES20 = 65 | CES45 = 80 | CES70 = 57 | CES95 = 72 |
| CES21 = 86 | CES46 = 77 | CES71 = 53 | CES96 = 78 |
| CES22 = 78 | CES47 = 74 | CES72 = 84 | CES97 = 83 |
| CES23 = 92 | CES48 = 66 | CES73 = 47 | CES98 = 73 |
| CES24 = 91 | CES49 = 76 | CES74 = 96 | CES99 = 63 |
| CES25 = 72 | CES50 = 85 | CES75 = 52 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)