

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P438547

Luminaire Tested: **ISW-SA1D-740-U-SLL**

Issue Date: 12/10/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P438547  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-074-20)  
Test Lab: INNOVATION CENTER  
Issue Date: 12/10/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: ISW-SA1D-740-U-SLL  
Description: IMPACT ELITE LED WEDGE LUMINAIRE  
(1) 70 CRI, 4000K, 800mA LIGHTSQUARE WITH 16 LEDS AND SPILL LIGHT  
ELIMINATOR LEFT OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5086 lumens  
Efficiency: N/A  
Efficacy: 112.5 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B1 - U0 - G1  
  
Input Watts (W): 45.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P438547  
 CATALOG NUMBER: ISW-SA1D-740-U-SLL

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 3.1 fc  
 Type IV - Short - N/A

REPORT NUMBER: P438547  
CATALOG NUMBER: ISW-SA1D-740-U-SLL

### Luminous Intensity Polar Plot



— Vertical Plane Through 85-Deg Lateral      - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P438547  
 CATALOG NUMBER: ISW-SA1D-740-U-SLL


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 995.3    | 0.0    | 995.3  |
|                    | % Fixture | 19.6     | 0.0    | 19.6   |
| <b>Street Side</b> | Lumens    | 4090.6   | 0.0    | 4090.6 |
|                    | % Fixture | 80.4     | 0.0    | 80.4   |
| <b>Total</b>       | Lumens    | 5086.0   | 0.0    | 5086.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 122.4  | 2.4       |
| 10°-20°   | 254.4  | 5.0       |
| 20°-30°   | 365.8  | 7.2       |
| 30°-40°   | 525.2  | 10.3      |
| 40°-50°   | 743.5  | 14.6      |
| 50°-60°   | 1033.8 | 20.3      |
| 60°-70°   | 1231.0 | 24.2      |
| 70°-80°   | 711.5  | 14.0      |
| 80°-90°   | 98.4   | 1.9       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 5086.0 | 100.0     |
| 0°-180°   | 5086.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P438547


CATALOG NUMBER: ISW-SA1D-740-U-SLL

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 506.8  | 10.0      |                         |      |         |
| FM (30°-60°)   | 1836.1 | 36.1      |                         |      |         |
| FH (60°-80°)   | 1665.4 | 32.7      |                         |      | G1/1800 |
| FVH (80°-90°)  | 82.3   | 1.6       |                         |      | G1/100  |
| BL (0°-30°)    | 235.8  | 4.6       | B1/500                  |      |         |
| BM (30°-60°)   | 466.4  | 9.2       | B1/1000                 |      |         |
| BH (60°-80°)   | 277.1  | 5.4       | B1/500                  |      | G1/500  |
| BVH (80°-90°)  | 16.1   | 0.3       |                         |      | G1/100  |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B1-U0-G1**

Type IV Short





REPORT NUMBER: P438547

CATALOG NUMBER: ISW-SA1D-740-U-SLL

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 1°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1606.7 | 1606.7 | 1606.7 | 1606.7 | 1606.7 | 1606.7 | 1606.7 | 1606.7 | 1606.7 | 1606.7 | 1606.7 |
| 2.5°  | 1683.6 | 1689.9 | 1704.4 | 1754.3 | 1785.5 | 1810.4 | 1841.6 | 1810.4 | 1802.1 | 1760.5 | 1752.2 |
| 5°    | 1623.3 | 1637.9 | 1679.5 | 1773.0 | 1849.9 | 1931.0 | 1972.5 | 1937.2 | 1889.4 | 1816.6 | 1743.9 |
| 7.5°  | 1504.9 | 1523.6 | 1577.6 | 1723.1 | 1868.6 | 1978.8 | 2032.8 | 1995.4 | 1897.7 | 1768.8 | 1637.9 |
| 10°   | 1384.3 | 1413.4 | 1477.8 | 1660.8 | 1814.6 | 1937.2 | 2020.3 | 1980.9 | 1862.4 | 1694.0 | 1538.1 |
| 12.5° | 1311.6 | 1332.3 | 1405.1 | 1596.3 | 1758.5 | 1881.1 | 1943.4 | 1920.6 | 1810.4 | 1650.4 | 1484.1 |
| 15°   | 1294.9 | 1315.7 | 1388.5 | 1573.5 | 1716.9 | 1808.3 | 1822.9 | 1829.1 | 1787.6 | 1664.9 | 1498.6 |
| 17.5° | 1340.7 | 1357.3 | 1457.1 | 1610.9 | 1669.1 | 1687.8 | 1710.6 | 1737.7 | 1758.5 | 1694.0 | 1558.9 |
| 20°   | 1450.8 | 1484.1 | 1571.4 | 1687.8 | 1656.6 | 1613.0 | 1625.4 | 1658.7 | 1737.7 | 1779.2 | 1698.2 |
| 22.5° | 1598.4 | 1635.8 | 1746.0 | 1793.8 | 1664.9 | 1571.4 | 1561.0 | 1590.1 | 1735.6 | 1872.8 | 1864.5 |
| 25°   | 1762.6 | 1814.6 | 1933.0 | 1935.1 | 1700.3 | 1542.3 | 1521.5 | 1548.5 | 1731.4 | 1955.9 | 1997.5 |
| 27.5° | 1933.0 | 1980.9 | 2109.7 | 2045.3 | 1768.8 | 1544.4 | 1519.4 | 1546.4 | 1741.8 | 2045.3 | 2145.1 |
| 30°   | 2059.8 | 2122.2 | 2234.4 | 2149.2 | 1812.5 | 1571.4 | 1534.0 | 1569.3 | 1764.7 | 2091.0 | 2276.0 |
| 32.5° | 2188.7 | 2228.2 | 2346.7 | 2209.5 | 1860.3 | 1613.0 | 1565.1 | 1619.2 | 1822.9 | 2134.7 | 2379.9 |
| 35°   | 2303.0 | 2355.0 | 2475.5 | 2244.8 | 1931.0 | 1683.6 | 1621.3 | 1691.9 | 1906.0 | 2197.0 | 2485.9 |
| 37.5° | 2448.5 | 2498.4 | 2608.6 | 2294.7 | 1989.2 | 1773.0 | 1721.0 | 1812.5 | 2007.9 | 2253.1 | 2627.3 |
| 40°   | 2577.4 | 2656.4 | 2739.5 | 2357.1 | 2055.7 | 1903.9 | 1870.7 | 1995.4 | 2145.1 | 2330.1 | 2764.5 |
| 42.5° | 2704.2 | 2770.7 | 2862.2 | 2427.7 | 2140.9 | 2064.0 | 2078.5 | 2209.5 | 2311.3 | 2446.4 | 2887.1 |
| 45°   | 2795.6 | 2872.6 | 2953.6 | 2483.9 | 2251.1 | 2236.5 | 2334.2 | 2444.4 | 2481.8 | 2569.1 | 2997.3 |
| 47.5° | 2885.0 | 2945.3 | 3018.0 | 2540.0 | 2384.1 | 2429.8 | 2600.3 | 2685.5 | 2648.1 | 2679.2 | 3084.6 |
| 50°   | 3003.5 | 3067.9 | 3088.7 | 2629.4 | 2552.5 | 2675.1 | 2860.1 | 2916.2 | 2808.1 | 2766.5 | 3176.0 |
| 52.5° | 3173.9 | 3205.1 | 3194.7 | 2735.4 | 2712.5 | 2930.8 | 3082.5 | 3167.7 | 2974.4 | 2849.7 | 3302.8 |
| 55°   | 3402.6 | 3456.6 | 3390.1 | 2907.9 | 2876.7 | 3176.0 | 3352.7 | 3394.3 | 3159.4 | 2953.6 | 3448.3 |
| 57.5° | 3620.8 | 3668.6 | 3647.8 | 3117.8 | 3090.8 | 3388.0 | 3558.5 | 3598.0 | 3340.2 | 3146.9 | 3614.6 |
| 60°   | 3701.9 | 3716.4 | 3791.3 | 3340.2 | 3304.9 | 3568.9 | 3762.2 | 3768.4 | 3556.4 | 3379.7 | 3884.8 |
| 62.5° | 3614.6 | 3672.8 | 3745.5 | 3548.1 | 3433.8 | 3724.8 | 3897.3 | 3936.8 | 3762.2 | 3662.4 | 4032.4 |
| 65°   | 3452.5 | 3504.4 | 3589.7 | 3687.3 | 3531.5 | 3762.2 | 3924.3 | 3974.2 | 3895.2 | 3959.6 | 4096.8 |
| 67.5° | 3265.4 | 3329.8 | 3388.0 | 3710.2 | 3519.0 | 3548.1 | 3683.2 | 3714.4 | 3824.5 | 4090.6 | 3978.3 |
| 70°   | 3024.3 | 3097.0 | 3146.9 | 3620.8 | 3221.7 | 2932.8 | 3028.4 | 3113.7 | 3282.0 | 3857.8 | 3701.9 |
| 72.5° | 2504.6 | 2621.0 | 2745.8 | 3215.5 | 2606.5 | 2278.1 | 2352.9 | 2409.0 | 2529.6 | 3294.5 | 3223.8 |
| 75°   | 1762.6 | 1847.8 | 2001.6 | 2589.9 | 2001.6 | 1613.0 | 1729.4 | 1729.4 | 1881.1 | 2706.3 | 2448.5 |
| 77.5° | 1053.8 | 1055.9 | 1205.6 | 1704.4 | 1218.0 | 1087.1 | 1153.6 | 1184.8 | 1230.5 | 1916.4 | 1625.4 |
| 80°   | 596.5  | 604.9  | 654.7  | 1101.6 | 721.3  | 742.0  | 821.0  | 904.2  | 835.6  | 1188.9 | 1045.5 |
| 82.5° | 278.5  | 245.3  | 259.8  | 519.6  | 409.5  | 484.3  | 496.8  | 534.2  | 538.3  | 760.7  | 685.9  |
| 85°   | 22.9   | 18.7   | 24.9   | 93.5   | 72.7   | 66.5   | 47.8   | 91.5   | 143.4  | 332.6  | 295.2  |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P438547  
 CATALOG NUMBER: ISW-SA1D-740-U-SLL

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1606.7 | 1606.7 | 1606.7 | 1606.7 | 1606.7 | 1606.7 | 1606.7 | 1606.7 | 1606.7 | 1606.7 | 1606.7 |
| 2.5°  | 1725.2 | 1704.4 | 1658.7 | 1623.3 | 1590.1 | 1527.7 | 1502.8 | 1467.5 | 1448.7 | 1415.5 | 1423.8 |
| 5°    | 1689.9 | 1642.1 | 1538.1 | 1467.5 | 1376.0 | 1301.2 | 1255.4 | 1213.9 | 1197.2 | 1161.9 | 1149.4 |
| 7.5°  | 1561.0 | 1519.4 | 1388.5 | 1272.1 | 1159.8 | 1070.5 | 985.2  | 922.9  | 893.8  | 862.6  | 860.5  |
| 10°   | 1450.8 | 1382.2 | 1232.6 | 1095.4 | 966.5  | 883.4  | 821.0  | 769.1  | 723.3  | 683.8  | 661.0  |
| 12.5° | 1388.5 | 1303.2 | 1137.0 | 970.7  | 881.3  | 823.1  | 754.5  | 690.1  | 638.1  | 592.4  | 565.4  |
| 15°   | 1388.5 | 1288.7 | 1091.2 | 929.1  | 839.7  | 752.4  | 673.4  | 606.9  | 538.3  | 484.3  | 467.7  |
| 17.5° | 1452.9 | 1330.3 | 1101.6 | 902.1  | 775.3  | 677.6  | 577.8  | 490.5  | 424.0  | 376.2  | 359.6  |
| 20°   | 1579.7 | 1432.1 | 1126.6 | 870.9  | 712.9  | 577.8  | 457.3  | 363.7  | 303.5  | 280.6  | 276.4  |
| 22.5° | 1727.3 | 1554.8 | 1164.0 | 841.8  | 648.5  | 471.8  | 343.0  | 276.4  | 249.4  | 241.1  | 241.1  |
| 25°   | 1889.4 | 1691.9 | 1211.8 | 810.6  | 582.0  | 374.1  | 261.9  | 230.7  | 220.3  | 216.2  | 216.2  |
| 27.5° | 2041.1 | 1841.6 | 1297.0 | 798.2  | 519.6  | 303.5  | 228.6  | 205.8  | 199.5  | 195.4  | 197.5  |
| 30°   | 2188.7 | 1974.6 | 1384.3 | 773.2  | 451.0  | 264.0  | 205.8  | 189.1  | 180.8  | 178.8  | 180.8  |
| 32.5° | 2315.5 | 2088.9 | 1444.6 | 735.8  | 403.2  | 237.0  | 191.2  | 174.6  | 166.3  | 164.2  | 166.3  |
| 35°   | 2461.0 | 2201.2 | 1504.9 | 708.8  | 378.3  | 220.3  | 180.8  | 164.2  | 155.9  | 151.7  | 151.7  |
| 37.5° | 2631.4 | 2336.3 | 1550.6 | 669.3  | 361.7  | 203.7  | 172.5  | 155.9  | 145.5  | 141.3  | 141.3  |
| 40°   | 2860.1 | 2500.5 | 1588.0 | 638.1  | 343.0  | 195.4  | 162.1  | 147.6  | 137.2  | 133.0  | 130.9  |
| 42.5° | 3018.0 | 2643.9 | 1619.2 | 617.3  | 324.3  | 191.2  | 155.9  | 143.4  | 130.9  | 124.7  | 122.6  |
| 45°   | 3126.1 | 2770.7 | 1640.0 | 606.9  | 307.6  | 180.8  | 151.7  | 139.3  | 124.7  | 116.4  | 116.4  |
| 47.5° | 3230.1 | 2874.6 | 1642.1 | 592.4  | 295.2  | 168.4  | 158.0  | 133.0  | 118.5  | 110.2  | 110.2  |
| 50°   | 3346.5 | 3005.6 | 1681.5 | 577.8  | 280.6  | 153.8  | 155.9  | 130.9  | 114.3  | 106.0  | 103.9  |
| 52.5° | 3462.9 | 3184.3 | 1758.5 | 557.1  | 259.8  | 141.3  | 147.6  | 133.0  | 110.2  | 101.8  | 99.8   |
| 55°   | 3670.7 | 3406.7 | 1854.1 | 525.9  | 232.8  | 128.9  | 137.2  | 130.9  | 103.9  | 95.6   | 93.5   |
| 57.5° | 3805.8 | 3614.6 | 1928.9 | 492.6  | 193.3  | 120.6  | 120.6  | 126.8  | 97.7   | 89.4   | 87.3   |
| 60°   | 3882.7 | 3654.1 | 1943.4 | 453.1  | 158.0  | 108.1  | 103.9  | 128.9  | 91.5   | 81.1   | 81.1   |
| 62.5° | 3880.6 | 3519.0 | 1870.7 | 415.7  | 137.2  | 99.8   | 93.5   | 112.2  | 85.2   | 76.9   | 74.8   |
| 65°   | 3841.2 | 3319.4 | 1706.5 | 367.9  | 128.9  | 91.5   | 83.1   | 85.2   | 79.0   | 70.7   | 68.6   |
| 67.5° | 3670.7 | 2974.4 | 1444.6 | 320.1  | 124.7  | 83.1   | 76.9   | 72.7   | 68.6   | 62.4   | 60.3   |
| 70°   | 3257.1 | 2585.7 | 1126.6 | 297.2  | 122.6  | 72.7   | 66.5   | 62.4   | 58.2   | 54.0   | 54.0   |
| 72.5° | 2648.1 | 2016.2 | 860.5  | 284.8  | 124.7  | 66.5   | 56.1   | 54.0   | 49.9   | 47.8   | 45.7   |
| 75°   | 1833.3 | 1490.3 | 623.6  | 251.5  | 120.6  | 56.1   | 47.8   | 43.6   | 41.6   | 37.4   | 37.4   |
| 77.5° | 1178.5 | 974.8  | 413.6  | 201.6  | 97.7   | 45.7   | 35.3   | 33.3   | 31.2   | 29.1   | 29.1   |
| 80°   | 775.3  | 663.1  | 241.1  | 143.4  | 60.3   | 31.2   | 24.9   | 24.9   | 22.9   | 18.7   | 18.7   |
| 82.5° | 492.6  | 500.9  | 124.7  | 66.5   | 35.3   | 18.7   | 14.5   | 12.5   | 12.5   | 8.3    | 8.3    |
| 85°   | 108.1  | 189.1  | 56.1   | 27.0   | 12.5   | 2.1    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |





REPORT NUMBER: P438547  
 CATALOG NUMBER: ISW-SA1D-740-U-SLL

**CANDELA DISTRIBUTION (continued):**

|       | 185°   | 195°   | 205°   | 215°   | 225°   | 235°   | 245°   | 255°   | 265°   | 270°   | 275°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1606.7 | 1606.7 | 1606.7 | 1606.7 | 1606.7 | 1606.7 | 1606.7 | 1606.7 | 1606.7 | 1606.7 | 1606.7 |
| 2.5°  | 1394.7 | 1378.1 | 1371.8 | 1371.8 | 1344.8 | 1346.9 | 1346.9 | 1363.5 | 1361.4 | 1376.0 | 1369.8 |
| 5°    | 1134.9 | 1118.3 | 1118.3 | 1122.4 | 1126.6 | 1107.9 | 1114.1 | 1097.5 | 1128.7 | 1105.8 | 1089.2 |
| 7.5°  | 837.7  | 835.6  | 850.1  | 883.4  | 877.1  | 870.9  | 858.4  | 827.3  | 810.6  | 827.3  | 818.9  |
| 10°   | 642.3  | 648.5  | 644.3  | 658.9  | 661.0  | 658.9  | 638.1  | 631.9  | 623.6  | 631.9  | 642.3  |
| 12.5° | 538.3  | 513.4  | 486.4  | 484.3  | 500.9  | 500.9  | 498.9  | 500.9  | 507.2  | 507.2  | 515.5  |
| 15°   | 449.0  | 432.3  | 397.0  | 380.4  | 392.8  | 384.5  | 386.6  | 394.9  | 401.2  | 409.5  | 405.3  |
| 17.5° | 357.5  | 343.0  | 326.3  | 315.9  | 322.2  | 315.9  | 313.9  | 311.8  | 311.8  | 309.7  | 318.0  |
| 20°   | 272.3  | 270.2  | 276.4  | 272.3  | 274.4  | 270.2  | 264.0  | 255.7  | 249.4  | 253.6  | 257.7  |
| 22.5° | 237.0  | 239.0  | 243.2  | 247.3  | 247.3  | 243.2  | 232.8  | 224.5  | 222.4  | 222.4  | 224.5  |
| 25°   | 218.2  | 218.2  | 224.5  | 226.6  | 228.6  | 222.4  | 209.9  | 203.7  | 203.7  | 203.7  | 203.7  |
| 27.5° | 197.5  | 201.6  | 205.8  | 209.9  | 212.0  | 205.8  | 195.4  | 189.1  | 189.1  | 187.1  | 185.0  |
| 30°   | 182.9  | 185.0  | 189.1  | 191.2  | 193.3  | 187.1  | 180.8  | 174.6  | 174.6  | 174.6  | 172.5  |
| 32.5° | 166.3  | 172.5  | 174.6  | 176.7  | 178.8  | 174.6  | 168.4  | 164.2  | 162.1  | 160.0  | 155.9  |
| 35°   | 153.8  | 155.9  | 162.1  | 162.1  | 164.2  | 162.1  | 158.0  | 153.8  | 147.6  | 145.5  | 145.5  |
| 37.5° | 141.3  | 141.3  | 145.5  | 149.7  | 153.8  | 151.7  | 145.5  | 139.3  | 137.2  | 137.2  | 137.2  |
| 40°   | 133.0  | 130.9  | 133.0  | 139.3  | 143.4  | 143.4  | 135.1  | 130.9  | 130.9  | 128.9  | 128.9  |
| 42.5° | 122.6  | 122.6  | 122.6  | 128.9  | 137.2  | 133.0  | 124.7  | 124.7  | 124.7  | 122.6  | 122.6  |
| 45°   | 116.4  | 114.3  | 116.4  | 116.4  | 126.8  | 120.6  | 118.5  | 116.4  | 118.5  | 116.4  | 118.5  |
| 47.5° | 108.1  | 108.1  | 108.1  | 110.2  | 116.4  | 112.2  | 110.2  | 110.2  | 112.2  | 112.2  | 112.2  |
| 50°   | 101.8  | 101.8  | 101.8  | 103.9  | 106.0  | 106.0  | 106.0  | 106.0  | 106.0  | 108.1  | 108.1  |
| 52.5° | 97.7   | 95.6   | 97.7   | 97.7   | 99.8   | 101.8  | 99.8   | 101.8  | 101.8  | 101.8  | 103.9  |
| 55°   | 93.5   | 91.5   | 93.5   | 93.5   | 97.7   | 95.6   | 95.6   | 97.7   | 97.7   | 99.8   | 101.8  |
| 57.5° | 87.3   | 85.2   | 89.4   | 89.4   | 93.5   | 93.5   | 91.5   | 93.5   | 93.5   | 95.6   | 95.6   |
| 60°   | 81.1   | 81.1   | 83.1   | 83.1   | 87.3   | 89.4   | 89.4   | 89.4   | 89.4   | 89.4   | 89.4   |
| 62.5° | 74.8   | 74.8   | 76.9   | 79.0   | 83.1   | 83.1   | 85.2   | 85.2   | 85.2   | 85.2   | 83.1   |
| 65°   | 68.6   | 70.7   | 72.7   | 72.7   | 76.9   | 79.0   | 79.0   | 79.0   | 79.0   | 79.0   | 79.0   |
| 67.5° | 60.3   | 64.4   | 66.5   | 68.6   | 72.7   | 72.7   | 74.8   | 74.8   | 72.7   | 72.7   | 72.7   |
| 70°   | 54.0   | 56.1   | 58.2   | 60.3   | 66.5   | 66.5   | 68.6   | 68.6   | 66.5   | 66.5   | 68.6   |
| 72.5° | 45.7   | 47.8   | 49.9   | 54.0   | 60.3   | 60.3   | 62.4   | 62.4   | 60.3   | 60.3   | 60.3   |
| 75°   | 39.5   | 39.5   | 41.6   | 45.7   | 54.0   | 54.0   | 54.0   | 56.1   | 54.0   | 54.0   | 52.0   |
| 77.5° | 29.1   | 31.2   | 33.3   | 39.5   | 45.7   | 47.8   | 47.8   | 47.8   | 45.7   | 45.7   | 43.6   |
| 80°   | 18.7   | 20.8   | 24.9   | 29.1   | 35.3   | 37.4   | 39.5   | 39.5   | 37.4   | 37.4   | 35.3   |
| 82.5° | 8.3    | 12.5   | 14.5   | 18.7   | 22.9   | 29.1   | 29.1   | 31.2   | 29.1   | 27.0   | 27.0   |
| 85°   | 0.0    | 0.0    | 2.1    | 6.2    | 10.4   | 16.6   | 18.7   | 20.8   | 18.7   | 16.6   | 16.6   |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 4.2    | 4.2    | 4.2    | 2.1    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P438547  
 CATALOG NUMBER: ISW-SA1D-740-U-SLL

**CANDELA DISTRIBUTION (continued):**

|       | 285°   | 295°   | 305°   | 315°   | 325°   | 335°   | 345°   | 355°   | 359°   | 360°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1606.7 | 1606.7 | 1606.7 | 1606.7 | 1606.7 | 1606.7 | 1606.7 | 1606.7 | 1606.7 | 1606.7 |
| 2.5°  | 1392.6 | 1415.5 | 1450.8 | 1471.6 | 1519.4 | 1563.1 | 1608.8 | 1669.1 | 1681.5 | 1683.6 |
| 5°    | 1105.8 | 1132.8 | 1199.3 | 1226.3 | 1313.6 | 1384.3 | 1488.2 | 1590.1 | 1617.1 | 1623.3 |
| 7.5°  | 843.9  | 864.7  | 937.4  | 989.4  | 1085.0 | 1184.8 | 1317.8 | 1438.4 | 1498.6 | 1504.9 |
| 10°   | 658.9  | 715.0  | 771.1  | 848.0  | 931.2  | 1028.9 | 1168.1 | 1322.0 | 1388.5 | 1384.3 |
| 12.5° | 555.0  | 613.2  | 681.8  | 758.7  | 843.9  | 931.2  | 1058.0 | 1228.4 | 1294.9 | 1311.6 |
| 15°   | 444.8  | 515.5  | 590.3  | 669.3  | 769.1  | 854.3  | 1001.9 | 1191.0 | 1272.1 | 1294.9 |
| 17.5° | 345.0  | 401.2  | 473.9  | 575.8  | 673.4  | 794.0  | 981.1  | 1226.3 | 1317.8 | 1340.7 |
| 20°   | 272.3  | 313.9  | 365.8  | 463.5  | 588.2  | 737.9  | 970.7  | 1292.9 | 1417.6 | 1450.8 |
| 22.5° | 232.8  | 249.4  | 286.8  | 372.1  | 503.0  | 677.6  | 964.4  | 1386.4 | 1542.3 | 1598.4 |
| 25°   | 207.9  | 218.2  | 239.0  | 293.1  | 417.8  | 625.6  | 974.8  | 1502.8 | 1716.9 | 1762.6 |
| 27.5° | 189.1  | 197.5  | 207.9  | 247.3  | 361.7  | 579.9  | 993.5  | 1633.7 | 1866.5 | 1933.0 |
| 30°   | 172.5  | 178.8  | 193.3  | 220.3  | 315.9  | 534.2  | 999.8  | 1762.6 | 1999.6 | 2059.8 |
| 32.5° | 160.0  | 168.4  | 180.8  | 203.7  | 288.9  | 503.0  | 983.2  | 1860.3 | 2122.2 | 2188.7 |
| 35°   | 147.6  | 158.0  | 170.4  | 189.1  | 266.1  | 476.0  | 945.7  | 1941.4 | 2238.6 | 2303.0 |
| 37.5° | 141.3  | 147.6  | 160.0  | 174.6  | 249.4  | 449.0  | 912.5  | 2022.4 | 2359.2 | 2448.5 |
| 40°   | 133.0  | 139.3  | 151.7  | 164.2  | 228.6  | 419.9  | 889.6  | 2126.4 | 2496.3 | 2577.4 |
| 42.5° | 126.8  | 135.1  | 145.5  | 160.0  | 212.0  | 388.7  | 866.8  | 2209.5 | 2619.0 | 2704.2 |
| 45°   | 122.6  | 130.9  | 141.3  | 160.0  | 197.5  | 363.7  | 841.8  | 2282.2 | 2712.5 | 2795.6 |
| 47.5° | 116.4  | 126.8  | 141.3  | 153.8  | 191.2  | 347.1  | 841.8  | 2369.5 | 2797.7 | 2885.0 |
| 50°   | 114.3  | 124.7  | 147.6  | 149.7  | 187.1  | 340.9  | 877.1  | 2469.3 | 2920.4 | 3003.5 |
| 52.5° | 112.2  | 122.6  | 147.6  | 141.3  | 182.9  | 345.0  | 931.2  | 2650.1 | 3078.3 | 3173.9 |
| 55°   | 106.0  | 120.6  | 141.3  | 130.9  | 172.5  | 349.2  | 991.5  | 2887.1 | 3313.2 | 3402.6 |
| 57.5° | 101.8  | 118.5  | 133.0  | 120.6  | 158.0  | 343.0  | 1072.5 | 3099.1 | 3558.5 | 3620.8 |
| 60°   | 95.6   | 116.4  | 116.4  | 112.2  | 141.3  | 324.3  | 1164.0 | 3234.2 | 3652.0 | 3701.9 |
| 62.5° | 91.5   | 114.3  | 103.9  | 103.9  | 128.9  | 295.2  | 1195.2 | 3201.0 | 3560.6 | 3614.6 |
| 65°   | 85.2   | 99.8   | 93.5   | 95.6   | 118.5  | 261.9  | 1141.1 | 2993.1 | 3388.0 | 3452.5 |
| 67.5° | 79.0   | 85.2   | 83.1   | 87.3   | 114.3  | 228.6  | 995.6  | 2745.8 | 3165.6 | 3265.4 |
| 70°   | 70.7   | 74.8   | 74.8   | 79.0   | 108.1  | 205.8  | 831.4  | 2427.7 | 2876.7 | 3024.3 |
| 72.5° | 64.4   | 66.5   | 66.5   | 72.7   | 101.8  | 193.3  | 656.8  | 2059.8 | 2413.2 | 2504.6 |
| 75°   | 54.0   | 58.2   | 58.2   | 62.4   | 91.5   | 164.2  | 449.0  | 1509.0 | 1687.8 | 1762.6 |
| 77.5° | 47.8   | 47.8   | 49.9   | 52.0   | 72.7   | 110.2  | 264.0  | 929.1  | 1014.3 | 1053.8 |
| 80°   | 37.4   | 39.5   | 37.4   | 37.4   | 45.7   | 72.7   | 143.4  | 544.6  | 617.3  | 596.5  |
| 82.5° | 27.0   | 27.0   | 22.9   | 22.9   | 27.0   | 39.5   | 62.4   | 282.7  | 288.9  | 278.5  |
| 85°   | 14.5   | 10.4   | 8.3    | 8.3    | 8.3    | 8.3    | 8.3    | 60.3   | 29.1   | 22.9   |
| 87.5° | 0.0    | 0.0    | 0.0    | 2.1    | 2.1    | 2.1    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



**Test Information**

Test Method: LM-79-08  
 Report Number: SP1-2101-121-2  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry: 4π  
 Issue Date: 03/05/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: **IFLD-S-SA2A-740-U-T3R-HSS**  
 Description: STREETWORKS INF FLOOD

SHIELD, DRIVER PROGRAMMED @ 615mA.

**Spectral Parameters**

|                           |         |           |      |      |       |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K):                  | 3905    | CRI (Ra): | 71.2 | R9:  | -29.7 |
| CIE u':                   | 0.2273  | R1:       | 68.9 | R10: | 46.2  |
| CIE v':                   | 0.5024  | R2:       | 77.0 | R11: | 68.8  |
| Duv:                      | -0.0008 | R3:       | 84.0 | R12: | 45.6  |
| CIE x:                    | 0.3841  | R4:       | 71.6 | R13: | 69.5  |
| CIE y:                    | 0.3774  | R5:       | 68.9 | R14: | 90.7  |
| CIE z:                    | 0.2385  | R6:       | 68.3 |      |       |
| Peak Wavelength (nm):     | 443     | R7:       | 78.7 |      |       |
| Dominant Wavelength (nm): | 579     | R8:       | 52.2 |      |       |
| Purity:                   | 28.7    |           |      |      |       |
| Rf:                       | 71.7    |           |      |      |       |
| Rg:                       | 96.9    |           |      |      |       |



**Test Conditions**

Stabilization Time: 211M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 24.8/312%  
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-2

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2101-121-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 3905K  
 CIE x = 0.3841  
 CIE y = 0.3774  
 Duv = -0.0008

Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-2

**Photopic Flux vs. Wavelength**



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2304          | 0.0           | 490    | 19043         | 2.7           | 620    | 97577         | 25.4          | 750    | 4830          | 0.0           | 880    | 3505          | 0.0           |
| 365    | 2150          | 0.0           | 495    | 26606         | 4.8           | 625    | 90158         | 19.9          | 755    | 4664          | 0.0           | 885    | 2991          | 0.0           |
| 370    | 2146          | 0.0           | 500    | 36376         | 8.0           | 630    | 82240         | 14.9          | 760    | 4006          | 0.0           | 890    | 2327          | 0.0           |
| 375    | 2332          | 0.0           | 505    | 47714         | 13.3          | 635    | 74361         | 11.2          | 765    | 3715          | 0.0           | 895    | 2775          | 0.0           |
| 380    | 2527          | 0.0           | 510    | 58741         | 20.2          | 640    | 66994         | 8.0           | 770    | 3696          | 0.0           | 900    | 2141          | 0.0           |
| 385    | 2304          | 0.0           | 515    | 68716         | 28.5          | 645    | 60405         | 5.8           | 775    | 3117          | 0.0           | 905    | 2421          | 0.0           |
| 390    | 2064          | 0.0           | 520    | 77136         | 37.4          | 650    | 53806         | 3.9           | 780    | 3062          | 0.0           | 910    | 2200          | 0.0           |
| 395    | 1856          | 0.0           | 525    | 83567         | 44.9          | 655    | 47610         | 2.7           | 785    | 2907          | 0.0           | 915    | 2716          | 0.0           |
| 400    | 1856          | 0.0           | 530    | 89283         | 52.6          | 660    | 42018         | 1.8           | 790    | 2655          | 0.0           | 920    | 2656          | 0.0           |
| 405    | 2374          | 0.0           | 535    | 94097         | 58.4          | 665    | 36742         | 1.2           | 795    | 2467          | 0.0           | 925    | 2671          | 0.0           |
| 410    | 4084          | 0.0           | 540    | 96845         | 63.1          | 670    | 32105         | 0.7           | 800    | 2609          | 0.0           | 930    | 3292          | 0.0           |
| 415    | 8543          | 0.0           | 545    | 100829        | 67.1          | 675    | 27946         | 0.5           | 805    | 2293          | 0.0           | 935    | 3188          | 0.0           |
| 420    | 18394         | 0.1           | 550    | 105648        | 71.8          | 680    | 24146         | 0.3           | 810    | 2188          | 0.0           | 940    | 1997          | 0.0           |
| 425    | 37987         | 0.2           | 555    | 110017        | 75.1          | 685    | 21191         | 0.2           | 815    | 2386          | 0.0           | 945    | 2623          | 0.0           |
| 430    | 67605         | 0.5           | 560    | 114586        | 77.9          | 690    | 18544         | 0.1           | 820    | 2712          | 0.0           | 950    | 2969          | 0.0           |
| 435    | 102160        | 1.2           | 565    | 118987        | 79.1          | 695    | 16058         | 0.1           | 825    | 2473          | 0.0           | 955    | 2277          | 0.0           |
| 440    | 135103        | 2.1           | 570    | 122326        | 79.5          | 700    | 14133         | 0.0           | 830    | 1969          | 0.0           | 960    | 4267          | 0.0           |
| 445    | 140126        | 2.9           | 575    | 125968        | 78.4          | 705    | 12309         | 0.0           | 835    | 1917          | 0.0           | 965    | 2034          | 0.0           |
| 450    | 102339        | 2.7           | 580    | 127613        | 75.8          | 710    | 11142         | 0.0           | 840    | 2248          | 0.0           | 970    | 3586          | 0.0           |
| 455    | 58751         | 2.0           | 585    | 129466        | 71.9          | 715    | 10143         | 0.0           | 845    | 2266          | 0.0           | 975    | 2505          | 0.0           |
| 460    | 36892         | 1.5           | 590    | 128813        | 66.6          | 720    | 9072          | 0.0           | 850    | 2558          | 0.0           | 980    | 2666          | 0.0           |
| 465    | 24637         | 1.3           | 595    | 126387        | 59.9          | 725    | 8130          | 0.0           | 855    | 2767          | 0.0           | 985    | 2934          | 0.0           |
| 470    | 16738         | 1.0           | 600    | 123477        | 53.2          | 730    | 7149          | 0.0           | 860    | 2826          | 0.0           | 990    | 4120          | 0.0           |
| 475    | 13456         | 1.1           | 605    | 118718        | 46.0          | 735    | 6311          | 0.0           | 865    | 2385          | 0.0           | 995    | 3858          | 0.0           |
| 480    | 13081         | 1.2           | 610    | 112091        | 38.5          | 740    | 5711          | 0.0           | 870    | 3194          | 0.0           | 1000   | 3405          | 0.0           |
| 485    | 14734         | 1.7           | 615    | 105039        | 31.7          | 745    | 5111          | 0.0           | 875    | 3189          | 0.0           |        |               |               |

REPORT NUMBER: SP1-2101-121-2

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: 10425.8 S/P: 1.47**

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 2304                                 | 0.0                            | 490               | 19043                                | 29.3                           | 620               | 97577                                | 1.2                            | 750               | 4830                                 | 0.0                            | 880               | 3505                                 | 0.0                            |
| 365               | 2150                                 | 0.0                            | 495               | 26606                                | 43.0                           | 625               | 90158                                | 0.8                            | 755               | 4664                                 | 0.0                            | 885               | 2991                                 | 0.0                            |
| 370               | 2146                                 | 0.0                            | 500               | 36376                                | 60.8                           | 630               | 82240                                | 0.5                            | 760               | 4006                                 | 0.0                            | 890               | 2327                                 | 0.0                            |
| 375               | 2332                                 | 0.0                            | 505               | 47714                                | 81.1                           | 635               | 74361                                | 0.3                            | 765               | 3715                                 | 0.0                            | 895               | 2775                                 | 0.0                            |
| 380               | 2527                                 | 0.0                            | 510               | 58741                                | 99.6                           | 640               | 66994                                | 0.2                            | 770               | 3696                                 | 0.0                            | 900               | 2141                                 | 0.0                            |
| 385               | 2304                                 | 0.0                            | 515               | 68716                                | 113.9                          | 645               | 60405                                | 0.1                            | 775               | 3117                                 | 0.0                            | 905               | 2421                                 | 0.0                            |
| 390               | 2064                                 | 0.0                            | 520               | 77136                                | 122.6                          | 650               | 53806                                | 0.1                            | 780               | 3062                                 | 0.0                            | 910               | 2200                                 | 0.0                            |
| 395               | 1856                                 | 0.0                            | 525               | 83567                                | 125.0                          | 655               | 47610                                | 0.0                            | 785               | 2907                                 | 0.0                            | 915               | 2716                                 | 0.0                            |
| 400               | 1856                                 | 0.0                            | 530               | 89283                                | 123.1                          | 660               | 42018                                | 0.0                            | 790               | 2655                                 | 0.0                            | 920               | 2656                                 | 0.0                            |
| 405               | 2374                                 | 0.1                            | 535               | 94097                                | 117.3                          | 665               | 36742                                | 0.0                            | 795               | 2467                                 | 0.0                            | 925               | 2671                                 | 0.0                            |
| 410               | 4084                                 | 0.2                            | 540               | 96845                                | 107.0                          | 670               | 32105                                | 0.0                            | 800               | 2609                                 | 0.0                            | 930               | 3292                                 | 0.0                            |
| 415               | 8543                                 | 0.9                            | 545               | 100829                               | 96.7                           | 675               | 27946                                | 0.0                            | 805               | 2293                                 | 0.0                            | 935               | 3188                                 | 0.0                            |
| 420               | 18394                                | 3.0                            | 550               | 105648                               | 86.4                           | 680               | 24146                                | 0.0                            | 810               | 2188                                 | 0.0                            | 940               | 1997                                 | 0.0                            |
| 425               | 37987                                | 9.3                            | 555               | 110017                               | 75.2                           | 685               | 21191                                | 0.0                            | 815               | 2386                                 | 0.0                            | 945               | 2623                                 | 0.0                            |
| 430               | 67605                                | 23.0                           | 560               | 114586                               | 64.0                           | 690               | 18544                                | 0.0                            | 820               | 2712                                 | 0.0                            | 950               | 2969                                 | 0.0                            |
| 435               | 102160                               | 45.7                           | 565               | 118987                               | 53.4                           | 695               | 16058                                | 0.0                            | 825               | 2473                                 | 0.0                            | 955               | 2277                                 | 0.0                            |
| 440               | 135103                               | 75.5                           | 570               | 122326                               | 43.2                           | 700               | 14133                                | 0.0                            | 830               | 1969                                 | 0.0                            | 960               | 4267                                 | 0.0                            |
| 445               | 140126                               | 93.8                           | 575               | 125968                               | 34.3                           | 705               | 12309                                | 0.0                            | 835               | 1917                                 | 0.0                            | 965               | 2034                                 | 0.0                            |
| 450               | 102339                               | 79.3                           | 580               | 127613                               | 26.3                           | 710               | 11142                                | 0.0                            | 840               | 2248                                 | 0.0                            | 970               | 3586                                 | 0.0                            |
| 455               | 58751                                | 51.3                           | 585               | 129466                               | 19.8                           | 715               | 10143                                | 0.0                            | 845               | 2266                                 | 0.0                            | 975               | 2505                                 | 0.0                            |
| 460               | 36892                                | 35.6                           | 590               | 128813                               | 14.3                           | 720               | 9072                                 | 0.0                            | 850               | 2558                                 | 0.0                            | 980               | 2666                                 | 0.0                            |
| 465               | 24637                                | 26.0                           | 595               | 126387                               | 10.1                           | 725               | 8130                                 | 0.0                            | 855               | 2767                                 | 0.0                            | 985               | 2934                                 | 0.0                            |
| 470               | 16738                                | 19.3                           | 600               | 123477                               | 7.0                            | 730               | 7149                                 | 0.0                            | 860               | 2826                                 | 0.0                            | 990               | 4120                                 | 0.0                            |
| 475               | 13456                                | 16.8                           | 605               | 118718                               | 4.7                            | 735               | 6311                                 | 0.0                            | 865               | 2385                                 | 0.0                            | 995               | 3858                                 | 0.0                            |
| 480               | 13081                                | 17.7                           | 610               | 112091                               | 3.0                            | 740               | 5711                                 | 0.0                            | 870               | 3194                                 | 0.0                            | 1000              | 3405                                 | 0.0                            |
| 485               | 14734                                | 21.4                           | 615               | 105039                               | 1.9                            | 745               | 5111                                 | 0.0                            | 875               | 3189                                 | 0.0                            |                   |                                      |                                |



REPORT NUMBER: SP1-2101-121-2

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 3927.2 M/P: 0.55**


| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2304          | 0.0           | 490    | 19043         | 15.8          | 620    | 97577         | 0.1           | 750    | 4830          | 0.0           | 880    | 3505          | 0.0           |
| 365    | 2150          | 0.0           | 495    | 26606         | 22.0          | 625    | 90158         | 0.0           | 755    | 4664          | 0.0           | 885    | 2991          | 0.0           |
| 370    | 2146          | 0.0           | 500    | 36376         | 29.2          | 630    | 82240         | 0.0           | 760    | 4006          | 0.0           | 890    | 2327          | 0.0           |
| 375    | 2332          | 0.0           | 505    | 47714         | 36.6          | 635    | 74361         | 0.0           | 765    | 3715          | 0.0           | 895    | 2775          | 0.0           |
| 380    | 2527          | 0.0           | 510    | 58741         | 42.2          | 640    | 66994         | 0.0           | 770    | 3696          | 0.0           | 900    | 2141          | 0.0           |
| 385    | 2304          | 0.0           | 515    | 68716         | 44.9          | 645    | 60405         | 0.0           | 775    | 3117          | 0.0           | 905    | 2421          | 0.0           |
| 390    | 2064          | 0.0           | 520    | 77136         | 44.9          | 650    | 53806         | 0.0           | 780    | 3062          | 0.0           | 910    | 2200          | 0.0           |
| 395    | 1856          | 0.0           | 525    | 83567         | 42.4          | 655    | 47610         | 0.0           | 785    | 2907          | 0.0           | 915    | 2716          | 0.0           |
| 400    | 1856          | 0.0           | 530    | 89283         | 38.6          | 660    | 42018         | 0.0           | 790    | 2655          | 0.0           | 920    | 2656          | 0.0           |
| 405    | 2374          | 0.0           | 535    | 94097         | 33.9          | 665    | 36742         | 0.0           | 795    | 2467          | 0.0           | 925    | 2671          | 0.0           |
| 410    | 4084          | 0.2           | 540    | 96845         | 28.3          | 670    | 32105         | 0.0           | 800    | 2609          | 0.0           | 930    | 3292          | 0.0           |
| 415    | 8543          | 0.6           | 545    | 100829        | 23.4          | 675    | 27946         | 0.0           | 805    | 2293          | 0.0           | 935    | 3188          | 0.0           |
| 420    | 18394         | 2.1           | 550    | 105648        | 19.0          | 680    | 24146         | 0.0           | 810    | 2188          | 0.0           | 940    | 1997          | 0.0           |
| 425    | 37987         | 5.9           | 555    | 110017        | 14.8          | 685    | 21191         | 0.0           | 815    | 2386          | 0.0           | 945    | 2623          | 0.0           |
| 430    | 67605         | 14.3          | 560    | 114586        | 11.3          | 690    | 18544         | 0.0           | 820    | 2712          | 0.0           | 950    | 2969          | 0.0           |
| 435    | 102160        | 27.3          | 565    | 118987        | 8.4           | 695    | 16058         | 0.0           | 825    | 2473          | 0.0           | 955    | 2277          | 0.0           |
| 440    | 135103        | 45.1          | 570    | 122326        | 6.0           | 700    | 14133         | 0.0           | 830    | 1969          | 0.0           | 960    | 4267          | 0.0           |
| 445    | 140126        | 55.3          | 575    | 125968        | 4.2           | 705    | 12309         | 0.0           | 835    | 1917          | 0.0           | 965    | 2034          | 0.0           |
| 450    | 102339        | 47.2          | 580    | 127613        | 2.9           | 710    | 11142         | 0.0           | 840    | 2248          | 0.0           | 970    | 3586          | 0.0           |
| 455    | 58751         | 30.8          | 585    | 129466        | 1.9           | 715    | 10143         | 0.0           | 845    | 2266          | 0.0           | 975    | 2505          | 0.0           |
| 460    | 36892         | 21.7          | 590    | 128813        | 1.3           | 720    | 9072          | 0.0           | 850    | 2558          | 0.0           | 980    | 2666          | 0.0           |
| 465    | 24637         | 16.1          | 595    | 126387        | 0.8           | 725    | 8130          | 0.0           | 855    | 2767          | 0.0           | 985    | 2934          | 0.0           |
| 470    | 16738         | 12.0          | 600    | 123477        | 0.5           | 730    | 7149          | 0.0           | 860    | 2826          | 0.0           | 990    | 4120          | 0.0           |
| 475    | 13456         | 10.3          | 605    | 118718        | 0.3           | 735    | 6311          | 0.0           | 865    | 2385          | 0.0           | 995    | 3858          | 0.0           |
| 480    | 13081         | 10.5          | 610    | 112091        | 0.2           | 740    | 5711          | 0.0           | 870    | 3194          | 0.0           | 1000   | 3405          | 0.0           |
| 485    | 14734         | 12.1          | 615    | 105039        | 0.1           | 745    | 5111          | 0.0           | 875    | 3189          | 0.0           |        |               |               |

**Summary**

$R_f = 71.7$   
 $R_g = 96.9$   
 CIE  $R_a = 71.2$   
 $R_g = -29.7$



**Color Vector Graphics**



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 55 | CES51 = 86 | CES76 = 45 |
| CES02 = 61 | CES27 = 80 | CES52 = 87 | CES77 = 68 |
| CES03 = 30 | CES28 = 79 | CES53 = 74 | CES78 = 49 |
| CES04 = 70 | CES29 = 51 | CES54 = 81 | CES79 = 77 |
| CES05 = 47 | CES30 = 60 | CES55 = 80 | CES80 = 75 |
| CES06 = 50 | CES31 = 56 | CES56 = 69 | CES81 = 75 |
| CES07 = 40 | CES32 = 52 | CES57 = 67 | CES82 = 90 |
| CES08 = 39 | CES33 = 62 | CES58 = 69 | CES83 = 85 |
| CES09 = 29 | CES34 = 65 | CES59 = 86 | CES84 = 87 |
| CES10 = 74 | CES35 = 81 | CES60 = 91 | CES85 = 83 |
| CES11 = 57 | CES36 = 92 | CES61 = 85 | CES86 = 72 |
| CES12 = 63 | CES37 = 74 | CES62 = 81 | CES87 = 77 |
| CES13 = 42 | CES38 = 69 | CES63 = 72 | CES88 = 77 |
| CES14 = 74 | CES39 = 92 | CES64 = 69 | CES89 = 72 |
| CES15 = 71 | CES40 = 86 | CES65 = 64 | CES90 = 75 |
| CES16 = 46 | CES41 = 84 | CES66 = 63 | CES91 = 91 |
| CES17 = 49 | CES42 = 75 | CES67 = 60 | CES92 = 66 |
| CES18 = 56 | CES43 = 70 | CES68 = 67 | CES93 = 80 |
| CES19 = 72 | CES44 = 98 | CES69 = 77 | CES94 = 56 |
| CES20 = 65 | CES45 = 80 | CES70 = 57 | CES95 = 72 |
| CES21 = 86 | CES46 = 77 | CES71 = 53 | CES96 = 78 |
| CES22 = 78 | CES47 = 74 | CES72 = 84 | CES97 = 83 |
| CES23 = 92 | CES48 = 66 | CES73 = 47 | CES98 = 73 |
| CES24 = 91 | CES49 = 76 | CES74 = 96 | CES99 = 63 |
| CES25 = 72 | CES50 = 85 | CES75 = 52 |            |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)