

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P438577

Luminaire Tested: **ISW-SA1D-760-U-RW**

Issue Date: 12/10/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P438577  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-074-24)  
Test Lab: INNOVATION CENTER  
Issue Date: 12/10/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: ISW-SA1D-760-U-RW  
Description: IMPACT ELITE LED WEDGE LUMINAIRE  
(1) 70 CRI, 5700K, 800mA LIGHTSQUARE WITH 16 LEDS AND RECTANGULAR WIDE OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5828 lumens  
Efficiency: N/A  
Efficacy: 128.9 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type III - Medium  
BUG Rating: B3 - U0 - G3  
  
Input Watts (W): 45.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P438577  
 CATALOG NUMBER: ISW-SA1D-760-U-RW

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1.1 fc  
 Type III - Medium - N/A

REPORT NUMBER: P438577  
CATALOG NUMBER: ISW-SA1D-760-U-RW

### Luminous Intensity Polar Plot



— Vertical Plane Through 65-Deg Lateral      - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P438577

CATALOG NUMBER: ISW-SA1D-760-U-RW


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 2914.0   | 0.0    | 2914.0 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Street Side</b> | Lumens    | 2914.0   | 0.0    | 2914.0 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Total</b>       | Lumens    | 5828.0   | 0.0    | 5828.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 60.6   | 1.0       |
| 10°-20°   | 201.6  | 3.5       |
| 20°-30°   | 389.4  | 6.7       |
| 30°-40°   | 649.8  | 11.1      |
| 40°-50°   | 1016.9 | 17.4      |
| 50°-60°   | 1375.0 | 23.6      |
| 60°-70°   | 1356.1 | 23.3      |
| 70°-80°   | 731.0  | 12.5      |
| 80°-90°   | 47.6   | 0.8       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 5828.0 | 100.0     |
| 0°-180°   | 5828.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P438577


CATALOG NUMBER: ISW-SA1D-760-U-RW

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 325.8  | 5.6       |                         |      |         |
| FM (30°-60°)   | 1520.8 | 26.1      |                         |      |         |
| FH (60°-80°)   | 1043.6 | 17.9      |                         |      | G1/1800 |
| FVH (80°-90°)  | 23.8   | 0.4       |                         |      | G1/100  |
| BL (0°-30°)    | 325.8  | 5.6       | B1/500                  |      |         |
| BM (30°-60°)   | 1520.8 | 26.1      | B2/2500                 |      |         |
| BH (60°-80°)   | 1043.6 | 17.9      | B3/2500                 |      | G3/2500 |
| BVH (80°-90°)  | 23.8   | 0.4       |                         |      | G1/100  |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B3-U0-G3**

Type III Medium





REPORT NUMBER: P438577  
 CATALOG NUMBER: ISW-SA1D-760-U-RW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    | 90°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 613.5  | 613.5  | 613.5  | 613.5  | 613.5  | 613.5  | 613.5  | 613.5  | 613.5  | 613.5  | 613.5  |
| 2.5°  | 615.6  | 619.6  | 615.6  | 615.6  | 619.6  | 617.6  | 621.7  | 621.7  | 621.7  | 623.7  | 621.7  |
| 5°    | 611.5  | 611.5  | 611.5  | 615.6  | 621.7  | 625.8  | 629.9  | 636.0  | 636.0  | 642.1  | 638.1  |
| 7.5°  | 607.4  | 607.4  | 609.4  | 615.6  | 623.7  | 631.9  | 644.2  | 658.5  | 662.6  | 666.7  | 666.7  |
| 10°   | 613.5  | 613.5  | 617.6  | 625.8  | 636.0  | 648.3  | 664.6  | 683.0  | 697.4  | 703.5  | 701.4  |
| 12.5° | 621.7  | 623.7  | 629.9  | 642.1  | 656.5  | 672.8  | 689.2  | 711.7  | 730.1  | 740.3  | 740.3  |
| 15°   | 629.9  | 631.9  | 642.1  | 660.5  | 687.1  | 703.5  | 721.9  | 744.4  | 764.8  | 779.2  | 779.2  |
| 17.5° | 646.2  | 648.3  | 662.6  | 689.2  | 719.9  | 742.4  | 758.7  | 773.0  | 791.4  | 809.8  | 809.8  |
| 20°   | 668.7  | 674.9  | 693.3  | 728.0  | 760.8  | 783.3  | 795.5  | 801.7  | 811.9  | 826.2  | 830.3  |
| 22.5° | 703.5  | 707.6  | 728.0  | 764.8  | 803.7  | 830.3  | 838.5  | 830.3  | 830.3  | 844.6  | 844.6  |
| 25°   | 746.4  | 746.4  | 771.0  | 813.9  | 854.8  | 877.3  | 879.4  | 861.0  | 852.8  | 863.0  | 863.0  |
| 27.5° | 785.3  | 789.4  | 809.8  | 856.9  | 899.8  | 926.4  | 924.4  | 899.8  | 873.2  | 879.4  | 881.4  |
| 30°   | 836.4  | 836.4  | 863.0  | 908.0  | 955.0  | 975.5  | 979.6  | 938.7  | 901.9  | 899.8  | 899.8  |
| 32.5° | 895.7  | 901.9  | 924.4  | 965.3  | 1010.3 | 1038.9 | 1032.7 | 983.7  | 936.6  | 928.4  | 934.6  |
| 35°   | 961.2  | 965.3  | 993.9  | 1036.8 | 1071.6 | 1094.1 | 1081.8 | 1030.7 | 979.6  | 967.3  | 971.4  |
| 37.5° | 1036.8 | 1038.9 | 1061.4 | 1106.4 | 1149.3 | 1155.4 | 1137.0 | 1085.9 | 1030.7 | 1012.3 | 1020.5 |
| 40°   | 1104.3 | 1118.6 | 1147.3 | 1186.1 | 1220.9 | 1237.3 | 1202.5 | 1153.4 | 1092.1 | 1081.8 | 1090.0 |
| 42.5° | 1190.2 | 1190.2 | 1222.9 | 1265.9 | 1302.7 | 1312.9 | 1282.2 | 1222.9 | 1161.6 | 1155.4 | 1163.6 |
| 45°   | 1251.6 | 1259.7 | 1298.6 | 1345.6 | 1384.5 | 1394.7 | 1368.1 | 1298.6 | 1235.2 | 1227.0 | 1235.2 |
| 47.5° | 1317.0 | 1323.1 | 1353.8 | 1411.1 | 1460.2 | 1470.4 | 1445.8 | 1384.5 | 1304.7 | 1304.7 | 1310.9 |
| 50°   | 1360.0 | 1368.1 | 1404.9 | 1460.2 | 1523.6 | 1546.1 | 1517.4 | 1456.1 | 1384.5 | 1376.3 | 1386.5 |
| 52.5° | 1400.9 | 1404.9 | 1441.8 | 1497.0 | 1574.7 | 1615.6 | 1589.0 | 1527.6 | 1454.0 | 1458.1 | 1462.2 |
| 55°   | 1390.6 | 1396.8 | 1445.8 | 1525.6 | 1613.5 | 1660.6 | 1646.3 | 1603.3 | 1523.6 | 1533.8 | 1550.1 |
| 57.5° | 1333.4 | 1335.4 | 1398.8 | 1494.9 | 1623.8 | 1695.3 | 1701.5 | 1656.5 | 1587.0 | 1603.3 | 1623.8 |
| 60°   | 1204.5 | 1220.9 | 1284.3 | 1400.9 | 1587.0 | 1719.9 | 1738.3 | 1711.7 | 1654.4 | 1683.1 | 1693.3 |
| 62.5° | 983.7  | 991.8  | 1077.7 | 1247.5 | 1480.6 | 1713.7 | 1777.1 | 1756.7 | 1707.6 | 1740.3 | 1760.8 |
| 65°   | 644.2  | 670.8  | 777.1  | 983.7  | 1290.4 | 1638.1 | 1844.6 | 1814.0 | 1769.0 | 1785.3 | 1807.8 |
| 67.5° | 390.6  | 396.7  | 470.4  | 646.2  | 987.8  | 1466.3 | 1844.6 | 1899.8 | 1816.0 | 1814.0 | 1828.3 |
| 70°   | 200.4  | 204.5  | 231.1  | 343.6  | 597.2  | 1092.1 | 1668.8 | 1938.7 | 1858.9 | 1824.2 | 1838.5 |
| 72.5° | 135.0  | 130.9  | 137.0  | 161.6  | 272.0  | 580.8  | 1239.3 | 1820.1 | 1932.6 | 1871.2 | 1877.3 |
| 75°   | 100.2  | 100.2  | 106.3  | 110.4  | 135.0  | 259.7  | 711.7  | 1443.8 | 1854.9 | 1826.2 | 1803.7 |
| 77.5° | 73.6   | 75.7   | 79.8   | 81.8   | 87.9   | 116.6  | 286.3  | 834.4  | 1368.1 | 1589.0 | 1582.9 |
| 80°   | 49.1   | 51.1   | 59.3   | 57.3   | 57.3   | 65.4   | 110.4  | 298.6  | 531.7  | 572.6  | 544.0  |
| 82.5° | 28.6   | 26.6   | 34.8   | 34.8   | 32.7   | 32.7   | 49.1   | 92.0   | 145.2  | 100.2  | 73.6   |
| 85°   | 2.0    | 4.1    | 6.1    | 6.1    | 6.1    | 6.1    | 12.3   | 20.5   | 36.8   | 28.6   | 22.5   |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 2.0    | 2.0    | 2.0    | 4.1    | 4.1    | 4.1    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269





**Test Information**

Test Method: LM-79-2008  
 Report Number: SP1-1908-441-9-R4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/28/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGRAW-EDISON  
 Catalog Number: **SA1C-760-U-5WQ**  
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

\*\*\*THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.\*\*\*TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

**Spectral Parameters**

|                           |        |           |      |      |       |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K):                  | 5474   | CRI (Ra): | 71.7 | R9:  | -27.1 |
| CIE u':                   | 0.2052 | R1:       | 70.6 | R10: | 40.8  |
| CIE v':                   | 0.4804 | R2:       | 74.6 | R11: | 74.6  |
| Duv:                      | 0.0025 | R3:       | 78.3 | R12: | 50.4  |
| CIE x:                    | 0.3330 | R4:       | 73.8 | R13: | 70.0  |
| CIE y:                    | 0.3466 | R5:       | 72.4 | R14: | 87.8  |
| CIE z:                    | 0.3204 | R6:       | 67.5 |      |       |
| Peak Wavelength (nm):     | 442    | R7:       | 77.5 |      |       |
| Dominant Wavelength (nm): | 554    | R8:       | 58.9 |      |       |
| Purity:                   | 4.1    |           |      |      |       |
| Rf:                       | 72.1   |           |      |      |       |
| Rg:                       | 97.2   |           |      |      |       |



**Test Conditions**

Stabilization Time: 240M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 24.6/31%  
 Sphere Temperature (°C): 25.9

REPORT NUMBER: SP1-1908-441-9-R4

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/28/2019        | 12/28/2019           |
| Power Meter                    | IN0071                | 12/5/2018        | 12/5/2019            |
| AC Power Source                | IN0063                | 12/5/2018        | 12/5/2019            |
| DC Power Source                | IN0208                | 12/5/2018        | 12/5/2019            |
| Sphere Thermometer             | IN0085                | 12/5/2018        | 12/5/2019            |
| Room Thermometer               | IN0046                | 12/5/2018        | 12/5/2019            |

REPORT NUMBER: SP1-1908-441-9-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-9-R4

**Photopic Flux vs. Wavelength**



#####

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 3540                                 | NR                             | 490               | 33363                                | NR                             | 620               | 80193                                | NR                             | 750               | 4663                                 | NR                             | 880               | 4678                                 | NR                             |
| 365               | 2862                                 | NR                             | 495               | 44177                                | NR                             | 625               | 73091                                | NR                             | 755               | 4147                                 | NR                             | 885               | 4128                                 | NR                             |
| 370               | 2865                                 | NR                             | 500               | 57019                                | NR                             | 630               | 66269                                | NR                             | 760               | 4040                                 | NR                             | 890               | 4504                                 | NR                             |
| 375               | 3254                                 | NR                             | 505               | 70030                                | NR                             | 635               | 60012                                | NR                             | 765               | 3474                                 | NR                             | 895               | 4371                                 | NR                             |
| 380               | 3076                                 | NR                             | 510               | 81972                                | NR                             | 640               | 53914                                | NR                             | 770               | 3469                                 | NR                             | 900               | 4082                                 | NR                             |
| 385               | 2904                                 | NR                             | 515               | 92590                                | NR                             | 645               | 48385                                | NR                             | 775               | 3181                                 | NR                             | 905               | 2982                                 | NR                             |
| 390               | 2689                                 | NR                             | 520               | 100305                               | NR                             | 650               | 43219                                | NR                             | 780               | 2969                                 | NR                             | 910               | 4351                                 | NR                             |
| 395               | 2619                                 | NR                             | 525               | 107452                               | NR                             | 655               | 38562                                | NR                             | 785               | 3132                                 | NR                             | 915               | 3365                                 | NR                             |
| 400               | 2679                                 | NR                             | 530               | 111373                               | NR                             | 660               | 34110                                | NR                             | 790               | 2507                                 | NR                             | 920               | 3430                                 | NR                             |
| 405               | 3515                                 | NR                             | 535               | 114505                               | NR                             | 665               | 30085                                | NR                             | 795               | 2968                                 | NR                             | 925               | 4264                                 | NR                             |
| 410               | 6934                                 | NR                             | 540               | 116408                               | NR                             | 670               | 26205                                | NR                             | 800               | 2758                                 | NR                             | 930               | 4095                                 | NR                             |
| 415               | 14943                                | NR                             | 545               | 118700                               | NR                             | 675               | 22906                                | NR                             | 805               | 2872                                 | NR                             | 935               | 5048                                 | NR                             |
| 420               | 31939                                | NR                             | 550               | 119209                               | NR                             | 680               | 20058                                | NR                             | 810               | 3094                                 | NR                             | 940               | 4074                                 | NR                             |
| 425               | 64701                                | NR                             | 555               | 120742                               | NR                             | 685               | 17413                                | NR                             | 815               | 3222                                 | NR                             | 945               | 4949                                 | NR                             |
| 430               | 110939                               | NR                             | 560               | 121594                               | NR                             | 690               | 15447                                | NR                             | 820               | 3238                                 | NR                             | 950               | 4387                                 | NR                             |
| 435               | 164597                               | NR                             | 565               | 121913                               | NR                             | 695               | 13398                                | NR                             | 825               | 3524                                 | NR                             | 955               | 4978                                 | NR                             |
| 440               | 207696                               | NR                             | 570               | 122147                               | NR                             | 700               | 11777                                | NR                             | 830               | 2921                                 | NR                             | 960               | 4706                                 | NR                             |
| 445               | 201830                               | NR                             | 575               | 121605                               | NR                             | 705               | 10412                                | NR                             | 835               | 3595                                 | NR                             | 965               | 5083                                 | NR                             |
| 450               | 145410                               | NR                             | 580               | 120248                               | NR                             | 710               | 9544                                 | NR                             | 840               | 3016                                 | NR                             | 970               | 4522                                 | NR                             |
| 455               | 89594                                | NR                             | 585               | 117717                               | NR                             | 715               | 8940                                 | NR                             | 845               | 4032                                 | NR                             | 975               | 4740                                 | NR                             |
| 460               | 58321                                | NR                             | 590               | 114359                               | NR                             | 720               | 7897                                 | NR                             | 850               | 3579                                 | NR                             | 980               | 6122                                 | NR                             |
| 465               | 39318                                | NR                             | 595               | 109974                               | NR                             | 725               | 7045                                 | NR                             | 855               | 4571                                 | NR                             | 985               | 6450                                 | NR                             |
| 470               | 27693                                | NR                             | 600               | 105269                               | NR                             | 730               | 6483                                 | NR                             | 860               | 4485                                 | NR                             | 990               | 4875                                 | NR                             |
| 475               | 23081                                | NR                             | 605               | 99453                                | NR                             | 735               | 5838                                 | NR                             | 865               | 3978                                 | NR                             | 995               | 4764                                 | NR                             |
| 480               | 23002                                | NR                             | 610               | 92921                                | NR                             | 740               | 5261                                 | NR                             | 870               | 4298                                 | NR                             | 1000              | 3640                                 | NR                             |
| 485               | 26201                                | NR                             | 615               | 86989                                | NR                             | 745               | 4760                                 | NR                             | 875               | 4356                                 | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-1908-441-9-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 13759.3 S/P: 1.85

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 3540          | NR            | 490    | 33363         | NR            | 620    | 80193         | NR            | 750    | 4663          | NR            | 880    | 4678          | NR            |
| 365    | 2862          | NR            | 495    | 44177         | NR            | 625    | 73091         | NR            | 755    | 4147          | NR            | 885    | 4128          | NR            |
| 370    | 2865          | NR            | 500    | 57019         | NR            | 630    | 66269         | NR            | 760    | 4040          | NR            | 890    | 4504          | NR            |
| 375    | 3254          | NR            | 505    | 70030         | NR            | 635    | 60012         | NR            | 765    | 3474          | NR            | 895    | 4371          | NR            |
| 380    | 3076          | NR            | 510    | 81972         | NR            | 640    | 53914         | NR            | 770    | 3469          | NR            | 900    | 4082          | NR            |
| 385    | 2904          | NR            | 515    | 92590         | NR            | 645    | 48385         | NR            | 775    | 3181          | NR            | 905    | 2982          | NR            |
| 390    | 2689          | NR            | 520    | 100305        | NR            | 650    | 43219         | NR            | 780    | 2969          | NR            | 910    | 4351          | NR            |
| 395    | 2619          | NR            | 525    | 107452        | NR            | 655    | 38562         | NR            | 785    | 3132          | NR            | 915    | 3365          | NR            |
| 400    | 2679          | NR            | 530    | 111373        | NR            | 660    | 34110         | NR            | 790    | 2507          | NR            | 920    | 3430          | NR            |
| 405    | 3515          | NR            | 535    | 114505        | NR            | 665    | 30085         | NR            | 795    | 2968          | NR            | 925    | 4264          | NR            |
| 410    | 6934          | NR            | 540    | 116408        | NR            | 670    | 26205         | NR            | 800    | 2758          | NR            | 930    | 4095          | NR            |
| 415    | 14943         | NR            | 545    | 118700        | NR            | 675    | 22906         | NR            | 805    | 2872          | NR            | 935    | 5048          | NR            |
| 420    | 31939         | NR            | 550    | 119209        | NR            | 680    | 20058         | NR            | 810    | 3094          | NR            | 940    | 4074          | NR            |
| 425    | 64701         | NR            | 555    | 120742        | NR            | 685    | 17413         | NR            | 815    | 3222          | NR            | 945    | 4949          | NR            |
| 430    | 110939        | NR            | 560    | 121594        | NR            | 690    | 15447         | NR            | 820    | 3238          | NR            | 950    | 4387          | NR            |
| 435    | 164597        | NR            | 565    | 121913        | NR            | 695    | 13398         | NR            | 825    | 3524          | NR            | 955    | 4978          | NR            |
| 440    | 207696        | NR            | 570    | 122147        | NR            | 700    | 11777         | NR            | 830    | 2921          | NR            | 960    | 4706          | NR            |
| 445    | 201830        | NR            | 575    | 121605        | NR            | 705    | 10412         | NR            | 835    | 3595          | NR            | 965    | 5083          | NR            |
| 450    | 145410        | NR            | 580    | 120248        | NR            | 710    | 9544          | NR            | 840    | 3016          | NR            | 970    | 4522          | NR            |
| 455    | 89594         | NR            | 585    | 117717        | NR            | 715    | 8940          | NR            | 845    | 4032          | NR            | 975    | 4740          | NR            |
| 460    | 58321         | NR            | 590    | 114359        | NR            | 720    | 7897          | NR            | 850    | 3579          | NR            | 980    | 6122          | NR            |
| 465    | 39318         | NR            | 595    | 109974        | NR            | 725    | 7045          | NR            | 855    | 4571          | NR            | 985    | 6450          | NR            |
| 470    | 27693         | NR            | 600    | 105269        | NR            | 730    | 6483          | NR            | 860    | 4485          | NR            | 990    | 4875          | NR            |
| 475    | 23081         | NR            | 605    | 99453         | NR            | 735    | 5838          | NR            | 865    | 3978          | NR            | 995    | 4764          | NR            |
| 480    | 23002         | NR            | 610    | 92921         | NR            | 740    | 5261          | NR            | 870    | 4298          | NR            | 1000   | 3640          | NR            |
| 485    | 26201         | NR            | 615    | 86989         | NR            | 745    | 4760          | NR            | 875    | 4356          | NR            |        |               |               |

REPORT NUMBER: SP1-1908-441-9-R4

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 5527.6 M/P: 0.74**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 3540          | NR            | 490    | 33363         | NR            | 620    | 80193         | NR            | 750    | 4663          | NR            | 880    | 4678          | NR            |
| 365    | 2862          | NR            | 495    | 44177         | NR            | 625    | 73091         | NR            | 755    | 4147          | NR            | 885    | 4128          | NR            |
| 370    | 2865          | NR            | 500    | 57019         | NR            | 630    | 66269         | NR            | 760    | 4040          | NR            | 890    | 4504          | NR            |
| 375    | 3254          | NR            | 505    | 70030         | NR            | 635    | 60012         | NR            | 765    | 3474          | NR            | 895    | 4371          | NR            |
| 380    | 3076          | NR            | 510    | 81972         | NR            | 640    | 53914         | NR            | 770    | 3469          | NR            | 900    | 4082          | NR            |
| 385    | 2904          | NR            | 515    | 92590         | NR            | 645    | 48385         | NR            | 775    | 3181          | NR            | 905    | 2982          | NR            |
| 390    | 2689          | NR            | 520    | 100305        | NR            | 650    | 43219         | NR            | 780    | 2969          | NR            | 910    | 4351          | NR            |
| 395    | 2619          | NR            | 525    | 107452        | NR            | 655    | 38562         | NR            | 785    | 3132          | NR            | 915    | 3365          | NR            |
| 400    | 2679          | NR            | 530    | 111373        | NR            | 660    | 34110         | NR            | 790    | 2507          | NR            | 920    | 3430          | NR            |
| 405    | 3515          | NR            | 535    | 114505        | NR            | 665    | 30085         | NR            | 795    | 2968          | NR            | 925    | 4264          | NR            |
| 410    | 6934          | NR            | 540    | 116408        | NR            | 670    | 26205         | NR            | 800    | 2758          | NR            | 930    | 4095          | NR            |
| 415    | 14943         | NR            | 545    | 118700        | NR            | 675    | 22906         | NR            | 805    | 2872          | NR            | 935    | 5048          | NR            |
| 420    | 31939         | NR            | 550    | 119209        | NR            | 680    | 20058         | NR            | 810    | 3094          | NR            | 940    | 4074          | NR            |
| 425    | 64701         | NR            | 555    | 120742        | NR            | 685    | 17413         | NR            | 815    | 3222          | NR            | 945    | 4949          | NR            |
| 430    | 110939        | NR            | 560    | 121594        | NR            | 690    | 15447         | NR            | 820    | 3238          | NR            | 950    | 4387          | NR            |
| 435    | 164597        | NR            | 565    | 121913        | NR            | 695    | 13398         | NR            | 825    | 3524          | NR            | 955    | 4978          | NR            |
| 440    | 207696        | NR            | 570    | 122147        | NR            | 700    | 11777         | NR            | 830    | 2921          | NR            | 960    | 4706          | NR            |
| 445    | 201830        | NR            | 575    | 121605        | NR            | 705    | 10412         | NR            | 835    | 3595          | NR            | 965    | 5083          | NR            |
| 450    | 145410        | NR            | 580    | 120248        | NR            | 710    | 9544          | NR            | 840    | 3016          | NR            | 970    | 4522          | NR            |
| 455    | 89594         | NR            | 585    | 117717        | NR            | 715    | 8940          | NR            | 845    | 4032          | NR            | 975    | 4740          | NR            |
| 460    | 58321         | NR            | 590    | 114359        | NR            | 720    | 7897          | NR            | 850    | 3579          | NR            | 980    | 6122          | NR            |
| 465    | 39318         | NR            | 595    | 109974        | NR            | 725    | 7045          | NR            | 855    | 4571          | NR            | 985    | 6450          | NR            |
| 470    | 27693         | NR            | 600    | 105269        | NR            | 730    | 6483          | NR            | 860    | 4485          | NR            | 990    | 4875          | NR            |
| 475    | 23081         | NR            | 605    | 99453         | NR            | 735    | 5838          | NR            | 865    | 3978          | NR            | 995    | 4764          | NR            |
| 480    | 23002         | NR            | 610    | 92921         | NR            | 740    | 5261          | NR            | 870    | 4298          | NR            | 1000   | 3640          | NR            |
| 485    | 26201         | NR            | 615    | 86989         | NR            | 745    | 4760          | NR            | 875    | 4356          | NR            |        |               |               |

REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

**Summary**

$R_f = 72.1$   
 $R_g = 97.2$   
 CIE  $R_a = 71.7$   
 $R_g = -27.1$



**Color Vector Graphics**



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 54 | CES51 = 88 | CES76 = 43 |
| CES02 = 59 | CES27 = 79 | CES52 = 90 | CES77 = 64 |
| CES03 = 30 | CES28 = 77 | CES53 = 77 | CES78 = 46 |
| CES04 = 69 | CES29 = 50 | CES54 = 81 | CES79 = 74 |
| CES05 = 46 | CES30 = 59 | CES55 = 80 | CES80 = 70 |
| CES06 = 50 | CES31 = 55 | CES56 = 70 | CES81 = 71 |
| CES07 = 38 | CES32 = 52 | CES57 = 68 | CES82 = 88 |
| CES08 = 38 | CES33 = 63 | CES58 = 70 | CES83 = 82 |
| CES09 = 29 | CES34 = 63 | CES59 = 88 | CES84 = 87 |
| CES10 = 72 | CES35 = 79 | CES60 = 92 | CES85 = 84 |
| CES11 = 55 | CES36 = 90 | CES61 = 88 | CES86 = 76 |
| CES12 = 61 | CES37 = 72 | CES62 = 81 | CES87 = 75 |
| CES13 = 41 | CES38 = 68 | CES63 = 75 | CES88 = 77 |
| CES14 = 74 | CES39 = 91 | CES64 = 72 | CES89 = 76 |
| CES15 = 70 | CES40 = 83 | CES65 = 65 | CES90 = 76 |
| CES16 = 46 | CES41 = 84 | CES66 = 66 | CES91 = 92 |
| CES17 = 48 | CES42 = 70 | CES67 = 64 | CES92 = 70 |
| CES18 = 55 | CES43 = 69 | CES68 = 71 | CES93 = 83 |
| CES19 = 70 | CES44 = 98 | CES69 = 80 | CES94 = 60 |
| CES20 = 64 | CES45 = 79 | CES70 = 58 | CES95 = 73 |
| CES21 = 85 | CES46 = 78 | CES71 = 55 | CES96 = 79 |
| CES22 = 77 | CES47 = 76 | CES72 = 84 | CES97 = 84 |
| CES23 = 91 | CES48 = 68 | CES73 = 47 | CES98 = 73 |
| CES24 = 90 | CES49 = 78 | CES74 = 94 | CES99 = 62 |
| CES25 = 71 | CES50 = 87 | CES75 = 51 |            |





REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Measure Comparisons



(END OF REPORT)