

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P436940

Luminaire Tested: **ISC-SA1A-722-U-T4FT**

Issue Date: 12/9/2020

Test Information

Test Method: LM-79-08
Report Number: P436940
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-074-10)
Test Lab: INNOVATION CENTER
Issue Date: 12/9/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: ISC-SA1A-722-U-T4FT
Description: IMPACT ELITE LED CYLINDER LUMINAIRE
(1) 70 CRI, 2200K, 350mA LIGHTSQUARE WITH 16 LEDS AND TYPE IV FORWARD
THROW OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2022 lumens
Efficiency: N/A
Efficacy: 100.6 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G1


Input Watts (W): 20.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P436940
 CATALOG NUMBER: ISC-SA1A-722-U-T4FT

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.5 fc
 Type IV - Short - N/A

REPORT NUMBER: P436940
CATALOG NUMBER: ISC-SA1A-722-U-T4FT

Luminous Intensity Polar Plot



— Vertical Plane Through 32-Deg Lateral - - - Horizontal Cone Through 75-Deg Vertical

REPORT NUMBER: P436940
 CATALOG NUMBER: ISC-SA1A-722-U-T4FT


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 443.0 | 0.0 | 443.0 |
| | % Fixture | 21.9 | 0.0 | 21.9 |
| Street Side | Lumens | 1579.0 | 0.0 | 1579.0 |
| | % Fixture | 78.1 | 0.0 | 78.1 |
| Total | Lumens | 2022.0 | 0.0 | 2022.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

Coefficient of Utilization

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 29.2 | 1.4 |
| 10°-20° | 79.9 | 4.0 |
| 20°-30° | 132.2 | 6.5 |
| 30°-40° | 197.1 | 9.7 |
| 40°-50° | 280.6 | 13.9 |
| 50°-60° | 386.1 | 19.1 |
| 60°-70° | 486.5 | 24.1 |
| 70°-80° | 393.3 | 19.5 |
| 80°-90° | 37.2 | 1.8 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 2022.0 | 100.0 |
| 0°-180° | 2022.0 | 100.0 |



REPORT NUMBER: P436940


CATALOG NUMBER: ISC-SA1A-722-U-T4FT

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 121.6 | 6.0 | | | |
| FM (30°-60°) | 644.9 | 31.9 | | | |
| FH (60°-80°) | 784.9 | 38.8 | | | G1/1800 |
| FVH (80°-90°) | 27.6 | 1.4 | | | G1/100 |
| BL (0°-30°) | 119.8 | 5.9 | B1/500 | | |
| BM (30°-60°) | 218.8 | 10.8 | B0/220 | | |
| BH (60°-80°) | 94.9 | 4.7 | B0/110 | | G0/110 |
| BVH (80°-90°) | 9.6 | 0.5 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G1

Type IV Short





REPORT NUMBER: P436940

CATALOG NUMBER: ISC-SA1A-722-U-T4FT

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 32° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|-------|-------|-------|-------|
| 0° | 321.9 | 321.9 | 321.9 | 321.9 | 321.9 | 321.9 | 321.9 | 321.9 | 321.9 | 321.9 | 321.9 |
| 2.5° | 294.0 | 296.2 | 296.9 | 298.4 | 301.3 | 299.8 | 303.5 | 307.9 | 313.8 | 316.7 | 322.6 |
| 5° | 269.0 | 269.0 | 271.2 | 274.8 | 280.0 | 280.0 | 286.6 | 294.7 | 305.0 | 313.1 | 323.4 |
| 7.5° | 246.9 | 246.9 | 249.1 | 253.5 | 258.7 | 262.4 | 270.4 | 282.9 | 296.9 | 312.3 | 325.6 |
| 10° | 228.6 | 229.3 | 230.8 | 235.2 | 241.8 | 245.5 | 257.2 | 271.2 | 289.5 | 309.4 | 327.8 |
| 12.5° | 221.9 | 221.2 | 220.5 | 224.1 | 229.3 | 232.2 | 245.5 | 263.1 | 284.4 | 308.7 | 332.2 |
| 15° | 227.1 | 225.6 | 223.4 | 223.4 | 225.6 | 227.1 | 238.1 | 256.5 | 280.0 | 307.9 | 337.3 |
| 17.5° | 240.3 | 238.8 | 233.7 | 228.6 | 230.0 | 230.8 | 238.1 | 252.8 | 277.8 | 310.9 | 344.7 |
| 20° | 258.7 | 256.5 | 247.7 | 241.0 | 239.6 | 239.6 | 244.0 | 255.0 | 279.3 | 316.7 | 354.2 |
| 22.5° | 280.7 | 278.5 | 268.2 | 256.5 | 255.0 | 254.3 | 256.5 | 263.8 | 283.7 | 323.4 | 368.9 |
| 25° | 310.1 | 307.9 | 295.4 | 280.7 | 275.6 | 274.8 | 272.6 | 277.1 | 291.0 | 332.2 | 379.2 |
| 27.5° | 341.7 | 342.5 | 327.8 | 307.9 | 302.8 | 300.6 | 294.7 | 294.0 | 299.8 | 339.5 | 396.8 |
| 30° | 371.1 | 369.6 | 354.2 | 338.0 | 330.7 | 327.8 | 318.2 | 313.8 | 310.1 | 350.5 | 417.4 |
| 32.5° | 385.1 | 387.3 | 379.9 | 364.5 | 358.6 | 353.5 | 342.5 | 335.1 | 330.0 | 367.4 | 442.4 |
| 35° | 408.6 | 409.3 | 406.4 | 396.8 | 385.1 | 381.4 | 371.1 | 366.0 | 355.0 | 388.0 | 472.5 |
| 37.5° | 432.1 | 434.3 | 433.6 | 427.7 | 417.4 | 413.7 | 404.9 | 402.7 | 380.7 | 413.7 | 510.0 |
| 40° | 467.4 | 463.7 | 458.6 | 460.8 | 457.1 | 454.9 | 451.2 | 443.9 | 416.7 | 441.7 | 546.8 |
| 42.5° | 505.6 | 499.0 | 480.6 | 486.5 | 491.6 | 493.8 | 499.0 | 490.9 | 454.2 | 483.6 | 576.9 |
| 45° | 536.5 | 531.3 | 507.1 | 508.5 | 518.8 | 526.2 | 550.4 | 546.0 | 502.7 | 529.1 | 617.3 |
| 47.5° | 554.1 | 549.7 | 532.8 | 540.1 | 546.8 | 557.0 | 604.1 | 600.4 | 548.2 | 578.4 | 665.8 |
| 50° | 579.1 | 571.7 | 555.6 | 568.8 | 580.6 | 588.6 | 656.3 | 654.8 | 587.2 | 629.1 | 720.9 |
| 52.5° | 593.1 | 585.7 | 584.2 | 602.6 | 616.6 | 627.6 | 712.1 | 707.7 | 625.4 | 679.8 | 773.1 |
| 55° | 612.2 | 613.6 | 623.2 | 637.1 | 657.0 | 675.4 | 766.5 | 744.4 | 660.7 | 729.7 | 824.5 |
| 57.5° | 654.1 | 652.6 | 671.0 | 677.6 | 703.3 | 726.8 | 831.2 | 783.4 | 690.1 | 765.8 | 848.8 |
| 60° | 709.9 | 712.8 | 719.5 | 736.4 | 764.3 | 800.3 | 893.6 | 823.8 | 709.2 | 791.5 | 844.4 |
| 62.5° | 815.7 | 798.8 | 795.9 | 800.3 | 855.4 | 897.3 | 954.6 | 859.8 | 717.3 | 792.2 | 798.1 |
| 65° | 923.0 | 916.4 | 893.6 | 904.6 | 984.8 | 1023.0 | 1033.3 | 883.3 | 701.1 | 746.6 | 695.2 |
| 67.5° | 1034.0 | 1033.3 | 1009.0 | 1040.6 | 1136.9 | 1181.7 | 1120.7 | 878.9 | 648.2 | 640.1 | 534.3 |
| 70° | 1147.9 | 1153.0 | 1153.0 | 1242.7 | 1374.2 | 1386.0 | 1218.4 | 837.0 | 543.1 | 453.4 | 312.3 |
| 72.5° | 1197.9 | 1200.8 | 1227.3 | 1426.4 | 1636.6 | 1640.3 | 1274.3 | 710.6 | 370.4 | 241.8 | 157.3 |
| 75° | 947.3 | 969.3 | 1040.6 | 1373.5 | 1646.2 | 1631.5 | 1135.4 | 454.9 | 180.8 | 120.5 | 87.5 |
| 77.5° | 371.9 | 379.9 | 524.7 | 874.5 | 1199.3 | 1214.0 | 734.9 | 181.5 | 91.9 | 76.4 | 63.2 |
| 80° | 105.1 | 110.2 | 185.9 | 347.6 | 592.3 | 654.8 | 292.5 | 78.6 | 61.7 | 55.9 | 45.6 |
| 82.5° | 37.5 | 42.6 | 69.1 | 133.0 | 252.8 | 266.8 | 79.4 | 38.9 | 39.7 | 36.0 | 27.9 |
| 85° | 5.1 | 4.4 | 9.6 | 24.3 | 55.9 | 47.0 | 13.2 | 10.3 | 16.2 | 16.9 | 11.8 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.7 | 0.7 | 0.7 | 0.0 | 0.0 | 0.0 | 0.7 | 0.7 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P436940
 CATALOG NUMBER: ISC-SA1A-722-U-T4FT

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 321.9 | 321.9 | 321.9 | 321.9 | 321.9 | 321.9 | 321.9 | 321.9 | 321.9 | 321.9 | 321.9 |
| 2.5° | 324.1 | 325.6 | 328.5 | 330.0 | 331.4 | 334.4 | 333.6 | 335.1 | 335.1 | 334.4 | 335.8 |
| 5° | 327.0 | 330.7 | 334.4 | 335.8 | 336.6 | 336.6 | 332.9 | 330.7 | 330.0 | 329.2 | 330.0 |
| 7.5° | 330.0 | 335.1 | 338.8 | 338.0 | 335.1 | 330.0 | 325.6 | 321.9 | 318.2 | 316.7 | 318.2 |
| 10° | 335.1 | 340.3 | 342.5 | 337.3 | 329.2 | 321.1 | 314.5 | 309.4 | 303.5 | 302.8 | 303.5 |
| 12.5° | 339.5 | 346.1 | 346.1 | 334.4 | 323.4 | 312.3 | 302.0 | 294.0 | 286.6 | 284.4 | 284.4 |
| 15° | 346.9 | 352.0 | 346.9 | 330.7 | 315.3 | 301.3 | 286.6 | 276.3 | 267.5 | 263.8 | 264.6 |
| 17.5° | 355.0 | 358.6 | 345.4 | 324.8 | 306.4 | 288.1 | 269.0 | 255.0 | 248.4 | 244.7 | 245.5 |
| 20° | 364.5 | 365.2 | 345.4 | 317.5 | 293.2 | 269.0 | 248.4 | 238.1 | 233.7 | 231.5 | 232.2 |
| 22.5° | 377.0 | 374.1 | 343.2 | 307.9 | 276.3 | 249.9 | 230.8 | 227.8 | 227.8 | 227.8 | 230.0 |
| 25° | 390.2 | 382.1 | 339.5 | 295.4 | 254.3 | 227.1 | 219.7 | 223.4 | 226.3 | 226.3 | 227.8 |
| 27.5° | 403.5 | 390.2 | 332.2 | 277.1 | 228.6 | 210.9 | 213.9 | 219.7 | 222.7 | 222.7 | 224.1 |
| 30° | 419.6 | 399.8 | 323.4 | 252.1 | 204.3 | 199.9 | 207.2 | 214.6 | 219.0 | 219.0 | 220.5 |
| 32.5° | 440.2 | 407.9 | 310.1 | 226.3 | 188.1 | 190.3 | 198.4 | 206.5 | 211.6 | 213.1 | 213.9 |
| 35° | 463.0 | 418.9 | 291.8 | 197.7 | 177.1 | 183.0 | 189.6 | 197.0 | 201.4 | 202.8 | 202.8 |
| 37.5° | 486.5 | 429.9 | 267.5 | 173.4 | 167.6 | 175.6 | 182.3 | 185.9 | 188.9 | 188.9 | 188.9 |
| 40° | 510.0 | 435.8 | 235.9 | 154.3 | 158.0 | 169.8 | 175.6 | 174.2 | 173.4 | 171.2 | 172.0 |
| 42.5° | 534.3 | 440.2 | 202.1 | 140.4 | 148.4 | 163.1 | 167.6 | 163.9 | 158.0 | 154.3 | 155.1 |
| 45° | 560.7 | 446.8 | 174.2 | 130.1 | 138.9 | 157.3 | 161.7 | 154.3 | 147.0 | 141.1 | 139.6 |
| 47.5° | 590.9 | 457.8 | 149.2 | 120.5 | 133.0 | 153.6 | 158.0 | 147.7 | 138.2 | 130.1 | 128.6 |
| 50° | 632.0 | 474.7 | 130.1 | 113.9 | 129.3 | 151.4 | 155.1 | 141.8 | 130.8 | 120.5 | 119.8 |
| 52.5° | 673.9 | 487.2 | 116.8 | 108.0 | 124.9 | 147.0 | 151.4 | 137.4 | 124.2 | 113.2 | 111.7 |
| 55° | 704.8 | 485.8 | 105.1 | 102.1 | 119.1 | 141.1 | 147.7 | 132.3 | 115.4 | 105.1 | 103.6 |
| 57.5° | 718.0 | 455.6 | 95.5 | 97.0 | 112.4 | 133.7 | 141.8 | 124.2 | 108.8 | 99.9 | 99.2 |
| 60° | 695.2 | 407.1 | 88.9 | 91.1 | 105.1 | 124.2 | 130.8 | 118.3 | 104.4 | 96.3 | 95.5 |
| 62.5° | 655.5 | 352.7 | 83.8 | 86.7 | 97.7 | 115.4 | 124.2 | 111.0 | 98.5 | 92.6 | 91.9 |
| 65° | 561.5 | 293.2 | 78.6 | 81.6 | 91.1 | 106.6 | 118.3 | 106.6 | 94.1 | 88.2 | 87.5 |
| 67.5° | 424.0 | 210.9 | 73.5 | 76.4 | 85.2 | 99.9 | 113.2 | 100.7 | 87.5 | 83.0 | 83.0 |
| 70° | 252.8 | 129.3 | 66.9 | 71.3 | 77.9 | 91.9 | 105.1 | 92.6 | 79.4 | 77.9 | 76.4 |
| 72.5° | 123.5 | 82.3 | 61.0 | 64.7 | 69.8 | 81.6 | 93.3 | 82.3 | 69.1 | 65.4 | 64.7 |
| 75° | 74.2 | 59.5 | 52.9 | 57.3 | 61.0 | 68.3 | 78.6 | 70.5 | 60.3 | 54.4 | 53.6 |
| 77.5° | 53.6 | 44.8 | 44.8 | 49.2 | 49.2 | 56.6 | 67.6 | 60.3 | 50.7 | 47.0 | 46.3 |
| 80° | 38.2 | 33.8 | 36.7 | 39.7 | 38.2 | 47.8 | 57.3 | 50.7 | 41.2 | 38.2 | 37.5 |
| 82.5° | 25.0 | 23.5 | 27.9 | 27.2 | 27.2 | 36.7 | 47.0 | 38.2 | 30.1 | 25.0 | 23.5 |
| 85° | 10.3 | 11.8 | 16.2 | 15.4 | 15.4 | 20.6 | 24.3 | 19.8 | 14.0 | 11.0 | 11.0 |
| 87.5° | 0.0 | 0.7 | 2.2 | 1.5 | 1.5 | 2.2 | 0.7 | 0.7 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Test Information

Test Method: LM-79-2008 Report
 Number: SP1-1908-441-10-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: MCGRAW-EDISON
 Catalog Number: **SA1C-722-U-5WQ**
 Description: MCGRAW EDISON ROADWAY AND AREA LUMINAIRE


THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2237
 CIE u': 0.2876
 CIE v': 0.5346
 Duv: -0.0006
 CIE x: 0.5005
 CIE y: 0.4134
 CIE z: 0.0860
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 587
 Purity: 74.5

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 72.0 | | |
| R1: | 68.9 | R9: | -17.4 |
| R2: | 83.0 | R10: | 61.3 |
| R3: | 95.2 | R11: | 59.8 |
| R4: | 66.2 | R12: | 50.5 |
| R5: | 65.9 | R13: | 71.1 |
| R6: | 76.3 | R14: | 96.9 |
| R7: | 76.7 | | |
| R8: | 43.8 | | |

Rf: 69.8
 Rg: 99.2



Test Conditions


Stabilization Time: 71M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.7/41%
 Sphere Temperature (°C): 25.6

REPORT NUMBER: SP1-1908-441-10-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-10-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2200K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-10-R4

Photopic Flux vs. Wavelength




#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 1768 | NR | 490 | 5206 | NR | 620 | 130919 | NR | 750 | 8553 | NR | 880 | 2713 | NR |
| 365 | 1569 | NR | 495 | 7286 | NR | 625 | 125335 | NR | 755 | 7696 | NR | 885 | 2316 | NR |
| 370 | 1594 | NR | 500 | 10654 | NR | 630 | 118388 | NR | 760 | 6978 | NR | 890 | 2539 | NR |
| 375 | 1744 | NR | 505 | 15189 | NR | 635 | 111855 | NR | 765 | 6377 | NR | 895 | 1933 | NR |
| 380 | 1659 | NR | 510 | 20541 | NR | 640 | 104062 | NR | 770 | 5600 | NR | 900 | 2216 | NR |
| 385 | 1504 | NR | 515 | 26492 | NR | 645 | 96365 | NR | 775 | 5000 | NR | 905 | 2067 | NR |
| 390 | 1541 | NR | 520 | 32294 | NR | 650 | 88651 | NR | 780 | 4709 | NR | 910 | 1959 | NR |
| 395 | 1355 | NR | 525 | 38123 | NR | 655 | 81152 | NR | 785 | 4305 | NR | 915 | 1874 | NR |
| 400 | 1243 | NR | 530 | 43232 | NR | 660 | 73523 | NR | 790 | 4040 | NR | 920 | 1484 | NR |
| 405 | 1417 | NR | 535 | 48012 | NR | 665 | 66123 | NR | 795 | 3642 | NR | 925 | 1914 | NR |
| 410 | 2147 | NR | 540 | 52623 | NR | 670 | 58677 | NR | 800 | 3594 | NR | 930 | 1948 | NR |
| 415 | 3837 | NR | 545 | 57516 | NR | 675 | 52349 | NR | 805 | 3190 | NR | 935 | 2079 | NR |
| 420 | 7159 | NR | 550 | 62613 | NR | 680 | 46159 | NR | 810 | 3241 | NR | 940 | 2263 | NR |
| 425 | 12599 | NR | 555 | 68554 | NR | 685 | 40525 | NR | 815 | 2732 | NR | 945 | 1688 | NR |
| 430 | 19019 | NR | 560 | 75325 | NR | 690 | 35615 | NR | 820 | 2612 | NR | 950 | 1560 | NR |
| 435 | 24875 | NR | 565 | 82533 | NR | 695 | 31158 | NR | 825 | 2966 | NR | 955 | 2826 | NR |
| 440 | 29103 | NR | 570 | 90909 | NR | 700 | 27409 | NR | 830 | 2574 | NR | 960 | 1477 | NR |
| 445 | 29901 | NR | 575 | 99621 | NR | 705 | 24204 | NR | 835 | 2633 | NR | 965 | 1568 | NR |
| 450 | 24862 | NR | 580 | 108484 | NR | 710 | 21558 | NR | 840 | 2526 | NR | 970 | 2030 | NR |
| 455 | 15942 | NR | 585 | 116679 | NR | 715 | 19222 | NR | 845 | 2631 | NR | 975 | 1986 | NR |
| 460 | 9916 | NR | 590 | 123752 | NR | 720 | 17310 | NR | 850 | 2079 | NR | 980 | 2540 | NR |
| 465 | 7051 | NR | 595 | 129324 | NR | 725 | 15280 | NR | 855 | 2309 | NR | 985 | 1139 | NR |
| 470 | 5227 | NR | 600 | 134082 | NR | 730 | 13282 | NR | 860 | 2528 | NR | 990 | 2018 | NR |
| 475 | 4257 | NR | 605 | 135698 | NR | 735 | 11753 | NR | 865 | 2121 | NR | 995 | 3445 | NR |
| 480 | 4052 | NR | 610 | 135144 | NR | 740 | 10654 | NR | 870 | 2751 | NR | 1000 | 3704 | NR |
| 485 | 4298 | NR | 615 | 134180 | NR | 745 | 9451 | NR | 875 | 2317 | NR | | | |

REPORT NUMBER: SP1-1908-441-10-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 4696.9

S/P: 0.85

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 1768 | NR | 490 | 5206 | NR | 620 | 130919 | NR | 750 | 8553 | NR | 880 | 2713 | NR |
| 365 | 1569 | NR | 495 | 7286 | NR | 625 | 125335 | NR | 755 | 7696 | NR | 885 | 2316 | NR |
| 370 | 1594 | NR | 500 | 10654 | NR | 630 | 118388 | NR | 760 | 6978 | NR | 890 | 2539 | NR |
| 375 | 1744 | NR | 505 | 15189 | NR | 635 | 111855 | NR | 765 | 6377 | NR | 895 | 1933 | NR |
| 380 | 1659 | NR | 510 | 20541 | NR | 640 | 104062 | NR | 770 | 5600 | NR | 900 | 2216 | NR |
| 385 | 1504 | NR | 515 | 26492 | NR | 645 | 96365 | NR | 775 | 5000 | NR | 905 | 2067 | NR |
| 390 | 1541 | NR | 520 | 32294 | NR | 650 | 88651 | NR | 780 | 4709 | NR | 910 | 1959 | NR |
| 395 | 1355 | NR | 525 | 38123 | NR | 655 | 81152 | NR | 785 | 4305 | NR | 915 | 1874 | NR |
| 400 | 1243 | NR | 530 | 43232 | NR | 660 | 73523 | NR | 790 | 4040 | NR | 920 | 1484 | NR |
| 405 | 1417 | NR | 535 | 48012 | NR | 665 | 66123 | NR | 795 | 3642 | NR | 925 | 1914 | NR |
| 410 | 2147 | NR | 540 | 52623 | NR | 670 | 58677 | NR | 800 | 3594 | NR | 930 | 1948 | NR |
| 415 | 3837 | NR | 545 | 57516 | NR | 675 | 52349 | NR | 805 | 3190 | NR | 935 | 2079 | NR |
| 420 | 7159 | NR | 550 | 62613 | NR | 680 | 46159 | NR | 810 | 3241 | NR | 940 | 2263 | NR |
| 425 | 12599 | NR | 555 | 68554 | NR | 685 | 40525 | NR | 815 | 2732 | NR | 945 | 1688 | NR |
| 430 | 19019 | NR | 560 | 75325 | NR | 690 | 35615 | NR | 820 | 2612 | NR | 950 | 1560 | NR |
| 435 | 24875 | NR | 565 | 82533 | NR | 695 | 31158 | NR | 825 | 2966 | NR | 955 | 2826 | NR |
| 440 | 29103 | NR | 570 | 90909 | NR | 700 | 27409 | NR | 830 | 2574 | NR | 960 | 1477 | NR |
| 445 | 29901 | NR | 575 | 99621 | NR | 705 | 24204 | NR | 835 | 2633 | NR | 965 | 1568 | NR |
| 450 | 24862 | NR | 580 | 108484 | NR | 710 | 21558 | NR | 840 | 2526 | NR | 970 | 2030 | NR |
| 455 | 15942 | NR | 585 | 116679 | NR | 715 | 19222 | NR | 845 | 2631 | NR | 975 | 1986 | NR |
| 460 | 9916 | NR | 590 | 123752 | NR | 720 | 17310 | NR | 850 | 2079 | NR | 980 | 2540 | NR |
| 465 | 7051 | NR | 595 | 129324 | NR | 725 | 15280 | NR | 855 | 2309 | NR | 985 | 1139 | NR |
| 470 | 5227 | NR | 600 | 134082 | NR | 730 | 13282 | NR | 860 | 2528 | NR | 990 | 2018 | NR |
| 475 | 4257 | NR | 605 | 135698 | NR | 735 | 11753 | NR | 865 | 2121 | NR | 995 | 3445 | NR |
| 480 | 4052 | NR | 610 | 135144 | NR | 740 | 10654 | NR | 870 | 2751 | NR | 1000 | 3704 | NR |
| 485 | 4298 | NR | 615 | 134180 | NR | 745 | 9451 | NR | 875 | 2317 | NR | | | |

REPORT NUMBER: SP1-1908-441-10-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 1470.8 M/P: 0.27


| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 1768 | NR | 490 | 5206 | NR | 620 | 130919 | NR | 750 | 8553 | NR | 880 | 2713 | NR |
| 365 | 1569 | NR | 495 | 7286 | NR | 625 | 125335 | NR | 755 | 7696 | NR | 885 | 2316 | NR |
| 370 | 1594 | NR | 500 | 10654 | NR | 630 | 118388 | NR | 760 | 6978 | NR | 890 | 2539 | NR |
| 375 | 1744 | NR | 505 | 15189 | NR | 635 | 111855 | NR | 765 | 6377 | NR | 895 | 1933 | NR |
| 380 | 1659 | NR | 510 | 20541 | NR | 640 | 104062 | NR | 770 | 5600 | NR | 900 | 2216 | NR |
| 385 | 1504 | NR | 515 | 26492 | NR | 645 | 96365 | NR | 775 | 5000 | NR | 905 | 2067 | NR |
| 390 | 1541 | NR | 520 | 32294 | NR | 650 | 88651 | NR | 780 | 4709 | NR | 910 | 1959 | NR |
| 395 | 1355 | NR | 525 | 38123 | NR | 655 | 81152 | NR | 785 | 4305 | NR | 915 | 1874 | NR |
| 400 | 1243 | NR | 530 | 43232 | NR | 660 | 73523 | NR | 790 | 4040 | NR | 920 | 1484 | NR |
| 405 | 1417 | NR | 535 | 48012 | NR | 665 | 66123 | NR | 795 | 3642 | NR | 925 | 1914 | NR |
| 410 | 2147 | NR | 540 | 52623 | NR | 670 | 58677 | NR | 800 | 3594 | NR | 930 | 1948 | NR |
| 415 | 3837 | NR | 545 | 57516 | NR | 675 | 52349 | NR | 805 | 3190 | NR | 935 | 2079 | NR |
| 420 | 7159 | NR | 550 | 62613 | NR | 680 | 46159 | NR | 810 | 3241 | NR | 940 | 2263 | NR |
| 425 | 12599 | NR | 555 | 68554 | NR | 685 | 40525 | NR | 815 | 2732 | NR | 945 | 1688 | NR |
| 430 | 19019 | NR | 560 | 75325 | NR | 690 | 35615 | NR | 820 | 2612 | NR | 950 | 1560 | NR |
| 435 | 24875 | NR | 565 | 82533 | NR | 695 | 31158 | NR | 825 | 2966 | NR | 955 | 2826 | NR |
| 440 | 29103 | NR | 570 | 90909 | NR | 700 | 27409 | NR | 830 | 2574 | NR | 960 | 1477 | NR |
| 445 | 29901 | NR | 575 | 99621 | NR | 705 | 24204 | NR | 835 | 2633 | NR | 965 | 1568 | NR |
| 450 | 24862 | NR | 580 | 108484 | NR | 710 | 21558 | NR | 840 | 2526 | NR | 970 | 2030 | NR |
| 455 | 15942 | NR | 585 | 116679 | NR | 715 | 19222 | NR | 845 | 2631 | NR | 975 | 1986 | NR |
| 460 | 9916 | NR | 590 | 123752 | NR | 720 | 17310 | NR | 850 | 2079 | NR | 980 | 2540 | NR |
| 465 | 7051 | NR | 595 | 129324 | NR | 725 | 15280 | NR | 855 | 2309 | NR | 985 | 1139 | NR |
| 470 | 5227 | NR | 600 | 134082 | NR | 730 | 13282 | NR | 860 | 2528 | NR | 990 | 2018 | NR |
| 475 | 4257 | NR | 605 | 135698 | NR | 735 | 11753 | NR | 865 | 2121 | NR | 995 | 3445 | NR |
| 480 | 4052 | NR | 610 | 135144 | NR | 740 | 10654 | NR | 870 | 2751 | NR | 1000 | 3704 | NR |
| 485 | 4298 | NR | 615 | 134180 | NR | 745 | 9451 | NR | 875 | 2317 | NR | | | |

REPORT NUMBER: SP1-1908-441-10-R4





TM-30-18

Summary

$R_f = 69.8$
 $R_g = 99.2$
 $CIE R_a = 72.0$
 $R_9 = -17.4$



Color Vector Graphics




REPORT NUMBER: SP1-1908-441-10-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)




| | | | |
|------------|------------|------------|------------|
| CES01 = 87 | CES26 = 56 | CES51 = 74 | CES76 = 56 |
| CES02 = 65 | CES27 = 76 | CES52 = 76 | CES77 = 81 |
| CES03 = 32 | CES28 = 83 | CES53 = 65 | CES78 = 63 |
| CES04 = 72 | CES29 = 46 | CES54 = 78 | CES79 = 84 |
| CES05 = 52 | CES30 = 48 | CES55 = 75 | CES80 = 84 |
| CES06 = 52 | CES31 = 51 | CES56 = 65 | CES81 = 63 |
| CES07 = 44 | CES32 = 51 | CES57 = 62 | CES82 = 92 |
| CES08 = 42 | CES33 = 53 | CES58 = 66 | CES83 = 83 |
| CES09 = 29 | CES34 = 70 | CES59 = 84 | CES84 = 92 |
| CES10 = 78 | CES35 = 85 | CES60 = 90 | CES85 = 81 |
| CES11 = 61 | CES36 = 78 | CES61 = 84 | CES86 = 56 |
| CES12 = 68 | CES37 = 80 | CES62 = 70 | CES87 = 78 |
| CES13 = 45 | CES38 = 53 | CES63 = 68 | CES88 = 72 |
| CES14 = 75 | CES39 = 90 | CES64 = 69 | CES89 = 62 |
| CES15 = 72 | CES40 = 84 | CES65 = 67 | CES90 = 67 |
| CES16 = 49 | CES41 = 75 | CES66 = 64 | CES91 = 90 |
| CES17 = 51 | CES42 = 79 | CES67 = 63 | CES92 = 67 |
| CES18 = 57 | CES43 = 64 | CES68 = 69 | CES93 = 79 |
| CES19 = 74 | CES44 = 98 | CES69 = 80 | CES94 = 52 |
| CES20 = 68 | CES45 = 73 | CES70 = 63 | CES95 = 76 |
| CES21 = 89 | CES46 = 67 | CES71 = 63 | CES96 = 78 |
| CES22 = 81 | CES47 = 60 | CES72 = 87 | CES97 = 77 |
| CES23 = 92 | CES48 = 48 | CES73 = 56 | CES98 = 71 |
| CES24 = 92 | CES49 = 64 | CES74 = 87 | CES99 = 65 |
| CES25 = 74 | CES50 = 74 | CES75 = 66 | |



REPORT NUMBER: SP1-1908-441-10-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-10-R4

TM-30-18

Measure Comparisons



(END OF REPORT)