

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P437437

Luminaire Tested: **ISC-SA1D-722-U-RW**

Issue Date: 12/9/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P437437  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-074-24)  
Test Lab: INNOVATION CENTER  
Issue Date: 12/9/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: ISC-SA1D-722-U-RW  
Description: IMPACT ELITE LED CYLINDER LUMINAIRE  
(1) 70 CRI, 2200K, 800mA LIGHTSQUARE WITH 16 LEDS AND RECTANGULAR WIDE OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4370 lumens  
Efficiency: N/A  
Efficacy: 96.7 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type III - Medium  
BUG Rating: B2 - U0 - G2  
  
Input Watts (W): 45.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P437437  
 CATALOG NUMBER: ISC-SA1D-722-U-RW

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.8 fc  
 Type III - Medium - N/A

REPORT NUMBER: P437437  
CATALOG NUMBER: ISC-SA1D-722-U-RW

### Luminous Intensity Polar Plot



— Vertical Plane Through 65-Deg Lateral      - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P437437  
 CATALOG NUMBER: ISC-SA1D-722-U-RW

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 2185.0   | 0.0    | 2185.0 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Street Side</b> | Lumens    | 2185.0   | 0.0    | 2185.0 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Total</b>       | Lumens    | 4370.0   | 0.0    | 4370.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 45.4   | 1.0       |
| 10°-20°   | 151.2  | 3.5       |
| 20°-30°   | 291.9  | 6.7       |
| 30°-40°   | 487.2  | 11.1      |
| 40°-50°   | 762.5  | 17.4      |
| 50°-60°   | 1031.0 | 23.6      |
| 60°-70°   | 1016.9 | 23.3      |
| 70°-80°   | 548.1  | 12.5      |
| 80°-90°   | 35.7   | 0.8       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 4370.0 | 100.0     |
| 0°-180°   | 4370.0 | 100.0     |

**Coefficient of Utilization**




REPORT NUMBER: P437437  
 CATALOG NUMBER: ISC-SA1D-722-U-RW

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 244.3  | 5.6       |                         |      |         |
| FM (30°-60°)   | 1140.4 | 26.1      |                         |      |         |
| FH (60°-80°)   | 782.5  | 17.9      |                         |      | G1/1800 |
| FVH (80°-90°)  | 17.9   | 0.4       |                         |      | G1/100  |
| BL (0°-30°)    | 244.3  | 5.6       | B1/500                  |      |         |
| BM (30°-60°)   | 1140.4 | 26.1      | B2/2500                 |      |         |
| BH (60°-80°)   | 782.5  | 17.9      | B2/1000                 |      | G2/1000 |
| BVH (80°-90°)  | 17.9   | 0.4       |                         |      | G1/100  |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B2-U0-G2**  
 Type III Medium





REPORT NUMBER: P437437  
 CATALOG NUMBER: ISC-SA1D-722-U-RW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    | 90°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 460.0  | 460.0  | 460.0  | 460.0  | 460.0  | 460.0  | 460.0  | 460.0  | 460.0  | 460.0  | 460.0  |
| 2.5°  | 461.6  | 464.6  | 461.6  | 461.6  | 464.6  | 463.1  | 466.2  | 466.2  | 466.2  | 467.7  | 466.2  |
| 5°    | 458.5  | 458.5  | 458.5  | 461.6  | 466.2  | 469.2  | 472.3  | 476.9  | 476.9  | 481.5  | 478.4  |
| 7.5°  | 455.4  | 455.4  | 457.0  | 461.6  | 467.7  | 473.8  | 483.0  | 493.8  | 496.8  | 499.9  | 499.9  |
| 10°   | 460.0  | 460.0  | 463.1  | 469.2  | 476.9  | 486.1  | 498.4  | 512.2  | 522.9  | 527.5  | 526.0  |
| 12.5° | 466.2  | 467.7  | 472.3  | 481.5  | 492.2  | 504.5  | 516.8  | 533.6  | 547.4  | 555.1  | 555.1  |
| 15°   | 472.3  | 473.8  | 481.5  | 495.3  | 515.2  | 527.5  | 541.3  | 558.2  | 573.5  | 584.2  | 584.2  |
| 17.5° | 484.6  | 486.1  | 496.8  | 516.8  | 539.8  | 556.6  | 568.9  | 579.6  | 593.4  | 607.2  | 607.2  |
| 20°   | 501.4  | 506.0  | 519.8  | 545.9  | 570.4  | 587.3  | 596.5  | 601.1  | 608.8  | 619.5  | 622.6  |
| 22.5° | 527.5  | 530.6  | 545.9  | 573.5  | 602.6  | 622.6  | 628.7  | 622.6  | 622.6  | 633.3  | 633.3  |
| 25°   | 559.7  | 559.7  | 578.1  | 610.3  | 641.0  | 657.8  | 659.4  | 645.6  | 639.4  | 647.1  | 647.1  |
| 27.5° | 588.8  | 591.9  | 607.2  | 642.5  | 674.7  | 694.6  | 693.1  | 674.7  | 654.8  | 659.4  | 660.9  |
| 30°   | 627.2  | 627.2  | 647.1  | 680.8  | 716.1  | 731.4  | 734.5  | 703.8  | 676.2  | 674.7  | 674.7  |
| 32.5° | 671.6  | 676.2  | 693.1  | 723.8  | 757.5  | 779.0  | 774.4  | 737.6  | 702.3  | 696.2  | 700.8  |
| 35°   | 720.7  | 723.8  | 745.2  | 777.4  | 803.5  | 820.4  | 811.2  | 772.8  | 734.5  | 725.3  | 728.4  |
| 37.5° | 777.4  | 779.0  | 795.9  | 829.6  | 861.8  | 866.4  | 852.6  | 814.3  | 772.8  | 759.0  | 765.2  |
| 40°   | 828.1  | 838.8  | 860.3  | 889.4  | 915.5  | 927.7  | 901.7  | 864.9  | 818.9  | 811.2  | 817.3  |
| 42.5° | 892.5  | 892.5  | 917.0  | 949.2  | 976.8  | 984.5  | 961.5  | 917.0  | 871.0  | 866.4  | 872.5  |
| 45°   | 938.5  | 944.6  | 973.7  | 1009.0 | 1038.1 | 1045.8 | 1025.9 | 973.7  | 926.2  | 920.1  | 926.2  |
| 47.5° | 987.5  | 992.1  | 1015.1 | 1058.1 | 1094.9 | 1102.5 | 1084.1 | 1038.1 | 978.3  | 978.3  | 982.9  |
| 50°   | 1019.7 | 1025.9 | 1053.5 | 1094.9 | 1142.4 | 1159.3 | 1137.8 | 1091.8 | 1038.1 | 1032.0 | 1039.7 |
| 52.5° | 1050.4 | 1053.5 | 1081.1 | 1122.5 | 1180.7 | 1211.4 | 1191.5 | 1145.5 | 1090.3 | 1093.3 | 1096.4 |
| 55°   | 1042.7 | 1047.3 | 1084.1 | 1143.9 | 1209.9 | 1245.1 | 1234.4 | 1202.2 | 1142.4 | 1150.1 | 1162.3 |
| 57.5° | 999.8  | 1001.3 | 1048.9 | 1120.9 | 1217.5 | 1271.2 | 1275.8 | 1242.1 | 1189.9 | 1202.2 | 1217.5 |
| 60°   | 903.2  | 915.5  | 963.0  | 1050.4 | 1189.9 | 1289.6 | 1303.4 | 1283.5 | 1240.5 | 1262.0 | 1269.7 |
| 62.5° | 737.6  | 743.7  | 808.1  | 935.4  | 1110.2 | 1285.0 | 1332.6 | 1317.2 | 1280.4 | 1304.9 | 1320.3 |
| 65°   | 483.0  | 503.0  | 582.7  | 737.6  | 967.6  | 1228.3 | 1383.2 | 1360.2 | 1326.4 | 1338.7 | 1355.6 |
| 67.5° | 292.9  | 297.5  | 352.7  | 484.6  | 740.6  | 1099.5 | 1383.2 | 1424.6 | 1361.7 | 1360.2 | 1370.9 |
| 70°   | 150.3  | 153.3  | 173.3  | 257.6  | 447.8  | 818.9  | 1251.3 | 1453.7 | 1393.9 | 1367.8 | 1378.6 |
| 72.5° | 101.2  | 98.1   | 102.7  | 121.1  | 203.9  | 435.5  | 929.3  | 1364.8 | 1449.1 | 1403.1 | 1407.7 |
| 75°   | 75.1   | 75.1   | 79.7   | 82.8   | 101.2  | 194.7  | 533.6  | 1082.6 | 1390.8 | 1369.4 | 1352.5 |
| 77.5° | 55.2   | 56.7   | 59.8   | 61.3   | 65.9   | 87.4   | 214.7  | 625.6  | 1025.9 | 1191.5 | 1186.9 |
| 80°   | 36.8   | 38.3   | 44.5   | 42.9   | 42.9   | 49.1   | 82.8   | 223.9  | 398.7  | 429.4  | 407.9  |
| 82.5° | 21.5   | 19.9   | 26.1   | 26.1   | 24.5   | 24.5   | 36.8   | 69.0   | 108.9  | 75.1   | 55.2   |
| 85°   | 1.5    | 3.1    | 4.6    | 4.6    | 4.6    | 4.6    | 9.2    | 15.3   | 27.6   | 21.5   | 16.9   |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 1.5    | 1.5    | 1.5    | 3.1    | 3.1    | 3.1    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269





**Test Information**

Test Method: LM-79-2008 Report  
 Number: SP1-1908-441-10-R4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/28/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGRAW-EDISON  
 Catalog Number: **SA1C-722-U-5WQ**  
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

\*\*\*THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.\*\*\*TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

**Spectral Parameters**

CCT (K): 2237  
 CIE u': 0.2876  
 CIE v': 0.5346  
 Duv: -0.0006  
 CIE x: 0.5005  
 CIE y: 0.4134  
 CIE z: 0.0860  
 Peak Wavelength (nm): 603  
 Dominant Wavelength (nm): 587  
 Purity: 74.5  
 Rf: 69.8  
 Rg: 99.2

|           |      |      |       |
|-----------|------|------|-------|
| CRI (Ra): | 72.0 |      |       |
| R1:       | 68.9 | R9:  | -17.4 |
| R2:       | 83.0 | R10: | 61.3  |
| R3:       | 95.2 | R11: | 59.8  |
| R4:       | 66.2 | R12: | 50.5  |
| R5:       | 65.9 | R13: | 71.1  |
| R6:       | 76.3 | R14: | 96.9  |
| R7:       | 76.7 |      |       |
| R8:       | 43.8 |      |       |



**Test Conditions**


Stabilization Time: 71M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 24.7/41%  
 Sphere Temperature (°C): 25.6

REPORT NUMBER: SP1-1908-441-10-R4

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/28/2019        | 12/28/2019           |
| Power Meter                    | IN0071                | 12/5/2018        | 12/5/2019            |
| AC Power Source                | IN0063                | 12/5/2018        | 12/5/2019            |
| DC Power Source                | IN0208                | 12/5/2018        | 12/5/2019            |
| Sphere Thermometer             | IN0085                | 12/5/2018        | 12/5/2019            |
| Room Thermometer               | IN0046                | 12/5/2018        | 12/5/2019            |

REPORT NUMBER: SP1-1908-441-10-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2200K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-10-R4

**Photopic Flux vs. Wavelength**



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 1768          | NR            | 490    | 5206          | NR            | 620    | 130919        | NR            | 750    | 8553          | NR            | 880    | 2713          | NR            |
| 365    | 1569          | NR            | 495    | 7286          | NR            | 625    | 125335        | NR            | 755    | 7696          | NR            | 885    | 2316          | NR            |
| 370    | 1594          | NR            | 500    | 10654         | NR            | 630    | 118388        | NR            | 760    | 6978          | NR            | 890    | 2539          | NR            |
| 375    | 1744          | NR            | 505    | 15189         | NR            | 635    | 111855        | NR            | 765    | 6377          | NR            | 895    | 1933          | NR            |
| 380    | 1659          | NR            | 510    | 20541         | NR            | 640    | 104062        | NR            | 770    | 5600          | NR            | 900    | 2216          | NR            |
| 385    | 1504          | NR            | 515    | 26492         | NR            | 645    | 96365         | NR            | 775    | 5000          | NR            | 905    | 2067          | NR            |
| 390    | 1541          | NR            | 520    | 32294         | NR            | 650    | 88651         | NR            | 780    | 4709          | NR            | 910    | 1959          | NR            |
| 395    | 1355          | NR            | 525    | 38123         | NR            | 655    | 81152         | NR            | 785    | 4305          | NR            | 915    | 1874          | NR            |
| 400    | 1243          | NR            | 530    | 43232         | NR            | 660    | 73523         | NR            | 790    | 4040          | NR            | 920    | 1484          | NR            |
| 405    | 1417          | NR            | 535    | 48012         | NR            | 665    | 66123         | NR            | 795    | 3642          | NR            | 925    | 1914          | NR            |
| 410    | 2147          | NR            | 540    | 52623         | NR            | 670    | 58677         | NR            | 800    | 3594          | NR            | 930    | 1948          | NR            |
| 415    | 3837          | NR            | 545    | 57516         | NR            | 675    | 52349         | NR            | 805    | 3190          | NR            | 935    | 2079          | NR            |
| 420    | 7159          | NR            | 550    | 62613         | NR            | 680    | 46159         | NR            | 810    | 3241          | NR            | 940    | 2263          | NR            |
| 425    | 12599         | NR            | 555    | 68554         | NR            | 685    | 40525         | NR            | 815    | 2732          | NR            | 945    | 1688          | NR            |
| 430    | 19019         | NR            | 560    | 75325         | NR            | 690    | 35615         | NR            | 820    | 2612          | NR            | 950    | 1560          | NR            |
| 435    | 24875         | NR            | 565    | 82533         | NR            | 695    | 31158         | NR            | 825    | 2966          | NR            | 955    | 2826          | NR            |
| 440    | 29103         | NR            | 570    | 90909         | NR            | 700    | 27409         | NR            | 830    | 2574          | NR            | 960    | 1477          | NR            |
| 445    | 29901         | NR            | 575    | 99621         | NR            | 705    | 24204         | NR            | 835    | 2633          | NR            | 965    | 1568          | NR            |
| 450    | 24862         | NR            | 580    | 108484        | NR            | 710    | 21558         | NR            | 840    | 2526          | NR            | 970    | 2030          | NR            |
| 455    | 15942         | NR            | 585    | 116679        | NR            | 715    | 19222         | NR            | 845    | 2631          | NR            | 975    | 1986          | NR            |
| 460    | 9916          | NR            | 590    | 123752        | NR            | 720    | 17310         | NR            | 850    | 2079          | NR            | 980    | 2540          | NR            |
| 465    | 7051          | NR            | 595    | 129324        | NR            | 725    | 15280         | NR            | 855    | 2309          | NR            | 985    | 1139          | NR            |
| 470    | 5227          | NR            | 600    | 134082        | NR            | 730    | 13282         | NR            | 860    | 2528          | NR            | 990    | 2018          | NR            |
| 475    | 4257          | NR            | 605    | 135698        | NR            | 735    | 11753         | NR            | 865    | 2121          | NR            | 995    | 3445          | NR            |
| 480    | 4052          | NR            | 610    | 135144        | NR            | 740    | 10654         | NR            | 870    | 2751          | NR            | 1000   | 3704          | NR            |
| 485    | 4298          | NR            | 615    | 134180        | NR            | 745    | 9451          | NR            | 875    | 2317          | NR            |        |               |               |

REPORT NUMBER: SP1-1908-441-10-R4

Scotopic Flux vs. Wavelength




Scotopic Lumens: 4696.9

S/P: 0.85

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 1768          | NR            | 490    | 5206          | NR            | 620    | 130919        | NR            | 750    | 8553          | NR            | 880    | 2713          | NR            |
| 365    | 1569          | NR            | 495    | 7286          | NR            | 625    | 125335        | NR            | 755    | 7696          | NR            | 885    | 2316          | NR            |
| 370    | 1594          | NR            | 500    | 10654         | NR            | 630    | 118388        | NR            | 760    | 6978          | NR            | 890    | 2539          | NR            |
| 375    | 1744          | NR            | 505    | 15189         | NR            | 635    | 111855        | NR            | 765    | 6377          | NR            | 895    | 1933          | NR            |
| 380    | 1659          | NR            | 510    | 20541         | NR            | 640    | 104062        | NR            | 770    | 5600          | NR            | 900    | 2216          | NR            |
| 385    | 1504          | NR            | 515    | 26492         | NR            | 645    | 96365         | NR            | 775    | 5000          | NR            | 905    | 2067          | NR            |
| 390    | 1541          | NR            | 520    | 32294         | NR            | 650    | 88651         | NR            | 780    | 4709          | NR            | 910    | 1959          | NR            |
| 395    | 1355          | NR            | 525    | 38123         | NR            | 655    | 81152         | NR            | 785    | 4305          | NR            | 915    | 1874          | NR            |
| 400    | 1243          | NR            | 530    | 43232         | NR            | 660    | 73523         | NR            | 790    | 4040          | NR            | 920    | 1484          | NR            |
| 405    | 1417          | NR            | 535    | 48012         | NR            | 665    | 66123         | NR            | 795    | 3642          | NR            | 925    | 1914          | NR            |
| 410    | 2147          | NR            | 540    | 52623         | NR            | 670    | 58677         | NR            | 800    | 3594          | NR            | 930    | 1948          | NR            |
| 415    | 3837          | NR            | 545    | 57516         | NR            | 675    | 52349         | NR            | 805    | 3190          | NR            | 935    | 2079          | NR            |
| 420    | 7159          | NR            | 550    | 62613         | NR            | 680    | 46159         | NR            | 810    | 3241          | NR            | 940    | 2263          | NR            |
| 425    | 12599         | NR            | 555    | 68554         | NR            | 685    | 40525         | NR            | 815    | 2732          | NR            | 945    | 1688          | NR            |
| 430    | 19019         | NR            | 560    | 75325         | NR            | 690    | 35615         | NR            | 820    | 2612          | NR            | 950    | 1560          | NR            |
| 435    | 24875         | NR            | 565    | 82533         | NR            | 695    | 31158         | NR            | 825    | 2966          | NR            | 955    | 2826          | NR            |
| 440    | 29103         | NR            | 570    | 90909         | NR            | 700    | 27409         | NR            | 830    | 2574          | NR            | 960    | 1477          | NR            |
| 445    | 29901         | NR            | 575    | 99621         | NR            | 705    | 24204         | NR            | 835    | 2633          | NR            | 965    | 1568          | NR            |
| 450    | 24862         | NR            | 580    | 108484        | NR            | 710    | 21558         | NR            | 840    | 2526          | NR            | 970    | 2030          | NR            |
| 455    | 15942         | NR            | 585    | 116679        | NR            | 715    | 19222         | NR            | 845    | 2631          | NR            | 975    | 1986          | NR            |
| 460    | 9916          | NR            | 590    | 123752        | NR            | 720    | 17310         | NR            | 850    | 2079          | NR            | 980    | 2540          | NR            |
| 465    | 7051          | NR            | 595    | 129324        | NR            | 725    | 15280         | NR            | 855    | 2309          | NR            | 985    | 1139          | NR            |
| 470    | 5227          | NR            | 600    | 134082        | NR            | 730    | 13282         | NR            | 860    | 2528          | NR            | 990    | 2018          | NR            |
| 475    | 4257          | NR            | 605    | 135698        | NR            | 735    | 11753         | NR            | 865    | 2121          | NR            | 995    | 3445          | NR            |
| 480    | 4052          | NR            | 610    | 135144        | NR            | 740    | 10654         | NR            | 870    | 2751          | NR            | 1000   | 3704          | NR            |
| 485    | 4298          | NR            | 615    | 134180        | NR            | 745    | 9451          | NR            | 875    | 2317          | NR            |        |               |               |

REPORT NUMBER: SP1-1908-441-10-R4

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 1470.8 M/P: 0.27**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 1768          | NR            | 490    | 5206          | NR            | 620    | 130919        | NR            | 750    | 8553          | NR            | 880    | 2713          | NR            |
| 365    | 1569          | NR            | 495    | 7286          | NR            | 625    | 125335        | NR            | 755    | 7696          | NR            | 885    | 2316          | NR            |
| 370    | 1594          | NR            | 500    | 10654         | NR            | 630    | 118388        | NR            | 760    | 6978          | NR            | 890    | 2539          | NR            |
| 375    | 1744          | NR            | 505    | 15189         | NR            | 635    | 111855        | NR            | 765    | 6377          | NR            | 895    | 1933          | NR            |
| 380    | 1659          | NR            | 510    | 20541         | NR            | 640    | 104062        | NR            | 770    | 5600          | NR            | 900    | 2216          | NR            |
| 385    | 1504          | NR            | 515    | 26492         | NR            | 645    | 96365         | NR            | 775    | 5000          | NR            | 905    | 2067          | NR            |
| 390    | 1541          | NR            | 520    | 32294         | NR            | 650    | 88651         | NR            | 780    | 4709          | NR            | 910    | 1959          | NR            |
| 395    | 1355          | NR            | 525    | 38123         | NR            | 655    | 81152         | NR            | 785    | 4305          | NR            | 915    | 1874          | NR            |
| 400    | 1243          | NR            | 530    | 43232         | NR            | 660    | 73523         | NR            | 790    | 4040          | NR            | 920    | 1484          | NR            |
| 405    | 1417          | NR            | 535    | 48012         | NR            | 665    | 66123         | NR            | 795    | 3642          | NR            | 925    | 1914          | NR            |
| 410    | 2147          | NR            | 540    | 52623         | NR            | 670    | 58677         | NR            | 800    | 3594          | NR            | 930    | 1948          | NR            |
| 415    | 3837          | NR            | 545    | 57516         | NR            | 675    | 52349         | NR            | 805    | 3190          | NR            | 935    | 2079          | NR            |
| 420    | 7159          | NR            | 550    | 62613         | NR            | 680    | 46159         | NR            | 810    | 3241          | NR            | 940    | 2263          | NR            |
| 425    | 12599         | NR            | 555    | 68554         | NR            | 685    | 40525         | NR            | 815    | 2732          | NR            | 945    | 1688          | NR            |
| 430    | 19019         | NR            | 560    | 75325         | NR            | 690    | 35615         | NR            | 820    | 2612          | NR            | 950    | 1560          | NR            |
| 435    | 24875         | NR            | 565    | 82533         | NR            | 695    | 31158         | NR            | 825    | 2966          | NR            | 955    | 2826          | NR            |
| 440    | 29103         | NR            | 570    | 90909         | NR            | 700    | 27409         | NR            | 830    | 2574          | NR            | 960    | 1477          | NR            |
| 445    | 29901         | NR            | 575    | 99621         | NR            | 705    | 24204         | NR            | 835    | 2633          | NR            | 965    | 1568          | NR            |
| 450    | 24862         | NR            | 580    | 108484        | NR            | 710    | 21558         | NR            | 840    | 2526          | NR            | 970    | 2030          | NR            |
| 455    | 15942         | NR            | 585    | 116679        | NR            | 715    | 19222         | NR            | 845    | 2631          | NR            | 975    | 1986          | NR            |
| 460    | 9916          | NR            | 590    | 123752        | NR            | 720    | 17310         | NR            | 850    | 2079          | NR            | 980    | 2540          | NR            |
| 465    | 7051          | NR            | 595    | 129324        | NR            | 725    | 15280         | NR            | 855    | 2309          | NR            | 985    | 1139          | NR            |
| 470    | 5227          | NR            | 600    | 134082        | NR            | 730    | 13282         | NR            | 860    | 2528          | NR            | 990    | 2018          | NR            |
| 475    | 4257          | NR            | 605    | 135698        | NR            | 735    | 11753         | NR            | 865    | 2121          | NR            | 995    | 3445          | NR            |
| 480    | 4052          | NR            | 610    | 135144        | NR            | 740    | 10654         | NR            | 870    | 2751          | NR            | 1000   | 3704          | NR            |
| 485    | 4298          | NR            | 615    | 134180        | NR            | 745    | 9451          | NR            | 875    | 2317          | NR            |        |               |               |

REPORT NUMBER: SP1-1908-441-10-R4



TM-30-18

**Summary**

$R_f = 69.8$   
 $R_g = 99.2$   
 $CIE R_a = 72.0$   
 $R_g = -17.4$



**Color Vector Graphics**



REPORT NUMBER: SP1-1908-441-10-R4

TM-30-18

**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 87 | CES26 = 56 | CES51 = 74 | CES76 = 56 |
| CES02 = 65 | CES27 = 76 | CES52 = 76 | CES77 = 81 |
| CES03 = 32 | CES28 = 83 | CES53 = 65 | CES78 = 63 |
| CES04 = 72 | CES29 = 46 | CES54 = 78 | CES79 = 84 |
| CES05 = 52 | CES30 = 48 | CES55 = 75 | CES80 = 84 |
| CES06 = 52 | CES31 = 51 | CES56 = 65 | CES81 = 63 |
| CES07 = 44 | CES32 = 51 | CES57 = 62 | CES82 = 92 |
| CES08 = 42 | CES33 = 53 | CES58 = 66 | CES83 = 83 |
| CES09 = 29 | CES34 = 70 | CES59 = 84 | CES84 = 92 |
| CES10 = 78 | CES35 = 85 | CES60 = 90 | CES85 = 81 |
| CES11 = 61 | CES36 = 78 | CES61 = 84 | CES86 = 56 |
| CES12 = 68 | CES37 = 80 | CES62 = 70 | CES87 = 78 |
| CES13 = 45 | CES38 = 53 | CES63 = 68 | CES88 = 72 |
| CES14 = 75 | CES39 = 90 | CES64 = 69 | CES89 = 62 |
| CES15 = 72 | CES40 = 84 | CES65 = 67 | CES90 = 67 |
| CES16 = 49 | CES41 = 75 | CES66 = 64 | CES91 = 90 |
| CES17 = 51 | CES42 = 79 | CES67 = 63 | CES92 = 67 |
| CES18 = 57 | CES43 = 64 | CES68 = 69 | CES93 = 79 |
| CES19 = 74 | CES44 = 98 | CES69 = 80 | CES94 = 52 |
| CES20 = 68 | CES45 = 73 | CES70 = 63 | CES95 = 76 |
| CES21 = 89 | CES46 = 67 | CES71 = 63 | CES96 = 78 |
| CES22 = 81 | CES47 = 60 | CES72 = 87 | CES97 = 77 |
| CES23 = 92 | CES48 = 48 | CES73 = 56 | CES98 = 71 |
| CES24 = 92 | CES49 = 64 | CES74 = 87 | CES99 = 65 |
| CES25 = 74 | CES50 = 74 | CES75 = 66 |            |






REPORT NUMBER: SP1-1908-441-10-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-10-R4

TM-30-18

Measure Comparisons



(END OF REPORT)