

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P437786

Luminaire Tested: **ISC-SA1F-722-U-SLL-HSS**

Issue Date: 12/9/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P437786  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-074-21)  
Test Lab: INNOVATION CENTER  
Issue Date: 12/9/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: ISC-SA1F-722-U-SLL-HSS  
Description: IMPACT ELITE LED CYLINDER LUMINAIRE  
(1) 70 CRI, 2200K, 1200mA LIGHTSQUARE WITH 16 LEDS AND SPILL LIGHT  
ELIMINATOR LEFT OPTICS WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4292 lumens  
Efficiency: N/A  
Efficacy: 65.0 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B1 - U0 - G1  
  
Input Watts (W): 66  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P437786  
 CATALOG NUMBER: ISC-SA1F-722-U-SLL-HSS

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 2.9 fc  
 Type IV - Short - N/A

REPORT NUMBER: P437786  
CATALOG NUMBER: ISC-SA1F-722-U-SLL-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 55-Deg Lateral      - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P437786  
 CATALOG NUMBER: ISC-SA1F-722-U-SLL-HSS


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 751.8    | 0.0    | 751.8  |
|                    | % Fixture | 17.5     | 0.0    | 17.5   |
| <b>Street Side</b> | Lumens    | 3540.2   | 0.0    | 3540.2 |
|                    | % Fixture | 82.5     | 0.0    | 82.5   |
| <b>Total</b>       | Lumens    | 4292.0   | 0.0    | 4292.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 107.9  | 2.5       |
| 10°-20°   | 211.4  | 4.9       |
| 20°-30°   | 310.7  | 7.2       |
| 30°-40°   | 464.7  | 10.8      |
| 40°-50°   | 687.5  | 16.0      |
| 50°-60°   | 988.1  | 23.0      |
| 60°-70°   | 1059.2 | 24.7      |
| 70°-80°   | 427.9  | 10.0      |
| 80°-90°   | 34.7   | 0.8       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 4292.0 | 100.0     |
| 0°-180°   | 4292.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P437786


CATALOG NUMBER: ISC-SA1F-722-U-SLL-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 450.4  | 10.5      |                         |      |         |
| FM (30°-60°)   | 1766.7 | 41.2      |                         |      |         |
| FH (60°-80°)   | 1291.5 | 30.1      |                         |      | G1/1800 |
| FVH (80°-90°)  | 31.5   | 0.7       |                         |      | G1/100  |
| BL (0°-30°)    | 179.6  | 4.2       | B1/500                  |      |         |
| BM (30°-60°)   | 373.6  | 8.7       | B1/1000                 |      |         |
| BH (60°-80°)   | 195.5  | 4.6       | B1/500                  |      | G1/500  |
| BVH (80°-90°)  | 3.2    | 0.1       |                         |      | G0/10   |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B1-U0-G1**

Type IV Short





REPORT NUMBER: P437786

CATALOG NUMBER: ISC-SA1F-722-U-SLL-HSS

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 1°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1448.2 | 1448.2 | 1448.2 | 1448.2 | 1448.2 | 1448.2 | 1448.2 | 1448.2 | 1448.2 | 1448.2 | 1448.2 |
| 2.5°  | 1555.9 | 1555.9 | 1568.3 | 1605.6 | 1647.1 | 1667.8 | 1690.6 | 1667.8 | 1663.6 | 1630.5 | 1605.6 |
| 5°    | 1508.3 | 1518.6 | 1558.0 | 1657.4 | 1763.1 | 1816.9 | 1846.0 | 1814.9 | 1758.9 | 1686.4 | 1595.3 |
| 7.5°  | 1400.5 | 1413.0 | 1458.5 | 1620.1 | 1765.2 | 1872.9 | 1924.7 | 1870.8 | 1775.5 | 1642.9 | 1510.3 |
| 10°   | 1284.5 | 1307.3 | 1367.4 | 1551.8 | 1719.6 | 1848.0 | 1920.5 | 1864.6 | 1746.5 | 1576.6 | 1413.0 |
| 12.5° | 1207.8 | 1224.4 | 1305.2 | 1489.6 | 1669.9 | 1783.8 | 1823.2 | 1810.7 | 1703.0 | 1545.5 | 1373.6 |
| 15°   | 1195.4 | 1216.1 | 1301.1 | 1485.5 | 1622.2 | 1690.6 | 1705.1 | 1721.6 | 1684.4 | 1549.7 | 1386.0 |
| 17.5° | 1249.3 | 1272.1 | 1367.4 | 1516.5 | 1578.7 | 1578.7 | 1593.2 | 1626.3 | 1661.6 | 1591.1 | 1460.6 |
| 20°   | 1359.1 | 1390.2 | 1495.8 | 1597.3 | 1555.9 | 1506.2 | 1508.3 | 1551.8 | 1647.1 | 1684.4 | 1593.2 |
| 22.5° | 1506.2 | 1547.6 | 1676.1 | 1723.7 | 1580.8 | 1466.8 | 1456.5 | 1493.8 | 1649.1 | 1779.7 | 1775.5 |
| 25°   | 1700.9 | 1750.7 | 1875.0 | 1872.9 | 1640.8 | 1450.2 | 1439.9 | 1466.8 | 1667.8 | 1883.2 | 1935.0 |
| 27.5° | 1877.0 | 1918.5 | 2042.8 | 1991.0 | 1700.9 | 1471.0 | 1448.2 | 1477.2 | 1682.3 | 1959.9 | 2078.0 |
| 30°   | 2026.2 | 2061.4 | 2171.2 | 2075.9 | 1752.7 | 1506.2 | 1466.8 | 1512.4 | 1713.4 | 2001.3 | 2206.4 |
| 32.5° | 2140.1 | 2191.9 | 2293.5 | 2142.2 | 1814.9 | 1551.8 | 1510.3 | 1572.5 | 1765.2 | 2055.2 | 2318.3 |
| 35°   | 2293.5 | 2320.4 | 2440.6 | 2208.5 | 1897.7 | 1649.1 | 1582.8 | 1665.7 | 1850.1 | 2125.6 | 2442.6 |
| 37.5° | 2426.1 | 2496.5 | 2575.2 | 2276.9 | 1999.3 | 1769.3 | 1696.8 | 1814.9 | 1966.1 | 2206.4 | 2587.6 |
| 40°   | 2583.5 | 2664.3 | 2749.2 | 2374.3 | 2092.5 | 1926.8 | 1895.7 | 2011.7 | 2140.1 | 2324.5 | 2730.6 |
| 42.5° | 2728.5 | 2803.1 | 2861.1 | 2488.2 | 2206.4 | 2104.9 | 2127.7 | 2249.9 | 2318.3 | 2446.8 | 2852.8 |
| 45°   | 2844.5 | 2910.8 | 2997.9 | 2566.9 | 2332.8 | 2303.8 | 2419.8 | 2515.1 | 2494.4 | 2552.4 | 2962.6 |
| 47.5° | 2964.7 | 3045.5 | 3080.7 | 2649.8 | 2496.5 | 2564.9 | 2772.0 | 2792.8 | 2678.8 | 2649.8 | 3057.9 |
| 50°   | 3047.6 | 3107.7 | 3130.5 | 2751.3 | 2697.5 | 2908.8 | 3074.5 | 3109.7 | 2879.8 | 2726.5 | 3182.2 |
| 52.5° | 3149.1 | 3207.1 | 3234.0 | 2871.5 | 2912.9 | 3217.5 | 3410.1 | 3401.9 | 3074.5 | 2852.8 | 3304.5 |
| 55°   | 3329.3 | 3383.2 | 3410.1 | 3018.6 | 3066.2 | 3482.7 | 3696.1 | 3687.8 | 3306.6 | 3035.2 | 3486.8 |
| 57.5° | 3457.8 | 3503.4 | 3546.9 | 3184.3 | 3256.8 | 3652.5 | 3890.8 | 3953.0 | 3586.2 | 3265.1 | 3685.7 |
| 60°   | 3399.8 | 3451.6 | 3557.2 | 3372.9 | 3424.6 | 3762.3 | 3965.4 | 4081.4 | 3853.5 | 3555.2 | 3890.8 |
| 62.5° | 3236.1 | 3312.8 | 3422.6 | 3522.0 | 3555.2 | 3781.0 | 3861.8 | 4017.2 | 3996.5 | 3847.3 | 3984.0 |
| 65°   | 3028.9 | 3107.7 | 3213.3 | 3542.7 | 3526.2 | 3503.4 | 3551.0 | 3644.3 | 3789.3 | 3988.2 | 3938.4 |
| 67.5° | 2656.0 | 2770.0 | 2902.6 | 3300.3 | 3066.2 | 2935.7 | 2948.1 | 2896.3 | 3188.5 | 3785.1 | 3706.4 |
| 70°   | 2162.9 | 2279.0 | 2421.9 | 2799.0 | 2363.9 | 2191.9 | 2235.4 | 2202.3 | 2432.3 | 3248.5 | 3176.0 |
| 72.5° | 1522.8 | 1647.1 | 1823.2 | 2332.8 | 1647.1 | 1369.4 | 1473.0 | 1560.0 | 1833.5 | 2606.3 | 2332.8 |
| 75°   | 1009.0 | 1098.0 | 1224.4 | 1756.9 | 1174.7 | 919.9  | 942.7  | 977.9  | 1226.5 | 1970.3 | 1473.0 |
| 77.5° | 522.1  | 611.2  | 667.1  | 940.6  | 727.2  | 725.1  | 708.5  | 754.1  | 766.6  | 1183.0 | 768.6  |
| 80°   | 292.1  | 321.1  | 350.1  | 457.9  | 364.6  | 430.9  | 445.4  | 544.9  | 505.5  | 592.5  | 321.1  |
| 82.5° | 143.0  | 180.2  | 196.8  | 281.8  | 234.1  | 172.0  | 84.9   | 178.2  | 300.4  | 321.1  | 149.2  |
| 85°   | 2.1    | 4.1    | 10.4   | 22.8   | 6.2    | 6.2    | 0.0    | 6.2    | 31.1   | 39.4   | 51.8   |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P437786  
 CATALOG NUMBER: ISC-SA1F-722-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1448.2 | 1448.2 | 1448.2 | 1448.2 | 1448.2 | 1448.2 | 1448.2 | 1448.2 | 1448.2 | 1448.2 | 1448.2 |
| 2.5°  | 1578.7 | 1562.1 | 1514.5 | 1473.0 | 1408.8 | 1381.9 | 1338.4 | 1328.0 | 1292.8 | 1257.6 | 1236.9 |
| 5°    | 1549.7 | 1502.0 | 1404.7 | 1309.4 | 1222.3 | 1141.5 | 1081.5 | 1031.7 | 975.8  | 953.0  | 967.5  |
| 7.5°  | 1433.7 | 1367.4 | 1226.5 | 1114.6 | 990.3  | 897.1  | 812.1  | 768.6  | 716.8  | 696.1  | 681.6  |
| 10°   | 1338.4 | 1257.6 | 1096.0 | 948.9  | 830.8  | 758.3  | 706.5  | 644.3  | 584.2  | 536.6  | 530.4  |
| 12.5° | 1278.3 | 1191.3 | 1011.0 | 855.6  | 768.6  | 698.2  | 638.1  | 557.3  | 488.9  | 443.4  | 422.6  |
| 15°   | 1276.2 | 1168.5 | 984.1  | 820.4  | 718.9  | 629.8  | 553.2  | 462.0  | 391.6  | 333.6  | 312.8  |
| 17.5° | 1350.8 | 1220.3 | 996.5  | 783.1  | 648.5  | 532.4  | 433.0  | 337.7  | 269.3  | 230.0  | 209.2  |
| 20°   | 1481.3 | 1338.4 | 1019.3 | 745.8  | 580.1  | 433.0  | 304.6  | 230.0  | 184.4  | 165.7  | 157.5  |
| 22.5° | 1638.8 | 1468.9 | 1060.7 | 716.8  | 509.7  | 327.3  | 215.5  | 165.7  | 145.0  | 132.6  | 130.5  |
| 25°   | 1829.4 | 1634.6 | 1118.8 | 696.1  | 445.4  | 252.8  | 167.8  | 136.7  | 124.3  | 116.0  | 111.9  |
| 27.5° | 1997.2 | 1794.2 | 1205.8 | 679.5  | 383.3  | 207.2  | 143.0  | 120.2  | 107.7  | 101.5  | 99.4   |
| 30°   | 2121.5 | 1924.7 | 1305.2 | 642.3  | 333.6  | 180.2  | 134.7  | 113.9  | 99.4   | 91.2   | 89.1   |
| 32.5° | 2264.5 | 2024.1 | 1352.9 | 605.0  | 304.6  | 159.5  | 118.1  | 101.5  | 91.2   | 82.9   | 80.8   |
| 35°   | 2421.9 | 2162.9 | 1400.5 | 576.0  | 285.9  | 143.0  | 107.7  | 89.1   | 76.7   | 68.4   | 66.3   |
| 37.5° | 2604.2 | 2316.2 | 1444.0 | 551.1  | 275.5  | 132.6  | 101.5  | 82.9   | 70.4   | 62.2   | 58.0   |
| 40°   | 2807.3 | 2436.4 | 1473.0 | 534.5  | 261.0  | 126.4  | 97.4   | 78.7   | 66.3   | 55.9   | 53.9   |
| 42.5° | 2968.9 | 2575.2 | 1481.3 | 528.3  | 246.5  | 124.3  | 93.2   | 76.7   | 62.2   | 53.9   | 49.7   |
| 45°   | 3084.9 | 2697.5 | 1510.3 | 522.1  | 236.2  | 116.0  | 91.2   | 74.6   | 58.0   | 49.7   | 45.6   |
| 47.5° | 3169.8 | 2828.0 | 1537.3 | 515.9  | 225.8  | 105.7  | 97.4   | 74.6   | 55.9   | 45.6   | 41.4   |
| 50°   | 3327.3 | 2981.3 | 1589.1 | 499.3  | 211.3  | 95.3   | 97.4   | 72.5   | 53.9   | 43.5   | 39.4   |
| 52.5° | 3497.2 | 3180.2 | 1705.1 | 480.7  | 192.7  | 84.9   | 89.1   | 72.5   | 51.8   | 41.4   | 37.3   |
| 55°   | 3658.8 | 3422.6 | 1812.8 | 455.8  | 161.6  | 76.7   | 82.9   | 72.5   | 47.7   | 39.4   | 35.2   |
| 57.5° | 3776.8 | 3584.2 | 1870.8 | 424.7  | 128.5  | 68.4   | 68.4   | 68.4   | 41.4   | 33.1   | 31.1   |
| 60°   | 3832.8 | 3567.6 | 1843.9 | 385.4  | 103.6  | 60.1   | 55.9   | 70.4   | 37.3   | 29.0   | 26.9   |
| 62.5° | 3789.3 | 3395.6 | 1725.8 | 343.9  | 91.2   | 51.8   | 45.6   | 62.2   | 33.1   | 24.9   | 22.8   |
| 65°   | 3654.6 | 3105.6 | 1529.0 | 310.8  | 89.1   | 43.5   | 37.3   | 37.3   | 26.9   | 20.7   | 18.6   |
| 67.5° | 3321.1 | 2724.4 | 1294.9 | 279.7  | 91.2   | 37.3   | 31.1   | 29.0   | 22.8   | 16.6   | 14.5   |
| 70°   | 2761.7 | 2189.9 | 980.0  | 265.2  | 91.2   | 31.1   | 26.9   | 22.8   | 16.6   | 14.5   | 12.4   |
| 72.5° | 1754.8 | 1359.1 | 679.5  | 234.1  | 91.2   | 24.9   | 22.8   | 20.7   | 12.4   | 10.4   | 6.2    |
| 75°   | 1040.0 | 826.6  | 319.1  | 180.2  | 76.7   | 20.7   | 16.6   | 12.4   | 6.2    | 4.1    | 4.1    |
| 77.5° | 611.2  | 530.4  | 138.8  | 99.4   | 33.1   | 12.4   | 8.3    | 4.1    | 2.1    | 0.0    | 0.0    |
| 80°   | 250.7  | 217.5  | 51.8   | 29.0   | 14.5   | 6.2    | 2.1    | 0.0    | 0.0    | 0.0    | 0.0    |
| 82.5° | 147.1  | 153.3  | 18.6   | 12.4   | 4.1    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 85°   | 45.6   | 70.4   | 0.0    | 2.1    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |





REPORT NUMBER: P437786  
 CATALOG NUMBER: ISC-SA1F-722-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 185°   | 195°   | 205°   | 215°   | 225°   | 235°   | 245°   | 255°   | 265°   | 270°   | 275°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1448.2 | 1448.2 | 1448.2 | 1448.2 | 1448.2 | 1448.2 | 1448.2 | 1448.2 | 1448.2 | 1448.2 | 1448.2 |
| 2.5°  | 1234.8 | 1214.1 | 1205.8 | 1193.3 | 1183.0 | 1170.6 | 1187.1 | 1201.6 | 1185.1 | 1203.7 | 1232.7 |
| 5°    | 953.0  | 921.9  | 963.4  | 936.4  | 950.9  | 934.4  | 911.6  | 915.7  | 919.9  | 911.6  | 934.4  |
| 7.5°  | 660.9  | 675.4  | 685.8  | 683.7  | 696.1  | 673.3  | 673.3  | 658.8  | 638.1  | 646.4  | 642.3  |
| 10°   | 501.4  | 472.4  | 482.7  | 480.7  | 503.4  | 472.4  | 451.6  | 428.9  | 426.8  | 430.9  | 426.8  |
| 12.5° | 399.9  | 364.6  | 341.8  | 329.4  | 327.3  | 312.8  | 294.2  | 271.4  | 256.9  | 254.8  | 267.3  |
| 15°   | 300.4  | 273.5  | 252.8  | 234.1  | 232.0  | 203.0  | 178.2  | 161.6  | 147.1  | 149.2  | 157.5  |
| 17.5° | 207.2  | 198.9  | 192.7  | 176.1  | 165.7  | 140.9  | 120.2  | 109.8  | 105.7  | 105.7  | 107.7  |
| 20°   | 151.2  | 147.1  | 143.0  | 136.7  | 126.4  | 107.7  | 95.3   | 91.2   | 89.1   | 89.1   | 91.2   |
| 22.5° | 126.4  | 120.2  | 116.0  | 113.9  | 105.7  | 91.2   | 82.9   | 78.7   | 78.7   | 78.7   | 78.7   |
| 25°   | 107.7  | 103.6  | 101.5  | 97.4   | 91.2   | 78.7   | 72.5   | 70.4   | 68.4   | 68.4   | 70.4   |
| 27.5° | 97.4   | 89.1   | 84.9   | 84.9   | 78.7   | 70.4   | 64.2   | 62.2   | 60.1   | 60.1   | 62.2   |
| 30°   | 87.0   | 80.8   | 76.7   | 72.5   | 68.4   | 60.1   | 55.9   | 53.9   | 53.9   | 53.9   | 53.9   |
| 32.5° | 76.7   | 72.5   | 68.4   | 64.2   | 58.0   | 53.9   | 49.7   | 47.7   | 45.6   | 45.6   | 45.6   |
| 35°   | 62.2   | 58.0   | 58.0   | 55.9   | 49.7   | 45.6   | 41.4   | 39.4   | 37.3   | 39.4   | 39.4   |
| 37.5° | 53.9   | 47.7   | 47.7   | 47.7   | 43.5   | 39.4   | 35.2   | 33.1   | 31.1   | 31.1   | 33.1   |
| 40°   | 49.7   | 41.4   | 39.4   | 39.4   | 39.4   | 33.1   | 29.0   | 26.9   | 24.9   | 24.9   | 26.9   |
| 42.5° | 43.5   | 37.3   | 33.1   | 31.1   | 33.1   | 29.0   | 22.8   | 20.7   | 20.7   | 20.7   | 20.7   |
| 45°   | 41.4   | 33.1   | 29.0   | 24.9   | 26.9   | 24.9   | 18.6   | 16.6   | 16.6   | 16.6   | 16.6   |
| 47.5° | 37.3   | 29.0   | 24.9   | 18.6   | 18.6   | 18.6   | 14.5   | 12.4   | 12.4   | 12.4   | 12.4   |
| 50°   | 35.2   | 26.9   | 18.6   | 16.6   | 14.5   | 14.5   | 12.4   | 10.4   | 8.3    | 8.3    | 10.4   |
| 52.5° | 33.1   | 24.9   | 16.6   | 12.4   | 10.4   | 10.4   | 8.3    | 8.3    | 6.2    | 6.2    | 6.2    |
| 55°   | 31.1   | 20.7   | 14.5   | 10.4   | 8.3    | 6.2    | 6.2    | 6.2    | 6.2    | 4.1    | 6.2    |
| 57.5° | 26.9   | 18.6   | 10.4   | 8.3    | 4.1    | 4.1    | 4.1    | 4.1    | 4.1    | 4.1    | 4.1    |
| 60°   | 24.9   | 14.5   | 8.3    | 4.1    | 2.1    | 2.1    | 2.1    | 2.1    | 2.1    | 2.1    | 2.1    |
| 62.5° | 20.7   | 12.4   | 6.2    | 4.1    | 2.1    | 0.0    | 2.1    | 2.1    | 2.1    | 2.1    | 2.1    |
| 65°   | 16.6   | 10.4   | 4.1    | 2.1    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 67.5° | 12.4   | 8.3    | 2.1    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 70°   | 10.4   | 4.1    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 72.5° | 6.2    | 2.1    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 75°   | 2.1    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 77.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 80°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 82.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 85°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P437786  
 CATALOG NUMBER: ISC-SA1F-722-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 285°   | 295°   | 305°   | 315°   | 325°   | 335°   | 345°   | 355°   | 359°   | 360°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1448.2 | 1448.2 | 1448.2 | 1448.2 | 1448.2 | 1448.2 | 1448.2 | 1448.2 | 1448.2 | 1448.2 |
| 2.5°  | 1230.6 | 1243.1 | 1288.6 | 1330.1 | 1375.7 | 1425.4 | 1466.8 | 1526.9 | 1545.5 | 1555.9 |
| 5°    | 930.2  | 975.8  | 1031.7 | 1081.5 | 1170.6 | 1253.4 | 1350.8 | 1456.5 | 1500.0 | 1508.3 |
| 7.5°  | 671.3  | 702.3  | 762.4  | 861.9  | 942.7  | 1067.0 | 1193.3 | 1334.2 | 1400.5 | 1400.5 |
| 10°   | 462.0  | 513.8  | 590.5  | 683.7  | 791.4  | 901.2  | 1048.3 | 1207.8 | 1270.0 | 1284.5 |
| 12.5° | 294.2  | 352.2  | 455.8  | 557.3  | 681.6  | 789.3  | 936.4  | 1116.7 | 1187.1 | 1207.8 |
| 15°   | 169.9  | 209.2  | 304.6  | 416.4  | 565.6  | 702.3  | 868.1  | 1087.7 | 1174.7 | 1195.4 |
| 17.5° | 113.9  | 128.5  | 180.2  | 277.6  | 443.4  | 625.7  | 847.4  | 1118.8 | 1224.4 | 1249.3 |
| 20°   | 95.3   | 101.5  | 120.2  | 172.0  | 312.8  | 544.9  | 839.1  | 1187.1 | 1315.6 | 1359.1 |
| 22.5° | 82.9   | 89.1   | 101.5  | 126.4  | 223.8  | 459.9  | 832.9  | 1286.6 | 1460.6 | 1506.2 |
| 25°   | 72.5   | 78.7   | 89.1   | 107.7  | 157.5  | 375.0  | 843.2  | 1427.5 | 1647.1 | 1700.9 |
| 27.5° | 64.2   | 70.4   | 80.8   | 93.2   | 126.4  | 290.0  | 845.3  | 1560.0 | 1821.1 | 1877.0 |
| 30°   | 55.9   | 62.2   | 70.4   | 80.8   | 101.5  | 223.8  | 808.0  | 1694.7 | 1962.0 | 2026.2 |
| 32.5° | 49.7   | 53.9   | 62.2   | 70.4   | 84.9   | 174.0  | 731.3  | 1798.3 | 2078.0 | 2140.1 |
| 35°   | 41.4   | 45.6   | 53.9   | 60.1   | 74.6   | 140.9  | 646.4  | 1893.6 | 2216.8 | 2293.5 |
| 37.5° | 35.2   | 39.4   | 45.6   | 53.9   | 66.3   | 109.8  | 561.5  | 1976.5 | 2351.5 | 2426.1 |
| 40°   | 29.0   | 35.2   | 41.4   | 47.7   | 60.1   | 84.9   | 468.2  | 2065.6 | 2504.8 | 2583.5 |
| 42.5° | 24.9   | 29.0   | 35.2   | 43.5   | 51.8   | 68.4   | 385.4  | 2121.5 | 2635.3 | 2728.5 |
| 45°   | 18.6   | 24.9   | 33.1   | 43.5   | 43.5   | 53.9   | 331.5  | 2162.9 | 2728.5 | 2844.5 |
| 47.5° | 14.5   | 20.7   | 29.0   | 41.4   | 39.4   | 45.6   | 304.6  | 2235.4 | 2857.0 | 2964.7 |
| 50°   | 12.4   | 16.6   | 29.0   | 35.2   | 33.1   | 39.4   | 312.8  | 2299.7 | 2954.4 | 3047.6 |
| 52.5° | 10.4   | 14.5   | 24.9   | 26.9   | 29.0   | 35.2   | 329.4  | 2417.8 | 3076.6 | 3149.1 |
| 55°   | 8.3    | 12.4   | 18.6   | 22.8   | 24.9   | 33.1   | 356.3  | 2564.9 | 3236.1 | 3329.3 |
| 57.5° | 6.2    | 10.4   | 14.5   | 18.6   | 22.8   | 31.1   | 375.0  | 2658.1 | 3385.3 | 3457.8 |
| 60°   | 6.2    | 8.3    | 12.4   | 16.6   | 20.7   | 29.0   | 348.1  | 2548.3 | 3321.1 | 3399.8 |
| 62.5° | 4.1    | 8.3    | 10.4   | 14.5   | 16.6   | 22.8   | 256.9  | 2308.0 | 3128.4 | 3236.1 |
| 65°   | 2.1    | 6.2    | 8.3    | 10.4   | 12.4   | 16.6   | 147.1  | 2017.9 | 2900.5 | 3028.9 |
| 67.5° | 0.0    | 4.1    | 6.2    | 8.3    | 8.3    | 12.4   | 68.4   | 1628.4 | 2525.5 | 2656.0 |
| 70°   | 0.0    | 2.1    | 4.1    | 4.1    | 6.2    | 10.4   | 35.2   | 1149.8 | 1986.8 | 2162.9 |
| 72.5° | 2.1    | 2.1    | 4.1    | 4.1    | 4.1    | 8.3    | 22.8   | 696.1  | 1336.3 | 1522.8 |
| 75°   | 2.1    | 2.1    | 2.1    | 2.1    | 4.1    | 6.2    | 14.5   | 447.5  | 841.1  | 1009.0 |
| 77.5° | 2.1    | 4.1    | 2.1    | 2.1    | 2.1    | 4.1    | 8.3    | 248.6  | 459.9  | 522.1  |
| 80°   | 2.1    | 2.1    | 2.1    | 2.1    | 2.1    | 4.1    | 4.1    | 22.8   | 217.5  | 292.1  |
| 82.5° | 0.0    | 0.0    | 0.0    | 0.0    | 2.1    | 2.1    | 2.1    | 2.1    | 111.9  | 143.0  |
| 85°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 2.1    | 0.0    | 0.0    | 2.1    | 2.1    |
| 87.5° | 0.0    | 0.0    | 0.0    | 2.1    | 2.1    | 2.1    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



**Test Information**


Test Method: LM-79-2008 Report  
 Number: SP1-1908-441-10-R4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/28/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGRAW-EDISON  
 Catalog Number: **SA1C-722-U-5WQ**  
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

\*\*\*THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.\*\*\*TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

**Spectral Parameters**

CCT (K): 2237  
 CIE u': 0.2876  
 CIE v': 0.5346  
 Duv: -0.0006  
 CIE x: 0.5005  
 CIE y: 0.4134  
 CIE z: 0.0860  
 Peak Wavelength (nm): 603  
 Dominant Wavelength (nm): 587  
 Purity: 74.5  
 Rf: 69.8  
 Rg: 99.2

|           |      |      |       |
|-----------|------|------|-------|
| CRI (Ra): | 72.0 |      |       |
| R1:       | 68.9 | R9:  | -17.4 |
| R2:       | 83.0 | R10: | 61.3  |
| R3:       | 95.2 | R11: | 59.8  |
| R4:       | 66.2 | R12: | 50.5  |
| R5:       | 65.9 | R13: | 71.1  |
| R6:       | 76.3 | R14: | 96.9  |
| R7:       | 76.7 |      |       |
| R8:       | 43.8 |      |       |



**Test Conditions**

Stabilization Time: 71M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 24.7/41%  
 Sphere Temperature (°C): 25.6

REPORT NUMBER: SP1-1908-441-10-R4

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/28/2019        | 12/28/2019           |
| Power Meter                    | IN0071                | 12/5/2018        | 12/5/2019            |
| AC Power Source                | IN0063                | 12/5/2018        | 12/5/2019            |
| DC Power Source                | IN0208                | 12/5/2018        | 12/5/2019            |
| Sphere Thermometer             | IN0085                | 12/5/2018        | 12/5/2019            |
| Room Thermometer               | IN0046                | 12/5/2018        | 12/5/2019            |

REPORT NUMBER: SP1-1908-441-10-R4

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2200K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-10-R4

**Photopic Flux vs. Wavelength**



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 1768          | NR            | 490    | 5206          | NR            | 620    | 130919        | NR            | 750    | 8553          | NR            | 880    | 2713          | NR            |
| 365    | 1569          | NR            | 495    | 7286          | NR            | 625    | 125335        | NR            | 755    | 7696          | NR            | 885    | 2316          | NR            |
| 370    | 1594          | NR            | 500    | 10654         | NR            | 630    | 118388        | NR            | 760    | 6978          | NR            | 890    | 2539          | NR            |
| 375    | 1744          | NR            | 505    | 15189         | NR            | 635    | 111855        | NR            | 765    | 6377          | NR            | 895    | 1933          | NR            |
| 380    | 1659          | NR            | 510    | 20541         | NR            | 640    | 104062        | NR            | 770    | 5600          | NR            | 900    | 2216          | NR            |
| 385    | 1504          | NR            | 515    | 26492         | NR            | 645    | 96365         | NR            | 775    | 5000          | NR            | 905    | 2067          | NR            |
| 390    | 1541          | NR            | 520    | 32294         | NR            | 650    | 88651         | NR            | 780    | 4709          | NR            | 910    | 1959          | NR            |
| 395    | 1355          | NR            | 525    | 38123         | NR            | 655    | 81152         | NR            | 785    | 4305          | NR            | 915    | 1874          | NR            |
| 400    | 1243          | NR            | 530    | 43232         | NR            | 660    | 73523         | NR            | 790    | 4040          | NR            | 920    | 1484          | NR            |
| 405    | 1417          | NR            | 535    | 48012         | NR            | 665    | 66123         | NR            | 795    | 3642          | NR            | 925    | 1914          | NR            |
| 410    | 2147          | NR            | 540    | 52623         | NR            | 670    | 58677         | NR            | 800    | 3594          | NR            | 930    | 1948          | NR            |
| 415    | 3837          | NR            | 545    | 57516         | NR            | 675    | 52349         | NR            | 805    | 3190          | NR            | 935    | 2079          | NR            |
| 420    | 7159          | NR            | 550    | 62613         | NR            | 680    | 46159         | NR            | 810    | 3241          | NR            | 940    | 2263          | NR            |
| 425    | 12599         | NR            | 555    | 68554         | NR            | 685    | 40525         | NR            | 815    | 2732          | NR            | 945    | 1688          | NR            |
| 430    | 19019         | NR            | 560    | 75325         | NR            | 690    | 35615         | NR            | 820    | 2612          | NR            | 950    | 1560          | NR            |
| 435    | 24875         | NR            | 565    | 82533         | NR            | 695    | 31158         | NR            | 825    | 2966          | NR            | 955    | 2826          | NR            |
| 440    | 29103         | NR            | 570    | 90909         | NR            | 700    | 27409         | NR            | 830    | 2574          | NR            | 960    | 1477          | NR            |
| 445    | 29901         | NR            | 575    | 99621         | NR            | 705    | 24204         | NR            | 835    | 2633          | NR            | 965    | 1568          | NR            |
| 450    | 24862         | NR            | 580    | 108484        | NR            | 710    | 21558         | NR            | 840    | 2526          | NR            | 970    | 2030          | NR            |
| 455    | 15942         | NR            | 585    | 116679        | NR            | 715    | 19222         | NR            | 845    | 2631          | NR            | 975    | 1986          | NR            |
| 460    | 9916          | NR            | 590    | 123752        | NR            | 720    | 17310         | NR            | 850    | 2079          | NR            | 980    | 2540          | NR            |
| 465    | 7051          | NR            | 595    | 129324        | NR            | 725    | 15280         | NR            | 855    | 2309          | NR            | 985    | 1139          | NR            |
| 470    | 5227          | NR            | 600    | 134082        | NR            | 730    | 13282         | NR            | 860    | 2528          | NR            | 990    | 2018          | NR            |
| 475    | 4257          | NR            | 605    | 135698        | NR            | 735    | 11753         | NR            | 865    | 2121          | NR            | 995    | 3445          | NR            |
| 480    | 4052          | NR            | 610    | 135144        | NR            | 740    | 10654         | NR            | 870    | 2751          | NR            | 1000   | 3704          | NR            |
| 485    | 4298          | NR            | 615    | 134180        | NR            | 745    | 9451          | NR            | 875    | 2317          | NR            |        |               |               |

REPORT NUMBER: SP1-1908-441-10-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 4696.9

S/P: 0.85

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 1768          | NR            | 490    | 5206          | NR            | 620    | 130919        | NR            | 750    | 8553          | NR            | 880    | 2713          | NR            |
| 365    | 1569          | NR            | 495    | 7286          | NR            | 625    | 125335        | NR            | 755    | 7696          | NR            | 885    | 2316          | NR            |
| 370    | 1594          | NR            | 500    | 10654         | NR            | 630    | 118388        | NR            | 760    | 6978          | NR            | 890    | 2539          | NR            |
| 375    | 1744          | NR            | 505    | 15189         | NR            | 635    | 111855        | NR            | 765    | 6377          | NR            | 895    | 1933          | NR            |
| 380    | 1659          | NR            | 510    | 20541         | NR            | 640    | 104062        | NR            | 770    | 5600          | NR            | 900    | 2216          | NR            |
| 385    | 1504          | NR            | 515    | 26492         | NR            | 645    | 96365         | NR            | 775    | 5000          | NR            | 905    | 2067          | NR            |
| 390    | 1541          | NR            | 520    | 32294         | NR            | 650    | 88651         | NR            | 780    | 4709          | NR            | 910    | 1959          | NR            |
| 395    | 1355          | NR            | 525    | 38123         | NR            | 655    | 81152         | NR            | 785    | 4305          | NR            | 915    | 1874          | NR            |
| 400    | 1243          | NR            | 530    | 43232         | NR            | 660    | 73523         | NR            | 790    | 4040          | NR            | 920    | 1484          | NR            |
| 405    | 1417          | NR            | 535    | 48012         | NR            | 665    | 66123         | NR            | 795    | 3642          | NR            | 925    | 1914          | NR            |
| 410    | 2147          | NR            | 540    | 52623         | NR            | 670    | 58677         | NR            | 800    | 3594          | NR            | 930    | 1948          | NR            |
| 415    | 3837          | NR            | 545    | 57516         | NR            | 675    | 52349         | NR            | 805    | 3190          | NR            | 935    | 2079          | NR            |
| 420    | 7159          | NR            | 550    | 62613         | NR            | 680    | 46159         | NR            | 810    | 3241          | NR            | 940    | 2263          | NR            |
| 425    | 12599         | NR            | 555    | 68554         | NR            | 685    | 40525         | NR            | 815    | 2732          | NR            | 945    | 1688          | NR            |
| 430    | 19019         | NR            | 560    | 75325         | NR            | 690    | 35615         | NR            | 820    | 2612          | NR            | 950    | 1560          | NR            |
| 435    | 24875         | NR            | 565    | 82533         | NR            | 695    | 31158         | NR            | 825    | 2966          | NR            | 955    | 2826          | NR            |
| 440    | 29103         | NR            | 570    | 90909         | NR            | 700    | 27409         | NR            | 830    | 2574          | NR            | 960    | 1477          | NR            |
| 445    | 29901         | NR            | 575    | 99621         | NR            | 705    | 24204         | NR            | 835    | 2633          | NR            | 965    | 1568          | NR            |
| 450    | 24862         | NR            | 580    | 108484        | NR            | 710    | 21558         | NR            | 840    | 2526          | NR            | 970    | 2030          | NR            |
| 455    | 15942         | NR            | 585    | 116679        | NR            | 715    | 19222         | NR            | 845    | 2631          | NR            | 975    | 1986          | NR            |
| 460    | 9916          | NR            | 590    | 123752        | NR            | 720    | 17310         | NR            | 850    | 2079          | NR            | 980    | 2540          | NR            |
| 465    | 7051          | NR            | 595    | 129324        | NR            | 725    | 15280         | NR            | 855    | 2309          | NR            | 985    | 1139          | NR            |
| 470    | 5227          | NR            | 600    | 134082        | NR            | 730    | 13282         | NR            | 860    | 2528          | NR            | 990    | 2018          | NR            |
| 475    | 4257          | NR            | 605    | 135698        | NR            | 735    | 11753         | NR            | 865    | 2121          | NR            | 995    | 3445          | NR            |
| 480    | 4052          | NR            | 610    | 135144        | NR            | 740    | 10654         | NR            | 870    | 2751          | NR            | 1000   | 3704          | NR            |
| 485    | 4298          | NR            | 615    | 134180        | NR            | 745    | 9451          | NR            | 875    | 2317          | NR            |        |               |               |



REPORT NUMBER: SP1-1908-441-10-R4

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 1470.8 M/P: 0.27**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 1768          | NR            | 490    | 5206          | NR            | 620    | 130919        | NR            | 750    | 8553          | NR            | 880    | 2713          | NR            |
| 365    | 1569          | NR            | 495    | 7286          | NR            | 625    | 125335        | NR            | 755    | 7696          | NR            | 885    | 2316          | NR            |
| 370    | 1594          | NR            | 500    | 10654         | NR            | 630    | 118388        | NR            | 760    | 6978          | NR            | 890    | 2539          | NR            |
| 375    | 1744          | NR            | 505    | 15189         | NR            | 635    | 111855        | NR            | 765    | 6377          | NR            | 895    | 1933          | NR            |
| 380    | 1659          | NR            | 510    | 20541         | NR            | 640    | 104062        | NR            | 770    | 5600          | NR            | 900    | 2216          | NR            |
| 385    | 1504          | NR            | 515    | 26492         | NR            | 645    | 96365         | NR            | 775    | 5000          | NR            | 905    | 2067          | NR            |
| 390    | 1541          | NR            | 520    | 32294         | NR            | 650    | 88651         | NR            | 780    | 4709          | NR            | 910    | 1959          | NR            |
| 395    | 1355          | NR            | 525    | 38123         | NR            | 655    | 81152         | NR            | 785    | 4305          | NR            | 915    | 1874          | NR            |
| 400    | 1243          | NR            | 530    | 43232         | NR            | 660    | 73523         | NR            | 790    | 4040          | NR            | 920    | 1484          | NR            |
| 405    | 1417          | NR            | 535    | 48012         | NR            | 665    | 66123         | NR            | 795    | 3642          | NR            | 925    | 1914          | NR            |
| 410    | 2147          | NR            | 540    | 52623         | NR            | 670    | 58677         | NR            | 800    | 3594          | NR            | 930    | 1948          | NR            |
| 415    | 3837          | NR            | 545    | 57516         | NR            | 675    | 52349         | NR            | 805    | 3190          | NR            | 935    | 2079          | NR            |
| 420    | 7159          | NR            | 550    | 62613         | NR            | 680    | 46159         | NR            | 810    | 3241          | NR            | 940    | 2263          | NR            |
| 425    | 12599         | NR            | 555    | 68554         | NR            | 685    | 40525         | NR            | 815    | 2732          | NR            | 945    | 1688          | NR            |
| 430    | 19019         | NR            | 560    | 75325         | NR            | 690    | 35615         | NR            | 820    | 2612          | NR            | 950    | 1560          | NR            |
| 435    | 24875         | NR            | 565    | 82533         | NR            | 695    | 31158         | NR            | 825    | 2966          | NR            | 955    | 2826          | NR            |
| 440    | 29103         | NR            | 570    | 90909         | NR            | 700    | 27409         | NR            | 830    | 2574          | NR            | 960    | 1477          | NR            |
| 445    | 29901         | NR            | 575    | 99621         | NR            | 705    | 24204         | NR            | 835    | 2633          | NR            | 965    | 1568          | NR            |
| 450    | 24862         | NR            | 580    | 108484        | NR            | 710    | 21558         | NR            | 840    | 2526          | NR            | 970    | 2030          | NR            |
| 455    | 15942         | NR            | 585    | 116679        | NR            | 715    | 19222         | NR            | 845    | 2631          | NR            | 975    | 1986          | NR            |
| 460    | 9916          | NR            | 590    | 123752        | NR            | 720    | 17310         | NR            | 850    | 2079          | NR            | 980    | 2540          | NR            |
| 465    | 7051          | NR            | 595    | 129324        | NR            | 725    | 15280         | NR            | 855    | 2309          | NR            | 985    | 1139          | NR            |
| 470    | 5227          | NR            | 600    | 134082        | NR            | 730    | 13282         | NR            | 860    | 2528          | NR            | 990    | 2018          | NR            |
| 475    | 4257          | NR            | 605    | 135698        | NR            | 735    | 11753         | NR            | 865    | 2121          | NR            | 995    | 3445          | NR            |
| 480    | 4052          | NR            | 610    | 135144        | NR            | 740    | 10654         | NR            | 870    | 2751          | NR            | 1000   | 3704          | NR            |
| 485    | 4298          | NR            | 615    | 134180        | NR            | 745    | 9451          | NR            | 875    | 2317          | NR            |        |               |               |

REPORT NUMBER: SP1-1908-441-10-R4



TM-30-18

**Summary**

$R_f = 69.8$   
 $R_g = 99.2$   
 CIE  $R_a = 72.0$   
 $R_9 = -17.4$



**Color Vector Graphics**




REPORT NUMBER: SP1-1908-441-10-R4

TM-30-18

**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 87 | CES26 = 56 | CES51 = 74 | CES76 = 56 |
| CES02 = 65 | CES27 = 76 | CES52 = 76 | CES77 = 81 |
| CES03 = 32 | CES28 = 83 | CES53 = 65 | CES78 = 63 |
| CES04 = 72 | CES29 = 46 | CES54 = 78 | CES79 = 84 |
| CES05 = 52 | CES30 = 48 | CES55 = 75 | CES80 = 84 |
| CES06 = 52 | CES31 = 51 | CES56 = 65 | CES81 = 63 |
| CES07 = 44 | CES32 = 51 | CES57 = 62 | CES82 = 92 |
| CES08 = 42 | CES33 = 53 | CES58 = 66 | CES83 = 83 |
| CES09 = 29 | CES34 = 70 | CES59 = 84 | CES84 = 92 |
| CES10 = 78 | CES35 = 85 | CES60 = 90 | CES85 = 81 |
| CES11 = 61 | CES36 = 78 | CES61 = 84 | CES86 = 56 |
| CES12 = 68 | CES37 = 80 | CES62 = 70 | CES87 = 78 |
| CES13 = 45 | CES38 = 53 | CES63 = 68 | CES88 = 72 |
| CES14 = 75 | CES39 = 90 | CES64 = 69 | CES89 = 62 |
| CES15 = 72 | CES40 = 84 | CES65 = 67 | CES90 = 67 |
| CES16 = 49 | CES41 = 75 | CES66 = 64 | CES91 = 90 |
| CES17 = 51 | CES42 = 79 | CES67 = 63 | CES92 = 67 |
| CES18 = 57 | CES43 = 64 | CES68 = 69 | CES93 = 79 |
| CES19 = 74 | CES44 = 98 | CES69 = 80 | CES94 = 52 |
| CES20 = 68 | CES45 = 73 | CES70 = 63 | CES95 = 76 |
| CES21 = 89 | CES46 = 67 | CES71 = 63 | CES96 = 78 |
| CES22 = 81 | CES47 = 60 | CES72 = 87 | CES97 = 77 |
| CES23 = 92 | CES48 = 48 | CES73 = 56 | CES98 = 71 |
| CES24 = 92 | CES49 = 64 | CES74 = 87 | CES99 = 65 |
| CES25 = 74 | CES50 = 74 | CES75 = 66 |            |



REPORT NUMBER: SP1-1908-441-10-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-10-R4

TM-30-18

Measure Comparisons



(END OF REPORT)