

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P437795

Luminaire Tested: **ISC-SA1F-722-U-T4FT**

Issue Date: 12/9/2020

Test Information

Test Method: LM-79-08
Report Number: P437795
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-074-10)
Test Lab: INNOVATION CENTER
Issue Date: 12/9/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: ISC-SA1F-722-U-T4FT
Description: IMPACT ELITE LED CYLINDER LUMINAIRE
(1) 70 CRI, 2200K, 1200mA LIGHTSQUARE WITH 16 LEDS AND TYPE IV FORWARD
THROW OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5698 lumens
Efficiency: N/A
Efficacy: 86.3 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 66
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P437795
 CATALOG NUMBER: ISC-SA1F-722-U-T4FT

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1.5 fc
 Type IV - Short - N/A

REPORT NUMBER: P437795
CATALOG NUMBER: ISC-SA1F-722-U-T4FT

Luminous Intensity Polar Plot



— Vertical Plane Through 32-Deg Lateral - - - Horizontal Cone Through 75-Deg Vertical

REPORT NUMBER: P437795

CATALOG NUMBER: ISC-SA1F-722-U-T4FT


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 1248.5 | 0.0 | 1248.5 |
| | % Fixture | 21.9 | 0.0 | 21.9 |
| Street Side | Lumens | 4449.5 | 0.0 | 4449.5 |
| | % Fixture | 78.1 | 0.0 | 78.1 |
| Total | Lumens | 5698.0 | 0.0 | 5698.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 82.3 | 1.4 |
| 10°-20° | 225.1 | 4.0 |
| 20°-30° | 372.6 | 6.5 |
| 30°-40° | 555.4 | 9.7 |
| 40°-50° | 790.7 | 13.9 |
| 50°-60° | 1087.9 | 19.1 |
| 60°-70° | 1371.0 | 24.1 |
| 70°-80° | 1108.3 | 19.5 |
| 80°-90° | 104.7 | 1.8 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 5698.0 | 100.0 |
| 0°-180° | 5698.0 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P437795


CATALOG NUMBER: ISC-SA1F-722-U-T4FT

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 342.6 | 6.0 | | | |
| FM (30°-60°) | 1817.3 | 31.9 | | | |
| FH (60°-80°) | 2211.9 | 38.8 | | | G2/5000 |
| FVH (80°-90°) | 77.8 | 1.4 | | | G1/100 |
| BL (0°-30°) | 337.5 | 5.9 | B1/500 | | |
| BM (30°-60°) | 616.7 | 10.8 | B1/1000 | | |
| BH (60°-80°) | 267.4 | 4.7 | B1/500 | | G1/500 |
| BVH (80°-90°) | 26.9 | 0.5 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P437795
 CATALOG NUMBER: ISC-SA1F-722-U-T4FT

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 32° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 907.1 | 907.1 | 907.1 | 907.1 | 907.1 | 907.1 | 907.1 | 907.1 | 907.1 | 907.1 | 907.1 |
| 2.5° | 828.4 | 834.6 | 836.7 | 840.8 | 849.1 | 844.9 | 855.3 | 867.7 | 884.3 | 892.6 | 909.1 |
| 5° | 758.0 | 758.0 | 764.2 | 774.5 | 789.0 | 789.0 | 807.7 | 830.4 | 859.4 | 882.2 | 911.2 |
| 7.5° | 695.8 | 695.8 | 702.0 | 714.5 | 729.0 | 739.3 | 762.1 | 797.3 | 836.7 | 880.1 | 917.4 |
| 10° | 644.1 | 646.1 | 650.3 | 662.7 | 681.3 | 691.7 | 724.8 | 764.2 | 815.9 | 871.9 | 923.6 |
| 12.5° | 625.4 | 623.3 | 621.3 | 631.6 | 646.1 | 654.4 | 691.7 | 741.4 | 801.4 | 869.8 | 936.1 |
| 15° | 639.9 | 635.8 | 629.6 | 629.6 | 635.8 | 639.9 | 671.0 | 722.8 | 789.0 | 867.7 | 950.6 |
| 17.5° | 677.2 | 673.0 | 658.6 | 644.1 | 648.2 | 650.3 | 671.0 | 712.4 | 782.8 | 876.0 | 971.3 |
| 20° | 729.0 | 722.8 | 697.9 | 679.3 | 675.1 | 675.1 | 687.5 | 718.6 | 787.0 | 892.6 | 998.2 |
| 22.5° | 791.1 | 784.9 | 755.9 | 722.8 | 718.6 | 716.5 | 722.8 | 743.5 | 799.4 | 911.2 | 1039.6 |
| 25° | 873.9 | 867.7 | 832.5 | 791.1 | 776.6 | 774.5 | 768.3 | 780.7 | 820.1 | 936.1 | 1068.6 |
| 27.5° | 963.0 | 965.0 | 923.6 | 867.7 | 853.2 | 847.0 | 830.4 | 828.4 | 844.9 | 956.8 | 1118.3 |
| 30° | 1045.8 | 1041.7 | 998.2 | 952.6 | 931.9 | 923.6 | 896.7 | 884.3 | 873.9 | 987.8 | 1176.3 |
| 32.5° | 1085.2 | 1091.4 | 1070.7 | 1027.2 | 1010.6 | 996.1 | 965.0 | 944.3 | 929.8 | 1035.5 | 1246.7 |
| 35° | 1151.4 | 1153.5 | 1145.2 | 1118.3 | 1085.2 | 1074.8 | 1045.8 | 1031.3 | 1000.3 | 1093.4 | 1331.6 |
| 37.5° | 1217.7 | 1223.9 | 1221.8 | 1205.3 | 1176.3 | 1165.9 | 1141.1 | 1134.9 | 1072.7 | 1165.9 | 1437.2 |
| 40° | 1317.1 | 1306.8 | 1292.3 | 1298.5 | 1288.1 | 1281.9 | 1271.5 | 1250.8 | 1174.2 | 1244.6 | 1540.8 |
| 42.5° | 1424.8 | 1406.2 | 1354.4 | 1371.0 | 1385.4 | 1391.7 | 1406.2 | 1383.4 | 1279.8 | 1362.7 | 1625.7 |
| 45° | 1511.8 | 1497.3 | 1428.9 | 1433.1 | 1462.1 | 1482.8 | 1551.1 | 1538.7 | 1416.5 | 1491.1 | 1739.6 |
| 47.5° | 1561.5 | 1549.0 | 1501.4 | 1522.1 | 1540.8 | 1569.8 | 1702.3 | 1691.9 | 1544.9 | 1629.8 | 1876.3 |
| 50° | 1631.9 | 1611.2 | 1565.6 | 1602.9 | 1636.0 | 1658.8 | 1849.3 | 1845.2 | 1654.7 | 1772.7 | 2031.6 |
| 52.5° | 1671.2 | 1650.5 | 1646.4 | 1698.2 | 1737.5 | 1768.6 | 2006.7 | 1994.3 | 1762.4 | 1915.6 | 2178.6 |
| 55° | 1725.1 | 1729.2 | 1756.1 | 1795.5 | 1851.4 | 1903.2 | 2160.0 | 2097.8 | 1861.8 | 2056.4 | 2323.6 |
| 57.5° | 1843.1 | 1839.0 | 1890.8 | 1909.4 | 1981.9 | 2048.1 | 2342.2 | 2207.6 | 1944.6 | 2157.9 | 2391.9 |
| 60° | 2000.5 | 2008.8 | 2027.4 | 2075.1 | 2153.8 | 2255.2 | 2518.2 | 2321.5 | 1998.4 | 2230.4 | 2379.5 |
| 62.5° | 2298.7 | 2251.1 | 2242.8 | 2255.2 | 2410.6 | 2528.6 | 2690.1 | 2423.0 | 2021.2 | 2232.5 | 2249.0 |
| 65° | 2601.1 | 2582.4 | 2518.2 | 2549.3 | 2775.0 | 2882.7 | 2911.7 | 2489.2 | 1975.7 | 2104.1 | 1959.1 |
| 67.5° | 2913.8 | 2911.7 | 2843.4 | 2932.4 | 3203.7 | 3330.0 | 3158.2 | 2476.8 | 1826.6 | 1803.8 | 1505.6 |
| 70° | 3234.8 | 3249.3 | 3249.3 | 3501.9 | 3872.6 | 3905.8 | 3433.6 | 2358.8 | 1530.4 | 1277.8 | 880.1 |
| 72.5° | 3375.6 | 3383.9 | 3458.4 | 4019.7 | 4611.9 | 4622.3 | 3591.0 | 2002.6 | 1043.7 | 681.3 | 443.2 |
| 75° | 2669.4 | 2731.5 | 2932.4 | 3870.6 | 4638.9 | 4597.4 | 3199.6 | 1281.9 | 509.4 | 339.6 | 246.4 |
| 77.5° | 1047.9 | 1070.7 | 1478.6 | 2464.4 | 3379.7 | 3421.2 | 2070.9 | 511.5 | 258.9 | 215.4 | 178.1 |
| 80° | 296.1 | 310.6 | 523.9 | 979.5 | 1669.2 | 1845.2 | 824.2 | 221.6 | 174.0 | 157.4 | 128.4 |
| 82.5° | 105.6 | 120.1 | 194.7 | 374.8 | 712.4 | 751.7 | 223.7 | 109.8 | 111.8 | 101.5 | 78.7 |
| 85° | 14.5 | 12.4 | 26.9 | 68.3 | 157.4 | 132.5 | 37.3 | 29.0 | 45.6 | 47.6 | 33.1 |
| 87.5° | 0.0 | 0.0 | 0.0 | 2.1 | 2.1 | 2.1 | 0.0 | 0.0 | 0.0 | 2.1 | 2.1 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P437795
 CATALOG NUMBER: ISC-SA1F-722-U-T4FT

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 907.1 | 907.1 | 907.1 | 907.1 | 907.1 | 907.1 | 907.1 | 907.1 | 907.1 | 907.1 | 907.1 |
| 2.5° | 913.3 | 917.4 | 925.7 | 929.8 | 934.0 | 942.3 | 940.2 | 944.3 | 944.3 | 942.3 | 946.4 |
| 5° | 921.6 | 931.9 | 942.3 | 946.4 | 948.5 | 948.5 | 938.1 | 931.9 | 929.8 | 927.8 | 929.8 |
| 7.5° | 929.8 | 944.3 | 954.7 | 952.6 | 944.3 | 929.8 | 917.4 | 907.1 | 896.7 | 892.6 | 896.7 |
| 10° | 944.3 | 958.8 | 965.0 | 950.6 | 927.8 | 905.0 | 886.4 | 871.9 | 855.3 | 853.2 | 855.3 |
| 12.5° | 956.8 | 975.4 | 975.4 | 942.3 | 911.2 | 880.1 | 851.1 | 828.4 | 807.7 | 801.4 | 801.4 |
| 15° | 977.5 | 992.0 | 977.5 | 931.9 | 888.4 | 849.1 | 807.7 | 778.7 | 753.8 | 743.5 | 745.5 |
| 17.5° | 1000.3 | 1010.6 | 973.3 | 915.3 | 863.6 | 811.8 | 758.0 | 718.6 | 700.0 | 689.6 | 691.7 |
| 20° | 1027.2 | 1029.2 | 973.3 | 894.6 | 826.3 | 758.0 | 700.0 | 671.0 | 658.6 | 652.3 | 654.4 |
| 22.5° | 1062.4 | 1054.1 | 967.1 | 867.7 | 778.7 | 704.1 | 650.3 | 642.0 | 642.0 | 642.0 | 648.2 |
| 25° | 1099.7 | 1076.9 | 956.8 | 832.5 | 716.5 | 639.9 | 619.2 | 629.6 | 637.8 | 637.8 | 642.0 |
| 27.5° | 1136.9 | 1099.7 | 936.1 | 780.7 | 644.1 | 594.4 | 602.6 | 619.2 | 627.5 | 627.5 | 631.6 |
| 30° | 1182.5 | 1126.6 | 911.2 | 710.3 | 575.7 | 563.3 | 584.0 | 604.7 | 617.1 | 617.1 | 621.3 |
| 32.5° | 1240.5 | 1149.4 | 873.9 | 637.8 | 530.2 | 536.4 | 559.1 | 581.9 | 596.4 | 600.6 | 602.6 |
| 35° | 1304.7 | 1180.4 | 822.2 | 557.1 | 499.1 | 515.7 | 534.3 | 555.0 | 567.4 | 571.6 | 571.6 |
| 37.5° | 1371.0 | 1211.5 | 753.8 | 488.7 | 472.2 | 495.0 | 513.6 | 523.9 | 532.2 | 532.2 | 532.2 |
| 40° | 1437.2 | 1228.1 | 664.8 | 434.9 | 445.2 | 478.4 | 495.0 | 490.8 | 488.7 | 482.5 | 484.6 |
| 42.5° | 1505.6 | 1240.5 | 569.5 | 395.5 | 418.3 | 459.7 | 472.2 | 461.8 | 445.2 | 434.9 | 437.0 |
| 45° | 1580.1 | 1259.1 | 490.8 | 366.6 | 391.4 | 443.2 | 455.6 | 434.9 | 414.2 | 397.6 | 393.5 |
| 47.5° | 1665.0 | 1290.2 | 420.4 | 339.6 | 374.8 | 432.8 | 445.2 | 416.3 | 389.3 | 366.6 | 362.4 |
| 50° | 1781.0 | 1337.8 | 366.6 | 321.0 | 364.5 | 426.6 | 437.0 | 399.7 | 368.6 | 339.6 | 337.6 |
| 52.5° | 1899.0 | 1373.0 | 329.3 | 304.4 | 352.1 | 414.2 | 426.6 | 387.3 | 350.0 | 318.9 | 314.8 |
| 55° | 1986.0 | 1368.9 | 296.1 | 287.9 | 335.5 | 397.6 | 416.3 | 372.8 | 325.1 | 296.1 | 292.0 |
| 57.5° | 2023.3 | 1284.0 | 269.2 | 273.4 | 316.9 | 376.9 | 399.7 | 350.0 | 306.5 | 281.6 | 279.6 |
| 60° | 1959.1 | 1147.3 | 250.6 | 256.8 | 296.1 | 350.0 | 368.6 | 333.4 | 294.1 | 271.3 | 269.2 |
| 62.5° | 1847.3 | 994.0 | 236.1 | 244.4 | 275.4 | 325.1 | 350.0 | 312.7 | 277.5 | 260.9 | 258.9 |
| 65° | 1582.2 | 826.3 | 221.6 | 229.9 | 256.8 | 300.3 | 333.4 | 300.3 | 265.1 | 248.5 | 246.4 |
| 67.5° | 1194.9 | 594.4 | 207.1 | 215.4 | 240.2 | 281.6 | 318.9 | 283.7 | 246.4 | 234.0 | 234.0 |
| 70° | 712.4 | 364.5 | 188.5 | 200.9 | 219.5 | 258.9 | 296.1 | 260.9 | 223.7 | 219.5 | 215.4 |
| 72.5° | 347.9 | 231.9 | 171.9 | 182.2 | 196.7 | 229.9 | 263.0 | 231.9 | 194.7 | 184.3 | 182.2 |
| 75° | 209.2 | 167.7 | 149.1 | 161.5 | 171.9 | 192.6 | 221.6 | 198.8 | 169.8 | 153.2 | 151.2 |
| 77.5° | 151.2 | 126.3 | 126.3 | 138.8 | 138.8 | 159.5 | 190.5 | 169.8 | 142.9 | 132.5 | 130.5 |
| 80° | 107.7 | 95.3 | 103.5 | 111.8 | 107.7 | 134.6 | 161.5 | 142.9 | 116.0 | 107.7 | 105.6 |
| 82.5° | 70.4 | 66.3 | 78.7 | 76.6 | 76.6 | 103.5 | 132.5 | 107.7 | 84.9 | 70.4 | 66.3 |
| 85° | 29.0 | 33.1 | 45.6 | 43.5 | 43.5 | 58.0 | 68.3 | 55.9 | 39.3 | 31.1 | 31.1 |
| 87.5° | 0.0 | 2.1 | 6.2 | 4.1 | 4.1 | 6.2 | 2.1 | 2.1 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Test Information

Test Method: LM-79-2008 Report
 Number: SP1-1908-441-10-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: MCGRAW-EDISON
 Catalog Number: **SA1C-722-U-5WQ**
 Description: MCGRAW EDISON ROADWAY AND AREA LUMINAIRE


THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2237
 CIE u': 0.2876
 CIE v': 0.5346
 Duv: -0.0006
 CIE x: 0.5005
 CIE y: 0.4134
 CIE z: 0.0860
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 587
 Purity: 74.5

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 72.0 | | |
| R1: | 68.9 | R9: | -17.4 |
| R2: | 83.0 | R10: | 61.3 |
| R3: | 95.2 | R11: | 59.8 |
| R4: | 66.2 | R12: | 50.5 |
| R5: | 65.9 | R13: | 71.1 |
| R6: | 76.3 | R14: | 96.9 |
| R7: | 76.7 | | |
| R8: | 43.8 | | |

Rf: 69.8
 Rg: 99.2



Test Conditions


Stabilization Time: 71M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.7/41%
 Sphere Temperature (°C): 25.6

REPORT NUMBER: SP1-1908-441-10-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-10-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2200K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-10-R4

Photopic Flux vs. Wavelength




#####

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 1768 | NR | 490 | 5206 | NR | 620 | 130919 | NR | 750 | 8553 | NR | 880 | 2713 | NR |
| 365 | 1569 | NR | 495 | 7286 | NR | 625 | 125335 | NR | 755 | 7696 | NR | 885 | 2316 | NR |
| 370 | 1594 | NR | 500 | 10654 | NR | 630 | 118388 | NR | 760 | 6978 | NR | 890 | 2539 | NR |
| 375 | 1744 | NR | 505 | 15189 | NR | 635 | 111855 | NR | 765 | 6377 | NR | 895 | 1933 | NR |
| 380 | 1659 | NR | 510 | 20541 | NR | 640 | 104062 | NR | 770 | 5600 | NR | 900 | 2216 | NR |
| 385 | 1504 | NR | 515 | 26492 | NR | 645 | 96365 | NR | 775 | 5000 | NR | 905 | 2067 | NR |
| 390 | 1541 | NR | 520 | 32294 | NR | 650 | 88651 | NR | 780 | 4709 | NR | 910 | 1959 | NR |
| 395 | 1355 | NR | 525 | 38123 | NR | 655 | 81152 | NR | 785 | 4305 | NR | 915 | 1874 | NR |
| 400 | 1243 | NR | 530 | 43232 | NR | 660 | 73523 | NR | 790 | 4040 | NR | 920 | 1484 | NR |
| 405 | 1417 | NR | 535 | 48012 | NR | 665 | 66123 | NR | 795 | 3642 | NR | 925 | 1914 | NR |
| 410 | 2147 | NR | 540 | 52623 | NR | 670 | 58677 | NR | 800 | 3594 | NR | 930 | 1948 | NR |
| 415 | 3837 | NR | 545 | 57516 | NR | 675 | 52349 | NR | 805 | 3190 | NR | 935 | 2079 | NR |
| 420 | 7159 | NR | 550 | 62613 | NR | 680 | 46159 | NR | 810 | 3241 | NR | 940 | 2263 | NR |
| 425 | 12599 | NR | 555 | 68554 | NR | 685 | 40525 | NR | 815 | 2732 | NR | 945 | 1688 | NR |
| 430 | 19019 | NR | 560 | 75325 | NR | 690 | 35615 | NR | 820 | 2612 | NR | 950 | 1560 | NR |
| 435 | 24875 | NR | 565 | 82533 | NR | 695 | 31158 | NR | 825 | 2966 | NR | 955 | 2826 | NR |
| 440 | 29103 | NR | 570 | 90909 | NR | 700 | 27409 | NR | 830 | 2574 | NR | 960 | 1477 | NR |
| 445 | 29901 | NR | 575 | 99621 | NR | 705 | 24204 | NR | 835 | 2633 | NR | 965 | 1568 | NR |
| 450 | 24862 | NR | 580 | 108484 | NR | 710 | 21558 | NR | 840 | 2526 | NR | 970 | 2030 | NR |
| 455 | 15942 | NR | 585 | 116679 | NR | 715 | 19222 | NR | 845 | 2631 | NR | 975 | 1986 | NR |
| 460 | 9916 | NR | 590 | 123752 | NR | 720 | 17310 | NR | 850 | 2079 | NR | 980 | 2540 | NR |
| 465 | 7051 | NR | 595 | 129324 | NR | 725 | 15280 | NR | 855 | 2309 | NR | 985 | 1139 | NR |
| 470 | 5227 | NR | 600 | 134082 | NR | 730 | 13282 | NR | 860 | 2528 | NR | 990 | 2018 | NR |
| 475 | 4257 | NR | 605 | 135698 | NR | 735 | 11753 | NR | 865 | 2121 | NR | 995 | 3445 | NR |
| 480 | 4052 | NR | 610 | 135144 | NR | 740 | 10654 | NR | 870 | 2751 | NR | 1000 | 3704 | NR |
| 485 | 4298 | NR | 615 | 134180 | NR | 745 | 9451 | NR | 875 | 2317 | NR | | | |

REPORT NUMBER: SP1-1908-441-10-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 4696.9

S/P: 0.85

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 1768 | NR | 490 | 5206 | NR | 620 | 130919 | NR | 750 | 8553 | NR | 880 | 2713 | NR |
| 365 | 1569 | NR | 495 | 7286 | NR | 625 | 125335 | NR | 755 | 7696 | NR | 885 | 2316 | NR |
| 370 | 1594 | NR | 500 | 10654 | NR | 630 | 118388 | NR | 760 | 6978 | NR | 890 | 2539 | NR |
| 375 | 1744 | NR | 505 | 15189 | NR | 635 | 111855 | NR | 765 | 6377 | NR | 895 | 1933 | NR |
| 380 | 1659 | NR | 510 | 20541 | NR | 640 | 104062 | NR | 770 | 5600 | NR | 900 | 2216 | NR |
| 385 | 1504 | NR | 515 | 26492 | NR | 645 | 96365 | NR | 775 | 5000 | NR | 905 | 2067 | NR |
| 390 | 1541 | NR | 520 | 32294 | NR | 650 | 88651 | NR | 780 | 4709 | NR | 910 | 1959 | NR |
| 395 | 1355 | NR | 525 | 38123 | NR | 655 | 81152 | NR | 785 | 4305 | NR | 915 | 1874 | NR |
| 400 | 1243 | NR | 530 | 43232 | NR | 660 | 73523 | NR | 790 | 4040 | NR | 920 | 1484 | NR |
| 405 | 1417 | NR | 535 | 48012 | NR | 665 | 66123 | NR | 795 | 3642 | NR | 925 | 1914 | NR |
| 410 | 2147 | NR | 540 | 52623 | NR | 670 | 58677 | NR | 800 | 3594 | NR | 930 | 1948 | NR |
| 415 | 3837 | NR | 545 | 57516 | NR | 675 | 52349 | NR | 805 | 3190 | NR | 935 | 2079 | NR |
| 420 | 7159 | NR | 550 | 62613 | NR | 680 | 46159 | NR | 810 | 3241 | NR | 940 | 2263 | NR |
| 425 | 12599 | NR | 555 | 68554 | NR | 685 | 40525 | NR | 815 | 2732 | NR | 945 | 1688 | NR |
| 430 | 19019 | NR | 560 | 75325 | NR | 690 | 35615 | NR | 820 | 2612 | NR | 950 | 1560 | NR |
| 435 | 24875 | NR | 565 | 82533 | NR | 695 | 31158 | NR | 825 | 2966 | NR | 955 | 2826 | NR |
| 440 | 29103 | NR | 570 | 90909 | NR | 700 | 27409 | NR | 830 | 2574 | NR | 960 | 1477 | NR |
| 445 | 29901 | NR | 575 | 99621 | NR | 705 | 24204 | NR | 835 | 2633 | NR | 965 | 1568 | NR |
| 450 | 24862 | NR | 580 | 108484 | NR | 710 | 21558 | NR | 840 | 2526 | NR | 970 | 2030 | NR |
| 455 | 15942 | NR | 585 | 116679 | NR | 715 | 19222 | NR | 845 | 2631 | NR | 975 | 1986 | NR |
| 460 | 9916 | NR | 590 | 123752 | NR | 720 | 17310 | NR | 850 | 2079 | NR | 980 | 2540 | NR |
| 465 | 7051 | NR | 595 | 129324 | NR | 725 | 15280 | NR | 855 | 2309 | NR | 985 | 1139 | NR |
| 470 | 5227 | NR | 600 | 134082 | NR | 730 | 13282 | NR | 860 | 2528 | NR | 990 | 2018 | NR |
| 475 | 4257 | NR | 605 | 135698 | NR | 735 | 11753 | NR | 865 | 2121 | NR | 995 | 3445 | NR |
| 480 | 4052 | NR | 610 | 135144 | NR | 740 | 10654 | NR | 870 | 2751 | NR | 1000 | 3704 | NR |
| 485 | 4298 | NR | 615 | 134180 | NR | 745 | 9451 | NR | 875 | 2317 | NR | | | |

REPORT NUMBER: SP1-1908-441-10-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 1470.8 M/P: 0.27

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 1768 | NR | 490 | 5206 | NR | 620 | 130919 | NR | 750 | 8553 | NR | 880 | 2713 | NR |
| 365 | 1569 | NR | 495 | 7286 | NR | 625 | 125335 | NR | 755 | 7696 | NR | 885 | 2316 | NR |
| 370 | 1594 | NR | 500 | 10654 | NR | 630 | 118388 | NR | 760 | 6978 | NR | 890 | 2539 | NR |
| 375 | 1744 | NR | 505 | 15189 | NR | 635 | 111855 | NR | 765 | 6377 | NR | 895 | 1933 | NR |
| 380 | 1659 | NR | 510 | 20541 | NR | 640 | 104062 | NR | 770 | 5600 | NR | 900 | 2216 | NR |
| 385 | 1504 | NR | 515 | 26492 | NR | 645 | 96365 | NR | 775 | 5000 | NR | 905 | 2067 | NR |
| 390 | 1541 | NR | 520 | 32294 | NR | 650 | 88651 | NR | 780 | 4709 | NR | 910 | 1959 | NR |
| 395 | 1355 | NR | 525 | 38123 | NR | 655 | 81152 | NR | 785 | 4305 | NR | 915 | 1874 | NR |
| 400 | 1243 | NR | 530 | 43232 | NR | 660 | 73523 | NR | 790 | 4040 | NR | 920 | 1484 | NR |
| 405 | 1417 | NR | 535 | 48012 | NR | 665 | 66123 | NR | 795 | 3642 | NR | 925 | 1914 | NR |
| 410 | 2147 | NR | 540 | 52623 | NR | 670 | 58677 | NR | 800 | 3594 | NR | 930 | 1948 | NR |
| 415 | 3837 | NR | 545 | 57516 | NR | 675 | 52349 | NR | 805 | 3190 | NR | 935 | 2079 | NR |
| 420 | 7159 | NR | 550 | 62613 | NR | 680 | 46159 | NR | 810 | 3241 | NR | 940 | 2263 | NR |
| 425 | 12599 | NR | 555 | 68554 | NR | 685 | 40525 | NR | 815 | 2732 | NR | 945 | 1688 | NR |
| 430 | 19019 | NR | 560 | 75325 | NR | 690 | 35615 | NR | 820 | 2612 | NR | 950 | 1560 | NR |
| 435 | 24875 | NR | 565 | 82533 | NR | 695 | 31158 | NR | 825 | 2966 | NR | 955 | 2826 | NR |
| 440 | 29103 | NR | 570 | 90909 | NR | 700 | 27409 | NR | 830 | 2574 | NR | 960 | 1477 | NR |
| 445 | 29901 | NR | 575 | 99621 | NR | 705 | 24204 | NR | 835 | 2633 | NR | 965 | 1568 | NR |
| 450 | 24862 | NR | 580 | 108484 | NR | 710 | 21558 | NR | 840 | 2526 | NR | 970 | 2030 | NR |
| 455 | 15942 | NR | 585 | 116679 | NR | 715 | 19222 | NR | 845 | 2631 | NR | 975 | 1986 | NR |
| 460 | 9916 | NR | 590 | 123752 | NR | 720 | 17310 | NR | 850 | 2079 | NR | 980 | 2540 | NR |
| 465 | 7051 | NR | 595 | 129324 | NR | 725 | 15280 | NR | 855 | 2309 | NR | 985 | 1139 | NR |
| 470 | 5227 | NR | 600 | 134082 | NR | 730 | 13282 | NR | 860 | 2528 | NR | 990 | 2018 | NR |
| 475 | 4257 | NR | 605 | 135698 | NR | 735 | 11753 | NR | 865 | 2121 | NR | 995 | 3445 | NR |
| 480 | 4052 | NR | 610 | 135144 | NR | 740 | 10654 | NR | 870 | 2751 | NR | 1000 | 3704 | NR |
| 485 | 4298 | NR | 615 | 134180 | NR | 745 | 9451 | NR | 875 | 2317 | NR | | | |

REPORT NUMBER: SP1-1908-441-10-R4





TM-30-18

Summary

$R_f = 69.8$
 $R_g = 99.2$
 $CIE R_a = 72.0$
 $R_9 = -17.4$



Color Vector Graphics




REPORT NUMBER: SP1-1908-441-10-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)




| | | | |
|------------|------------|------------|------------|
| CES01 = 87 | CES26 = 56 | CES51 = 74 | CES76 = 56 |
| CES02 = 65 | CES27 = 76 | CES52 = 76 | CES77 = 81 |
| CES03 = 32 | CES28 = 83 | CES53 = 65 | CES78 = 63 |
| CES04 = 72 | CES29 = 46 | CES54 = 78 | CES79 = 84 |
| CES05 = 52 | CES30 = 48 | CES55 = 75 | CES80 = 84 |
| CES06 = 52 | CES31 = 51 | CES56 = 65 | CES81 = 63 |
| CES07 = 44 | CES32 = 51 | CES57 = 62 | CES82 = 92 |
| CES08 = 42 | CES33 = 53 | CES58 = 66 | CES83 = 83 |
| CES09 = 29 | CES34 = 70 | CES59 = 84 | CES84 = 92 |
| CES10 = 78 | CES35 = 85 | CES60 = 90 | CES85 = 81 |
| CES11 = 61 | CES36 = 78 | CES61 = 84 | CES86 = 56 |
| CES12 = 68 | CES37 = 80 | CES62 = 70 | CES87 = 78 |
| CES13 = 45 | CES38 = 53 | CES63 = 68 | CES88 = 72 |
| CES14 = 75 | CES39 = 90 | CES64 = 69 | CES89 = 62 |
| CES15 = 72 | CES40 = 84 | CES65 = 67 | CES90 = 67 |
| CES16 = 49 | CES41 = 75 | CES66 = 64 | CES91 = 90 |
| CES17 = 51 | CES42 = 79 | CES67 = 63 | CES92 = 67 |
| CES18 = 57 | CES43 = 64 | CES68 = 69 | CES93 = 79 |
| CES19 = 74 | CES44 = 98 | CES69 = 80 | CES94 = 52 |
| CES20 = 68 | CES45 = 73 | CES70 = 63 | CES95 = 76 |
| CES21 = 89 | CES46 = 67 | CES71 = 63 | CES96 = 78 |
| CES22 = 81 | CES47 = 60 | CES72 = 87 | CES97 = 77 |
| CES23 = 92 | CES48 = 48 | CES73 = 56 | CES98 = 71 |
| CES24 = 92 | CES49 = 64 | CES74 = 87 | CES99 = 65 |
| CES25 = 74 | CES50 = 74 | CES75 = 66 | |



REPORT NUMBER: SP1-1908-441-10-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-10-R4

TM-30-18

Measure Comparisons



(END OF REPORT)