

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P436991

Luminaire Tested: **ISC-SA1A-735-U-SLR**

Issue Date: 12/9/2020

Test Information

Test Method: LM-79-08
Report Number: P436991
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-074-22)
Test Lab: INNOVATION CENTER
Issue Date: 12/9/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: ISC-SA1A-735-U-SLR
Description: IMPACT ELITE LED CYLINDER LUMINAIRE
(1) 70 CRI, 3500K, 350mA LIGHTSQUARE WITH 16 LEDS AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2299 lumens
Efficiency: N/A
Efficacy: 114.4 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G1


Input Watts (W): 20.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P436991
 CATALOG NUMBER: ISC-SA1A-735-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1.2 fc
 Type IV - Short - N/A

REPORT NUMBER: P436991
CATALOG NUMBER: ISC-SA1A-735-U-SLR

Luminous Intensity Polar Plot



— Vertical Plane Through 355-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P436991
 CATALOG NUMBER: ISC-SA1A-735-U-SLR


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 414.4 | 0.0 | 414.4 |
| | % Fixture | 18.0 | 0.0 | 18.0 |
| Street Side | Lumens | 1884.5 | 0.0 | 1884.5 |
| | % Fixture | 82.0 | 0.0 | 82.0 |
| Total | Lumens | 2299.0 | 0.0 | 2299.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 55.5 | 2.4 |
| 10°-20° | 114.7 | 5.0 |
| 20°-30° | 163.4 | 7.1 |
| 30°-40° | 233.6 | 10.2 |
| 40°-50° | 326.2 | 14.2 |
| 50°-60° | 453.8 | 19.7 |
| 60°-70° | 552.8 | 24.0 |
| 70°-80° | 340.4 | 14.8 |
| 80°-90° | 58.5 | 2.5 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 2299.0 | 100.0 |
| 0°-180° | 2299.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P436991
 CATALOG NUMBER: ISC-SA1A-735-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 229.9 | 10.0 | | | |
| FM (30°-60°) | 834.8 | 36.3 | | | |
| FH (60°-80°) | 772.9 | 33.6 | | | G1/1800 |
| FVH (80°-90°) | 47.0 | 2.0 | | | G1/100 |
| BL (0°-30°) | 103.8 | 4.5 | B0/110 | | |
| BM (30°-60°) | 178.8 | 7.8 | B0/220 | | |
| BH (60°-80°) | 120.4 | 5.2 | B1/500 | | G1/500 |
| BVH (80°-90°) | 11.5 | 0.5 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G1
 Type IV Short





REPORT NUMBER: P436991
 CATALOG NUMBER: ISC-SA1A-735-U-SLR

CANDELA DISTRIBUTION (FULL):

| | 0° | 1° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 735.6 | 735.6 | 735.6 | 735.6 | 735.6 | 735.6 | 735.6 | 735.6 | 735.6 | 735.6 | 735.6 |
| 2.5° | 754.2 | 754.2 | 744.9 | 721.6 | 700.2 | 677.9 | 670.4 | 649.9 | 636.9 | 624.8 | 629.4 |
| 5° | 710.5 | 707.7 | 690.9 | 642.5 | 605.2 | 568.9 | 546.6 | 513.1 | 509.3 | 479.5 | 477.7 |
| 7.5° | 651.8 | 649.9 | 624.8 | 569.9 | 527.0 | 470.2 | 436.7 | 407.8 | 382.7 | 365.0 | 359.4 |
| 10° | 611.8 | 605.2 | 574.5 | 507.5 | 445.1 | 404.1 | 385.5 | 360.3 | 338.9 | 316.6 | 298.0 |
| 12.5° | 585.7 | 578.2 | 547.5 | 473.9 | 413.4 | 385.5 | 359.4 | 329.6 | 300.8 | 274.7 | 256.1 |
| 15° | 590.3 | 578.2 | 543.8 | 465.6 | 402.3 | 362.2 | 325.9 | 290.5 | 257.0 | 228.1 | 204.8 |
| 17.5° | 623.9 | 609.0 | 570.8 | 471.2 | 384.6 | 331.5 | 282.1 | 241.2 | 200.2 | 170.4 | 151.8 |
| 20° | 682.5 | 661.1 | 612.7 | 487.0 | 371.5 | 302.6 | 237.4 | 183.4 | 140.6 | 120.1 | 114.5 |
| 22.5° | 754.2 | 735.6 | 669.5 | 500.0 | 357.6 | 270.0 | 188.1 | 132.2 | 110.8 | 100.6 | 97.8 |
| 25° | 828.7 | 808.2 | 734.7 | 521.4 | 346.4 | 240.2 | 148.1 | 105.2 | 95.0 | 90.3 | 88.5 |
| 27.5° | 905.1 | 884.6 | 798.9 | 555.9 | 333.3 | 208.6 | 119.2 | 92.2 | 84.7 | 81.0 | 81.0 |
| 30° | 959.1 | 942.3 | 856.6 | 586.6 | 318.4 | 183.4 | 105.2 | 85.7 | 79.1 | 75.4 | 74.5 |
| 32.5° | 1019.6 | 996.3 | 910.6 | 607.1 | 307.3 | 163.9 | 95.9 | 80.1 | 74.5 | 69.8 | 69.8 |
| 35° | 1087.6 | 1061.5 | 960.9 | 627.6 | 296.1 | 154.6 | 89.4 | 76.4 | 70.8 | 66.1 | 65.2 |
| 37.5° | 1162.1 | 1128.5 | 1012.1 | 645.3 | 284.0 | 149.9 | 85.7 | 72.6 | 67.0 | 63.3 | 61.5 |
| 40° | 1244.0 | 1208.6 | 1080.1 | 660.2 | 275.6 | 144.3 | 82.9 | 69.8 | 64.2 | 59.6 | 58.7 |
| 42.5° | 1312.9 | 1281.2 | 1127.6 | 669.5 | 271.9 | 136.9 | 81.9 | 67.0 | 62.4 | 56.8 | 54.9 |
| 45° | 1348.3 | 1321.3 | 1185.3 | 672.3 | 270.0 | 132.2 | 77.3 | 67.0 | 60.5 | 54.9 | 52.1 |
| 47.5° | 1379.0 | 1359.5 | 1227.2 | 686.2 | 265.4 | 127.6 | 71.7 | 70.8 | 59.6 | 52.1 | 49.4 |
| 50° | 1431.2 | 1410.7 | 1292.4 | 712.3 | 259.8 | 122.0 | 66.1 | 68.0 | 59.6 | 50.3 | 47.5 |
| 52.5° | 1493.5 | 1488.0 | 1378.1 | 753.3 | 251.4 | 114.5 | 60.5 | 64.2 | 59.6 | 49.4 | 45.6 |
| 55° | 1584.8 | 1576.4 | 1491.7 | 806.4 | 241.2 | 104.3 | 54.9 | 58.7 | 58.7 | 46.6 | 42.8 |
| 57.5° | 1662.1 | 1663.0 | 1596.0 | 843.6 | 231.9 | 87.5 | 51.2 | 50.3 | 55.9 | 43.8 | 40.0 |
| 60° | 1697.5 | 1697.5 | 1629.5 | 857.6 | 219.7 | 73.6 | 48.4 | 44.7 | 57.7 | 41.0 | 37.2 |
| 62.5° | 1719.8 | 1701.2 | 1582.9 | 844.5 | 205.8 | 66.1 | 43.8 | 41.0 | 46.6 | 38.2 | 34.5 |
| 65° | 1713.3 | 1677.9 | 1489.8 | 778.4 | 185.3 | 64.2 | 41.0 | 37.2 | 37.2 | 35.4 | 32.6 |
| 67.5° | 1654.6 | 1599.7 | 1352.9 | 666.7 | 163.9 | 63.3 | 37.2 | 34.5 | 33.5 | 31.7 | 29.8 |
| 70° | 1495.4 | 1456.3 | 1190.0 | 543.8 | 149.9 | 63.3 | 34.5 | 30.7 | 29.8 | 27.9 | 27.0 |
| 72.5° | 1222.6 | 1164.8 | 949.8 | 407.8 | 138.7 | 63.3 | 31.7 | 27.0 | 26.1 | 25.1 | 24.2 |
| 75° | 835.2 | 769.1 | 667.6 | 250.5 | 108.9 | 54.9 | 27.9 | 22.3 | 22.3 | 21.4 | 20.5 |
| 77.5° | 460.9 | 446.0 | 376.2 | 132.2 | 68.0 | 33.5 | 21.4 | 17.7 | 18.6 | 17.7 | 16.8 |
| 80° | 267.2 | 251.4 | 223.5 | 64.2 | 39.1 | 19.6 | 13.0 | 13.0 | 14.0 | 14.0 | 13.0 |
| 82.5° | 129.4 | 112.7 | 115.5 | 26.1 | 14.0 | 8.4 | 5.6 | 6.5 | 7.4 | 9.3 | 9.3 |
| 85° | 4.7 | 4.7 | 9.3 | 1.9 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 1.9 | 2.8 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P436991
 CATALOG NUMBER: ISC-SA1A-735-U-SLR

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 735.6 | 735.6 | 735.6 | 735.6 | 735.6 | 735.6 | 735.6 | 735.6 | 735.6 | 735.6 | 735.6 |
| 2.5° | 614.5 | 614.5 | 618.3 | 634.1 | 621.1 | 619.2 | 622.9 | 629.4 | 632.2 | 645.3 | 644.3 |
| 5° | 473.9 | 471.2 | 482.3 | 497.2 | 505.6 | 510.3 | 517.7 | 534.5 | 528.0 | 538.2 | 536.3 |
| 7.5° | 350.1 | 354.8 | 350.1 | 366.9 | 379.9 | 399.5 | 414.4 | 410.6 | 411.6 | 403.2 | 415.3 |
| 10° | 285.9 | 284.0 | 272.8 | 278.4 | 285.9 | 298.0 | 308.2 | 310.1 | 319.4 | 304.5 | 314.7 |
| 12.5° | 244.0 | 236.5 | 225.3 | 219.7 | 217.9 | 227.2 | 230.0 | 234.6 | 240.2 | 244.9 | 246.8 |
| 15° | 195.5 | 190.0 | 182.5 | 174.1 | 172.3 | 172.3 | 178.8 | 185.3 | 192.7 | 194.6 | 201.1 |
| 17.5° | 146.2 | 143.4 | 140.6 | 140.6 | 140.6 | 140.6 | 146.2 | 149.0 | 152.7 | 158.3 | 157.4 |
| 20° | 110.8 | 110.8 | 111.7 | 116.4 | 119.2 | 121.0 | 124.8 | 125.7 | 124.8 | 125.7 | 125.7 |
| 22.5° | 97.8 | 96.8 | 99.6 | 101.5 | 106.1 | 110.8 | 112.7 | 111.7 | 108.9 | 107.1 | 108.9 |
| 25° | 88.5 | 89.4 | 90.3 | 93.1 | 96.8 | 101.5 | 102.4 | 101.5 | 98.7 | 98.7 | 98.7 |
| 27.5° | 81.0 | 81.9 | 83.8 | 86.6 | 90.3 | 94.0 | 95.0 | 93.1 | 90.3 | 91.3 | 90.3 |
| 30° | 75.4 | 77.3 | 78.2 | 81.0 | 83.8 | 87.5 | 87.5 | 85.7 | 83.8 | 83.8 | 83.8 |
| 32.5° | 68.9 | 70.8 | 72.6 | 75.4 | 79.1 | 81.0 | 81.0 | 80.1 | 78.2 | 77.3 | 77.3 |
| 35° | 65.2 | 65.2 | 67.0 | 70.8 | 72.6 | 74.5 | 75.4 | 74.5 | 72.6 | 70.8 | 69.8 |
| 37.5° | 61.5 | 61.5 | 62.4 | 64.2 | 68.0 | 69.8 | 70.8 | 68.9 | 67.0 | 65.2 | 65.2 |
| 40° | 57.7 | 57.7 | 58.7 | 59.6 | 63.3 | 66.1 | 66.1 | 63.3 | 61.5 | 62.4 | 61.5 |
| 42.5° | 54.9 | 54.9 | 55.9 | 55.9 | 57.7 | 62.4 | 61.5 | 59.6 | 58.7 | 58.7 | 57.7 |
| 45° | 52.1 | 51.2 | 52.1 | 52.1 | 53.1 | 57.7 | 57.7 | 54.9 | 54.9 | 55.9 | 54.9 |
| 47.5° | 49.4 | 48.4 | 49.4 | 49.4 | 50.3 | 53.1 | 53.1 | 52.1 | 52.1 | 52.1 | 53.1 |
| 50° | 46.6 | 46.6 | 46.6 | 46.6 | 47.5 | 48.4 | 50.3 | 49.4 | 49.4 | 49.4 | 50.3 |
| 52.5° | 43.8 | 43.8 | 43.8 | 44.7 | 44.7 | 46.6 | 47.5 | 46.6 | 47.5 | 47.5 | 47.5 |
| 55° | 41.9 | 41.0 | 41.0 | 42.8 | 42.8 | 44.7 | 45.6 | 44.7 | 45.6 | 45.6 | 45.6 |
| 57.5° | 39.1 | 39.1 | 39.1 | 40.0 | 41.0 | 42.8 | 44.7 | 42.8 | 43.8 | 43.8 | 44.7 |
| 60° | 36.3 | 36.3 | 36.3 | 38.2 | 39.1 | 41.0 | 41.9 | 41.0 | 41.9 | 41.9 | 41.9 |
| 62.5° | 33.5 | 34.5 | 34.5 | 35.4 | 36.3 | 39.1 | 40.0 | 39.1 | 40.0 | 40.0 | 40.0 |
| 65° | 31.7 | 31.7 | 32.6 | 33.5 | 34.5 | 36.3 | 37.2 | 37.2 | 37.2 | 38.2 | 37.2 |
| 67.5° | 28.9 | 28.9 | 29.8 | 30.7 | 31.7 | 34.5 | 34.5 | 34.5 | 35.4 | 34.5 | 34.5 |
| 70° | 26.1 | 26.1 | 27.0 | 27.9 | 28.9 | 31.7 | 31.7 | 31.7 | 32.6 | 30.7 | 30.7 |
| 72.5° | 23.3 | 23.3 | 24.2 | 25.1 | 27.0 | 29.8 | 28.9 | 28.9 | 28.9 | 27.9 | 27.9 |
| 75° | 20.5 | 20.5 | 21.4 | 22.3 | 23.3 | 27.0 | 26.1 | 25.1 | 25.1 | 24.2 | 24.2 |
| 77.5° | 16.8 | 16.8 | 17.7 | 19.6 | 20.5 | 23.3 | 22.3 | 21.4 | 20.5 | 20.5 | 20.5 |
| 80° | 13.0 | 14.0 | 14.9 | 15.8 | 16.8 | 18.6 | 17.7 | 16.8 | 15.8 | 15.8 | 15.8 |
| 82.5° | 9.3 | 10.2 | 11.2 | 12.1 | 13.0 | 13.0 | 13.0 | 13.0 | 12.1 | 11.2 | 11.2 |
| 85° | 3.7 | 5.6 | 7.4 | 7.4 | 8.4 | 7.4 | 8.4 | 7.4 | 6.5 | 6.5 | 5.6 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.9 | 1.9 | 2.8 | 2.8 | 2.8 | 2.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P436991
 CATALOG NUMBER: ISC-SA1A-735-U-SLR

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|--------|--------|--------|
| 0° | 735.6 | 735.6 | 735.6 | 735.6 | 735.6 | 735.6 | 735.6 | 735.6 | 735.6 | 735.6 | 735.6 |
| 2.5° | 651.8 | 666.7 | 675.1 | 690.0 | 705.8 | 727.2 | 744.9 | 770.0 | 792.4 | 797.1 | 802.6 |
| 5° | 540.1 | 559.6 | 568.9 | 593.1 | 630.4 | 653.7 | 690.9 | 730.0 | 778.4 | 793.3 | 812.9 |
| 7.5° | 406.0 | 420.9 | 445.1 | 466.5 | 510.3 | 549.4 | 599.7 | 656.4 | 713.2 | 745.8 | 777.5 |
| 10° | 309.1 | 327.8 | 353.8 | 379.0 | 421.8 | 460.9 | 520.5 | 583.8 | 656.4 | 686.2 | 719.8 |
| 12.5° | 257.0 | 271.9 | 298.0 | 332.4 | 372.5 | 409.7 | 454.4 | 523.3 | 599.7 | 637.8 | 678.8 |
| 15° | 207.6 | 223.5 | 256.1 | 294.2 | 333.3 | 375.2 | 418.1 | 484.2 | 577.3 | 616.4 | 655.5 |
| 17.5° | 165.7 | 179.7 | 207.6 | 248.6 | 291.4 | 338.0 | 390.1 | 473.9 | 582.0 | 630.4 | 676.0 |
| 20° | 128.5 | 140.6 | 162.0 | 199.3 | 243.0 | 298.0 | 365.0 | 470.2 | 609.9 | 677.9 | 723.5 |
| 22.5° | 110.8 | 115.5 | 127.6 | 153.6 | 198.3 | 262.6 | 341.7 | 473.0 | 654.6 | 742.1 | 794.3 |
| 25° | 98.7 | 102.4 | 107.1 | 122.9 | 158.3 | 226.3 | 321.2 | 478.6 | 702.1 | 814.7 | 874.3 |
| 27.5° | 91.3 | 93.1 | 95.9 | 103.4 | 129.4 | 196.5 | 300.8 | 486.1 | 766.3 | 888.3 | 946.0 |
| 30° | 83.8 | 83.8 | 86.6 | 94.0 | 113.6 | 175.1 | 285.9 | 501.0 | 829.6 | 951.6 | 1008.4 |
| 32.5° | 76.4 | 76.4 | 81.0 | 87.5 | 103.4 | 157.4 | 271.0 | 505.6 | 877.1 | 1007.5 | 1053.1 |
| 35° | 69.8 | 71.7 | 75.4 | 82.9 | 96.8 | 144.3 | 257.0 | 497.2 | 911.6 | 1055.0 | 1101.5 |
| 37.5° | 66.1 | 67.0 | 71.7 | 78.2 | 88.5 | 132.2 | 243.0 | 486.1 | 958.1 | 1118.3 | 1154.6 |
| 40° | 61.5 | 63.3 | 68.0 | 74.5 | 82.9 | 122.9 | 227.2 | 473.9 | 999.1 | 1189.1 | 1207.7 |
| 42.5° | 58.7 | 60.5 | 64.2 | 70.8 | 79.1 | 111.7 | 212.3 | 464.6 | 1042.9 | 1249.6 | 1262.6 |
| 45° | 55.9 | 57.7 | 62.4 | 68.0 | 79.1 | 103.4 | 197.4 | 458.1 | 1085.7 | 1296.1 | 1306.4 |
| 47.5° | 53.1 | 54.9 | 59.6 | 67.0 | 78.2 | 98.7 | 187.2 | 451.6 | 1112.7 | 1336.2 | 1339.0 |
| 50° | 51.2 | 53.1 | 58.7 | 68.9 | 75.4 | 96.8 | 182.5 | 458.1 | 1158.3 | 1367.8 | 1359.5 |
| 52.5° | 48.4 | 51.2 | 57.7 | 71.7 | 71.7 | 95.0 | 178.8 | 481.4 | 1215.1 | 1414.4 | 1393.0 |
| 55° | 47.5 | 49.4 | 55.9 | 68.9 | 65.2 | 90.3 | 178.8 | 499.1 | 1290.6 | 1506.6 | 1471.2 |
| 57.5° | 44.7 | 46.6 | 54.0 | 64.2 | 59.6 | 82.9 | 176.9 | 528.0 | 1397.6 | 1608.1 | 1576.4 |
| 60° | 41.9 | 44.7 | 52.1 | 57.7 | 54.0 | 73.6 | 168.5 | 559.6 | 1471.2 | 1663.0 | 1668.6 |
| 62.5° | 40.0 | 42.8 | 52.1 | 50.3 | 49.4 | 64.2 | 155.5 | 579.2 | 1463.7 | 1645.3 | 1698.4 |
| 65° | 37.2 | 40.0 | 47.5 | 45.6 | 46.6 | 57.7 | 138.7 | 569.9 | 1366.0 | 1570.8 | 1663.9 |
| 67.5° | 34.5 | 37.2 | 41.0 | 41.0 | 42.8 | 55.9 | 121.0 | 515.8 | 1259.8 | 1480.5 | 1587.6 |
| 70° | 31.7 | 33.5 | 35.4 | 37.2 | 39.1 | 54.9 | 107.1 | 442.3 | 1137.8 | 1393.9 | 1478.6 |
| 72.5° | 27.9 | 28.9 | 30.7 | 32.6 | 36.3 | 52.1 | 101.5 | 359.4 | 969.3 | 1206.8 | 1338.0 |
| 75° | 24.2 | 25.1 | 27.0 | 28.9 | 31.7 | 49.4 | 93.1 | 272.8 | 798.9 | 953.5 | 1081.0 |
| 77.5° | 20.5 | 21.4 | 23.3 | 24.2 | 27.0 | 43.8 | 80.1 | 197.4 | 622.0 | 687.2 | 790.5 |
| 80° | 15.8 | 16.8 | 18.6 | 18.6 | 22.3 | 32.6 | 62.4 | 137.8 | 436.7 | 487.0 | 541.0 |
| 82.5° | 11.2 | 12.1 | 13.0 | 14.0 | 16.8 | 22.3 | 41.0 | 82.9 | 296.1 | 334.3 | 325.0 |
| 85° | 6.5 | 7.4 | 7.4 | 9.3 | 10.2 | 14.9 | 23.3 | 42.8 | 193.7 | 152.7 | 150.8 |
| 87.5° | 2.8 | 2.8 | 2.8 | 3.7 | 3.7 | 5.6 | 7.4 | 8.4 | 18.6 | 6.5 | 4.7 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P436991
 CATALOG NUMBER: ISC-SA1A-735-U-SLR

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 359° | 360° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 735.6 | 735.6 | 735.6 | 735.6 | 735.6 | 735.6 | 735.6 | 735.6 | 735.6 | 735.6 |
| 2.5° | 811.0 | 817.5 | 822.2 | 820.3 | 817.5 | 801.7 | 785.9 | 769.1 | 754.2 | 754.2 |
| 5° | 844.5 | 871.5 | 882.7 | 873.4 | 852.9 | 820.3 | 779.4 | 736.5 | 716.0 | 710.5 |
| 7.5° | 826.8 | 878.1 | 905.1 | 893.0 | 866.0 | 806.4 | 744.0 | 688.1 | 657.4 | 651.8 |
| 10° | 791.5 | 858.5 | 889.2 | 885.5 | 855.7 | 786.8 | 711.4 | 648.1 | 615.5 | 611.8 |
| 12.5° | 750.5 | 815.7 | 854.8 | 856.6 | 837.1 | 776.6 | 697.4 | 622.0 | 593.1 | 585.7 |
| 15° | 725.4 | 782.2 | 809.2 | 802.6 | 808.2 | 768.2 | 703.0 | 632.2 | 596.9 | 590.3 |
| 17.5° | 726.3 | 750.5 | 757.0 | 746.8 | 768.2 | 766.3 | 734.7 | 669.5 | 630.4 | 623.9 |
| 20° | 750.5 | 730.0 | 709.5 | 707.7 | 735.6 | 772.8 | 784.9 | 731.9 | 687.2 | 682.5 |
| 22.5° | 792.4 | 724.4 | 681.6 | 675.1 | 710.5 | 779.4 | 833.4 | 808.2 | 766.3 | 754.2 |
| 25° | 839.0 | 730.0 | 663.9 | 655.5 | 687.2 | 784.0 | 885.5 | 886.4 | 839.9 | 828.7 |
| 27.5° | 889.2 | 747.7 | 663.9 | 654.6 | 688.1 | 791.5 | 920.0 | 957.2 | 914.4 | 905.1 |
| 30° | 933.9 | 772.8 | 670.4 | 660.2 | 699.3 | 798.9 | 943.2 | 1020.5 | 972.1 | 959.1 |
| 32.5° | 960.9 | 794.3 | 686.2 | 667.6 | 718.8 | 813.8 | 964.7 | 1074.5 | 1037.3 | 1019.6 |
| 35° | 982.3 | 819.4 | 712.3 | 688.1 | 747.7 | 838.0 | 982.3 | 1133.2 | 1097.8 | 1087.6 |
| 37.5° | 998.2 | 849.2 | 739.3 | 716.0 | 785.9 | 870.6 | 1007.5 | 1195.6 | 1184.4 | 1162.1 |
| 40° | 1024.2 | 867.8 | 787.7 | 779.4 | 852.0 | 921.8 | 1037.3 | 1249.6 | 1257.0 | 1244.0 |
| 42.5° | 1047.5 | 904.1 | 856.6 | 866.0 | 936.7 | 978.6 | 1077.3 | 1289.6 | 1329.7 | 1312.9 |
| 45° | 1066.1 | 954.4 | 943.2 | 974.0 | 1034.5 | 1051.3 | 1099.7 | 1317.6 | 1359.5 | 1348.3 |
| 47.5° | 1092.2 | 1020.5 | 1058.7 | 1098.7 | 1149.0 | 1126.7 | 1122.9 | 1347.4 | 1390.2 | 1379.0 |
| 50° | 1129.5 | 1097.8 | 1174.2 | 1226.3 | 1258.9 | 1188.1 | 1151.8 | 1374.4 | 1437.7 | 1431.2 |
| 52.5° | 1167.6 | 1187.2 | 1291.5 | 1339.9 | 1361.3 | 1264.5 | 1192.8 | 1417.2 | 1493.5 | 1493.5 |
| 55° | 1238.4 | 1274.7 | 1416.3 | 1447.0 | 1475.8 | 1333.4 | 1247.7 | 1481.4 | 1580.1 | 1584.8 |
| 57.5° | 1341.8 | 1368.8 | 1511.2 | 1546.6 | 1554.1 | 1410.7 | 1334.3 | 1570.8 | 1653.7 | 1662.1 |
| 60° | 1448.8 | 1461.9 | 1605.3 | 1636.9 | 1611.8 | 1510.3 | 1435.8 | 1675.1 | 1702.1 | 1697.5 |
| 62.5° | 1567.1 | 1552.2 | 1670.5 | 1692.8 | 1686.3 | 1597.8 | 1563.4 | 1770.1 | 1737.5 | 1719.8 |
| 65° | 1661.1 | 1605.3 | 1704.0 | 1708.6 | 1712.4 | 1658.4 | 1693.7 | 1812.9 | 1752.4 | 1713.3 |
| 67.5° | 1717.9 | 1613.7 | 1636.0 | 1614.6 | 1629.5 | 1642.5 | 1782.2 | 1795.2 | 1689.1 | 1654.6 |
| 70° | 1704.9 | 1495.4 | 1394.8 | 1370.6 | 1371.6 | 1462.8 | 1725.4 | 1684.4 | 1544.8 | 1495.4 |
| 72.5° | 1584.8 | 1257.0 | 1110.8 | 1078.3 | 1084.8 | 1093.2 | 1450.7 | 1470.3 | 1248.7 | 1222.6 |
| 75° | 1334.3 | 968.4 | 799.8 | 792.4 | 783.1 | 819.4 | 1160.2 | 1074.5 | 828.7 | 835.2 |
| 77.5° | 1088.5 | 713.2 | 587.5 | 549.4 | 543.8 | 549.4 | 791.5 | 613.6 | 481.4 | 460.9 |
| 80° | 784.9 | 474.9 | 438.6 | 430.2 | 404.1 | 325.0 | 414.4 | 394.8 | 271.9 | 267.2 |
| 82.5° | 516.8 | 327.8 | 335.2 | 279.3 | 262.6 | 205.8 | 251.4 | 201.1 | 135.9 | 129.4 |
| 85° | 268.2 | 170.4 | 140.6 | 61.5 | 68.9 | 57.7 | 54.9 | 44.7 | 4.7 | 4.7 |
| 87.5° | 9.3 | 3.7 | 2.8 | 2.8 | 1.9 | 0.9 | 0.9 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269




Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-121-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 03/04/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: **IFLD-S-SA2A-735-U-T2**
 Description: STREETWORKS INF FLOOD

PROGRAMMED @ 615mA.

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K): | 3388 | CRI (Ra): | 73.1 | R9: | -34.6 |
| CIE u': | 0.2371 | R1: | 68.9 | R10: | 57.8 |
| CIE v': | 0.5177 | R2: | 81.1 | R11: | 68.6 |
| Duv: | 0.0032 | R3: | 93.1 | R12: | 53.9 |
| CIE x: | 0.4153 | R4: | 71.6 | R13: | 70.9 |
| CIE y: | 0.4030 | R5: | 69.4 | R14: | 96.2 |
| CIE z: | 0.1817 | R6: | 75.0 | | |
| Peak Wavelength (nm): | 590 | R7: | 79.5 | | |
| Dominant Wavelength (nm): | 580 | R8: | 46.4 | | |
| Purity: | 45.7 | | | | |
| Rf: | 76.9 | | | | |
| Rg: | 94.4 | | | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0/30%
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-7

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 1/31/2021 | 7/31/2021 |
| Power Meter | IN0071 | 12/1/2020 | 12/1/2021 |
| AC Power Source | IN0063 | 12/1/2020 | 12/1/2021 |
| DC Power Source | IN0208 | 12/1/2020 | 12/1/2021 |
| Sphere Thermometer | IN0085 | 12/1/2020 | 12/1/2021 |
| Room Thermometer | IN0046 | 12/1/2020 | 12/1/2021 |

REPORT NUMBER: SP1-2101-121-7

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-7

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 4.9 | 620 | 136720 | 35.6 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 8.0 | 625 | 126308 | 27.9 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 12.1 | 630 | 114625 | 20.7 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 18.1 | 635 | 103216 | 15.5 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 25.4 | 640 | 92605 | 11.1 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 33.9 | 645 | 83234 | 8.0 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 43.0 | 650 | 73263 | 5.4 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 50.1 | 655 | 64627 | 3.7 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 57.9 | 660 | 56614 | 2.4 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.0 | 535 | 103269 | 64.0 | 665 | 49537 | 1.6 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.0 | 540 | 107316 | 69.9 | 670 | 42866 | 0.9 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.0 | 545 | 113101 | 75.3 | 675 | 36708 | 0.6 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 0.0 | 550 | 120690 | 82.0 | 680 | 31814 | 0.4 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 0.1 | 555 | 128583 | 87.8 | 685 | 27485 | 0.2 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 0.3 | 560 | 137796 | 93.6 | 690 | 23698 | 0.1 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 0.8 | 565 | 146577 | 97.5 | 695 | 20309 | 0.1 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 1.6 | 570 | 154581 | 100.5 | 700 | 17890 | 0.1 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 2.4 | 575 | 162633 | 101.2 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 2.5 | 580 | 168101 | 99.9 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 2.1 | 585 | 173145 | 96.2 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 1.8 | 590 | 174675 | 90.3 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 1.7 | 595 | 173724 | 82.3 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 1.5 | 600 | 171241 | 73.8 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 1.7 | 605 | 165134 | 64.0 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 2.2 | 610 | 156652 | 53.8 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 3.3 | 615 | 147879 | 44.6 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-7

Scotopic Flux vs. Wavelength



Scotopic Lumens: 12126

S/P: 1.36

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 53.2 | 620 | 136720 | 1.7 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 71.7 | 625 | 126308 | 1.1 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 91.4 | 630 | 114625 | 0.6 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 110.0 | 635 | 103216 | 0.4 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 125.1 | 640 | 92605 | 0.2 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 135.7 | 645 | 83234 | 0.1 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 140.8 | 650 | 73263 | 0.1 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 139.6 | 655 | 64627 | 0.1 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 135.7 | 660 | 56614 | 0.0 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.1 | 535 | 103269 | 128.7 | 665 | 49537 | 0.0 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.2 | 540 | 107316 | 118.6 | 670 | 42866 | 0.0 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.6 | 545 | 113101 | 108.4 | 675 | 36708 | 0.0 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 2.0 | 550 | 120690 | 98.7 | 680 | 31814 | 0.0 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 5.9 | 555 | 128583 | 87.9 | 685 | 27485 | 0.0 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 14.3 | 560 | 137796 | 77.0 | 690 | 23698 | 0.0 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 30.5 | 565 | 146577 | 65.8 | 695 | 20309 | 0.0 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 55.5 | 570 | 154581 | 54.6 | 700 | 17890 | 0.0 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 77.4 | 575 | 162633 | 44.3 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 73.6 | 580 | 168101 | 34.6 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 53.7 | 585 | 173145 | 26.5 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 41.9 | 590 | 174675 | 19.5 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 34.3 | 595 | 173724 | 13.9 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 27.9 | 600 | 171241 | 9.7 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 27.1 | 605 | 165134 | 6.5 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 31.3 | 610 | 156652 | 4.2 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 40.0 | 615 | 147879 | 2.7 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: 4490.7 M/P: 0.5

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 28.8 | 620 | 136720 | 0.1 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 36.6 | 625 | 126308 | 0.1 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 43.9 | 630 | 114625 | 0.0 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 49.6 | 635 | 103216 | 0.0 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 53.0 | 640 | 92605 | 0.0 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 53.5 | 645 | 83234 | 0.0 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 51.6 | 650 | 73263 | 0.0 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 47.3 | 655 | 64627 | 0.0 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 42.5 | 660 | 56614 | 0.0 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.0 | 535 | 103269 | 37.2 | 665 | 49537 | 0.0 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.1 | 540 | 107316 | 31.4 | 670 | 42866 | 0.0 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.4 | 545 | 113101 | 26.3 | 675 | 36708 | 0.0 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 1.4 | 550 | 120690 | 21.7 | 680 | 31814 | 0.0 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 3.7 | 555 | 128583 | 17.3 | 685 | 27485 | 0.0 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 8.9 | 560 | 137796 | 13.6 | 690 | 23698 | 0.0 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 18.2 | 565 | 146577 | 10.3 | 695 | 20309 | 0.0 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 33.2 | 570 | 154581 | 7.6 | 700 | 17890 | 0.0 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 45.6 | 575 | 162633 | 5.4 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 43.8 | 580 | 168101 | 3.8 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 32.2 | 585 | 173145 | 2.6 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 25.6 | 590 | 174675 | 1.7 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 21.2 | 595 | 173724 | 1.1 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 17.4 | 600 | 171241 | 0.7 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 16.6 | 605 | 165134 | 0.5 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 18.6 | 610 | 156652 | 0.3 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 22.7 | 615 | 147879 | 0.2 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

Summary

$R_f = 76.9$
 $R_g = 94.4$
 $CIE R_a = 73.1$
 $R_g = -34.6$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 68 | CES51 = 90 | CES76 = 63 |
| CES02 = 62 | CES27 = 88 | CES52 = 89 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 80 | CES78 = 65 |
| CES04 = 70 | CES29 = 67 | CES54 = 84 | CES79 = 87 |
| CES05 = 48 | CES30 = 74 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 71 | CES56 = 75 | CES81 = 75 |
| CES07 = 40 | CES32 = 67 | CES57 = 74 | CES82 = 94 |
| CES08 = 39 | CES33 = 74 | CES58 = 76 | CES83 = 91 |
| CES09 = 29 | CES34 = 78 | CES59 = 87 | CES84 = 89 |
| CES10 = 75 | CES35 = 89 | CES60 = 93 | CES85 = 80 |
| CES11 = 58 | CES36 = 98 | CES61 = 86 | CES86 = 66 |
| CES12 = 64 | CES37 = 86 | CES62 = 89 | CES87 = 79 |
| CES13 = 43 | CES38 = 82 | CES63 = 77 | CES88 = 79 |
| CES14 = 74 | CES39 = 95 | CES64 = 74 | CES89 = 70 |
| CES15 = 71 | CES40 = 91 | CES65 = 68 | CES90 = 77 |
| CES16 = 47 | CES41 = 89 | CES66 = 71 | CES91 = 88 |
| CES17 = 50 | CES42 = 88 | CES67 = 69 | CES92 = 60 |
| CES18 = 56 | CES43 = 82 | CES68 = 74 | CES93 = 77 |
| CES19 = 72 | CES44 = 99 | CES69 = 82 | CES94 = 52 |
| CES20 = 65 | CES45 = 87 | CES70 = 67 | CES95 = 69 |
| CES21 = 86 | CES46 = 82 | CES71 = 66 | CES96 = 78 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 85 |
| CES23 = 92 | CES48 = 72 | CES73 = 59 | CES98 = 76 |
| CES24 = 91 | CES49 = 82 | CES74 = 97 | CES99 = 63 |
| CES25 = 72 | CES50 = 88 | CES75 = 66 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)