

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P437578

Luminaire Tested: **ISC-SA1D-827-U-SLL**

Issue Date: 12/9/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P437578  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-074-20)  
Test Lab: INNOVATION CENTER  
Issue Date: 12/9/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: ISC-SA1D-827-U-SLL  
Description: IMPACT ELITE LED CYLINDER LUMINAIRE  
(1) 80 CRI, 2700K, 800mA LIGHTSQUARE WITH 16 LEDS AND SPILL LIGHT  
ELIMINATOR LEFT OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3709 lumens  
Efficiency: N/A  
Efficacy: 82.1 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B1 - U0 - G1


Input Watts (W): 45.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P437578  
 CATALOG NUMBER: ISC-SA1D-827-U-SLL

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 2.3 fc  
 Type IV - Short - N/A

REPORT NUMBER: P437578  
CATALOG NUMBER: ISC-SA1D-827-U-SLL

### Luminous Intensity Polar Plot



— Vertical Plane Through 85-Deg Lateral      - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P437578  
 CATALOG NUMBER: ISC-SA1D-827-U-SLL

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 725.9    | 0.0    | 725.9  |
|                    | % Fixture | 19.6     | 0.0    | 19.6   |
| <b>Street Side</b> | Lumens    | 2983.1   | 0.0    | 2983.1 |
|                    | % Fixture | 80.4     | 0.0    | 80.4   |
| <b>Total</b>       | Lumens    | 3709.0   | 0.0    | 3709.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 89.2   | 2.4       |
| 10°-20°   | 185.5  | 5.0       |
| 20°-30°   | 266.8  | 7.2       |
| 30°-40°   | 383.0  | 10.3      |
| 40°-50°   | 542.2  | 14.6      |
| 50°-60°   | 753.9  | 20.3      |
| 60°-70°   | 897.7  | 24.2      |
| 70°-80°   | 518.9  | 14.0      |
| 80°-90°   | 71.7   | 1.9       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 3709.0 | 100.0     |
| 0°-180°   | 3709.0 | 100.0     |

**Coefficient of Utilization**




REPORT NUMBER: P437578  
 CATALOG NUMBER: ISC-SA1D-827-U-SLL

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 369.6  | 10.0      |                         |      |         |
| FM (30°-60°)   | 1339.0 | 36.1      |                         |      |         |
| FH (60°-80°)   | 1214.5 | 32.7      |                         |      | G1/1800 |
| FVH (80°-90°)  | 60.0   | 1.6       |                         |      | G1/100  |
| BL (0°-30°)    | 171.9  | 4.6       | B1/500                  |      |         |
| BM (30°-60°)   | 340.1  | 9.2       | B1/1000                 |      |         |
| BH (60°-80°)   | 202.1  | 5.4       | B1/500                  |      | G1/500  |
| BVH (80°-90°)  | 11.7   | 0.3       |                         |      | G1/100  |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B1-U0-G1**  
 Type IV Short





REPORT NUMBER: P437578

CATALOG NUMBER: ISC-SA1D-827-U-SLL

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 1°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1171.7 | 1171.7 | 1171.7 | 1171.7 | 1171.7 | 1171.7 | 1171.7 | 1171.7 | 1171.7 | 1171.7 | 1171.7 |
| 2.5°  | 1227.8 | 1232.3 | 1243.0 | 1279.3 | 1302.1 | 1320.3 | 1343.0 | 1320.3 | 1314.2 | 1283.9 | 1277.8 |
| 5°    | 1183.8 | 1194.4 | 1224.8 | 1293.0 | 1349.1 | 1408.2 | 1438.5 | 1412.7 | 1377.9 | 1324.8 | 1271.8 |
| 7.5°  | 1097.4 | 1111.1 | 1150.5 | 1256.6 | 1362.7 | 1443.0 | 1482.4 | 1455.2 | 1383.9 | 1289.9 | 1194.4 |
| 10°   | 1009.5 | 1030.7 | 1077.7 | 1211.1 | 1323.3 | 1412.7 | 1473.4 | 1444.6 | 1358.2 | 1235.4 | 1121.7 |
| 12.5° | 956.5  | 971.6  | 1024.7 | 1164.1 | 1282.4 | 1371.8 | 1417.3 | 1400.6 | 1320.3 | 1203.5 | 1082.3 |
| 15°   | 944.3  | 959.5  | 1012.6 | 1147.5 | 1252.0 | 1318.7 | 1329.4 | 1333.9 | 1303.6 | 1214.2 | 1092.9 |
| 17.5° | 977.7  | 989.8  | 1062.6 | 1174.7 | 1217.2 | 1230.8 | 1247.5 | 1267.2 | 1282.4 | 1235.4 | 1136.8 |
| 20°   | 1058.0 | 1082.3 | 1145.9 | 1230.8 | 1208.1 | 1176.3 | 1185.4 | 1209.6 | 1267.2 | 1297.5 | 1238.4 |
| 22.5° | 1165.6 | 1192.9 | 1273.3 | 1308.1 | 1214.2 | 1145.9 | 1138.4 | 1159.6 | 1265.7 | 1365.7 | 1359.7 |
| 25°   | 1285.4 | 1323.3 | 1409.7 | 1411.2 | 1239.9 | 1124.7 | 1109.6 | 1129.3 | 1262.7 | 1426.4 | 1456.7 |
| 27.5° | 1409.7 | 1444.6 | 1538.5 | 1491.5 | 1289.9 | 1126.2 | 1108.0 | 1127.8 | 1270.2 | 1491.5 | 1564.3 |
| 30°   | 1502.2 | 1547.6 | 1629.5 | 1567.3 | 1321.8 | 1145.9 | 1118.7 | 1144.4 | 1286.9 | 1524.9 | 1659.8 |
| 32.5° | 1596.1 | 1624.9 | 1711.3 | 1611.3 | 1356.6 | 1176.3 | 1141.4 | 1180.8 | 1329.4 | 1556.7 | 1735.6 |
| 35°   | 1679.5 | 1717.4 | 1805.3 | 1637.1 | 1408.2 | 1227.8 | 1182.3 | 1233.9 | 1390.0 | 1602.2 | 1812.9 |
| 37.5° | 1785.6 | 1822.0 | 1902.3 | 1673.4 | 1450.6 | 1293.0 | 1255.1 | 1321.8 | 1464.3 | 1643.1 | 1916.0 |
| 40°   | 1879.6 | 1937.2 | 1997.8 | 1718.9 | 1499.1 | 1388.5 | 1364.2 | 1455.2 | 1564.3 | 1699.2 | 2016.0 |
| 42.5° | 1972.0 | 2020.6 | 2087.2 | 1770.4 | 1561.3 | 1505.2 | 1515.8 | 1611.3 | 1685.6 | 1784.1 | 2105.4 |
| 45°   | 2038.7 | 2094.8 | 2153.9 | 1811.4 | 1641.6 | 1631.0 | 1702.2 | 1782.6 | 1809.9 | 1873.5 | 2185.8 |
| 47.5° | 2103.9 | 2147.9 | 2200.9 | 1852.3 | 1738.6 | 1772.0 | 1896.3 | 1958.4 | 1931.1 | 1953.9 | 2249.4 |
| 50°   | 2190.3 | 2237.3 | 2252.5 | 1917.5 | 1861.4 | 1950.8 | 2085.7 | 2126.7 | 2047.8 | 2017.5 | 2316.1 |
| 52.5° | 2314.6 | 2337.4 | 2329.8 | 1994.8 | 1978.1 | 2137.3 | 2247.9 | 2310.1 | 2169.1 | 2078.2 | 2408.6 |
| 55°   | 2481.4 | 2520.8 | 2472.3 | 2120.6 | 2097.9 | 2316.1 | 2445.0 | 2475.3 | 2304.0 | 2153.9 | 2514.7 |
| 57.5° | 2640.5 | 2675.4 | 2660.2 | 2273.7 | 2254.0 | 2470.7 | 2595.0 | 2623.8 | 2435.9 | 2294.9 | 2636.0 |
| 60°   | 2699.6 | 2710.2 | 2764.8 | 2435.9 | 2410.1 | 2602.6 | 2743.6 | 2748.1 | 2593.5 | 2464.7 | 2833.0 |
| 62.5° | 2636.0 | 2678.4 | 2731.5 | 2587.5 | 2504.1 | 2716.3 | 2842.1 | 2870.9 | 2743.6 | 2670.8 | 2940.6 |
| 65°   | 2517.7 | 2555.6 | 2617.8 | 2689.0 | 2575.3 | 2743.6 | 2861.8 | 2898.2 | 2840.6 | 2887.6 | 2987.6 |
| 67.5° | 2381.3 | 2428.3 | 2470.7 | 2705.7 | 2566.2 | 2587.5 | 2686.0 | 2708.7 | 2789.1 | 2983.1 | 2901.2 |
| 70°   | 2205.5 | 2258.5 | 2294.9 | 2640.5 | 2349.5 | 2138.8 | 2208.5 | 2270.7 | 2393.4 | 2813.3 | 2699.6 |
| 72.5° | 1826.5 | 1911.4 | 2002.4 | 2344.9 | 1900.8 | 1661.3 | 1715.9 | 1756.8 | 1844.7 | 2402.5 | 2351.0 |
| 75°   | 1285.4 | 1347.5 | 1459.7 | 1888.7 | 1459.7 | 1176.3 | 1261.1 | 1261.1 | 1371.8 | 1973.6 | 1785.6 |
| 77.5° | 768.5  | 770.0  | 879.2  | 1243.0 | 888.3  | 792.8  | 841.3  | 864.0  | 897.4  | 1397.6 | 1185.4 |
| 80°   | 435.0  | 441.1  | 477.5  | 803.4  | 526.0  | 541.1  | 598.7  | 659.4  | 609.3  | 867.0  | 762.4  |
| 82.5° | 203.1  | 178.9  | 189.5  | 378.9  | 298.6  | 353.2  | 362.3  | 389.6  | 392.6  | 554.8  | 500.2  |
| 85°   | 16.7   | 13.6   | 18.2   | 68.2   | 53.1   | 48.5   | 34.9   | 66.7   | 104.6  | 242.5  | 215.2  |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P437578  
 CATALOG NUMBER: ISC-SA1D-827-U-SLL

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1171.7 | 1171.7 | 1171.7 | 1171.7 | 1171.7 | 1171.7 | 1171.7 | 1171.7 | 1171.7 | 1171.7 | 1171.7 |
| 2.5°  | 1258.1 | 1243.0 | 1209.6 | 1183.8 | 1159.6 | 1114.1 | 1095.9 | 1070.2 | 1056.5 | 1032.3 | 1038.3 |
| 5°    | 1232.3 | 1197.5 | 1121.7 | 1070.2 | 1003.5 | 948.9  | 915.5  | 885.2  | 873.1  | 847.3  | 838.2  |
| 7.5°  | 1138.4 | 1108.0 | 1012.6 | 927.7  | 845.8  | 780.6  | 718.5  | 673.0  | 651.8  | 629.1  | 627.5  |
| 10°   | 1058.0 | 1008.0 | 898.9  | 798.8  | 704.8  | 644.2  | 598.7  | 560.8  | 527.5  | 498.7  | 482.0  |
| 12.5° | 1012.6 | 950.4  | 829.1  | 707.9  | 642.7  | 600.3  | 550.2  | 503.2  | 465.3  | 432.0  | 412.3  |
| 15°   | 1012.6 | 939.8  | 795.8  | 677.6  | 612.4  | 548.7  | 491.1  | 442.6  | 392.6  | 353.2  | 341.1  |
| 17.5° | 1059.5 | 970.1  | 803.4  | 657.9  | 565.4  | 494.1  | 421.4  | 357.7  | 309.2  | 274.4  | 262.2  |
| 20°   | 1152.0 | 1044.4 | 821.6  | 635.1  | 519.9  | 421.4  | 333.5  | 265.3  | 221.3  | 204.6  | 201.6  |
| 22.5° | 1259.6 | 1133.8 | 848.8  | 613.9  | 472.9  | 344.1  | 250.1  | 201.6  | 181.9  | 175.8  | 175.8  |
| 25°   | 1377.9 | 1233.9 | 883.7  | 591.2  | 424.4  | 272.8  | 191.0  | 168.3  | 160.7  | 157.6  | 157.6  |
| 27.5° | 1488.5 | 1343.0 | 945.9  | 582.1  | 378.9  | 221.3  | 166.7  | 150.1  | 145.5  | 142.5  | 144.0  |
| 30°   | 1596.1 | 1440.0 | 1009.5 | 563.9  | 328.9  | 192.5  | 150.1  | 137.9  | 131.9  | 130.4  | 131.9  |
| 32.5° | 1688.6 | 1523.4 | 1053.5 | 536.6  | 294.1  | 172.8  | 139.5  | 127.3  | 121.3  | 119.7  | 121.3  |
| 35°   | 1794.7 | 1605.2 | 1097.4 | 516.9  | 275.9  | 160.7  | 131.9  | 119.7  | 113.7  | 110.7  | 110.7  |
| 37.5° | 1919.0 | 1703.8 | 1130.8 | 488.1  | 263.7  | 148.5  | 125.8  | 113.7  | 106.1  | 103.1  | 103.1  |
| 40°   | 2085.7 | 1823.5 | 1158.1 | 465.3  | 250.1  | 142.5  | 118.2  | 107.6  | 100.0  | 97.0   | 95.5   |
| 42.5° | 2200.9 | 1928.1 | 1180.8 | 450.2  | 236.5  | 139.5  | 113.7  | 104.6  | 95.5   | 90.9   | 89.4   |
| 45°   | 2279.8 | 2020.6 | 1196.0 | 442.6  | 224.3  | 131.9  | 110.7  | 101.6  | 90.9   | 84.9   | 84.9   |
| 47.5° | 2355.5 | 2096.3 | 1197.5 | 432.0  | 215.2  | 122.8  | 115.2  | 97.0   | 86.4   | 80.3   | 80.3   |
| 50°   | 2440.4 | 2191.8 | 1226.3 | 421.4  | 204.6  | 112.2  | 113.7  | 95.5   | 83.4   | 77.3   | 75.8   |
| 52.5° | 2525.3 | 2322.2 | 1282.4 | 406.2  | 189.5  | 103.1  | 107.6  | 97.0   | 80.3   | 74.3   | 72.8   |
| 55°   | 2676.9 | 2484.4 | 1352.1 | 383.5  | 169.8  | 94.0   | 100.0  | 95.5   | 75.8   | 69.7   | 68.2   |
| 57.5° | 2775.4 | 2636.0 | 1406.7 | 359.2  | 141.0  | 87.9   | 87.9   | 92.5   | 71.2   | 65.2   | 63.7   |
| 60°   | 2831.5 | 2664.8 | 1417.3 | 330.4  | 115.2  | 78.8   | 75.8   | 94.0   | 66.7   | 59.1   | 59.1   |
| 62.5° | 2830.0 | 2566.2 | 1364.2 | 303.2  | 100.0  | 72.8   | 68.2   | 81.9   | 62.1   | 56.1   | 54.6   |
| 65°   | 2801.2 | 2420.7 | 1244.5 | 268.3  | 94.0   | 66.7   | 60.6   | 62.1   | 57.6   | 51.5   | 50.0   |
| 67.5° | 2676.9 | 2169.1 | 1053.5 | 233.4  | 90.9   | 60.6   | 56.1   | 53.1   | 50.0   | 45.5   | 44.0   |
| 70°   | 2375.2 | 1885.6 | 821.6  | 216.8  | 89.4   | 53.1   | 48.5   | 45.5   | 42.4   | 39.4   | 39.4   |
| 72.5° | 1931.1 | 1470.3 | 627.5  | 207.7  | 90.9   | 48.5   | 40.9   | 39.4   | 36.4   | 34.9   | 33.3   |
| 75°   | 1336.9 | 1086.8 | 454.7  | 183.4  | 87.9   | 40.9   | 34.9   | 31.8   | 30.3   | 27.3   | 27.3   |
| 77.5° | 859.5  | 710.9  | 301.6  | 147.0  | 71.2   | 33.3   | 25.8   | 24.3   | 22.7   | 21.2   | 21.2   |
| 80°   | 565.4  | 483.5  | 175.8  | 104.6  | 44.0   | 22.7   | 18.2   | 18.2   | 16.7   | 13.6   | 13.6   |
| 82.5° | 359.2  | 365.3  | 90.9   | 48.5   | 25.8   | 13.6   | 10.6   | 9.1    | 9.1    | 6.1    | 6.1    |
| 85°   | 78.8   | 137.9  | 40.9   | 19.7   | 9.1    | 1.5    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |





REPORT NUMBER: P437578  
 CATALOG NUMBER: ISC-SA1D-827-U-SLL

**CANDELA DISTRIBUTION (continued):**

|       | 185°   | 195°   | 205°   | 215°   | 225°   | 235°   | 245°   | 255°   | 265°   | 270°   | 275°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1171.7 | 1171.7 | 1171.7 | 1171.7 | 1171.7 | 1171.7 | 1171.7 | 1171.7 | 1171.7 | 1171.7 | 1171.7 |
| 2.5°  | 1017.1 | 1005.0 | 1000.4 | 1000.4 | 980.7  | 982.2  | 982.2  | 994.4  | 992.8  | 1003.5 | 998.9  |
| 5°    | 827.6  | 815.5  | 815.5  | 818.5  | 821.6  | 807.9  | 812.5  | 800.3  | 823.1  | 806.4  | 794.3  |
| 7.5°  | 610.9  | 609.3  | 620.0  | 644.2  | 639.7  | 635.1  | 626.0  | 603.3  | 591.2  | 603.3  | 597.2  |
| 10°   | 468.4  | 472.9  | 469.9  | 480.5  | 482.0  | 480.5  | 465.3  | 460.8  | 454.7  | 460.8  | 468.4  |
| 12.5° | 392.6  | 374.4  | 354.7  | 353.2  | 365.3  | 365.3  | 363.8  | 365.3  | 369.9  | 369.9  | 375.9  |
| 15°   | 327.4  | 315.3  | 289.5  | 277.4  | 286.5  | 280.4  | 281.9  | 288.0  | 292.5  | 298.6  | 295.6  |
| 17.5° | 260.7  | 250.1  | 238.0  | 230.4  | 234.9  | 230.4  | 228.9  | 227.4  | 227.4  | 225.9  | 231.9  |
| 20°   | 198.6  | 197.1  | 201.6  | 198.6  | 200.1  | 197.1  | 192.5  | 186.4  | 181.9  | 184.9  | 188.0  |
| 22.5° | 172.8  | 174.3  | 177.3  | 180.4  | 180.4  | 177.3  | 169.8  | 163.7  | 162.2  | 162.2  | 163.7  |
| 25°   | 159.2  | 159.2  | 163.7  | 165.2  | 166.7  | 162.2  | 153.1  | 148.5  | 148.5  | 148.5  | 148.5  |
| 27.5° | 144.0  | 147.0  | 150.1  | 153.1  | 154.6  | 150.1  | 142.5  | 137.9  | 137.9  | 136.4  | 134.9  |
| 30°   | 133.4  | 134.9  | 137.9  | 139.5  | 141.0  | 136.4  | 131.9  | 127.3  | 127.3  | 127.3  | 125.8  |
| 32.5° | 121.3  | 125.8  | 127.3  | 128.8  | 130.4  | 127.3  | 122.8  | 119.7  | 118.2  | 116.7  | 113.7  |
| 35°   | 112.2  | 113.7  | 118.2  | 118.2  | 119.7  | 118.2  | 115.2  | 112.2  | 107.6  | 106.1  | 106.1  |
| 37.5° | 103.1  | 103.1  | 106.1  | 109.1  | 112.2  | 110.7  | 106.1  | 101.6  | 100.0  | 100.0  | 100.0  |
| 40°   | 97.0   | 95.5   | 97.0   | 101.6  | 104.6  | 104.6  | 98.5   | 95.5   | 95.5   | 94.0   | 94.0   |
| 42.5° | 89.4   | 89.4   | 89.4   | 94.0   | 100.0  | 97.0   | 90.9   | 90.9   | 90.9   | 89.4   | 89.4   |
| 45°   | 84.9   | 83.4   | 84.9   | 84.9   | 92.5   | 87.9   | 86.4   | 84.9   | 86.4   | 84.9   | 86.4   |
| 47.5° | 78.8   | 78.8   | 78.8   | 80.3   | 84.9   | 81.9   | 80.3   | 80.3   | 81.9   | 81.9   | 81.9   |
| 50°   | 74.3   | 74.3   | 74.3   | 75.8   | 77.3   | 77.3   | 77.3   | 77.3   | 77.3   | 78.8   | 78.8   |
| 52.5° | 71.2   | 69.7   | 71.2   | 71.2   | 72.8   | 74.3   | 72.8   | 74.3   | 74.3   | 74.3   | 75.8   |
| 55°   | 68.2   | 66.7   | 68.2   | 68.2   | 71.2   | 69.7   | 69.7   | 71.2   | 71.2   | 72.8   | 74.3   |
| 57.5° | 63.7   | 62.1   | 65.2   | 65.2   | 68.2   | 68.2   | 66.7   | 68.2   | 68.2   | 69.7   | 69.7   |
| 60°   | 59.1   | 59.1   | 60.6   | 60.6   | 63.7   | 65.2   | 65.2   | 65.2   | 65.2   | 65.2   | 65.2   |
| 62.5° | 54.6   | 54.6   | 56.1   | 57.6   | 60.6   | 60.6   | 62.1   | 62.1   | 62.1   | 62.1   | 60.6   |
| 65°   | 50.0   | 51.5   | 53.1   | 53.1   | 56.1   | 57.6   | 57.6   | 57.6   | 57.6   | 57.6   | 57.6   |
| 67.5° | 44.0   | 47.0   | 48.5   | 50.0   | 53.1   | 53.1   | 54.6   | 54.6   | 53.1   | 53.1   | 53.1   |
| 70°   | 39.4   | 40.9   | 42.4   | 44.0   | 48.5   | 48.5   | 50.0   | 50.0   | 48.5   | 48.5   | 50.0   |
| 72.5° | 33.3   | 34.9   | 36.4   | 39.4   | 44.0   | 44.0   | 45.5   | 45.5   | 44.0   | 44.0   | 44.0   |
| 75°   | 28.8   | 28.8   | 30.3   | 33.3   | 39.4   | 39.4   | 39.4   | 40.9   | 39.4   | 39.4   | 37.9   |
| 77.5° | 21.2   | 22.7   | 24.3   | 28.8   | 33.3   | 34.9   | 34.9   | 34.9   | 33.3   | 33.3   | 31.8   |
| 80°   | 13.6   | 15.2   | 18.2   | 21.2   | 25.8   | 27.3   | 28.8   | 28.8   | 27.3   | 27.3   | 25.8   |
| 82.5° | 6.1    | 9.1    | 10.6   | 13.6   | 16.7   | 21.2   | 21.2   | 22.7   | 21.2   | 19.7   | 19.7   |
| 85°   | 0.0    | 0.0    | 1.5    | 4.5    | 7.6    | 12.1   | 13.6   | 15.2   | 13.6   | 12.1   | 12.1   |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 3.0    | 3.0    | 3.0    | 1.5    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P437578  
 CATALOG NUMBER: ISC-SA1D-827-U-SLL

**CANDELA DISTRIBUTION (continued):**

|       | 285°   | 295°   | 305°   | 315°   | 325°   | 335°   | 345°   | 355°   | 359°   | 360°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1171.7 | 1171.7 | 1171.7 | 1171.7 | 1171.7 | 1171.7 | 1171.7 | 1171.7 | 1171.7 | 1171.7 |
| 2.5°  | 1015.6 | 1032.3 | 1058.0 | 1073.2 | 1108.0 | 1139.9 | 1173.2 | 1217.2 | 1226.3 | 1227.8 |
| 5°    | 806.4  | 826.1  | 874.6  | 894.3  | 958.0  | 1009.5 | 1085.3 | 1159.6 | 1179.3 | 1183.8 |
| 7.5°  | 615.4  | 630.6  | 683.6  | 721.5  | 791.2  | 864.0  | 961.0  | 1048.9 | 1092.9 | 1097.4 |
| 10°   | 480.5  | 521.4  | 562.4  | 618.4  | 679.1  | 750.3  | 851.9  | 964.0  | 1012.6 | 1009.5 |
| 12.5° | 404.7  | 447.2  | 497.2  | 553.3  | 615.4  | 679.1  | 771.5  | 895.8  | 944.3  | 956.5  |
| 15°   | 324.4  | 375.9  | 430.5  | 488.1  | 560.8  | 623.0  | 730.6  | 868.6  | 927.7  | 944.3  |
| 17.5° | 251.6  | 292.5  | 345.6  | 419.9  | 491.1  | 579.0  | 715.5  | 894.3  | 961.0  | 977.7  |
| 20°   | 198.6  | 228.9  | 266.8  | 338.0  | 429.0  | 538.1  | 707.9  | 942.8  | 1033.8 | 1058.0 |
| 22.5° | 169.8  | 181.9  | 209.2  | 271.3  | 366.8  | 494.1  | 703.3  | 1011.0 | 1124.7 | 1165.6 |
| 25°   | 151.6  | 159.2  | 174.3  | 213.7  | 304.7  | 456.3  | 710.9  | 1095.9 | 1252.0 | 1285.4 |
| 27.5° | 137.9  | 144.0  | 151.6  | 180.4  | 263.7  | 422.9  | 724.5  | 1191.4 | 1361.2 | 1409.7 |
| 30°   | 125.8  | 130.4  | 141.0  | 160.7  | 230.4  | 389.6  | 729.1  | 1285.4 | 1458.2 | 1502.2 |
| 32.5° | 116.7  | 122.8  | 131.9  | 148.5  | 210.7  | 366.8  | 717.0  | 1356.6 | 1547.6 | 1596.1 |
| 35°   | 107.6  | 115.2  | 124.3  | 137.9  | 194.0  | 347.1  | 689.7  | 1415.8 | 1632.5 | 1679.5 |
| 37.5° | 103.1  | 107.6  | 116.7  | 127.3  | 181.9  | 327.4  | 665.4  | 1474.9 | 1720.4 | 1785.6 |
| 40°   | 97.0   | 101.6  | 110.7  | 119.7  | 166.7  | 306.2  | 648.8  | 1550.7 | 1820.5 | 1879.6 |
| 42.5° | 92.5   | 98.5   | 106.1  | 116.7  | 154.6  | 283.5  | 632.1  | 1611.3 | 1909.9 | 1972.0 |
| 45°   | 89.4   | 95.5   | 103.1  | 116.7  | 144.0  | 265.3  | 613.9  | 1664.3 | 1978.1 | 2038.7 |
| 47.5° | 84.9   | 92.5   | 103.1  | 112.2  | 139.5  | 253.1  | 613.9  | 1728.0 | 2040.3 | 2103.9 |
| 50°   | 83.4   | 90.9   | 107.6  | 109.1  | 136.4  | 248.6  | 639.7  | 1800.8 | 2129.7 | 2190.3 |
| 52.5° | 81.9   | 89.4   | 107.6  | 103.1  | 133.4  | 251.6  | 679.1  | 1932.6 | 2244.9 | 2314.6 |
| 55°   | 77.3   | 87.9   | 103.1  | 95.5   | 125.8  | 254.7  | 723.0  | 2105.4 | 2416.2 | 2481.4 |
| 57.5° | 74.3   | 86.4   | 97.0   | 87.9   | 115.2  | 250.1  | 782.1  | 2260.0 | 2595.0 | 2640.5 |
| 60°   | 69.7   | 84.9   | 84.9   | 81.9   | 103.1  | 236.5  | 848.8  | 2358.6 | 2663.3 | 2699.6 |
| 62.5° | 66.7   | 83.4   | 75.8   | 75.8   | 94.0   | 215.2  | 871.6  | 2334.3 | 2596.6 | 2636.0 |
| 65°   | 62.1   | 72.8   | 68.2   | 69.7   | 86.4   | 191.0  | 832.2  | 2182.7 | 2470.7 | 2517.7 |
| 67.5° | 57.6   | 62.1   | 60.6   | 63.7   | 83.4   | 166.7  | 726.1  | 2002.4 | 2308.6 | 2381.3 |
| 70°   | 51.5   | 54.6   | 54.6   | 57.6   | 78.8   | 150.1  | 606.3  | 1770.4 | 2097.9 | 2205.5 |
| 72.5° | 47.0   | 48.5   | 48.5   | 53.1   | 74.3   | 141.0  | 479.0  | 1502.2 | 1759.8 | 1826.5 |
| 75°   | 39.4   | 42.4   | 42.4   | 45.5   | 66.7   | 119.7  | 327.4  | 1100.5 | 1230.8 | 1285.4 |
| 77.5° | 34.9   | 34.9   | 36.4   | 37.9   | 53.1   | 80.3   | 192.5  | 677.6  | 739.7  | 768.5  |
| 80°   | 27.3   | 28.8   | 27.3   | 27.3   | 33.3   | 53.1   | 104.6  | 397.1  | 450.2  | 435.0  |
| 82.5° | 19.7   | 19.7   | 16.7   | 16.7   | 19.7   | 28.8   | 45.5   | 206.1  | 210.7  | 203.1  |
| 85°   | 10.6   | 7.6    | 6.1    | 6.1    | 6.1    | 6.1    | 6.1    | 44.0   | 21.2   | 16.7   |
| 87.5° | 0.0    | 0.0    | 0.0    | 1.5    | 1.5    | 1.5    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2407-157-9  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/03/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Invue  
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**  
 Description: Epic Modern Light Square 40W 5WQ Optic

**Spectral Parameters**

CCT (K): 2764  
 CIE u': 0.2591  
 CIE v': 0.5290  
 Duv: 0.0020  
 CIE x: 0.4581  
 CIE y: 0.4156  
 CIE z: 0.1263  
 Peak Wavelength (nm): 603  
 Dominant Wavelength (nm): 583  
 Purity: 62.2537  
 Rf: 84.7  
 Rg: 94.6

|           |      |      |      |
|-----------|------|------|------|
| CRI (Ra): | 80.9 |      |      |
| R1:       | 78.8 | R9:  | -1.5 |
| R2:       | 89.9 | R10: | 77.9 |
| R3:       | 96.2 | R11: | 78.9 |
| R4:       | 79.1 | R12: | 71.6 |
| R5:       | 79.1 | R13: | 81.2 |
| R6:       | 88.8 | R14: | 98.5 |
| R7:       | 81.3 | R15: | 69.9 |
| R8:       | 54.3 |      |      |



**Test Conditions**

Stabilization Time: 81M  
 Operation Time: 2H 21M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

**Photopic Flux vs. Wavelength**



**Photopic Lumens: 4337.9**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 0             | 0.0           | 490    | 18018         | 2.6           | 620    | 87426         | 22.8          | 750    | 2680          | 0.0           | 880    | 58            | 0.0           |
| 365    | 0             | 0.0           | 495    | 22295         | 3.9           | 625    | 83013         | 18.2          | 755    | 2287          | 0.0           | 885    | 46            | 0.0           |
| 370    | 0             | 0.0           | 500    | 26478         | 5.8           | 630    | 78077         | 14.1          | 760    | 1944          | 0.0           | 890    | 45            | 0.0           |
| 375    | 0             | 0.0           | 505    | 30524         | 8.5           | 635    | 72080         | 10.7          | 765    | 1653          | 0.0           | 895    | 41            | 0.0           |
| 380    | 0             | 0.0           | 510    | 33611         | 11.5          | 640    | 66249         | 7.9           | 770    | 1413          | 0.0           | 900    | 38            | 0.0           |
| 385    | 0             | 0.0           | 515    | 36490         | 15.2          | 645    | 59973         | 5.7           | 775    | 1198          | 0.0           | 905    | 33            | 0.0           |
| 390    | 0             | 0.0           | 520    | 38610         | 18.7          | 650    | 53972         | 3.9           | 780    | 1025          | 0.0           | 910    | 30            | 0.0           |
| 395    | 0             | 0.0           | 525    | 40511         | 21.9          | 655    | 48369         | 2.7           | 785    | 874           | 0.0           | 915    | 23            | 0.0           |
| 400    | 48            | 0.0           | 530    | 42223         | 24.9          | 660    | 42641         | 1.8           | 790    | 747           | 0.0           | 920    | 24            | 0.0           |
| 405    | 201           | 0.0           | 535    | 44137         | 27.6          | 665    | 37602         | 1.1           | 795    | 639           | 0.0           | 925    | 22            | 0.0           |
| 410    | 457           | 0.0           | 540    | 46032         | 30.0          | 670    | 32798         | 0.7           | 800    | 547           | 0.0           | 930    | 22            | 0.0           |
| 415    | 925           | 0.0           | 545    | 48553         | 32.5          | 675    | 28558         | 0.5           | 805    | 473           | 0.0           | 935    | 17            | 0.0           |
| 420    | 1816          | 0.0           | 550    | 51408         | 34.9          | 680    | 24782         | 0.3           | 810    | 401           | 0.0           | 940    | 13            | 0.0           |
| 425    | 3217          | 0.0           | 555    | 54711         | 37.4          | 685    | 21386         | 0.2           | 815    | 351           | 0.0           | 945    | 6             | 0.0           |
| 430    | 5520          | 0.0           | 560    | 58847         | 40.0          | 690    | 18413         | 0.1           | 820    | 307           | 0.0           | 950    | 10            | 0.0           |
| 435    | 9225          | 0.1           | 565    | 63386         | 42.4          | 695    | 15721         | 0.1           | 825    | 261           | 0.0           | 955    | 11            | 0.0           |
| 440    | 15522         | 0.2           | 570    | 68196         | 44.3          | 700    | 13432         | 0.0           | 830    | 228           | 0.0           | 960    | 8             | 0.0           |
| 445    | 27642         | 0.6           | 575    | 73613         | 46.0          | 705    | 11513         | 0.0           | 835    | 193           | 0.0           | 965    | 12            | 0.0           |
| 450    | 36602         | 0.9           | 580    | 79207         | 47.1          | 710    | 9780          | 0.0           | 840    | 174           | 0.0           | 970    | 3             | 0.0           |
| 455    | 28292         | 0.9           | 585    | 84248         | 47.0          | 715    | 8356          | 0.0           | 845    | 151           | 0.0           | 975    | 8             | 0.0           |
| 460    | 21166         | 0.9           | 590    | 88397         | 45.7          | 720    | 7161          | 0.0           | 850    | 123           | 0.0           | 980    | 2             | 0.0           |
| 465    | 19092         | 1.0           | 595    | 91428         | 43.4          | 725    | 6067          | 0.0           | 855    | 106           | 0.0           | 985    | 13            | 0.0           |
| 470    | 14951         | 0.9           | 600    | 93452         | 40.3          | 730    | 5164          | 0.0           | 860    | 95            | 0.0           | 990    | 16            | 0.0           |
| 475    | 12606         | 1.0           | 605    | 93959         | 36.4          | 735    | 4393          | 0.0           | 865    | 82            | 0.0           | 995    | 20            | 0.0           |
| 480    | 13323         | 1.3           | 610    | 93079         | 32.0          | 740    | 3694          | 0.0           | 870    | 77            | 0.0           | 1000   | 0             | 0.0           |
| 485    | 15164         | 1.8           | 615    | 90707         | 27.3          | 745    | 3157          | 0.0           | 875    | 65            | 0.0           |        |               |               |

REPORT NUMBER: SP1-2407-157-9

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: 5286.7**

**S/P: 1.22**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 0             | 0.0           | 490    | 18018         | 75.9          | 620    | 87426         | 0.4           | 750    | 2680          | 0.0           | 880    | 58            | 0.0           |
| 365    | 0             | 0.0           | 495    | 22295         | 93.2          | 625    | 83013         | 0.2           | 755    | 2287          | 0.0           | 885    | 46            | 0.0           |
| 370    | 0             | 0.0           | 500    | 26478         | 107.8         | 630    | 78077         | 0.1           | 760    | 1944          | 0.0           | 890    | 45            | 0.0           |
| 375    | 0             | 0.0           | 505    | 30524         | 118.7         | 635    | 72080         | 0.1           | 765    | 1653          | 0.0           | 895    | 41            | 0.0           |
| 380    | 0             | 0.0           | 510    | 33611         | 122.2         | 640    | 66249         | 0.1           | 770    | 1413          | 0.0           | 900    | 38            | 0.0           |
| 385    | 0             | 0.0           | 515    | 36490         | 120.8         | 645    | 59973         | 0.0           | 775    | 1198          | 0.0           | 905    | 33            | 0.0           |
| 390    | 0             | 0.0           | 520    | 38610         | 113.9         | 650    | 53972         | 0.0           | 780    | 1025          | 0.0           | 910    | 30            | 0.0           |
| 395    | 0             | 0.0           | 525    | 40511         | 104.1         | 655    | 48369         | 0.0           | 785    | 874           | 0.0           | 915    | 23            | 0.0           |
| 400    | 48            | 0.0           | 530    | 42223         | 92.4          | 660    | 42641         | 0.0           | 790    | 747           | 0.0           | 920    | 24            | 0.0           |
| 405    | 201           | 0.0           | 535    | 44137         | 80.5          | 665    | 37602         | 0.0           | 795    | 639           | 0.0           | 925    | 22            | 0.0           |
| 410    | 457           | 0.1           | 540    | 46032         | 68.2          | 670    | 32798         | 0.0           | 800    | 547           | 0.0           | 930    | 22            | 0.0           |
| 415    | 925           | 0.3           | 545    | 48553         | 57.1          | 675    | 28558         | 0.0           | 805    | 473           | 0.0           | 935    | 17            | 0.0           |
| 420    | 1816          | 1.1           | 550    | 51408         | 46.7          | 680    | 24782         | 0.0           | 810    | 401           | 0.0           | 940    | 13            | 0.0           |
| 425    | 3217          | 2.5           | 555    | 54711         | 37.4          | 685    | 21386         | 0.0           | 815    | 351           | 0.0           | 945    | 6             | 0.0           |
| 430    | 5520          | 5.9           | 560    | 58847         | 29.4          | 690    | 18413         | 0.0           | 820    | 307           | 0.0           | 950    | 10            | 0.0           |
| 435    | 9225          | 12.5          | 565    | 63386         | 22.5          | 695    | 15721         | 0.0           | 825    | 261           | 0.0           | 955    | 11            | 0.0           |
| 440    | 15522         | 26.3          | 570    | 68196         | 16.9          | 700    | 13432         | 0.0           | 830    | 228           | 0.0           | 960    | 8             | 0.0           |
| 445    | 27642         | 55.2          | 575    | 73613         | 12.4          | 705    | 11513         | 0.0           | 835    | 193           | 0.0           | 965    | 12            | 0.0           |
| 450    | 36602         | 85.4          | 580    | 79207         | 9.0           | 710    | 9780          | 0.0           | 840    | 174           | 0.0           | 970    | 3             | 0.0           |
| 455    | 28292         | 75.1          | 585    | 84248         | 6.3           | 715    | 8356          | 0.0           | 845    | 151           | 0.0           | 975    | 8             | 0.0           |
| 460    | 21166         | 63.2          | 590    | 88397         | 4.4           | 720    | 7161          | 0.0           | 850    | 123           | 0.0           | 980    | 2             | 0.0           |
| 465    | 19092         | 63.2          | 595    | 91428         | 3.0           | 725    | 6067          | 0.0           | 855    | 106           | 0.0           | 985    | 13            | 0.0           |
| 470    | 14951         | 54.2          | 600    | 93452         | 2.0           | 730    | 5164          | 0.0           | 860    | 95            | 0.0           | 990    | 16            | 0.0           |
| 475    | 12606         | 48.8          | 605    | 93959         | 1.3           | 735    | 4393          | 0.0           | 865    | 82            | 0.0           | 995    | 20            | 0.0           |
| 480    | 13323         | 54.2          | 610    | 93079         | 0.9           | 740    | 3694          | 0.0           | 870    | 77            | 0.0           | 1000   | 0             | 0.0           |
| 485    | 15164         | 63.3          | 615    | 90707         | 0.5           | 745    | 3157          | 0.0           | 875    | 65            | 0.0           |        |               |               |



REPORT NUMBER: SP1-2407-157-9

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 9797**

**M/P: 2.26**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 0             | 0.0           | 490    | 18018         | 27.7          | 620    | 87426         | 1.1           | 750    | 2680          | 0.0           | 880    | 58            | 0.0           |
| 365    | 0             | 0.0           | 495    | 22295         | 36.0          | 625    | 83013         | 0.7           | 755    | 2287          | 0.0           | 885    | 46            | 0.0           |
| 370    | 0             | 0.0           | 500    | 26478         | 44.2          | 630    | 78077         | 0.4           | 760    | 1944          | 0.0           | 890    | 45            | 0.0           |
| 375    | 0             | 0.0           | 505    | 30524         | 51.8          | 635    | 72080         | 0.3           | 765    | 1653          | 0.0           | 895    | 41            | 0.0           |
| 380    | 0             | 0.0           | 510    | 33611         | 57.0          | 640    | 66249         | 0.2           | 770    | 1413          | 0.0           | 900    | 38            | 0.0           |
| 385    | 0             | 0.0           | 515    | 36490         | 60.5          | 645    | 59973         | 0.1           | 775    | 1198          | 0.0           | 905    | 33            | 0.0           |
| 390    | 0             | 0.0           | 520    | 38610         | 61.4          | 650    | 53972         | 0.1           | 780    | 1025          | 0.0           | 910    | 30            | 0.0           |
| 395    | 0             | 0.0           | 525    | 40511         | 60.6          | 655    | 48369         | 0.0           | 785    | 874           | 0.0           | 915    | 23            | 0.0           |
| 400    | 48            | 0.0           | 530    | 42223         | 58.2          | 660    | 42641         | 0.0           | 790    | 747           | 0.0           | 920    | 24            | 0.0           |
| 405    | 201           | 0.0           | 535    | 44137         | 55.0          | 665    | 37602         | 0.0           | 795    | 639           | 0.0           | 925    | 22            | 0.0           |
| 410    | 457           | 0.0           | 540    | 46032         | 50.9          | 670    | 32798         | 0.0           | 800    | 547           | 0.0           | 930    | 22            | 0.0           |
| 415    | 925           | 0.1           | 545    | 48553         | 46.6          | 675    | 28558         | 0.0           | 805    | 473           | 0.0           | 935    | 17            | 0.0           |
| 420    | 1816          | 0.3           | 550    | 51408         | 42.0          | 680    | 24782         | 0.0           | 810    | 401           | 0.0           | 940    | 13            | 0.0           |
| 425    | 3217          | 0.8           | 555    | 54711         | 37.4          | 685    | 21386         | 0.0           | 815    | 351           | 0.0           | 945    | 6             | 0.0           |
| 430    | 5520          | 1.9           | 560    | 58847         | 32.9          | 690    | 18413         | 0.0           | 820    | 307           | 0.0           | 950    | 10            | 0.0           |
| 435    | 9225          | 4.1           | 565    | 63386         | 28.4          | 695    | 15721         | 0.0           | 825    | 261           | 0.0           | 955    | 11            | 0.0           |
| 440    | 15522         | 8.7           | 570    | 68196         | 24.1          | 700    | 13432         | 0.0           | 830    | 228           | 0.0           | 960    | 8             | 0.0           |
| 445    | 27642         | 18.5          | 575    | 73613         | 20.0          | 705    | 11513         | 0.0           | 835    | 193           | 0.0           | 965    | 12            | 0.0           |
| 450    | 36602         | 28.3          | 580    | 79207         | 16.3          | 710    | 9780          | 0.0           | 840    | 174           | 0.0           | 970    | 3             | 0.0           |
| 455    | 28292         | 24.7          | 585    | 84248         | 12.9          | 715    | 8356          | 0.0           | 845    | 151           | 0.0           | 975    | 8             | 0.0           |
| 460    | 21166         | 20.4          | 590    | 88397         | 9.8           | 720    | 7161          | 0.0           | 850    | 123           | 0.0           | 980    | 2             | 0.0           |
| 465    | 19092         | 20.1          | 595    | 91428         | 7.3           | 725    | 6067          | 0.0           | 855    | 106           | 0.0           | 985    | 13            | 0.0           |
| 470    | 14951         | 17.2          | 600    | 93452         | 5.3           | 730    | 5164          | 0.0           | 860    | 95            | 0.0           | 990    | 16            | 0.0           |
| 475    | 12606         | 15.7          | 605    | 93959         | 3.7           | 735    | 4393          | 0.0           | 865    | 82            | 0.0           | 995    | 20            | 0.0           |
| 480    | 13323         | 18.0          | 610    | 93079         | 2.5           | 740    | 3694          | 0.0           | 870    | 77            | 0.0           | 1000   | 0             | 0.0           |
| 485    | 15164         | 21.9          | 615    | 90707         | 1.7           | 745    | 3157          | 0.0           | 875    | 65            | 0.0           |        |               |               |

**Summary**

$R_f = 84.7$   
 $R_g = 94.6$   
 CIE  $R_a = 80.9$   
 $R_9 = -1.5$



**Color Vector Graphics**



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 |            |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)