

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P437253

Luminaire Tested: **ISC-SA1B-830-U-SL4**

Issue Date: 12/9/2020

Test Information

Test Method: LM-79-08
Report Number: P437253
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-074-18)
Test Lab: INNOVATION CENTER
Issue Date: 12/9/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: ISC-SA1B-830-U-SL4
Description: IMPACT ELITE LED CYLINDER LUMINAIRE
(1) 80 CRI, 3000K, 450mA LIGHTSQUARE WITH 16 LEDS AND TYPE IV SPILL LIGHT
ELIMINATOR OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2660 lumens
Efficiency: N/A
Efficacy: 104.7 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G1


Input Watts (W): 25.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P437253
 CATALOG NUMBER: ISC-SA1B-830-U-SL4

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.8 fc
 Type IV - Short - N/A

REPORT NUMBER: P437253
CATALOG NUMBER: ISC-SA1B-830-U-SL4

Luminous Intensity Polar Plot



— Vertical Plane Through 36-Deg Lateral - - - Horizontal Cone Through 75-Deg Vertical

REPORT NUMBER: P437253
 CATALOG NUMBER: ISC-SA1B-830-U-SL4


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 392.6 | 0.0 | 392.6 |
| | % Fixture | 14.8 | 0.0 | 14.8 |
| Street Side | Lumens | 2267.4 | 0.0 | 2267.4 |
| | % Fixture | 85.2 | 0.0 | 85.2 |
| Total | Lumens | 2660.0 | 0.0 | 2660.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 42.8 | 1.6 |
| 10°-20° | 110.7 | 4.2 |
| 20°-30° | 171.2 | 6.4 |
| 30°-40° | 247.9 | 9.3 |
| 40°-50° | 358.5 | 13.5 |
| 50°-60° | 497.3 | 18.7 |
| 60°-70° | 628.0 | 23.6 |
| 70°-80° | 539.4 | 20.3 |
| 80°-90° | 64.3 | 2.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 2660.0 | 100.0 |
| 0°-180° | 2660.0 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P437253


CATALOG NUMBER: ISC-SA1B-830-U-SL4

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 213.6 | 8.0 | | | |
| FM (30°-60°) | 915.5 | 34.4 | | | |
| FH (60°-80°) | 1080.0 | 40.6 | | | G1/1800 |
| FVH (80°-90°) | 58.3 | 2.2 | | | G1/100 |
| BL (0°-30°) | 111.0 | 4.2 | B1/500 | | |
| BM (30°-60°) | 188.2 | 7.1 | B0/220 | | |
| BH (60°-80°) | 87.4 | 3.3 | B0/110 | | G0/110 |
| BVH (80°-90°) | 5.9 | 0.2 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G1

Type IV Short





REPORT NUMBER: P437253
 CATALOG NUMBER: ISC-SA1B-830-U-SL4

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 36° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|-------|
| 0° | 485.3 | 485.3 | 485.3 | 485.3 | 485.3 | 485.3 | 485.3 | 485.3 | 485.3 | 485.3 | 485.3 |
| 2.5° | 499.2 | 499.2 | 499.2 | 498.2 | 496.2 | 495.2 | 493.2 | 491.3 | 490.3 | 486.3 | 485.3 |
| 5° | 499.2 | 500.2 | 499.2 | 498.2 | 496.2 | 494.2 | 492.3 | 488.3 | 485.3 | 480.3 | 475.4 |
| 7.5° | 494.2 | 495.2 | 495.2 | 494.2 | 492.3 | 491.3 | 489.3 | 484.3 | 480.3 | 473.4 | 465.5 |
| 10° | 486.3 | 488.3 | 488.3 | 489.3 | 490.3 | 490.3 | 488.3 | 484.3 | 478.4 | 470.4 | 457.5 |
| 12.5° | 476.4 | 481.3 | 484.3 | 487.3 | 491.3 | 491.3 | 492.3 | 486.3 | 481.3 | 470.4 | 457.5 |
| 15° | 473.4 | 476.4 | 482.3 | 491.3 | 495.2 | 492.3 | 496.2 | 493.2 | 487.3 | 476.4 | 460.5 |
| 17.5° | 472.4 | 475.4 | 485.3 | 496.2 | 502.2 | 504.2 | 504.2 | 500.2 | 493.2 | 482.3 | 462.5 |
| 20° | 476.4 | 480.3 | 493.2 | 507.1 | 516.1 | 516.1 | 515.1 | 510.1 | 501.2 | 488.3 | 466.4 |
| 22.5° | 489.3 | 490.3 | 505.2 | 522.0 | 529.0 | 527.0 | 529.0 | 520.0 | 510.1 | 497.2 | 471.4 |
| 25° | 506.1 | 508.1 | 520.0 | 539.9 | 543.9 | 544.9 | 541.9 | 531.9 | 521.0 | 508.1 | 477.4 |
| 27.5° | 529.0 | 531.9 | 540.9 | 559.7 | 562.7 | 560.7 | 556.8 | 544.9 | 533.9 | 522.0 | 489.3 |
| 30° | 555.8 | 557.8 | 568.7 | 576.6 | 579.6 | 577.6 | 574.6 | 561.7 | 552.8 | 541.9 | 507.1 |
| 32.5° | 581.6 | 582.6 | 594.5 | 602.4 | 597.4 | 597.4 | 593.5 | 580.6 | 573.6 | 571.6 | 530.0 |
| 35° | 608.4 | 610.4 | 621.3 | 625.2 | 617.3 | 618.3 | 617.3 | 606.4 | 608.4 | 612.3 | 564.7 |
| 37.5° | 633.2 | 636.2 | 649.1 | 650.0 | 647.1 | 644.1 | 647.1 | 641.1 | 645.1 | 661.0 | 605.4 |
| 40° | 655.0 | 659.0 | 674.9 | 677.8 | 676.8 | 676.8 | 678.8 | 677.8 | 692.7 | 718.5 | 655.0 |
| 42.5° | 672.9 | 677.8 | 696.7 | 704.6 | 710.6 | 713.6 | 720.5 | 722.5 | 744.3 | 786.0 | 712.6 |
| 45° | 690.7 | 695.7 | 721.5 | 734.4 | 748.3 | 749.3 | 763.2 | 770.1 | 810.8 | 848.5 | 775.1 |
| 47.5° | 711.6 | 717.5 | 741.4 | 767.2 | 783.0 | 786.0 | 811.8 | 825.7 | 875.3 | 924.0 | 833.7 |
| 50° | 740.4 | 742.3 | 761.2 | 804.9 | 824.7 | 829.7 | 858.5 | 887.2 | 941.8 | 990.5 | 885.3 |
| 52.5° | 776.1 | 774.1 | 783.0 | 838.6 | 869.4 | 876.3 | 923.0 | 951.8 | 1017.3 | 1061.9 | 925.9 |
| 55° | 805.9 | 803.9 | 816.8 | 877.3 | 925.9 | 927.9 | 983.5 | 1011.3 | 1086.7 | 1114.5 | 960.7 |
| 57.5° | 840.6 | 836.6 | 849.5 | 924.0 | 990.5 | 991.4 | 1056.0 | 1087.7 | 1149.2 | 1161.2 | 983.5 |
| 60° | 869.4 | 869.4 | 886.2 | 969.6 | 1061.9 | 1072.8 | 1131.4 | 1156.2 | 1209.8 | 1194.9 | 994.4 |
| 62.5° | 896.2 | 901.1 | 925.0 | 1030.2 | 1146.3 | 1155.2 | 1214.7 | 1224.7 | 1272.3 | 1220.7 | 982.5 |
| 65° | 927.9 | 935.9 | 981.5 | 1102.6 | 1246.5 | 1252.5 | 1302.1 | 1316.0 | 1334.8 | 1219.7 | 930.9 |
| 67.5° | 961.7 | 974.6 | 1035.1 | 1184.0 | 1356.7 | 1372.5 | 1426.1 | 1412.2 | 1376.5 | 1181.0 | 822.7 |
| 70° | 1007.3 | 1023.2 | 1109.5 | 1292.2 | 1507.5 | 1527.4 | 1597.8 | 1512.5 | 1354.7 | 1043.1 | 666.9 |
| 72.5° | 1042.1 | 1062.9 | 1181.0 | 1432.1 | 1712.0 | 1742.7 | 1725.9 | 1514.5 | 1214.7 | 831.7 | 446.6 |
| 75° | 914.0 | 945.8 | 1124.4 | 1454.9 | 1799.3 | 1813.2 | 1632.6 | 1280.2 | 860.4 | 429.7 | 192.5 |
| 77.5° | 667.9 | 665.9 | 821.7 | 1130.4 | 1474.8 | 1438.0 | 1238.6 | 832.7 | 408.9 | 155.8 | 97.3 |
| 80° | 335.4 | 322.5 | 444.6 | 602.4 | 795.9 | 820.7 | 732.4 | 432.7 | 161.8 | 83.4 | 58.6 |
| 82.5° | 124.1 | 127.0 | 162.8 | 246.1 | 400.0 | 405.9 | 295.7 | 183.6 | 88.3 | 43.7 | 30.8 |
| 85° | 47.6 | 49.6 | 53.6 | 53.6 | 74.4 | 82.4 | 76.4 | 73.4 | 29.8 | 14.9 | 16.9 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 1.0 | 1.0 | 1.0 | 1.0 | 1.0 | 1.0 | 1.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P437253
 CATALOG NUMBER: ISC-SA1B-830-U-SL4

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 485.3 | 485.3 | 485.3 | 485.3 | 485.3 | 485.3 | 485.3 | 485.3 | 485.3 | 485.3 | 485.3 |
| 2.5° | 482.3 | 480.3 | 476.4 | 469.4 | 465.5 | 462.5 | 458.5 | 454.5 | 453.5 | 452.6 | 457.5 |
| 5° | 470.4 | 467.4 | 457.5 | 448.6 | 438.7 | 430.7 | 422.8 | 415.8 | 411.9 | 410.9 | 412.9 |
| 7.5° | 458.5 | 454.5 | 439.7 | 421.8 | 404.9 | 391.0 | 377.1 | 370.2 | 359.3 | 359.3 | 360.3 |
| 10° | 451.6 | 444.6 | 423.8 | 397.0 | 375.1 | 350.3 | 333.5 | 316.6 | 309.6 | 304.7 | 302.7 |
| 12.5° | 447.6 | 436.7 | 408.9 | 379.1 | 345.4 | 312.6 | 289.8 | 269.0 | 258.0 | 250.1 | 250.1 |
| 15° | 448.6 | 436.7 | 399.0 | 360.3 | 316.6 | 276.9 | 248.1 | 225.3 | 211.4 | 203.5 | 201.5 |
| 17.5° | 447.6 | 432.7 | 387.1 | 336.4 | 287.8 | 246.1 | 211.4 | 187.6 | 173.7 | 168.7 | 167.7 |
| 20° | 449.6 | 429.7 | 373.2 | 314.6 | 260.0 | 215.4 | 179.6 | 157.8 | 149.9 | 145.9 | 144.9 |
| 22.5° | 450.6 | 423.8 | 359.3 | 290.8 | 230.2 | 186.6 | 156.8 | 141.9 | 136.0 | 133.0 | 132.0 |
| 25° | 452.6 | 422.8 | 343.4 | 269.0 | 205.4 | 164.7 | 141.9 | 129.0 | 126.0 | 124.1 | 124.1 |
| 27.5° | 460.5 | 422.8 | 329.5 | 241.2 | 179.6 | 146.9 | 129.0 | 121.1 | 119.1 | 118.1 | 118.1 |
| 30° | 470.4 | 424.8 | 316.6 | 218.3 | 159.8 | 133.0 | 120.1 | 114.1 | 113.1 | 112.1 | 112.1 |
| 32.5° | 487.3 | 431.7 | 301.7 | 196.5 | 142.9 | 123.1 | 113.1 | 108.2 | 106.2 | 106.2 | 106.2 |
| 35° | 510.1 | 443.6 | 286.8 | 176.7 | 129.0 | 113.1 | 106.2 | 101.2 | 100.2 | 101.2 | 101.2 |
| 37.5° | 542.9 | 457.5 | 273.9 | 158.8 | 118.1 | 105.2 | 99.2 | 96.3 | 95.3 | 95.3 | 96.3 |
| 40° | 583.6 | 482.3 | 261.0 | 144.9 | 110.2 | 98.3 | 94.3 | 91.3 | 90.3 | 91.3 | 91.3 |
| 42.5° | 628.2 | 509.1 | 250.1 | 131.0 | 102.2 | 93.3 | 88.3 | 86.3 | 85.3 | 86.3 | 87.3 |
| 45° | 677.8 | 536.9 | 241.2 | 121.1 | 96.3 | 88.3 | 84.4 | 83.4 | 82.4 | 82.4 | 83.4 |
| 47.5° | 719.5 | 566.7 | 234.2 | 114.1 | 91.3 | 84.4 | 81.4 | 79.4 | 78.4 | 77.4 | 78.4 |
| 50° | 758.2 | 589.5 | 232.2 | 110.2 | 88.3 | 80.4 | 77.4 | 75.4 | 74.4 | 73.4 | 74.4 |
| 52.5° | 787.0 | 601.4 | 232.2 | 107.2 | 85.3 | 77.4 | 74.4 | 72.4 | 71.5 | 69.5 | 70.5 |
| 55° | 806.9 | 607.4 | 229.3 | 105.2 | 82.4 | 74.4 | 70.5 | 69.5 | 68.5 | 66.5 | 66.5 |
| 57.5° | 818.8 | 606.4 | 218.3 | 104.2 | 81.4 | 70.5 | 67.5 | 66.5 | 65.5 | 63.5 | 63.5 |
| 60° | 816.8 | 587.5 | 198.5 | 100.2 | 79.4 | 67.5 | 63.5 | 63.5 | 63.5 | 61.5 | 61.5 |
| 62.5° | 788.0 | 534.9 | 165.7 | 94.3 | 77.4 | 64.5 | 59.5 | 61.5 | 62.5 | 60.5 | 60.5 |
| 65° | 710.6 | 454.5 | 137.0 | 86.3 | 72.4 | 61.5 | 56.6 | 59.5 | 61.5 | 60.5 | 59.5 |
| 67.5° | 598.4 | 360.3 | 113.1 | 78.4 | 67.5 | 57.6 | 52.6 | 56.6 | 57.6 | 57.6 | 57.6 |
| 70° | 462.5 | 259.0 | 93.3 | 68.5 | 60.5 | 51.6 | 47.6 | 49.6 | 50.6 | 50.6 | 51.6 |
| 72.5° | 273.9 | 154.8 | 76.4 | 58.6 | 51.6 | 44.7 | 41.7 | 42.7 | 41.7 | 41.7 | 41.7 |
| 75° | 135.0 | 96.3 | 61.5 | 49.6 | 43.7 | 37.7 | 34.7 | 32.8 | 32.8 | 32.8 | 31.8 |
| 77.5° | 82.4 | 71.5 | 50.6 | 39.7 | 34.7 | 28.8 | 26.8 | 24.8 | 24.8 | 24.8 | 24.8 |
| 80° | 58.6 | 55.6 | 38.7 | 29.8 | 23.8 | 20.8 | 19.8 | 18.9 | 18.9 | 17.9 | 17.9 |
| 82.5° | 36.7 | 41.7 | 28.8 | 19.8 | 15.9 | 14.9 | 13.9 | 12.9 | 11.9 | 10.9 | 10.9 |
| 85° | 20.8 | 26.8 | 16.9 | 10.9 | 8.9 | 6.9 | 6.0 | 6.0 | 5.0 | 5.0 | 4.0 |
| 87.5° | 1.0 | 2.0 | 2.0 | 2.0 | 2.0 | 1.0 | 1.0 | 1.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW EDISON

Report Number: SP1-2408-195-9

Test Date: 08/07/2024

Luminaire Tested: GALN-SB1A-830-U-5WQ

Data in this report applies to families of products including GALN-SB1A-830-U-5WQ.

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2408-195-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/07/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: MCGRAW EDISON
 Catalog Number: **GALN-SB1A-830-U-5WQ**
 Description: GALLEON AREA AND ROADWAY LUMINAIRE. (1) 80 CRI, 3000K, 350MA HIGH DENSITY LIGHTSQUARE WITH 26 LEDS AND TYPE V WIDE OPTICS

Spectral Parameters

CCT (K): 3050
 CIE u': 0.2476
 CIE v': 0.5251
 Duv: 0.0034
 CIE x: 0.4383
 CIE y: 0.4131
 CIE z: 0.1487
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 581
 Purity: 55.55201
 Rf: 81.5
 Rg: 99.2

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 81.0 | | |
| R1: | 79.6 | R9: | 7.1 |
| R2: | 85.6 | R10: | 67.0 |
| R3: | 92.0 | R11: | 82.7 |
| R4: | 82.6 | R12: | 63.2 |
| R5: | 78.9 | R13: | 80.3 |
| R6: | 81.7 | R14: | 95.0 |
| R7: | 85.2 | R15: | 71.7 |
| R8: | 62.0 | | |



Test Conditions

Stabilization Time: 20M
 Operation Time: 1H 20M
 Sphere Temperature (°C): 24.2

REPORT NUMBER: SP1-2408-195-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2408-195-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2408-195-9

Photopic Flux vs. Wavelength



Photopic Lumens: NR

| λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) |
|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|
| 360 | 0 | NR | 490 | 168 | NR | 620 | 940 | NR | 750 | 35 | NR | 880 | 1 | NR |
| 365 | 0 | NR | 495 | 233 | NR | 625 | 897 | NR | 755 | 30 | NR | 885 | 1 | NR |
| 370 | 0 | NR | 500 | 300 | NR | 630 | 847 | NR | 760 | 26 | NR | 890 | 1 | NR |
| 375 | 0 | NR | 505 | 372 | NR | 635 | 790 | NR | 765 | 22 | NR | 895 | 1 | NR |
| 380 | 0 | NR | 510 | 430 | NR | 640 | 730 | NR | 770 | 19 | NR | 900 | 1 | NR |
| 385 | 0 | NR | 515 | 483 | NR | 645 | 668 | NR | 775 | 16 | NR | 905 | 1 | NR |
| 390 | 0 | NR | 520 | 524 | NR | 650 | 605 | NR | 780 | 14 | NR | 910 | 0 | NR |
| 395 | 2 | NR | 525 | 555 | NR | 655 | 545 | NR | 785 | 12 | NR | 915 | 0 | NR |
| 400 | 4 | NR | 530 | 581 | NR | 660 | 485 | NR | 790 | 10 | NR | 920 | 0 | NR |
| 405 | 7 | NR | 535 | 604 | NR | 665 | 430 | NR | 795 | 9 | NR | 925 | 0 | NR |
| 410 | 17 | NR | 540 | 623 | NR | 670 | 378 | NR | 800 | 8 | NR | 930 | 0 | NR |
| 415 | 34 | NR | 545 | 645 | NR | 675 | 331 | NR | 805 | 7 | NR | 935 | 0 | NR |
| 420 | 68 | NR | 550 | 667 | NR | 680 | 290 | NR | 810 | 6 | NR | 940 | 0 | NR |
| 425 | 128 | NR | 555 | 693 | NR | 685 | 251 | NR | 815 | 5 | NR | 945 | 0 | NR |
| 430 | 214 | NR | 560 | 719 | NR | 690 | 218 | NR | 820 | 4 | NR | 950 | 0 | NR |
| 435 | 339 | NR | 565 | 754 | NR | 695 | 188 | NR | 825 | 4 | NR | 955 | 0 | NR |
| 440 | 507 | NR | 570 | 791 | NR | 700 | 162 | NR | 830 | 3 | NR | 960 | 0 | NR |
| 445 | 573 | NR | 575 | 830 | NR | 705 | 139 | NR | 835 | 3 | NR | 965 | 0 | NR |
| 450 | 356 | NR | 580 | 873 | NR | 710 | 119 | NR | 840 | 3 | NR | 970 | 0 | NR |
| 455 | 217 | NR | 585 | 913 | NR | 715 | 102 | NR | 845 | 2 | NR | 975 | 0 | NR |
| 460 | 168 | NR | 590 | 948 | NR | 720 | 88 | NR | 850 | 2 | NR | 980 | 0 | NR |
| 465 | 113 | NR | 595 | 974 | NR | 725 | 76 | NR | 855 | 2 | NR | 985 | 0 | NR |
| 470 | 85 | NR | 600 | 994 | NR | 730 | 65 | NR | 860 | 1 | NR | 990 | 0 | NR |
| 475 | 85 | NR | 605 | 998 | NR | 735 | 55 | NR | 865 | 1 | NR | 995 | 0 | NR |
| 480 | 94 | NR | 610 | 994 | NR | 740 | 47 | NR | 870 | 1 | NR | 1000 | 0 | NR |
| 485 | 120 | NR | 615 | 973 | NR | 745 | 41 | NR | 875 | 1 | NR | | | |

REPORT NUMBER: SP1-2408-195-9

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.27

| λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) |
|----------------|--------------------------|----------------------|----------------|--------------------------|----------------------|----------------|--------------------------|----------------------|----------------|--------------------------|----------------------|----------------|--------------------------|----------------------|
| 360 | 0 | NR | 490 | 168 | NR | 620 | 940 | NR | 750 | 35 | NR | 880 | 1 | NR |
| 365 | 0 | NR | 495 | 233 | NR | 625 | 897 | NR | 755 | 30 | NR | 885 | 1 | NR |
| 370 | 0 | NR | 500 | 300 | NR | 630 | 847 | NR | 760 | 26 | NR | 890 | 1 | NR |
| 375 | 0 | NR | 505 | 372 | NR | 635 | 790 | NR | 765 | 22 | NR | 895 | 1 | NR |
| 380 | 0 | NR | 510 | 430 | NR | 640 | 730 | NR | 770 | 19 | NR | 900 | 1 | NR |
| 385 | 0 | NR | 515 | 483 | NR | 645 | 668 | NR | 775 | 16 | NR | 905 | 1 | NR |
| 390 | 0 | NR | 520 | 524 | NR | 650 | 605 | NR | 780 | 14 | NR | 910 | 0 | NR |
| 395 | 2 | NR | 525 | 555 | NR | 655 | 545 | NR | 785 | 12 | NR | 915 | 0 | NR |
| 400 | 4 | NR | 530 | 581 | NR | 660 | 485 | NR | 790 | 10 | NR | 920 | 0 | NR |
| 405 | 7 | NR | 535 | 604 | NR | 665 | 430 | NR | 795 | 9 | NR | 925 | 0 | NR |
| 410 | 17 | NR | 540 | 623 | NR | 670 | 378 | NR | 800 | 8 | NR | 930 | 0 | NR |
| 415 | 34 | NR | 545 | 645 | NR | 675 | 331 | NR | 805 | 7 | NR | 935 | 0 | NR |
| 420 | 68 | NR | 550 | 667 | NR | 680 | 290 | NR | 810 | 6 | NR | 940 | 0 | NR |
| 425 | 128 | NR | 555 | 693 | NR | 685 | 251 | NR | 815 | 5 | NR | 945 | 0 | NR |
| 430 | 214 | NR | 560 | 719 | NR | 690 | 218 | NR | 820 | 4 | NR | 950 | 0 | NR |
| 435 | 339 | NR | 565 | 754 | NR | 695 | 188 | NR | 825 | 4 | NR | 955 | 0 | NR |
| 440 | 507 | NR | 570 | 791 | NR | 700 | 162 | NR | 830 | 3 | NR | 960 | 0 | NR |
| 445 | 573 | NR | 575 | 830 | NR | 705 | 139 | NR | 835 | 3 | NR | 965 | 0 | NR |
| 450 | 356 | NR | 580 | 873 | NR | 710 | 119 | NR | 840 | 3 | NR | 970 | 0 | NR |
| 455 | 217 | NR | 585 | 913 | NR | 715 | 102 | NR | 845 | 2 | NR | 975 | 0 | NR |
| 460 | 168 | NR | 590 | 948 | NR | 720 | 88 | NR | 850 | 2 | NR | 980 | 0 | NR |
| 465 | 113 | NR | 595 | 974 | NR | 725 | 76 | NR | 855 | 2 | NR | 985 | 0 | NR |
| 470 | 85 | NR | 600 | 994 | NR | 730 | 65 | NR | 860 | 1 | NR | 990 | 0 | NR |
| 475 | 85 | NR | 605 | 998 | NR | 735 | 55 | NR | 865 | 1 | NR | 995 | 0 | NR |
| 480 | 94 | NR | 610 | 994 | NR | 740 | 47 | NR | 870 | 1 | NR | 1000 | 0 | NR |
| 485 | 120 | NR | 615 | 973 | NR | 745 | 41 | NR | 875 | 1 | NR | | | |

REPORT NUMBER: SP1-2408-195-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.32

| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 168 | NR | 620 | 940 | NR | 750 | 35 | NR | 880 | 1 | NR |
| 365 | 0 | NR | 495 | 233 | NR | 625 | 897 | NR | 755 | 30 | NR | 885 | 1 | NR |
| 370 | 0 | NR | 500 | 300 | NR | 630 | 847 | NR | 760 | 26 | NR | 890 | 1 | NR |
| 375 | 0 | NR | 505 | 372 | NR | 635 | 790 | NR | 765 | 22 | NR | 895 | 1 | NR |
| 380 | 0 | NR | 510 | 430 | NR | 640 | 730 | NR | 770 | 19 | NR | 900 | 1 | NR |
| 385 | 0 | NR | 515 | 483 | NR | 645 | 668 | NR | 775 | 16 | NR | 905 | 1 | NR |
| 390 | 0 | NR | 520 | 524 | NR | 650 | 605 | NR | 780 | 14 | NR | 910 | 0 | NR |
| 395 | 2 | NR | 525 | 555 | NR | 655 | 545 | NR | 785 | 12 | NR | 915 | 0 | NR |
| 400 | 4 | NR | 530 | 581 | NR | 660 | 485 | NR | 790 | 10 | NR | 920 | 0 | NR |
| 405 | 7 | NR | 535 | 604 | NR | 665 | 430 | NR | 795 | 9 | NR | 925 | 0 | NR |
| 410 | 17 | NR | 540 | 623 | NR | 670 | 378 | NR | 800 | 8 | NR | 930 | 0 | NR |
| 415 | 34 | NR | 545 | 645 | NR | 675 | 331 | NR | 805 | 7 | NR | 935 | 0 | NR |
| 420 | 68 | NR | 550 | 667 | NR | 680 | 290 | NR | 810 | 6 | NR | 940 | 0 | NR |
| 425 | 128 | NR | 555 | 693 | NR | 685 | 251 | NR | 815 | 5 | NR | 945 | 0 | NR |
| 430 | 214 | NR | 560 | 719 | NR | 690 | 218 | NR | 820 | 4 | NR | 950 | 0 | NR |
| 435 | 339 | NR | 565 | 754 | NR | 695 | 188 | NR | 825 | 4 | NR | 955 | 0 | NR |
| 440 | 507 | NR | 570 | 791 | NR | 700 | 162 | NR | 830 | 3 | NR | 960 | 0 | NR |
| 445 | 573 | NR | 575 | 830 | NR | 705 | 139 | NR | 835 | 3 | NR | 965 | 0 | NR |
| 450 | 356 | NR | 580 | 873 | NR | 710 | 119 | NR | 840 | 3 | NR | 970 | 0 | NR |
| 455 | 217 | NR | 585 | 913 | NR | 715 | 102 | NR | 845 | 2 | NR | 975 | 0 | NR |
| 460 | 168 | NR | 590 | 948 | NR | 720 | 88 | NR | 850 | 2 | NR | 980 | 0 | NR |
| 465 | 113 | NR | 595 | 974 | NR | 725 | 76 | NR | 855 | 2 | NR | 985 | 0 | NR |
| 470 | 85 | NR | 600 | 994 | NR | 730 | 65 | NR | 860 | 1 | NR | 990 | 0 | NR |
| 475 | 85 | NR | 605 | 998 | NR | 735 | 55 | NR | 865 | 1 | NR | 995 | 0 | NR |
| 480 | 94 | NR | 610 | 994 | NR | 740 | 47 | NR | 870 | 1 | NR | 1000 | 0 | NR |
| 485 | 120 | NR | 615 | 973 | NR | 745 | 41 | NR | 875 | 1 | NR | | | |

Summary

$R_f = 81.5$
 $R_g = 99.2$
 $CIE R_a = 81.0$
 $R_9 = 7.1$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 74 | CES51 = 89 | CES76 = 70 |
| CES02 = 63 | CES27 = 88 | CES52 = 92 | CES77 = 86 |
| CES03 = 31 | CES28 = 89 | CES53 = 81 | CES78 = 72 |
| CES04 = 70 | CES29 = 67 | CES54 = 87 | CES79 = 90 |
| CES05 = 50 | CES30 = 68 | CES55 = 85 | CES80 = 88 |
| CES06 = 51 | CES31 = 71 | CES56 = 78 | CES81 = 78 |
| CES07 = 42 | CES32 = 70 | CES57 = 76 | CES82 = 95 |
| CES08 = 41 | CES33 = 71 | CES58 = 78 | CES83 = 90 |
| CES09 = 29 | CES34 = 82 | CES59 = 92 | CES84 = 94 |
| CES10 = 76 | CES35 = 90 | CES60 = 95 | CES85 = 86 |
| CES11 = 59 | CES36 = 93 | CES61 = 93 | CES86 = 72 |
| CES12 = 65 | CES37 = 87 | CES62 = 83 | CES87 = 85 |
| CES13 = 43 | CES38 = 75 | CES63 = 77 | CES88 = 83 |
| CES14 = 74 | CES39 = 94 | CES64 = 83 | CES89 = 75 |
| CES15 = 71 | CES40 = 89 | CES65 = 77 | CES90 = 81 |
| CES16 = 47 | CES41 = 85 | CES66 = 80 | CES91 = 96 |
| CES17 = 50 | CES42 = 86 | CES67 = 79 | CES92 = 73 |
| CES18 = 56 | CES43 = 81 | CES68 = 84 | CES93 = 84 |
| CES19 = 72 | CES44 = 99 | CES69 = 91 | CES94 = 64 |
| CES20 = 66 | CES45 = 87 | CES70 = 78 | CES95 = 80 |
| CES21 = 87 | CES46 = 82 | CES71 = 76 | CES96 = 84 |
| CES22 = 79 | CES47 = 77 | CES72 = 92 | CES97 = 87 |
| CES23 = 92 | CES48 = 71 | CES73 = 71 | CES98 = 81 |
| CES24 = 91 | CES49 = 81 | CES74 = 93 | CES99 = 74 |
| CES25 = 72 | CES50 = 89 | CES75 = 74 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)