

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P334407

Luminaire Tested: **S125RDS-S850D830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P334407
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-27)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDS-S850D830-4F0-1E-UDD-F
Description: DEFINE 5 REGRESSED DIRECT LED LUMINAIRE, FLUSH SATIN WHITE DIFFUSER
PENDANT/SURFACE/WALL MOUNT, 850 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2948.4 lumens
Efficiency: N/A
Efficacy: 112.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 26.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P334407
CATALOG NUMBER: S125RDS-S850D830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P334407

CATALOG NUMBER: S125RDS-S850D830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	105	101	97	107	103	99	96	99	96	93		95	92	90		91	89	87	85
2	100	92	86	80	98	90	84	79	87	82	78		84	79	76		81	77	74	72
3	92	82	74	68	89	80	73	67	77	71	66		74	69	65		72	67	64	61
4	84	73	64	58	82	71	64	57	69	62	57		67	61	56		64	59	55	53
5	78	65	57	50	76	64	56	50	62	55	49		60	54	49		58	53	48	46
6	72	59	50	44	70	58	50	44	56	49	44		55	48	43		53	47	43	41
7	67	54	45	39	65	53	45	39	51	44	39		50	43	39		49	43	38	36
8	62	49	41	35	61	48	41	35	47	40	35		46	39	35		45	39	34	33
9	58	45	37	32	57	45	37	32	44	37	32		42	36	31		41	36	31	29
10	55	42	34	29	54	41	34	29	40	34	29		39	33	29		39	33	29	27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8059	8059	8059
5°	8078	7986	8035
10°	8017	7912	7912
15°	7922	7751	7688
20°	7799	7527	7436
25°	7657	7308	7147
30°	7479	7050	6825
35°	7298	6784	6465
40°	7128	6508	6111
45°	6921	6198	5725
50°	6715	5862	5322
55°	6474	5540	4892
60°	6234	5150	4432
65°	5949	4696	3903
70°	5623	4130	3363
75°	5175	3481	2800
80°	4556	2734	2351
85°	3838	2238	2097



TEST NUMBER: P334407

CATALOG NUMBER: S125RDS-S850D830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.5	4.0
10°-20°	328.2	11.1
20°-30°	475.9	16.1
30°-40°	542.2	18.4
40°-50°	528.5	17.9
50°-60°	444.8	15.1
60°-70°	311.7	10.6
70°-80°	159.8	5.4
80°-90°	39.8	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	921.6	31.3
0°-40°	1463.8	49.6
0°-60°	2437.1	82.7
0°-90°	2948.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2948.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1248	1248	1248	1248	1248	
5°	1246	1242	1232	1241	1239	118
15°	1185	1179	1159	1158	1150	334
25°	1074	1060	1026	1013	1003	495
35°	926	903	860	833	820	580
45°	758	730	679	641	627	584
55°	575	545	492	450	434	514
65°	389	357	307	270	255	385
75°	207	179	140	119	112	219
85°	52	35	30	29	28	60
90°	0	0	0	0	0	



TEST NUMBER: P334407

CATALOG NUMBER: S125RDS-S850D830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1247.9	1247.9	1247.9	1247.9	1247.9
2.5°	1250.8	1247.9	1238.5	1247.9	1247.0
5°	1246.0	1242.3	1231.9	1241.3	1239.4
7.5°	1236.6	1232.8	1220.6	1228.1	1226.2
10°	1222.5	1219.6	1206.5	1209.3	1206.5
12.5°	1206.5	1202.7	1183.8	1185.7	1181.0
15°	1184.8	1179.1	1159.3	1158.4	1149.9
17.5°	1162.2	1153.7	1130.1	1125.4	1118.8
20°	1134.8	1125.4	1095.2	1090.5	1082.0
22.5°	1104.7	1095.2	1063.2	1052.8	1046.2
25°	1074.5	1060.4	1025.5	1013.2	1002.9
27.5°	1040.6	1023.6	986.8	970.8	960.5
30°	1002.9	985.0	945.4	923.7	915.2
32.5°	966.1	944.4	903.9	879.4	868.1
35°	925.6	903.0	860.5	833.2	820.0
37.5°	886.9	859.6	816.2	784.2	771.0
40°	845.5	817.2	771.9	736.1	724.8
42.5°	802.1	772.9	725.8	691.8	673.9
45°	757.8	730.5	678.6	640.9	626.8
47.5°	711.6	683.3	631.5	592.9	576.8
50°	668.3	637.2	583.4	543.8	529.7
52.5°	621.1	589.1	539.1	495.8	481.6
55°	575.0	544.8	492.0	449.6	434.5
57.5°	527.8	495.8	444.9	403.4	390.2
60°	482.6	449.6	398.7	357.2	343.1
62.5°	434.5	403.4	351.6	313.9	299.7
65°	389.3	357.2	307.3	269.6	255.4
67.5°	344.0	312.0	263.9	228.1	216.8
70°	297.8	265.8	218.7	189.5	178.1
72.5°	252.6	221.5	178.1	151.7	145.2
75°	207.4	179.1	139.5	118.8	112.2
77.5°	161.2	138.6	105.6	89.5	83.9
80°	122.5	99.9	73.5	65.0	63.2
82.5°	84.8	65.0	49.0	46.2	45.2
85°	51.8	34.9	30.2	29.2	28.3
87.5°	21.7	15.1	14.1	14.1	13.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)