

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P334323

Luminaire Tested: **S125DS-S1090D930-4F0-1E-UDD-D**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P334323  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DS-S1090D930-4F0-1E-UDD-D  
Description: DEFINE 5 DIRECT LED LUMINAIRE, DROP SATIN WHITE DIFFUSER  
PENDANT/SURFACE/WALL MOUNT, 1090 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3285.3 lumens  
Efficiency: N/A  
Efficacy: 94.4 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Direct


Input Watts (W): 34.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P334323

CATALOG NUMBER: S125DS-S1090D930-4F0-1E-UDD-D

### Luminous Intensity Polar Plot





TEST NUMBER: P334323

CATALOG NUMBER: S125DS-S1090D930-4F0-1E-UDD-D

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	118	118	118	118	114	114	114	114	108	108	108	102	102	102	96	96	96	94
1	106	101	96	92	103	98	94	90	93	89	86	88	85	82	83	81	79	76
2	96	88	80	74	93	85	78	73	81	75	70	76	72	68	72	69	65	63
3	88	77	68	61	84	75	67	60	71	64	59	67	61	57	64	59	55	53
4	80	68	59	52	77	66	58	51	63	55	50	60	53	48	57	51	47	45
5	74	60	51	44	71	59	50	44	56	49	43	53	47	42	51	45	41	39
6	68	54	45	39	66	53	45	38	51	43	38	48	42	37	46	40	36	34
7	63	49	40	34	61	48	40	34	46	39	33	44	37	33	42	36	32	30
8	59	45	36	30	57	44	36	30	42	35	30	40	34	29	39	33	29	27
9	55	41	33	27	53	40	33	27	39	32	27	37	31	26	36	30	26	24
10	51	38	30	25	50	37	30	25	36	29	24	35	28	24	33	28	23	22

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6849	6849	6849
5°	6875	6814	6862
10°	6839	6784	6825
15°	6771	6729	6743
20°	6674	6638	6660
25°	6557	6535	6527
30°	6412	6412	6420
35°	6279	6312	6337
40°	6144	6206	6259
45°	5992	6144	6220
50°	5850	6080	6226
55°	5678	6052	6228
60°	5492	6030	6271
65°	5307	6053	6356
70°	5104	6067	6558
75°	4774	6278	6927
80°	4370	6843	7851
85°	4239	9478	11789



TEST NUMBER: P334323

CATALOG NUMBER: S125DS-S1090D930-4F0-1E-UDD-D

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	100.4	3.1
10°-20°	284.9	8.7
20°-30°	423.6	12.9
30°-40°	501.7	15.3
40°-50°	518.7	15.8
50°-60°	477.8	14.5
60°-70°	386.2	11.8
70°-80°	258.4	7.9
80°-90°	133.6	4.1
90°-100°	75.2	2.3
100°-110°	55.5	1.7
110°-120°	37.1	1.1
120°-130°	21.0	0.6
130°-140°	9.2	0.3
140°-150°	1.8	0.1
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	808.9	24.6
0°-40°	1310.6	39.9
0°-60°	2307.1	70.2
0°-90°	3085.3	93.9
90°-120°	167.9	5.1
90°-150°	199.9	6.1
90°-180°	200.0	6.1
0°-180°	3285.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1060	1060	1060	1060	1060	
5°	1060	1058	1051	1060	1058	101
15°	1013	1014	1006	1013	1008	285
25°	920	923	917	921	916	424
35°	796	804	801	804	804	499
45°	656	668	673	680	681	506
55°	504	521	538	549	553	451
65°	347	371	396	412	416	345
75°	191	218	252	272	278	203
85°	57	92	128	151	159	60
90°	17	50	85	109	116	12
95°	14	40	76	99	106	11
105°	9	26	57	78	85	10
115°	6	14	40	59	66	6
125°	4	3	24	40	46	4
135°	2	1	8	22	27	2
145°	1	0	0	5	9	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: P334323

CATALOG NUMBER: S125DS-S1090D930-4F0-1E-UDD-D

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1060.5	1060.5	1060.5	1060.5	1060.5
2.5°	1063.6	1061.5	1054.3	1061.5	1060.5
5°	1060.5	1058.4	1051.1	1059.5	1058.4
7.5°	1053.2	1052.2	1044.9	1052.2	1051.1
10°	1042.8	1042.8	1034.5	1041.8	1040.7
12.5°	1028.3	1029.3	1023.1	1028.3	1025.2
15°	1012.7	1013.7	1006.4	1012.7	1008.5
17.5°	992.9	995.0	987.7	992.9	989.8
20°	971.1	973.2	965.9	969.0	969.0
22.5°	946.1	950.3	942.0	946.1	943.0
25°	920.1	923.3	917.0	921.2	916.0
27.5°	892.1	896.2	888.9	892.1	890.0
30°	859.8	866.1	859.8	861.9	860.9
32.5°	830.7	835.9	831.8	833.8	832.8
35°	796.4	803.7	800.6	803.7	803.7
37.5°	763.1	769.4	768.3	772.5	771.5
40°	728.8	737.2	736.1	740.3	742.4
42.5°	691.4	702.8	706.0	711.2	711.2
45°	656.1	667.5	672.7	680.0	681.0
47.5°	619.7	630.1	638.4	648.8	650.9
50°	582.2	593.7	605.1	616.5	619.7
52.5°	542.7	557.3	571.8	584.3	586.4
55°	504.3	520.9	537.5	549.0	553.1
57.5°	464.7	484.5	503.2	515.7	518.8
60°	425.2	446.0	466.8	482.4	485.5
62.5°	386.8	407.6	430.4	448.1	452.3
65°	347.3	371.2	396.1	411.7	415.9
67.5°	310.9	333.7	358.7	377.4	382.6
70°	270.3	294.2	321.3	341.0	347.3
72.5°	230.8	255.8	285.9	307.8	311.9
75°	191.3	218.3	251.6	272.4	277.6
77.5°	152.8	184.0	215.2	238.1	242.3
80°	117.5	148.7	184.0	206.9	211.1
82.5°	85.3	118.5	154.9	176.8	185.1
85°	57.2	91.5	127.9	150.8	159.1
87.5°	36.4	69.7	105.0	128.9	136.2
90°	16.6	49.9	85.3	109.2	116.4
92.5°	14.6	44.7	81.1	104.0	111.2
95°	13.5	40.5	75.9	98.8	106.1
97.5°	12.5	37.4	71.7	93.6	100.9
100°	11.4	33.3	66.5	88.4	94.6
102.5°	10.4	30.2	62.4	83.2	89.4
105°	9.4	26.0	57.2	78.0	85.3
107.5°	8.3	22.9	53.0	73.8	80.1
110°	7.3	19.8	48.9	68.6	75.9



TEST NUMBER: P334323

CATALOG NUMBER: S125DS-S1090D930-4F0-1E-UDD-D

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	7.3	16.6	44.7	63.4	70.7
115°	6.2	13.5	40.5	59.3	65.5
117.5°	5.2	10.4	36.4	54.1	61.3
120°	5.2	8.3	32.2	49.9	56.1
122.5°	4.2	5.2	28.1	44.7	50.9
125°	4.2	3.1	23.9	40.5	45.7
127.5°	3.1	2.1	19.8	35.4	41.6
130°	3.1	2.1	16.6	31.2	36.4
132.5°	2.1	2.1	12.5	27.0	31.2
135°	2.1	1.0	8.3	21.8	27.0
137.5°	2.1	1.0	5.2	17.7	21.8
140°	1.0	1.0	2.1	13.5	17.7
142.5°	1.0	0.0	0.0	9.4	13.5
145°	1.0	0.0	0.0	5.2	9.4
147.5°	0.0	0.0	0.0	2.1	4.2
150°	0.0	0.0	0.0	0.0	1.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)