

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929823

Luminaire Tested: DFN2DS-4P2F0-040DS830-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929823
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P2F0-040DS830-FLL
Description: 2 foot, 90deg - 4way Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3730.3 lumens
Efficiency: N/A
Efficacy: 86.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.07' x L: 2.07' x H: 0')
CIE Type: Direct

Input Watts (W): 43.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929823

CATALOG NUMBER: DFN2DS-4P2F0-040DS830-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P929823

CATALOG NUMBER: DFN2DS-4P2F0-040DS830-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3671	3671	3671
5°	3685	3632	3654
10°	3664	3596	3613
15°	3618	3549	3545
20°	3554	3479	3475
25°	3490	3393	3393
30°	3408	3314	3285
35°	3331	3219	3172
40°	3235	3124	3065
45°	3140	3030	2955
50°	3037	2933	2828
55°	2930	2819	2715
60°	2810	2683	2584
65°	2682	2548	2431
70°	2518	2384	2271
75°	2291	2195	2142
80°	2033	1971	1870
85°	1658	1580	1419

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3140 cd/sqm

TEST NUMBER: P929823

CATALOG NUMBER: DFN2DS-4P2F0-040DS830-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.0	3.7
10°-20°	388.3	10.4
20°-30°	570.6	15.3
30°-40°	662.7	17.8
40°-50°	661.9	17.7
50°-60°	577.1	15.5
60°-70°	426.6	11.4
70°-80°	241.4	6.5
80°-90°	63.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1096.8	29.4
0°-40°	1759.5	47.2
0°-60°	2998.6	80.4
0°-90°	3730.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3730.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1466	1466	1466	1466	1466	
5°	1466	1461	1445	1456	1454	139
15°	1396	1387	1369	1375	1368	393
25°	1263	1252	1228	1231	1228	581
35°	1090	1076	1053	1045	1038	681
45°	887	877	856	840	835	684
55°	671	663	646	629	622	600
65°	453	444	430	417	410	447
75°	237	234	227	218	221	253
85°	58	56	55	51	49	68
90°	0	0	0	0	0	

TEST NUMBER: P929823

CATALOG NUMBER: DFN2DS-4P2F0-040DS830-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1466.1	1466.1	1466.1	1466.1	1466.1
2.5°	1474.7	1467.6	1452.1	1466.1	1463.5
5°	1466.1	1460.6	1445.0	1456.2	1453.6
7.5°	1456.2	1447.9	1432.3	1443.7	1440.9
10°	1440.9	1431.0	1414.1	1425.3	1421.1
12.5°	1419.6	1411.2	1394.3	1401.4	1398.5
15°	1395.7	1387.3	1368.9	1374.6	1367.6
17.5°	1366.1	1357.7	1339.3	1346.3	1339.3
20°	1333.6	1325.2	1305.5	1309.7	1304.2
22.5°	1301.3	1288.6	1270.2	1270.2	1267.4
25°	1263.1	1251.9	1228.0	1230.7	1228.0
27.5°	1220.8	1210.9	1192.8	1188.5	1181.6
30°	1178.6	1167.3	1146.2	1142.0	1136.3
32.5°	1133.5	1125.1	1102.5	1094.0	1088.3
35°	1089.8	1075.8	1053.2	1044.7	1037.6
37.5°	1040.4	1027.7	1005.1	995.3	988.3
40°	989.8	978.4	955.8	943.2	937.6
42.5°	940.4	929.0	906.6	892.4	884.0
45°	886.8	877.0	855.7	840.4	834.6
47.5°	834.6	824.7	802.2	786.7	778.3
50°	779.6	772.5	752.8	733.1	726.0
52.5°	726.0	716.2	697.9	682.4	672.5
55°	671.2	662.6	645.7	628.8	621.8
57.5°	616.1	609.1	590.6	573.8	568.1
60°	561.1	555.5	535.8	520.3	516.0
62.5°	507.5	497.7	483.6	469.5	463.8
65°	452.6	444.1	430.0	417.3	410.3
67.5°	396.2	389.0	376.5	366.6	361.0
70°	344.0	338.4	325.6	315.8	310.2
72.5°	290.5	284.8	277.8	267.9	263.7
75°	236.8	234.1	226.9	218.5	221.4
77.5°	188.9	183.2	180.4	176.2	172.0
80°	141.0	139.5	136.7	132.5	129.7
82.5°	95.9	95.9	94.6	88.8	88.8
85°	57.7	56.4	55.0	50.7	49.4
87.5°	25.4	22.6	19.8	15.5	14.0
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929823

CATALOG NUMBER: DFN2DS-4P2F0-040DS830-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.80	17.41	16.17	17.73	18.04	15.36	16.97	15.72	17.28	17.60
	3H	17.55	19.01	17.93	19.33	19.69	17.06	18.51	17.44	18.84	19.20
	4H	18.20	19.57	18.60	19.91	20.29	17.70	19.07	18.10	19.42	19.80
	6H	18.67	19.94	19.08	20.30	20.69	18.17	19.43	18.58	19.80	20.19
	8H	18.81	20.02	19.23	20.41	20.81	18.31	19.52	18.73	19.91	20.31
	12H	18.90	20.06	19.33	20.44	20.87	18.39	19.55	18.82	19.93	20.36
4H	2H	16.36	17.73	16.76	18.08	18.45	16.01	17.38	16.41	17.73	18.10
	3H	18.34	19.48	18.75	19.88	20.28	17.93	19.08	18.34	19.47	19.87
	4H	19.11	20.15	19.54	20.56	21.00	18.69	19.73	19.12	20.14	20.58
	6H	19.71	20.61	20.16	21.06	21.51	19.28	20.18	19.73	20.62	21.08
	8H	19.90	20.75	20.36	21.19	21.65	19.46	20.31	19.92	20.75	21.22
	12H	20.03	20.79	20.51	21.27	21.74	19.58	20.34	20.06	20.81	21.28
8H	4H	19.39	20.23	19.85	20.68	21.14	19.01	19.86	19.47	20.30	20.77
	6H	20.10	20.80	20.59	21.29	21.77	19.72	20.42	20.21	20.91	21.39
	8H	20.36	20.99	20.87	21.50	21.98	19.97	20.60	20.48	21.11	21.59
	12H	20.56	21.12	21.07	21.61	22.17	20.15	20.70	20.65	21.19	21.76
12H	4H	19.41	20.17	19.89	20.65	21.12	19.05	19.81	19.53	20.28	20.75
	6H	20.15	20.78	20.66	21.28	21.77	19.78	20.41	20.29	20.92	21.40
	8H	20.46	21.02	20.97	21.51	22.07	20.08	20.64	20.59	21.13	21.69