

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929827

Luminaire Tested: DFN2DS-4P2F0-040DS840-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929827
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P2F0-040DS840-FLL
Description: 2 foot, 90deg - 4way Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3963.9 lumens
Efficiency: N/A
Efficacy: 92.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.07' x L: 2.07' x H: 0')
CIE Type: Direct

Input Watts (W): 43.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929827
CATALOG NUMBER: DFN2DS-4P2F0-040DS840-FLL

Luminous Intensity Polar Plot





TEST NUMBER: P929827

CATALOG NUMBER: DFN2DS-4P2F0-040DS840-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86	86	86	86	84
2	99	91	85	79	97	89	83	78	86	81	76	83	78	74	80	76	73	73	73	73	71
3	91	80	72	66	88	79	71	65	76	69	64	73	68	63	71	66	62	62	62	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	54	54	54	54	51
5	77	64	55	49	75	63	55	48	61	53	48	59	52	47	57	51	47	47	47	47	45
6	71	58	49	43	69	57	48	42	55	48	42	53	47	42	52	46	41	41	41	41	39
7	66	52	44	38	64	52	43	38	50	43	37	49	42	37	47	41	37	37	37	37	35
8	61	48	40	34	60	47	39	34	46	39	33	45	38	33	44	38	33	33	33	33	31
9	57	44	36	30	56	43	36	30	42	35	30	41	35	30	40	34	30	30	30	30	28
10	54	41	33	28	53	40	33	28	39	32	27	38	32	27	37	32	27	27	27	27	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3901	3901	3901
5°	3916	3860	3882
10°	3893	3821	3840
15°	3845	3771	3767
20°	3776	3697	3693
25°	3708	3605	3605
30°	3621	3522	3491
35°	3540	3421	3370
40°	3438	3320	3257
45°	3337	3220	3141
50°	3227	3116	3005
55°	3114	2996	2885
60°	2986	2852	2746
65°	2850	2708	2583
70°	2677	2533	2413
75°	2435	2333	2275
80°	2160	2094	1987
85°	1764	1681	1508

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3337 cd/sqm



TEST NUMBER: P929827
 CATALOG NUMBER: DFN2DS-4P2F0-040DS840-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.6	3.7
10°-20°	412.6	10.4
20°-30°	606.3	15.3
30°-40°	704.2	17.8
40°-50°	703.3	17.7
50°-60°	613.3	15.5
60°-70°	453.4	11.4
70°-80°	256.5	6.5
80°-90°	67.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1165.5	29.4
0°-40°	1869.8	47.2
0°-60°	3186.4	80.4
0°-90°	3963.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3963.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1558	1558	1558	1558	1558	
5°	1558	1552	1536	1547	1545	148
15°	1483	1474	1455	1461	1453	418
25°	1342	1330	1305	1308	1305	618
35°	1158	1143	1119	1110	1103	723
45°	942	932	909	893	887	727
55°	713	704	686	668	661	638
65°	481	472	457	443	436	476
75°	252	249	241	232	235	269
85°	61	60	58	54	52	72
90°	0	0	0	0	0	



TEST NUMBER: P929827

CATALOG NUMBER: DFN2DS-4P2F0-040DS840-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1558.0	1558.0	1558.0	1558.0	1558.0
2.5°	1567.1	1559.6	1543.0	1558.0	1555.2
5°	1558.0	1552.1	1535.5	1547.4	1544.6
7.5°	1547.4	1538.5	1522.0	1534.1	1531.1
10°	1531.1	1520.6	1502.7	1514.6	1510.1
12.5°	1508.5	1499.6	1481.7	1489.2	1486.1
15°	1483.1	1474.2	1454.7	1460.7	1453.3
17.5°	1451.7	1442.7	1423.2	1430.6	1423.2
20°	1417.1	1408.2	1387.3	1391.7	1385.9
22.5°	1382.8	1369.3	1349.7	1349.7	1346.7
25°	1342.2	1330.3	1304.9	1307.8	1304.9
27.5°	1297.3	1286.8	1267.5	1263.0	1255.6
30°	1252.5	1240.4	1218.0	1213.5	1207.5
32.5°	1204.5	1195.6	1171.6	1162.6	1156.5
35°	1158.1	1143.1	1119.1	1110.1	1102.6
37.5°	1105.6	1092.1	1068.1	1057.7	1050.1
40°	1051.8	1039.6	1015.6	1002.3	996.3
42.5°	999.3	987.2	963.4	948.2	939.3
45°	942.3	931.9	909.3	893.0	886.9
47.5°	886.9	876.4	852.5	835.9	827.0
50°	828.4	820.9	800.0	779.0	771.5
52.5°	771.5	761.1	741.6	725.1	714.6
55°	713.2	704.1	686.2	668.2	660.8
57.5°	654.7	647.2	627.6	609.7	603.7
60°	596.2	590.3	569.4	552.9	548.3
62.5°	539.3	528.8	513.9	498.9	492.9
65°	481.0	471.9	457.0	443.4	436.0
67.5°	421.0	413.4	400.1	389.6	383.6
70°	365.6	359.6	346.0	335.5	329.6
72.5°	308.7	302.6	295.2	284.7	280.2
75°	251.7	248.7	241.1	232.2	235.2
77.5°	200.7	194.7	191.7	187.2	182.8
80°	149.8	148.2	145.2	140.8	137.8
82.5°	101.9	101.9	100.5	94.4	94.4
85°	61.4	60.0	58.5	53.9	52.5
87.5°	27.0	24.0	21.0	16.5	14.9
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P929827
 CATALOG NUMBER: DFN2DS-4P2F0-040DS840-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.01	17.62	16.38	17.94	18.25	15.57	17.18	15.93	17.49	17.81
	3H	17.76	19.22	18.14	19.54	19.90	17.27	18.73	17.65	19.05	19.41
	4H	18.41	19.78	18.81	20.13	20.50	17.91	19.28	18.31	19.63	20.01
	6H	18.88	20.15	19.29	20.51	20.90	18.38	19.64	18.79	20.01	20.40
	8H	19.02	20.23	19.45	20.62	21.02	18.52	19.73	18.94	20.12	20.52
	12H	19.11	20.27	19.54	20.65	21.08	18.60	19.76	19.03	20.14	20.57
4H	2H	16.57	17.94	16.97	18.29	18.67	16.22	17.59	16.62	17.94	18.31
	3H	18.55	19.69	18.96	20.09	20.49	18.14	19.29	18.55	19.68	20.08
	4H	19.32	20.36	19.76	20.77	21.21	18.90	19.94	19.33	20.35	20.79
	6H	19.92	20.83	20.37	21.27	21.72	19.49	20.39	19.94	20.83	21.29
	8H	20.11	20.96	20.57	21.40	21.86	19.67	20.52	20.13	20.96	21.43
	12H	20.24	21.00	20.72	21.48	21.95	19.79	20.55	20.27	21.03	21.49
8H	4H	19.60	20.44	20.06	20.89	21.35	19.22	20.07	19.68	20.51	20.98
	6H	20.31	21.01	20.81	21.50	21.98	19.93	20.63	20.42	21.12	21.60
	8H	20.57	21.20	21.08	21.71	22.19	20.18	20.81	20.69	21.32	21.80
	12H	20.77	21.33	21.28	21.82	22.38	20.36	20.92	20.86	21.41	21.97
12H	4H	19.62	20.38	20.10	20.86	21.33	19.26	20.02	19.74	20.49	20.96
	6H	20.36	20.99	20.87	21.50	21.98	19.99	20.62	20.50	21.13	21.61
	8H	20.67	21.23	21.18	21.72	22.28	20.29	20.85	20.80	21.34	21.90